

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332761-935

Luminaire Tested: **S124DIW-S575D1050U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332761-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1050U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5756.9 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332761-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332761-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	50	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332761-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	1.4
10°-20°	221.9	3.9
20°-30°	326.6	5.7
30°-40°	379.6	6.6
40°-50°	379.6	6.6
50°-60°	332.1	5.8
60°-70°	246.6	4.3
70°-80°	140.1	2.4
80°-90°	43.8	0.8
90°-100°	39.9	0.7
100°-110°	254.3	4.4
110°-120°	486.6	8.5
120°-130°	617.7	10.7
130°-140°	660.8	11.5
140°-150°	618.0	10.7
150°-160°	498.3	8.7
160°-170°	321.4	5.6
170°-180°	110.8	1.9
0°-30°	627.2	10.9
0°-40°	1006.8	17.5
0°-60°	1718.5	29.9
0°-90°	2149.1	37.3
90°-120°	780.8	13.6
90°-150°	2677.3	46.5
90°-180°	3608.0	62.7
0°-180°	5756.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	3	12	19	24	26	4
95°	48	20	19	24	25	62
105°	263	268	272	278	249	275
115°	490	493	492	494	494	482
125°	689	692	691	693	694	615
135°	855	854	858	859	861	658
145°	986	988	988	989	991	616
155°	1081	1082	1079	1082	1080	498
165°	1140	1136	1136	1142	1135	322
175°	1166	1161	1162	1169	1159	111
180°	1166	1166	1166	1166	1166	



TEST NUMBER: P332761-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.5	14.8	15.1	15.4	15.7	15.9	16.1	16.4	16.5	16.7	17.0
90°	2.6	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3
92.5°	11.0	11.1	11.2	11.4	11.5	12.3	13.9	15.4	17.0	18.5	19.6
95°	48.0	41.4	34.8	28.2	21.6	18.4	18.6	18.8	19.0	19.2	20.3
97.5°	101.9	106.0	110.1	114.3	118.3	109.6	87.9	66.3	44.7	23.0	23.2
100°	143.1	146.5	150.1	153.5	157.0	145.4	118.6	91.9	65.2	38.4	35.1
102.5°	189.2	191.7	194.2	196.8	199.3	198.9	195.4	191.9	188.4	184.9	149.4
105°	262.6	263.7	264.9	266.0	267.3	268.3	269.2	270.3	271.2	272.2	273.9
107.5°	330.8	331.4	331.9	332.5	333.1	334.1	335.4	336.7	338.0	339.3	340.2
110°	376.9	377.5	378.0	378.6	379.2	380.0	381.3	382.4	383.6	384.7	385.1



TEST NUMBER: P332761-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.5	422.6	423.6	424.6	425.7	426.5	427.1	427.6	428.1	428.7	428.6
115°	490.3	490.9	491.5	492.0	492.6	492.8	492.6	492.4	492.2	492.0	492.4
117.5°	552.2	552.9	553.7	554.5	555.3	555.9	556.3	556.7	557.2	557.6	557.5
120°	594.1	594.9	595.6	596.4	597.2	597.4	597.3	597.1	596.8	596.7	597.1
122.5°	633.2	633.6	634.0	634.6	635.0	635.4	635.7	635.9	636.2	636.5	636.7
125°	689.1	689.9	690.7	691.5	692.2	692.4	692.1	691.6	691.3	690.9	691.5
127.5°	742.2	742.4	742.6	742.8	743.0	743.5	744.4	745.3	746.1	747.1	747.0
130°	776.4	776.6	776.8	777.0	777.1	777.6	778.2	778.7	779.3	779.9	780.1
132.5°	807.8	808.1	808.5	808.8	809.2	809.8	810.5	811.2	811.9	812.7	812.9
135°	854.9	854.7	854.5	854.3	854.1	854.5	855.2	856.0	856.8	857.6	857.9
137.5°	896.6	896.6	896.7	896.8	896.9	897.3	898.2	899.1	899.9	900.8	901.2
140°	923.9	924.2	924.6	925.0	925.4	925.7	926.2	926.5	927.0	927.3	927.9
142.5°	948.2	948.9	949.6	950.4	951.1	951.5	951.7	951.9	952.2	952.4	952.9
145°	985.8	986.4	986.9	987.5	988.1	988.3	988.3	988.3	988.3	988.3	988.6
147.5°	1015.5	1016.7	1017.8	1018.8	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8
150°	1037.2	1038.0	1038.8	1039.6	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8
152.5°	1055.3	1056.0	1056.6	1057.2	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9
155°	1080.8	1081.1	1081.2	1081.4	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9
157.5°	1102.3	1102.2	1102.1	1101.9	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8
160°	1114.8	1114.3	1113.7	1113.1	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5
162.5°	1126.0	1125.3	1124.6	1123.8	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0
165°	1140.1	1139.2	1138.2	1137.2	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4
167.5°	1151.3	1150.3	1149.3	1148.3	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0
170°	1157.6	1156.4	1155.3	1154.1	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8
172.5°	1161.7	1160.6	1159.4	1158.3	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0
175°	1166.3	1165.2	1164.0	1162.9	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7
177.5°	1168.4	1167.3	1166.2	1165.2	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P332761-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	17.1	17.4	17.7	17.8	17.8	17.9	18.0	18.1
90°	21.5	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	20.8	22.0	23.2	23.8	23.8	23.9	24.0	24.1
95°	21.5	22.6	23.8	24.5	24.7	24.9	25.1	25.3
97.5°	23.2	23.4	23.5	23.7	23.8	24.0	24.2	24.5
100°	31.8	28.5	25.2	23.7	23.8	24.0	24.2	24.5
102.5°	113.8	78.3	42.7	25.0	25.0	25.1	25.1	25.1
105°	275.7	277.4	279.1	276.6	269.6	262.6	255.6	248.7
107.5°	341.0	341.9	342.8	343.5	344.3	345.0	345.8	346.5
110°	385.5	385.9	386.2	386.8	387.4	387.9	388.5	389.1



TEST NUMBER: P332761-935

CATALOG NUMBER: S124DIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.5	428.4	428.3	428.7	429.5	430.2	430.9	431.6
115°	492.8	493.2	493.5	493.8	493.8	493.8	493.8	493.8
117.5°	557.4	557.4	557.3	557.2	557.2	557.1	557.0	556.9
120°	597.4	597.9	598.2	598.2	597.9	597.4	597.1	596.7
122.5°	637.0	637.1	637.4	637.3	637.0	636.5	636.2	635.8
125°	692.1	692.7	693.2	693.6	693.8	694.0	694.2	694.4
127.5°	746.8	746.7	746.6	746.5	746.3	746.1	746.0	745.9
130°	780.2	780.5	780.7	780.8	780.8	780.8	780.8	780.8
132.5°	813.0	813.3	813.5	813.5	813.3	813.1	813.0	812.9
135°	858.3	858.7	859.1	859.5	859.9	860.2	860.7	861.0
137.5°	901.6	902.1	902.5	902.7	902.5	902.4	902.3	902.2
140°	928.5	929.0	929.6	930.1	930.2	930.4	930.6	930.8
142.5°	953.3	953.7	954.2	954.3	954.4	954.4	954.5	954.5
145°	988.8	988.9	989.1	989.5	989.8	990.2	990.6	991.0
147.5°	1019.9	1020.0	1020.2	1020.4	1020.6	1020.8	1021.0	1021.1
150°	1039.8	1039.8	1039.8	1039.9	1040.1	1040.3	1040.5	1040.7
152.5°	1057.2	1057.5	1057.8	1057.9	1057.8	1057.7	1057.6	1057.5
155°	1080.6	1081.4	1082.2	1082.3	1081.7	1081.2	1080.6	1080.0
157.5°	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8
160°	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4
162.5°	1124.1	1125.3	1126.4	1126.4	1125.1	1123.8	1122.5	1121.1
165°	1138.9	1140.5	1142.0	1141.9	1140.1	1138.4	1136.7	1134.9
167.5°	1149.7	1151.4	1153.1	1153.0	1151.1	1149.1	1147.2	1145.2
170°	1156.3	1157.9	1159.4	1159.3	1157.3	1155.4	1153.4	1151.5
172.5°	1160.5	1162.1	1163.6	1163.4	1161.2	1159.2	1157.1	1154.9
175°	1165.4	1167.2	1169.0	1168.6	1166.3	1164.0	1161.7	1159.3
177.5°	1167.4	1168.6	1169.9	1169.6	1167.7	1165.9	1164.0	1162.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3

(END OF REPORT)