

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332749-935

Luminaire Tested: **S124DIW-S575D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332749-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D470U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3761.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332749-935

CATALOG NUMBER: S124DIW-S575D470U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332749-935

CATALOG NUMBER: S124DIW-S575D470U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	99	95	91	87	92	89	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	83	73	65	59	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332749-935

CATALOG NUMBER: S124DIW-S575D470U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	2.1
10°-20°	221.9	5.9
20°-30°	326.6	8.7
30°-40°	379.6	10.1
40°-50°	379.6	10.1
50°-60°	332.1	8.8
60°-70°	246.6	6.6
70°-80°	140.1	3.7
80°-90°	42.0	1.1
90°-100°	17.8	0.5
100°-110°	113.8	3.0
110°-120°	217.6	5.8
120°-130°	276.3	7.3
130°-140°	295.6	7.9
140°-150°	276.4	7.3
150°-160°	222.9	5.9
160°-170°	143.8	3.8
170°-180°	49.6	1.3
0°-30°	627.2	16.7
0°-40°	1006.8	26.8
0°-60°	1718.5	45.7
0°-90°	2147.2	57.1
90°-120°	349.2	9.3
90°-150°	1197.5	31.8
90°-180°	1614.0	42.9
0°-180°	3761.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	1	5	9	11	12	3
95°	21	9	9	11	11	28
105°	117	120	122	124	111	123
115°	219	220	220	221	221	216
125°	308	310	309	310	311	275
135°	382	382	384	384	385	295
145°	441	442	442	443	443	275
155°	484	484	483	484	483	223
165°	510	508	508	511	508	144
175°	522	520	520	523	519	50
180°	522	522	522	522	522	



TEST NUMBER: P332749-935

CATALOG NUMBER: S124DIW-S575D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.2	14.2	14.3	14.4	14.5	14.5	14.6	14.6	14.6	14.6	14.7
90°	1.2	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1
92.5°	4.9	5.0	5.0	5.1	5.2	5.5	6.2	6.9	7.6	8.3	8.8
95°	21.4	18.5	15.6	12.7	9.6	8.3	8.4	8.4	8.5	8.6	9.1
97.5°	45.5	47.4	49.2	51.1	53.0	49.0	39.3	29.6	20.0	10.3	10.3
100°	64.0	65.5	67.2	68.7	70.3	65.0	53.0	41.1	29.1	17.1	15.7
102.5°	84.6	85.8	86.9	88.0	89.2	88.9	87.4	85.8	84.3	82.7	66.8
105°	117.4	118.0	118.5	119.0	119.5	120.0	120.5	120.9	121.3	121.7	122.5
107.5°	148.0	148.3	148.5	148.8	149.0	149.5	150.0	150.6	151.2	151.8	152.1
110°	168.6	168.8	169.1	169.4	169.6	170.0	170.5	171.1	171.6	172.1	172.3



TEST NUMBER: P332749-935

CATALOG NUMBER: S124DIW-S575D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.6	189.0	189.5	189.9	190.5	190.8	191.1	191.2	191.5	191.7	191.7
115°	219.3	219.6	219.8	220.1	220.3	220.4	220.3	220.2	220.2	220.1	220.2
117.5°	247.0	247.4	247.7	248.1	248.4	248.7	248.8	249.0	249.3	249.4	249.3
120°	265.7	266.0	266.4	266.7	267.1	267.3	267.2	267.1	267.0	266.9	267.1
122.5°	283.2	283.4	283.6	283.9	284.0	284.2	284.3	284.5	284.6	284.7	284.8
125°	308.2	308.6	308.9	309.3	309.6	309.7	309.5	309.4	309.2	309.0	309.3
127.5°	332.0	332.1	332.2	332.3	332.3	332.6	332.9	333.4	333.8	334.2	334.2
130°	347.2	347.3	347.5	347.6	347.7	347.8	348.1	348.4	348.6	348.9	349.0
132.5°	361.4	361.4	361.6	361.8	362.0	362.2	362.6	362.8	363.2	363.5	363.6
135°	382.4	382.3	382.2	382.1	382.0	382.2	382.5	382.9	383.2	383.6	383.7
137.5°	401.1	401.1	401.1	401.1	401.2	401.4	401.7	402.2	402.5	402.9	403.1
140°	413.2	413.4	413.5	413.7	413.9	414.1	414.2	414.5	414.7	414.8	415.1
142.5°	424.1	424.5	424.8	425.1	425.4	425.6	425.7	425.9	425.9	426.0	426.2
145°	440.9	441.2	441.4	441.7	442.0	442.1	442.1	442.1	442.1	442.1	442.2
147.5°	454.3	454.8	455.2	455.7	456.2	456.4	456.3	456.2	456.2	456.1	456.2
150°	464.0	464.3	464.7	465.0	465.4	465.5	465.4	465.3	465.2	465.1	465.1
152.5°	472.1	472.3	472.6	472.9	473.2	473.2	473.1	472.9	472.8	472.6	472.8
155°	483.5	483.5	483.6	483.7	483.8	483.7	483.5	483.2	482.9	482.7	483.0
157.5°	493.1	493.0	492.9	492.9	492.8	492.7	492.4	492.1	491.8	491.5	492.0
160°	498.7	498.4	498.2	497.9	497.7	497.5	497.4	497.3	497.2	497.1	497.7
162.5°	503.7	503.3	503.0	502.7	502.4	502.1	502.0	502.0	501.9	501.8	502.3
165°	510.0	509.5	509.1	508.7	508.2	508.1	508.1	508.1	508.1	508.1	508.8
167.5°	515.0	514.5	514.1	513.7	513.2	512.9	512.9	512.8	512.8	512.7	513.5
170°	517.8	517.3	516.8	516.3	515.7	515.5	515.6	515.7	515.7	515.8	516.5
172.5°	519.7	519.2	518.7	518.1	517.6	517.4	517.5	517.5	517.6	517.7	518.4
175°	521.7	521.2	520.6	520.1	519.6	519.4	519.5	519.6	519.7	519.8	520.6
177.5°	522.6	522.2	521.7	521.2	520.7	520.6	520.6	520.8	520.9	521.1	521.6
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P332749-935

CATALOG NUMBER: S124DIW-S575D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	14.8	14.9	15.0	15.1	15.1	15.2	15.2	15.2
90°	9.6	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	9.3	9.8	10.3	10.6	10.7	10.7	10.8	10.8
95°	9.6	10.2	10.7	10.9	11.0	11.1	11.2	11.3
97.5°	10.4	10.4	10.5	10.6	10.7	10.8	10.8	10.9
100°	14.2	12.7	11.3	10.6	10.7	10.8	10.8	10.9
102.5°	50.9	35.0	19.1	11.2	11.2	11.2	11.2	11.3
105°	123.3	124.1	124.8	123.7	120.5	117.4	114.3	111.2
107.5°	152.6	152.9	153.3	153.7	154.0	154.3	154.6	155.0
110°	172.5	172.6	172.8	173.0	173.2	173.5	173.7	174.0



TEST NUMBER: P332749-935

CATALOG NUMBER: S124DIW-S575D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.7	191.7	191.6	191.7	192.1	192.4	192.8	193.0
115°	220.4	220.6	220.8	220.8	220.8	220.8	220.8	220.8
117.5°	249.3	249.3	249.3	249.3	249.2	249.2	249.2	249.1
120°	267.3	267.4	267.6	267.6	267.4	267.3	267.1	266.9
122.5°	284.9	285.0	285.1	285.1	284.9	284.7	284.6	284.4
125°	309.5	309.8	310.0	310.2	310.3	310.4	310.5	310.6
127.5°	334.1	334.0	334.0	333.9	333.8	333.7	333.7	333.6
130°	349.0	349.1	349.2	349.2	349.2	349.2	349.2	349.2
132.5°	363.7	363.8	363.9	363.9	363.8	363.8	363.7	363.6
135°	383.9	384.1	384.3	384.4	384.6	384.8	385.0	385.1
137.5°	403.3	403.5	403.7	403.7	403.7	403.6	403.6	403.6
140°	415.3	415.6	415.9	416.0	416.1	416.2	416.3	416.4
142.5°	426.4	426.6	426.8	426.9	426.9	427.0	427.0	427.0
145°	442.3	442.4	442.5	442.6	442.7	442.9	443.1	443.2
147.5°	456.2	456.2	456.3	456.4	456.5	456.6	456.7	456.8
150°	465.1	465.1	465.1	465.2	465.3	465.4	465.5	465.5
152.5°	472.9	473.0	473.2	473.2	473.2	473.1	473.0	473.0
155°	483.4	483.7	484.1	484.1	483.9	483.6	483.4	483.1
157.5°	492.4	492.8	493.3	493.3	492.8	492.4	492.0	491.5
160°	498.2	498.7	499.2	499.2	498.7	498.2	497.7	497.1
162.5°	502.8	503.3	503.9	503.9	503.3	502.7	502.0	501.5
165°	509.5	510.1	510.8	510.7	510.0	509.2	508.4	507.6
167.5°	514.3	515.1	515.8	515.7	514.9	514.0	513.2	512.3
170°	517.2	517.9	518.7	518.6	517.6	516.8	515.9	515.1
172.5°	519.1	519.8	520.5	520.4	519.4	518.5	517.5	516.6
175°	521.3	522.1	522.9	522.7	521.7	520.6	519.6	518.6
177.5°	522.2	522.7	523.3	523.1	522.4	521.5	520.6	519.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7

(END OF REPORT)