

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332794-935

Luminaire Tested: **S124DIW-S795D1340U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332794-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1340U935-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7059.8 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	74	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8924	8924	8924	8924
5°	10509	8947	7897	8947
10°	12582	8908	7110	8908
15°	14888	8818	6529	8818
20°	16578	8725	6010	8725
25°	16846	8590	5653	8590
30°	14334	8460	5540	8460
35°	11020	8250	5542	8250
40°	8590	8001	5647	8001
45°	7162	7628	5740	7628
50°	6303	7171	5936	7171
55°	5775	6625	6175	6625
60°	5412	6135	6462	6135
65°	5037	5589	6701	5589
70°	4605	5049	6852	5049
75°	4114	4442	6772	4442
80°	3450	3640	6555	3640
85°	2547	2631	6280	2631



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.7	1.5
10°-20°	331.9	4.7
20°-30°	526.4	7.5
30°-40°	585.8	8.3
40°-50°	533.2	7.6
50°-60°	435.7	6.2
60°-70°	311.1	4.4
70°-80°	171.3	2.4
80°-90°	51.1	0.7
90°-100°	95.2	1.3
100°-110°	282.1	4.0
110°-120°	478.8	6.8
120°-130°	631.3	8.9
130°-140°	709.0	10.0
140°-150°	696.7	9.9
150°-160°	586.0	8.3
160°-170°	389.9	5.5
170°-180°	136.5	1.9
0°-30°	966.0	13.7
0°-40°	1551.8	22.0
0°-60°	2520.7	35.7
0°-90°	3054.1	43.3
90°-120°	856.1	12.1
90°-150°	2893.2	41.0
90°-180°	4006.0	56.7
0°-180°	7059.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1105	1105	1105	1105	1105	
5°	1297	1104	974	1104	1297	132
15°	1781	1055	781	1055	1781	503
25°	1891	964	635	964	1891	834
35°	1118	837	562	837	1118	710
45°	627	668	503	668	627	494
55°	410	471	439	471	410	371
65°	264	293	351	293	264	261
75°	132	142	217	142	132	140
85°	28	28	68	28	28	34
90°	34	3	34	3	34	18
95°	88	67	88	67	88	92
105°	272	260	272	260	272	287
115°	482	487	482	487	482	477
125°	703	709	703	709	703	628
135°	916	914	916	914	916	707
145°	1112	1111	1112	1111	1112	696
155°	1272	1273	1272	1273	1272	585
165°	1382	1386	1382	1386	1382	389
175°	1435	1442	1435	1442	1435	136
180°	1444	1444	1444	1444	1444	



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4
2.5°	1176.5	1176.1	1172.4	1171.7	1169.2	1165.9	1165.1	1159.3	1147.5	1142.0	1140.6
5°	1296.8	1306.0	1294.1	1291.8	1290.4	1275.3	1267.5	1258.4	1237.3	1224.9	1215.3
7.5°	1440.5	1441.5	1436.3	1432.1	1420.5	1407.2	1387.5	1366.4	1341.4	1315.2	1295.5
10°	1534.9	1538.6	1532.7	1531.7	1508.4	1493.7	1464.4	1439.7	1411.3	1379.7	1350.8
12.5°	1634.6	1629.4	1626.4	1606.8	1602.5	1575.8	1541.7	1516.2	1472.5	1436.1	1397.7
15°	1781.3	1771.2	1764.8	1737.8	1724.5	1687.4	1651.2	1623.3	1566.1	1511.6	1470.3
17.5°	1867.3	1877.4	1862.6	1851.5	1817.1	1791.1	1754.2	1695.6	1650.8	1583.1	1531.1
20°	1929.7	1930.5	1922.4	1910.9	1883.9	1850.9	1810.6	1746.5	1692.9	1625.6	1554.2
22.5°	1946.5	1946.7	1943.2	1932.5	1912.0	1885.3	1844.7	1791.1	1726.2	1653.0	1581.7
25°	1891.2	1889.4	1893.5	1905.4	1897.6	1889.4	1866.0	1826.2	1765.7	1688.3	1611.4
27.5°	1685.7	1698.3	1721.6	1750.8	1779.1	1800.6	1806.6	1798.5	1761.0	1697.4	1616.8
30°	1537.7	1553.2	1570.6	1599.9	1656.7	1689.3	1724.9	1752.0	1736.9	1686.0	1610.9
32.5°	1375.0	1378.9	1404.7	1438.0	1490.0	1552.6	1609.2	1664.1	1682.3	1655.6	1593.0
35°	1118.2	1124.6	1152.5	1185.5	1249.2	1325.7	1410.8	1486.9	1549.5	1574.8	1542.7
37.5°	912.5	930.9	950.6	986.1	1042.2	1110.9	1199.5	1297.8	1391.3	1454.0	1464.6
40°	815.1	826.6	840.8	867.7	915.3	983.2	1059.1	1171.8	1271.2	1360.9	1390.3
42.5°	738.1	744.9	753.5	778.0	814.2	881.7	951.1	1050.2	1150.0	1257.2	1306.3
45°	627.3	634.2	648.8	663.1	690.5	737.3	801.8	883.3	983.6	1087.1	1177.8
47.5°	547.3	551.7	560.4	575.6	598.9	629.7	682.3	750.4	843.3	943.7	1040.3
50°	501.9	505.5	512.4	526.2	544.0	571.4	614.5	678.2	751.0	852.2	946.9
52.5°	466.0	467.4	472.5	481.8	496.0	519.1	554.4	607.1	674.8	765.0	859.5
55°	410.3	412.2	416.7	423.6	435.9	450.6	477.6	516.9	576.1	654.4	736.3
57.5°	364.5	365.8	369.6	372.3	382.5	394.3	415.2	443.2	488.0	554.4	627.6
60°	335.2	334.2	338.9	341.1	348.0	358.1	374.1	401.1	440.1	493.6	560.9
62.5°	306.6	305.3	309.2	312.2	316.2	324.8	337.9	359.0	390.6	439.0	497.2
65°	263.7	261.9	264.2	267.9	271.6	276.1	285.8	304.5	329.7	364.5	408.9
67.5°	220.7	222.7	223.0	224.8	227.0	233.2	239.8	253.0	270.8	298.7	336.3
70°	195.1	195.5	197.3	197.3	198.7	204.2	209.7	217.5	234.9	260.5	291.2
72.5°	169.4	171.3	170.7	172.1	173.1	176.8	180.8	188.2	203.0	222.1	248.0
75°	131.9	133.3	133.3	133.7	135.1	136.5	139.7	145.2	155.7	169.9	187.8
77.5°	96.2	96.3	96.9	98.7	98.7	100.8	103.2	107.6	112.8	122.5	133.5
80°	74.2	75.1	74.6	75.6	75.6	77.4	78.3	83.8	86.1	92.5	101.2
82.5°	54.4	55.3	55.2	56.5	57.3	57.6	58.9	61.0	63.4	69.1	72.6
85°	27.5	28.4	27.5	28.4	29.8	30.2	31.6	32.0	33.9	35.3	38.5
87.5°	14.7	15.8	15.7	15.9	16.5	16.7	16.8	16.1	17.3	17.4	18.4
90°	33.5	33.0	32.5	32.0	31.5	30.5	29.0	27.6	26.1	24.5	22.6
92.5°	49.6	49.2	49.0	48.6	48.4	47.8	46.9	46.0	45.1	44.3	42.8
95°	88.3	88.3	88.3	88.3	88.3	87.8	87.1	86.4	85.6	84.9	83.1
97.5°	138.3	138.3	138.3	138.3	138.3	137.8	136.9	136.0	135.1	134.2	132.2
100°	173.1	173.1	173.1	173.1	173.1	172.8	172.4	171.9	171.3	170.8	168.6
102.5°	212.4	212.2	212.0	211.8	211.5	211.1	210.4	209.7	209.1	208.4	206.3
105°	272.4	271.7	271.0	270.2	269.5	268.7	268.0	267.3	266.5	265.8	264.8
107.5°	331.0	331.1	331.1	331.1	331.1	330.9	330.1	329.4	328.7	328.0	328.0
110°	373.0	372.2	371.4	370.7	370.0	369.9	370.3	370.8	371.3	371.9	372.1



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.9	415.7	415.5	415.3	415.3	415.2	415.3	415.4	415.5	415.6	416.0
115°	482.4	482.6	482.8	483.1	483.4	483.6	483.9	484.1	484.4	484.6	485.1
117.5°	545.8	546.3	546.8	547.3	547.8	548.5	549.3	550.2	551.0	551.8	552.2
120°	594.0	593.6	593.1	592.5	592.0	592.5	593.7	595.0	596.2	597.4	598.1
122.5°	634.2	635.2	636.0	636.9	637.8	638.7	639.6	640.3	641.2	642.0	642.4
125°	703.4	704.0	704.5	705.0	705.4	705.9	706.5	707.0	707.4	707.9	708.2
127.5°	767.6	767.9	768.4	768.8	769.1	769.6	770.1	770.6	771.1	771.5	772.0
130°	809.5	810.5	811.5	812.5	813.6	814.2	814.8	815.3	815.7	816.2	816.2
132.5°	854.2	854.6	855.0	855.4	855.8	856.3	856.8	857.2	857.7	858.2	858.4
135°	915.6	916.4	917.1	917.8	918.6	919.2	919.7	920.2	920.8	921.2	921.2
137.5°	980.2	980.0	979.9	979.7	979.6	979.8	980.5	981.1	981.7	982.4	982.0
140°	1019.5	1019.7	1019.9	1020.2	1020.5	1020.7	1021.0	1021.2	1021.5	1021.7	1021.7
142.5°	1058.8	1058.9	1058.9	1058.9	1058.9	1059.0	1059.1	1059.1	1059.2	1059.2	1059.5
145°	1112.2	1112.9	1113.6	1114.4	1115.2	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4
147.5°	1166.2	1166.5	1166.7	1166.9	1167.2	1167.4	1167.6	1167.8	1168.0	1168.2	1168.4
150°	1199.3	1199.5	1199.7	1200.0	1200.2	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1229.6	1230.3	1230.9	1231.6	1232.2	1232.3	1231.7	1231.1	1230.5	1229.9	1229.7
155°	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9	1272.0
157.5°	1309.6	1310.4	1311.2	1312.1	1312.9	1313.0	1312.3	1311.5	1310.8	1310.0	1310.1
160°	1331.0	1332.2	1333.5	1334.7	1335.9	1336.2	1335.5	1334.7	1333.9	1333.3	1333.5
162.5°	1353.3	1354.6	1355.8	1357.0	1358.3	1358.2	1356.9	1355.6	1354.3	1352.9	1353.1
165°	1382.3	1383.4	1384.3	1385.3	1386.4	1386.1	1384.6	1383.1	1381.6	1380.1	1380.6
167.5°	1403.2	1404.7	1406.2	1407.7	1409.3	1409.3	1407.8	1406.4	1404.9	1403.3	1403.3
170°	1414.8	1416.5	1418.2	1420.0	1421.7	1421.9	1420.3	1418.8	1417.4	1415.8	1415.7
172.5°	1424.6	1426.3	1428.1	1429.8	1431.5	1431.6	1429.9	1428.1	1426.5	1424.8	1424.8
175°	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9	1435.1
177.5°	1440.2	1441.8	1443.4	1445.0	1446.6	1446.7	1445.3	1443.9	1442.5	1441.1	1441.1
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4
2.5°	1140.9	1135.8	1132.1	1129.2	1121.2	1116.4	1112.8	1107.6	1101.7	1095.5	1087.8
5°	1205.7	1190.1	1178.7	1161.2	1144.8	1131.0	1116.9	1104.1	1088.5	1071.5	1059.1
7.5°	1273.8	1250.6	1220.9	1195.2	1166.2	1141.0	1118.5	1095.5	1071.4	1048.2	1026.8
10°	1317.0	1287.2	1254.2	1215.3	1178.7	1146.2	1115.9	1086.7	1058.3	1029.8	1005.6
12.5°	1363.5	1326.4	1277.6	1232.2	1191.1	1147.6	1111.2	1075.3	1041.0	1011.2	982.8
15°	1425.9	1372.3	1316.0	1255.2	1201.1	1150.3	1100.4	1055.1	1016.6	977.1	949.7
17.5°	1464.3	1398.0	1333.6	1270.0	1204.6	1140.5	1086.7	1034.3	986.2	947.0	912.4
20°	1489.6	1423.7	1343.5	1279.9	1202.0	1136.1	1073.8	1015.6	965.3	923.6	887.9
22.5°	1511.6	1435.4	1355.2	1271.4	1193.9	1124.0	1055.8	997.3	945.9	902.0	867.7
25°	1523.5	1436.0	1349.0	1265.7	1177.8	1094.8	1033.0	964.4	909.4	863.2	826.6
27.5°	1524.7	1431.2	1332.8	1240.2	1149.4	1072.3	994.2	932.9	875.8	826.9	791.7
30°	1520.7	1423.2	1317.4	1217.1	1126.0	1042.2	974.5	907.6	849.5	800.9	764.2
32.5°	1507.9	1406.4	1297.6	1191.5	1097.1	1015.1	945.1	881.6	824.9	777.1	738.7
35°	1470.8	1370.5	1254.6	1144.4	1047.7	964.8	901.6	837.1	780.3	734.9	697.8
37.5°	1412.8	1322.2	1204.4	1090.2	995.3	912.1	849.5	791.1	739.9	693.8	655.8
40°	1362.3	1282.6	1164.5	1053.2	950.6	871.4	812.8	759.2	708.4	664.9	628.7
42.5°	1304.1	1234.6	1125.7	1007.8	908.9	829.3	772.1	724.0	676.1	635.9	599.8
45°	1200.1	1154.4	1051.8	942.9	839.8	764.7	710.2	668.1	627.8	588.4	558.2
47.5°	1080.7	1058.1	971.7	868.2	770.4	696.4	649.1	610.2	574.9	541.6	514.9
50°	1000.6	989.5	914.9	815.1	721.7	652.0	604.4	571.0	540.8	511.5	486.3
52.5°	921.4	921.0	853.8	762.3	675.9	608.8	561.5	530.4	504.2	480.4	457.7
55°	800.5	813.2	760.6	679.1	601.7	541.2	498.7	470.7	452.5	432.7	415.8
57.5°	689.3	710.6	667.2	595.4	530.8	475.1	438.1	417.1	397.5	385.6	373.3
60°	616.8	637.0	603.0	542.6	481.7	434.1	398.8	380.0	363.1	354.9	346.2
62.5°	552.3	570.3	545.2	489.1	436.3	390.5	360.8	342.7	331.2	322.3	316.5
65°	460.2	475.3	453.8	413.0	367.7	331.1	306.8	292.6	281.6	277.9	271.6
67.5°	372.0	385.7	374.1	339.5	303.2	275.3	256.4	242.8	236.3	233.1	228.5
70°	319.6	333.4	321.0	290.8	262.9	239.5	221.6	213.9	207.0	205.6	199.1
72.5°	275.3	284.6	272.2	248.7	224.7	205.1	191.2	183.0	179.5	177.0	173.6
75°	206.6	214.7	206.6	188.2	171.3	157.6	145.6	142.4	138.3	136.9	134.7
77.5°	146.2	153.3	147.0	135.5	122.9	112.3	105.9	101.8	100.8	98.4	99.5
80°	111.8	116.3	110.4	102.5	92.5	85.2	80.6	78.3	75.6	74.6	76.5
82.5°	80.2	82.2	79.2	74.0	66.5	61.7	58.6	56.0	55.4	55.6	55.6
85°	41.7	41.2	40.7	36.2	33.9	30.7	28.8	28.4	27.9	28.8	29.8
87.5°	18.1	18.0	17.2	15.3	13.7	12.1	11.1	10.2	11.1	12.1	12.9
90°	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4	6.1	8.8	11.5
92.5°	41.4	40.0	38.7	36.4	33.2	30.1	27.0	23.9	27.0	30.1	33.2
95°	81.4	79.6	77.9	75.9	73.7	71.5	69.2	67.0	69.2	71.5	73.7
97.5°	130.2	128.1	126.1	124.2	122.3	120.6	118.8	117.0	118.8	120.6	122.3
100°	166.3	164.1	161.9	160.3	159.3	158.3	157.3	156.4	157.3	158.3	159.3
102.5°	204.3	202.2	200.2	199.0	198.6	198.2	197.9	197.4	197.9	198.2	198.6
105°	263.8	262.8	261.7	261.1	260.9	260.7	260.5	260.2	260.5	260.7	260.9
107.5°	327.8	327.6	327.4	327.3	326.9	326.7	326.3	326.1	326.3	326.7	326.9
110°	372.3	372.6	372.8	372.7	372.2	371.7	371.2	370.7	371.2	371.7	372.2



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.5	417.0	417.4	417.6	417.5	417.3	417.2	417.2	417.2	417.3	417.5
115°	485.6	486.1	486.6	486.8	486.8	486.8	486.8	486.8	486.8	486.8	486.8
117.5°	552.5	552.8	553.2	553.3	553.1	552.9	552.7	552.5	552.7	552.9	553.1
120°	598.9	599.6	600.4	600.2	599.3	598.2	597.3	596.2	597.3	598.2	599.3
122.5°	642.7	643.1	643.4	643.4	643.0	642.7	642.2	641.8	642.2	642.7	643.0
125°	708.4	708.7	708.9	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
127.5°	772.4	772.7	773.2	773.0	772.2	771.5	770.8	770.0	770.8	771.5	772.2
130°	816.2	816.2	816.2	815.9	815.1	814.4	813.6	812.9	813.6	814.4	815.1
132.5°	858.6	858.8	859.0	858.8	858.3	857.7	857.2	856.7	857.2	857.7	858.3
135°	921.2	921.2	921.2	920.5	918.9	917.5	916.0	914.5	916.0	917.5	918.9
137.5°	981.6	981.2	980.9	980.2	979.6	978.9	978.2	977.5	978.2	978.9	979.6
140°	1021.7	1021.7	1021.7	1021.5	1021.0	1020.5	1019.9	1019.5	1019.9	1020.5	1021.0
142.5°	1059.6	1059.8	1060.0	1059.9	1059.4	1058.9	1058.3	1057.9	1058.3	1058.9	1059.4
145°	1116.1	1115.9	1115.6	1115.0	1114.0	1113.0	1112.1	1111.0	1112.1	1113.0	1114.0
147.5°	1168.6	1168.8	1169.0	1168.5	1167.3	1166.1	1164.9	1163.7	1164.9	1166.1	1167.3
150°	1200.3	1200.3	1200.3	1199.9	1198.9	1197.9	1196.9	1195.9	1196.9	1197.9	1198.9
152.5°	1229.4	1229.2	1229.1	1228.6	1228.0	1227.4	1226.8	1226.2	1226.8	1227.4	1228.0
155°	1272.3	1272.6	1272.8	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9
157.5°	1310.1	1310.2	1310.2	1310.4	1310.9	1311.4	1311.8	1312.3	1311.8	1311.4	1310.9
160°	1333.8	1333.9	1334.2	1334.5	1334.7	1335.0	1335.2	1335.5	1335.2	1335.0	1334.7
162.5°	1353.4	1353.7	1353.9	1354.4	1355.0	1355.6	1356.2	1356.9	1356.2	1355.6	1355.0
165°	1381.1	1381.6	1382.2	1382.8	1383.5	1384.2	1385.0	1385.7	1385.0	1384.2	1383.5
167.5°	1403.3	1403.3	1403.2	1403.7	1404.7	1405.8	1406.8	1407.8	1406.8	1405.8	1404.7
170°	1415.4	1415.1	1414.9	1415.4	1416.6	1417.9	1419.1	1420.3	1419.1	1417.9	1416.6
172.5°	1424.7	1424.7	1424.6	1425.1	1426.2	1427.2	1428.2	1429.3	1428.2	1427.2	1426.2
175°	1435.4	1435.6	1435.8	1436.6	1437.9	1439.1	1440.3	1441.6	1440.3	1439.1	1437.9
177.5°	1441.1	1441.1	1441.1	1441.6	1442.6	1443.6	1444.6	1445.5	1444.6	1443.6	1442.6
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4
2.5°	1084.2	1080.9	1076.1	1069.5	1064.0	1058.2	1056.7	1054.5	1058.9	1055.2	1054.1
5°	1048.6	1039.0	1026.7	1012.4	1004.2	992.3	990.0	985.4	980.9	980.4	975.8
7.5°	1011.0	996.9	980.7	966.2	952.8	939.8	931.3	929.4	922.7	918.8	914.2
10°	986.8	969.4	950.6	936.9	921.4	907.6	897.9	892.5	887.9	882.9	878.3
12.5°	958.2	939.7	924.3	909.4	890.9	880.5	864.6	855.1	854.2	854.3	842.4
15°	925.0	906.6	882.9	861.8	851.7	831.6	822.9	811.8	805.0	798.1	792.6
17.5°	887.0	864.2	845.6	821.4	802.2	786.2	774.7	768.1	757.8	748.0	741.0
20°	863.2	838.9	819.2	793.6	772.5	752.8	743.2	734.0	726.3	718.0	710.2
22.5°	839.0	813.6	789.5	764.7	745.0	724.3	715.0	702.5	695.1	690.5	682.8
25°	800.9	773.4	746.0	722.1	702.0	683.6	671.3	661.7	653.4	649.8	644.7
27.5°	759.5	732.2	705.7	678.6	655.7	642.5	632.6	625.3	620.5	615.7	613.5
30°	733.1	704.7	676.3	651.2	630.1	616.8	607.6	602.6	598.9	596.7	594.3
32.5°	706.4	678.4	648.5	625.5	606.7	594.9	587.9	582.8	581.0	580.1	579.4
35°	663.5	635.2	607.6	587.0	569.2	564.6	558.6	555.9	555.0	558.2	559.6
37.5°	622.0	595.6	570.4	550.4	538.7	532.0	529.9	530.1	533.4	536.2	539.5
40°	595.3	569.6	545.9	528.4	517.5	513.3	512.4	514.7	518.3	521.6	525.2
42.5°	569.3	544.0	522.4	506.1	498.4	494.6	495.2	497.5	502.6	506.5	512.0
45°	528.9	507.8	486.7	473.5	467.1	468.0	468.0	472.1	477.2	483.1	489.0
47.5°	490.9	469.7	452.3	441.2	437.8	437.0	439.6	445.0	452.2	459.6	467.9
50°	465.2	445.1	430.0	419.9	416.2	417.6	421.3	426.3	435.0	444.2	452.9
52.5°	439.2	420.9	406.9	397.5	395.0	397.4	401.1	409.1	416.7	426.6	437.1
55°	398.8	383.2	372.3	365.4	364.5	365.8	370.0	378.7	389.7	402.1	412.2
57.5°	358.6	345.6	335.5	330.8	331.2	332.5	339.3	349.7	361.4	374.5	387.5
60°	331.6	319.6	311.4	307.7	308.2	310.9	319.2	328.8	343.5	356.3	370.0
62.5°	305.9	295.4	287.6	284.3	283.6	289.6	297.6	307.5	322.2	336.5	351.3
65°	264.7	256.4	250.0	248.2	249.6	254.2	264.2	277.5	289.9	305.0	320.6
67.5°	224.4	217.6	213.2	214.0	215.7	222.5	230.9	242.3	256.3	272.0	287.4
70°	198.7	192.3	188.6	189.1	191.8	200.1	207.4	218.9	234.0	250.0	262.9
72.5°	172.4	168.2	164.9	166.8	169.5	175.2	184.3	195.8	209.1	224.0	237.5
75°	132.3	132.3	130.5	131.9	136.0	141.5	148.4	160.2	173.6	185.5	196.5
77.5°	98.2	97.2	98.3	100.0	102.4	108.9	116.8	125.3	135.3	147.1	156.3
80°	75.1	75.6	77.8	80.6	81.5	86.5	94.8	102.5	110.4	120.5	129.2
82.5°	56.4	56.9	58.0	61.6	62.4	67.8	73.2	80.9	88.0	94.8	102.0
85°	30.7	30.7	33.0	34.4	36.6	40.3	43.5	48.0	54.5	59.1	66.0
87.5°	14.6	15.1	16.9	18.1	19.5	21.8	22.8	27.1	28.8	31.0	34.5
90°	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6	29.0	30.5	31.5
92.5°	36.4	38.7	40.0	41.4	42.8	44.3	45.1	46.0	46.9	47.8	48.4
95°	75.9	77.9	79.6	81.4	83.1	84.9	85.6	86.4	87.1	87.8	88.3
97.5°	124.2	126.1	128.1	130.2	132.2	134.2	135.1	136.0	136.9	137.8	138.3
100°	160.3	161.9	164.1	166.3	168.6	170.8	171.3	171.9	172.4	172.8	173.1
102.5°	199.0	200.2	202.2	204.3	206.3	208.4	209.1	209.7	210.4	211.1	211.5
105°	261.1	261.7	262.8	263.8	264.8	265.8	266.5	267.3	268.0	268.7	269.5
107.5°	327.3	327.4	327.6	327.8	328.0	328.0	328.7	329.4	330.1	330.9	331.1
110°	372.7	372.8	372.6	372.3	372.1	371.9	371.3	370.8	370.3	369.9	370.0



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	417.6	417.4	417.0	416.5	416.0	415.6	415.5	415.4	415.3	415.2	415.3
115°	486.8	486.6	486.1	485.6	485.1	484.6	484.4	484.1	483.9	483.6	483.4
117.5°	553.3	553.2	552.8	552.5	552.2	551.8	551.0	550.2	549.3	548.5	547.8
120°	600.2	600.4	599.6	598.9	598.1	597.4	596.2	595.0	593.7	592.5	592.0
122.5°	643.4	643.4	643.1	642.7	642.4	642.0	641.2	640.3	639.6	638.7	637.8
125°	709.0	708.9	708.7	708.4	708.2	707.9	707.4	707.0	706.5	705.9	705.4
127.5°	773.0	773.2	772.7	772.4	772.0	771.5	771.1	770.6	770.1	769.6	769.1
130°	815.9	816.2	816.2	816.2	816.2	816.2	815.7	815.3	814.8	814.2	813.6
132.5°	858.8	859.0	858.8	858.6	858.4	858.2	857.7	857.2	856.8	856.3	855.8
135°	920.5	921.2	921.2	921.2	921.2	921.2	920.8	920.2	919.7	919.2	918.6
137.5°	980.2	980.9	981.2	981.6	982.0	982.4	981.7	981.1	980.5	979.8	979.6
140°	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.2	1021.0	1020.7	1020.5
142.5°	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2	1059.1	1059.1	1059.0	1058.9
145°	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4	1116.1	1115.9	1115.6	1115.2
147.5°	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0	1167.8	1167.6	1167.4	1167.2
150°	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.2
152.5°	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5	1231.1	1231.7	1232.3	1232.2
155°	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8
157.5°	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8	1311.5	1312.3	1313.0	1312.9
160°	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9	1334.7	1335.5	1336.2	1335.9
162.5°	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3	1355.6	1356.9	1358.2	1358.3
165°	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6	1383.1	1384.6	1386.1	1386.4
167.5°	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9	1406.4	1407.8	1409.3	1409.3
170°	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4	1418.8	1420.3	1421.9	1421.7
172.5°	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5	1428.1	1429.9	1431.6	1431.5
175°	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8
177.5°	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5	1443.9	1445.3	1446.7	1446.6
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4
2.5°	1053.3	1052.7	1050.1	1049.7	1050.1	1052.7	1053.3	1054.1	1055.2	1058.9	1054.5
5°	973.1	970.8	969.4	974.5	969.4	970.8	973.1	975.8	980.4	980.9	985.4
7.5°	912.5	910.7	906.6	905.4	906.6	910.7	912.5	914.2	918.8	922.7	929.4
10°	873.7	871.8	868.2	867.3	868.2	871.8	873.7	878.3	882.9	887.9	892.5
12.5°	836.3	832.7	831.9	832.8	831.9	832.7	836.3	842.4	854.3	854.2	855.1
15°	786.7	784.9	779.8	781.2	779.8	784.9	786.7	792.6	798.1	805.0	811.8
17.5°	737.8	735.6	729.4	734.9	729.4	735.6	737.8	741.0	748.0	757.8	768.1
20°	707.1	703.4	700.2	699.6	700.2	703.4	707.1	710.2	718.0	726.3	734.0
22.5°	677.7	674.4	674.2	671.1	674.2	674.4	677.7	682.8	690.5	695.1	702.5
25°	641.1	637.9	637.0	634.6	637.0	637.9	641.1	644.7	649.8	653.4	661.7
27.5°	612.9	611.4	609.8	610.4	609.8	611.4	612.9	613.5	615.7	620.5	625.3
30°	595.7	595.3	594.3	594.3	594.3	595.3	595.7	594.3	596.7	598.9	602.6
32.5°	581.4	581.3	581.9	581.9	581.9	581.3	581.4	579.4	580.1	581.0	582.8
35°	561.4	562.7	563.7	562.3	563.7	562.7	561.4	559.6	558.2	555.0	555.9
37.5°	543.3	544.7	546.0	547.5	546.0	544.7	543.3	539.5	536.2	533.4	530.1
40°	529.3	532.5	533.5	535.8	533.5	532.5	529.3	525.2	521.6	518.3	514.7
42.5°	516.2	519.7	522.1	522.5	522.1	519.7	516.2	512.0	506.5	502.6	497.5
45°	495.9	499.6	502.8	502.8	502.8	499.6	495.9	489.0	483.1	477.2	472.1
47.5°	474.9	480.3	483.5	484.3	483.5	480.3	474.9	467.9	459.6	452.2	445.0
50°	460.6	467.1	470.3	472.6	470.3	467.1	460.6	452.9	444.2	435.0	426.3
52.5°	446.8	453.1	457.4	458.7	457.4	453.1	446.8	437.1	426.6	416.7	409.1
55°	422.7	431.8	436.9	438.7	436.9	431.8	422.7	412.2	402.1	389.7	378.7
57.5°	399.9	408.4	414.2	415.6	414.2	408.4	399.9	387.5	374.5	361.4	349.7
60°	382.4	391.5	398.8	400.2	398.8	391.5	382.4	370.0	356.3	343.5	328.8
62.5°	364.4	373.9	380.6	384.1	380.6	373.9	364.4	351.3	336.5	322.2	307.5
65°	333.4	342.9	349.4	350.8	349.4	342.9	333.4	320.6	305.0	289.9	277.5
67.5°	299.5	309.1	313.3	316.0	313.3	309.1	299.5	287.4	272.0	256.3	242.3
70°	275.7	283.4	288.0	290.3	288.0	283.4	275.7	262.9	250.0	234.0	218.9
72.5°	248.6	256.7	262.0	262.4	262.0	256.7	248.6	237.5	224.0	209.1	195.8
75°	207.0	214.3	217.1	217.1	217.1	214.3	207.0	196.5	185.5	173.6	160.2
77.5°	163.8	167.6	171.1	171.8	171.1	167.6	163.8	156.3	147.1	135.3	125.3
80°	136.0	138.3	141.0	141.0	141.0	138.3	136.0	129.2	120.5	110.4	102.5
82.5°	107.5	109.3	112.1	111.8	112.1	109.3	107.5	102.0	94.8	88.0	80.9
85°	65.0	69.1	68.7	67.8	68.7	69.1	65.0	66.0	59.1	54.5	48.0
87.5°	35.7	36.2	37.4	38.2	37.4	36.2	35.7	34.5	31.0	28.8	27.1
90°	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	30.5	29.0	27.6
92.5°	48.6	49.0	49.2	49.6	49.2	49.0	48.6	48.4	47.8	46.9	46.0
95°	88.3	88.3	88.3	88.3	88.3	88.3	88.3	88.3	87.8	87.1	86.4
97.5°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	137.8	136.9	136.0
100°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	172.8	172.4	171.9
102.5°	211.8	212.0	212.2	212.4	212.2	212.0	211.8	211.5	211.1	210.4	209.7
105°	270.2	271.0	271.7	272.4	271.7	271.0	270.2	269.5	268.7	268.0	267.3
107.5°	331.1	331.1	331.1	331.0	331.1	331.1	331.1	331.1	330.9	330.1	329.4
110°	370.7	371.4	372.2	373.0	372.2	371.4	370.7	370.0	369.9	370.3	370.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	415.3	415.5	415.7	415.9	415.7	415.5	415.3	415.3	415.2	415.3	415.4
115°	483.1	482.8	482.6	482.4	482.6	482.8	483.1	483.4	483.6	483.9	484.1
117.5°	547.3	546.8	546.3	545.8	546.3	546.8	547.3	547.8	548.5	549.3	550.2
120°	592.5	593.1	593.6	594.0	593.6	593.1	592.5	592.0	592.5	593.7	595.0
122.5°	636.9	636.0	635.2	634.2	635.2	636.0	636.9	637.8	638.7	639.6	640.3
125°	705.0	704.5	704.0	703.4	704.0	704.5	705.0	705.4	705.9	706.5	707.0
127.5°	768.8	768.4	767.9	767.6	767.9	768.4	768.8	769.1	769.6	770.1	770.6
130°	812.5	811.5	810.5	809.5	810.5	811.5	812.5	813.6	814.2	814.8	815.3
132.5°	855.4	855.0	854.6	854.2	854.6	855.0	855.4	855.8	856.3	856.8	857.2
135°	917.8	917.1	916.4	915.6	916.4	917.1	917.8	918.6	919.2	919.7	920.2
137.5°	979.7	979.9	980.0	980.2	980.0	979.9	979.7	979.6	979.8	980.5	981.1
140°	1020.2	1019.9	1019.7	1019.5	1019.7	1019.9	1020.2	1020.5	1020.7	1021.0	1021.2
142.5°	1058.9	1058.9	1058.9	1058.8	1058.9	1058.9	1058.9	1058.9	1059.0	1059.1	1059.1
145°	1114.4	1113.6	1112.9	1112.2	1112.9	1113.6	1114.4	1115.2	1115.6	1115.9	1116.1
147.5°	1166.9	1166.7	1166.5	1166.2	1166.5	1166.7	1166.9	1167.2	1167.4	1167.6	1167.8
150°	1200.0	1199.7	1199.5	1199.3	1199.5	1199.7	1200.0	1200.2	1200.3	1200.3	1200.3
152.5°	1231.6	1230.9	1230.3	1229.6	1230.3	1230.9	1231.6	1232.2	1232.3	1231.7	1231.1
155°	1274.8	1273.8	1272.8	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8
157.5°	1312.1	1311.2	1310.4	1309.6	1310.4	1311.2	1312.1	1312.9	1313.0	1312.3	1311.5
160°	1334.7	1333.5	1332.2	1331.0	1332.2	1333.5	1334.7	1335.9	1336.2	1335.5	1334.7
162.5°	1357.0	1355.8	1354.6	1353.3	1354.6	1355.8	1357.0	1358.3	1358.2	1356.9	1355.6
165°	1385.3	1384.3	1383.4	1382.3	1383.4	1384.3	1385.3	1386.4	1386.1	1384.6	1383.1
167.5°	1407.7	1406.2	1404.7	1403.2	1404.7	1406.2	1407.7	1409.3	1409.3	1407.8	1406.4
170°	1420.0	1418.2	1416.5	1414.8	1416.5	1418.2	1420.0	1421.7	1421.9	1420.3	1418.8
172.5°	1429.8	1428.1	1426.3	1424.6	1426.3	1428.1	1429.8	1431.5	1431.6	1429.9	1428.1
175°	1440.0	1438.3	1436.6	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3
177.5°	1445.0	1443.4	1441.8	1440.2	1441.8	1443.4	1445.0	1446.6	1446.7	1445.3	1443.9
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4
2.5°	1056.7	1058.2	1064.0	1069.5	1076.1	1080.9	1084.2	1087.8	1095.5	1101.7	1107.6
5°	990.0	992.3	1004.2	1012.4	1026.7	1039.0	1048.6	1059.1	1071.5	1088.5	1104.1
7.5°	931.3	939.8	952.8	966.2	980.7	996.9	1011.0	1026.8	1048.2	1071.4	1095.5
10°	897.9	907.6	921.4	936.9	950.6	969.4	986.8	1005.6	1029.8	1058.3	1086.7
12.5°	864.6	880.5	890.9	909.4	924.3	939.7	958.2	982.8	1011.2	1041.0	1075.3
15°	822.9	831.6	851.7	861.8	882.9	906.6	925.0	949.7	977.1	1016.6	1055.1
17.5°	774.7	786.2	802.2	821.4	845.6	864.2	887.0	912.4	947.0	986.2	1034.3
20°	743.2	752.8	772.5	793.6	819.2	838.9	863.2	887.9	923.6	965.3	1015.6
22.5°	715.0	724.3	745.0	764.7	789.5	813.6	839.0	867.7	902.0	945.9	997.3
25°	671.3	683.6	702.0	722.1	746.0	773.4	800.9	826.6	863.2	909.4	964.4
27.5°	632.6	642.5	655.7	678.6	705.7	732.2	759.5	791.7	826.9	875.8	932.9
30°	607.6	616.8	630.1	651.2	676.3	704.7	733.1	764.2	800.9	849.5	907.6
32.5°	587.9	594.9	606.7	625.5	648.5	678.4	706.4	738.7	777.1	824.9	881.6
35°	558.6	564.6	569.2	587.0	607.6	635.2	663.5	697.8	734.9	780.3	837.1
37.5°	529.9	532.0	538.7	550.4	570.4	595.6	622.0	655.8	693.8	739.9	791.1
40°	512.4	513.3	517.5	528.4	545.9	569.6	595.3	628.7	664.9	708.4	759.2
42.5°	495.2	494.6	498.4	506.1	522.4	544.0	569.3	599.8	635.9	676.1	724.0
45°	468.0	468.0	467.1	473.5	486.7	507.8	528.9	558.2	588.4	627.8	668.1
47.5°	439.6	437.0	437.8	441.2	452.3	469.7	490.9	514.9	541.6	574.9	610.2
50°	421.3	417.6	416.2	419.9	430.0	445.1	465.2	486.3	511.5	540.8	571.0
52.5°	401.1	397.4	395.0	397.5	406.9	420.9	439.2	457.7	480.4	504.2	530.4
55°	370.0	365.8	364.5	365.4	372.3	383.2	398.8	415.8	432.7	452.5	470.7
57.5°	339.3	332.5	331.2	330.8	335.5	345.6	358.6	373.3	385.6	397.5	417.1
60°	319.2	310.9	308.2	307.7	311.4	319.6	331.6	346.2	354.9	363.1	380.0
62.5°	297.6	289.6	283.6	284.3	287.6	295.4	305.9	316.5	322.3	331.2	342.7
65°	264.2	254.2	249.6	248.2	250.0	256.4	264.7	271.6	277.9	281.6	292.6
67.5°	230.9	222.5	215.7	214.0	213.2	217.6	224.4	228.5	233.1	236.3	242.8
70°	207.4	200.1	191.8	189.1	188.6	192.3	198.7	199.1	205.6	207.0	213.9
72.5°	184.3	175.2	169.5	166.8	164.9	168.2	172.4	173.6	177.0	179.5	183.0
75°	148.4	141.5	136.0	131.9	130.5	132.3	132.3	134.7	136.9	138.3	142.4
77.5°	116.8	108.9	102.4	100.0	98.3	97.2	98.2	99.5	98.4	100.8	101.8
80°	94.8	86.5	81.5	80.6	77.8	75.6	75.1	76.5	74.6	75.6	78.3
82.5°	73.2	67.8	62.4	61.6	58.0	56.9	56.4	55.6	55.6	55.4	56.0
85°	43.5	40.3	36.6	34.4	33.0	30.7	30.7	29.8	28.8	27.9	28.4
87.5°	22.8	21.8	19.5	18.1	16.9	15.1	14.6	12.9	12.1	11.1	10.2
90°	26.1	24.5	22.6	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4
92.5°	45.1	44.3	42.8	41.4	40.0	38.7	36.4	33.2	30.1	27.0	23.9
95°	85.6	84.9	83.1	81.4	79.6	77.9	75.9	73.7	71.5	69.2	67.0
97.5°	135.1	134.2	132.2	130.2	128.1	126.1	124.2	122.3	120.6	118.8	117.0
100°	171.3	170.8	168.6	166.3	164.1	161.9	160.3	159.3	158.3	157.3	156.4
102.5°	209.1	208.4	206.3	204.3	202.2	200.2	199.0	198.6	198.2	197.9	197.4
105°	266.5	265.8	264.8	263.8	262.8	261.7	261.1	260.9	260.7	260.5	260.2
107.5°	328.7	328.0	328.0	327.8	327.6	327.4	327.3	326.9	326.7	326.3	326.1
110°	371.3	371.9	372.1	372.3	372.6	372.8	372.7	372.2	371.7	371.2	370.7



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.5	415.6	416.0	416.5	417.0	417.4	417.6	417.5	417.3	417.2	417.2
115°	484.4	484.6	485.1	485.6	486.1	486.6	486.8	486.8	486.8	486.8	486.8
117.5°	551.0	551.8	552.2	552.5	552.8	553.2	553.3	553.1	552.9	552.7	552.5
120°	596.2	597.4	598.1	598.9	599.6	600.4	600.2	599.3	598.2	597.3	596.2
122.5°	641.2	642.0	642.4	642.7	643.1	643.4	643.4	643.0	642.7	642.2	641.8
125°	707.4	707.9	708.2	708.4	708.7	708.9	709.0	709.0	709.0	709.0	709.0
127.5°	771.1	771.5	772.0	772.4	772.7	773.2	773.0	772.2	771.5	770.8	770.0
130°	815.7	816.2	816.2	816.2	816.2	816.2	815.9	815.1	814.4	813.6	812.9
132.5°	857.7	858.2	858.4	858.6	858.8	859.0	858.8	858.3	857.7	857.2	856.7
135°	920.8	921.2	921.2	921.2	921.2	921.2	920.5	918.9	917.5	916.0	914.5
137.5°	981.7	982.4	982.0	981.6	981.2	980.9	980.2	979.6	978.9	978.2	977.5
140°	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.0	1020.5	1019.9	1019.5
142.5°	1059.2	1059.2	1059.5	1059.6	1059.8	1060.0	1059.9	1059.4	1058.9	1058.3	1057.9
145°	1116.4	1116.6	1116.4	1116.1	1115.9	1115.6	1115.0	1114.0	1113.0	1112.1	1111.0
147.5°	1168.0	1168.2	1168.4	1168.6	1168.8	1169.0	1168.5	1167.3	1166.1	1164.9	1163.7
150°	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1199.9	1198.9	1197.9	1196.9	1195.9
152.5°	1230.5	1229.9	1229.7	1229.4	1229.2	1229.1	1228.6	1228.0	1227.4	1226.8	1226.2
155°	1272.8	1271.9	1272.0	1272.3	1272.6	1272.8	1272.9	1272.9	1272.9	1272.9	1272.9
157.5°	1310.8	1310.0	1310.1	1310.1	1310.2	1310.2	1310.4	1310.9	1311.4	1311.8	1312.3
160°	1333.9	1333.3	1333.5	1333.8	1333.9	1334.2	1334.5	1334.7	1335.0	1335.2	1335.5
162.5°	1354.3	1352.9	1353.1	1353.4	1353.7	1353.9	1354.4	1355.0	1355.6	1356.2	1356.9
165°	1381.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.8	1383.5	1384.2	1385.0	1385.7
167.5°	1404.9	1403.3	1403.3	1403.3	1403.3	1403.2	1403.7	1404.7	1405.8	1406.8	1407.8
170°	1417.4	1415.8	1415.7	1415.4	1415.1	1414.9	1415.4	1416.6	1417.9	1419.1	1420.3
172.5°	1426.5	1424.8	1424.8	1424.7	1424.7	1424.6	1425.1	1426.2	1427.2	1428.2	1429.3
175°	1436.6	1434.9	1435.1	1435.4	1435.6	1435.8	1436.6	1437.9	1439.1	1440.3	1441.6
177.5°	1442.5	1441.1	1441.1	1441.1	1441.1	1441.1	1441.6	1442.6	1443.6	1444.6	1445.5
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4
2.5°	1112.8	1116.4	1121.2	1129.2	1132.1	1135.8	1140.9	1140.6	1142.0	1147.5	1159.3
5°	1116.9	1131.0	1144.8	1161.2	1178.7	1190.1	1205.7	1215.3	1224.9	1237.3	1258.4
7.5°	1118.5	1141.0	1166.2	1195.2	1220.9	1250.6	1273.8	1295.5	1315.2	1341.4	1366.4
10°	1115.9	1146.2	1178.7	1215.3	1254.2	1287.2	1317.0	1350.8	1379.7	1411.3	1439.7
12.5°	1111.2	1147.6	1191.1	1232.2	1277.6	1326.4	1363.5	1397.7	1436.1	1472.5	1516.2
15°	1100.4	1150.3	1201.1	1255.2	1316.0	1372.3	1425.9	1470.3	1511.6	1566.1	1623.3
17.5°	1086.7	1140.5	1204.6	1270.0	1333.6	1398.0	1464.3	1531.1	1583.1	1650.8	1695.6
20°	1073.8	1136.1	1202.0	1279.9	1343.5	1423.7	1489.6	1554.2	1625.6	1692.9	1746.5
22.5°	1055.8	1124.0	1193.9	1271.4	1355.2	1435.4	1511.6	1581.7	1653.0	1726.2	1791.1
25°	1033.0	1094.8	1177.8	1265.7	1349.0	1436.0	1523.5	1611.4	1688.3	1765.7	1826.2
27.5°	994.2	1072.3	1149.4	1240.2	1332.8	1431.2	1524.7	1616.8	1697.4	1761.0	1798.5
30°	974.5	1042.2	1126.0	1217.1	1317.4	1423.2	1520.7	1610.9	1686.0	1736.9	1752.0
32.5°	945.1	1015.1	1097.1	1191.5	1297.6	1406.4	1507.9	1593.0	1655.6	1682.3	1664.1
35°	901.6	964.8	1047.7	1144.4	1254.6	1370.5	1470.8	1542.7	1574.8	1549.5	1486.9
37.5°	849.5	912.1	995.3	1090.2	1204.4	1322.2	1412.8	1464.6	1454.0	1391.3	1297.8
40°	812.8	871.4	950.6	1053.2	1164.5	1282.6	1362.3	1390.3	1360.9	1271.2	1171.8
42.5°	772.1	829.3	908.9	1007.8	1125.7	1234.6	1304.1	1306.3	1257.2	1150.0	1050.2
45°	710.2	764.7	839.8	942.9	1051.8	1154.4	1200.1	1177.8	1087.1	983.6	883.3
47.5°	649.1	696.4	770.4	868.2	971.7	1058.1	1080.7	1040.3	943.7	843.3	750.4
50°	604.4	652.0	721.7	815.1	914.9	989.5	1000.6	946.9	852.2	751.0	678.2
52.5°	561.5	608.8	675.9	762.3	853.8	921.0	921.4	859.5	765.0	674.8	607.1
55°	498.7	541.2	601.7	679.1	760.6	813.2	800.5	736.3	654.4	576.1	516.9
57.5°	438.1	475.1	530.8	595.4	667.2	710.6	689.3	627.6	554.4	488.0	443.2
60°	398.8	434.1	481.7	542.6	603.0	637.0	616.8	560.9	493.6	440.1	401.1
62.5°	360.8	390.5	436.3	489.1	545.2	570.3	552.3	497.2	439.0	390.6	359.0
65°	306.8	331.1	367.7	413.0	453.8	475.3	460.2	408.9	364.5	329.7	304.5
67.5°	256.4	275.3	303.2	339.5	374.1	385.7	372.0	336.3	298.7	270.8	253.0
70°	221.6	239.5	262.9	290.8	321.0	333.4	319.6	291.2	260.5	234.9	217.5
72.5°	191.2	205.1	224.7	248.7	272.2	284.6	275.3	248.0	222.1	203.0	188.2
75°	145.6	157.6	171.3	188.2	206.6	214.7	206.6	187.8	169.9	155.7	145.2
77.5°	105.9	112.3	122.9	135.5	147.0	153.3	146.2	133.5	122.5	112.8	107.6
80°	80.6	85.2	92.5	102.5	110.4	116.3	111.8	101.2	92.5	86.1	83.8
82.5°	58.6	61.7	66.5	74.0	79.2	82.2	80.2	72.6	69.1	63.4	61.0
85°	28.8	30.7	33.9	36.2	40.7	41.2	41.7	38.5	35.3	33.9	32.0
87.5°	11.1	12.1	13.7	15.3	17.2	18.0	18.1	18.4	17.4	17.3	16.1
90°	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6
92.5°	27.0	30.1	33.2	36.4	38.7	40.0	41.4	42.8	44.3	45.1	46.0
95°	69.2	71.5	73.7	75.9	77.9	79.6	81.4	83.1	84.9	85.6	86.4
97.5°	118.8	120.6	122.3	124.2	126.1	128.1	130.2	132.2	134.2	135.1	136.0
100°	157.3	158.3	159.3	160.3	161.9	164.1	166.3	168.6	170.8	171.3	171.9
102.5°	197.9	198.2	198.6	199.0	200.2	202.2	204.3	206.3	208.4	209.1	209.7
105°	260.5	260.7	260.9	261.1	261.7	262.8	263.8	264.8	265.8	266.5	267.3
107.5°	326.3	326.7	326.9	327.3	327.4	327.6	327.8	328.0	328.0	328.7	329.4
110°	371.2	371.7	372.2	372.7	372.8	372.6	372.3	372.1	371.9	371.3	370.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	417.2	417.3	417.5	417.6	417.4	417.0	416.5	416.0	415.6	415.5	415.4
115°	486.8	486.8	486.8	486.8	486.6	486.1	485.6	485.1	484.6	484.4	484.1
117.5°	552.7	552.9	553.1	553.3	553.2	552.8	552.5	552.2	551.8	551.0	550.2
120°	597.3	598.2	599.3	600.2	600.4	599.6	598.9	598.1	597.4	596.2	595.0
122.5°	642.2	642.7	643.0	643.4	643.4	643.1	642.7	642.4	642.0	641.2	640.3
125°	709.0	709.0	709.0	709.0	708.9	708.7	708.4	708.2	707.9	707.4	707.0
127.5°	770.8	771.5	772.2	773.0	773.2	772.7	772.4	772.0	771.5	771.1	770.6
130°	813.6	814.4	815.1	815.9	816.2	816.2	816.2	816.2	816.2	815.7	815.3
132.5°	857.2	857.7	858.3	858.8	859.0	858.8	858.6	858.4	858.2	857.7	857.2
135°	916.0	917.5	918.9	920.5	921.2	921.2	921.2	921.2	921.2	920.8	920.2
137.5°	978.2	978.9	979.6	980.2	980.9	981.2	981.6	982.0	982.4	981.7	981.1
140°	1019.9	1020.5	1021.0	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.2
142.5°	1058.3	1058.9	1059.4	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2	1059.1
145°	1112.1	1113.0	1114.0	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4	1116.1
147.5°	1164.9	1166.1	1167.3	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0	1167.8
150°	1196.9	1197.9	1198.9	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1226.8	1227.4	1228.0	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5	1231.1
155°	1272.9	1272.9	1272.9	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8	1273.8
157.5°	1311.8	1311.4	1310.9	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8	1311.5
160°	1335.2	1335.0	1334.7	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9	1334.7
162.5°	1356.2	1355.6	1355.0	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3	1355.6
165°	1385.0	1384.2	1383.5	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6	1383.1
167.5°	1406.8	1405.8	1404.7	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9	1406.4
170°	1419.1	1417.9	1416.6	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4	1418.8
172.5°	1428.2	1427.2	1426.2	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5	1428.1
175°	1440.3	1439.1	1437.9	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6	1438.3
177.5°	1444.6	1443.6	1442.6	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5	1443.9
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4	1105.4
2.5°	1165.1	1165.9	1169.2	1171.7	1172.4	1176.1	1176.5
5°	1267.5	1275.3	1290.4	1291.8	1294.1	1306.0	1296.8
7.5°	1387.5	1407.2	1420.5	1432.1	1436.3	1441.5	1440.5
10°	1464.4	1493.7	1508.4	1531.7	1532.7	1538.6	1534.9
12.5°	1541.7	1575.8	1602.5	1606.8	1626.4	1629.4	1634.6
15°	1651.2	1687.4	1724.5	1737.8	1764.8	1771.2	1781.3
17.5°	1754.2	1791.1	1817.1	1851.5	1862.6	1877.4	1867.3
20°	1810.6	1850.9	1883.9	1910.9	1922.4	1930.5	1929.7
22.5°	1844.7	1885.3	1912.0	1932.5	1943.2	1946.7	1946.5
25°	1866.0	1889.4	1897.6	1905.4	1893.5	1889.4	1891.2
27.5°	1806.6	1800.6	1779.1	1750.8	1721.6	1698.3	1685.7
30°	1724.9	1689.3	1656.7	1599.9	1570.6	1553.2	1537.7
32.5°	1609.2	1552.6	1490.0	1438.0	1404.7	1378.9	1375.0
35°	1410.8	1325.7	1249.2	1185.5	1152.5	1124.6	1118.2
37.5°	1199.5	1110.9	1042.2	986.1	950.6	930.9	912.5
40°	1059.1	983.2	915.3	867.7	840.8	826.6	815.1
42.5°	951.1	881.7	814.2	778.0	753.5	744.9	738.1
45°	801.8	737.3	690.5	663.1	648.8	634.2	627.3
47.5°	682.3	629.7	598.9	575.6	560.4	551.7	547.3
50°	614.5	571.4	544.0	526.2	512.4	505.5	501.9
52.5°	554.4	519.1	496.0	481.8	472.5	467.4	466.0
55°	477.6	450.6	435.9	423.6	416.7	412.2	410.3
57.5°	415.2	394.3	382.5	372.3	369.6	365.8	364.5
60°	374.1	358.1	348.0	341.1	338.9	334.2	335.2
62.5°	337.9	324.8	316.2	312.2	309.2	305.3	306.6
65°	285.8	276.1	271.6	267.9	264.2	261.9	263.7
67.5°	239.8	233.2	227.0	224.8	223.0	222.7	220.7
70°	209.7	204.2	198.7	197.3	197.3	195.5	195.1
72.5°	180.8	176.8	173.1	172.1	170.7	171.3	169.4
75°	139.7	136.5	135.1	133.7	133.3	133.3	131.9
77.5°	103.2	100.8	98.7	98.7	96.9	96.3	96.2
80°	78.3	77.4	75.6	75.6	74.6	75.1	74.2
82.5°	58.9	57.6	57.3	56.5	55.2	55.3	54.4
85°	31.6	30.2	29.8	28.4	27.5	28.4	27.5
87.5°	16.8	16.7	16.5	15.9	15.7	15.8	14.7
90°	29.0	30.5	31.5	32.0	32.5	33.0	33.5
92.5°	46.9	47.8	48.4	48.6	49.0	49.2	49.6
95°	87.1	87.8	88.3	88.3	88.3	88.3	88.3
97.5°	136.9	137.8	138.3	138.3	138.3	138.3	138.3
100°	172.4	172.8	173.1	173.1	173.1	173.1	173.1
102.5°	210.4	211.1	211.5	211.8	212.0	212.2	212.4
105°	268.0	268.7	269.5	270.2	271.0	271.7	272.4
107.5°	330.1	330.9	331.1	331.1	331.1	331.1	331.0
110°	370.3	369.9	370.0	370.7	371.4	372.2	373.0



TEST NUMBER: P332794-935

CATALOG NUMBER: S124DIW-S795D1340U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	415.3	415.2	415.3	415.3	415.5	415.7	415.9
115°	483.9	483.6	483.4	483.1	482.8	482.6	482.4
117.5°	549.3	548.5	547.8	547.3	546.8	546.3	545.8
120°	593.7	592.5	592.0	592.5	593.1	593.6	594.0
122.5°	639.6	638.7	637.8	636.9	636.0	635.2	634.2
125°	706.5	705.9	705.4	705.0	704.5	704.0	703.4
127.5°	770.1	769.6	769.1	768.8	768.4	767.9	767.6
130°	814.8	814.2	813.6	812.5	811.5	810.5	809.5
132.5°	856.8	856.3	855.8	855.4	855.0	854.6	854.2
135°	919.7	919.2	918.6	917.8	917.1	916.4	915.6
137.5°	980.5	979.8	979.6	979.7	979.9	980.0	980.2
140°	1021.0	1020.7	1020.5	1020.2	1019.9	1019.7	1019.5
142.5°	1059.1	1059.0	1058.9	1058.9	1058.9	1058.9	1058.8
145°	1115.9	1115.6	1115.2	1114.4	1113.6	1112.9	1112.2
147.5°	1167.6	1167.4	1167.2	1166.9	1166.7	1166.5	1166.2
150°	1200.3	1200.3	1200.2	1200.0	1199.7	1199.5	1199.3
152.5°	1231.7	1232.3	1232.2	1231.6	1230.9	1230.3	1229.6
155°	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9
157.5°	1312.3	1313.0	1312.9	1312.1	1311.2	1310.4	1309.6
160°	1335.5	1336.2	1335.9	1334.7	1333.5	1332.2	1331.0
162.5°	1356.9	1358.2	1358.3	1357.0	1355.8	1354.6	1353.3
165°	1384.6	1386.1	1386.4	1385.3	1384.3	1383.4	1382.3
167.5°	1407.8	1409.3	1409.3	1407.7	1406.2	1404.7	1403.2
170°	1420.3	1421.9	1421.7	1420.0	1418.2	1416.5	1414.8
172.5°	1429.9	1431.6	1431.5	1429.8	1428.1	1426.3	1424.6
175°	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9
177.5°	1445.3	1446.7	1446.6	1445.0	1443.4	1441.8	1440.2
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8

(END OF REPORT)