

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333089-830

Luminaire Tested: **S124RDIW-S1020D1340U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333089-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1340U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8993.0 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333089-830

CATALOG NUMBER: S124RDIW-S1020D1340U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333089-830

CATALOG NUMBER: S124RDIW-S1020D1340U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P333089-830

CATALOG NUMBER: S124RDIW-S1020D1340U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	1.8
10°-20°	445.8	5.0
20°-30°	643.8	7.2
30°-40°	729.7	8.1
40°-50°	704.7	7.8
50°-60°	586.0	6.5
60°-70°	404.6	4.5
70°-80°	205.1	2.3
80°-90°	57.3	0.6
90°-100°	55.9	0.6
100°-110°	356.4	4.0
110°-120°	681.9	7.6
120°-130°	865.6	9.6
130°-140°	926.1	10.3
140°-150°	866.0	9.6
150°-160°	698.4	7.8
160°-170°	450.5	5.0
170°-180°	155.3	1.7
0°-30°	1249.5	13.9
0°-40°	1979.2	22.0
0°-60°	3269.8	36.4
0°-90°	3936.9	43.8
90°-120°	1094.2	12.2
90°-150°	3752.0	41.7
90°-180°	5056.0	56.2
0°-180°	8993.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	4	17	27	34	37	7
95°	67	28	27	34	35	86
105°	368	375	381	389	348	385
115°	687	690	690	692	692	676
125°	966	970	968	972	973	862
135°	1198	1197	1202	1204	1207	923
145°	1382	1385	1385	1386	1389	863
155°	1515	1516	1512	1517	1514	698
165°	1598	1592	1592	1600	1590	451
175°	1635	1628	1628	1638	1625	156
180°	1635	1635	1635	1635	1635	



TEST NUMBER: P333089-830

CATALOG NUMBER: S124RDIW-S1020D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.7	23.5	22.2	20.9	19.7	19.1	19.3	19.6	19.8	20.0	20.1
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	15.4	15.6	15.7	15.9	16.0	17.2	19.4	21.6	23.8	25.9	27.5
95°	67.2	58.0	48.7	39.5	30.3	25.8	26.1	26.4	26.6	26.9	28.6
97.5°	142.8	148.5	154.3	160.0	165.8	153.5	123.2	92.9	62.6	32.2	32.4
100°	200.5	205.4	210.3	215.2	220.1	203.8	166.3	128.8	91.2	53.8	49.2
102.5°	265.0	268.6	272.2	275.8	279.4	278.7	273.8	269.0	264.1	259.2	209.3
105°	368.0	369.6	371.3	372.9	374.5	376.0	377.4	378.7	380.0	381.4	383.9
107.5°	463.5	464.4	465.2	466.0	466.8	468.2	470.0	471.8	473.7	475.6	476.7
110°	528.1	529.0	529.8	530.6	531.4	532.6	534.2	535.8	537.5	539.1	539.7



TEST NUMBER: P333089-830

CATALOG NUMBER: S124RDIW-S1020D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	590.7	592.2	593.7	595.1	596.6	597.7	598.5	599.3	600.0	600.8	600.7
115°	687.0	687.9	688.7	689.5	690.3	690.6	690.3	690.0	689.8	689.5	690.0
117.5°	773.8	775.0	776.0	777.1	778.2	779.0	779.7	780.2	780.8	781.5	781.4
120°	832.5	833.6	834.7	835.8	836.9	837.3	837.1	836.8	836.5	836.2	836.8
122.5°	887.3	888.0	888.6	889.3	889.9	890.4	890.8	891.2	891.6	891.9	892.3
125°	965.8	966.9	968.0	969.0	970.2	970.4	969.9	969.3	968.7	968.3	969.0
127.5°	1040.1	1040.4	1040.7	1040.9	1041.2	1042.0	1043.2	1044.4	1045.8	1047.0	1046.8
130°	1088.1	1088.4	1088.6	1088.8	1089.1	1089.7	1090.5	1091.3	1092.1	1093.0	1093.3
132.5°	1132.1	1132.6	1133.0	1133.5	1134.0	1134.8	1135.9	1136.8	1137.8	1138.9	1139.2
135°	1198.1	1197.8	1197.5	1197.3	1197.0	1197.4	1198.4	1199.6	1200.7	1201.7	1202.3
137.5°	1256.5	1256.6	1256.7	1256.9	1257.0	1257.6	1258.8	1260.0	1261.2	1262.3	1263.0
140°	1294.7	1295.2	1295.7	1296.3	1296.8	1297.4	1297.9	1298.4	1299.0	1299.6	1300.3
142.5°	1328.9	1329.8	1330.9	1331.8	1332.8	1333.4	1333.8	1334.1	1334.5	1334.7	1335.4
145°	1381.5	1382.2	1383.1	1383.9	1384.7	1385.2	1385.2	1385.2	1385.2	1385.2	1385.4
147.5°	1423.2	1424.7	1426.3	1427.9	1429.4	1430.0	1429.7	1429.5	1429.2	1428.9	1429.1
150°	1453.6	1454.7	1455.8	1456.9	1457.9	1458.3	1458.1	1457.8	1457.5	1457.3	1457.3
152.5°	1479.0	1479.9	1480.7	1481.6	1482.5	1482.7	1482.2	1481.7	1481.2	1480.7	1481.2
155°	1514.8	1514.9	1515.2	1515.5	1515.8	1515.5	1514.8	1513.9	1513.1	1512.3	1513.3
157.5°	1544.8	1544.6	1544.5	1544.3	1544.2	1543.6	1542.7	1541.7	1540.9	1539.9	1541.3
160°	1562.4	1561.6	1560.8	1559.9	1559.2	1558.6	1558.3	1558.0	1557.7	1557.6	1559.2
162.5°	1578.0	1577.0	1576.0	1575.0	1574.0	1573.3	1573.0	1572.7	1572.4	1572.2	1573.8
165°	1597.9	1596.5	1595.2	1593.7	1592.4	1591.8	1591.8	1591.8	1591.8	1591.8	1593.9
167.5°	1613.5	1612.1	1610.7	1609.3	1607.9	1607.0	1606.9	1606.8	1606.6	1606.4	1608.8
170°	1622.3	1620.7	1619.0	1617.4	1615.8	1615.1	1615.3	1615.6	1615.9	1616.2	1618.3
172.5°	1628.1	1626.5	1624.9	1623.2	1621.6	1621.0	1621.3	1621.6	1621.7	1622.0	1624.2
175°	1634.6	1632.9	1631.3	1629.7	1628.0	1627.3	1627.6	1627.9	1628.1	1628.4	1630.9
177.5°	1637.5	1636.0	1634.4	1632.9	1631.4	1630.8	1631.3	1631.7	1632.1	1632.6	1634.3
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333089-830

CATALOG NUMBER: S124RDIW-S1020D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	20.2	20.3	20.4	20.5	20.9	21.2	21.6	22.0
90°	30.2	31.8	33.5	34.5	35.1	35.6	36.1	36.7
92.5°	29.2	30.8	32.4	33.3	33.5	33.6	33.6	33.7
95°	30.2	31.8	33.5	34.4	34.6	34.9	35.2	35.4
97.5°	32.6	32.8	32.9	33.2	33.5	33.6	33.9	34.2
100°	44.6	40.0	35.3	33.2	33.5	33.6	33.9	34.2
102.5°	159.6	109.7	59.9	35.0	35.1	35.1	35.2	35.3
105°	386.3	388.8	391.2	387.6	377.8	368.0	358.2	348.5
107.5°	478.0	479.2	480.3	481.5	482.5	483.5	484.6	485.6
110°	540.3	540.7	541.3	542.0	542.8	543.7	544.4	545.3



TEST NUMBER: P333089-830

CATALOG NUMBER: S124RDIW-S1020D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	600.5	600.4	600.3	600.8	601.8	602.9	603.9	604.9
115°	690.6	691.2	691.6	691.9	691.9	691.9	691.9	691.9
117.5°	781.2	781.1	781.0	780.9	780.8	780.7	780.6	780.4
120°	837.3	837.8	838.4	838.4	837.8	837.3	836.8	836.2
122.5°	892.6	893.0	893.2	893.2	892.6	892.0	891.6	891.0
125°	969.9	970.7	971.5	972.0	972.3	972.6	972.9	973.2
127.5°	1046.7	1046.5	1046.3	1046.1	1045.9	1045.7	1045.5	1045.3
130°	1093.4	1093.7	1094.0	1094.2	1094.2	1094.2	1094.2	1094.2
132.5°	1139.4	1139.7	1140.0	1140.0	1139.8	1139.6	1139.3	1139.2
135°	1202.9	1203.3	1203.9	1204.5	1205.0	1205.5	1206.1	1206.6
137.5°	1263.6	1264.1	1264.8	1265.0	1264.8	1264.7	1264.5	1264.3
140°	1301.2	1302.0	1302.8	1303.3	1303.6	1303.9	1304.2	1304.5
142.5°	1336.0	1336.5	1337.2	1337.5	1337.6	1337.6	1337.7	1337.7
145°	1385.6	1385.9	1386.2	1386.7	1387.1	1387.7	1388.3	1388.8
147.5°	1429.4	1429.6	1429.7	1430.0	1430.3	1430.6	1430.8	1431.1
150°	1457.3	1457.3	1457.3	1457.4	1457.6	1457.9	1458.2	1458.5
152.5°	1481.6	1482.1	1482.4	1482.6	1482.4	1482.2	1482.1	1482.0
155°	1514.5	1515.5	1516.6	1516.7	1516.0	1515.1	1514.3	1513.5
157.5°	1542.8	1544.2	1545.6	1545.6	1544.2	1542.8	1541.3	1539.9
160°	1560.8	1562.4	1564.1	1564.1	1562.4	1560.8	1559.2	1557.6
162.5°	1575.5	1577.1	1578.7	1578.6	1576.8	1574.9	1573.0	1571.2
165°	1596.1	1598.3	1600.4	1600.2	1597.9	1595.4	1593.0	1590.5
167.5°	1611.2	1613.5	1616.0	1615.8	1613.1	1610.3	1607.7	1605.0
170°	1620.5	1622.7	1624.8	1624.6	1621.9	1619.2	1616.5	1613.7
172.5°	1626.4	1628.6	1630.8	1630.4	1627.4	1624.5	1621.6	1618.6
175°	1633.3	1635.8	1638.2	1637.8	1634.6	1631.3	1628.0	1624.8
177.5°	1636.1	1637.8	1639.6	1639.1	1636.4	1633.9	1631.3	1628.6
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6

(END OF REPORT)