

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332803-935

Luminaire Tested: **S124DIW-S795D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332803-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1560U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8307.9 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332803-935

CATALOG NUMBER: S124DIW-S795D1560U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332803-935

CATALOG NUMBER: S124DIW-S795D1560U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	94	90	86	83	85	82	78	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	32	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9227	9227	9227
5°	9255	9143	9210
10°	9197	9069	9114
15°	9086	8940	8964
20°	8937	8781	8789
25°	8769	8598	8573
30°	8563	8383	8307
35°	8348	8159	8051
40°	8126	7904	7759
45°	7895	7654	7507
50°	7637	7430	7200
55°	7361	7142	6909
60°	7083	6817	6610
65°	6770	6508	6245
70°	6420	6097	5858
75°	5883	5599	5459
80°	5235	5026	4895
85°	4576	4409	4326



TEST NUMBER: P332803-935

CATALOG NUMBER: S124DIW-S795D1560U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.6	1.3
10°-20°	303.3	3.7
20°-30°	446.4	5.4
30°-40°	518.9	6.2
40°-50°	518.9	6.2
50°-60°	453.9	5.5
60°-70°	337.1	4.1
70°-80°	191.5	2.3
80°-90°	60.3	0.7
90°-100°	59.4	0.7
100°-110°	378.6	4.6
110°-120°	724.2	8.7
120°-130°	919.3	11.1
130°-140°	983.6	11.8
140°-150°	919.8	11.1
150°-160°	741.8	8.9
160°-170°	478.4	5.8
170°-180°	164.9	2.0
0°-30°	857.3	10.3
0°-40°	1376.2	16.6
0°-60°	2349.1	28.3
0°-90°	2938.0	35.4
90°-120°	1162.1	14.0
90°-150°	3984.9	48.0
90°-180°	5370.0	64.6
0°-180°	8307.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1143	1143	1143	1143	1143	
5°	1142	1138	1128	1138	1136	108
15°	1087	1083	1070	1075	1072	306
25°	984	978	965	966	962	453
35°	847	840	828	822	817	529
45°	692	685	670	661	658	533
55°	523	520	507	497	491	468
65°	354	350	341	332	327	351
75°	189	184	180	176	175	200
85°	49	49	48	48	47	54
90°	4	18	29	36	39	6
95°	71	30	29	36	38	92
105°	391	399	405	414	370	409
115°	730	733	732	735	735	718
125°	1026	1030	1028	1032	1034	915
135°	1272	1272	1276	1279	1282	980
145°	1467	1471	1471	1472	1475	916
155°	1609	1610	1606	1611	1608	741
165°	1697	1691	1691	1700	1689	479
175°	1736	1729	1730	1740	1726	165
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P332803-935

CATALOG NUMBER: S124DIW-S795D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1145.9	1145.4	1144.9	1144.4	1143.9	1142.8	1141.0	1139.2	1137.4	1135.7	1137.2
5°	1142.0	1141.3	1140.4	1139.6	1138.8	1137.2	1135.0	1132.7	1130.5	1128.3	1130.5
7.5°	1131.4	1130.6	1129.8	1128.9	1128.2	1126.5	1124.0	1121.5	1119.0	1116.5	1118.4
10°	1121.9	1121.1	1120.2	1119.5	1118.6	1116.9	1114.2	1111.6	1109.0	1106.3	1107.9
12.5°	1109.4	1108.6	1107.8	1107.0	1106.2	1104.3	1101.6	1098.7	1096.0	1093.1	1094.9
15°	1087.1	1086.2	1085.5	1084.6	1083.8	1081.9	1078.8	1075.8	1072.7	1069.7	1070.9
17.5°	1060.1	1059.1	1058.1	1057.1	1056.1	1054.1	1051.3	1048.4	1045.4	1042.6	1043.4
20°	1040.3	1039.3	1038.4	1037.3	1036.3	1034.2	1031.2	1028.1	1025.1	1022.1	1022.7
22.5°	1019.2	1017.8	1016.4	1015.1	1013.7	1011.6	1008.5	1005.5	1002.4	999.4	1000.5
25°	984.5	983.1	981.6	980.2	978.8	976.6	973.8	970.9	968.1	965.3	965.4
27.5°	944.9	943.5	942.0	940.6	939.1	937.0	934.4	931.8	929.1	926.4	925.9
30°	918.6	917.0	915.3	913.7	912.1	909.9	907.2	904.7	902.0	899.3	898.5
32.5°	890.7	889.2	887.8	886.3	884.8	882.7	879.9	877.1	874.3	871.5	870.6
35°	847.1	845.7	844.3	842.8	841.5	839.3	836.5	833.6	830.8	827.9	826.5
37.5°	801.2	799.9	798.6	797.3	795.9	793.8	790.7	787.6	784.6	781.5	780.0
40°	771.1	769.5	767.8	766.2	764.6	762.2	759.2	756.1	753.1	750.0	748.0
42.5°	738.9	737.9	736.9	736.0	734.9	732.8	729.4	726.1	722.6	719.3	717.0
45°	691.5	690.0	688.6	687.2	685.8	683.4	680.2	676.9	673.6	670.4	668.1
47.5°	641.8	640.8	639.9	638.9	637.9	635.9	632.9	629.9	626.9	623.9	621.3
50°	608.1	607.3	606.5	605.6	604.9	603.0	600.2	597.4	594.4	591.6	588.8
52.5°	575.1	574.2	573.2	572.2	571.2	569.2	566.2	563.2	560.2	557.2	554.7
55°	523.0	522.3	521.7	521.1	520.5	518.8	515.9	513.1	510.2	507.4	504.9
57.5°	473.1	472.4	471.7	471.1	470.4	468.6	465.8	463.0	460.2	457.4	455.0
60°	438.7	437.6	436.6	435.7	434.6	432.7	430.2	427.5	424.8	422.2	420.3
62.5°	405.0	404.2	403.3	402.4	401.6	399.8	396.9	394.1	391.3	388.5	386.8
65°	354.4	353.4	352.4	351.4	350.3	348.8	346.8	344.7	342.7	340.7	338.6
67.5°	303.5	302.6	301.6	300.7	299.8	298.3	296.4	294.4	292.5	290.5	288.5
70°	272.0	270.6	269.1	267.7	266.3	264.8	263.1	261.5	259.8	258.3	256.7
72.5°	238.3	236.9	235.5	234.0	232.6	231.3	230.0	228.6	227.3	226.0	224.7
75°	188.6	187.6	186.7	185.6	184.6	183.6	182.5	181.5	180.6	179.5	178.7
77.5°	141.2	140.8	140.3	139.9	139.4	138.8	137.8	137.0	136.0	135.2	134.9
80°	112.6	112.0	111.4	110.8	110.2	109.7	109.3	108.9	108.5	108.1	107.6
82.5°	84.8	84.6	84.2	83.9	83.7	83.5	83.4	83.3	83.3	83.2	82.9
85°	49.4	49.4	49.4	49.4	49.4	49.2	48.8	48.5	48.0	47.6	47.6
87.5°	19.8	20.3	20.8	21.3	21.7	22.1	22.4	22.7	23.0	23.3	23.7
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	16.4	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3
95°	71.4	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3
97.5°	151.6	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4
100°	212.9	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3
102.5°	281.5	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3
105°	390.8	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7
107.5°	492.3	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4
110°	560.9	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2



TEST NUMBER: P332803-935

CATALOG NUMBER: S124DIW-S795D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	627.4	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9
115°	729.7	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9
117.5°	821.9	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8
120°	884.2	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7
122.5°	942.4	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7
125°	1025.8	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2
127.5°	1104.7	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8
130°	1155.6	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1
132.5°	1202.3	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9
135°	1272.5	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9
137.5°	1334.6	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4
140°	1375.0	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1
142.5°	1411.4	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2
145°	1467.2	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4
147.5°	1511.7	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9
150°	1543.9	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7
152.5°	1570.8	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1
155°	1608.8	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3
157.5°	1640.7	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0
160°	1659.4	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0
162.5°	1676.0	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5
165°	1697.0	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8
167.5°	1713.6	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7
170°	1723.0	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8
172.5°	1729.2	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0
175°	1735.9	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1
177.5°	1739.1	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P332803-935

CATALOG NUMBER: S124DIW-S795D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1138.8	1140.5	1142.1	1142.9	1142.7	1142.5	1142.4	1142.2
5°	1132.7	1135.0	1137.2	1138.2	1137.7	1137.4	1137.0	1136.5
7.5°	1120.2	1122.0	1123.7	1124.5	1124.3	1124.0	1123.8	1123.5
10°	1109.6	1111.2	1112.8	1113.4	1113.0	1112.6	1112.2	1111.8
12.5°	1096.7	1098.5	1100.3	1100.9	1100.4	1099.8	1099.2	1098.6
15°	1072.1	1073.3	1074.5	1074.9	1074.3	1073.7	1073.1	1072.5
17.5°	1044.1	1044.9	1045.7	1045.9	1045.4	1045.0	1044.7	1044.2
20°	1023.3	1023.9	1024.5	1024.6	1024.2	1023.8	1023.4	1023.0
22.5°	1001.5	1002.6	1003.8	1003.9	1003.2	1002.5	1001.7	1001.0
25°	965.7	965.9	966.1	965.8	965.0	964.1	963.4	962.5
27.5°	925.5	925.0	924.5	923.8	922.7	921.7	920.7	919.6
30°	897.7	896.9	896.0	895.2	894.1	893.1	892.1	891.1
32.5°	869.5	868.6	867.6	866.6	865.6	864.5	863.5	862.5
35°	825.1	823.6	822.2	821.0	819.9	819.0	817.9	816.9
37.5°	778.4	776.9	775.4	774.0	772.6	771.3	769.9	768.5
40°	746.0	744.0	741.9	740.4	739.3	738.4	737.4	736.3
42.5°	714.5	712.2	709.8	708.3	707.7	707.0	706.3	705.6
45°	665.9	663.7	661.4	660.0	659.4	658.8	658.1	657.5
47.5°	618.8	616.3	613.7	611.7	610.2	608.6	607.1	605.5
50°	585.9	583.1	580.2	578.2	577.0	575.8	574.5	573.3
52.5°	552.2	549.6	547.1	545.1	543.5	542.0	540.4	538.9
55°	502.5	500.1	497.6	495.8	494.6	493.4	492.1	490.9
57.5°	452.7	450.4	448.1	446.3	445.1	443.9	442.8	441.6
60°	418.5	416.7	414.8	413.5	412.4	411.4	410.4	409.4
62.5°	385.1	383.5	381.9	380.5	379.4	378.4	377.5	376.4
65°	336.7	334.6	332.5	331.1	330.0	329.0	328.0	326.9
67.5°	286.6	284.6	282.7	281.5	281.3	281.0	280.7	280.4
70°	255.0	253.4	251.8	250.6	250.0	249.4	248.8	248.2
72.5°	223.4	222.1	220.8	219.9	219.2	218.6	218.0	217.4
75°	177.9	177.0	176.2	175.7	175.6	175.3	175.1	175.0
77.5°	134.7	134.4	134.2	133.8	133.3	132.8	132.2	131.7
80°	107.3	106.9	106.4	106.2	105.9	105.7	105.6	105.3
82.5°	82.7	82.4	82.1	82.0	81.8	81.5	81.4	81.1
85°	47.6	47.6	47.6	47.5	47.4	47.1	46.9	46.7
87.5°	24.0	24.4	24.7	24.9	25.1	25.1	25.2	25.4
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	31.0	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	32.0	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.6	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	47.4	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	169.4	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	410.3	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	507.6	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	573.8	574.4	574.9	575.7	576.5	577.4	578.2	579.1



TEST NUMBER: P332803-935

CATALOG NUMBER: S124DIW-S795D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.8	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	733.5	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.7	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.0	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1030.1	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.6	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.4	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.2	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1277.5	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.0	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.0	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1418.9	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1471.7	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.0	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1573.6	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1608.4	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1673.3	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1695.1	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1711.2	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1721.1	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1727.3	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1734.7	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1737.6	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)