

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333093-830

Luminaire Tested: **S124RDIW-S1020D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333093-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1560U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9816.2 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333093-830

CATALOG NUMBER: S124RDIW-S1020D1560U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333093-830

CATALOG NUMBER: S124RDIW-S1020D1560U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40				
1	96	92	88	84	87	84	80	78	68	66	64	55	53	52	42	41	40	34				
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29				
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25				
4	73	63	55	49	66	57	51	46	47	42	39	38	35	32	30	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	17				
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	17	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13				
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P333093-830

CATALOG NUMBER: S124RDIW-S1020D1560U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	1.6
10°-20°	445.8	4.5
20°-30°	643.8	6.6
30°-40°	729.7	7.4
40°-50°	704.7	7.2
50°-60°	586.0	6.0
60°-70°	404.6	4.1
70°-80°	205.1	2.1
80°-90°	58.1	0.6
90°-100°	65.0	0.7
100°-110°	414.4	4.2
110°-120°	792.8	8.1
120°-130°	1006.4	10.3
130°-140°	1076.8	11.0
140°-150°	1006.9	10.3
150°-160°	812.0	8.3
160°-170°	523.7	5.3
170°-180°	180.5	1.8
0°-30°	1249.5	12.7
0°-40°	1979.2	20.2
0°-60°	3269.8	33.3
0°-90°	3937.7	40.1
90°-120°	1272.2	13.0
90°-150°	4362.3	44.4
90°-180°	5879.0	59.9
0°-180°	9816.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	4	20	31	40	43	7
95°	78	33	31	39	41	100
105°	428	436	444	453	405	448
115°	799	803	802	804	805	786
125°	1123	1128	1126	1130	1131	1002
135°	1393	1392	1397	1400	1403	1073
145°	1606	1610	1610	1612	1615	1003
155°	1761	1762	1758	1763	1760	812
165°	1858	1851	1851	1861	1849	525
175°	1900	1892	1893	1904	1889	181
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P333093-830

CATALOG NUMBER: S124RDIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.8	23.7	22.5	21.4	20.2	19.8	20.0	20.3	20.5	20.8	21.0
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	17.9	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0
95°	78.1	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2
97.5°	166.0	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7
100°	233.1	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2
102.5°	308.1	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4
105°	427.8	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3
107.5°	538.9	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3
110°	614.1	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5



TEST NUMBER: P333093-830

CATALOG NUMBER: S124RDIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	686.8	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3
115°	798.8	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3
117.5°	899.8	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4
120°	968.0	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9
122.5°	1031.6	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5
125°	1122.9	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7
127.5°	1209.3	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1
130°	1265.1	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0
132.5°	1316.2	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5
135°	1393.0	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9
137.5°	1460.9	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4
140°	1505.2	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9
142.5°	1545.0	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6
145°	1606.2	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7
147.5°	1654.8	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6
150°	1690.1	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3
152.5°	1719.6	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1
155°	1761.1	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5
157.5°	1796.1	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1
160°	1816.6	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8
162.5°	1834.8	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8
165°	1857.8	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1
167.5°	1875.9	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5
170°	1886.2	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6
172.5°	1893.0	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4
175°	1900.4	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1
177.5°	1903.8	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P333093-830

CATALOG NUMBER: S124RDIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	21.1	21.3	21.4	21.7	22.1	22.4	22.8	23.1
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	33.9	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	35.1	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	37.9	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	51.8	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	185.5	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	449.1	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	555.7	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.1	628.8	629.3	630.2	631.1	632.1	633.0	634.0



TEST NUMBER: P333093-830

CATALOG NUMBER: S124RDIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	698.2	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.0	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.3	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1037.8	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1127.7	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.9	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.4	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1324.8	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1398.5	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.1	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1512.9	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1553.3	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.1	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1661.8	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1722.6	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1760.8	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1831.7	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1855.7	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1873.3	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1884.1	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1890.9	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1898.9	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1902.1	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)