

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332785-935

Luminaire Tested: **S124DIW-S795D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332785-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D770U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5578.6 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332785-935

CATALOG NUMBER: S124DIW-S795D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332785-935

CATALOG NUMBER: S124DIW-S795D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42
3	82	72	65	59	75	67	61	55	57	52	48	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9227	9227	9227
5°	9255	9143	9210
10°	9197	9069	9114
15°	9086	8940	8964
20°	8937	8781	8789
25°	8769	8598	8573
30°	8563	8383	8307
35°	8348	8159	8051
40°	8126	7904	7759
45°	7895	7654	7507
50°	7637	7430	7200
55°	7361	7142	6909
60°	7083	6817	6610
65°	6770	6508	6245
70°	6420	6097	5858
75°	5883	5599	5459
80°	5235	5026	4895
85°	4576	4409	4326



TEST NUMBER: P332785-935

CATALOG NUMBER: S124DIW-S795D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.6	1.9
10°-20°	303.3	5.4
20°-30°	446.4	8.0
30°-40°	518.9	9.3
40°-50°	518.9	9.3
50°-60°	453.9	8.1
60°-70°	337.1	6.0
70°-80°	191.5	3.4
80°-90°	57.7	1.0
90°-100°	29.2	0.5
100°-110°	186.3	3.3
110°-120°	356.5	6.4
120°-130°	452.5	8.1
130°-140°	484.2	8.7
140°-150°	452.7	8.1
150°-160°	365.1	6.5
160°-170°	235.5	4.2
170°-180°	81.2	1.5
0°-30°	857.3	15.4
0°-40°	1376.2	24.7
0°-60°	2349.1	42.1
0°-90°	2935.4	52.6
90°-120°	572.0	10.3
90°-150°	1961.4	35.2
90°-180°	2643.0	47.4
0°-180°	5578.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1143	1143	1143	1143	1143	
5°	1142	1138	1128	1138	1136	108
15°	1087	1083	1070	1075	1072	306
25°	984	978	965	966	962	453
35°	847	840	828	822	817	529
45°	692	685	670	661	658	533
55°	523	520	507	497	491	468
65°	354	350	341	332	327	351
75°	189	184	180	176	175	200
85°	49	49	48	48	47	54
90°	2	9	14	18	19	4
95°	35	15	14	18	18	45
105°	192	196	199	204	182	201
115°	359	361	360	362	362	353
125°	505	507	506	508	509	451
135°	626	626	628	630	631	482
145°	722	724	724	725	726	451
155°	792	792	791	793	791	365
165°	835	832	832	837	832	236
175°	854	851	851	856	849	81
180°	854	854	854	854	854	



TEST NUMBER: P332785-935

CATALOG NUMBER: S124DIW-S795D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1145.9	1145.4	1144.9	1144.4	1143.9	1142.8	1141.0	1139.2	1137.4	1135.7	1137.2
5°	1142.0	1141.3	1140.4	1139.6	1138.8	1137.2	1135.0	1132.7	1130.5	1128.3	1130.5
7.5°	1131.4	1130.6	1129.8	1128.9	1128.2	1126.5	1124.0	1121.5	1119.0	1116.5	1118.4
10°	1121.9	1121.1	1120.2	1119.5	1118.6	1116.9	1114.2	1111.6	1109.0	1106.3	1107.9
12.5°	1109.4	1108.6	1107.8	1107.0	1106.2	1104.3	1101.6	1098.7	1096.0	1093.1	1094.9
15°	1087.1	1086.2	1085.5	1084.6	1083.8	1081.9	1078.8	1075.8	1072.7	1069.7	1070.9
17.5°	1060.1	1059.1	1058.1	1057.1	1056.1	1054.1	1051.3	1048.4	1045.4	1042.6	1043.4
20°	1040.3	1039.3	1038.4	1037.3	1036.3	1034.2	1031.2	1028.1	1025.1	1022.1	1022.7
22.5°	1019.2	1017.8	1016.4	1015.1	1013.7	1011.6	1008.5	1005.5	1002.4	999.4	1000.5
25°	984.5	983.1	981.6	980.2	978.8	976.6	973.8	970.9	968.1	965.3	965.4
27.5°	944.9	943.5	942.0	940.6	939.1	937.0	934.4	931.8	929.1	926.4	925.9
30°	918.6	917.0	915.3	913.7	912.1	909.9	907.2	904.7	902.0	899.3	898.5
32.5°	890.7	889.2	887.8	886.3	884.8	882.7	879.9	877.1	874.3	871.5	870.6
35°	847.1	845.7	844.3	842.8	841.5	839.3	836.5	833.6	830.8	827.9	826.5
37.5°	801.2	799.9	798.6	797.3	795.9	793.8	790.7	787.6	784.6	781.5	780.0
40°	771.1	769.5	767.8	766.2	764.6	762.2	759.2	756.1	753.1	750.0	748.0
42.5°	738.9	737.9	736.9	736.0	734.9	732.8	729.4	726.1	722.6	719.3	717.0
45°	691.5	690.0	688.6	687.2	685.8	683.4	680.2	676.9	673.6	670.4	668.1
47.5°	641.8	640.8	639.9	638.9	637.9	635.9	632.9	629.9	626.9	623.9	621.3
50°	608.1	607.3	606.5	605.6	604.9	603.0	600.2	597.4	594.4	591.6	588.8
52.5°	575.1	574.2	573.2	572.2	571.2	569.2	566.2	563.2	560.2	557.2	554.7
55°	523.0	522.3	521.7	521.1	520.5	518.8	515.9	513.1	510.2	507.4	504.9
57.5°	473.1	472.4	471.7	471.1	470.4	468.6	465.8	463.0	460.2	457.4	455.0
60°	438.7	437.6	436.6	435.7	434.6	432.7	430.2	427.5	424.8	422.2	420.3
62.5°	405.0	404.2	403.3	402.4	401.6	399.8	396.9	394.1	391.3	388.5	386.8
65°	354.4	353.4	352.4	351.4	350.3	348.8	346.8	344.7	342.7	340.7	338.6
67.5°	303.5	302.6	301.6	300.7	299.8	298.3	296.4	294.4	292.5	290.5	288.5
70°	272.0	270.6	269.1	267.7	266.3	264.8	263.1	261.5	259.8	258.3	256.7
72.5°	238.3	236.9	235.5	234.0	232.6	231.3	230.0	228.6	227.3	226.0	224.7
75°	188.6	187.6	186.7	185.6	184.6	183.6	182.5	181.5	180.6	179.5	178.7
77.5°	141.2	140.8	140.3	139.9	139.4	138.8	137.8	137.0	136.0	135.2	134.9
80°	112.6	112.0	111.4	110.8	110.2	109.7	109.3	108.9	108.5	108.1	107.6
82.5°	84.8	84.6	84.2	83.9	83.7	83.5	83.4	83.3	83.3	83.2	82.9
85°	49.4	49.4	49.4	49.4	49.4	49.2	48.8	48.5	48.0	47.6	47.6
87.5°	19.5	19.5	19.7	19.9	20.1	20.1	20.2	20.2	20.3	20.4	20.6
90°	1.9	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9
92.5°	8.1	8.2	8.3	8.3	8.4	9.0	10.2	11.3	12.4	13.5	14.4
95°	35.1	30.3	25.5	20.7	15.8	13.5	13.6	13.8	13.9	14.0	14.9
97.5°	74.6	77.7	80.7	83.7	86.7	80.2	64.4	48.6	32.7	16.9	17.0
100°	104.8	107.4	109.9	112.4	115.0	106.5	87.0	67.3	47.7	28.2	25.7
102.5°	138.5	140.4	142.3	144.2	146.0	145.7	143.2	140.6	138.0	135.5	109.4
105°	192.3	193.2	194.1	194.9	195.8	196.6	197.3	197.9	198.7	199.4	200.7
107.5°	242.4	242.8	243.2	243.7	244.1	244.8	245.7	246.7	247.6	248.6	249.3
110°	276.1	276.6	277.0	277.4	277.8	278.4	279.3	280.2	281.0	281.8	282.1



TEST NUMBER: P332785-935

CATALOG NUMBER: S124DIW-S795D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.8	309.6	310.4	311.1	311.9	312.5	312.9	313.2	313.7	314.1	314.0
115°	359.2	359.6	360.1	360.4	360.8	361.0	360.8	360.8	360.6	360.4	360.8
117.5°	404.6	405.1	405.7	406.2	406.8	407.3	407.6	407.9	408.2	408.5	408.5
120°	435.2	435.8	436.4	437.0	437.5	437.7	437.6	437.5	437.3	437.1	437.5
122.5°	463.9	464.2	464.5	464.9	465.2	465.5	465.7	465.9	466.1	466.3	466.5
125°	504.9	505.5	506.0	506.6	507.1	507.3	507.0	506.8	506.4	506.2	506.6
127.5°	543.7	543.9	544.1	544.2	544.3	544.8	545.4	546.0	546.6	547.3	547.3
130°	568.8	568.9	569.1	569.2	569.4	569.6	570.1	570.5	570.9	571.4	571.5
132.5°	591.9	592.1	592.4	592.5	592.8	593.2	593.7	594.3	594.9	595.4	595.6
135°	626.3	626.2	626.0	625.9	625.8	625.9	626.5	627.1	627.7	628.3	628.5
137.5°	656.9	656.9	657.0	657.0	657.1	657.5	658.1	658.7	659.4	660.0	660.2
140°	676.8	677.1	677.3	677.7	678.0	678.2	678.6	678.8	679.1	679.4	679.8
142.5°	694.7	695.3	695.8	696.2	696.7	697.1	697.2	697.4	697.6	697.8	698.1
145°	722.2	722.6	723.1	723.5	723.9	724.1	724.1	724.1	724.1	724.1	724.3
147.5°	744.1	744.9	745.6	746.4	747.3	747.5	747.4	747.3	747.1	747.0	747.1
150°	759.9	760.4	761.0	761.6	762.2	762.4	762.2	762.1	762.0	761.8	761.8
152.5°	773.2	773.6	774.1	774.6	775.0	775.1	774.8	774.6	774.4	774.1	774.3
155°	791.9	792.0	792.1	792.3	792.5	792.3	791.9	791.4	791.0	790.6	791.2
157.5°	807.6	807.5	807.4	807.4	807.3	806.9	806.5	806.0	805.5	805.0	805.7
160°	816.7	816.3	816.0	815.5	815.1	814.8	814.7	814.5	814.3	814.2	815.1
162.5°	824.9	824.4	823.9	823.4	822.8	822.4	822.3	822.2	822.0	821.9	822.8
165°	835.3	834.6	833.9	833.2	832.5	832.2	832.2	832.2	832.2	832.2	833.3
167.5°	843.5	842.7	842.1	841.3	840.5	840.2	840.1	840.0	839.9	839.8	841.0
170°	848.1	847.2	846.4	845.5	844.7	844.3	844.5	844.6	844.7	844.9	846.0
172.5°	851.2	850.3	849.5	848.6	847.7	847.4	847.6	847.7	847.8	848.0	849.1
175°	854.5	853.6	852.8	852.0	851.1	850.8	850.8	851.0	851.2	851.3	852.6
177.5°	856.0	855.2	854.5	853.6	852.8	852.6	852.8	853.0	853.3	853.4	854.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P332785-935

CATALOG NUMBER: S124DIW-S795D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0	1143.0
2.5°	1138.8	1140.5	1142.1	1142.9	1142.7	1142.5	1142.4	1142.2
5°	1132.7	1135.0	1137.2	1138.2	1137.7	1137.4	1137.0	1136.5
7.5°	1120.2	1122.0	1123.7	1124.5	1124.3	1124.0	1123.8	1123.5
10°	1109.6	1111.2	1112.8	1113.4	1113.0	1112.6	1112.2	1111.8
12.5°	1096.7	1098.5	1100.3	1100.9	1100.4	1099.8	1099.2	1098.6
15°	1072.1	1073.3	1074.5	1074.9	1074.3	1073.7	1073.1	1072.5
17.5°	1044.1	1044.9	1045.7	1045.9	1045.4	1045.0	1044.7	1044.2
20°	1023.3	1023.9	1024.5	1024.6	1024.2	1023.8	1023.4	1023.0
22.5°	1001.5	1002.6	1003.8	1003.9	1003.2	1002.5	1001.7	1001.0
25°	965.7	965.9	966.1	965.8	965.0	964.1	963.4	962.5
27.5°	925.5	925.0	924.5	923.8	922.7	921.7	920.7	919.6
30°	897.7	896.9	896.0	895.2	894.1	893.1	892.1	891.1
32.5°	869.5	868.6	867.6	866.6	865.6	864.5	863.5	862.5
35°	825.1	823.6	822.2	821.0	819.9	819.0	817.9	816.9
37.5°	778.4	776.9	775.4	774.0	772.6	771.3	769.9	768.5
40°	746.0	744.0	741.9	740.4	739.3	738.4	737.4	736.3
42.5°	714.5	712.2	709.8	708.3	707.7	707.0	706.3	705.6
45°	665.9	663.7	661.4	660.0	659.4	658.8	658.1	657.5
47.5°	618.8	616.3	613.7	611.7	610.2	608.6	607.1	605.5
50°	585.9	583.1	580.2	578.2	577.0	575.8	574.5	573.3
52.5°	552.2	549.6	547.1	545.1	543.5	542.0	540.4	538.9
55°	502.5	500.1	497.6	495.8	494.6	493.4	492.1	490.9
57.5°	452.7	450.4	448.1	446.3	445.1	443.9	442.8	441.6
60°	418.5	416.7	414.8	413.5	412.4	411.4	410.4	409.4
62.5°	385.1	383.5	381.9	380.5	379.4	378.4	377.5	376.4
65°	336.7	334.6	332.5	331.1	330.0	329.0	328.0	326.9
67.5°	286.6	284.6	282.7	281.5	281.3	281.0	280.7	280.4
70°	255.0	253.4	251.8	250.6	250.0	249.4	248.8	248.2
72.5°	223.4	222.1	220.8	219.9	219.2	218.6	218.0	217.4
75°	177.9	177.0	176.2	175.7	175.6	175.3	175.1	175.0
77.5°	134.7	134.4	134.2	133.8	133.3	132.8	132.2	131.7
80°	107.3	106.9	106.4	106.2	105.9	105.7	105.6	105.3
82.5°	82.7	82.4	82.1	82.0	81.8	81.5	81.4	81.1
85°	47.6	47.6	47.6	47.5	47.4	47.1	46.9	46.7
87.5°	20.8	20.9	21.1	21.2	21.3	21.3	21.4	21.4
90°	15.8	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	15.2	16.1	17.0	17.4	17.5	17.6	17.6	17.7
95°	15.8	16.6	17.5	18.0	18.1	18.3	18.4	18.5
97.5°	17.0	17.1	17.2	17.3	17.5	17.7	17.7	17.9
100°	23.3	20.8	18.4	17.3	17.5	17.7	17.7	17.9
102.5°	83.4	57.3	31.3	18.3	18.3	18.3	18.3	18.4
105°	202.0	203.2	204.5	202.6	197.5	192.3	187.3	182.2
107.5°	249.9	250.5	251.2	251.7	252.3	252.8	253.3	253.8
110°	282.4	282.7	283.0	283.4	283.8	284.2	284.6	285.1



TEST NUMBER: P332785-935

CATALOG NUMBER: S124DIW-S795D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.9	313.9	313.8	314.1	314.6	315.1	315.7	316.2
115°	361.0	361.3	361.6	361.7	361.7	361.7	361.7	361.7
117.5°	408.4	408.4	408.3	408.2	408.2	408.1	408.0	408.0
120°	437.7	438.0	438.2	438.2	438.0	437.7	437.5	437.1
122.5°	466.7	466.8	467.0	466.9	466.7	466.3	466.1	465.8
125°	507.0	507.5	507.9	508.2	508.3	508.4	508.6	508.8
127.5°	547.2	547.1	547.0	546.9	546.8	546.6	546.6	546.5
130°	571.6	571.8	572.0	572.0	572.0	572.0	572.0	572.0
132.5°	595.6	595.8	596.0	596.0	595.9	595.7	595.6	595.6
135°	628.8	629.1	629.4	629.6	629.9	630.3	630.5	630.8
137.5°	660.6	660.9	661.2	661.3	661.2	661.2	661.1	661.0
140°	680.2	680.6	681.1	681.4	681.5	681.7	681.8	681.9
142.5°	698.4	698.7	699.0	699.2	699.2	699.2	699.3	699.3
145°	724.4	724.5	724.7	724.9	725.1	725.5	725.7	726.0
147.5°	747.2	747.3	747.4	747.6	747.7	747.9	748.0	748.1
150°	761.8	761.8	761.8	761.9	762.1	762.2	762.3	762.4
152.5°	774.6	774.7	775.0	775.1	775.0	774.9	774.8	774.7
155°	791.7	792.3	792.8	792.9	792.5	792.0	791.6	791.3
157.5°	806.5	807.3	808.0	808.0	807.3	806.5	805.7	805.0
160°	816.0	816.7	817.6	817.6	816.7	816.0	815.1	814.2
162.5°	823.6	824.4	825.3	825.3	824.3	823.3	822.3	821.4
165°	834.4	835.5	836.6	836.6	835.3	834.1	832.8	831.5
167.5°	842.3	843.5	844.8	844.7	843.3	841.9	840.4	839.0
170°	847.1	848.3	849.5	849.3	847.9	846.4	845.1	843.6
172.5°	850.2	851.4	852.5	852.3	850.8	849.3	847.7	846.2
175°	853.9	855.1	856.4	856.2	854.5	852.8	851.1	849.4
177.5°	855.3	856.2	857.1	856.9	855.5	854.1	852.8	851.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5

(END OF REPORT)