

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333075-830

Luminaire Tested: **S124RDIW-S1020D470U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333075-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D470U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5856.3 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	77	73	74	70	66	67	63	61	60	57	55	51
3	86	77	70	64	81	73	67	61	66	61	57	59	55	52	53	50	47	44
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41	38
5	73	62	53	47	69	59	51	46	53	47	43	48	43	39	44	40	36	34
6	68	56	47	42	64	53	46	40	48	42	38	44	39	35	40	36	32	30
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29	27
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24
9	54	42	35	29	52	40	33	29	37	31	27	34	29	25	31	27	24	22
10	51	39	32	27	48	37	30	26	34	28	24	31	27	23	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13056	13056	13056	13056
5°	15144	13095	11574	13095
10°	17915	13038	10330	13038
15°	20695	12918	8877	12918
20°	23040	12752	8027	12752
25°	23785	12588	7452	12588
30°	20821	12392	7106	12392
35°	16208	12098	6897	12098
40°	12154	11763	6785	11763
45°	9597	11226	6725	11226
50°	8102	10605	6531	10605
55°	7061	9923	6180	9923
60°	6353	9216	5470	9216
65°	5601	8451	4705	8451
70°	5044	7659	4244	7659
75°	4226	6787	3618	6787
80°	3575	5783	3394	5783
85°	3020	4520	3020	4520



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	2.7
10°-20°	472.7	8.1
20°-30°	739.3	12.6
30°-40°	821.9	14.0
40°-50°	729.2	12.5
50°-60°	568.2	9.7
60°-70°	372.0	6.4
70°-80°	182.9	3.1
80°-90°	46.8	0.8
90°-100°	19.5	0.3
100°-110°	124.6	2.1
110°-120°	238.3	4.1
120°-130°	302.4	5.2
130°-140°	323.6	5.5
140°-150°	302.6	5.2
150°-160°	244.0	4.2
160°-170°	157.4	2.7
170°-180°	54.2	0.9
0°-30°	1368.7	23.4
0°-40°	2190.5	37.4
0°-60°	3487.9	59.6
0°-90°	4089.6	69.8
90°-120°	382.4	6.5
90°-150°	1311.0	22.4
90°-180°	1767.0	30.2
0°-180°	5856.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1617	1617	1617	1617	1617	
5°	1869	1616	1428	1616	1869	189
15°	2476	1546	1062	1546	2476	704
25°	2670	1413	837	1413	2670	1185
35°	1645	1228	700	1228	1645	1031
45°	841	983	589	983	841	666
55°	502	705	439	705	502	456
65°	293	442	246	442	293	295
75°	136	218	116	218	136	149
85°	33	49	33	49	33	37
90°	13	1	13	1	13	7
95°	12	24	12	24	12	10
105°	122	129	122	129	122	106
115°	242	240	242	240	242	239
125°	340	337	340	337	340	303
135°	422	419	422	419	422	325
145°	485	483	485	483	485	303
155°	529	529	529	529	529	244
165°	556	558	556	558	556	157
175°	568	571	568	571	568	54
180°	571	571	571	571	571	



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1705.8	1710.5	1705.8	1705.3	1700.2	1698.6	1696.5	1689.7	1677.2	1669.9	1671.4
5°	1868.8	1885.0	1875.9	1874.6	1860.3	1846.0	1836.8	1816.0	1793.8	1778.9	1766.4
7.5°	2057.2	2066.5	2060.9	2051.7	2028.5	2015.3	1994.2	1966.7	1927.0	1896.6	1868.9
10°	2185.4	2193.2	2190.7	2173.7	2156.7	2122.2	2102.6	2064.3	2014.0	1974.3	1937.1
12.5°	2311.6	2319.9	2297.0	2297.7	2265.7	2238.4	2207.4	2159.1	2101.1	2049.8	2003.4
15°	2476.1	2465.6	2465.6	2452.6	2416.7	2379.0	2347.0	2296.2	2223.2	2161.9	2097.4
17.5°	2604.8	2608.4	2603.1	2572.3	2544.2	2505.1	2446.6	2387.3	2319.5	2237.3	2171.3
20°	2681.9	2681.9	2676.1	2655.2	2618.8	2577.0	2513.9	2449.3	2363.3	2280.6	2206.3
22.5°	2713.2	2715.3	2708.4	2691.1	2658.3	2617.6	2563.8	2498.3	2409.7	2316.5	2224.5
25°	2670.2	2682.6	2683.9	2679.3	2669.6	2644.8	2598.5	2531.4	2451.9	2350.9	2251.8
27.5°	2451.6	2467.2	2480.9	2503.4	2533.4	2549.0	2551.1	2517.0	2447.6	2350.4	2250.7
30°	2233.6	2246.6	2289.1	2344.4	2387.4	2426.5	2460.4	2469.5	2430.4	2343.1	2238.2
32.5°	1991.8	2009.5	2051.8	2111.4	2183.0	2249.3	2325.3	2364.2	2363.1	2310.7	2213.7
35°	1644.6	1657.6	1696.8	1759.3	1845.3	1943.7	2064.3	2158.0	2221.9	2217.3	2158.0
37.5°	1326.3	1341.0	1380.5	1432.5	1515.9	1637.7	1754.4	1883.6	2001.7	2068.0	2048.1
40°	1153.3	1154.0	1192.4	1245.9	1324.0	1430.2	1557.3	1700.6	1832.2	1939.8	1960.6
42.5°	1016.7	1016.8	1042.3	1099.9	1156.2	1256.1	1377.4	1519.8	1673.8	1798.0	1853.2
45°	840.6	846.4	867.2	901.8	946.1	1030.8	1127.8	1260.2	1432.9	1580.1	1672.0
47.5°	711.8	720.4	733.7	761.9	797.1	853.6	933.9	1052.7	1193.2	1355.2	1485.9
50°	645.1	646.4	663.3	678.9	709.5	754.5	824.9	924.0	1052.9	1208.7	1354.0
52.5°	587.8	587.5	597.7	617.5	642.3	677.4	734.2	824.3	938.8	1078.4	1228.3
55°	501.7	505.0	512.8	528.4	547.3	572.1	617.1	684.9	774.8	894.0	1030.2
57.5°	436.3	438.0	444.1	450.7	468.1	486.1	519.8	566.8	642.7	740.4	867.2
60°	393.5	394.2	396.2	406.0	419.6	436.6	459.4	499.1	563.0	652.2	752.6
62.5°	351.9	353.0	356.0	363.2	373.7	385.5	409.3	441.3	494.2	570.4	660.8
65°	293.2	293.9	298.4	301.0	309.5	319.9	337.5	359.0	395.5	459.4	527.8
67.5°	245.0	245.0	245.2	248.7	254.7	261.6	272.1	289.3	316.8	356.0	416.3
70°	213.7	213.7	215.0	217.0	220.3	226.1	232.0	245.0	265.2	297.1	343.4
72.5°	184.5	185.0	186.3	186.7	188.4	193.2	197.6	205.9	220.9	245.0	282.4
75°	135.5	137.5	140.7	143.4	146.6	146.0	150.5	155.7	160.3	174.7	196.1
77.5°	100.9	99.8	100.2	102.5	102.8	103.5	106.7	110.7	114.1	120.9	128.7
80°	76.9	76.9	78.8	79.5	78.8	79.5	82.8	84.7	86.1	88.6	95.8
82.5°	58.2	59.2	58.5	59.2	59.6	60.2	63.0	63.3	64.7	65.7	68.7
85°	32.6	33.3	33.8	32.6	32.6	32.6	33.8	34.5	35.8	35.2	36.5
87.5°	14.0	13.5	13.9	13.9	14.4	13.8	14.2	15.2	13.9	14.4	14.2
90°	12.8	12.6	12.4	12.3	12.1	11.7	11.1	10.6	10.0	9.4	8.7
92.5°	11.8	11.8	11.7	11.7	11.6	11.3	10.7	10.2	9.6	9.0	8.3
95°	12.3	12.3	12.2	12.1	12.0	11.7	11.1	10.6	10.0	9.4	9.3
97.5°	12.0	11.9	11.8	11.7	11.6	11.5	11.4	11.4	11.3	11.3	21.9
100°	12.0	11.9	11.8	11.7	11.6	12.3	13.9	15.6	17.2	18.8	31.9
102.5°	12.3	12.3	12.3	12.3	12.3	20.9	38.4	55.7	73.1	90.6	92.3
105°	121.8	125.2	128.6	132.0	135.4	136.7	135.8	135.0	134.1	133.3	132.8
107.5°	169.7	169.3	168.9	168.6	168.2	167.9	167.4	167.0	166.5	166.2	165.5
110°	190.5	190.2	189.9	189.6	189.4	189.2	189.0	188.8	188.6	188.4	187.8



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.3	211.0	210.7	210.3	209.9	209.7	209.8	209.8	209.9	209.9	209.6
115°	241.8	241.8	241.8	241.8	241.8	241.7	241.5	241.3	241.1	240.9	241.0
117.5°	272.7	272.8	272.8	272.8	272.9	272.9	273.0	273.0	273.0	273.1	272.9
120°	292.2	292.4	292.6	292.8	292.9	292.9	292.8	292.6	292.4	292.2	292.3
122.5°	311.3	311.5	311.7	311.9	312.1	312.1	312.0	311.9	311.8	311.7	311.5
125°	340.0	339.9	339.8	339.7	339.6	339.4	339.1	338.8	338.6	338.3	338.5
127.5°	365.2	365.3	365.3	365.4	365.5	365.6	365.6	365.7	365.8	365.8	365.4
130°	382.3	382.3	382.3	382.3	382.3	382.3	382.2	382.1	382.0	381.9	381.6
132.5°	398.0	398.1	398.2	398.2	398.3	398.3	398.2	398.1	398.0	397.9	397.6
135°	421.6	421.4	421.2	421.0	420.8	420.7	420.5	420.3	420.1	419.9	419.5
137.5°	441.8	441.9	441.9	442.0	442.0	442.0	441.7	441.5	441.3	441.1	440.6
140°	455.8	455.7	455.6	455.5	455.4	455.2	455.0	454.7	454.4	454.1	453.9
142.5°	467.4	467.4	467.4	467.3	467.3	467.2	467.0	466.7	466.6	466.4	466.3
145°	485.2	485.0	484.8	484.7	484.5	484.4	484.3	484.2	484.1	484.0	484.0
147.5°	500.0	499.9	499.8	499.7	499.6	499.5	499.5	499.5	499.4	499.3	499.4
150°	509.6	509.5	509.4	509.3	509.3	509.2	509.2	509.2	509.2	509.2	509.3
152.5°	517.8	517.8	517.9	518.0	518.0	518.0	517.8	517.6	517.6	517.4	517.6
155°	528.9	529.1	529.4	529.7	530.0	529.9	529.5	529.1	528.8	528.4	528.7
157.5°	538.1	538.6	539.0	539.5	540.0	540.0	539.5	539.0	538.6	538.1	538.4
160°	544.2	544.8	545.4	545.9	546.5	546.5	545.9	545.4	544.8	544.2	544.3
162.5°	549.0	549.6	550.3	550.9	551.6	551.6	551.0	550.4	549.9	549.3	549.4
165°	555.7	556.6	557.4	558.3	559.1	559.2	558.5	557.7	556.9	556.2	556.2
167.5°	560.8	561.8	562.7	563.6	564.6	564.7	563.8	563.0	562.1	561.3	561.4
170°	563.8	564.8	565.7	566.7	567.7	567.8	566.9	566.2	565.4	564.7	564.6
172.5°	565.5	566.6	567.6	568.6	569.7	569.8	569.0	568.3	567.5	566.8	566.7
175°	567.7	568.8	570.0	571.1	572.2	572.4	571.6	570.7	569.9	569.0	568.9
177.5°	569.1	570.0	570.9	571.8	572.7	572.9	572.2	571.7	571.0	570.4	570.2
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1666.2	1659.0	1655.3	1646.9	1637.0	1631.8	1627.1	1620.3	1611.5	1602.1	1595.3
5°	1750.8	1735.1	1715.6	1692.1	1671.3	1651.1	1633.5	1615.9	1595.7	1574.9	1554.1
7.5°	1837.6	1806.9	1773.6	1735.1	1697.8	1663.8	1632.5	1602.5	1568.6	1538.2	1510.6
10°	1898.1	1856.3	1810.1	1761.2	1712.3	1670.0	1628.3	1590.5	1548.8	1511.6	1480.4
12.5°	1947.1	1898.1	1842.4	1781.6	1722.8	1671.6	1623.6	1574.3	1526.9	1486.7	1444.9
15°	2028.4	1961.2	1886.3	1813.4	1737.1	1667.4	1602.9	1545.6	1491.5	1434.8	1395.1
17.5°	2084.2	2004.7	1913.5	1825.9	1735.8	1653.6	1579.1	1510.9	1448.5	1390.6	1343.3
20°	2117.6	2029.7	1928.7	1829.0	1728.0	1640.0	1559.9	1484.3	1419.8	1357.3	1308.3
22.5°	2136.4	2039.1	1928.7	1824.3	1719.7	1624.4	1536.4	1457.7	1387.5	1324.9	1270.8
25°	2142.4	2038.2	1925.4	1805.5	1690.8	1589.9	1498.6	1413.2	1335.1	1272.5	1215.2
27.5°	2134.1	2011.3	1895.8	1772.8	1654.5	1548.0	1452.3	1362.6	1284.3	1217.2	1158.4
30°	2121.6	1989.9	1866.1	1738.4	1618.5	1516.3	1415.2	1329.3	1247.7	1178.1	1118.8
32.5°	2094.4	1963.9	1830.7	1699.9	1578.4	1473.0	1377.1	1290.6	1210.8	1139.5	1076.6
35°	2040.8	1908.5	1763.9	1629.7	1510.3	1400.9	1311.0	1227.6	1151.3	1075.2	1008.6
37.5°	1970.0	1834.8	1691.0	1544.0	1424.7	1321.3	1238.8	1160.5	1086.1	1016.4	942.8
40°	1903.3	1780.1	1631.5	1485.6	1363.1	1263.4	1187.2	1116.2	1041.2	972.1	898.5
42.5°	1822.5	1717.6	1567.4	1421.0	1300.0	1204.0	1132.9	1063.5	995.3	928.4	851.6
45°	1687.6	1608.1	1467.4	1326.6	1204.8	1109.7	1044.5	983.3	923.3	859.4	787.1
47.5°	1533.0	1479.2	1357.7	1213.6	1100.9	1015.3	952.3	902.3	851.6	787.8	724.3
50°	1425.7	1391.1	1273.8	1142.3	1034.7	955.8	891.4	844.4	802.1	740.8	684.2
52.5°	1311.0	1292.6	1193.5	1067.7	963.8	886.6	831.4	789.2	746.3	695.5	642.4
55°	1136.3	1146.1	1062.1	953.3	855.5	790.4	740.2	705.0	668.5	625.6	584.5
57.5°	957.8	993.5	937.1	841.6	750.0	689.8	652.0	622.4	591.7	556.1	521.0
60°	850.9	880.9	849.0	765.0	684.9	628.8	593.6	570.8	540.2	507.6	480.9
62.5°	746.7	778.7	759.9	692.0	617.6	569.4	538.4	517.1	494.3	465.9	438.1
65°	615.8	636.6	627.5	580.6	527.8	486.7	458.1	442.4	421.6	400.8	376.0
67.5°	471.6	511.9	506.5	481.6	436.0	404.0	385.2	371.4	352.4	336.9	320.1
70°	387.7	424.8	424.1	404.0	379.2	349.2	336.2	324.5	307.6	292.6	278.9
72.5°	317.4	351.4	356.4	340.9	324.0	301.3	288.8	280.7	264.3	254.0	242.9
75°	222.2	246.9	253.4	253.4	245.6	233.9	222.8	217.6	205.9	196.8	190.3
77.5°	145.7	161.4	171.5	173.8	175.0	171.1	162.0	158.3	149.3	146.1	139.9
80°	102.9	113.4	125.1	129.0	132.2	131.0	127.1	124.4	116.0	112.7	110.1
82.5°	71.2	76.9	86.5	95.1	94.3	97.6	94.3	92.2	85.8	84.5	82.0
85°	37.1	37.8	39.1	45.0	48.3	49.5	50.1	48.8	46.9	46.9	42.3
87.5°	14.0	13.4	14.3	14.1	14.4	16.3	17.6	18.0	16.6	15.3	13.9
90°	7.9	7.2	6.3	5.5	4.4	3.4	2.4	1.3	2.4	3.4	4.4
92.5°	7.5	6.8	6.0	5.7	5.6	5.5	5.5	5.4	5.5	5.5	5.6
95°	9.2	9.1	9.0	10.6	13.9	17.1	20.3	23.5	20.3	17.1	13.9
97.5°	32.4	43.1	53.6	58.0	55.9	53.9	51.9	49.9	51.9	53.9	55.9
100°	45.0	58.1	71.2	76.9	75.2	73.5	71.7	70.0	71.7	73.5	75.2
102.5°	94.0	95.7	97.4	97.6	96.3	95.1	93.9	92.7	93.9	95.1	96.3
105°	132.3	131.9	131.4	130.8	130.3	129.7	129.1	128.6	129.1	129.7	130.3
107.5°	164.9	164.2	163.6	163.2	162.9	162.6	162.3	162.0	162.3	162.6	162.9
110°	187.3	186.6	186.1	185.7	185.4	185.1	184.8	184.5	184.8	185.1	185.4



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	209.3	209.2	208.9	208.5	207.9	207.5	206.9	206.4	206.9	207.5	207.9
115°	241.1	241.2	241.3	241.2	240.9	240.6	240.3	240.1	240.3	240.6	240.9
117.5°	272.6	272.4	272.2	271.9	271.5	271.2	270.8	270.4	270.8	271.2	271.5
120°	292.4	292.5	292.6	292.4	292.0	291.6	291.2	290.9	291.2	291.6	292.0
122.5°	311.4	311.2	311.1	310.9	310.8	310.5	310.3	310.0	310.3	310.5	310.8
125°	338.7	338.8	339.0	338.9	338.6	338.2	337.8	337.4	337.8	338.2	338.6
127.5°	365.0	364.5	364.1	363.8	363.7	363.6	363.5	363.4	363.5	363.6	363.7
130°	381.4	381.1	380.8	380.6	380.5	380.4	380.2	380.1	380.2	380.4	380.5
132.5°	397.2	396.9	396.5	396.2	396.1	395.9	395.7	395.6	395.7	395.9	396.1
135°	419.1	418.8	418.4	418.2	418.3	418.4	418.5	418.6	418.5	418.4	418.3
137.5°	440.3	439.8	439.4	439.2	439.1	439.1	439.0	439.0	439.0	439.1	439.1
140°	453.7	453.5	453.3	453.1	452.9	452.7	452.5	452.3	452.5	452.7	452.9
142.5°	466.2	466.0	465.9	465.7	465.3	465.1	464.7	464.3	464.7	465.1	465.3
145°	484.0	484.0	484.0	483.8	483.5	483.2	483.0	482.7	483.0	483.2	483.5
147.5°	499.5	499.5	499.6	499.5	498.9	498.3	497.9	497.3	497.9	498.3	498.9
150°	509.3	509.4	509.5	509.4	509.1	508.7	508.3	507.9	508.3	508.7	509.1
152.5°	517.7	517.9	518.0	518.0	517.6	517.4	517.1	516.8	517.1	517.4	517.6
155°	529.0	529.2	529.5	529.6	529.5	529.4	529.3	529.2	529.3	529.4	529.5
157.5°	538.7	539.0	539.3	539.5	539.6	539.6	539.7	539.8	539.7	539.6	539.6
160°	544.4	544.5	544.6	544.8	545.1	545.4	545.6	545.9	545.6	545.4	545.1
162.5°	549.5	549.6	549.7	550.0	550.3	550.6	551.0	551.4	551.0	550.6	550.3
165°	556.2	556.2	556.2	556.4	556.9	557.3	557.8	558.3	557.8	557.3	556.9
167.5°	561.4	561.5	561.5	561.8	562.3	562.8	563.3	563.7	563.3	562.8	562.3
170°	564.5	564.4	564.3	564.6	565.1	565.7	566.3	566.8	566.3	565.7	565.1
172.5°	566.6	566.5	566.4	566.7	567.2	567.8	568.4	568.9	568.4	567.8	567.2
175°	568.8	568.7	568.6	568.8	569.4	570.0	570.5	571.1	570.5	570.0	569.4
177.5°	570.1	570.0	569.9	570.0	570.5	571.1	571.7	572.1	571.7	571.1	570.5
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1588.0	1582.8	1576.0	1568.2	1558.9	1550.5	1546.9	1550.0	1551.5	1547.4	1546.9
5°	1539.7	1523.4	1510.3	1490.8	1475.2	1462.2	1453.0	1449.2	1450.4	1440.0	1437.4
7.5°	1485.4	1466.0	1444.7	1421.4	1399.9	1380.7	1370.6	1365.2	1354.2	1349.4	1341.5
10°	1450.4	1424.4	1403.5	1376.1	1351.4	1328.6	1317.5	1308.3	1297.3	1292.1	1281.0
12.5°	1414.5	1384.2	1361.3	1332.8	1307.6	1280.1	1269.5	1252.6	1235.3	1224.4	1210.1
15°	1363.8	1327.3	1299.3	1265.4	1235.4	1204.1	1176.1	1144.8	1133.1	1108.3	1094.0
17.5°	1304.5	1267.4	1232.8	1187.3	1141.0	1102.2	1072.3	1042.4	1024.4	1008.6	1001.4
20°	1265.4	1231.5	1183.3	1130.5	1079.0	1036.0	1011.9	992.4	972.8	961.8	953.9
22.5°	1228.3	1185.1	1129.1	1072.1	1020.7	987.0	966.6	946.5	930.6	920.0	909.6
25°	1166.3	1109.7	1050.4	985.2	950.0	920.7	898.5	882.2	872.5	858.8	853.6
27.5°	1102.6	1034.0	968.6	924.7	888.1	861.3	842.0	829.7	817.4	808.6	801.8
30°	1053.6	983.9	925.3	883.5	846.4	824.3	808.6	794.3	784.5	777.3	772.1
32.5°	1005.1	935.4	886.2	841.3	812.0	790.4	773.7	763.0	755.4	746.0	742.9
35°	935.0	873.1	830.1	789.8	759.8	740.2	727.2	716.0	709.5	707.0	705.0
37.5°	867.6	817.0	770.7	737.6	710.9	695.5	680.1	674.7	670.2	665.5	667.6
40°	824.9	777.3	736.3	701.1	679.6	662.7	653.6	647.1	643.1	643.1	643.1
42.5°	787.9	741.4	701.3	669.9	648.3	634.0	623.9	618.3	617.1	616.5	619.6
45°	730.5	687.4	647.1	620.9	602.8	588.3	582.5	578.0	578.0	580.6	581.2
47.5°	673.4	633.2	600.8	571.6	554.9	545.9	540.8	538.5	538.8	541.3	544.3
50°	638.6	598.8	566.8	540.8	525.2	516.7	512.2	510.9	512.2	512.2	516.7
52.5°	600.5	565.0	533.5	511.6	493.9	486.0	483.4	481.6	482.4	484.6	486.4
55°	544.7	512.8	482.9	461.9	448.9	443.7	437.9	438.5	437.2	438.5	438.5
57.5°	488.8	460.1	432.3	415.8	404.3	396.7	390.3	392.1	390.2	389.9	388.9
60°	452.9	421.6	399.4	384.5	371.4	364.9	359.0	360.3	358.4	357.0	354.5
62.5°	413.8	387.7	366.6	352.1	341.7	334.1	328.3	327.0	322.4	318.0	312.3
65°	357.0	335.5	316.7	303.0	293.2	287.4	282.8	278.9	269.1	258.6	253.4
67.5°	302.0	286.4	268.8	257.2	249.3	241.6	232.9	226.2	217.1	211.4	208.1
70°	266.5	251.5	236.5	225.5	217.0	209.8	200.0	195.5	189.0	186.3	183.1
72.5°	232.6	218.7	204.7	194.7	185.7	180.1	172.4	167.9	164.9	163.9	160.7
75°	181.2	170.0	159.7	150.5	143.4	139.4	136.2	132.9	131.6	125.7	122.5
77.5°	132.1	124.9	118.3	111.8	106.7	104.2	97.8	94.1	91.9	89.2	88.5
80°	102.9	97.7	91.2	87.3	80.1	77.6	74.9	74.3	73.6	73.0	72.3
82.5°	77.4	72.2	65.7	63.3	61.4	59.9	58.2	57.6	56.9	57.3	57.2
85°	39.1	36.5	36.5	35.8	35.2	34.5	33.8	33.8	33.3	33.8	33.3
87.5°	14.1	13.8	13.9	13.0	13.8	13.9	13.5	13.6	14.2	13.3	13.4
90°	5.5	6.3	7.2	7.9	8.7	9.4	10.0	10.6	11.1	11.7	12.1
92.5°	5.7	6.0	6.8	7.5	8.3	9.0	9.6	10.2	10.7	11.3	11.6
95°	10.6	9.0	9.1	9.2	9.3	9.4	10.0	10.6	11.1	11.7	12.0
97.5°	58.0	53.6	43.1	32.4	21.9	11.3	11.3	11.4	11.4	11.5	11.6
100°	76.9	71.2	58.1	45.0	31.9	18.8	17.2	15.6	13.9	12.3	11.6
102.5°	97.6	97.4	95.7	94.0	92.3	90.6	73.1	55.7	38.4	20.9	12.3
105°	130.8	131.4	131.9	132.3	132.8	133.3	134.1	135.0	135.8	136.7	135.4
107.5°	163.2	163.6	164.2	164.9	165.5	166.2	166.5	167.0	167.4	167.9	168.2
110°	185.7	186.1	186.6	187.3	187.8	188.4	188.6	188.8	189.0	189.2	189.4



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	208.5	208.9	209.2	209.3	209.6	209.9	209.9	209.8	209.8	209.7	209.9
115°	241.2	241.3	241.2	241.1	241.0	240.9	241.1	241.3	241.5	241.7	241.8
117.5°	271.9	272.2	272.4	272.6	272.9	273.1	273.0	273.0	273.0	272.9	272.9
120°	292.4	292.6	292.5	292.4	292.3	292.2	292.4	292.6	292.8	292.9	292.9
122.5°	310.9	311.1	311.2	311.4	311.5	311.7	311.8	311.9	312.0	312.1	312.1
125°	338.9	339.0	338.8	338.7	338.5	338.3	338.6	338.8	339.1	339.4	339.6
127.5°	363.8	364.1	364.5	365.0	365.4	365.8	365.8	365.7	365.6	365.6	365.5
130°	380.6	380.8	381.1	381.4	381.6	381.9	382.0	382.1	382.2	382.3	382.3
132.5°	396.2	396.5	396.9	397.2	397.6	397.9	398.0	398.1	398.2	398.3	398.3
135°	418.2	418.4	418.8	419.1	419.5	419.9	420.1	420.3	420.5	420.7	420.8
137.5°	439.2	439.4	439.8	440.3	440.6	441.1	441.3	441.5	441.7	442.0	442.0
140°	453.1	453.3	453.5	453.7	453.9	454.1	454.4	454.7	455.0	455.2	455.4
142.5°	465.7	465.9	466.0	466.2	466.3	466.4	466.6	466.7	467.0	467.2	467.3
145°	483.8	484.0	484.0	484.0	484.0	484.0	484.1	484.2	484.3	484.4	484.5
147.5°	499.5	499.6	499.5	499.5	499.4	499.3	499.4	499.5	499.5	499.5	499.6
150°	509.4	509.5	509.4	509.3	509.3	509.2	509.2	509.2	509.2	509.2	509.3
152.5°	518.0	518.0	517.9	517.7	517.6	517.4	517.6	517.6	517.8	518.0	518.0
155°	529.6	529.5	529.2	529.0	528.7	528.4	528.8	529.1	529.5	529.9	530.0
157.5°	539.5	539.3	539.0	538.7	538.4	538.1	538.6	539.0	539.5	540.0	540.0
160°	544.8	544.6	544.5	544.4	544.3	544.2	544.8	545.4	545.9	546.5	546.5
162.5°	550.0	549.7	549.6	549.5	549.4	549.3	549.9	550.4	551.0	551.6	551.6
165°	556.4	556.2	556.2	556.2	556.2	556.2	556.9	557.7	558.5	559.2	559.1
167.5°	561.8	561.5	561.5	561.4	561.4	561.3	562.1	563.0	563.8	564.7	564.6
170°	564.6	564.3	564.4	564.5	564.6	564.7	565.4	566.2	566.9	567.8	567.7
172.5°	566.7	566.4	566.5	566.6	566.7	566.8	567.5	568.3	569.0	569.8	569.7
175°	568.8	568.6	568.7	568.8	568.9	569.0	569.9	570.7	571.6	572.4	572.2
177.5°	570.0	569.9	570.0	570.1	570.2	570.4	571.0	571.7	572.2	572.9	572.7
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1543.7	1544.7	1541.2	1540.1	1541.2	1544.7	1543.7	1546.9	1547.4	1551.5	1550.0
5°	1432.2	1430.9	1427.6	1428.2	1427.6	1430.9	1432.2	1437.4	1440.0	1450.4	1449.2
7.5°	1336.8	1331.7	1333.1	1327.9	1333.1	1331.7	1336.8	1341.5	1349.4	1354.2	1365.2
10°	1278.4	1271.2	1265.4	1260.2	1265.4	1271.2	1278.4	1281.0	1292.1	1297.3	1308.3
12.5°	1198.6	1192.5	1184.6	1186.2	1184.6	1192.5	1198.6	1210.1	1224.4	1235.3	1252.6
15°	1085.5	1075.7	1060.2	1062.1	1060.2	1075.7	1085.5	1094.0	1108.3	1133.1	1144.8
17.5°	989.8	989.9	982.7	984.4	982.7	989.9	989.8	1001.4	1008.6	1024.4	1042.4
20°	940.3	935.7	936.3	934.3	936.3	935.7	940.3	953.9	961.8	972.8	992.4
22.5°	905.9	900.2	895.7	891.6	895.7	900.2	905.9	909.6	920.0	930.6	946.5
25°	847.7	843.8	837.9	836.6	837.9	843.8	847.7	853.6	858.8	872.5	882.2
27.5°	796.6	795.9	793.5	790.5	793.5	795.9	796.6	801.8	808.6	817.4	829.7
30°	766.9	765.6	764.3	762.3	764.3	765.6	766.9	772.1	777.3	784.5	794.3
32.5°	740.4	739.5	738.2	738.4	738.2	739.5	740.4	742.9	746.0	755.4	763.0
35°	702.4	701.7	700.5	699.8	700.5	701.7	702.4	705.0	707.0	709.5	716.0
37.5°	666.9	668.6	667.9	667.7	667.9	668.6	666.9	667.6	665.5	670.2	674.7
40°	642.4	643.1	644.4	643.8	644.4	643.1	642.4	643.1	643.1	643.1	647.1
42.5°	622.2	622.3	624.1	621.9	624.1	622.3	622.2	619.6	616.5	617.1	618.3
45°	585.8	589.7	589.0	589.0	589.0	589.7	585.8	581.2	580.6	578.0	578.0
47.5°	546.0	549.4	550.4	550.2	550.4	549.4	546.0	544.3	541.3	538.8	538.5
50°	520.0	518.7	520.7	520.0	520.7	518.7	520.0	516.7	512.2	512.2	510.9
52.5°	488.1	488.4	488.3	487.7	488.3	488.4	488.1	486.4	484.6	482.4	481.6
55°	439.1	439.8	438.5	439.1	438.5	439.8	439.1	438.5	438.5	437.2	438.5
57.5°	386.0	382.9	384.2	382.6	384.2	382.9	386.0	388.9	389.9	390.2	392.1
60°	348.0	342.7	341.4	338.8	341.4	342.7	348.0	354.5	357.0	358.4	360.3
62.5°	305.2	301.5	297.1	299.2	297.1	301.5	305.2	312.3	318.0	322.4	327.0
65°	248.3	245.6	243.6	246.3	243.6	245.6	248.3	253.4	258.6	269.1	278.9
67.5°	205.5	204.1	204.1	202.7	204.1	204.1	205.5	208.1	211.4	217.1	226.2
70°	183.1	181.2	181.2	179.8	181.2	181.2	183.1	183.1	186.3	189.0	195.5
72.5°	160.1	158.2	158.7	158.0	158.7	158.2	160.1	160.7	163.9	164.9	167.9
75°	118.6	115.4	115.4	116.0	115.4	115.4	118.6	122.5	125.7	131.6	132.9
77.5°	88.5	87.8	88.8	87.6	88.8	87.8	88.5	88.5	89.2	91.9	94.1
80°	72.3	71.6	71.1	73.0	71.1	71.6	72.3	72.3	73.0	73.6	74.3
82.5°	56.2	56.1	55.9	58.3	55.9	56.1	56.2	57.2	57.3	56.9	57.6
85°	33.8	32.6	33.8	32.6	33.8	32.6	33.8	33.3	33.8	33.3	33.8
87.5°	14.4	13.9	13.5	14.0	13.5	13.9	14.4	13.4	13.3	14.2	13.6
90°	12.3	12.4	12.6	12.8	12.6	12.4	12.3	12.1	11.7	11.1	10.6
92.5°	11.7	11.7	11.8	11.8	11.8	11.7	11.7	11.6	11.3	10.7	10.2
95°	12.1	12.2	12.3	12.3	12.3	12.2	12.1	12.0	11.7	11.1	10.6
97.5°	11.7	11.8	11.9	12.0	11.9	11.8	11.7	11.6	11.5	11.4	11.4
100°	11.7	11.8	11.9	12.0	11.9	11.8	11.7	11.6	12.3	13.9	15.6
102.5°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	20.9	38.4	55.7
105°	132.0	128.6	125.2	121.8	125.2	128.6	132.0	135.4	136.7	135.8	135.0
107.5°	168.6	168.9	169.3	169.7	169.3	168.9	168.6	168.2	167.9	167.4	167.0
110°	189.6	189.9	190.2	190.5	190.2	189.9	189.6	189.4	189.2	189.0	188.8



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	210.3	210.7	211.0	211.3	211.0	210.7	210.3	209.9	209.7	209.8	209.8
115°	241.8	241.8	241.8	241.8	241.8	241.8	241.8	241.8	241.7	241.5	241.3
117.5°	272.8	272.8	272.8	272.7	272.8	272.8	272.8	272.9	272.9	273.0	273.0
120°	292.8	292.6	292.4	292.2	292.4	292.6	292.8	292.9	292.9	292.8	292.6
122.5°	311.9	311.7	311.5	311.3	311.5	311.7	311.9	312.1	312.1	312.0	311.9
125°	339.7	339.8	339.9	340.0	339.9	339.8	339.7	339.6	339.4	339.1	338.8
127.5°	365.4	365.3	365.3	365.2	365.3	365.3	365.4	365.5	365.6	365.6	365.7
130°	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.2	382.1
132.5°	398.2	398.2	398.1	398.0	398.1	398.2	398.2	398.3	398.3	398.2	398.1
135°	421.0	421.2	421.4	421.6	421.4	421.2	421.0	420.8	420.7	420.5	420.3
137.5°	442.0	441.9	441.9	441.8	441.9	441.9	442.0	442.0	442.0	441.7	441.5
140°	455.5	455.6	455.7	455.8	455.7	455.6	455.5	455.4	455.2	455.0	454.7
142.5°	467.3	467.4	467.4	467.4	467.4	467.4	467.3	467.3	467.2	467.0	466.7
145°	484.7	484.8	485.0	485.2	485.0	484.8	484.7	484.5	484.4	484.3	484.2
147.5°	499.7	499.8	499.9	500.0	499.9	499.8	499.7	499.6	499.5	499.5	499.5
150°	509.3	509.4	509.5	509.6	509.5	509.4	509.3	509.3	509.2	509.2	509.2
152.5°	518.0	517.9	517.8	517.8	517.8	517.9	518.0	518.0	518.0	517.8	517.6
155°	529.7	529.4	529.1	528.9	529.1	529.4	529.7	530.0	529.9	529.5	529.1
157.5°	539.5	539.0	538.6	538.1	538.6	539.0	539.5	540.0	540.0	539.5	539.0
160°	545.9	545.4	544.8	544.2	544.8	545.4	545.9	546.5	546.5	545.9	545.4
162.5°	550.9	550.3	549.6	549.0	549.6	550.3	550.9	551.6	551.6	551.0	550.4
165°	558.3	557.4	556.6	555.7	556.6	557.4	558.3	559.1	559.2	558.5	557.7
167.5°	563.6	562.7	561.8	560.8	561.8	562.7	563.6	564.6	564.7	563.8	563.0
170°	566.7	565.7	564.8	563.8	564.8	565.7	566.7	567.7	567.8	566.9	566.2
172.5°	568.6	567.6	566.6	565.5	566.6	567.6	568.6	569.7	569.8	569.0	568.3
175°	571.1	570.0	568.8	567.7	568.8	570.0	571.1	572.2	572.4	571.6	570.7
177.5°	571.8	570.9	570.0	569.1	570.0	570.9	571.8	572.7	572.9	572.2	571.7
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1546.9	1550.5	1558.9	1568.2	1576.0	1582.8	1588.0	1595.3	1602.1	1611.5	1620.3
5°	1453.0	1462.2	1475.2	1490.8	1510.3	1523.4	1539.7	1554.1	1574.9	1595.7	1615.9
7.5°	1370.6	1380.7	1399.9	1421.4	1444.7	1466.0	1485.4	1510.6	1538.2	1568.6	1602.5
10°	1317.5	1328.6	1351.4	1376.1	1403.5	1424.4	1450.4	1480.4	1511.6	1548.8	1590.5
12.5°	1269.5	1280.1	1307.6	1332.8	1361.3	1384.2	1414.5	1444.9	1486.7	1526.9	1574.3
15°	1176.1	1204.1	1235.4	1265.4	1299.3	1327.3	1363.8	1395.1	1434.8	1491.5	1545.6
17.5°	1072.3	1102.2	1141.0	1187.3	1232.8	1267.4	1304.5	1343.3	1390.6	1448.5	1510.9
20°	1011.9	1036.0	1079.0	1130.5	1183.3	1231.5	1265.4	1308.3	1357.3	1419.8	1484.3
22.5°	966.6	987.0	1020.7	1072.1	1129.1	1185.1	1228.3	1270.8	1324.9	1387.5	1457.7
25°	898.5	920.7	950.0	985.2	1050.4	1109.7	1166.3	1215.2	1272.5	1335.1	1413.2
27.5°	842.0	861.3	888.1	924.7	968.6	1034.0	1102.6	1158.4	1217.2	1284.3	1362.6
30°	808.6	824.3	846.4	883.5	925.3	983.9	1053.6	1118.8	1178.1	1247.7	1329.3
32.5°	773.7	790.4	812.0	841.3	886.2	935.4	1005.1	1076.6	1139.5	1210.8	1290.6
35°	727.2	740.2	759.8	789.8	830.1	873.1	935.0	1008.6	1075.2	1151.3	1227.6
37.5°	680.1	695.5	710.9	737.6	770.7	817.0	867.6	942.8	1016.4	1086.1	1160.5
40°	653.6	662.7	679.6	701.1	736.3	777.3	824.9	898.5	972.1	1041.2	1116.2
42.5°	623.9	634.0	648.3	669.9	701.3	741.4	787.9	851.6	928.4	995.3	1063.5
45°	582.5	588.3	602.8	620.9	647.1	687.4	730.5	787.1	859.4	923.3	983.3
47.5°	540.8	545.9	554.9	571.6	600.8	633.2	673.4	724.3	787.8	851.6	902.3
50°	512.2	516.7	525.2	540.8	566.8	598.8	638.6	684.2	740.8	802.1	844.4
52.5°	483.4	486.0	493.9	511.6	533.5	565.0	600.5	642.4	695.5	746.3	789.2
55°	437.9	443.7	448.9	461.9	482.9	512.8	544.7	584.5	625.6	668.5	705.0
57.5°	390.3	396.7	404.3	415.8	432.3	460.1	488.8	521.0	556.1	591.7	622.4
60°	359.0	364.9	371.4	384.5	399.4	421.6	452.9	480.9	507.6	540.2	570.8
62.5°	328.3	334.1	341.7	352.1	366.6	387.7	413.8	438.1	465.9	494.3	517.1
65°	282.8	287.4	293.2	303.0	316.7	335.5	357.0	376.0	400.8	421.6	442.4
67.5°	232.9	241.6	249.3	257.2	268.8	286.4	302.0	320.1	336.9	352.4	371.4
70°	200.0	209.8	217.0	225.5	236.5	251.5	266.5	278.9	292.6	307.6	324.5
72.5°	172.4	180.1	185.7	194.7	204.7	218.7	232.6	242.9	254.0	264.3	280.7
75°	136.2	139.4	143.4	150.5	159.7	170.0	181.2	190.3	196.8	205.9	217.6
77.5°	97.8	104.2	106.7	111.8	118.3	124.9	132.1	139.9	146.1	149.3	158.3
80°	74.9	77.6	80.1	87.3	91.2	97.7	102.9	110.1	112.7	116.0	124.4
82.5°	58.2	59.9	61.4	63.3	65.7	72.2	77.4	82.0	84.5	85.8	92.2
85°	33.8	34.5	35.2	35.8	36.5	36.5	39.1	42.3	46.9	46.9	48.8
87.5°	13.5	13.9	13.8	13.0	13.9	13.8	14.1	13.9	15.3	16.6	18.0
90°	10.0	9.4	8.7	7.9	7.2	6.3	5.5	4.4	3.4	2.4	1.3
92.5°	9.6	9.0	8.3	7.5	6.8	6.0	5.7	5.6	5.5	5.5	5.4
95°	10.0	9.4	9.3	9.2	9.1	9.0	10.6	13.9	17.1	20.3	23.5
97.5°	11.3	11.3	21.9	32.4	43.1	53.6	58.0	55.9	53.9	51.9	49.9
100°	17.2	18.8	31.9	45.0	58.1	71.2	76.9	75.2	73.5	71.7	70.0
102.5°	73.1	90.6	92.3	94.0	95.7	97.4	97.6	96.3	95.1	93.9	92.7
105°	134.1	133.3	132.8	132.3	131.9	131.4	130.8	130.3	129.7	129.1	128.6
107.5°	166.5	166.2	165.5	164.9	164.2	163.6	163.2	162.9	162.6	162.3	162.0
110°	188.6	188.4	187.8	187.3	186.6	186.1	185.7	185.4	185.1	184.8	184.5



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	209.9	209.9	209.6	209.3	209.2	208.9	208.5	207.9	207.5	206.9	206.4
115°	241.1	240.9	241.0	241.1	241.2	241.3	241.2	240.9	240.6	240.3	240.1
117.5°	273.0	273.1	272.9	272.6	272.4	272.2	271.9	271.5	271.2	270.8	270.4
120°	292.4	292.2	292.3	292.4	292.5	292.6	292.4	292.0	291.6	291.2	290.9
122.5°	311.8	311.7	311.5	311.4	311.2	311.1	310.9	310.8	310.5	310.3	310.0
125°	338.6	338.3	338.5	338.7	338.8	339.0	338.9	338.6	338.2	337.8	337.4
127.5°	365.8	365.8	365.4	365.0	364.5	364.1	363.8	363.7	363.6	363.5	363.4
130°	382.0	381.9	381.6	381.4	381.1	380.8	380.6	380.5	380.4	380.2	380.1
132.5°	398.0	397.9	397.6	397.2	396.9	396.5	396.2	396.1	395.9	395.7	395.6
135°	420.1	419.9	419.5	419.1	418.8	418.4	418.2	418.3	418.4	418.5	418.6
137.5°	441.3	441.1	440.6	440.3	439.8	439.4	439.2	439.1	439.1	439.0	439.0
140°	454.4	454.1	453.9	453.7	453.5	453.3	453.1	452.9	452.7	452.5	452.3
142.5°	466.6	466.4	466.3	466.2	466.0	465.9	465.7	465.3	465.1	464.7	464.3
145°	484.1	484.0	484.0	484.0	484.0	484.0	483.8	483.5	483.2	483.0	482.7
147.5°	499.4	499.3	499.4	499.5	499.5	499.6	499.5	498.9	498.3	497.9	497.3
150°	509.2	509.2	509.3	509.3	509.4	509.5	509.4	509.1	508.7	508.3	507.9
152.5°	517.6	517.4	517.6	517.7	517.9	518.0	518.0	517.6	517.4	517.1	516.8
155°	528.8	528.4	528.7	529.0	529.2	529.5	529.6	529.5	529.4	529.3	529.2
157.5°	538.6	538.1	538.4	538.7	539.0	539.3	539.5	539.6	539.6	539.7	539.8
160°	544.8	544.2	544.3	544.4	544.5	544.6	544.8	545.1	545.4	545.6	545.9
162.5°	549.9	549.3	549.4	549.5	549.6	549.7	550.0	550.3	550.6	551.0	551.4
165°	556.9	556.2	556.2	556.2	556.2	556.2	556.4	556.9	557.3	557.8	558.3
167.5°	562.1	561.3	561.4	561.4	561.5	561.5	561.8	562.3	562.8	563.3	563.7
170°	565.4	564.7	564.6	564.5	564.4	564.3	564.6	565.1	565.7	566.3	566.8
172.5°	567.5	566.8	566.7	566.6	566.5	566.4	566.7	567.2	567.8	568.4	568.9
175°	569.9	569.0	568.9	568.8	568.7	568.6	568.8	569.4	570.0	570.5	571.1
177.5°	571.0	570.4	570.2	570.1	570.0	569.9	570.0	570.5	571.1	571.7	572.1
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1627.1	1631.8	1637.0	1646.9	1655.3	1659.0	1666.2	1671.4	1669.9	1677.2	1689.7
5°	1633.5	1651.1	1671.3	1692.1	1715.6	1735.1	1750.8	1766.4	1778.9	1793.8	1816.0
7.5°	1632.5	1663.8	1697.8	1735.1	1773.6	1806.9	1837.6	1868.9	1896.6	1927.0	1966.7
10°	1628.3	1670.0	1712.3	1761.2	1810.1	1856.3	1898.1	1937.1	1974.3	2014.0	2064.3
12.5°	1623.6	1671.6	1722.8	1781.6	1842.4	1898.1	1947.1	2003.4	2049.8	2101.1	2159.1
15°	1602.9	1667.4	1737.1	1813.4	1886.3	1961.2	2028.4	2097.4	2161.9	2223.2	2296.2
17.5°	1579.1	1653.6	1735.8	1825.9	1913.5	2004.7	2084.2	2171.3	2237.3	2319.5	2387.3
20°	1559.9	1640.0	1728.0	1829.0	1928.7	2029.7	2117.6	2206.3	2280.6	2363.3	2449.3
22.5°	1536.4	1624.4	1719.7	1824.3	1928.7	2039.1	2136.4	2224.5	2316.5	2409.7	2498.3
25°	1498.6	1589.9	1690.8	1805.5	1925.4	2038.2	2142.4	2251.8	2350.9	2451.9	2531.4
27.5°	1452.3	1548.0	1654.5	1772.8	1895.8	2011.3	2134.1	2250.7	2350.4	2447.6	2517.0
30°	1415.2	1516.3	1618.5	1738.4	1866.1	1989.9	2121.6	2238.2	2343.1	2430.4	2469.5
32.5°	1377.1	1473.0	1578.4	1699.9	1830.7	1963.9	2094.4	2213.7	2310.7	2363.1	2364.2
35°	1311.0	1400.9	1510.3	1629.7	1763.9	1908.5	2040.8	2158.0	2217.3	2221.9	2158.0
37.5°	1238.8	1321.3	1424.7	1544.0	1691.0	1834.8	1970.0	2048.1	2068.0	2001.7	1883.6
40°	1187.2	1263.4	1363.1	1485.6	1631.5	1780.1	1903.3	1960.6	1939.8	1832.2	1700.6
42.5°	1132.9	1204.0	1300.0	1421.0	1567.4	1717.6	1822.5	1853.2	1798.0	1673.8	1519.8
45°	1044.5	1109.7	1204.8	1326.6	1467.4	1608.1	1687.6	1672.0	1580.1	1432.9	1260.2
47.5°	952.3	1015.3	1100.9	1213.6	1357.7	1479.2	1533.0	1485.9	1355.2	1193.2	1052.7
50°	891.4	955.8	1034.7	1142.3	1273.8	1391.1	1425.7	1354.0	1208.7	1052.9	924.0
52.5°	831.4	886.6	963.8	1067.7	1193.5	1292.6	1311.0	1228.3	1078.4	938.8	824.3
55°	740.2	790.4	855.5	953.3	1062.1	1146.1	1136.3	1030.2	894.0	774.8	684.9
57.5°	652.0	689.8	750.0	841.6	937.1	993.5	957.8	867.2	740.4	642.7	566.8
60°	593.6	628.8	684.9	765.0	849.0	880.9	850.9	752.6	652.2	563.0	499.1
62.5°	538.4	569.4	617.6	692.0	759.9	778.7	746.7	660.8	570.4	494.2	441.3
65°	458.1	486.7	527.8	580.6	627.5	636.6	615.8	527.8	459.4	395.5	359.0
67.5°	385.2	404.0	436.0	481.6	506.5	511.9	471.6	416.3	356.0	316.8	289.3
70°	336.2	349.2	379.2	404.0	424.1	424.8	387.7	343.4	297.1	265.2	245.0
72.5°	288.8	301.3	324.0	340.9	356.4	351.4	317.4	282.4	245.0	220.9	205.9
75°	222.8	233.9	245.6	253.4	253.4	246.9	222.2	196.1	174.7	160.3	155.7
77.5°	162.0	171.1	175.0	173.8	171.5	161.4	145.7	128.7	120.9	114.1	110.7
80°	127.1	131.0	132.2	129.0	125.1	113.4	102.9	95.8	88.6	86.1	84.7
82.5°	94.3	97.6	94.3	95.1	86.5	76.9	71.2	68.7	65.7	64.7	63.3
85°	50.1	49.5	48.3	45.0	39.1	37.8	37.1	36.5	35.2	35.8	34.5
87.5°	17.6	16.3	14.4	14.1	14.3	13.4	14.0	14.2	14.4	13.9	15.2
90°	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0	10.6
92.5°	5.5	5.5	5.6	5.7	6.0	6.8	7.5	8.3	9.0	9.6	10.2
95°	20.3	17.1	13.9	10.6	9.0	9.1	9.2	9.3	9.4	10.0	10.6
97.5°	51.9	53.9	55.9	58.0	53.6	43.1	32.4	21.9	11.3	11.3	11.4
100°	71.7	73.5	75.2	76.9	71.2	58.1	45.0	31.9	18.8	17.2	15.6
102.5°	93.9	95.1	96.3	97.6	97.4	95.7	94.0	92.3	90.6	73.1	55.7
105°	129.1	129.7	130.3	130.8	131.4	131.9	132.3	132.8	133.3	134.1	135.0
107.5°	162.3	162.6	162.9	163.2	163.6	164.2	164.9	165.5	166.2	166.5	167.0
110°	184.8	185.1	185.4	185.7	186.1	186.6	187.3	187.8	188.4	188.6	188.8



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	206.9	207.5	207.9	208.5	208.9	209.2	209.3	209.6	209.9	209.9	209.8
115°	240.3	240.6	240.9	241.2	241.3	241.2	241.1	241.0	240.9	241.1	241.3
117.5°	270.8	271.2	271.5	271.9	272.2	272.4	272.6	272.9	273.1	273.0	273.0
120°	291.2	291.6	292.0	292.4	292.6	292.5	292.4	292.3	292.2	292.4	292.6
122.5°	310.3	310.5	310.8	310.9	311.1	311.2	311.4	311.5	311.7	311.8	311.9
125°	337.8	338.2	338.6	338.9	339.0	338.8	338.7	338.5	338.3	338.6	338.8
127.5°	363.5	363.6	363.7	363.8	364.1	364.5	365.0	365.4	365.8	365.8	365.7
130°	380.2	380.4	380.5	380.6	380.8	381.1	381.4	381.6	381.9	382.0	382.1
132.5°	395.7	395.9	396.1	396.2	396.5	396.9	397.2	397.6	397.9	398.0	398.1
135°	418.5	418.4	418.3	418.2	418.4	418.8	419.1	419.5	419.9	420.1	420.3
137.5°	439.0	439.1	439.1	439.2	439.4	439.8	440.3	440.6	441.1	441.3	441.5
140°	452.5	452.7	452.9	453.1	453.3	453.5	453.7	453.9	454.1	454.4	454.7
142.5°	464.7	465.1	465.3	465.7	465.9	466.0	466.2	466.3	466.4	466.6	466.7
145°	483.0	483.2	483.5	483.8	484.0	484.0	484.0	484.0	484.0	484.1	484.2
147.5°	497.9	498.3	498.9	499.5	499.6	499.5	499.5	499.4	499.3	499.4	499.5
150°	508.3	508.7	509.1	509.4	509.5	509.4	509.3	509.3	509.2	509.2	509.2
152.5°	517.1	517.4	517.6	518.0	518.0	517.9	517.7	517.6	517.4	517.6	517.6
155°	529.3	529.4	529.5	529.6	529.5	529.2	529.0	528.7	528.4	528.8	529.1
157.5°	539.7	539.6	539.6	539.5	539.3	539.0	538.7	538.4	538.1	538.6	539.0
160°	545.6	545.4	545.1	544.8	544.6	544.5	544.4	544.3	544.2	544.8	545.4
162.5°	551.0	550.6	550.3	550.0	549.7	549.6	549.5	549.4	549.3	549.9	550.4
165°	557.8	557.3	556.9	556.4	556.2	556.2	556.2	556.2	556.2	556.9	557.7
167.5°	563.3	562.8	562.3	561.8	561.5	561.5	561.4	561.4	561.3	562.1	563.0
170°	566.3	565.7	565.1	564.6	564.3	564.4	564.5	564.6	564.7	565.4	566.2
172.5°	568.4	567.8	567.2	566.7	566.4	566.5	566.6	566.7	566.8	567.5	568.3
175°	570.5	570.0	569.4	568.8	568.6	568.7	568.8	568.9	569.0	569.9	570.7
177.5°	571.7	571.1	570.5	570.0	569.9	570.0	570.1	570.2	570.4	571.0	571.7
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1696.5	1698.6	1700.2	1705.3	1705.8	1710.5	1705.8
5°	1836.8	1846.0	1860.3	1874.6	1875.9	1885.0	1868.8
7.5°	1994.2	2015.3	2028.5	2051.7	2060.9	2066.5	2057.2
10°	2102.6	2122.2	2156.7	2173.7	2190.7	2193.2	2185.4
12.5°	2207.4	2238.4	2265.7	2297.7	2297.0	2319.9	2311.6
15°	2347.0	2379.0	2416.7	2452.6	2465.6	2465.6	2476.1
17.5°	2446.6	2505.1	2544.2	2572.3	2603.1	2608.4	2604.8
20°	2513.9	2577.0	2618.8	2655.2	2676.1	2681.9	2681.9
22.5°	2563.8	2617.6	2658.3	2691.1	2708.4	2715.3	2713.2
25°	2598.5	2644.8	2669.6	2679.3	2683.9	2682.6	2670.2
27.5°	2551.1	2549.0	2533.4	2503.4	2480.9	2467.2	2451.6
30°	2460.4	2426.5	2387.4	2344.4	2289.1	2246.6	2233.6
32.5°	2325.3	2249.3	2183.0	2111.4	2051.8	2009.5	1991.8
35°	2064.3	1943.7	1845.3	1759.3	1696.8	1657.6	1644.6
37.5°	1754.4	1637.7	1515.9	1432.5	1380.5	1341.0	1326.3
40°	1557.3	1430.2	1324.0	1245.9	1192.4	1154.0	1153.3
42.5°	1377.4	1256.1	1156.2	1099.9	1042.3	1016.8	1016.7
45°	1127.8	1030.8	946.1	901.8	867.2	846.4	840.6
47.5°	933.9	853.6	797.1	761.9	733.7	720.4	711.8
50°	824.9	754.5	709.5	678.9	663.3	646.4	645.1
52.5°	734.2	677.4	642.3	617.5	597.7	587.5	587.8
55°	617.1	572.1	547.3	528.4	512.8	505.0	501.7
57.5°	519.8	486.1	468.1	450.7	444.1	438.0	436.3
60°	459.4	436.6	419.6	406.0	396.2	394.2	393.5
62.5°	409.3	385.5	373.7	363.2	356.0	353.0	351.9
65°	337.5	319.9	309.5	301.0	298.4	293.9	293.2
67.5°	272.1	261.6	254.7	248.7	245.2	245.0	245.0
70°	232.0	226.1	220.3	217.0	215.0	213.7	213.7
72.5°	197.6	193.2	188.4	186.7	186.3	185.0	184.5
75°	150.5	146.0	146.6	143.4	140.7	137.5	135.5
77.5°	106.7	103.5	102.8	102.5	100.2	99.8	100.9
80°	82.8	79.5	78.8	79.5	78.8	76.9	76.9
82.5°	63.0	60.2	59.6	59.2	58.5	59.2	58.2
85°	33.8	32.6	32.6	32.6	33.8	33.3	32.6
87.5°	14.2	13.8	14.4	13.9	13.9	13.5	14.0
90°	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	10.7	11.3	11.6	11.7	11.7	11.8	11.8
95°	11.1	11.7	12.0	12.1	12.2	12.3	12.3
97.5°	11.4	11.5	11.6	11.7	11.8	11.9	12.0
100°	13.9	12.3	11.6	11.7	11.8	11.9	12.0
102.5°	38.4	20.9	12.3	12.3	12.3	12.3	12.3
105°	135.8	136.7	135.4	132.0	128.6	125.2	121.8
107.5°	167.4	167.9	168.2	168.6	168.9	169.3	169.7
110°	189.0	189.2	189.4	189.6	189.9	190.2	190.5



TEST NUMBER: P333075-830

CATALOG NUMBER: S124RDIW-S1020D470U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	209.8	209.7	209.9	210.3	210.7	211.0	211.3
115°	241.5	241.7	241.8	241.8	241.8	241.8	241.8
117.5°	273.0	272.9	272.9	272.8	272.8	272.8	272.7
120°	292.8	292.9	292.9	292.8	292.6	292.4	292.2
122.5°	312.0	312.1	312.1	311.9	311.7	311.5	311.3
125°	339.1	339.4	339.6	339.7	339.8	339.9	340.0
127.5°	365.6	365.6	365.5	365.4	365.3	365.3	365.2
130°	382.2	382.3	382.3	382.3	382.3	382.3	382.3
132.5°	398.2	398.3	398.3	398.2	398.2	398.1	398.0
135°	420.5	420.7	420.8	421.0	421.2	421.4	421.6
137.5°	441.7	442.0	442.0	442.0	441.9	441.9	441.8
140°	455.0	455.2	455.4	455.5	455.6	455.7	455.8
142.5°	467.0	467.2	467.3	467.3	467.4	467.4	467.4
145°	484.3	484.4	484.5	484.7	484.8	485.0	485.2
147.5°	499.5	499.5	499.6	499.7	499.8	499.9	500.0
150°	509.2	509.2	509.3	509.3	509.4	509.5	509.6
152.5°	517.8	518.0	518.0	518.0	517.9	517.8	517.8
155°	529.5	529.9	530.0	529.7	529.4	529.1	528.9
157.5°	539.5	540.0	540.0	539.5	539.0	538.6	538.1
160°	545.9	546.5	546.5	545.9	545.4	544.8	544.2
162.5°	551.0	551.6	551.6	550.9	550.3	549.6	549.0
165°	558.5	559.2	559.1	558.3	557.4	556.6	555.7
167.5°	563.8	564.7	564.6	563.6	562.7	561.8	560.8
170°	566.9	567.8	567.7	566.7	565.7	564.8	563.8
172.5°	569.0	569.8	569.7	568.6	567.6	566.6	565.5
175°	571.6	572.4	572.2	571.1	570.0	568.8	567.7
177.5°	572.2	572.9	572.7	571.8	570.9	570.0	569.1
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1

(END OF REPORT)