

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333079-830

Luminaire Tested: **S124RDIW-S1020D770U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333079-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D770U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6984.2 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55	50
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41	37
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	36	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	32	27	34	29	25	30	26	22	27	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13056	13056	13056	13056
5°	15144	13095	11574	13095
10°	17915	13038	10330	13038
15°	20695	12918	8877	12918
20°	23040	12752	8027	12752
25°	23785	12588	7452	12588
30°	20821	12392	7106	12392
35°	16208	12098	6897	12098
40°	12154	11763	6785	11763
45°	9597	11226	6725	11226
50°	8102	10605	6531	10605
55°	7061	9923	6180	9923
60°	6353	9216	5470	9216
65°	5601	8451	4705	8451
70°	5044	7659	4244	7659
75°	4226	6787	3618	6787
80°	3575	5783	3394	5783
85°	3020	4520	3020	4520



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	2.2
10°-20°	472.7	6.8
20°-30°	739.3	10.6
30°-40°	821.9	11.8
40°-50°	729.2	10.4
50°-60°	568.2	8.1
60°-70°	372.0	5.3
70°-80°	182.9	2.6
80°-90°	47.8	0.7
90°-100°	32.0	0.5
100°-110°	204.0	2.9
110°-120°	390.2	5.6
120°-130°	495.4	7.1
130°-140°	530.0	7.6
140°-150°	495.6	7.1
150°-160°	399.7	5.7
160°-170°	257.8	3.7
170°-180°	88.8	1.3
0°-30°	1368.7	19.6
0°-40°	2190.5	31.4
0°-60°	3487.9	49.9
0°-90°	4090.7	58.6
90°-120°	626.2	9.0
90°-150°	2147.2	30.7
90°-180°	2894.0	41.4
0°-180°	6984.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1617	1617	1617	1617	1617	
5°	1869	1616	1428	1616	1869	189
15°	2476	1546	1062	1546	2476	704
25°	2670	1413	837	1413	2670	1185
35°	1645	1228	700	1228	1645	1031
45°	841	983	589	983	841	666
55°	502	705	439	705	502	456
65°	293	442	246	442	293	295
75°	136	218	116	218	136	149
85°	33	49	33	49	33	37
90°	21	2	21	2	21	11
95°	20	38	20	38	20	16
105°	199	211	199	211	199	174
115°	396	393	396	393	396	392
125°	557	553	557	553	557	496
135°	690	686	690	686	690	532
145°	795	791	795	791	795	497
155°	866	867	866	867	866	399
165°	910	914	910	914	910	257
175°	930	935	930	935	930	89
180°	935	935	935	935	935	



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1705.8	1710.5	1705.8	1705.3	1700.2	1698.6	1696.5	1689.7	1677.2	1669.9	1671.4
5°	1868.8	1885.0	1875.9	1874.6	1860.3	1846.0	1836.8	1816.0	1793.8	1778.9	1766.4
7.5°	2057.2	2066.5	2060.9	2051.7	2028.5	2015.3	1994.2	1966.7	1927.0	1896.6	1868.9
10°	2185.4	2193.2	2190.7	2173.7	2156.7	2122.2	2102.6	2064.3	2014.0	1974.3	1937.1
12.5°	2311.6	2319.9	2297.0	2297.7	2265.7	2238.4	2207.4	2159.1	2101.1	2049.8	2003.4
15°	2476.1	2465.6	2465.6	2452.6	2416.7	2379.0	2347.0	2296.2	2223.2	2161.9	2097.4
17.5°	2604.8	2608.4	2603.1	2572.3	2544.2	2505.1	2446.6	2387.3	2319.5	2237.3	2171.3
20°	2681.9	2681.9	2676.1	2655.2	2618.8	2577.0	2513.9	2449.3	2363.3	2280.6	2206.3
22.5°	2713.2	2715.3	2708.4	2691.1	2658.3	2617.6	2563.8	2498.3	2409.7	2316.5	2224.5
25°	2670.2	2682.6	2683.9	2679.3	2669.6	2644.8	2598.5	2531.4	2451.9	2350.9	2251.8
27.5°	2451.6	2467.2	2480.9	2503.4	2533.4	2549.0	2551.1	2517.0	2447.6	2350.4	2250.7
30°	2233.6	2246.6	2289.1	2344.4	2387.4	2426.5	2460.4	2469.5	2430.4	2343.1	2238.2
32.5°	1991.8	2009.5	2051.8	2111.4	2183.0	2249.3	2325.3	2364.2	2363.1	2310.7	2213.7
35°	1644.6	1657.6	1696.8	1759.3	1845.3	1943.7	2064.3	2158.0	2221.9	2217.3	2158.0
37.5°	1326.3	1341.0	1380.5	1432.5	1515.9	1637.7	1754.4	1883.6	2001.7	2068.0	2048.1
40°	1153.3	1154.0	1192.4	1245.9	1324.0	1430.2	1557.3	1700.6	1832.2	1939.8	1960.6
42.5°	1016.7	1016.8	1042.3	1099.9	1156.2	1256.1	1377.4	1519.8	1673.8	1798.0	1853.2
45°	840.6	846.4	867.2	901.8	946.1	1030.8	1127.8	1260.2	1432.9	1580.1	1672.0
47.5°	711.8	720.4	733.7	761.9	797.1	853.6	933.9	1052.7	1193.2	1355.2	1485.9
50°	645.1	646.4	663.3	678.9	709.5	754.5	824.9	924.0	1052.9	1208.7	1354.0
52.5°	587.8	587.5	597.7	617.5	642.3	677.4	734.2	824.3	938.8	1078.4	1228.3
55°	501.7	505.0	512.8	528.4	547.3	572.1	617.1	684.9	774.8	894.0	1030.2
57.5°	436.3	438.0	444.1	450.7	468.1	486.1	519.8	566.8	642.7	740.4	867.2
60°	393.5	394.2	396.2	406.0	419.6	436.6	459.4	499.1	563.0	652.2	752.6
62.5°	351.9	353.0	356.0	363.2	373.7	385.5	409.3	441.3	494.2	570.4	660.8
65°	293.2	293.9	298.4	301.0	309.5	319.9	337.5	359.0	395.5	459.4	527.8
67.5°	245.0	245.0	245.2	248.7	254.7	261.6	272.1	289.3	316.8	356.0	416.3
70°	213.7	213.7	215.0	217.0	220.3	226.1	232.0	245.0	265.2	297.1	343.4
72.5°	184.5	185.0	186.3	186.7	188.4	193.2	197.6	205.9	220.9	245.0	282.4
75°	135.5	137.5	140.7	143.4	146.6	146.0	150.5	155.7	160.3	174.7	196.1
77.5°	100.9	99.8	100.2	102.5	102.8	103.5	106.7	110.7	114.1	120.9	128.7
80°	76.9	76.9	78.8	79.5	78.8	79.5	82.8	84.7	86.1	88.6	95.8
82.5°	58.2	59.2	58.5	59.2	59.6	60.2	63.0	63.3	64.7	65.7	68.7
85°	32.6	33.3	33.8	32.6	32.6	32.6	33.8	34.5	35.8	35.2	36.5
87.5°	15.6	15.1	15.6	15.5	15.9	15.3	15.6	16.5	15.3	15.6	15.4
90°	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2	16.3	15.4	14.1
92.5°	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7	15.7	14.8	13.6
95°	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2	16.3	15.4	15.3
97.5°	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6	18.5	35.8
100°	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5	28.2	30.8	52.2
102.5°	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3	119.8	148.4	151.1
105°	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1	219.7	218.3	217.5
107.5°	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5	272.9	272.1	271.1
110°	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2	308.9	308.5	307.6



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7	343.7	343.8	343.4
115°	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2	394.9	394.5	394.7
117.5°	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0	447.1	447.2	446.9
120°	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5	478.7
122.5°	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9	510.7	510.5	510.2
125°	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1	554.6	554.1	554.4
127.5°	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0	599.1	599.2	598.4
130°	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8	625.7	625.5	625.0
132.5°	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1	652.0	651.8	651.2
135°	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3	688.1	687.8	687.1
137.5°	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1	722.7	722.5	721.8
140°	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6	744.1	743.8	743.4
142.5°	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6	764.2	763.8	763.6
145°	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0	792.9	792.7	792.7
147.5°	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9	817.8	817.7	817.8
150°	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0	834.0	834.0	834.2
152.5°	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9	847.6	847.4	847.7
155°	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7	866.1	865.4	865.9
157.5°	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3	881.7
160°	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4	891.5
162.5°	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6	900.7	899.8	899.8
165°	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4	912.2	911.0	911.0
167.5°	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1	920.7	919.4	919.5
170°	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4	926.1	924.9	924.7
172.5°	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8	929.5	928.3	928.1
175°	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7	933.3	931.9	931.8
177.5°	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3	935.3	934.2	934.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1666.2	1659.0	1655.3	1646.9	1637.0	1631.8	1627.1	1620.3	1611.5	1602.1	1595.3
5°	1750.8	1735.1	1715.6	1692.1	1671.3	1651.1	1633.5	1615.9	1595.7	1574.9	1554.1
7.5°	1837.6	1806.9	1773.6	1735.1	1697.8	1663.8	1632.5	1602.5	1568.6	1538.2	1510.6
10°	1898.1	1856.3	1810.1	1761.2	1712.3	1670.0	1628.3	1590.5	1548.8	1511.6	1480.4
12.5°	1947.1	1898.1	1842.4	1781.6	1722.8	1671.6	1623.6	1574.3	1526.9	1486.7	1444.9
15°	2028.4	1961.2	1886.3	1813.4	1737.1	1667.4	1602.9	1545.6	1491.5	1434.8	1395.1
17.5°	2084.2	2004.7	1913.5	1825.9	1735.8	1653.6	1579.1	1510.9	1448.5	1390.6	1343.3
20°	2117.6	2029.7	1928.7	1829.0	1728.0	1640.0	1559.9	1484.3	1419.8	1357.3	1308.3
22.5°	2136.4	2039.1	1928.7	1824.3	1719.7	1624.4	1536.4	1457.7	1387.5	1324.9	1270.8
25°	2142.4	2038.2	1925.4	1805.5	1690.8	1589.9	1498.6	1413.2	1335.1	1272.5	1215.2
27.5°	2134.1	2011.3	1895.8	1772.8	1654.5	1548.0	1452.3	1362.6	1284.3	1217.2	1158.4
30°	2121.6	1989.9	1866.1	1738.4	1618.5	1516.3	1415.2	1329.3	1247.7	1178.1	1118.8
32.5°	2094.4	1963.9	1830.7	1699.9	1578.4	1473.0	1377.1	1290.6	1210.8	1139.5	1076.6
35°	2040.8	1908.5	1763.9	1629.7	1510.3	1400.9	1311.0	1227.6	1151.3	1075.2	1008.6
37.5°	1970.0	1834.8	1691.0	1544.0	1424.7	1321.3	1238.8	1160.5	1086.1	1016.4	942.8
40°	1903.3	1780.1	1631.5	1485.6	1363.1	1263.4	1187.2	1116.2	1041.2	972.1	898.5
42.5°	1822.5	1717.6	1567.4	1421.0	1300.0	1204.0	1132.9	1063.5	995.3	928.4	851.6
45°	1687.6	1608.1	1467.4	1326.6	1204.8	1109.7	1044.5	983.3	923.3	859.4	787.1
47.5°	1533.0	1479.2	1357.7	1213.6	1100.9	1015.3	952.3	902.3	851.6	787.8	724.3
50°	1425.7	1391.1	1273.8	1142.3	1034.7	955.8	891.4	844.4	802.1	740.8	684.2
52.5°	1311.0	1292.6	1193.5	1067.7	963.8	886.6	831.4	789.2	746.3	695.5	642.4
55°	1136.3	1146.1	1062.1	953.3	855.5	790.4	740.2	705.0	668.5	625.6	584.5
57.5°	957.8	993.5	937.1	841.6	750.0	689.8	652.0	622.4	591.7	556.1	521.0
60°	850.9	880.9	849.0	765.0	684.9	628.8	593.6	570.8	540.2	507.6	480.9
62.5°	746.7	778.7	759.9	692.0	617.6	569.4	538.4	517.1	494.3	465.9	438.1
65°	615.8	636.6	627.5	580.6	527.8	486.7	458.1	442.4	421.6	400.8	376.0
67.5°	471.6	511.9	506.5	481.6	436.0	404.0	385.2	371.4	352.4	336.9	320.1
70°	387.7	424.8	424.1	404.0	379.2	349.2	336.2	324.5	307.6	292.6	278.9
72.5°	317.4	351.4	356.4	340.9	324.0	301.3	288.8	280.7	264.3	254.0	242.9
75°	222.2	246.9	253.4	253.4	245.6	233.9	222.8	217.6	205.9	196.8	190.3
77.5°	145.7	161.4	171.5	173.8	175.0	171.1	162.0	158.3	149.3	146.1	139.9
80°	102.9	113.4	125.1	129.0	132.2	131.0	127.1	124.4	116.0	112.7	110.1
82.5°	71.2	76.9	86.5	95.1	94.3	97.6	94.3	92.2	85.8	84.5	82.0
85°	37.1	37.8	39.1	45.0	48.3	49.5	50.1	48.8	46.9	46.9	42.3
87.5°	15.1	14.3	15.1	14.8	15.0	16.8	18.0	18.1	17.0	15.7	14.5
90°	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1	3.8	5.6	7.3
92.5°	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9	9.0	9.0	9.0
95°	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5	33.2	27.9	22.6
97.5°	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7	85.0	88.3	91.6
100°	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7	117.5	120.4	123.1
102.5°	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7	153.7	155.8	157.9
105°	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6	211.5	212.4	213.4
107.5°	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3	265.8	266.3	266.7
110°	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3	302.7	303.2	303.7



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1	338.9	339.8	340.5
115°	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2	393.7	394.2	394.5
117.5°	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9	443.5	444.1	444.7
120°	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5	477.1	477.7	478.3
122.5°	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8	508.1	508.5	508.9
125°	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7	553.4	553.9	554.6
127.5°	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2	595.4	595.6	595.7
130°	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6	622.8	623.0	623.1
132.5°	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9	648.2	648.5	648.7
135°	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6	685.5	685.3	685.1
137.5°	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1	719.2	719.3	719.3
140°	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9	741.2	741.5	741.9
142.5°	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5	761.1	761.7	762.1
145°	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6	791.1	791.5	792.0
147.5°	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5	815.4	816.2	817.1
150°	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9	832.5	833.1	833.8
152.5°	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4	846.9	847.4	847.9
155°	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9	867.0	867.1	867.3
157.5°	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1	884.0	883.9	883.8
160°	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1	893.6	893.2	892.8
162.5°	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1	902.5	901.9	901.4
165°	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5	913.6	912.9	912.1
167.5°	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4	922.6	921.8	921.0
170°	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4	927.5	926.5	925.6
172.5°	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8	930.9	929.9	929.0
175°	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4	934.4	933.6	932.6
177.5°	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1	936.2	935.4	934.4
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1588.0	1582.8	1576.0	1568.2	1558.9	1550.5	1546.9	1550.0	1551.5	1547.4	1546.9
5°	1539.7	1523.4	1510.3	1490.8	1475.2	1462.2	1453.0	1449.2	1450.4	1440.0	1437.4
7.5°	1485.4	1466.0	1444.7	1421.4	1399.9	1380.7	1370.6	1365.2	1354.2	1349.4	1341.5
10°	1450.4	1424.4	1403.5	1376.1	1351.4	1328.6	1317.5	1308.3	1297.3	1292.1	1281.0
12.5°	1414.5	1384.2	1361.3	1332.8	1307.6	1280.1	1269.5	1252.6	1235.3	1224.4	1210.1
15°	1363.8	1327.3	1299.3	1265.4	1235.4	1204.1	1176.1	1144.8	1133.1	1108.3	1094.0
17.5°	1304.5	1267.4	1232.8	1187.3	1141.0	1102.2	1072.3	1042.4	1024.4	1008.6	1001.4
20°	1265.4	1231.5	1183.3	1130.5	1079.0	1036.0	1011.9	992.4	972.8	961.8	953.9
22.5°	1228.3	1185.1	1129.1	1072.1	1020.7	987.0	966.6	946.5	930.6	920.0	909.6
25°	1166.3	1109.7	1050.4	985.2	950.0	920.7	898.5	882.2	872.5	858.8	853.6
27.5°	1102.6	1034.0	968.6	924.7	888.1	861.3	842.0	829.7	817.4	808.6	801.8
30°	1053.6	983.9	925.3	883.5	846.4	824.3	808.6	794.3	784.5	777.3	772.1
32.5°	1005.1	935.4	886.2	841.3	812.0	790.4	773.7	763.0	755.4	746.0	742.9
35°	935.0	873.1	830.1	789.8	759.8	740.2	727.2	716.0	709.5	707.0	705.0
37.5°	867.6	817.0	770.7	737.6	710.9	695.5	680.1	674.7	670.2	665.5	667.6
40°	824.9	777.3	736.3	701.1	679.6	662.7	653.6	647.1	643.1	643.1	643.1
42.5°	787.9	741.4	701.3	669.9	648.3	634.0	623.9	618.3	617.1	616.5	619.6
45°	730.5	687.4	647.1	620.9	602.8	588.3	582.5	578.0	578.0	580.6	581.2
47.5°	673.4	633.2	600.8	571.6	554.9	545.9	540.8	538.5	538.8	541.3	544.3
50°	638.6	598.8	566.8	540.8	525.2	516.7	512.2	510.9	512.2	512.2	516.7
52.5°	600.5	565.0	533.5	511.6	493.9	486.0	483.4	481.6	482.4	484.6	486.4
55°	544.7	512.8	482.9	461.9	448.9	443.7	437.9	438.5	437.2	438.5	438.5
57.5°	488.8	460.1	432.3	415.8	404.3	396.7	390.3	392.1	390.2	389.9	388.9
60°	452.9	421.6	399.4	384.5	371.4	364.9	359.0	360.3	358.4	357.0	354.5
62.5°	413.8	387.7	366.6	352.1	341.7	334.1	328.3	327.0	322.4	318.0	312.3
65°	357.0	335.5	316.7	303.0	293.2	287.4	282.8	278.9	269.1	258.6	253.4
67.5°	302.0	286.4	268.8	257.2	249.3	241.6	232.9	226.2	217.1	211.4	208.1
70°	266.5	251.5	236.5	225.5	217.0	209.8	200.0	195.5	189.0	186.3	183.1
72.5°	232.6	218.7	204.7	194.7	185.7	180.1	172.4	167.9	164.9	163.9	160.7
75°	181.2	170.0	159.7	150.5	143.4	139.4	136.2	132.9	131.6	125.7	122.5
77.5°	132.1	124.9	118.3	111.8	106.7	104.2	97.8	94.1	91.9	89.2	88.5
80°	102.9	97.7	91.2	87.3	80.1	77.6	74.9	74.3	73.6	73.0	72.3
82.5°	77.4	72.2	65.7	63.3	61.4	59.9	58.2	57.6	56.9	57.3	57.2
85°	39.1	36.5	36.5	35.8	35.2	34.5	33.8	33.8	33.3	33.8	33.3
87.5°	14.8	14.6	14.8	14.0	14.8	15.1	14.7	14.9	15.6	14.8	14.9
90°	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2	18.2	19.1	19.7
92.5°	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7	17.6	18.6	19.0
95°	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2	18.2	19.1	19.7
97.5°	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7	18.8	18.9	18.9
100°	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5	22.8	20.2	18.9
102.5°	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3	62.8	34.3	20.0
105°	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1	222.4	223.9	221.8
107.5°	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5	274.2	274.9	275.5
110°	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2	309.4	309.8	310.2



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7	343.7	343.6	343.8
115°	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2	395.5	395.9	396.0
117.5°	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0	447.0	447.0	446.9
120°	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2	479.5	479.8	479.8
122.5°	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9	511.0	511.2	511.1
125°	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1	555.5	556.0	556.3
127.5°	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0	598.9	598.8	598.7
130°	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8	625.9	626.1	626.1
132.5°	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1	652.2	652.4	652.4
135°	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3	688.7	689.0	689.3
137.5°	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1	723.5	723.8	724.0
140°	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6	745.1	745.6	745.9
142.5°	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6	764.9	765.3	765.4
145°	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0	793.1	793.3	793.5
147.5°	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9	818.1	818.2	818.4
150°	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0	834.0	834.0	834.1
152.5°	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9	848.1	848.4	848.5
155°	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7	867.3	867.9	868.0
157.5°	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9	883.7	884.5	884.5
160°	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2	894.1	895.0	895.0
162.5°	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6	902.5	903.4	903.4
165°	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4	914.6	915.9	915.9
167.5°	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1	923.4	924.8	924.7
170°	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4	928.7	929.9	929.7
172.5°	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8	932.0	933.2	933.0
175°	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7	936.1	937.5	937.3
177.5°	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3	937.3	938.3	938.0
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1543.7	1544.7	1541.2	1540.1	1541.2	1544.7	1543.7	1546.9	1547.4	1551.5	1550.0
5°	1432.2	1430.9	1427.6	1428.2	1427.6	1430.9	1432.2	1437.4	1440.0	1450.4	1449.2
7.5°	1336.8	1331.7	1333.1	1327.9	1333.1	1331.7	1336.8	1341.5	1349.4	1354.2	1365.2
10°	1278.4	1271.2	1265.4	1260.2	1265.4	1271.2	1278.4	1281.0	1292.1	1297.3	1308.3
12.5°	1198.6	1192.5	1184.6	1186.2	1184.6	1192.5	1198.6	1210.1	1224.4	1235.3	1252.6
15°	1085.5	1075.7	1060.2	1062.1	1060.2	1075.7	1085.5	1094.0	1108.3	1133.1	1144.8
17.5°	989.8	989.9	982.7	984.4	982.7	989.9	989.8	1001.4	1008.6	1024.4	1042.4
20°	940.3	935.7	936.3	934.3	936.3	935.7	940.3	953.9	961.8	972.8	992.4
22.5°	905.9	900.2	895.7	891.6	895.7	900.2	905.9	909.6	920.0	930.6	946.5
25°	847.7	843.8	837.9	836.6	837.9	843.8	847.7	853.6	858.8	872.5	882.2
27.5°	796.6	795.9	793.5	790.5	793.5	795.9	796.6	801.8	808.6	817.4	829.7
30°	766.9	765.6	764.3	762.3	764.3	765.6	766.9	772.1	777.3	784.5	794.3
32.5°	740.4	739.5	738.2	738.4	738.2	739.5	740.4	742.9	746.0	755.4	763.0
35°	702.4	701.7	700.5	699.8	700.5	701.7	702.4	705.0	707.0	709.5	716.0
37.5°	666.9	668.6	667.9	667.7	667.9	668.6	666.9	667.6	665.5	670.2	674.7
40°	642.4	643.1	644.4	643.8	644.4	643.1	642.4	643.1	643.1	643.1	647.1
42.5°	622.2	622.3	624.1	621.9	624.1	622.3	622.2	619.6	616.5	617.1	618.3
45°	585.8	589.7	589.0	589.0	589.0	589.7	585.8	581.2	580.6	578.0	578.0
47.5°	546.0	549.4	550.4	550.2	550.4	549.4	546.0	544.3	541.3	538.8	538.5
50°	520.0	518.7	520.7	520.0	520.7	518.7	520.0	516.7	512.2	512.2	510.9
52.5°	488.1	488.4	488.3	487.7	488.3	488.4	488.1	486.4	484.6	482.4	481.6
55°	439.1	439.8	438.5	439.1	438.5	439.8	439.1	438.5	438.5	437.2	438.5
57.5°	386.0	382.9	384.2	382.6	384.2	382.9	386.0	388.9	389.9	390.2	392.1
60°	348.0	342.7	341.4	338.8	341.4	342.7	348.0	354.5	357.0	358.4	360.3
62.5°	305.2	301.5	297.1	299.2	297.1	301.5	305.2	312.3	318.0	322.4	327.0
65°	248.3	245.6	243.6	246.3	243.6	245.6	248.3	253.4	258.6	269.1	278.9
67.5°	205.5	204.1	204.1	202.7	204.1	204.1	205.5	208.1	211.4	217.1	226.2
70°	183.1	181.2	181.2	179.8	181.2	181.2	183.1	183.1	186.3	189.0	195.5
72.5°	160.1	158.2	158.7	158.0	158.7	158.2	160.1	160.7	163.9	164.9	167.9
75°	118.6	115.4	115.4	116.0	115.4	115.4	118.6	122.5	125.7	131.6	132.9
77.5°	88.5	87.8	88.8	87.6	88.8	87.8	88.5	88.5	89.2	91.9	94.1
80°	72.3	71.6	71.1	73.0	71.1	71.6	72.3	72.3	73.0	73.6	74.3
82.5°	56.2	56.1	55.9	58.3	55.9	56.1	56.2	57.2	57.3	56.9	57.6
85°	33.8	32.6	33.8	32.6	33.8	32.6	33.8	33.3	33.8	33.3	33.8
87.5°	16.0	15.6	15.1	15.6	15.1	15.6	16.0	14.9	14.8	15.6	14.9
90°	20.1	20.4	20.6	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2
92.5°	19.1	19.2	19.2	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7
95°	19.8	20.0	20.2	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2
97.5°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7
100°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5
102.5°	20.1	20.1	20.1	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3
105°	216.2	210.6	205.0	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1
107.5°	276.2	276.7	277.3	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5
110°	310.7	311.1	311.6	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	344.4	345.0	345.6	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7
115°	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2
117.5°	446.9	446.8	446.7	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0
120°	479.5	479.2	478.9	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2
122.5°	510.9	510.5	510.2	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9
125°	556.5	556.6	556.8	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1
127.5°	598.6	598.4	598.3	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0
130°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8
132.5°	652.3	652.1	652.1	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1
135°	689.6	689.9	690.2	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3
137.5°	723.9	723.8	723.7	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1
140°	746.0	746.2	746.4	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6
142.5°	765.4	765.4	765.5	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6
145°	793.8	794.2	794.5	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0
147.5°	818.5	818.7	818.9	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9
150°	834.2	834.3	834.5	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0
152.5°	848.4	848.3	848.2	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9
155°	867.5	867.0	866.6	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7
157.5°	883.7	882.9	882.0	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9
160°	894.1	893.2	892.3	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2
162.5°	902.4	901.3	900.2	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6
165°	914.5	913.0	911.6	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4
167.5°	923.1	921.6	920.0	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1
170°	928.2	926.6	925.1	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4
172.5°	931.3	929.7	928.0	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8
175°	935.4	933.6	931.7	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7
177.5°	936.5	935.0	933.6	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1546.9	1550.5	1558.9	1568.2	1576.0	1582.8	1588.0	1595.3	1602.1	1611.5	1620.3
5°	1453.0	1462.2	1475.2	1490.8	1510.3	1523.4	1539.7	1554.1	1574.9	1595.7	1615.9
7.5°	1370.6	1380.7	1399.9	1421.4	1444.7	1466.0	1485.4	1510.6	1538.2	1568.6	1602.5
10°	1317.5	1328.6	1351.4	1376.1	1403.5	1424.4	1450.4	1480.4	1511.6	1548.8	1590.5
12.5°	1269.5	1280.1	1307.6	1332.8	1361.3	1384.2	1414.5	1444.9	1486.7	1526.9	1574.3
15°	1176.1	1204.1	1235.4	1265.4	1299.3	1327.3	1363.8	1395.1	1434.8	1491.5	1545.6
17.5°	1072.3	1102.2	1141.0	1187.3	1232.8	1267.4	1304.5	1343.3	1390.6	1448.5	1510.9
20°	1011.9	1036.0	1079.0	1130.5	1183.3	1231.5	1265.4	1308.3	1357.3	1419.8	1484.3
22.5°	966.6	987.0	1020.7	1072.1	1129.1	1185.1	1228.3	1270.8	1324.9	1387.5	1457.7
25°	898.5	920.7	950.0	985.2	1050.4	1109.7	1166.3	1215.2	1272.5	1335.1	1413.2
27.5°	842.0	861.3	888.1	924.7	968.6	1034.0	1102.6	1158.4	1217.2	1284.3	1362.6
30°	808.6	824.3	846.4	883.5	925.3	983.9	1053.6	1118.8	1178.1	1247.7	1329.3
32.5°	773.7	790.4	812.0	841.3	886.2	935.4	1005.1	1076.6	1139.5	1210.8	1290.6
35°	727.2	740.2	759.8	789.8	830.1	873.1	935.0	1008.6	1075.2	1151.3	1227.6
37.5°	680.1	695.5	710.9	737.6	770.7	817.0	867.6	942.8	1016.4	1086.1	1160.5
40°	653.6	662.7	679.6	701.1	736.3	777.3	824.9	898.5	972.1	1041.2	1116.2
42.5°	623.9	634.0	648.3	669.9	701.3	741.4	787.9	851.6	928.4	995.3	1063.5
45°	582.5	588.3	602.8	620.9	647.1	687.4	730.5	787.1	859.4	923.3	983.3
47.5°	540.8	545.9	554.9	571.6	600.8	633.2	673.4	724.3	787.8	851.6	902.3
50°	512.2	516.7	525.2	540.8	566.8	598.8	638.6	684.2	740.8	802.1	844.4
52.5°	483.4	486.0	493.9	511.6	533.5	565.0	600.5	642.4	695.5	746.3	789.2
55°	437.9	443.7	448.9	461.9	482.9	512.8	544.7	584.5	625.6	668.5	705.0
57.5°	390.3	396.7	404.3	415.8	432.3	460.1	488.8	521.0	556.1	591.7	622.4
60°	359.0	364.9	371.4	384.5	399.4	421.6	452.9	480.9	507.6	540.2	570.8
62.5°	328.3	334.1	341.7	352.1	366.6	387.7	413.8	438.1	465.9	494.3	517.1
65°	282.8	287.4	293.2	303.0	316.7	335.5	357.0	376.0	400.8	421.6	442.4
67.5°	232.9	241.6	249.3	257.2	268.8	286.4	302.0	320.1	336.9	352.4	371.4
70°	200.0	209.8	217.0	225.5	236.5	251.5	266.5	278.9	292.6	307.6	324.5
72.5°	172.4	180.1	185.7	194.7	204.7	218.7	232.6	242.9	254.0	264.3	280.7
75°	136.2	139.4	143.4	150.5	159.7	170.0	181.2	190.3	196.8	205.9	217.6
77.5°	97.8	104.2	106.7	111.8	118.3	124.9	132.1	139.9	146.1	149.3	158.3
80°	74.9	77.6	80.1	87.3	91.2	97.7	102.9	110.1	112.7	116.0	124.4
82.5°	58.2	59.9	61.4	63.3	65.7	72.2	77.4	82.0	84.5	85.8	92.2
85°	33.8	34.5	35.2	35.8	36.5	36.5	39.1	42.3	46.9	46.9	48.8
87.5°	14.7	15.1	14.8	14.0	14.8	14.6	14.8	14.5	15.7	17.0	18.1
90°	16.3	15.4	14.1	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1
92.5°	15.7	14.8	13.6	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9
95°	16.3	15.4	15.3	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5
97.5°	18.6	18.5	35.8	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7
100°	28.2	30.8	52.2	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7
102.5°	119.8	148.4	151.1	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7
105°	219.7	218.3	217.5	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6
107.5°	272.9	272.1	271.1	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3
110°	308.9	308.5	307.6	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	343.7	343.8	343.4	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1
115°	394.9	394.5	394.7	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2
117.5°	447.1	447.2	446.9	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9
120°	478.9	478.5	478.7	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5
122.5°	510.7	510.5	510.2	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8
125°	554.6	554.1	554.4	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7
127.5°	599.1	599.2	598.4	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2
130°	625.7	625.5	625.0	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6
132.5°	652.0	651.8	651.2	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9
135°	688.1	687.8	687.1	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6
137.5°	722.7	722.5	721.8	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1
140°	744.1	743.8	743.4	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9
142.5°	764.2	763.8	763.6	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5
145°	792.9	792.7	792.7	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6
147.5°	817.8	817.7	817.8	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5
150°	834.0	834.0	834.2	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9
152.5°	847.6	847.4	847.7	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4
155°	866.1	865.4	865.9	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9
157.5°	882.0	881.3	881.7	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1
160°	892.3	891.4	891.5	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1
162.5°	900.7	899.8	899.8	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1
165°	912.2	911.0	911.0	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5
167.5°	920.7	919.4	919.5	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4
170°	926.1	924.9	924.7	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4
172.5°	929.5	928.3	928.1	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8
175°	933.3	931.9	931.8	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4
177.5°	935.3	934.2	934.1	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1627.1	1631.8	1637.0	1646.9	1655.3	1659.0	1666.2	1671.4	1669.9	1677.2	1689.7
5°	1633.5	1651.1	1671.3	1692.1	1715.6	1735.1	1750.8	1766.4	1778.9	1793.8	1816.0
7.5°	1632.5	1663.8	1697.8	1735.1	1773.6	1806.9	1837.6	1868.9	1896.6	1927.0	1966.7
10°	1628.3	1670.0	1712.3	1761.2	1810.1	1856.3	1898.1	1937.1	1974.3	2014.0	2064.3
12.5°	1623.6	1671.6	1722.8	1781.6	1842.4	1898.1	1947.1	2003.4	2049.8	2101.1	2159.1
15°	1602.9	1667.4	1737.1	1813.4	1886.3	1961.2	2028.4	2097.4	2161.9	2223.2	2296.2
17.5°	1579.1	1653.6	1735.8	1825.9	1913.5	2004.7	2084.2	2171.3	2237.3	2319.5	2387.3
20°	1559.9	1640.0	1728.0	1829.0	1928.7	2029.7	2117.6	2206.3	2280.6	2363.3	2449.3
22.5°	1536.4	1624.4	1719.7	1824.3	1928.7	2039.1	2136.4	2224.5	2316.5	2409.7	2498.3
25°	1498.6	1589.9	1690.8	1805.5	1925.4	2038.2	2142.4	2251.8	2350.9	2451.9	2531.4
27.5°	1452.3	1548.0	1654.5	1772.8	1895.8	2011.3	2134.1	2250.7	2350.4	2447.6	2517.0
30°	1415.2	1516.3	1618.5	1738.4	1866.1	1989.9	2121.6	2238.2	2343.1	2430.4	2469.5
32.5°	1377.1	1473.0	1578.4	1699.9	1830.7	1963.9	2094.4	2213.7	2310.7	2363.1	2364.2
35°	1311.0	1400.9	1510.3	1629.7	1763.9	1908.5	2040.8	2158.0	2217.3	2221.9	2158.0
37.5°	1238.8	1321.3	1424.7	1544.0	1691.0	1834.8	1970.0	2048.1	2068.0	2001.7	1883.6
40°	1187.2	1263.4	1363.1	1485.6	1631.5	1780.1	1903.3	1960.6	1939.8	1832.2	1700.6
42.5°	1132.9	1204.0	1300.0	1421.0	1567.4	1717.6	1822.5	1853.2	1798.0	1673.8	1519.8
45°	1044.5	1109.7	1204.8	1326.6	1467.4	1608.1	1687.6	1672.0	1580.1	1432.9	1260.2
47.5°	952.3	1015.3	1100.9	1213.6	1357.7	1479.2	1533.0	1485.9	1355.2	1193.2	1052.7
50°	891.4	955.8	1034.7	1142.3	1273.8	1391.1	1425.7	1354.0	1208.7	1052.9	924.0
52.5°	831.4	886.6	963.8	1067.7	1193.5	1292.6	1311.0	1228.3	1078.4	938.8	824.3
55°	740.2	790.4	855.5	953.3	1062.1	1146.1	1136.3	1030.2	894.0	774.8	684.9
57.5°	652.0	689.8	750.0	841.6	937.1	993.5	957.8	867.2	740.4	642.7	566.8
60°	593.6	628.8	684.9	765.0	849.0	880.9	850.9	752.6	652.2	563.0	499.1
62.5°	538.4	569.4	617.6	692.0	759.9	778.7	746.7	660.8	570.4	494.2	441.3
65°	458.1	486.7	527.8	580.6	627.5	636.6	615.8	527.8	459.4	395.5	359.0
67.5°	385.2	404.0	436.0	481.6	506.5	511.9	471.6	416.3	356.0	316.8	289.3
70°	336.2	349.2	379.2	404.0	424.1	424.8	387.7	343.4	297.1	265.2	245.0
72.5°	288.8	301.3	324.0	340.9	356.4	351.4	317.4	282.4	245.0	220.9	205.9
75°	222.8	233.9	245.6	253.4	253.4	246.9	222.2	196.1	174.7	160.3	155.7
77.5°	162.0	171.1	175.0	173.8	171.5	161.4	145.7	128.7	120.9	114.1	110.7
80°	127.1	131.0	132.2	129.0	125.1	113.4	102.9	95.8	88.6	86.1	84.7
82.5°	94.3	97.6	94.3	95.1	86.5	76.9	71.2	68.7	65.7	64.7	63.3
85°	50.1	49.5	48.3	45.0	39.1	37.8	37.1	36.5	35.2	35.8	34.5
87.5°	18.0	16.8	15.0	14.8	15.1	14.3	15.1	15.4	15.6	15.3	16.5
90°	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2
92.5°	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7
95°	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2
97.5°	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7
100°	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5
102.5°	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3
105°	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1
107.5°	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5
110°	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7
115°	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2
117.5°	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0
120°	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2
122.5°	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9
125°	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1
127.5°	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0
130°	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8
132.5°	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1
135°	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3
137.5°	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1
140°	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6
142.5°	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6
145°	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0
147.5°	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9
150°	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0
152.5°	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9
155°	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7
157.5°	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9
160°	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2
162.5°	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6
165°	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4
167.5°	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1
170°	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4
172.5°	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8
175°	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7
177.5°	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2	1617.2
2.5°	1696.5	1698.6	1700.2	1705.3	1705.8	1710.5	1705.8
5°	1836.8	1846.0	1860.3	1874.6	1875.9	1885.0	1868.8
7.5°	1994.2	2015.3	2028.5	2051.7	2060.9	2066.5	2057.2
10°	2102.6	2122.2	2156.7	2173.7	2190.7	2193.2	2185.4
12.5°	2207.4	2238.4	2265.7	2297.7	2297.0	2319.9	2311.6
15°	2347.0	2379.0	2416.7	2452.6	2465.6	2465.6	2476.1
17.5°	2446.6	2505.1	2544.2	2572.3	2603.1	2608.4	2604.8
20°	2513.9	2577.0	2618.8	2655.2	2676.1	2681.9	2681.9
22.5°	2563.8	2617.6	2658.3	2691.1	2708.4	2715.3	2713.2
25°	2598.5	2644.8	2669.6	2679.3	2683.9	2682.6	2670.2
27.5°	2551.1	2549.0	2533.4	2503.4	2480.9	2467.2	2451.6
30°	2460.4	2426.5	2387.4	2344.4	2289.1	2246.6	2233.6
32.5°	2325.3	2249.3	2183.0	2111.4	2051.8	2009.5	1991.8
35°	2064.3	1943.7	1845.3	1759.3	1696.8	1657.6	1644.6
37.5°	1754.4	1637.7	1515.9	1432.5	1380.5	1341.0	1326.3
40°	1557.3	1430.2	1324.0	1245.9	1192.4	1154.0	1153.3
42.5°	1377.4	1256.1	1156.2	1099.9	1042.3	1016.8	1016.7
45°	1127.8	1030.8	946.1	901.8	867.2	846.4	840.6
47.5°	933.9	853.6	797.1	761.9	733.7	720.4	711.8
50°	824.9	754.5	709.5	678.9	663.3	646.4	645.1
52.5°	734.2	677.4	642.3	617.5	597.7	587.5	587.8
55°	617.1	572.1	547.3	528.4	512.8	505.0	501.7
57.5°	519.8	486.1	468.1	450.7	444.1	438.0	436.3
60°	459.4	436.6	419.6	406.0	396.2	394.2	393.5
62.5°	409.3	385.5	373.7	363.2	356.0	353.0	351.9
65°	337.5	319.9	309.5	301.0	298.4	293.9	293.2
67.5°	272.1	261.6	254.7	248.7	245.2	245.0	245.0
70°	232.0	226.1	220.3	217.0	215.0	213.7	213.7
72.5°	197.6	193.2	188.4	186.7	186.3	185.0	184.5
75°	150.5	146.0	146.6	143.4	140.7	137.5	135.5
77.5°	106.7	103.5	102.8	102.5	100.2	99.8	100.9
80°	82.8	79.5	78.8	79.5	78.8	76.9	76.9
82.5°	63.0	60.2	59.6	59.2	58.5	59.2	58.2
85°	33.8	32.6	32.6	32.6	33.8	33.3	32.6
87.5°	15.6	15.3	15.9	15.5	15.6	15.1	15.6
90°	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.4	309.8	310.2	310.7	311.1	311.6	312.1



TEST NUMBER: P333079-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)