

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333093-935

Luminaire Tested: **S124RDIW-S1020D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333093-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1560U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8966.9 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333093-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333093-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40				
1	96	92	88	84	87	84	80	78	68	66	64	55	53	52	42	41	40	34				
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29				
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25				
4	73	63	55	49	66	57	51	46	47	42	39	38	35	32	30	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	17				
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	17	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13				
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P333093-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.6
10°-20°	407.3	4.5
20°-30°	588.1	6.6
30°-40°	666.6	7.4
40°-50°	643.7	7.2
50°-60°	535.3	6.0
60°-70°	369.6	4.1
70°-80°	187.4	2.1
80°-90°	53.1	0.6
90°-100°	59.4	0.7
100°-110°	378.6	4.2
110°-120°	724.2	8.1
120°-130°	919.3	10.3
130°-140°	983.6	11.0
140°-150°	919.8	10.3
150°-160°	741.8	8.3
160°-170°	478.4	5.3
170°-180°	164.9	1.8
0°-30°	1141.4	12.7
0°-40°	1808.0	20.2
0°-60°	2987.0	33.3
0°-90°	3597.0	40.1
90°-120°	1162.1	13.0
90°-150°	3984.9	44.4
90°-180°	5370.0	59.9
0°-180°	8966.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	4	18	29	36	39	6
95°	71	30	29	36	38	92
105°	391	399	405	414	370	409
115°	730	733	732	735	735	718
125°	1026	1030	1028	1032	1034	915
135°	1272	1272	1276	1279	1282	980
145°	1467	1471	1471	1472	1475	916
155°	1609	1610	1606	1611	1608	741
165°	1697	1691	1691	1700	1689	479
175°	1736	1729	1730	1740	1726	165
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P333093-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.6	21.6	20.6	19.5	18.4	18.1	18.3	18.5	18.8	19.0	19.2
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	16.4	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3
95°	71.4	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3
97.5°	151.6	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4
100°	212.9	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3
102.5°	281.5	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3
105°	390.8	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7
107.5°	492.3	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4
110°	560.9	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2



TEST NUMBER: P333093-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	627.4	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9
115°	729.7	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9
117.5°	821.9	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8
120°	884.2	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7
122.5°	942.4	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7
125°	1025.8	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2
127.5°	1104.7	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8
130°	1155.6	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1
132.5°	1202.3	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9
135°	1272.5	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9
137.5°	1334.6	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4
140°	1375.0	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1
142.5°	1411.4	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2
145°	1467.2	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4
147.5°	1511.7	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9
150°	1543.9	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7
152.5°	1570.8	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1
155°	1608.8	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3
157.5°	1640.7	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0
160°	1659.4	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0
162.5°	1676.0	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5
165°	1697.0	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8
167.5°	1713.6	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7
170°	1723.0	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8
172.5°	1729.2	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0
175°	1735.9	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1
177.5°	1739.1	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333093-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	19.3	19.5	19.5	19.8	20.1	20.5	20.8	21.1
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	31.0	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	32.0	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.6	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	47.4	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	169.4	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	410.3	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	507.6	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	573.8	574.4	574.9	575.7	576.5	577.4	578.2	579.1



TEST NUMBER: P333093-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.8	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	733.5	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.7	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.0	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1030.1	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.6	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.4	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.2	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1277.5	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.0	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.0	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1418.9	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1471.7	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.0	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1573.6	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1608.4	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1673.3	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1695.1	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1711.2	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1721.1	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1727.3	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1734.7	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1737.6	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)