

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333081-830

Luminaire Tested: **S124RDIW-S1020D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333081-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D770U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6828.4 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333081-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333081-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	88	88	88		75	75	75		63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73		66	65	63		56	55	54	49
2	91	84	78	73	85	78	73	69	68	64	61		59	56	53		50	48	46	42
3	83	74	67	61	77	69	63	58	60	55	51		52	48	45		44	42	39	36
4	76	66	58	52	71	62	55	49	54	48	44		47	42	39		40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38		42	38	34		36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33		38	33	30		33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30		35	30	27		30	26	24	21
8	56	43	36	30	52	41	34	29	36	31	26		32	27	24		28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24		29	25	22		26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22		27	23	20		24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P333081-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.3
10°-20°	445.8	6.5
20°-30°	643.8	9.4
30°-40°	729.7	10.7
40°-50°	704.7	10.3
50°-60°	586.0	8.6
60°-70°	404.6	5.9
70°-80°	205.1	3.0
80°-90°	55.3	0.8
90°-100°	32.0	0.5
100°-110°	204.0	3.0
110°-120°	390.2	5.7
120°-130°	495.4	7.3
130°-140°	530.0	7.8
140°-150°	495.6	7.3
150°-160°	399.7	5.9
160°-170°	257.8	3.8
170°-180°	88.8	1.3
0°-30°	1249.5	18.3
0°-40°	1979.2	29.0
0°-60°	3269.8	47.9
0°-90°	3934.9	57.6
90°-120°	626.2	9.2
90°-150°	2147.2	31.4
90°-180°	2894.0	42.4
0°-180°	6828.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	2	10	15	19	21	5
95°	38	16	15	19	20	49
105°	211	215	218	223	199	220
115°	393	395	394	396	396	387
125°	553	555	554	556	557	493
135°	686	685	688	689	690	528
145°	791	793	793	793	795	494
155°	867	867	865	868	866	400
165°	914	911	911	916	910	258
175°	935	932	932	937	930	89
180°	935	935	935	935	935	



TEST NUMBER: P333081-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.4	22.9	21.4	19.9	18.4	17.6	17.6	17.6	17.6	17.7	17.6
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	8.9	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7
95°	38.5	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3
97.5°	81.7	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6
100°	114.7	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2
102.5°	151.7	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8
105°	210.6	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7
107.5°	265.3	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9
110°	302.3	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9



TEST NUMBER: P333081-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	338.1	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7
115°	393.2	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9
117.5°	442.9	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1
120°	476.5	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9
122.5°	507.8	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7
125°	552.7	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6
127.5°	595.2	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1
130°	622.6	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7
132.5°	647.9	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0
135°	685.6	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1
137.5°	719.1	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7
140°	740.9	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1
142.5°	760.5	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2
145°	790.6	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9
147.5°	814.5	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8
150°	831.9	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0
152.5°	846.4	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6
155°	866.9	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1
157.5°	884.1	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0
160°	894.1	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3
162.5°	903.1	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7
165°	914.5	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2
167.5°	923.4	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7
170°	928.4	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1
172.5°	931.8	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5
175°	935.4	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3
177.5°	937.1	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333081-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	17.6	17.5	17.5	17.6	17.9	18.2	18.5	18.8
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	16.7	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	17.2	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.7	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	25.5	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	91.3	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	221.1	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	273.5	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.2	309.4	309.8	310.2	310.7	311.1	311.6	312.1



TEST NUMBER: P333081-830

CATALOG NUMBER: S124RDIW-S1020D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	343.7	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.2	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	510.9	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.1	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	599.0	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.8	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.1	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.3	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.1	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	744.6	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.6	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.0	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	817.9	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	847.9	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	866.7	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	901.6	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	913.4	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	922.1	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	927.4	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	930.8	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	934.7	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	936.3	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)