

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333112-830

Luminaire Tested: **S124RDIW-S1195D1560U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333112-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9825.1 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	94	90	87	90	86	83	80	73	71	68	60	59	57	49	48	47	41
2	89	82	76	71	82	76	71	67	64	61	57	53	51	49	43	42	40	35
3	82	73	66	60	75	67	61	56	57	52	49	48	44	42	39	37	35	30
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	32	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15079	15079	15079	15079
5°	17490	15124	13367	15124
10°	20690	15058	11931	15058
15°	23901	14919	10252	14919
20°	26611	14728	9271	14728
25°	27470	14539	8607	14539
30°	24047	14311	8207	14311
35°	18719	13973	7965	13973
40°	14037	13585	7835	13585
45°	11082	12965	7767	12965
50°	9357	12248	7542	12248
55°	8156	11461	7139	11461
60°	7338	10643	6318	10643
65°	6470	9761	5435	9761
70°	5828	8847	4902	8847
75°	4885	7842	4177	7842
80°	4128	6681	3919	6681
85°	3483	5233	3483	5233



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	1.8
10°-20°	545.9	5.6
20°-30°	853.8	8.7
30°-40°	949.2	9.7
40°-50°	842.2	8.6
50°-60°	656.2	6.7
60°-70°	429.6	4.4
70°-80°	211.3	2.2
80°-90°	57.6	0.6
90°-100°	121.2	1.2
100°-110°	359.1	3.7
110°-120°	609.4	6.2
120°-130°	803.6	8.2
130°-140°	902.4	9.2
140°-150°	886.8	9.0
150°-160°	745.9	7.6
160°-170°	496.2	5.1
170°-180°	173.8	1.8
0°-30°	1580.7	16.1
0°-40°	2529.9	25.7
0°-60°	4028.3	41.0
0°-90°	4726.8	48.1
90°-120°	1089.7	11.1
90°-150°	3682.5	37.5
90°-180°	5098.0	51.9
0°-180°	9825.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1868	1868	1868	1868	1868	
5°	2158	1866	1650	1866	2158	218
15°	2860	1785	1227	1785	2860	813
25°	3084	1632	966	1632	3084	1368
35°	1899	1418	808	1418	1899	1191
45°	971	1136	680	1136	971	769
55°	580	814	507	814	580	527
65°	339	511	284	511	339	341
75°	157	251	134	251	157	172
85°	38	56	38	56	38	44
90°	43	4	43	4	43	23
95°	112	85	112	85	112	117
105°	347	331	347	331	347	365
115°	614	620	614	620	614	607
125°	895	902	895	902	895	799
135°	1165	1164	1165	1164	1165	900
145°	1416	1414	1416	1414	1416	886
155°	1619	1620	1619	1620	1619	745
165°	1759	1764	1759	1764	1759	495
175°	1826	1835	1826	1835	1826	173
180°	1838	1838	1838	1838	1838	



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1970.1	1975.6	1970.1	1969.5	1963.5	1961.7	1959.3	1951.4	1937.0	1928.6	1930.4
5°	2158.2	2177.1	2166.5	2165.0	2148.5	2131.9	2121.4	2097.3	2071.7	2054.5	2040.1
7.5°	2375.9	2386.7	2380.1	2369.6	2342.8	2327.6	2303.2	2271.4	2225.5	2190.5	2158.4
10°	2524.0	2533.0	2530.1	2510.5	2490.9	2451.0	2428.5	2384.1	2326.1	2280.2	2237.3
12.5°	2669.7	2679.4	2652.9	2653.7	2616.7	2585.3	2549.5	2493.6	2426.7	2367.5	2313.8
15°	2859.7	2847.6	2847.6	2832.5	2791.2	2747.5	2710.7	2651.9	2567.7	2496.9	2422.4
17.5°	3008.3	3012.6	3006.3	2970.9	2938.4	2893.2	2825.6	2757.1	2678.9	2583.9	2507.7
20°	3097.5	3097.5	3090.7	3066.6	3024.4	2976.3	2903.3	2828.8	2729.4	2633.8	2548.1
22.5°	3133.6	3135.9	3128.0	3108.1	3070.2	3023.2	2961.1	2885.4	2783.0	2675.4	2569.2
25°	3083.9	3098.2	3099.6	3094.5	3083.2	3054.5	3001.1	2923.6	2831.8	2715.2	2600.8
27.5°	2831.3	2849.4	2865.2	2891.2	2925.8	2943.9	2946.3	2906.9	2826.8	2714.5	2599.4
30°	2579.6	2594.7	2643.6	2707.6	2757.3	2802.5	2841.6	2852.1	2807.0	2706.1	2584.9
32.5°	2300.4	2320.8	2369.7	2438.5	2521.3	2597.7	2685.7	2730.5	2729.3	2668.8	2556.6
35°	1899.4	1914.5	1959.6	2031.8	2131.2	2244.9	2384.1	2492.4	2566.2	2560.9	2492.4
37.5°	1531.8	1548.9	1594.5	1654.4	1750.7	1891.4	2026.1	2175.4	2311.8	2388.4	2365.5
40°	1332.0	1332.8	1377.1	1438.9	1529.2	1651.8	1798.6	1964.1	2116.1	2240.3	2264.4
42.5°	1174.2	1174.4	1203.7	1270.3	1335.3	1450.8	1590.8	1755.2	1933.2	2076.5	2140.3
45°	970.7	977.5	1001.6	1041.5	1092.7	1190.5	1302.6	1455.4	1654.8	1824.9	1931.0
47.5°	822.1	832.0	847.3	879.9	920.7	985.8	1078.6	1215.8	1378.0	1565.1	1716.1
50°	745.0	746.5	766.1	784.1	819.5	871.5	952.7	1067.1	1216.1	1395.9	1563.8
52.5°	678.8	678.4	690.2	713.1	741.9	782.3	847.9	952.1	1084.2	1245.5	1418.7
55°	579.5	583.2	592.2	610.3	632.2	660.7	712.7	790.9	894.8	1032.5	1189.8
57.5°	503.9	505.9	512.9	520.6	540.6	561.4	600.4	654.7	742.3	855.1	1001.6
60°	454.5	455.2	457.5	468.8	484.7	504.2	530.6	576.5	650.2	753.3	869.2
62.5°	406.3	407.7	411.2	419.4	431.7	445.2	472.8	509.6	570.7	658.7	763.2
65°	338.7	339.4	344.7	347.7	357.4	369.5	389.8	414.6	456.8	530.6	609.5
67.5°	283.0	283.0	283.2	287.3	294.1	302.1	314.2	334.1	365.9	411.2	480.9
70°	246.9	246.9	248.4	250.6	254.4	261.1	267.9	283.0	306.3	343.2	396.6
72.5°	213.1	213.7	215.2	215.7	217.6	223.2	228.2	237.8	255.1	283.0	326.1
75°	156.6	158.8	162.6	165.6	169.3	168.5	173.8	179.8	185.1	201.7	226.5
77.5°	116.5	115.3	115.7	118.3	118.8	119.5	123.3	127.9	131.9	139.7	148.5
80°	88.8	88.8	91.0	91.8	91.0	91.8	95.6	97.8	99.3	102.4	110.7
82.5°	67.1	68.3	67.6	68.3	68.8	69.6	72.7	73.1	74.6	75.9	79.4
85°	37.6	38.4	39.1	37.6	37.6	37.6	39.1	39.9	41.4	40.6	42.1
87.5°	21.8	21.0	21.5	21.4	21.9	21.0	21.2	22.1	20.5	20.7	20.2
90°	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1	33.2	31.3	28.7
92.5°	63.1	62.7	62.3	61.9	61.5	60.8	59.7	58.5	57.4	56.3	54.5
95°	112.3	112.3	112.3	112.3	112.3	111.8	110.8	109.9	109.0	108.0	105.8
97.5°	176.0	176.0	176.0	176.0	176.0	175.4	174.3	173.1	171.9	170.8	168.2
100°	220.3	220.3	220.3	220.3	220.3	220.0	219.3	218.7	218.1	217.4	214.6
102.5°	270.3	270.0	269.8	269.6	269.3	268.7	267.9	266.9	266.1	265.2	262.6
105°	346.8	345.8	344.9	343.9	343.0	342.0	341.1	340.2	339.2	338.3	337.0
107.5°	421.2	421.3	421.4	421.4	421.5	421.1	420.2	419.3	418.4	417.5	417.4
110°	474.7	473.7	472.8	471.8	470.9	470.7	471.4	472.0	472.6	473.3	473.5



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	529.2	529.0	528.9	528.7	528.5	528.5	528.6	528.7	528.9	529.0	529.5
115°	614.0	614.3	614.6	614.9	615.2	615.6	615.9	616.1	616.5	616.8	617.5
117.5°	694.7	695.3	696.0	696.5	697.2	698.0	699.2	700.2	701.3	702.4	702.8
120°	756.1	755.4	754.8	754.2	753.6	754.0	755.6	757.1	758.7	760.3	761.3
122.5°	807.3	808.4	809.5	810.7	811.8	812.9	814.0	815.0	816.1	817.2	817.7
125°	895.3	896.0	896.6	897.2	897.9	898.5	899.2	899.8	900.4	901.1	901.4
127.5°	976.9	977.4	978.0	978.5	978.9	979.5	980.1	980.8	981.4	982.0	982.6
130°	1030.4	1031.6	1032.9	1034.2	1035.4	1036.3	1037.0	1037.6	1038.3	1038.9	1038.9
132.5°	1087.2	1087.7	1088.3	1088.7	1089.2	1089.8	1090.4	1091.1	1091.7	1092.3	1092.6
135°	1165.4	1166.3	1167.2	1168.2	1169.1	1170.0	1170.6	1171.2	1171.9	1172.5	1172.5
137.5°	1247.5	1247.4	1247.2	1247.0	1246.8	1247.1	1247.9	1248.8	1249.5	1250.4	1249.9
140°	1297.6	1297.9	1298.2	1298.5	1298.8	1299.1	1299.5	1299.8	1300.0	1300.4	1300.4
142.5°	1347.6	1347.6	1347.7	1347.7	1347.8	1347.9	1347.9	1348.0	1348.1	1348.1	1348.4
145°	1415.5	1416.5	1417.4	1418.3	1419.3	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9
147.5°	1484.3	1484.6	1485.0	1485.3	1485.5	1485.8	1486.1	1486.4	1486.6	1486.9	1487.1
150°	1526.4	1526.7	1527.0	1527.3	1527.7	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8
152.5°	1565.0	1565.8	1566.7	1567.4	1568.3	1568.3	1567.5	1566.8	1566.0	1565.3	1565.1
155°	1618.7	1620.0	1621.3	1622.5	1623.8	1623.8	1622.5	1621.3	1620.0	1618.7	1619.1
157.5°	1666.8	1667.8	1669.0	1670.0	1671.0	1671.1	1670.2	1669.2	1668.3	1667.4	1667.5
160°	1694.0	1695.6	1697.2	1698.8	1700.3	1700.7	1699.8	1698.8	1697.9	1697.0	1697.2
162.5°	1722.5	1724.1	1725.7	1727.2	1728.8	1728.7	1727.0	1725.3	1723.6	1721.9	1722.2
165°	1759.4	1760.7	1762.0	1763.2	1764.5	1764.2	1762.3	1760.4	1758.5	1756.6	1757.3
167.5°	1785.8	1787.8	1789.8	1791.8	1793.8	1793.8	1791.9	1790.0	1788.1	1786.2	1786.1
170°	1800.6	1802.9	1805.1	1807.3	1809.5	1809.7	1807.8	1805.9	1803.9	1802.0	1801.8
172.5°	1813.2	1815.3	1817.6	1819.8	1822.0	1822.0	1819.9	1817.8	1815.6	1813.5	1813.4
175°	1826.3	1828.4	1830.7	1832.9	1835.1	1835.1	1832.9	1830.7	1828.4	1826.3	1826.6
177.5°	1833.1	1835.1	1837.1	1839.1	1841.2	1841.3	1839.5	1837.8	1836.0	1834.2	1834.2
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1924.4	1916.0	1911.8	1902.1	1890.6	1884.6	1879.2	1871.4	1861.1	1850.3	1842.5
5°	2022.0	2004.0	1981.4	1954.4	1930.2	1907.0	1886.6	1866.3	1843.0	1818.9	1794.8
7.5°	2122.3	2086.8	2048.4	2004.0	1960.8	1921.6	1885.4	1850.8	1811.7	1776.6	1744.6
10°	2192.2	2144.0	2090.6	2034.1	1977.6	1928.7	1880.6	1836.9	1788.8	1745.9	1709.8
12.5°	2248.7	2192.2	2127.9	2057.6	1989.7	1930.5	1875.2	1818.3	1763.5	1717.0	1668.9
15°	2342.6	2265.1	2178.6	2094.3	2006.3	1925.7	1851.2	1785.0	1722.6	1657.1	1611.2
17.5°	2407.3	2315.3	2210.1	2108.8	2004.8	1909.8	1823.8	1745.0	1672.9	1606.1	1551.4
20°	2445.7	2344.1	2227.5	2112.3	1995.7	1894.1	1801.6	1714.3	1639.7	1567.5	1511.1
22.5°	2467.4	2354.9	2227.5	2107.0	1986.1	1876.0	1774.4	1683.6	1602.4	1530.2	1467.7
25°	2474.4	2353.9	2223.7	2085.3	1952.9	1836.2	1730.8	1632.2	1541.9	1469.7	1403.4
27.5°	2464.7	2322.9	2189.6	2047.5	1910.8	1787.9	1677.3	1573.7	1483.3	1405.7	1337.8
30°	2450.2	2298.2	2155.2	2007.8	1869.3	1751.1	1634.5	1535.2	1441.1	1360.6	1292.1
32.5°	2418.9	2268.1	2114.3	1963.2	1823.0	1701.2	1590.5	1490.6	1398.4	1316.1	1243.3
35°	2356.9	2204.1	2037.1	1882.1	1744.4	1618.0	1514.1	1417.8	1329.7	1241.7	1164.9
37.5°	2275.2	2119.1	1952.9	1783.2	1645.3	1526.0	1430.7	1340.3	1254.3	1173.9	1088.9
40°	2198.2	2056.0	1884.3	1715.8	1574.3	1459.2	1371.1	1289.1	1202.6	1122.8	1037.7
42.5°	2104.9	1983.7	1810.3	1641.2	1501.5	1390.5	1308.5	1228.3	1149.6	1072.2	983.5
45°	1949.1	1857.3	1694.7	1532.2	1391.5	1281.6	1206.4	1135.6	1066.3	992.6	909.1
47.5°	1770.6	1708.4	1568.1	1401.7	1271.5	1172.6	1099.9	1042.1	983.5	909.8	836.5
50°	1646.5	1606.7	1471.2	1319.2	1195.0	1104.0	1029.4	975.2	926.3	855.6	790.1
52.5°	1514.1	1492.9	1378.5	1233.1	1113.1	1023.9	960.3	911.4	862.0	803.2	742.0
55°	1312.4	1323.7	1226.6	1101.0	988.1	912.9	854.9	814.3	772.1	722.5	675.0
57.5°	1106.3	1147.5	1082.3	971.9	866.2	796.6	753.0	718.8	683.4	642.2	601.7
60°	982.8	1017.4	980.5	883.4	790.9	726.2	685.6	659.2	623.9	586.3	555.3
62.5°	862.4	899.5	877.6	799.2	713.2	657.6	621.7	597.2	570.9	538.1	506.1
65°	711.1	735.2	724.7	670.5	609.5	562.1	529.0	511.0	486.9	462.8	434.2
67.5°	544.7	591.2	585.0	556.3	503.6	466.6	444.9	429.0	407.0	389.1	369.7
70°	447.8	490.7	489.9	466.6	438.0	403.3	388.3	374.8	355.2	337.9	322.1
72.5°	366.5	405.8	411.6	393.7	374.2	348.0	333.6	324.2	305.2	293.3	280.5
75°	256.7	285.2	292.8	292.8	283.7	270.1	257.4	251.4	237.8	227.2	219.7
77.5°	168.2	186.3	198.0	200.8	202.2	197.7	187.1	182.9	172.5	168.7	161.5
80°	118.9	130.9	144.5	149.0	152.8	151.3	146.8	143.7	133.9	130.2	127.1
82.5°	82.2	88.8	99.9	109.9	108.8	112.7	108.8	106.4	99.1	97.6	94.6
85°	42.9	43.6	45.1	51.9	55.7	57.2	58.0	56.5	54.2	54.2	48.9
87.5°	19.7	18.6	19.3	18.7	18.6	20.3	21.4	21.3	20.2	19.1	18.0
90°	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2	7.7	11.2	14.7
92.5°	52.8	51.0	49.2	46.4	42.3	38.4	34.4	30.4	34.4	38.4	42.3
95°	103.6	101.4	99.2	96.6	93.8	91.0	88.1	85.3	88.1	91.0	93.8
97.5°	165.6	163.1	160.5	158.1	155.8	153.4	151.2	148.9	151.2	153.4	155.8
100°	211.8	209.0	206.0	204.1	202.7	201.5	200.2	199.0	200.2	201.5	202.7
102.5°	260.0	257.4	254.9	253.3	252.8	252.3	251.8	251.3	251.8	252.3	252.8
105°	335.7	334.4	333.2	332.4	332.1	331.8	331.5	331.1	331.5	331.8	332.1
107.5°	417.2	417.0	416.8	416.5	416.1	415.8	415.4	415.0	415.4	415.8	416.1
110°	473.9	474.2	474.6	474.4	473.7	473.1	472.5	471.8	472.5	473.1	473.7



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	530.1	530.7	531.2	531.5	531.3	531.2	531.1	530.9	531.1	531.2	531.3
115°	618.0	618.7	619.3	619.6	619.6	619.6	619.6	619.6	619.6	619.6	619.6
117.5°	703.2	703.7	704.2	704.3	704.0	703.7	703.4	703.2	703.4	703.7	704.0
120°	762.2	763.2	764.1	763.9	762.7	761.5	760.2	758.9	760.2	761.5	762.7
122.5°	818.0	818.5	819.0	818.9	818.4	817.9	817.4	816.9	817.4	817.9	818.4
125°	901.6	902.0	902.3	902.5	902.5	902.5	902.5	902.5	902.5	902.5	902.5
127.5°	983.1	983.5	984.1	983.8	982.9	981.9	981.0	980.1	981.0	981.9	982.9
130°	1038.9	1038.9	1038.9	1038.4	1037.5	1036.5	1035.6	1034.6	1035.6	1036.5	1037.5
132.5°	1092.9	1093.1	1093.3	1093.2	1092.4	1091.7	1091.1	1090.3	1091.1	1091.7	1092.4
135°	1172.5	1172.5	1172.5	1171.6	1169.7	1167.7	1165.8	1163.9	1165.8	1167.7	1169.7
137.5°	1249.3	1248.9	1248.4	1247.6	1246.8	1245.9	1245.0	1244.2	1245.0	1245.9	1246.8
140°	1300.4	1300.4	1300.4	1300.0	1299.5	1298.8	1298.2	1297.6	1298.2	1298.8	1299.5
142.5°	1348.7	1348.9	1349.2	1349.0	1348.3	1347.7	1347.1	1346.4	1347.1	1347.7	1348.3
145°	1420.6	1420.2	1419.9	1419.2	1417.9	1416.6	1415.3	1414.1	1415.3	1416.6	1417.9
147.5°	1487.3	1487.6	1487.9	1487.2	1485.7	1484.2	1482.7	1481.2	1482.7	1484.2	1485.7
150°	1527.8	1527.8	1527.8	1527.2	1525.9	1524.7	1523.3	1522.1	1523.3	1524.7	1525.9
152.5°	1564.8	1564.5	1564.3	1563.8	1563.0	1562.3	1561.5	1560.8	1561.5	1562.3	1563.0
155°	1619.4	1619.7	1620.0	1620.1	1620.1	1620.1	1620.1	1620.1	1620.1	1620.1	1620.1
157.5°	1667.5	1667.5	1667.6	1667.9	1668.5	1669.1	1669.6	1670.2	1669.6	1669.1	1668.5
160°	1697.5	1697.9	1698.2	1698.5	1698.8	1699.1	1699.4	1699.8	1699.4	1699.1	1698.8
162.5°	1722.6	1722.9	1723.2	1723.7	1724.6	1725.4	1726.3	1727.0	1726.3	1725.4	1724.6
165°	1757.8	1758.5	1759.2	1759.9	1760.9	1761.8	1762.7	1763.7	1762.7	1761.8	1760.9
167.5°	1786.0	1786.0	1785.9	1786.6	1787.9	1789.2	1790.5	1791.9	1790.5	1789.2	1787.9
170°	1801.5	1801.1	1800.8	1801.5	1803.0	1804.6	1806.2	1807.8	1806.2	1804.6	1803.0
172.5°	1813.4	1813.3	1813.2	1813.8	1815.1	1816.5	1817.8	1819.1	1817.8	1816.5	1815.1
175°	1826.8	1827.2	1827.5	1828.4	1830.0	1831.6	1833.2	1834.8	1833.2	1831.6	1830.0
177.5°	1834.2	1834.2	1834.2	1834.8	1836.1	1837.4	1838.6	1839.8	1838.6	1837.4	1836.1
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1834.1	1828.1	1820.2	1811.2	1800.4	1790.7	1786.5	1790.2	1792.0	1787.2	1786.5
5°	1778.2	1759.4	1744.4	1721.8	1703.7	1688.7	1678.2	1673.7	1675.2	1663.1	1660.1
7.5°	1715.5	1693.2	1668.5	1641.7	1616.7	1594.6	1583.0	1576.7	1564.0	1558.5	1549.4
10°	1675.2	1645.0	1621.0	1589.3	1560.8	1534.5	1521.6	1511.1	1498.3	1492.2	1479.5
12.5°	1633.6	1598.6	1572.2	1539.4	1510.1	1478.5	1466.2	1446.7	1426.6	1414.0	1397.6
15°	1575.1	1533.0	1500.5	1461.4	1426.8	1390.7	1358.3	1322.2	1308.6	1280.1	1263.5
17.5°	1506.6	1463.9	1423.8	1371.3	1317.9	1273.0	1238.5	1203.9	1183.2	1164.9	1156.5
20°	1461.4	1422.3	1366.6	1305.6	1246.2	1196.6	1168.7	1146.1	1123.5	1110.8	1101.7
22.5°	1418.7	1368.7	1304.0	1238.2	1178.7	1139.9	1116.3	1093.2	1074.8	1062.6	1050.6
25°	1347.1	1281.6	1213.1	1137.8	1097.2	1063.4	1037.7	1018.9	1007.7	991.8	985.8
27.5°	1273.5	1194.1	1118.6	1068.0	1025.7	994.7	972.4	958.3	944.0	933.9	926.0
30°	1216.8	1136.3	1068.6	1020.4	977.5	952.0	933.9	917.4	906.1	897.8	891.7
32.5°	1160.8	1080.3	1023.4	971.7	937.8	912.9	893.5	881.2	872.3	861.7	858.0
35°	1079.9	1008.4	958.8	912.1	877.4	854.9	839.8	827.1	819.5	816.5	814.3
37.5°	1002.1	943.5	890.1	851.9	821.0	803.2	785.5	779.2	774.0	768.6	771.1
40°	952.7	897.8	850.4	809.7	784.9	765.3	754.8	747.2	742.7	742.7	742.7
42.5°	909.9	856.2	810.0	773.6	748.8	732.3	720.5	714.2	712.7	712.1	715.7
45°	843.6	793.9	747.2	717.2	696.1	679.6	672.8	667.5	667.5	670.5	671.3
47.5°	777.8	731.3	693.8	660.2	640.8	630.5	624.6	621.9	622.2	625.2	628.7
50°	737.4	691.5	654.7	624.6	606.5	596.7	591.4	590.0	591.4	591.4	596.7
52.5°	693.5	652.4	616.1	590.9	570.4	561.3	558.4	556.3	557.1	559.6	561.8
55°	629.1	592.2	557.6	533.6	518.5	512.5	505.7	506.4	504.9	506.4	506.4
57.5°	564.6	531.4	499.3	480.1	466.8	458.2	450.7	452.9	450.6	450.3	449.1
60°	523.0	486.9	461.3	444.0	429.0	421.4	414.6	416.1	413.9	412.4	409.3
62.5°	477.9	447.8	423.4	406.7	394.6	385.9	379.1	377.6	372.4	367.2	360.6
65°	412.4	387.6	365.7	350.0	338.7	331.9	326.6	322.1	310.8	298.8	292.8
67.5°	348.7	330.8	310.5	297.1	287.9	279.1	269.0	261.3	250.7	244.1	240.3
70°	307.7	290.5	273.1	260.3	250.6	242.3	231.0	225.7	218.2	215.2	211.5
72.5°	268.6	252.5	236.5	224.9	214.4	208.0	199.2	193.9	190.6	189.4	185.6
75°	209.2	196.4	184.4	173.8	165.6	161.1	157.3	153.5	152.0	145.2	141.5
77.5°	152.6	144.2	136.7	129.1	123.3	120.3	113.0	108.7	106.1	102.9	102.2
80°	118.9	112.9	105.4	100.9	92.6	89.5	86.5	85.8	85.0	84.3	83.5
82.5°	89.4	83.4	75.9	73.1	70.9	69.1	67.3	66.5	65.8	66.3	66.1
85°	45.1	42.1	42.1	41.4	40.6	39.9	39.1	39.1	38.4	39.1	38.4
87.5°	18.7	18.7	19.2	18.5	19.6	20.1	19.9	20.3	21.2	20.5	20.6
90°	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1	36.9	38.8	40.2
92.5°	46.4	49.2	51.0	52.8	54.5	56.3	57.4	58.5	59.7	60.8	61.5
95°	96.6	99.2	101.4	103.6	105.8	108.0	109.0	109.9	110.8	111.8	112.3
97.5°	158.1	160.5	163.1	165.6	168.2	170.8	171.9	173.1	174.3	175.4	176.0
100°	204.1	206.0	209.0	211.8	214.6	217.4	218.1	218.7	219.3	220.0	220.3
102.5°	253.3	254.9	257.4	260.0	262.6	265.2	266.1	266.9	267.9	268.7	269.3
105°	332.4	333.2	334.4	335.7	337.0	338.3	339.2	340.2	341.1	342.0	343.0
107.5°	416.5	416.8	417.0	417.2	417.4	417.5	418.4	419.3	420.2	421.1	421.5
110°	474.4	474.6	474.2	473.9	473.5	473.3	472.6	472.0	471.4	470.7	470.9



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	531.5	531.2	530.7	530.1	529.5	529.0	528.9	528.7	528.6	528.5	528.5
115°	619.6	619.3	618.7	618.0	617.5	616.8	616.5	616.1	615.9	615.6	615.2
117.5°	704.3	704.2	703.7	703.2	702.8	702.4	701.3	700.2	699.2	698.0	697.2
120°	763.9	764.1	763.2	762.2	761.3	760.3	758.7	757.1	755.6	754.0	753.6
122.5°	818.9	819.0	818.5	818.0	817.7	817.2	816.1	815.0	814.0	812.9	811.8
125°	902.5	902.3	902.0	901.6	901.4	901.1	900.4	899.8	899.2	898.5	897.9
127.5°	983.8	984.1	983.5	983.1	982.6	982.0	981.4	980.8	980.1	979.5	978.9
130°	1038.4	1038.9	1038.9	1038.9	1038.9	1038.9	1038.3	1037.6	1037.0	1036.3	1035.4
132.5°	1093.2	1093.3	1093.1	1092.9	1092.6	1092.3	1091.7	1091.1	1090.4	1089.8	1089.2
135°	1171.6	1172.5	1172.5	1172.5	1172.5	1172.5	1171.9	1171.2	1170.6	1170.0	1169.1
137.5°	1247.6	1248.4	1248.9	1249.3	1249.9	1250.4	1249.5	1248.8	1247.9	1247.1	1246.8
140°	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0	1299.8	1299.5	1299.1	1298.8
142.5°	1349.0	1349.2	1348.9	1348.7	1348.4	1348.1	1348.1	1348.0	1347.9	1347.9	1347.8
145°	1419.2	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9	1420.6	1420.2	1419.9	1419.3
147.5°	1487.2	1487.9	1487.6	1487.3	1487.1	1486.9	1486.6	1486.4	1486.1	1485.8	1485.5
150°	1527.2	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8	1527.7
152.5°	1563.8	1564.3	1564.5	1564.8	1565.1	1565.3	1566.0	1566.8	1567.5	1568.3	1568.3
155°	1620.1	1620.0	1619.7	1619.4	1619.1	1618.7	1620.0	1621.3	1622.5	1623.8	1623.8
157.5°	1667.9	1667.6	1667.5	1667.5	1667.5	1667.4	1668.3	1669.2	1670.2	1671.1	1671.0
160°	1698.5	1698.2	1697.9	1697.5	1697.2	1697.0	1697.9	1698.8	1699.8	1700.7	1700.3
162.5°	1723.7	1723.2	1722.9	1722.6	1722.2	1721.9	1723.6	1725.3	1727.0	1728.7	1728.8
165°	1759.9	1759.2	1758.5	1757.8	1757.3	1756.6	1758.5	1760.4	1762.3	1764.2	1764.5
167.5°	1786.6	1785.9	1786.0	1786.0	1786.1	1786.2	1788.1	1790.0	1791.9	1793.8	1793.8
170°	1801.5	1800.8	1801.1	1801.5	1801.8	1802.0	1803.9	1805.9	1807.8	1809.7	1809.5
172.5°	1813.8	1813.2	1813.3	1813.4	1813.4	1813.5	1815.6	1817.8	1819.9	1822.0	1822.0
175°	1828.4	1827.5	1827.2	1826.8	1826.6	1826.3	1828.4	1830.7	1832.9	1835.1	1835.1
177.5°	1834.8	1834.2	1834.2	1834.2	1834.2	1834.2	1836.0	1837.8	1839.5	1841.3	1841.2
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1782.9	1784.1	1779.9	1778.7	1779.9	1784.1	1782.9	1786.5	1787.2	1792.0	1790.2
5°	1654.1	1652.6	1648.8	1649.5	1648.8	1652.6	1654.1	1660.1	1663.1	1675.2	1673.7
7.5°	1543.9	1538.0	1539.6	1533.7	1539.6	1538.0	1543.9	1549.4	1558.5	1564.0	1576.7
10°	1476.5	1468.2	1461.4	1455.4	1461.4	1468.2	1476.5	1479.5	1492.2	1498.3	1511.1
12.5°	1384.4	1377.2	1368.1	1369.9	1368.1	1377.2	1384.4	1397.6	1414.0	1426.6	1446.7
15°	1253.7	1242.5	1224.4	1226.6	1224.4	1242.5	1253.7	1263.5	1280.1	1308.6	1322.2
17.5°	1143.1	1143.2	1135.0	1136.9	1135.0	1143.2	1143.1	1156.5	1164.9	1183.2	1203.9
20°	1085.9	1080.6	1081.4	1079.1	1081.4	1080.6	1085.9	1101.7	1110.8	1123.5	1146.1
22.5°	1046.1	1039.7	1034.4	1029.7	1034.4	1039.7	1046.1	1050.6	1062.6	1074.8	1093.2
25°	979.0	974.5	967.8	966.3	967.8	974.5	979.0	985.8	991.8	1007.7	1018.9
27.5°	920.0	919.2	916.4	912.9	916.4	919.2	920.0	926.0	933.9	944.0	958.3
30°	885.7	884.2	882.7	880.4	882.7	884.2	885.7	891.7	897.8	906.1	917.4
32.5°	855.1	854.1	852.6	852.8	852.6	854.1	855.1	858.0	861.7	872.3	881.2
35°	811.2	810.5	809.0	808.2	809.0	810.5	811.2	814.3	816.5	819.5	827.1
37.5°	770.3	772.2	771.4	771.2	771.4	772.2	770.3	771.1	768.6	774.0	779.2
40°	742.0	742.7	744.2	743.5	744.2	742.7	742.0	742.7	742.7	742.7	747.2
42.5°	718.5	718.7	720.8	718.2	720.8	718.7	718.5	715.7	712.1	712.7	714.2
45°	676.6	681.1	680.3	680.3	680.3	681.1	676.6	671.3	670.5	667.5	667.5
47.5°	630.7	634.5	635.6	635.5	635.6	634.5	630.7	628.7	625.2	622.2	621.9
50°	600.5	599.0	601.2	600.5	601.2	599.0	600.5	596.7	591.4	591.4	590.0
52.5°	563.8	564.1	563.9	563.2	563.9	564.1	563.8	561.8	559.6	557.1	556.3
55°	507.2	507.9	506.4	507.2	506.4	507.9	507.2	506.4	506.4	504.9	506.4
57.5°	445.8	442.1	443.7	441.9	443.7	442.1	445.8	449.1	450.3	450.6	452.9
60°	401.9	395.9	394.4	391.3	394.4	395.9	401.9	409.3	412.4	413.9	416.1
62.5°	352.5	348.3	343.2	345.5	343.2	348.3	352.5	360.6	367.2	372.4	377.6
65°	286.7	283.7	281.4	284.5	281.4	283.7	286.7	292.8	298.8	310.8	322.1
67.5°	237.3	235.7	235.7	234.2	235.7	235.7	237.3	240.3	244.1	250.7	261.3
70°	211.5	209.2	209.2	207.7	209.2	209.2	211.5	211.5	215.2	218.2	225.7
72.5°	184.9	182.8	183.3	182.4	183.3	182.8	184.9	185.6	189.4	190.6	193.9
75°	137.0	133.2	133.2	133.9	133.2	133.2	137.0	141.5	145.2	152.0	153.5
77.5°	102.2	101.4	102.5	101.1	102.5	101.4	102.2	102.2	102.9	106.1	108.7
80°	83.5	82.8	82.0	84.3	82.0	82.8	83.5	83.5	84.3	85.0	85.8
82.5°	64.8	64.8	64.6	67.4	64.6	64.8	64.8	66.1	66.3	65.8	66.5
85°	39.1	37.6	39.1	37.6	39.1	37.6	39.1	38.4	39.1	38.4	39.1
87.5°	22.0	21.5	21.0	21.8	21.0	21.5	22.0	20.6	20.5	21.2	20.3
90°	40.7	41.4	42.0	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1
92.5°	61.9	62.3	62.7	63.1	62.7	62.3	61.9	61.5	60.8	59.7	58.5
95°	112.3	112.3	112.3	112.3	112.3	112.3	112.3	112.3	111.8	110.8	109.9
97.5°	176.0	176.0	176.0	176.0	176.0	176.0	176.0	176.0	175.4	174.3	173.1
100°	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.3	220.0	219.3	218.7
102.5°	269.6	269.8	270.0	270.3	270.0	269.8	269.6	269.3	268.7	267.9	266.9
105°	343.9	344.9	345.8	346.8	345.8	344.9	343.9	343.0	342.0	341.1	340.2
107.5°	421.4	421.4	421.3	421.2	421.3	421.4	421.4	421.5	421.1	420.2	419.3
110°	471.8	472.8	473.7	474.7	473.7	472.8	471.8	470.9	470.7	471.4	472.0



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	528.7	528.9	529.0	529.2	529.0	528.9	528.7	528.5	528.5	528.6	528.7
115°	614.9	614.6	614.3	614.0	614.3	614.6	614.9	615.2	615.6	615.9	616.1
117.5°	696.5	696.0	695.3	694.7	695.3	696.0	696.5	697.2	698.0	699.2	700.2
120°	754.2	754.8	755.4	756.1	755.4	754.8	754.2	753.6	754.0	755.6	757.1
122.5°	810.7	809.5	808.4	807.3	808.4	809.5	810.7	811.8	812.9	814.0	815.0
125°	897.2	896.6	896.0	895.3	896.0	896.6	897.2	897.9	898.5	899.2	899.8
127.5°	978.5	978.0	977.4	976.9	977.4	978.0	978.5	978.9	979.5	980.1	980.8
130°	1034.2	1032.9	1031.6	1030.4	1031.6	1032.9	1034.2	1035.4	1036.3	1037.0	1037.6
132.5°	1088.7	1088.3	1087.7	1087.2	1087.7	1088.3	1088.7	1089.2	1089.8	1090.4	1091.1
135°	1168.2	1167.2	1166.3	1165.4	1166.3	1167.2	1168.2	1169.1	1170.0	1170.6	1171.2
137.5°	1247.0	1247.2	1247.4	1247.5	1247.4	1247.2	1247.0	1246.8	1247.1	1247.9	1248.8
140°	1298.5	1298.2	1297.9	1297.6	1297.9	1298.2	1298.5	1298.8	1299.1	1299.5	1299.8
142.5°	1347.7	1347.7	1347.6	1347.6	1347.6	1347.7	1347.7	1347.8	1347.9	1347.9	1348.0
145°	1418.3	1417.4	1416.5	1415.5	1416.5	1417.4	1418.3	1419.3	1419.9	1420.2	1420.6
147.5°	1485.3	1485.0	1484.6	1484.3	1484.6	1485.0	1485.3	1485.5	1485.8	1486.1	1486.4
150°	1527.3	1527.0	1526.7	1526.4	1526.7	1527.0	1527.3	1527.7	1527.8	1527.8	1527.8
152.5°	1567.4	1566.7	1565.8	1565.0	1565.8	1566.7	1567.4	1568.3	1568.3	1567.5	1566.8
155°	1622.5	1621.3	1620.0	1618.7	1620.0	1621.3	1622.5	1623.8	1623.8	1622.5	1621.3
157.5°	1670.0	1669.0	1667.8	1666.8	1667.8	1669.0	1670.0	1671.0	1671.1	1670.2	1669.2
160°	1698.8	1697.2	1695.6	1694.0	1695.6	1697.2	1698.8	1700.3	1700.7	1699.8	1698.8
162.5°	1727.2	1725.7	1724.1	1722.5	1724.1	1725.7	1727.2	1728.8	1728.7	1727.0	1725.3
165°	1763.2	1762.0	1760.7	1759.4	1760.7	1762.0	1763.2	1764.5	1764.2	1762.3	1760.4
167.5°	1791.8	1789.8	1787.8	1785.8	1787.8	1789.8	1791.8	1793.8	1793.8	1791.9	1790.0
170°	1807.3	1805.1	1802.9	1800.6	1802.9	1805.1	1807.3	1809.5	1809.7	1807.8	1805.9
172.5°	1819.8	1817.6	1815.3	1813.2	1815.3	1817.6	1819.8	1822.0	1822.0	1819.9	1817.8
175°	1832.9	1830.7	1828.4	1826.3	1828.4	1830.7	1832.9	1835.1	1835.1	1832.9	1830.7
177.5°	1839.1	1837.1	1835.1	1833.1	1835.1	1837.1	1839.1	1841.2	1841.3	1839.5	1837.8
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1786.5	1790.7	1800.4	1811.2	1820.2	1828.1	1834.1	1842.5	1850.3	1861.1	1871.4
5°	1678.2	1688.7	1703.7	1721.8	1744.4	1759.4	1778.2	1794.8	1818.9	1843.0	1866.3
7.5°	1583.0	1594.6	1616.7	1641.7	1668.5	1693.2	1715.5	1744.6	1776.6	1811.7	1850.8
10°	1521.6	1534.5	1560.8	1589.3	1621.0	1645.0	1675.2	1709.8	1745.9	1788.8	1836.9
12.5°	1466.2	1478.5	1510.1	1539.4	1572.2	1598.6	1633.6	1668.9	1717.0	1763.5	1818.3
15°	1358.3	1390.7	1426.8	1461.4	1500.5	1533.0	1575.1	1611.2	1657.1	1722.6	1785.0
17.5°	1238.5	1273.0	1317.9	1371.3	1423.8	1463.9	1506.6	1551.4	1606.1	1672.9	1745.0
20°	1168.7	1196.6	1246.2	1305.6	1366.6	1422.3	1461.4	1511.1	1567.5	1639.7	1714.3
22.5°	1116.3	1139.9	1178.7	1238.2	1304.0	1368.7	1418.7	1467.7	1530.2	1602.4	1683.6
25°	1037.7	1063.4	1097.2	1137.8	1213.1	1281.6	1347.1	1403.4	1469.7	1541.9	1632.2
27.5°	972.4	994.7	1025.7	1068.0	1118.6	1194.1	1273.5	1337.8	1405.7	1483.3	1573.7
30°	933.9	952.0	977.5	1020.4	1068.6	1136.3	1216.8	1292.1	1360.6	1441.1	1535.2
32.5°	893.5	912.9	937.8	971.7	1023.4	1080.3	1160.8	1243.3	1316.1	1398.4	1490.6
35°	839.8	854.9	877.4	912.1	958.8	1008.4	1079.9	1164.9	1241.7	1329.7	1417.8
37.5°	785.5	803.2	821.0	851.9	890.1	943.5	1002.1	1088.9	1173.9	1254.3	1340.3
40°	754.8	765.3	784.9	809.7	850.4	897.8	952.7	1037.7	1122.8	1202.6	1289.1
42.5°	720.5	732.3	748.8	773.6	810.0	856.2	909.9	983.5	1072.2	1149.6	1228.3
45°	672.8	679.6	696.1	717.2	747.2	793.9	843.6	909.1	992.6	1066.3	1135.6
47.5°	624.6	630.5	640.8	660.2	693.8	731.3	777.8	836.5	909.8	983.5	1042.1
50°	591.4	596.7	606.5	624.6	654.7	691.5	737.4	790.1	855.6	926.3	975.2
52.5°	558.4	561.3	570.4	590.9	616.1	652.4	693.5	742.0	803.2	862.0	911.4
55°	505.7	512.5	518.5	533.6	557.6	592.2	629.1	675.0	722.5	772.1	814.3
57.5°	450.7	458.2	466.8	480.1	499.3	531.4	564.6	601.7	642.2	683.4	718.8
60°	414.6	421.4	429.0	444.0	461.3	486.9	523.0	555.3	586.3	623.9	659.2
62.5°	379.1	385.9	394.6	406.7	423.4	447.8	477.9	506.1	538.1	570.9	597.2
65°	326.6	331.9	338.7	350.0	365.7	387.6	412.4	434.2	462.8	486.9	511.0
67.5°	269.0	279.1	287.9	297.1	310.5	330.8	348.7	369.7	389.1	407.0	429.0
70°	231.0	242.3	250.6	260.3	273.1	290.5	307.7	322.1	337.9	355.2	374.8
72.5°	199.2	208.0	214.4	224.9	236.5	252.5	268.6	280.5	293.3	305.2	324.2
75°	157.3	161.1	165.6	173.8	184.4	196.4	209.2	219.7	227.2	237.8	251.4
77.5°	113.0	120.3	123.3	129.1	136.7	144.2	152.6	161.5	168.7	172.5	182.9
80°	86.5	89.5	92.6	100.9	105.4	112.9	118.9	127.1	130.2	133.9	143.7
82.5°	67.3	69.1	70.9	73.1	75.9	83.4	89.4	94.6	97.6	99.1	106.4
85°	39.1	39.9	40.6	41.4	42.1	42.1	45.1	48.9	54.2	54.2	56.5
87.5°	19.9	20.1	19.6	18.5	19.2	18.7	18.7	18.0	19.1	20.2	21.3
90°	33.2	31.3	28.7	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2
92.5°	57.4	56.3	54.5	52.8	51.0	49.2	46.4	42.3	38.4	34.4	30.4
95°	109.0	108.0	105.8	103.6	101.4	99.2	96.6	93.8	91.0	88.1	85.3
97.5°	171.9	170.8	168.2	165.6	163.1	160.5	158.1	155.8	153.4	151.2	148.9
100°	218.1	217.4	214.6	211.8	209.0	206.0	204.1	202.7	201.5	200.2	199.0
102.5°	266.1	265.2	262.6	260.0	257.4	254.9	253.3	252.8	252.3	251.8	251.3
105°	339.2	338.3	337.0	335.7	334.4	333.2	332.4	332.1	331.8	331.5	331.1
107.5°	418.4	417.5	417.4	417.2	417.0	416.8	416.5	416.1	415.8	415.4	415.0
110°	472.6	473.3	473.5	473.9	474.2	474.6	474.4	473.7	473.1	472.5	471.8



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	528.9	529.0	529.5	530.1	530.7	531.2	531.5	531.3	531.2	531.1	530.9
115°	616.5	616.8	617.5	618.0	618.7	619.3	619.6	619.6	619.6	619.6	619.6
117.5°	701.3	702.4	702.8	703.2	703.7	704.2	704.3	704.0	703.7	703.4	703.2
120°	758.7	760.3	761.3	762.2	763.2	764.1	763.9	762.7	761.5	760.2	758.9
122.5°	816.1	817.2	817.7	818.0	818.5	819.0	818.9	818.4	817.9	817.4	816.9
125°	900.4	901.1	901.4	901.6	902.0	902.3	902.5	902.5	902.5	902.5	902.5
127.5°	981.4	982.0	982.6	983.1	983.5	984.1	983.8	982.9	981.9	981.0	980.1
130°	1038.3	1038.9	1038.9	1038.9	1038.9	1038.9	1038.4	1037.5	1036.5	1035.6	1034.6
132.5°	1091.7	1092.3	1092.6	1092.9	1093.1	1093.3	1093.2	1092.4	1091.7	1091.1	1090.3
135°	1171.9	1172.5	1172.5	1172.5	1172.5	1172.5	1171.6	1169.7	1167.7	1165.8	1163.9
137.5°	1249.5	1250.4	1249.9	1249.3	1248.9	1248.4	1247.6	1246.8	1245.9	1245.0	1244.2
140°	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0	1299.5	1298.8	1298.2	1297.6
142.5°	1348.1	1348.1	1348.4	1348.7	1348.9	1349.2	1349.0	1348.3	1347.7	1347.1	1346.4
145°	1420.9	1421.2	1420.9	1420.6	1420.2	1419.9	1419.2	1417.9	1416.6	1415.3	1414.1
147.5°	1486.6	1486.9	1487.1	1487.3	1487.6	1487.9	1487.2	1485.7	1484.2	1482.7	1481.2
150°	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8	1527.2	1525.9	1524.7	1523.3	1522.1
152.5°	1566.0	1565.3	1565.1	1564.8	1564.5	1564.3	1563.8	1563.0	1562.3	1561.5	1560.8
155°	1620.0	1618.7	1619.1	1619.4	1619.7	1620.0	1620.1	1620.1	1620.1	1620.1	1620.1
157.5°	1668.3	1667.4	1667.5	1667.5	1667.5	1667.6	1667.9	1668.5	1669.1	1669.6	1670.2
160°	1697.9	1697.0	1697.2	1697.5	1697.9	1698.2	1698.5	1698.8	1699.1	1699.4	1699.8
162.5°	1723.6	1721.9	1722.2	1722.6	1722.9	1723.2	1723.7	1724.6	1725.4	1726.3	1727.0
165°	1758.5	1756.6	1757.3	1757.8	1758.5	1759.2	1759.9	1760.9	1761.8	1762.7	1763.7
167.5°	1788.1	1786.2	1786.1	1786.0	1786.0	1785.9	1786.6	1787.9	1789.2	1790.5	1791.9
170°	1803.9	1802.0	1801.8	1801.5	1801.1	1800.8	1801.5	1803.0	1804.6	1806.2	1807.8
172.5°	1815.6	1813.5	1813.4	1813.4	1813.3	1813.2	1813.8	1815.1	1816.5	1817.8	1819.1
175°	1828.4	1826.3	1826.6	1826.8	1827.2	1827.5	1828.4	1830.0	1831.6	1833.2	1834.8
177.5°	1836.0	1834.2	1834.2	1834.2	1834.2	1834.2	1834.8	1836.1	1837.4	1838.6	1839.8
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1879.2	1884.6	1890.6	1902.1	1911.8	1916.0	1924.4	1930.4	1928.6	1937.0	1951.4
5°	1886.6	1907.0	1930.2	1954.4	1981.4	2004.0	2022.0	2040.1	2054.5	2071.7	2097.3
7.5°	1885.4	1921.6	1960.8	2004.0	2048.4	2086.8	2122.3	2158.4	2190.5	2225.5	2271.4
10°	1880.6	1928.7	1977.6	2034.1	2090.6	2144.0	2192.2	2237.3	2280.2	2326.1	2384.1
12.5°	1875.2	1930.5	1989.7	2057.6	2127.9	2192.2	2248.7	2313.8	2367.5	2426.7	2493.6
15°	1851.2	1925.7	2006.3	2094.3	2178.6	2265.1	2342.6	2422.4	2496.9	2567.7	2651.9
17.5°	1823.8	1909.8	2004.8	2108.8	2210.1	2315.3	2407.3	2507.7	2583.9	2678.9	2757.1
20°	1801.6	1894.1	1995.7	2112.3	2227.5	2344.1	2445.7	2548.1	2633.8	2729.4	2828.8
22.5°	1774.4	1876.0	1986.1	2107.0	2227.5	2354.9	2467.4	2569.2	2675.4	2783.0	2885.4
25°	1730.8	1836.2	1952.9	2085.3	2223.7	2353.9	2474.4	2600.8	2715.2	2831.8	2923.6
27.5°	1677.3	1787.9	1910.8	2047.5	2189.6	2322.9	2464.7	2599.4	2714.5	2826.8	2906.9
30°	1634.5	1751.1	1869.3	2007.8	2155.2	2298.2	2450.2	2584.9	2706.1	2807.0	2852.1
32.5°	1590.5	1701.2	1823.0	1963.2	2114.3	2268.1	2418.9	2556.6	2668.8	2729.3	2730.5
35°	1514.1	1618.0	1744.4	1882.1	2037.1	2204.1	2356.9	2492.4	2560.9	2566.2	2492.4
37.5°	1430.7	1526.0	1645.3	1783.2	1952.9	2119.1	2275.2	2365.5	2388.4	2311.8	2175.4
40°	1371.1	1459.2	1574.3	1715.8	1884.3	2056.0	2198.2	2264.4	2240.3	2116.1	1964.1
42.5°	1308.5	1390.5	1501.5	1641.2	1810.3	1983.7	2104.9	2140.3	2076.5	1933.2	1755.2
45°	1206.4	1281.6	1391.5	1532.2	1694.7	1857.3	1949.1	1931.0	1824.9	1654.8	1455.4
47.5°	1099.9	1172.6	1271.5	1401.7	1568.1	1708.4	1770.6	1716.1	1565.1	1378.0	1215.8
50°	1029.4	1104.0	1195.0	1319.2	1471.2	1606.7	1646.5	1563.8	1395.9	1216.1	1067.1
52.5°	960.3	1023.9	1113.1	1233.1	1378.5	1492.9	1514.1	1418.7	1245.5	1084.2	952.1
55°	854.9	912.9	988.1	1101.0	1226.6	1323.7	1312.4	1189.8	1032.5	894.8	790.9
57.5°	753.0	796.6	866.2	971.9	1082.3	1147.5	1106.3	1001.6	855.1	742.3	654.7
60°	685.6	726.2	790.9	883.4	980.5	1017.4	982.8	869.2	753.3	650.2	576.5
62.5°	621.7	657.6	713.2	799.2	877.6	899.5	862.4	763.2	658.7	570.7	509.6
65°	529.0	562.1	609.5	670.5	724.7	735.2	711.1	609.5	530.6	456.8	414.6
67.5°	444.9	466.6	503.6	556.3	585.0	591.2	544.7	480.9	411.2	365.9	334.1
70°	388.3	403.3	438.0	466.6	489.9	490.7	447.8	396.6	343.2	306.3	283.0
72.5°	333.6	348.0	374.2	393.7	411.6	405.8	366.5	326.1	283.0	255.1	237.8
75°	257.4	270.1	283.7	292.8	292.8	285.2	256.7	226.5	201.7	185.1	179.8
77.5°	187.1	197.7	202.2	200.8	198.0	186.3	168.2	148.5	139.7	131.9	127.9
80°	146.8	151.3	152.8	149.0	144.5	130.9	118.9	110.7	102.4	99.3	97.8
82.5°	108.8	112.7	108.8	109.9	99.9	88.8	82.2	79.4	75.9	74.6	73.1
85°	58.0	57.2	55.7	51.9	45.1	43.6	42.9	42.1	40.6	41.4	39.9
87.5°	21.4	20.3	18.6	18.7	19.3	18.6	19.7	20.2	20.7	20.5	22.1
90°	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1
92.5°	34.4	38.4	42.3	46.4	49.2	51.0	52.8	54.5	56.3	57.4	58.5
95°	88.1	91.0	93.8	96.6	99.2	101.4	103.6	105.8	108.0	109.0	109.9
97.5°	151.2	153.4	155.8	158.1	160.5	163.1	165.6	168.2	170.8	171.9	173.1
100°	200.2	201.5	202.7	204.1	206.0	209.0	211.8	214.6	217.4	218.1	218.7
102.5°	251.8	252.3	252.8	253.3	254.9	257.4	260.0	262.6	265.2	266.1	266.9
105°	331.5	331.8	332.1	332.4	333.2	334.4	335.7	337.0	338.3	339.2	340.2
107.5°	415.4	415.8	416.1	416.5	416.8	417.0	417.2	417.4	417.5	418.4	419.3
110°	472.5	473.1	473.7	474.4	474.6	474.2	473.9	473.5	473.3	472.6	472.0



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	531.1	531.2	531.3	531.5	531.2	530.7	530.1	529.5	529.0	528.9	528.7
115°	619.6	619.6	619.6	619.6	619.3	618.7	618.0	617.5	616.8	616.5	616.1
117.5°	703.4	703.7	704.0	704.3	704.2	703.7	703.2	702.8	702.4	701.3	700.2
120°	760.2	761.5	762.7	763.9	764.1	763.2	762.2	761.3	760.3	758.7	757.1
122.5°	817.4	817.9	818.4	818.9	819.0	818.5	818.0	817.7	817.2	816.1	815.0
125°	902.5	902.5	902.5	902.5	902.3	902.0	901.6	901.4	901.1	900.4	899.8
127.5°	981.0	981.9	982.9	983.8	984.1	983.5	983.1	982.6	982.0	981.4	980.8
130°	1035.6	1036.5	1037.5	1038.4	1038.9	1038.9	1038.9	1038.9	1038.9	1038.3	1037.6
132.5°	1091.1	1091.7	1092.4	1093.2	1093.3	1093.1	1092.9	1092.6	1092.3	1091.7	1091.1
135°	1165.8	1167.7	1169.7	1171.6	1172.5	1172.5	1172.5	1172.5	1172.5	1171.9	1171.2
137.5°	1245.0	1245.9	1246.8	1247.6	1248.4	1248.9	1249.3	1249.9	1250.4	1249.5	1248.8
140°	1298.2	1298.8	1299.5	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0	1299.8
142.5°	1347.1	1347.7	1348.3	1349.0	1349.2	1348.9	1348.7	1348.4	1348.1	1348.1	1348.0
145°	1415.3	1416.6	1417.9	1419.2	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9	1420.6
147.5°	1482.7	1484.2	1485.7	1487.2	1487.9	1487.6	1487.3	1487.1	1486.9	1486.6	1486.4
150°	1523.3	1524.7	1525.9	1527.2	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8
152.5°	1561.5	1562.3	1563.0	1563.8	1564.3	1564.5	1564.8	1565.1	1565.3	1566.0	1566.8
155°	1620.1	1620.1	1620.1	1620.1	1620.0	1619.7	1619.4	1619.1	1618.7	1620.0	1621.3
157.5°	1669.6	1669.1	1668.5	1667.9	1667.6	1667.5	1667.5	1667.5	1667.4	1668.3	1669.2
160°	1699.4	1699.1	1698.8	1698.5	1698.2	1697.9	1697.5	1697.2	1697.0	1697.9	1698.8
162.5°	1726.3	1725.4	1724.6	1723.7	1723.2	1722.9	1722.6	1722.2	1721.9	1723.6	1725.3
165°	1762.7	1761.8	1760.9	1759.9	1759.2	1758.5	1757.8	1757.3	1756.6	1758.5	1760.4
167.5°	1790.5	1789.2	1787.9	1786.6	1785.9	1786.0	1786.0	1786.1	1786.2	1788.1	1790.0
170°	1806.2	1804.6	1803.0	1801.5	1800.8	1801.1	1801.5	1801.8	1802.0	1803.9	1805.9
172.5°	1817.8	1816.5	1815.1	1813.8	1813.2	1813.3	1813.4	1813.4	1813.5	1815.6	1817.8
175°	1833.2	1831.6	1830.0	1828.4	1827.5	1827.2	1826.8	1826.6	1826.3	1828.4	1830.7
177.5°	1838.6	1837.4	1836.1	1834.8	1834.2	1834.2	1834.2	1834.2	1834.2	1836.0	1837.8
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8	1867.8
2.5°	1959.3	1961.7	1963.5	1969.5	1970.1	1975.6	1970.1
5°	2121.4	2131.9	2148.5	2165.0	2166.5	2177.1	2158.2
7.5°	2303.2	2327.6	2342.8	2369.6	2380.1	2386.7	2375.9
10°	2428.5	2451.0	2490.9	2510.5	2530.1	2533.0	2524.0
12.5°	2549.5	2585.3	2616.7	2653.7	2652.9	2679.4	2669.7
15°	2710.7	2747.5	2791.2	2832.5	2847.6	2847.6	2859.7
17.5°	2825.6	2893.2	2938.4	2970.9	3006.3	3012.6	3008.3
20°	2903.3	2976.3	3024.4	3066.6	3090.7	3097.5	3097.5
22.5°	2961.1	3023.2	3070.2	3108.1	3128.0	3135.9	3133.6
25°	3001.1	3054.5	3083.2	3094.5	3099.6	3098.2	3083.9
27.5°	2946.3	2943.9	2925.8	2891.2	2865.2	2849.4	2831.3
30°	2841.6	2802.5	2757.3	2707.6	2643.6	2594.7	2579.6
32.5°	2685.7	2597.7	2521.3	2438.5	2369.7	2320.8	2300.4
35°	2384.1	2244.9	2131.2	2031.8	1959.6	1914.5	1899.4
37.5°	2026.1	1891.4	1750.7	1654.4	1594.5	1548.9	1531.8
40°	1798.6	1651.8	1529.2	1438.9	1377.1	1332.8	1332.0
42.5°	1590.8	1450.8	1335.3	1270.3	1203.7	1174.4	1174.2
45°	1302.6	1190.5	1092.7	1041.5	1001.6	977.5	970.7
47.5°	1078.6	985.8	920.7	879.9	847.3	832.0	822.1
50°	952.7	871.5	819.5	784.1	766.1	746.5	745.0
52.5°	847.9	782.3	741.9	713.1	690.2	678.4	678.8
55°	712.7	660.7	632.2	610.3	592.2	583.2	579.5
57.5°	600.4	561.4	540.6	520.6	512.9	505.9	503.9
60°	530.6	504.2	484.7	468.8	457.5	455.2	454.5
62.5°	472.8	445.2	431.7	419.4	411.2	407.7	406.3
65°	389.8	369.5	357.4	347.7	344.7	339.4	338.7
67.5°	314.2	302.1	294.1	287.3	283.2	283.0	283.0
70°	267.9	261.1	254.4	250.6	248.4	246.9	246.9
72.5°	228.2	223.2	217.6	215.7	215.2	213.7	213.1
75°	173.8	168.5	169.3	165.6	162.6	158.8	156.6
77.5°	123.3	119.5	118.8	118.3	115.7	115.3	116.5
80°	95.6	91.8	91.0	91.8	91.0	88.8	88.8
82.5°	72.7	69.6	68.8	68.3	67.6	68.3	67.1
85°	39.1	37.6	37.6	37.6	39.1	38.4	37.6
87.5°	21.2	21.0	21.9	21.4	21.5	21.0	21.8
90°	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	59.7	60.8	61.5	61.9	62.3	62.7	63.1
95°	110.8	111.8	112.3	112.3	112.3	112.3	112.3
97.5°	174.3	175.4	176.0	176.0	176.0	176.0	176.0
100°	219.3	220.0	220.3	220.3	220.3	220.3	220.3
102.5°	267.9	268.7	269.3	269.6	269.8	270.0	270.3
105°	341.1	342.0	343.0	343.9	344.9	345.8	346.8
107.5°	420.2	421.1	421.5	421.4	421.4	421.3	421.2
110°	471.4	470.7	470.9	471.8	472.8	473.7	474.7



TEST NUMBER: P333112-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	528.6	528.5	528.5	528.7	528.9	529.0	529.2
115°	615.9	615.6	615.2	614.9	614.6	614.3	614.0
117.5°	699.2	698.0	697.2	696.5	696.0	695.3	694.7
120°	755.6	754.0	753.6	754.2	754.8	755.4	756.1
122.5°	814.0	812.9	811.8	810.7	809.5	808.4	807.3
125°	899.2	898.5	897.9	897.2	896.6	896.0	895.3
127.5°	980.1	979.5	978.9	978.5	978.0	977.4	976.9
130°	1037.0	1036.3	1035.4	1034.2	1032.9	1031.6	1030.4
132.5°	1090.4	1089.8	1089.2	1088.7	1088.3	1087.7	1087.2
135°	1170.6	1170.0	1169.1	1168.2	1167.2	1166.3	1165.4
137.5°	1247.9	1247.1	1246.8	1247.0	1247.2	1247.4	1247.5
140°	1299.5	1299.1	1298.8	1298.5	1298.2	1297.9	1297.6
142.5°	1347.9	1347.9	1347.8	1347.7	1347.7	1347.6	1347.6
145°	1420.2	1419.9	1419.3	1418.3	1417.4	1416.5	1415.5
147.5°	1486.1	1485.8	1485.5	1485.3	1485.0	1484.6	1484.3
150°	1527.8	1527.8	1527.7	1527.3	1527.0	1526.7	1526.4
152.5°	1567.5	1568.3	1568.3	1567.4	1566.7	1565.8	1565.0
155°	1622.5	1623.8	1623.8	1622.5	1621.3	1620.0	1618.7
157.5°	1670.2	1671.1	1671.0	1670.0	1669.0	1667.8	1666.8
160°	1699.8	1700.7	1700.3	1698.8	1697.2	1695.6	1694.0
162.5°	1727.0	1728.7	1728.8	1727.2	1725.7	1724.1	1722.5
165°	1762.3	1764.2	1764.5	1763.2	1762.0	1760.7	1759.4
167.5°	1791.9	1793.8	1793.8	1791.8	1789.8	1787.8	1785.8
170°	1807.8	1809.7	1809.5	1807.3	1805.1	1802.9	1800.6
172.5°	1819.9	1822.0	1822.0	1819.8	1817.6	1815.3	1813.2
175°	1832.9	1835.1	1835.1	1832.9	1830.7	1828.4	1826.3
177.5°	1839.5	1841.3	1841.2	1839.1	1837.1	1835.1	1833.1
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6

(END OF REPORT)