

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333094-935

Luminaire Tested: **S124RDIW-S1020D1560U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333094-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8254.3 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333094-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333094-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P333094-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.8
10°-20°	407.3	4.9
20°-30°	588.1	7.1
30°-40°	666.6	8.1
40°-50°	643.7	7.8
50°-60°	535.3	6.5
60°-70°	369.6	4.5
70°-80°	187.4	2.3
80°-90°	53.1	0.6
90°-100°	110.7	1.3
100°-110°	328.0	4.0
110°-120°	556.7	6.7
120°-130°	734.0	8.9
130°-140°	824.4	10.0
140°-150°	810.1	9.8
150°-160°	681.3	8.3
160°-170°	453.3	5.5
170°-180°	158.7	1.9
0°-30°	1141.4	13.8
0°-40°	1808.0	21.9
0°-60°	2987.0	36.2
0°-90°	3597.0	43.6
90°-120°	995.4	12.1
90°-150°	3363.9	40.8
90°-180°	4657.0	56.4
0°-180°	8254.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	4	18	29	36	39	8
95°	78	89	99	102	102	87
105°	302	304	309	313	317	321
115°	566	566	563	562	561	558
125°	824	824	823	820	818	734
135°	1063	1071	1071	1068	1064	822
145°	1292	1297	1298	1297	1293	808
155°	1480	1480	1479	1483	1479	681
165°	1611	1607	1605	1612	1607	454
175°	1676	1670	1668	1676	1668	159
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P333094-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.6	21.6	20.6	19.5	18.4	18.1	18.3	18.5	18.8	19.0	19.2
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	27.8	31.4	35.0	38.7	42.4	44.9	46.6	48.2	49.8	51.4	52.4
95°	77.9	80.5	83.1	85.7	88.3	90.6	92.6	94.6	96.7	98.7	99.5
97.5°	136.0	138.1	140.2	142.3	144.4	146.6	149.0	151.3	153.7	156.0	157.0
100°	181.8	182.9	184.1	185.2	186.4	188.2	190.9	193.5	196.0	198.6	199.2
102.5°	229.5	230.0	230.5	230.9	231.4	232.8	235.1	237.5	239.9	242.3	243.1
105°	302.5	302.8	303.1	303.3	303.7	304.4	305.5	306.7	307.8	309.0	309.9
107.5°	379.1	379.4	379.8	380.1	380.5	380.7	380.9	381.1	381.3	381.4	382.2
110°	431.0	431.6	432.1	432.7	433.3	433.5	433.2	432.9	432.6	432.3	431.7



TEST NUMBER: P333094-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.0	485.2	485.3	485.3	485.5	485.3	484.7	484.2	483.7	483.2	483.1
115°	566.0	566.0	566.0	566.0	566.0	565.8	565.2	564.6	564.0	563.4	563.2
117.5°	642.4	642.6	642.8	643.1	643.3	643.3	642.8	642.4	642.0	641.6	640.6
120°	693.3	694.4	695.6	696.7	697.8	698.0	697.2	696.3	695.4	694.6	693.1
122.5°	746.2	746.7	747.2	747.6	748.0	748.1	747.7	747.3	746.9	746.5	745.5
125°	824.4	824.4	824.4	824.4	824.4	824.2	824.0	823.6	823.4	823.1	822.5
127.5°	895.3	896.1	897.0	897.9	898.7	899.0	898.5	898.0	897.6	897.1	896.5
130°	945.1	946.0	946.8	947.7	948.6	949.0	949.0	949.0	949.0	949.0	948.5
132.5°	996.0	996.7	997.3	997.9	998.6	998.8	998.5	998.3	998.1	997.8	997.3
135°	1063.2	1065.0	1066.7	1068.5	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5
137.5°	1136.5	1137.3	1138.1	1138.9	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4
140°	1185.3	1185.9	1186.5	1187.1	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6
142.5°	1229.9	1230.5	1231.1	1231.7	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5
145°	1291.8	1292.9	1294.1	1295.2	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0
147.5°	1353.1	1354.4	1355.8	1357.2	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0
150°	1390.4	1391.5	1392.8	1393.9	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1425.7	1426.4	1427.1	1427.8	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6
155°	1480.0	1480.0	1480.0	1480.0	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9
157.5°	1525.7	1525.2	1524.7	1524.1	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0
160°	1552.7	1552.4	1552.1	1551.9	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0
162.5°	1577.6	1576.9	1576.1	1575.4	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5
165°	1611.1	1610.2	1609.4	1608.5	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4
167.5°	1636.8	1635.6	1634.4	1633.2	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4
170°	1651.4	1649.9	1648.5	1647.0	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9
172.5°	1661.7	1660.5	1659.3	1658.1	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5
175°	1676.0	1674.6	1673.2	1671.7	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3
177.5°	1680.7	1679.6	1678.4	1677.2	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333094-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	19.3	19.5	19.5	19.8	20.1	20.5	20.8	21.1
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	53.5	54.5	55.5	56.2	56.6	56.9	57.3	57.6
95°	100.4	101.3	102.1	102.5	102.5	102.5	102.5	102.5
97.5°	158.2	159.2	160.2	160.7	160.7	160.7	160.7	160.7
100°	199.8	200.4	201.0	201.2	201.2	201.2	201.2	201.2
102.5°	243.8	244.7	245.5	246.0	246.2	246.5	246.7	246.9
105°	310.7	311.6	312.5	313.3	314.2	315.0	315.9	316.8
107.5°	383.1	383.8	384.7	385.0	385.0	385.0	384.9	384.8
110°	431.2	430.6	430.0	430.2	431.0	431.9	432.7	433.6



TEST NUMBER: P333094-935

CATALOG NUMBER: S124RDIW-S1020D1560U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	482.8	482.8	482.8	482.9	483.1	483.3	483.5
115°	562.8	562.6	562.3	562.0	561.7	561.5	561.1	560.9
117.5°	639.6	638.7	637.7	636.9	636.3	635.8	635.2	634.6
120°	691.6	690.3	688.8	688.4	689.0	689.5	690.1	690.7
122.5°	744.5	743.6	742.6	741.6	740.5	739.5	738.5	737.4
125°	821.9	821.4	820.8	820.2	819.6	819.1	818.5	817.9
127.5°	896.0	895.4	894.8	894.2	893.8	893.4	892.9	892.4
130°	947.9	947.3	946.7	945.8	944.7	943.6	942.4	941.2
132.5°	996.7	996.1	995.5	995.0	994.5	994.1	993.6	993.2
135°	1069.9	1069.4	1068.8	1068.0	1067.1	1066.3	1065.4	1064.5
137.5°	1140.7	1140.0	1139.2	1138.9	1139.1	1139.3	1139.4	1139.6
140°	1187.3	1187.1	1186.7	1186.5	1186.2	1185.9	1185.6	1185.3
142.5°	1231.4	1231.3	1231.3	1231.2	1231.1	1231.1	1231.1	1231.0
145°	1297.7	1297.4	1297.1	1296.5	1295.6	1294.8	1293.9	1293.0
147.5°	1357.8	1357.5	1357.3	1357.0	1356.8	1356.5	1356.2	1355.9
150°	1395.6	1395.6	1395.6	1395.5	1395.2	1394.9	1394.6	1394.3
152.5°	1431.2	1431.9	1432.6	1432.6	1431.8	1431.2	1430.4	1429.6
155°	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7
157.5°	1524.8	1525.7	1526.6	1526.5	1525.5	1524.6	1523.5	1522.6
160°	1551.9	1552.7	1553.6	1553.2	1551.9	1550.4	1548.9	1547.5
162.5°	1576.1	1577.6	1579.2	1579.2	1577.8	1576.4	1574.9	1573.5
165°	1608.1	1609.8	1611.5	1611.9	1610.7	1609.6	1608.3	1607.2
167.5°	1635.1	1636.8	1638.6	1638.6	1636.8	1635.0	1633.1	1631.3
170°	1649.7	1651.4	1653.1	1652.9	1651.0	1648.9	1646.9	1644.9
172.5°	1660.5	1662.4	1664.4	1664.4	1662.3	1660.4	1658.3	1656.3
175°	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3
177.5°	1678.8	1680.3	1682.0	1681.9	1680.0	1678.2	1676.4	1674.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6

(END OF REPORT)