

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333114-830

Luminaire Tested: **S124RDIW-S1195D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333114-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9645.2 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333114-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333114-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P333114-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	1.9
10°-20°	514.9	5.3
20°-30°	743.5	7.7
30°-40°	842.8	8.7
40°-50°	813.8	8.4
50°-60°	676.7	7.0
60°-70°	467.3	4.8
70°-80°	236.9	2.5
80°-90°	66.3	0.7
90°-100°	121.2	1.3
100°-110°	359.1	3.7
110°-120°	609.4	6.3
120°-130°	803.6	8.3
130°-140°	902.4	9.4
140°-150°	886.8	9.2
150°-160°	745.9	7.7
160°-170°	496.2	5.1
170°-180°	173.8	1.8
0°-30°	1443.1	15.0
0°-40°	2285.8	23.7
0°-60°	3776.4	39.2
0°-90°	4546.9	47.1
90°-120°	1089.7	11.3
90°-150°	3682.5	38.2
90°-180°	5098.0	52.9
0°-180°	9645.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	4	20	31	40	43	9
95°	85	98	108	112	112	95
105°	331	333	338	342	347	351
115°	620	619	617	615	614	611
125°	902	902	901	898	895	804
135°	1164	1172	1172	1170	1165	900
145°	1414	1420	1421	1420	1416	885
155°	1620	1620	1619	1624	1619	745
165°	1764	1760	1757	1764	1759	497
175°	1835	1828	1826	1835	1826	174
180°	1838	1838	1838	1838	1838	



TEST NUMBER: P333114-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	28.6	27.1	25.6	24.2	22.8	22.1	22.4	22.6	22.9	23.1	23.2
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	30.4	34.4	38.4	42.3	46.4	49.2	51.0	52.8	54.5	56.3	57.4
95°	85.3	88.1	91.0	93.8	96.6	99.2	101.4	103.6	105.8	108.0	109.0
97.5°	148.9	151.2	153.4	155.8	158.1	160.5	163.1	165.6	168.2	170.8	171.9
100°	199.0	200.2	201.5	202.7	204.1	206.0	209.0	211.8	214.6	217.4	218.1
102.5°	251.3	251.8	252.3	252.8	253.3	254.9	257.4	260.0	262.6	265.2	266.1
105°	331.1	331.5	331.8	332.1	332.4	333.2	334.4	335.7	337.0	338.3	339.2
107.5°	415.0	415.4	415.8	416.1	416.5	416.8	417.0	417.2	417.4	417.5	418.4
110°	471.8	472.5	473.1	473.7	474.4	474.6	474.2	473.9	473.5	473.3	472.6



TEST NUMBER: P333114-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.9	531.1	531.2	531.3	531.5	531.2	530.7	530.1	529.5	529.0	528.9
115°	619.6	619.6	619.6	619.6	619.6	619.3	618.7	618.0	617.5	616.8	616.5
117.5°	703.2	703.4	703.7	704.0	704.3	704.2	703.7	703.2	702.8	702.4	701.3
120°	758.9	760.2	761.5	762.7	763.9	764.1	763.2	762.2	761.3	760.3	758.7
122.5°	816.9	817.4	817.9	818.4	818.9	819.0	818.5	818.0	817.7	817.2	816.1
125°	902.5	902.5	902.5	902.5	902.5	902.3	902.0	901.6	901.4	901.1	900.4
127.5°	980.1	981.0	981.9	982.9	983.8	984.1	983.5	983.1	982.6	982.0	981.4
130°	1034.6	1035.6	1036.5	1037.5	1038.4	1038.9	1038.9	1038.9	1038.9	1038.9	1038.3
132.5°	1090.3	1091.1	1091.7	1092.4	1093.2	1093.3	1093.1	1092.9	1092.6	1092.3	1091.7
135°	1163.9	1165.8	1167.7	1169.7	1171.6	1172.5	1172.5	1172.5	1172.5	1172.5	1171.9
137.5°	1244.2	1245.0	1245.9	1246.8	1247.6	1248.4	1248.9	1249.3	1249.9	1250.4	1249.5
140°	1297.6	1298.2	1298.8	1299.5	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0
142.5°	1346.4	1347.1	1347.7	1348.3	1349.0	1349.2	1348.9	1348.7	1348.4	1348.1	1348.1
145°	1414.1	1415.3	1416.6	1417.9	1419.2	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9
147.5°	1481.2	1482.7	1484.2	1485.7	1487.2	1487.9	1487.6	1487.3	1487.1	1486.9	1486.6
150°	1522.1	1523.3	1524.7	1525.9	1527.2	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8
152.5°	1560.8	1561.5	1562.3	1563.0	1563.8	1564.3	1564.5	1564.8	1565.1	1565.3	1566.0
155°	1620.1	1620.1	1620.1	1620.1	1620.1	1620.0	1619.7	1619.4	1619.1	1618.7	1620.0
157.5°	1670.2	1669.6	1669.1	1668.5	1667.9	1667.6	1667.5	1667.5	1667.5	1667.4	1668.3
160°	1699.8	1699.4	1699.1	1698.8	1698.5	1698.2	1697.9	1697.5	1697.2	1697.0	1697.9
162.5°	1727.0	1726.3	1725.4	1724.6	1723.7	1723.2	1722.9	1722.6	1722.2	1721.9	1723.6
165°	1763.7	1762.7	1761.8	1760.9	1759.9	1759.2	1758.5	1757.8	1757.3	1756.6	1758.5
167.5°	1791.9	1790.5	1789.2	1787.9	1786.6	1785.9	1786.0	1786.0	1786.1	1786.2	1788.1
170°	1807.8	1806.2	1804.6	1803.0	1801.5	1800.8	1801.1	1801.5	1801.8	1802.0	1803.9
172.5°	1819.1	1817.8	1816.5	1815.1	1813.8	1813.2	1813.3	1813.4	1813.4	1813.5	1815.6
175°	1834.8	1833.2	1831.6	1830.0	1828.4	1827.5	1827.2	1826.8	1826.6	1826.3	1828.4
177.5°	1839.8	1838.6	1837.4	1836.1	1834.8	1834.2	1834.2	1834.2	1834.2	1834.2	1836.0
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333114-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	23.4	23.5	23.6	23.8	24.2	24.6	25.0	25.4
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	58.5	59.7	60.8	61.5	61.9	62.3	62.7	63.1
95°	109.9	110.8	111.8	112.3	112.3	112.3	112.3	112.3
97.5°	173.1	174.3	175.4	176.0	176.0	176.0	176.0	176.0
100°	218.7	219.3	220.0	220.3	220.3	220.3	220.3	220.3
102.5°	266.9	267.9	268.7	269.3	269.6	269.8	270.0	270.3
105°	340.2	341.1	342.0	343.0	343.9	344.9	345.8	346.8
107.5°	419.3	420.2	421.1	421.5	421.4	421.4	421.3	421.2
110°	472.0	471.4	470.7	470.9	471.8	472.8	473.7	474.7



TEST NUMBER: P333114-830

CATALOG NUMBER: S124RDIW-S1195D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	528.7	528.6	528.5	528.5	528.7	528.9	529.0	529.2
115°	616.1	615.9	615.6	615.2	614.9	614.6	614.3	614.0
117.5°	700.2	699.2	698.0	697.2	696.5	696.0	695.3	694.7
120°	757.1	755.6	754.0	753.6	754.2	754.8	755.4	756.1
122.5°	815.0	814.0	812.9	811.8	810.7	809.5	808.4	807.3
125°	899.8	899.2	898.5	897.9	897.2	896.6	896.0	895.3
127.5°	980.8	980.1	979.5	978.9	978.5	978.0	977.4	976.9
130°	1037.6	1037.0	1036.3	1035.4	1034.2	1032.9	1031.6	1030.4
132.5°	1091.1	1090.4	1089.8	1089.2	1088.7	1088.3	1087.7	1087.2
135°	1171.2	1170.6	1170.0	1169.1	1168.2	1167.2	1166.3	1165.4
137.5°	1248.8	1247.9	1247.1	1246.8	1247.0	1247.2	1247.4	1247.5
140°	1299.8	1299.5	1299.1	1298.8	1298.5	1298.2	1297.9	1297.6
142.5°	1348.0	1347.9	1347.9	1347.8	1347.7	1347.7	1347.6	1347.6
145°	1420.6	1420.2	1419.9	1419.3	1418.3	1417.4	1416.5	1415.5
147.5°	1486.4	1486.1	1485.8	1485.5	1485.3	1485.0	1484.6	1484.3
150°	1527.8	1527.8	1527.8	1527.7	1527.3	1527.0	1526.7	1526.4
152.5°	1566.8	1567.5	1568.3	1568.3	1567.4	1566.7	1565.8	1565.0
155°	1621.3	1622.5	1623.8	1623.8	1622.5	1621.3	1620.0	1618.7
157.5°	1669.2	1670.2	1671.1	1671.0	1670.0	1669.0	1667.8	1666.8
160°	1698.8	1699.8	1700.7	1700.3	1698.8	1697.2	1695.6	1694.0
162.5°	1725.3	1727.0	1728.7	1728.8	1727.2	1725.7	1724.1	1722.5
165°	1760.4	1762.3	1764.2	1764.5	1763.2	1762.0	1760.7	1759.4
167.5°	1790.0	1791.9	1793.8	1793.8	1791.8	1789.8	1787.8	1785.8
170°	1805.9	1807.8	1809.7	1809.5	1807.3	1805.1	1802.9	1800.6
172.5°	1817.8	1819.9	1822.0	1822.0	1819.8	1817.6	1815.3	1813.2
175°	1830.7	1832.9	1835.1	1835.1	1832.9	1830.7	1828.4	1826.3
177.5°	1837.8	1839.5	1841.3	1841.2	1839.1	1837.1	1835.1	1833.1
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6

(END OF REPORT)