

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333030-830

Luminaire Tested: **S124RDIW-S350D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333030-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5735.9 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333030-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333030-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	15
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P333030-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	1.0
10°-20°	152.6	2.7
20°-30°	220.4	3.8
30°-40°	249.8	4.4
40°-50°	241.2	4.2
50°-60°	200.6	3.5
60°-70°	138.5	2.4
70°-80°	70.2	1.2
80°-90°	22.7	0.4
90°-100°	104.3	1.8
100°-110°	308.8	5.4
110°-120°	524.1	9.1
120°-130°	691.1	12.0
130°-140°	776.2	13.5
140°-150°	762.7	13.3
150°-160°	641.5	11.2
160°-170°	426.8	7.4
170°-180°	149.5	2.6
0°-30°	427.8	7.5
0°-40°	677.6	11.8
0°-60°	1119.4	19.5
0°-90°	1350.9	23.6
90°-120°	937.2	16.3
90°-150°	3167.3	55.2
90°-180°	4385.0	76.4
0°-180°	5735.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	4	17	27	34	37	6
95°	73	84	93	96	97	82
105°	285	286	291	295	298	302
115°	533	533	530	529	528	525
125°	776	776	775	772	770	692
135°	1001	1008	1008	1006	1002	774
145°	1216	1221	1222	1221	1218	761
155°	1394	1393	1392	1397	1392	641
165°	1517	1513	1511	1518	1513	427
175°	1578	1572	1571	1578	1571	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333030-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	9.0	8.9	8.9	8.9	8.8	9.0	9.3	9.7	10.0	10.4	10.7
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	26.2	29.6	33.0	36.4	39.9	42.3	43.8	45.3	46.8	48.4	49.4
95°	73.3	75.8	78.2	80.7	83.1	85.3	87.2	89.1	91.0	92.9	93.7
97.5°	128.1	130.1	132.1	133.9	135.9	138.0	140.3	142.5	144.7	146.9	147.9
100°	171.2	172.2	173.3	174.4	175.5	177.2	179.6	182.1	184.5	187.0	187.6
102.5°	216.1	216.6	217.0	217.4	217.8	219.1	221.4	223.7	225.8	228.1	228.8
105°	284.8	285.1	285.4	285.6	285.9	286.5	287.7	288.8	289.8	291.0	291.7
107.5°	356.9	357.2	357.6	357.9	358.3	358.4	358.6	358.8	359.0	359.1	359.9
110°	405.9	406.3	406.9	407.5	408.0	408.1	407.8	407.6	407.4	407.1	406.5



TEST NUMBER: P333030-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	456.7	456.8	456.9	457.0	457.1	456.9	456.5	455.9	455.4	455.0	454.9
115°	532.9	532.9	532.9	532.9	532.9	532.7	532.2	531.6	531.0	530.5	530.3
117.5°	604.8	605.0	605.3	605.5	605.7	605.6	605.2	604.8	604.5	604.1	603.1
120°	652.7	653.8	654.9	656.0	657.0	657.2	656.4	655.6	654.8	653.9	652.6
122.5°	702.6	703.0	703.5	703.9	704.4	704.4	704.0	703.6	703.2	702.9	701.9
125°	776.2	776.2	776.2	776.2	776.2	776.1	775.8	775.5	775.2	775.0	774.4
127.5°	842.9	843.8	844.6	845.4	846.2	846.4	845.9	845.6	845.1	844.6	844.1
130°	889.9	890.7	891.6	892.3	893.2	893.5	893.5	893.5	893.5	893.5	893.0
132.5°	937.8	938.4	939.0	939.6	940.2	940.4	940.2	939.9	939.7	939.5	939.0
135°	1001.1	1002.8	1004.4	1006.0	1007.7	1008.4	1008.4	1008.4	1008.4	1008.4	1008.0
137.5°	1070.1	1070.8	1071.6	1072.3	1073.1	1073.7	1074.1	1074.6	1075.0	1075.4	1074.7
140°	1116.1	1116.5	1117.1	1117.7	1118.2	1118.4	1118.4	1118.4	1118.4	1118.4	1118.2
142.5°	1158.1	1158.6	1159.1	1159.7	1160.3	1160.4	1160.2	1160.0	1159.8	1159.5	1159.5
145°	1216.3	1217.4	1218.4	1219.6	1220.6	1221.3	1221.5	1221.8	1222.1	1222.4	1222.1
147.5°	1273.9	1275.3	1276.6	1277.9	1279.1	1279.7	1279.5	1279.3	1279.0	1278.8	1278.7
150°	1309.2	1310.2	1311.4	1312.4	1313.5	1314.0	1314.0	1314.0	1314.0	1314.0	1314.0
152.5°	1342.4	1343.0	1343.7	1344.3	1345.0	1345.5	1345.7	1345.9	1346.1	1346.3	1347.0
155°	1393.5	1393.5	1393.5	1393.5	1393.5	1393.4	1393.1	1392.8	1392.5	1392.3	1393.4
157.5°	1436.5	1436.1	1435.6	1435.0	1434.5	1434.3	1434.3	1434.2	1434.2	1434.1	1434.9
160°	1462.0	1461.7	1461.4	1461.1	1460.8	1460.6	1460.3	1460.1	1459.8	1459.5	1460.3
162.5°	1485.4	1484.7	1484.0	1483.3	1482.6	1482.1	1481.9	1481.6	1481.3	1481.0	1482.5
165°	1516.9	1516.2	1515.3	1514.5	1513.7	1513.1	1512.5	1511.9	1511.4	1510.8	1512.5
167.5°	1541.2	1540.0	1538.9	1537.8	1536.6	1536.1	1536.2	1536.2	1536.3	1536.3	1537.9
170°	1554.8	1553.5	1552.2	1550.8	1549.4	1548.9	1549.2	1549.4	1549.7	1549.9	1551.6
172.5°	1564.6	1563.5	1562.4	1561.2	1560.1	1559.5	1559.6	1559.6	1559.7	1559.7	1561.6
175°	1578.1	1576.7	1575.4	1574.0	1572.6	1571.8	1571.6	1571.3	1571.0	1570.7	1572.6
177.5°	1582.4	1581.4	1580.3	1579.2	1578.1	1577.6	1577.6	1577.6	1577.6	1577.6	1579.1
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5



TEST NUMBER: P333030-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	10.8	11.1	11.4	11.6	11.8	12.0	12.2	12.3
90°	30.2	31.8	33.4	34.5	35.1	35.6	36.1	36.7
92.5°	50.3	51.4	52.3	53.0	53.3	53.6	53.9	54.3
95°	94.5	95.4	96.1	96.6	96.6	96.6	96.6	96.6
97.5°	148.9	149.9	150.8	151.4	151.4	151.4	151.4	151.4
100°	188.1	188.7	189.2	189.5	189.5	189.5	189.5	189.5
102.5°	229.6	230.4	231.1	231.6	231.9	232.1	232.2	232.5
105°	292.6	293.4	294.2	295.0	295.8	296.6	297.5	298.2
107.5°	360.6	361.4	362.2	362.5	362.5	362.4	362.4	362.3
110°	406.0	405.4	404.9	405.0	405.9	406.6	407.5	408.3



TEST NUMBER: P333030-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	454.8	454.7	454.5	454.6	454.7	454.9	455.1	455.2
115°	530.0	529.7	529.4	529.1	528.9	528.6	528.3	528.1
117.5°	602.3	601.3	600.4	599.6	599.1	598.6	598.0	597.5
120°	651.3	649.9	648.6	648.1	648.7	649.2	649.8	650.3
122.5°	701.0	700.1	699.2	698.2	697.2	696.3	695.3	694.3
125°	773.9	773.4	772.8	772.2	771.8	771.2	770.6	770.1
127.5°	843.6	843.0	842.4	842.0	841.6	841.1	840.7	840.3
130°	892.5	891.9	891.4	890.6	889.5	888.3	887.3	886.2
132.5°	938.4	937.9	937.4	936.9	936.4	935.9	935.6	935.1
135°	1007.4	1006.8	1006.3	1005.6	1004.8	1004.0	1003.1	1002.3
137.5°	1074.0	1073.4	1072.6	1072.3	1072.5	1072.7	1072.8	1073.0
140°	1117.9	1117.7	1117.4	1117.1	1116.8	1116.5	1116.3	1116.1
142.5°	1159.4	1159.4	1159.3	1159.2	1159.2	1159.1	1159.1	1159.0
145°	1221.8	1221.5	1221.3	1220.8	1219.9	1219.1	1218.3	1217.5
147.5°	1278.4	1278.2	1278.0	1277.7	1277.4	1277.1	1277.0	1276.7
150°	1314.0	1314.0	1314.0	1313.9	1313.6	1313.3	1313.1	1312.9
152.5°	1347.6	1348.3	1349.0	1348.9	1348.2	1347.5	1346.8	1346.0
155°	1394.5	1395.5	1396.7	1396.7	1395.5	1394.5	1393.4	1392.3
157.5°	1435.7	1436.5	1437.4	1437.3	1436.3	1435.4	1434.5	1433.6
160°	1461.1	1462.0	1462.7	1462.4	1461.1	1459.8	1458.4	1457.1
162.5°	1483.9	1485.4	1486.9	1487.0	1485.5	1484.2	1482.9	1481.5
165°	1514.1	1515.7	1517.4	1517.7	1516.6	1515.4	1514.4	1513.3
167.5°	1539.5	1541.2	1542.8	1542.8	1541.1	1539.4	1537.8	1536.1
170°	1553.2	1554.8	1556.5	1556.3	1554.4	1552.6	1550.7	1548.8
172.5°	1563.4	1565.3	1567.2	1567.1	1565.2	1563.3	1561.4	1559.5
175°	1574.5	1576.4	1578.4	1578.4	1576.4	1574.5	1572.6	1570.7
177.5°	1580.6	1582.2	1583.7	1583.6	1581.9	1580.1	1578.4	1576.6
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5

(END OF REPORT)