

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333081-935

Luminaire Tested: **S124RDIW-S1020D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333081-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D770U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6237.7 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333081-935

CATALOG NUMBER: S124RDIW-S1020D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333081-935

CATALOG NUMBER: S124RDIW-S1020D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	36
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P333081-935

CATALOG NUMBER: S124RDIW-S1020D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	2.3
10°-20°	407.3	6.5
20°-30°	588.1	9.4
30°-40°	666.6	10.7
40°-50°	643.7	10.3
50°-60°	535.3	8.6
60°-70°	369.6	5.9
70°-80°	187.4	3.0
80°-90°	50.5	0.8
90°-100°	29.2	0.5
100°-110°	186.3	3.0
110°-120°	356.5	5.7
120°-130°	452.5	7.3
130°-140°	484.2	7.8
140°-150°	452.7	7.3
150°-160°	365.1	5.9
160°-170°	235.5	3.8
170°-180°	81.2	1.3
0°-30°	1141.4	18.3
0°-40°	1808.0	29.0
0°-60°	2987.0	47.9
0°-90°	3594.5	57.6
90°-120°	572.0	9.2
90°-150°	1961.4	31.4
90°-180°	2643.0	42.4
0°-180°	6237.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	2	9	14	18	19	5
95°	35	15	14	18	18	45
105°	192	196	199	204	182	201
115°	359	361	360	362	362	353
125°	505	507	506	508	509	451
135°	626	626	628	630	631	482
145°	722	724	724	725	726	451
155°	792	792	791	793	791	365
165°	835	832	832	837	832	236
175°	854	851	851	856	849	81
180°	854	854	854	854	854	



TEST NUMBER: P333081-935

CATALOG NUMBER: S124RDIW-S1020D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.3	20.9	19.5	18.2	16.8	16.1	16.1	16.1	16.1	16.2	16.1
90°	1.9	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9
92.5°	8.1	8.2	8.3	8.3	8.4	9.0	10.2	11.3	12.4	13.5	14.4
95°	35.1	30.3	25.5	20.7	15.8	13.5	13.6	13.8	13.9	14.0	14.9
97.5°	74.6	77.7	80.7	83.7	86.7	80.2	64.4	48.6	32.7	16.9	17.0
100°	104.8	107.4	109.9	112.4	115.0	106.5	87.0	67.3	47.7	28.2	25.7
102.5°	138.5	140.4	142.3	144.2	146.0	145.7	143.2	140.6	138.0	135.5	109.4
105°	192.3	193.2	194.1	194.9	195.8	196.6	197.3	197.9	198.7	199.4	200.7
107.5°	242.4	242.8	243.2	243.7	244.1	244.8	245.7	246.7	247.6	248.6	249.3
110°	276.1	276.6	277.0	277.4	277.8	278.4	279.3	280.2	281.0	281.8	282.1



TEST NUMBER: P333081-935

CATALOG NUMBER: S124RDIW-S1020D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.8	309.6	310.4	311.1	311.9	312.5	312.9	313.2	313.7	314.1	314.0
115°	359.2	359.6	360.1	360.4	360.8	361.0	360.8	360.8	360.6	360.4	360.8
117.5°	404.6	405.1	405.7	406.2	406.8	407.3	407.6	407.9	408.2	408.5	408.5
120°	435.2	435.8	436.4	437.0	437.5	437.7	437.6	437.5	437.3	437.1	437.5
122.5°	463.9	464.2	464.5	464.9	465.2	465.5	465.7	465.9	466.1	466.3	466.5
125°	504.9	505.5	506.0	506.6	507.1	507.3	507.0	506.8	506.4	506.2	506.6
127.5°	543.7	543.9	544.1	544.2	544.3	544.8	545.4	546.0	546.6	547.3	547.3
130°	568.8	568.9	569.1	569.2	569.4	569.6	570.1	570.5	570.9	571.4	571.5
132.5°	591.9	592.1	592.4	592.5	592.8	593.2	593.7	594.3	594.9	595.4	595.6
135°	626.3	626.2	626.0	625.9	625.8	625.9	626.5	627.1	627.7	628.3	628.5
137.5°	656.9	656.9	657.0	657.0	657.1	657.5	658.1	658.7	659.4	660.0	660.2
140°	676.8	677.1	677.3	677.7	678.0	678.2	678.6	678.8	679.1	679.4	679.8
142.5°	694.7	695.3	695.8	696.2	696.7	697.1	697.2	697.4	697.6	697.8	698.1
145°	722.2	722.6	723.1	723.5	723.9	724.1	724.1	724.1	724.1	724.1	724.3
147.5°	744.1	744.9	745.6	746.4	747.3	747.5	747.4	747.3	747.1	747.0	747.1
150°	759.9	760.4	761.0	761.6	762.2	762.4	762.2	762.1	762.0	761.8	761.8
152.5°	773.2	773.6	774.1	774.6	775.0	775.1	774.8	774.6	774.4	774.1	774.3
155°	791.9	792.0	792.1	792.3	792.5	792.3	791.9	791.4	791.0	790.6	791.2
157.5°	807.6	807.5	807.4	807.4	807.3	806.9	806.5	806.0	805.5	805.0	805.7
160°	816.7	816.3	816.0	815.5	815.1	814.8	814.7	814.5	814.3	814.2	815.1
162.5°	824.9	824.4	823.9	823.4	822.8	822.4	822.3	822.2	822.0	821.9	822.8
165°	835.3	834.6	833.9	833.2	832.5	832.2	832.2	832.2	832.2	832.2	833.3
167.5°	843.5	842.7	842.1	841.3	840.5	840.2	840.1	840.0	839.9	839.8	841.0
170°	848.1	847.2	846.4	845.5	844.7	844.3	844.5	844.6	844.7	844.9	846.0
172.5°	851.2	850.3	849.5	848.6	847.7	847.4	847.6	847.7	847.8	848.0	849.1
175°	854.5	853.6	852.8	852.0	851.1	850.8	850.8	851.0	851.2	851.3	852.6
177.5°	856.0	855.2	854.5	853.6	852.8	852.6	852.8	853.0	853.3	853.4	854.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P333081-935

CATALOG NUMBER: S124RDIW-S1020D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	16.1	16.0	16.0	16.1	16.4	16.6	16.9	17.1
90°	15.8	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	15.2	16.1	17.0	17.4	17.5	17.6	17.6	17.7
95°	15.8	16.6	17.5	18.0	18.1	18.3	18.4	18.5
97.5°	17.0	17.1	17.2	17.3	17.5	17.7	17.7	17.9
100°	23.3	20.8	18.4	17.3	17.5	17.7	17.7	17.9
102.5°	83.4	57.3	31.3	18.3	18.3	18.3	18.3	18.4
105°	202.0	203.2	204.5	202.6	197.5	192.3	187.3	182.2
107.5°	249.9	250.5	251.2	251.7	252.3	252.8	253.3	253.8
110°	282.4	282.7	283.0	283.4	283.8	284.2	284.6	285.1



TEST NUMBER: P333081-935

CATALOG NUMBER: S124RDIW-S1020D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.9	313.9	313.8	314.1	314.6	315.1	315.7	316.2
115°	361.0	361.3	361.6	361.7	361.7	361.7	361.7	361.7
117.5°	408.4	408.4	408.3	408.2	408.2	408.1	408.0	408.0
120°	437.7	438.0	438.2	438.2	438.0	437.7	437.5	437.1
122.5°	466.7	466.8	467.0	466.9	466.7	466.3	466.1	465.8
125°	507.0	507.5	507.9	508.2	508.3	508.4	508.6	508.8
127.5°	547.2	547.1	547.0	546.9	546.8	546.6	546.6	546.5
130°	571.6	571.8	572.0	572.0	572.0	572.0	572.0	572.0
132.5°	595.6	595.8	596.0	596.0	595.9	595.7	595.6	595.6
135°	628.8	629.1	629.4	629.6	629.9	630.3	630.5	630.8
137.5°	660.6	660.9	661.2	661.3	661.2	661.2	661.1	661.0
140°	680.2	680.6	681.1	681.4	681.5	681.7	681.8	681.9
142.5°	698.4	698.7	699.0	699.2	699.2	699.2	699.3	699.3
145°	724.4	724.5	724.7	724.9	725.1	725.5	725.7	726.0
147.5°	747.2	747.3	747.4	747.6	747.7	747.9	748.0	748.1
150°	761.8	761.8	761.8	761.9	762.1	762.2	762.3	762.4
152.5°	774.6	774.7	775.0	775.1	775.0	774.9	774.8	774.7
155°	791.7	792.3	792.8	792.9	792.5	792.0	791.6	791.3
157.5°	806.5	807.3	808.0	808.0	807.3	806.5	805.7	805.0
160°	816.0	816.7	817.6	817.6	816.7	816.0	815.1	814.2
162.5°	823.6	824.4	825.3	825.3	824.3	823.3	822.3	821.4
165°	834.4	835.5	836.6	836.6	835.3	834.1	832.8	831.5
167.5°	842.3	843.5	844.8	844.7	843.3	841.9	840.4	839.0
170°	847.1	848.3	849.5	849.3	847.9	846.4	845.1	843.6
172.5°	850.2	851.4	852.5	852.3	850.8	849.3	847.7	846.2
175°	853.9	855.1	856.4	856.2	854.5	852.8	851.1	849.4
177.5°	855.3	856.2	857.1	856.9	855.5	854.1	852.8	851.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5

(END OF REPORT)