

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333031-830

Luminaire Tested: **S124RDIW-S350D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333031-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1560U830-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7283.5 lumens  
Efficiency: N/A  
Efficacy: 136.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17
2	83	76	70	66	73	67	63	59	51	48	45	36	34	32	22	21	20	14
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	18	17	12
4	69	59	52	46	61	53	46	42	40	36	32	28	26	24	18	16	15	11
5	63	53	45	39	56	47	40	36	36	31	28	25	23	20	16	14	13	9
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	14	13	12	8
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9	7
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4469	4469	4469	4469
5°	5185	4483	3963	4483
10°	6133	4464	3536	4464
15°	7084	4422	3039	4422
20°	7887	4365	2748	4365
25°	8143	4309	2551	4309
30°	7128	4242	2433	4242
35°	5549	4142	2361	4142
40°	4161	4027	2323	4027
45°	3286	3843	2302	3843
50°	2773	3631	2236	3631
55°	2417	3398	2115	3398
60°	2175	3155	1873	3155
65°	1918	2894	1612	2894
70°	1725	2622	1452	2622
75°	1447	2324	1238	2324
80°	1223	1980	1162	1980
85°	1028	1556	1028	1556



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.6	0.7
10°-20°	161.8	2.2
20°-30°	253.1	3.5
30°-40°	281.4	3.9
40°-50°	249.6	3.4
50°-60°	194.5	2.7
60°-70°	127.4	1.7
70°-80°	62.6	0.9
80°-90°	20.9	0.3
90°-100°	65.0	0.9
100°-110°	414.4	5.7
110°-120°	792.8	10.9
120°-130°	1006.4	13.8
130°-140°	1076.8	14.8
140°-150°	1006.9	13.8
150°-160°	812.0	11.1
160°-170°	523.7	7.2
170°-180°	180.5	2.5
0°-30°	468.6	6.4
0°-40°	749.9	10.3
0°-60°	1194.1	16.4
0°-90°	1405.0	19.3
90°-120°	1272.2	17.5
90°-150°	4362.3	59.9
90°-180°	5879.0	80.7
0°-180°	7283.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	554	554	554	554	554	
5°	640	553	489	553	640	65
15°	848	529	364	529	848	241
25°	914	484	286	484	914	406
35°	563	420	240	420	563	353
45°	288	337	202	337	288	228
55°	172	241	150	241	172	156
65°	100	152	84	152	100	101
75°	46	74	40	74	46	51
85°	11	17	11	17	11	14
90°	43	4	43	4	43	19
95°	41	78	41	78	41	33
105°	405	428	405	428	405	353
115°	805	799	805	799	805	796
125°	1131	1123	1131	1123	1131	1008
135°	1403	1393	1403	1393	1403	1080
145°	1615	1606	1615	1606	1615	1009
155°	1760	1761	1760	1761	1760	811
165°	1849	1858	1849	1858	1849	522
175°	1889	1900	1889	1900	1889	180
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	584.0	585.6	584.0	583.8	582.0	581.5	580.8	578.4	574.2	571.7	572.2
5°	639.8	645.4	642.2	641.8	636.9	632.0	628.9	621.7	614.1	609.0	604.7
7.5°	704.3	707.5	705.5	702.4	694.5	689.9	682.7	673.4	659.7	649.3	639.8
10°	748.2	750.8	750.0	744.1	738.4	726.5	719.8	706.7	689.5	675.9	663.2
12.5°	791.4	794.2	786.4	786.6	775.6	766.3	755.7	739.1	719.3	701.8	685.9
15°	847.6	844.0	844.0	839.6	827.4	814.5	803.5	786.1	761.1	740.2	718.0
17.5°	891.7	893.0	891.2	880.6	871.0	857.6	837.5	817.3	794.1	765.9	743.4
20°	918.1	918.1	916.2	909.0	896.5	882.2	860.6	838.5	809.1	780.7	755.4
22.5°	928.9	929.5	927.2	921.3	910.1	896.2	877.7	855.3	824.9	793.1	761.6
25°	914.2	918.4	918.8	917.3	913.9	905.4	889.6	866.7	839.4	804.8	770.9
27.5°	839.2	844.6	849.3	857.1	867.3	872.6	873.4	861.7	837.9	804.6	770.5
30°	764.7	769.1	783.6	802.6	817.3	830.7	842.4	845.5	832.1	802.2	766.3
32.5°	681.8	688.0	702.5	722.8	747.3	770.1	796.1	809.4	809.0	791.1	757.9
35°	563.0	567.5	580.9	602.3	631.7	665.4	706.7	738.8	760.6	759.1	738.8
37.5°	454.1	459.1	472.6	490.4	519.0	560.6	600.6	644.9	685.2	707.9	701.2
40°	394.8	395.0	408.2	426.5	453.3	489.7	533.1	582.2	627.3	664.1	671.2
42.5°	348.1	348.1	356.8	376.5	395.8	430.0	471.6	520.3	573.1	615.6	634.4
45°	287.8	289.7	296.9	308.7	323.9	352.9	386.2	431.4	490.5	540.9	572.4
47.5°	243.6	246.7	251.2	260.8	272.9	292.2	319.7	360.4	408.5	463.9	508.7
50°	220.8	221.3	227.1	232.4	242.9	258.4	282.4	316.3	360.5	413.8	463.5
52.5°	201.2	201.1	204.6	211.4	219.9	231.9	251.4	282.2	321.4	369.2	420.6
55°	171.7	172.9	175.6	180.9	187.4	195.9	211.2	234.4	265.2	306.0	352.7
57.5°	149.4	150.0	152.0	154.3	160.2	166.5	178.0	194.1	220.0	253.4	296.9
60°	134.7	135.0	135.6	138.9	143.6	149.5	157.3	170.9	192.7	223.3	257.7
62.5°	120.5	120.8	121.9	124.3	128.0	132.0	140.2	151.1	169.2	195.3	226.2
65°	100.4	100.6	102.2	103.0	105.9	109.5	115.6	122.9	135.4	157.3	180.7
67.5°	83.9	83.9	84.0	85.2	87.2	89.5	93.1	99.1	108.5	121.9	142.5
70°	73.1	73.1	73.6	74.3	75.4	77.4	79.5	83.9	90.8	101.7	117.5
72.5°	63.2	63.3	63.8	63.9	64.5	66.2	67.7	70.5	75.6	83.9	96.7
75°	46.4	47.0	48.2	49.1	50.2	50.0	51.6	53.3	54.9	59.8	67.1
77.5°	34.5	34.2	34.3	35.1	35.2	35.4	36.6	37.9	39.1	41.4	44.0
80°	26.3	26.3	27.0	27.2	27.0	27.2	28.4	29.0	29.4	30.3	32.8
82.5°	19.9	20.3	20.1	20.3	20.4	20.6	21.6	21.7	22.1	22.5	23.5
85°	11.1	11.4	11.6	11.1	11.1	11.1	11.6	11.8	12.3	12.1	12.5
87.5°	12.4	12.2	12.2	12.1	12.2	11.7	11.5	11.5	10.7	10.6	10.0
90°	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1	33.2	31.3	28.7
92.5°	39.2	39.1	39.0	38.8	38.7	37.7	35.8	33.9	32.0	30.2	27.6
95°	41.2	40.9	40.6	40.2	40.0	38.8	36.9	35.1	33.2	31.3	30.9
97.5°	39.8	39.5	39.2	38.8	38.5	38.3	38.1	37.9	37.7	37.5	72.8
100°	39.8	39.5	39.2	38.8	38.5	41.1	46.5	51.8	57.2	62.6	106.1
102.5°	40.9	40.9	40.8	40.7	40.7	69.7	127.5	185.5	243.4	301.3	307.0
105°	405.1	416.5	427.8	439.2	450.5	454.9	452.0	449.1	446.3	443.5	441.9
107.5°	564.6	563.4	562.1	561.0	559.8	558.5	557.1	555.7	554.3	552.9	550.7
110°	634.0	633.0	632.1	631.1	630.2	629.3	628.8	628.1	627.5	626.8	624.9



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	703.3	702.1	700.9	699.7	698.5	698.0	698.0	698.2	698.3	698.5	697.6
115°	804.6	804.6	804.6	804.6	804.6	804.2	803.5	803.0	802.3	801.6	802.0
117.5°	907.4	907.6	907.7	907.8	908.0	908.0	908.1	908.3	908.4	908.5	907.9
120°	972.2	972.9	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2	972.5
122.5°	1035.9	1036.5	1037.2	1037.8	1038.4	1038.6	1038.2	1037.8	1037.5	1037.1	1036.6
125°	1131.4	1131.1	1130.8	1130.5	1130.2	1129.5	1128.6	1127.7	1126.7	1125.8	1126.3
127.5°	1215.3	1215.5	1215.8	1216.1	1216.3	1216.5	1216.7	1216.9	1217.1	1217.3	1215.8
130°	1272.1	1272.1	1272.1	1272.1	1272.1	1272.0	1271.7	1271.4	1271.0	1270.7	1269.8
132.5°	1324.5	1324.7	1324.9	1325.2	1325.5	1325.4	1325.1	1324.8	1324.5	1324.2	1323.0
135°	1402.9	1402.3	1401.7	1401.0	1400.4	1399.8	1399.1	1398.5	1397.9	1397.2	1396.0
137.5°	1470.0	1470.2	1470.4	1470.6	1470.7	1470.6	1469.8	1469.1	1468.4	1467.7	1466.3
140°	1516.6	1516.3	1516.0	1515.7	1515.3	1514.8	1513.8	1512.9	1511.9	1510.9	1510.3
142.5°	1555.3	1555.2	1555.2	1555.1	1555.0	1554.6	1554.0	1553.3	1552.6	1551.9	1551.5
145°	1614.7	1614.1	1613.4	1612.8	1612.2	1611.7	1611.4	1611.1	1610.7	1610.4	1610.4
147.5°	1663.9	1663.6	1663.2	1662.9	1662.6	1662.4	1662.1	1661.8	1661.6	1661.3	1661.6
150°	1695.7	1695.4	1695.1	1694.8	1694.5	1694.3	1694.3	1694.3	1694.3	1694.3	1694.6
152.5°	1723.0	1723.2	1723.3	1723.5	1723.7	1723.6	1723.1	1722.6	1722.1	1721.6	1722.1
155°	1759.7	1760.7	1761.6	1762.6	1763.5	1763.3	1762.1	1760.8	1759.5	1758.2	1759.3
157.5°	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4	1791.5
160°	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8	1811.2
162.5°	1826.7	1828.9	1831.1	1833.2	1835.3	1835.5	1833.6	1831.7	1829.8	1827.9	1828.2
165°	1849.3	1852.1	1854.9	1857.8	1860.6	1860.8	1858.2	1855.7	1853.1	1850.7	1850.7
167.5°	1866.0	1869.2	1872.4	1875.5	1878.7	1878.9	1876.0	1873.3	1870.5	1867.7	1867.9
170°	1876.2	1879.4	1882.5	1885.7	1888.9	1889.2	1886.7	1884.1	1881.6	1879.1	1878.8
172.5°	1881.9	1885.4	1888.8	1892.2	1895.5	1896.0	1893.5	1890.9	1888.4	1885.9	1885.6
175°	1889.0	1892.8	1896.6	1900.4	1904.2	1904.7	1901.9	1898.9	1896.1	1893.3	1893.0
177.5°	1893.6	1896.6	1899.6	1902.7	1905.7	1906.2	1904.2	1902.1	1900.2	1898.1	1897.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	570.4	568.0	566.7	563.8	560.4	558.6	557.0	554.7	551.7	548.5	546.2
5°	599.4	594.0	587.3	579.3	572.2	565.2	559.2	553.2	546.3	539.1	532.1
7.5°	629.1	618.6	607.2	594.0	581.3	569.6	558.8	548.7	537.1	526.6	517.2
10°	649.8	635.6	619.7	602.9	586.3	571.7	557.4	544.5	530.3	517.6	506.8
12.5°	666.6	649.8	630.7	609.9	589.7	572.2	555.8	538.9	522.7	509.0	494.6
15°	694.4	671.5	645.8	620.8	594.7	570.8	548.7	529.1	510.6	491.2	477.6
17.5°	713.6	686.3	655.1	625.1	594.3	566.1	540.6	517.3	495.9	476.1	459.9
20°	725.0	694.8	660.3	626.1	591.5	561.5	534.0	508.1	486.1	464.7	447.9
22.5°	731.4	698.0	660.3	624.5	588.7	556.1	526.0	499.1	475.0	453.6	435.1
25°	733.5	697.8	659.2	618.1	578.9	544.3	513.0	483.8	457.0	435.6	416.0
27.5°	730.6	688.5	649.0	606.9	566.4	530.0	497.2	466.5	439.7	416.7	396.5
30°	726.3	681.3	638.9	595.1	554.1	519.1	484.5	455.1	427.2	403.3	383.0
32.5°	717.0	672.3	626.7	581.9	540.4	504.3	471.5	441.9	414.5	390.1	368.5
35°	698.6	653.4	603.9	557.9	517.1	479.6	448.8	420.3	394.2	368.1	345.3
37.5°	674.4	628.2	578.9	528.6	487.7	452.3	424.1	397.3	371.8	348.0	322.8
40°	651.6	609.4	558.6	508.6	466.7	432.5	406.4	382.1	356.5	332.8	307.6
42.5°	624.0	588.1	536.6	486.4	445.1	412.2	387.9	364.1	340.7	317.8	291.5
45°	577.8	550.5	502.4	454.2	412.5	379.8	357.6	336.6	316.1	294.3	269.5
47.5°	524.8	506.4	464.9	415.5	376.9	347.6	326.0	308.9	291.5	269.7	248.0
50°	488.0	476.3	436.1	391.1	354.2	327.3	305.2	289.1	274.6	253.6	234.2
52.5°	448.8	442.5	408.6	365.5	330.0	303.5	284.6	270.2	255.5	238.1	220.0
55°	389.0	392.4	363.6	326.3	292.8	270.6	253.4	241.4	228.8	214.1	200.1
57.5°	327.9	340.2	320.8	288.1	256.7	236.1	223.2	213.1	202.6	190.4	178.3
60°	291.3	301.6	290.7	261.8	234.4	215.3	203.2	195.4	184.9	173.8	164.7
62.5°	255.6	266.6	260.1	236.9	211.4	194.9	184.3	177.0	169.2	159.5	150.0
65°	210.8	217.9	214.8	198.8	180.7	166.6	156.8	151.5	144.3	137.2	128.8
67.5°	161.5	175.2	173.4	164.9	149.3	138.3	131.9	127.1	120.6	115.4	109.6
70°	132.7	145.4	145.2	138.3	129.8	119.6	115.1	111.1	105.3	100.2	95.5
72.5°	108.7	120.3	122.1	116.7	110.9	103.1	98.9	96.1	90.5	87.0	83.1
75°	76.1	84.5	86.8	86.8	84.1	80.1	76.3	74.5	70.5	67.4	65.1
77.5°	49.9	55.2	58.7	59.5	59.9	58.5	55.4	54.2	51.1	50.0	47.9
80°	35.3	38.8	42.8	44.2	45.2	44.9	43.5	42.6	39.7	38.5	37.7
82.5°	24.3	26.3	29.6	32.6	32.2	33.5	32.2	31.6	29.3	28.9	28.1
85°	12.7	12.9	13.4	15.4	16.5	17.0	17.2	16.8	16.0	16.0	14.5
87.5°	9.5	8.9	8.7	8.1	7.5	7.6	7.4	6.9	7.1	7.3	7.4
90°	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2	7.7	11.2	14.7
92.5°	25.1	22.5	20.0	18.7	18.5	18.3	18.1	17.9	18.1	18.3	18.5
95°	30.6	30.3	30.0	35.3	46.0	56.7	67.4	78.1	67.4	56.7	46.0
97.5°	108.0	143.3	178.5	192.8	186.2	179.4	172.7	166.0	172.7	179.4	186.2
100°	149.7	193.3	236.9	255.8	250.2	244.5	238.8	233.1	238.8	244.5	250.2
102.5°	312.7	318.4	324.0	324.8	320.7	316.5	312.4	308.1	312.4	316.5	320.7
105°	440.4	438.8	437.2	435.5	433.6	431.6	429.7	427.8	429.7	431.6	433.6
107.5°	548.7	546.5	544.3	542.8	541.9	540.9	540.0	538.9	540.0	540.9	541.9
110°	623.0	621.1	619.3	617.8	616.9	616.0	615.0	614.1	615.0	616.0	616.9





TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	696.7	695.8	694.9	693.6	691.9	690.2	688.5	686.8	688.5	690.2	691.9
115°	802.3	802.6	803.0	802.6	801.6	800.7	799.7	798.8	799.7	800.7	801.6
117.5°	907.2	906.4	905.8	904.8	903.5	902.3	901.0	899.8	901.0	902.3	903.5
120°	972.9	973.2	973.5	973.0	971.8	970.5	969.2	968.0	969.2	970.5	971.8
122.5°	1036.1	1035.8	1035.3	1034.7	1033.9	1033.1	1032.4	1031.6	1032.4	1033.1	1033.9
125°	1127.0	1127.7	1128.2	1127.9	1126.7	1125.4	1124.2	1122.9	1124.2	1125.4	1126.7
127.5°	1214.4	1213.0	1211.4	1210.6	1210.2	1209.9	1209.7	1209.3	1209.7	1209.9	1210.2
130°	1268.9	1267.9	1267.0	1266.3	1266.0	1265.6	1265.4	1265.1	1265.4	1265.6	1266.0
132.5°	1321.7	1320.6	1319.4	1318.5	1318.0	1317.4	1316.7	1316.2	1316.7	1317.4	1318.0
135°	1394.7	1393.5	1392.1	1391.7	1392.0	1392.3	1392.6	1393.0	1392.6	1392.3	1392.0
137.5°	1465.0	1463.6	1462.2	1461.4	1461.3	1461.1	1461.0	1460.9	1461.0	1461.1	1461.3
140°	1509.7	1509.0	1508.4	1507.8	1507.1	1506.6	1505.9	1505.2	1505.9	1506.6	1507.1
142.5°	1551.1	1550.8	1550.4	1549.6	1548.5	1547.4	1546.1	1545.0	1546.1	1547.4	1548.5
145°	1610.4	1610.4	1610.4	1610.0	1609.0	1608.1	1607.1	1606.2	1607.1	1608.1	1609.0
147.5°	1662.0	1662.3	1662.6	1661.9	1660.1	1658.3	1656.5	1654.8	1656.5	1658.3	1660.1
150°	1695.0	1695.3	1695.5	1695.1	1693.8	1692.5	1691.3	1690.1	1691.3	1692.5	1693.8
152.5°	1722.7	1723.3	1723.9	1723.6	1722.6	1721.6	1720.6	1719.6	1720.6	1721.6	1722.6
155°	1760.2	1761.1	1762.1	1762.4	1762.1	1761.7	1761.4	1761.1	1761.4	1761.7	1762.1
157.5°	1792.5	1793.6	1794.7	1795.4	1795.5	1795.7	1795.9	1796.1	1795.9	1795.7	1795.5
160°	1811.5	1811.8	1812.1	1812.8	1813.7	1814.7	1815.6	1816.6	1815.6	1814.7	1813.7
162.5°	1828.5	1828.8	1829.2	1829.9	1831.2	1832.3	1833.5	1834.8	1833.5	1832.3	1831.2
165°	1850.7	1850.7	1850.7	1851.4	1853.0	1854.6	1856.1	1857.8	1856.1	1854.6	1853.0
167.5°	1868.1	1868.3	1868.5	1869.3	1871.0	1872.6	1874.3	1875.9	1874.3	1872.6	1871.0
170°	1878.5	1878.1	1877.8	1878.6	1880.5	1882.4	1884.3	1886.2	1884.3	1882.4	1880.5
172.5°	1885.3	1885.0	1884.6	1885.5	1887.3	1889.2	1891.1	1893.0	1891.1	1889.2	1887.3
175°	1892.6	1892.3	1892.1	1892.8	1894.7	1896.6	1898.5	1900.4	1898.5	1896.6	1894.7
177.5°	1897.1	1896.6	1896.1	1896.8	1898.5	1900.3	1902.1	1903.8	1902.1	1900.3	1898.5
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	543.7	541.9	539.6	536.9	533.7	530.8	529.5	530.7	531.2	529.7	529.5
5°	527.1	521.5	517.1	510.4	505.0	500.6	497.5	496.1	496.5	492.9	492.1
7.5°	508.5	501.9	494.6	486.6	479.3	472.7	469.3	467.4	463.5	461.9	459.2
10°	496.5	487.7	480.5	471.1	462.6	454.9	451.0	447.9	444.1	442.3	438.6
12.5°	484.3	473.9	466.0	456.3	447.6	438.3	434.6	428.9	422.9	419.1	414.2
15°	466.8	454.4	444.8	433.2	422.9	412.3	402.7	391.9	388.0	379.5	374.6
17.5°	446.6	433.9	422.1	406.5	390.7	377.3	367.1	356.8	350.7	345.3	342.8
20°	433.2	421.6	405.1	387.0	369.4	354.7	346.4	339.7	333.0	329.2	326.6
22.5°	420.6	405.7	386.5	367.0	349.4	337.9	330.9	324.0	318.6	315.0	311.4
25°	399.3	379.8	359.6	337.2	325.3	315.2	307.6	302.0	298.7	294.0	292.2
27.5°	377.5	353.9	331.6	316.6	304.1	294.8	288.2	284.1	279.8	276.8	274.5
30°	360.7	336.9	316.8	302.5	289.7	282.2	276.8	271.9	268.5	266.1	264.4
32.5°	344.1	320.3	303.4	288.0	278.0	270.6	264.9	261.2	258.5	255.4	254.3
35°	320.1	298.9	284.2	270.3	260.1	253.4	248.9	245.2	242.9	242.0	241.4
37.5°	297.0	279.7	263.8	252.5	243.4	238.1	232.8	230.9	229.4	227.8	228.6
40°	282.4	266.1	252.0	240.1	232.6	226.9	223.8	221.5	220.2	220.2	220.2
42.5°	269.8	253.8	240.1	229.3	222.0	217.1	213.6	211.7	211.2	211.0	212.2
45°	250.1	235.4	221.5	212.5	206.3	201.4	199.4	197.8	197.8	198.8	199.0
47.5°	230.5	216.8	205.7	195.7	189.9	186.9	185.1	184.4	184.5	185.3	186.3
50°	218.6	205.0	194.1	185.1	179.8	176.9	175.3	174.8	175.3	175.3	176.9
52.5°	205.6	193.4	182.7	175.1	169.1	166.4	165.5	164.9	165.1	165.9	166.5
55°	186.5	175.6	165.3	158.2	153.7	151.9	149.9	150.1	149.7	150.1	150.1
57.5°	167.3	157.5	148.0	142.3	138.4	135.8	133.7	134.2	133.6	133.5	133.1
60°	155.0	144.3	136.8	131.6	127.1	124.9	122.9	123.4	122.7	122.2	121.3
62.5°	141.7	132.7	125.5	120.6	117.0	114.4	112.4	112.0	110.4	108.9	106.9
65°	122.2	114.9	108.4	103.8	100.4	98.4	96.8	95.5	92.1	88.6	86.8
67.5°	103.4	98.0	92.0	88.0	85.3	82.8	79.7	77.5	74.4	72.4	71.3
70°	91.2	86.1	81.0	77.2	74.3	71.8	68.5	66.9	64.7	63.8	62.7
72.5°	79.6	74.8	70.1	66.6	63.6	61.6	59.0	57.5	56.5	56.1	55.0
75°	62.0	58.2	54.7	51.6	49.1	47.7	46.7	45.5	45.1	43.1	41.9
77.5°	45.2	42.7	40.5	38.3	36.6	35.6	33.5	32.2	31.5	30.5	30.3
80°	35.3	33.5	31.2	29.9	27.4	26.6	25.6	25.4	25.2	25.0	24.8
82.5°	26.5	24.7	22.5	21.7	21.0	20.5	20.0	19.7	19.5	19.6	19.6
85°	13.4	12.5	12.5	12.3	12.1	11.8	11.6	11.6	11.4	11.6	11.4
87.5°	8.1	8.5	9.0	9.1	9.9	10.4	10.6	10.9	11.5	11.5	11.8
90°	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1	36.9	38.8	40.2
92.5°	18.7	20.0	22.5	25.1	27.6	30.2	32.0	33.9	35.8	37.7	38.7
95°	35.3	30.0	30.3	30.6	30.9	31.3	33.2	35.1	36.9	38.8	40.0
97.5°	192.8	178.5	143.3	108.0	72.8	37.5	37.7	37.9	38.1	38.3	38.5
100°	255.8	236.9	193.3	149.7	106.1	62.6	57.2	51.8	46.5	41.1	38.5
102.5°	324.8	324.0	318.4	312.7	307.0	301.3	243.4	185.5	127.5	69.7	40.7
105°	435.5	437.2	438.8	440.4	441.9	443.5	446.3	449.1	452.0	454.9	450.5
107.5°	542.8	544.3	546.5	548.7	550.7	552.9	554.3	555.7	557.1	558.5	559.8
110°	617.8	619.3	621.1	623.0	624.9	626.8	627.5	628.1	628.8	629.3	630.2



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	693.6	694.9	695.8	696.7	697.6	698.5	698.3	698.2	698.0	698.0	698.5
115°	802.6	803.0	802.6	802.3	802.0	801.6	802.3	803.0	803.5	804.2	804.6
117.5°	904.8	905.8	906.4	907.2	907.9	908.5	908.4	908.3	908.1	908.0	908.0
120°	973.0	973.5	973.2	972.9	972.5	972.2	972.9	973.5	974.1	974.8	974.8
122.5°	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5	1037.8	1038.2	1038.6	1038.4
125°	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7	1127.7	1128.6	1129.5	1130.2
127.5°	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1	1216.9	1216.7	1216.5	1216.3
130°	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0	1271.4	1271.7	1272.0	1272.1
132.5°	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5	1324.8	1325.1	1325.4	1325.5
135°	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9	1398.5	1399.1	1399.8	1400.4
137.5°	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4	1469.1	1469.8	1470.6	1470.7
140°	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9	1512.9	1513.8	1514.8	1515.3
142.5°	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6	1553.3	1554.0	1554.6	1555.0
145°	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7	1611.1	1611.4	1611.7	1612.2
147.5°	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6	1661.8	1662.1	1662.4	1662.6
150°	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3	1694.3	1694.3	1694.3	1694.5
152.5°	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1	1722.6	1723.1	1723.6	1723.7
155°	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5	1760.8	1762.1	1763.3	1763.5
157.5°	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0
160°	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4
162.5°	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8	1831.7	1833.6	1835.5	1835.3
165°	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1	1855.7	1858.2	1860.8	1860.6
167.5°	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5	1873.3	1876.0	1878.9	1878.7
170°	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6	1884.1	1886.7	1889.2	1888.9
172.5°	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4	1890.9	1893.5	1896.0	1895.5
175°	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1	1898.9	1901.9	1904.7	1904.2
177.5°	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2	1902.1	1904.2	1906.2	1905.7
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	528.5	528.9	527.6	527.3	527.6	528.9	528.5	529.5	529.7	531.2	530.7
5°	490.3	489.8	488.7	489.0	488.7	489.8	490.3	492.1	492.9	496.5	496.1
7.5°	457.6	455.9	456.4	454.6	456.4	455.9	457.6	459.2	461.9	463.5	467.4
10°	437.6	435.2	433.2	431.4	433.2	435.2	437.6	438.6	442.3	444.1	447.9
12.5°	410.4	408.2	405.6	406.0	405.6	408.2	410.4	414.2	419.1	422.9	428.9
15°	371.6	368.3	363.0	363.6	363.0	368.3	371.6	374.6	379.5	388.0	391.9
17.5°	338.8	338.8	336.4	337.1	336.4	338.8	338.8	342.8	345.3	350.7	356.8
20°	321.9	320.4	320.6	319.9	320.6	320.4	321.9	326.6	329.2	333.0	339.7
22.5°	310.1	308.2	306.6	305.3	306.6	308.2	310.1	311.4	315.0	318.6	324.0
25°	290.2	288.9	286.9	286.4	286.9	288.9	290.2	292.2	294.0	298.7	302.0
27.5°	272.7	272.5	271.6	270.6	271.6	272.5	272.7	274.5	276.8	279.8	284.1
30°	262.6	262.1	261.6	261.0	261.6	262.1	262.6	264.4	266.1	268.5	271.9
32.5°	253.4	253.2	252.7	252.8	252.7	253.2	253.4	254.3	255.4	258.5	261.2
35°	240.4	240.3	239.8	239.6	239.8	240.3	240.4	241.4	242.0	242.9	245.2
37.5°	228.4	228.9	228.7	228.6	228.7	228.9	228.4	228.6	227.8	229.4	230.9
40°	220.0	220.2	220.6	220.4	220.6	220.2	220.0	220.2	220.2	220.2	221.5
42.5°	213.0	213.0	213.7	212.9	213.7	213.0	213.0	212.2	211.0	211.2	211.7
45°	200.6	201.9	201.6	201.6	201.6	201.9	200.6	199.0	198.8	197.8	197.8
47.5°	186.9	188.1	188.4	188.3	188.4	188.1	186.9	186.3	185.3	184.5	184.4
50°	178.0	177.6	178.2	178.0	178.2	177.6	178.0	176.9	175.3	175.3	174.8
52.5°	167.1	167.2	167.2	166.9	167.2	167.2	167.1	166.5	165.9	165.1	164.9
55°	150.3	150.6	150.1	150.3	150.1	150.6	150.3	150.1	150.1	149.7	150.1
57.5°	132.1	131.1	131.5	131.0	131.5	131.1	132.1	133.1	133.5	133.6	134.2
60°	119.1	117.3	116.9	116.0	116.9	117.3	119.1	121.3	122.2	122.7	123.4
62.5°	104.5	103.2	101.7	102.5	101.7	103.2	104.5	106.9	108.9	110.4	112.0
65°	85.0	84.1	83.4	84.4	83.4	84.1	85.0	86.8	88.6	92.1	95.5
67.5°	70.3	69.8	69.8	69.5	69.8	69.8	70.3	71.3	72.4	74.4	77.5
70°	62.7	62.0	62.0	61.5	62.0	62.0	62.7	62.7	63.8	64.7	66.9
72.5°	54.9	54.2	54.4	54.1	54.4	54.2	54.9	55.0	56.1	56.5	57.5
75°	40.6	39.5	39.5	39.7	39.5	39.5	40.6	41.9	43.1	45.1	45.5
77.5°	30.3	30.1	30.3	30.0	30.3	30.1	30.3	30.3	30.5	31.5	32.2
80°	24.8	24.5	24.3	25.0	24.3	24.5	24.8	24.8	25.0	25.2	25.4
82.5°	19.2	19.2	19.1	20.0	19.1	19.2	19.2	19.6	19.6	19.5	19.7
85°	11.6	11.1	11.6	11.1	11.6	11.1	11.6	11.4	11.6	11.4	11.6
87.5°	12.3	12.2	12.2	12.4	12.2	12.2	12.3	11.8	11.5	11.5	10.9
90°	40.7	41.4	42.0	42.6	42.0	41.4	40.7	40.2	38.8	36.9	35.1
92.5°	38.8	39.0	39.1	39.2	39.1	39.0	38.8	38.7	37.7	35.8	33.9
95°	40.2	40.6	40.9	41.2	40.9	40.6	40.2	40.0	38.8	36.9	35.1
97.5°	38.8	39.2	39.5	39.8	39.5	39.2	38.8	38.5	38.3	38.1	37.9
100°	38.8	39.2	39.5	39.8	39.5	39.2	38.8	38.5	41.1	46.5	51.8
102.5°	40.7	40.8	40.9	40.9	40.9	40.8	40.7	40.7	69.7	127.5	185.5
105°	439.2	427.8	416.5	405.1	416.5	427.8	439.2	450.5	454.9	452.0	449.1
107.5°	561.0	562.1	563.4	564.6	563.4	562.1	561.0	559.8	558.5	557.1	555.7
110°	631.1	632.1	633.0	634.0	633.0	632.1	631.1	630.2	629.3	628.8	628.1



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	699.7	700.9	702.1	703.3	702.1	700.9	699.7	698.5	698.0	698.0	698.2
115°	804.6	804.6	804.6	804.6	804.6	804.6	804.6	804.6	804.2	803.5	803.0
117.5°	907.8	907.7	907.6	907.4	907.6	907.7	907.8	908.0	908.0	908.1	908.3
120°	974.1	973.5	972.9	972.2	972.9	973.5	974.1	974.8	974.8	974.1	973.5
122.5°	1037.8	1037.2	1036.5	1035.9	1036.5	1037.2	1037.8	1038.4	1038.6	1038.2	1037.8
125°	1130.5	1130.8	1131.1	1131.4	1131.1	1130.8	1130.5	1130.2	1129.5	1128.6	1127.7
127.5°	1216.1	1215.8	1215.5	1215.3	1215.5	1215.8	1216.1	1216.3	1216.5	1216.7	1216.9
130°	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.1	1272.0	1271.7	1271.4
132.5°	1325.2	1324.9	1324.7	1324.5	1324.7	1324.9	1325.2	1325.5	1325.4	1325.1	1324.8
135°	1401.0	1401.7	1402.3	1402.9	1402.3	1401.7	1401.0	1400.4	1399.8	1399.1	1398.5
137.5°	1470.6	1470.4	1470.2	1470.0	1470.2	1470.4	1470.6	1470.7	1470.6	1469.8	1469.1
140°	1515.7	1516.0	1516.3	1516.6	1516.3	1516.0	1515.7	1515.3	1514.8	1513.8	1512.9
142.5°	1555.1	1555.2	1555.2	1555.3	1555.2	1555.2	1555.1	1555.0	1554.6	1554.0	1553.3
145°	1612.8	1613.4	1614.1	1614.7	1614.1	1613.4	1612.8	1612.2	1611.7	1611.4	1611.1
147.5°	1662.9	1663.2	1663.6	1663.9	1663.6	1663.2	1662.9	1662.6	1662.4	1662.1	1661.8
150°	1694.8	1695.1	1695.4	1695.7	1695.4	1695.1	1694.8	1694.5	1694.3	1694.3	1694.3
152.5°	1723.5	1723.3	1723.2	1723.0	1723.2	1723.3	1723.5	1723.7	1723.6	1723.1	1722.6
155°	1762.6	1761.6	1760.7	1759.7	1760.7	1761.6	1762.6	1763.5	1763.3	1762.1	1760.8
157.5°	1795.4	1793.7	1792.1	1790.4	1792.1	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7
160°	1816.6	1814.7	1812.8	1810.8	1812.8	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7
162.5°	1833.2	1831.1	1828.9	1826.7	1828.9	1831.1	1833.2	1835.3	1835.5	1833.6	1831.7
165°	1857.8	1854.9	1852.1	1849.3	1852.1	1854.9	1857.8	1860.6	1860.8	1858.2	1855.7
167.5°	1875.5	1872.4	1869.2	1866.0	1869.2	1872.4	1875.5	1878.7	1878.9	1876.0	1873.3
170°	1885.7	1882.5	1879.4	1876.2	1879.4	1882.5	1885.7	1888.9	1889.2	1886.7	1884.1
172.5°	1892.2	1888.8	1885.4	1881.9	1885.4	1888.8	1892.2	1895.5	1896.0	1893.5	1890.9
175°	1900.4	1896.6	1892.8	1889.0	1892.8	1896.6	1900.4	1904.2	1904.7	1901.9	1898.9
177.5°	1902.7	1899.6	1896.6	1893.6	1896.6	1899.6	1902.7	1905.7	1906.2	1904.2	1902.1
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	529.5	530.8	533.7	536.9	539.6	541.9	543.7	546.2	548.5	551.7	554.7
5°	497.5	500.6	505.0	510.4	517.1	521.5	527.1	532.1	539.1	546.3	553.2
7.5°	469.3	472.7	479.3	486.6	494.6	501.9	508.5	517.2	526.6	537.1	548.7
10°	451.0	454.9	462.6	471.1	480.5	487.7	496.5	506.8	517.6	530.3	544.5
12.5°	434.6	438.3	447.6	456.3	466.0	473.9	484.3	494.6	509.0	522.7	538.9
15°	402.7	412.3	422.9	433.2	444.8	454.4	466.8	477.6	491.2	510.6	529.1
17.5°	367.1	377.3	390.7	406.5	422.1	433.9	446.6	459.9	476.1	495.9	517.3
20°	346.4	354.7	369.4	387.0	405.1	421.6	433.2	447.9	464.7	486.1	508.1
22.5°	330.9	337.9	349.4	367.0	386.5	405.7	420.6	435.1	453.6	475.0	499.1
25°	307.6	315.2	325.3	337.2	359.6	379.8	399.3	416.0	435.6	457.0	483.8
27.5°	288.2	294.8	304.1	316.6	331.6	353.9	377.5	396.5	416.7	439.7	466.5
30°	276.8	282.2	289.7	302.5	316.8	336.9	360.7	383.0	403.3	427.2	455.1
32.5°	264.9	270.6	278.0	288.0	303.4	320.3	344.1	368.5	390.1	414.5	441.9
35°	248.9	253.4	260.1	270.3	284.2	298.9	320.1	345.3	368.1	394.2	420.3
37.5°	232.8	238.1	243.4	252.5	263.8	279.7	297.0	322.8	348.0	371.8	397.3
40°	223.8	226.9	232.6	240.1	252.0	266.1	282.4	307.6	332.8	356.5	382.1
42.5°	213.6	217.1	222.0	229.3	240.1	253.8	269.8	291.5	317.8	340.7	364.1
45°	199.4	201.4	206.3	212.5	221.5	235.4	250.1	269.5	294.3	316.1	336.6
47.5°	185.1	186.9	189.9	195.7	205.7	216.8	230.5	248.0	269.7	291.5	308.9
50°	175.3	176.9	179.8	185.1	194.1	205.0	218.6	234.2	253.6	274.6	289.1
52.5°	165.5	166.4	169.1	175.1	182.7	193.4	205.6	220.0	238.1	255.5	270.2
55°	149.9	151.9	153.7	158.2	165.3	175.6	186.5	200.1	214.1	228.8	241.4
57.5°	133.7	135.8	138.4	142.3	148.0	157.5	167.3	178.3	190.4	202.6	213.1
60°	122.9	124.9	127.1	131.6	136.8	144.3	155.0	164.7	173.8	184.9	195.4
62.5°	112.4	114.4	117.0	120.6	125.5	132.7	141.7	150.0	159.5	169.2	177.0
65°	96.8	98.4	100.4	103.8	108.4	114.9	122.2	128.8	137.2	144.3	151.5
67.5°	79.7	82.8	85.3	88.0	92.0	98.0	103.4	109.6	115.4	120.6	127.1
70°	68.5	71.8	74.3	77.2	81.0	86.1	91.2	95.5	100.2	105.3	111.1
72.5°	59.0	61.6	63.6	66.6	70.1	74.8	79.6	83.1	87.0	90.5	96.1
75°	46.7	47.7	49.1	51.6	54.7	58.2	62.0	65.1	67.4	70.5	74.5
77.5°	33.5	35.6	36.6	38.3	40.5	42.7	45.2	47.9	50.0	51.1	54.2
80°	25.6	26.6	27.4	29.9	31.2	33.5	35.3	37.7	38.5	39.7	42.6
82.5°	20.0	20.5	21.0	21.7	22.5	24.7	26.5	28.1	28.9	29.3	31.6
85°	11.6	11.8	12.1	12.3	12.5	12.5	13.4	14.5	16.0	16.0	16.8
87.5°	10.6	10.4	9.9	9.1	9.0	8.5	8.1	7.4	7.3	7.1	6.9
90°	33.2	31.3	28.7	26.2	23.7	21.2	18.2	14.7	11.2	7.7	4.2
92.5°	32.0	30.2	27.6	25.1	22.5	20.0	18.7	18.5	18.3	18.1	17.9
95°	33.2	31.3	30.9	30.6	30.3	30.0	35.3	46.0	56.7	67.4	78.1
97.5°	37.7	37.5	72.8	108.0	143.3	178.5	192.8	186.2	179.4	172.7	166.0
100°	57.2	62.6	106.1	149.7	193.3	236.9	255.8	250.2	244.5	238.8	233.1
102.5°	243.4	301.3	307.0	312.7	318.4	324.0	324.8	320.7	316.5	312.4	308.1
105°	446.3	443.5	441.9	440.4	438.8	437.2	435.5	433.6	431.6	429.7	427.8
107.5°	554.3	552.9	550.7	548.7	546.5	544.3	542.8	541.9	540.9	540.0	538.9
110°	627.5	626.8	624.9	623.0	621.1	619.3	617.8	616.9	616.0	615.0	614.1



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.3	698.5	697.6	696.7	695.8	694.9	693.6	691.9	690.2	688.5	686.8
115°	802.3	801.6	802.0	802.3	802.6	803.0	802.6	801.6	800.7	799.7	798.8
117.5°	908.4	908.5	907.9	907.2	906.4	905.8	904.8	903.5	902.3	901.0	899.8
120°	972.9	972.2	972.5	972.9	973.2	973.5	973.0	971.8	970.5	969.2	968.0
122.5°	1037.5	1037.1	1036.6	1036.1	1035.8	1035.3	1034.7	1033.9	1033.1	1032.4	1031.6
125°	1126.7	1125.8	1126.3	1127.0	1127.7	1128.2	1127.9	1126.7	1125.4	1124.2	1122.9
127.5°	1217.1	1217.3	1215.8	1214.4	1213.0	1211.4	1210.6	1210.2	1209.9	1209.7	1209.3
130°	1271.0	1270.7	1269.8	1268.9	1267.9	1267.0	1266.3	1266.0	1265.6	1265.4	1265.1
132.5°	1324.5	1324.2	1323.0	1321.7	1320.6	1319.4	1318.5	1318.0	1317.4	1316.7	1316.2
135°	1397.9	1397.2	1396.0	1394.7	1393.5	1392.1	1391.7	1392.0	1392.3	1392.6	1393.0
137.5°	1468.4	1467.7	1466.3	1465.0	1463.6	1462.2	1461.4	1461.3	1461.1	1461.0	1460.9
140°	1511.9	1510.9	1510.3	1509.7	1509.0	1508.4	1507.8	1507.1	1506.6	1505.9	1505.2
142.5°	1552.6	1551.9	1551.5	1551.1	1550.8	1550.4	1549.6	1548.5	1547.4	1546.1	1545.0
145°	1610.7	1610.4	1610.4	1610.4	1610.4	1610.4	1610.0	1609.0	1608.1	1607.1	1606.2
147.5°	1661.6	1661.3	1661.6	1662.0	1662.3	1662.6	1661.9	1660.1	1658.3	1656.5	1654.8
150°	1694.3	1694.3	1694.6	1695.0	1695.3	1695.5	1695.1	1693.8	1692.5	1691.3	1690.1
152.5°	1722.1	1721.6	1722.1	1722.7	1723.3	1723.9	1723.6	1722.6	1721.6	1720.6	1719.6
155°	1759.5	1758.2	1759.3	1760.2	1761.1	1762.1	1762.4	1762.1	1761.7	1761.4	1761.1
157.5°	1792.1	1790.4	1791.5	1792.5	1793.6	1794.7	1795.4	1795.5	1795.7	1795.9	1796.1
160°	1812.8	1810.8	1811.2	1811.5	1811.8	1812.1	1812.8	1813.7	1814.7	1815.6	1816.6
162.5°	1829.8	1827.9	1828.2	1828.5	1828.8	1829.2	1829.9	1831.2	1832.3	1833.5	1834.8
165°	1853.1	1850.7	1850.7	1850.7	1850.7	1850.7	1851.4	1853.0	1854.6	1856.1	1857.8
167.5°	1870.5	1867.7	1867.9	1868.1	1868.3	1868.5	1869.3	1871.0	1872.6	1874.3	1875.9
170°	1881.6	1879.1	1878.8	1878.5	1878.1	1877.8	1878.6	1880.5	1882.4	1884.3	1886.2
172.5°	1888.4	1885.9	1885.6	1885.3	1885.0	1884.6	1885.5	1887.3	1889.2	1891.1	1893.0
175°	1896.1	1893.3	1893.0	1892.6	1892.3	1892.1	1892.8	1894.7	1896.6	1898.5	1900.4
177.5°	1900.2	1898.1	1897.6	1897.1	1896.6	1896.1	1896.8	1898.5	1900.3	1902.1	1903.8
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	557.0	558.6	560.4	563.8	566.7	568.0	570.4	572.2	571.7	574.2	578.4
5°	559.2	565.2	572.2	579.3	587.3	594.0	599.4	604.7	609.0	614.1	621.7
7.5°	558.8	569.6	581.3	594.0	607.2	618.6	629.1	639.8	649.3	659.7	673.4
10°	557.4	571.7	586.3	602.9	619.7	635.6	649.8	663.2	675.9	689.5	706.7
12.5°	555.8	572.2	589.7	609.9	630.7	649.8	666.6	685.9	701.8	719.3	739.1
15°	548.7	570.8	594.7	620.8	645.8	671.5	694.4	718.0	740.2	761.1	786.1
17.5°	540.6	566.1	594.3	625.1	655.1	686.3	713.6	743.4	765.9	794.1	817.3
20°	534.0	561.5	591.5	626.1	660.3	694.8	725.0	755.4	780.7	809.1	838.5
22.5°	526.0	556.1	588.7	624.5	660.3	698.0	731.4	761.6	793.1	824.9	855.3
25°	513.0	544.3	578.9	618.1	659.2	697.8	733.5	770.9	804.8	839.4	866.7
27.5°	497.2	530.0	566.4	606.9	649.0	688.5	730.6	770.5	804.6	837.9	861.7
30°	484.5	519.1	554.1	595.1	638.9	681.3	726.3	766.3	802.2	832.1	845.5
32.5°	471.5	504.3	540.4	581.9	626.7	672.3	717.0	757.9	791.1	809.0	809.4
35°	448.8	479.6	517.1	557.9	603.9	653.4	698.6	738.8	759.1	760.6	738.8
37.5°	424.1	452.3	487.7	528.6	578.9	628.2	674.4	701.2	707.9	685.2	644.9
40°	406.4	432.5	466.7	508.6	558.6	609.4	651.6	671.2	664.1	627.3	582.2
42.5°	387.9	412.2	445.1	486.4	536.6	588.1	624.0	634.4	615.6	573.1	520.3
45°	357.6	379.8	412.5	454.2	502.4	550.5	577.8	572.4	540.9	490.5	431.4
47.5°	326.0	347.6	376.9	415.5	464.9	506.4	524.8	508.7	463.9	408.5	360.4
50°	305.2	327.3	354.2	391.1	436.1	476.3	488.0	463.5	413.8	360.5	316.3
52.5°	284.6	303.5	330.0	365.5	408.6	442.5	448.8	420.6	369.2	321.4	282.2
55°	253.4	270.6	292.8	326.3	363.6	392.4	389.0	352.7	306.0	265.2	234.4
57.5°	223.2	236.1	256.7	288.1	320.8	340.2	327.9	296.9	253.4	220.0	194.1
60°	203.2	215.3	234.4	261.8	290.7	301.6	291.3	257.7	223.3	192.7	170.9
62.5°	184.3	194.9	211.4	236.9	260.1	266.6	255.6	226.2	195.3	169.2	151.1
65°	156.8	166.6	180.7	198.8	214.8	217.9	210.8	180.7	157.3	135.4	122.9
67.5°	131.9	138.3	149.3	164.9	173.4	175.2	161.5	142.5	121.9	108.5	99.1
70°	115.1	119.6	129.8	138.3	145.2	145.4	132.7	117.5	101.7	90.8	83.9
72.5°	98.9	103.1	110.9	116.7	122.1	120.3	108.7	96.7	83.9	75.6	70.5
75°	76.3	80.1	84.1	86.8	86.8	84.5	76.1	67.1	59.8	54.9	53.3
77.5°	55.4	58.5	59.9	59.5	58.7	55.2	49.9	44.0	41.4	39.1	37.9
80°	43.5	44.9	45.2	44.2	42.8	38.8	35.3	32.8	30.3	29.4	29.0
82.5°	32.2	33.5	32.2	32.6	29.6	26.3	24.3	23.5	22.5	22.1	21.7
85°	17.2	17.0	16.5	15.4	13.4	12.9	12.7	12.5	12.1	12.3	11.8
87.5°	7.4	7.6	7.5	8.1	8.7	8.9	9.5	10.0	10.6	10.7	11.5
90°	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2	35.1
92.5°	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0	33.9
95°	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2	35.1
97.5°	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7	37.9
100°	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2	51.8
102.5°	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4	185.5
105°	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3	449.1
107.5°	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3	555.7
110°	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5	628.1





TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3	698.2
115°	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3	803.0
117.5°	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4	908.3
120°	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9	973.5
122.5°	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5	1037.8
125°	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7	1127.7
127.5°	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1	1216.9
130°	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0	1271.4
132.5°	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5	1324.8
135°	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9	1398.5
137.5°	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4	1469.1
140°	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9	1512.9
142.5°	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6	1553.3
145°	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7	1611.1
147.5°	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6	1661.8
150°	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3	1694.3
152.5°	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1	1722.6
155°	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5	1760.8
157.5°	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1	1793.7
160°	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8	1814.7
162.5°	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8	1831.7
165°	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1	1855.7
167.5°	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5	1873.3
170°	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6	1884.1
172.5°	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4	1890.9
175°	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1	1898.9
177.5°	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2	1902.1
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	580.8	581.5	582.0	583.8	584.0	585.6	584.0
5°	628.9	632.0	636.9	641.8	642.2	645.4	639.8
7.5°	682.7	689.9	694.5	702.4	705.5	707.5	704.3
10°	719.8	726.5	738.4	744.1	750.0	750.8	748.2
12.5°	755.7	766.3	775.6	786.6	786.4	794.2	791.4
15°	803.5	814.5	827.4	839.6	844.0	844.0	847.6
17.5°	837.5	857.6	871.0	880.6	891.2	893.0	891.7
20°	860.6	882.2	896.5	909.0	916.2	918.1	918.1
22.5°	877.7	896.2	910.1	921.3	927.2	929.5	928.9
25°	889.6	905.4	913.9	917.3	918.8	918.4	914.2
27.5°	873.4	872.6	867.3	857.1	849.3	844.6	839.2
30°	842.4	830.7	817.3	802.6	783.6	769.1	764.7
32.5°	796.1	770.1	747.3	722.8	702.5	688.0	681.8
35°	706.7	665.4	631.7	602.3	580.9	567.5	563.0
37.5°	600.6	560.6	519.0	490.4	472.6	459.1	454.1
40°	533.1	489.7	453.3	426.5	408.2	395.0	394.8
42.5°	471.6	430.0	395.8	376.5	356.8	348.1	348.1
45°	386.2	352.9	323.9	308.7	296.9	289.7	287.8
47.5°	319.7	292.2	272.9	260.8	251.2	246.7	243.6
50°	282.4	258.4	242.9	232.4	227.1	221.3	220.8
52.5°	251.4	231.9	219.9	211.4	204.6	201.1	201.2
55°	211.2	195.9	187.4	180.9	175.6	172.9	171.7
57.5°	178.0	166.5	160.2	154.3	152.0	150.0	149.4
60°	157.3	149.5	143.6	138.9	135.6	135.0	134.7
62.5°	140.2	132.0	128.0	124.3	121.9	120.8	120.5
65°	115.6	109.5	105.9	103.0	102.2	100.6	100.4
67.5°	93.1	89.5	87.2	85.2	84.0	83.9	83.9
70°	79.5	77.4	75.4	74.3	73.6	73.1	73.1
72.5°	67.7	66.2	64.5	63.9	63.8	63.3	63.2
75°	51.6	50.0	50.2	49.1	48.2	47.0	46.4
77.5°	36.6	35.4	35.2	35.1	34.3	34.2	34.5
80°	28.4	27.2	27.0	27.2	27.0	26.3	26.3
82.5°	21.6	20.6	20.4	20.3	20.1	20.3	19.9
85°	11.6	11.1	11.1	11.1	11.6	11.4	11.1
87.5°	11.5	11.7	12.2	12.1	12.2	12.2	12.4
90°	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.8	629.3	630.2	631.1	632.1	633.0	634.0



TEST NUMBER: P333031-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)