

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333103-935

Luminaire Tested: **S124RDIW-S1195D1050U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333103-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1050U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7924.1 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot



46% Up

54% Dn



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	55	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	38	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	39	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13774	13774	13774	13774
5°	15977	13816	12211	13816
10°	18901	13755	10899	13755
15°	21833	13628	9365	13628
20°	24308	13454	8469	13454
25°	25093	13281	7863	13281
30°	21967	13073	7498	13073
35°	17100	12764	7276	12764
40°	12823	12410	7158	12410
45°	10123	11843	7096	11843
50°	8547	11189	6889	11189
55°	7450	10469	6521	10469
60°	6704	9723	5772	9723
65°	5910	8915	4963	8915
70°	5323	8080	4480	8080
75°	4460	7162	3815	7162
80°	3770	6104	3580	6104
85°	3186	4780	3186	4780



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.3	2.1
10°-20°	498.7	6.3
20°-30°	780.0	9.8
30°-40°	867.1	10.9
40°-50°	769.3	9.7
50°-60°	599.5	7.6
60°-70°	392.5	5.0
70°-80°	193.0	2.4
80°-90°	51.0	0.6
90°-100°	39.9	0.5
100°-110°	254.3	3.2
110°-120°	486.6	6.1
120°-130°	617.7	7.8
130°-140°	660.8	8.3
140°-150°	618.0	7.8
150°-160°	498.3	6.3
160°-170°	321.4	4.1
170°-180°	110.8	1.4
0°-30°	1444.0	18.2
0°-40°	2311.0	29.2
0°-60°	3679.8	46.4
0°-90°	4316.2	54.5
90°-120°	780.8	9.9
90°-150°	2677.3	33.8
90°-180°	3608.0	45.5
0°-180°	7924.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1972	1705	1507	1705	1972	199
15°	2612	1631	1120	1631	2612	743
25°	2817	1491	883	1491	2817	1250
35°	1735	1295	738	1295	1735	1088
45°	887	1037	622	1037	887	702
55°	529	744	463	744	529	481
65°	309	467	260	467	309	311
75°	143	230	122	230	143	157
85°	34	52	34	52	34	39
90°	26	3	26	3	26	13
95°	25	48	25	48	25	20
105°	249	263	249	263	249	217
115°	494	490	494	490	494	489
125°	694	689	694	689	694	618
135°	861	855	861	855	861	663
145°	991	986	991	986	991	619
155°	1080	1081	1080	1081	1080	498
165°	1135	1140	1135	1140	1135	321
175°	1159	1166	1159	1166	1159	110
180°	1166	1166	1166	1166	1166	



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1799.7	1804.7	1799.7	1799.1	1793.6	1792.0	1789.8	1782.6	1769.4	1761.8	1763.4
5°	1971.5	1988.7	1979.1	1977.7	1962.6	1947.5	1937.9	1915.9	1892.5	1876.7	1863.6
7.5°	2170.3	2180.2	2174.2	2164.6	2140.1	2126.2	2103.9	2074.9	2033.0	2001.0	1971.7
10°	2305.7	2313.9	2311.2	2293.3	2275.4	2238.9	2218.4	2177.8	2124.9	2082.9	2043.8
12.5°	2438.7	2447.6	2423.4	2424.1	2390.3	2361.6	2328.9	2277.9	2216.7	2162.7	2113.6
15°	2612.3	2601.3	2601.3	2587.5	2549.7	2509.8	2476.1	2422.5	2345.5	2280.9	2212.9
17.5°	2748.1	2751.9	2746.2	2713.9	2684.2	2642.9	2581.2	2518.6	2447.1	2360.3	2290.8
20°	2829.5	2829.5	2823.3	2801.3	2762.8	2718.8	2652.1	2584.0	2493.3	2406.0	2327.6
22.5°	2862.5	2864.6	2857.4	2839.2	2804.6	2761.7	2704.9	2635.8	2542.3	2443.9	2346.9
25°	2817.1	2830.2	2831.5	2826.7	2816.4	2790.2	2741.5	2670.6	2586.8	2480.3	2375.8
27.5°	2586.4	2602.9	2617.4	2641.1	2672.7	2689.2	2691.4	2655.4	2582.2	2479.7	2374.6
30°	2356.5	2370.2	2414.9	2473.4	2518.8	2560.0	2595.7	2605.4	2564.1	2472.0	2361.3
32.5°	2101.4	2120.0	2164.7	2227.6	2303.2	2373.0	2453.3	2494.2	2493.2	2437.9	2335.5
35°	1735.1	1748.9	1790.1	1856.1	1946.8	2050.6	2177.8	2276.7	2344.2	2339.3	2276.7
37.5°	1399.3	1414.9	1456.6	1511.2	1599.2	1727.8	1850.8	1987.2	2111.8	2181.8	2160.9
40°	1216.8	1217.5	1258.0	1314.4	1396.9	1508.9	1643.0	1794.2	1933.0	2046.5	2068.5
42.5°	1072.6	1072.8	1099.6	1160.4	1219.8	1325.3	1453.2	1603.4	1765.9	1896.9	1955.2
45°	886.7	892.9	915.0	951.4	998.2	1087.5	1189.9	1329.5	1511.7	1667.0	1763.9
47.5°	751.0	760.0	774.0	803.7	841.0	900.5	985.2	1110.6	1258.8	1429.7	1567.6
50°	680.5	681.9	699.8	716.3	748.6	796.1	870.3	974.7	1110.9	1275.1	1428.5
52.5°	620.1	619.7	630.5	651.4	677.7	714.6	774.6	869.7	990.4	1137.7	1296.0
55°	529.3	532.8	541.0	557.5	577.5	603.6	651.0	722.5	817.3	943.1	1086.8
57.5°	460.3	462.1	468.6	475.5	493.9	512.8	548.5	598.1	678.1	781.1	915.0
60°	415.2	415.9	417.9	428.3	442.7	460.5	484.7	526.6	593.9	688.1	794.0
62.5°	371.2	372.5	375.7	383.1	394.3	406.7	431.9	465.5	521.3	601.8	697.2
65°	309.4	310.0	314.9	317.6	326.5	337.5	356.1	378.8	417.2	484.7	556.8
67.5°	258.5	258.5	258.7	262.4	268.6	276.0	287.1	305.2	334.2	375.7	439.3
70°	225.5	225.5	226.9	228.9	232.4	238.5	244.7	258.5	279.8	313.5	362.3
72.5°	194.7	195.2	196.6	197.0	198.8	203.9	208.4	217.2	233.1	258.5	297.9
75°	143.0	145.1	148.5	151.3	154.6	153.9	158.8	164.3	169.1	184.3	206.9
77.5°	106.4	105.3	105.7	108.1	108.5	109.2	112.6	116.8	120.5	127.6	135.7
80°	81.1	81.1	83.2	83.9	83.2	83.9	87.3	89.4	90.7	93.5	101.1
82.5°	61.3	62.4	61.7	62.4	62.9	63.5	66.4	66.8	68.2	69.3	72.5
85°	34.4	35.0	35.7	34.4	34.4	34.4	35.7	36.4	37.8	37.1	38.5
87.5°	17.3	16.7	17.2	17.1	17.6	16.9	17.2	18.1	16.7	17.0	16.7
90°	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5	20.3	19.2	17.7
92.5°	24.1	24.0	23.9	23.8	23.8	23.2	22.0	20.8	19.6	18.5	17.0
95°	25.3	25.1	24.9	24.7	24.5	23.8	22.6	21.5	20.3	19.2	19.0
97.5°	24.5	24.2	24.0	23.8	23.7	23.5	23.4	23.2	23.2	23.0	44.7
100°	24.5	24.2	24.0	23.8	23.7	25.2	28.5	31.8	35.1	38.4	65.2
102.5°	25.1	25.1	25.1	25.0	25.0	42.7	78.3	113.8	149.4	184.9	188.4
105°	248.7	255.6	262.6	269.6	276.6	279.1	277.4	275.7	273.9	272.2	271.2
107.5°	346.5	345.8	345.0	344.3	343.5	342.8	341.9	341.0	340.2	339.3	338.0
110°	389.1	388.5	387.9	387.4	386.8	386.2	385.9	385.5	385.1	384.7	383.6



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	431.6	430.9	430.2	429.5	428.7	428.3	428.4	428.5	428.6	428.7	428.1
115°	493.8	493.8	493.8	493.8	493.8	493.5	493.2	492.8	492.4	492.0	492.2
117.5°	556.9	557.0	557.1	557.2	557.2	557.3	557.4	557.4	557.5	557.6	557.2
120°	596.7	597.1	597.4	597.9	598.2	598.2	597.9	597.4	597.1	596.7	596.8
122.5°	635.8	636.2	636.5	637.0	637.3	637.4	637.1	637.0	636.7	636.5	636.2
125°	694.4	694.2	694.0	693.8	693.6	693.2	692.7	692.1	691.5	690.9	691.3
127.5°	745.9	746.0	746.1	746.3	746.5	746.6	746.7	746.8	747.0	747.1	746.1
130°	780.8	780.8	780.8	780.8	780.8	780.7	780.5	780.2	780.1	779.9	779.3
132.5°	812.9	813.0	813.1	813.3	813.5	813.5	813.3	813.0	812.9	812.7	811.9
135°	861.0	860.7	860.2	859.9	859.5	859.1	858.7	858.3	857.9	857.6	856.8
137.5°	902.2	902.3	902.4	902.5	902.7	902.5	902.1	901.6	901.2	900.8	899.9
140°	930.8	930.6	930.4	930.2	930.1	929.6	929.0	928.5	927.9	927.3	927.0
142.5°	954.5	954.5	954.4	954.4	954.3	954.2	953.7	953.3	952.9	952.4	952.2
145°	991.0	990.6	990.2	989.8	989.5	989.1	988.9	988.8	988.6	988.3	988.3
147.5°	1021.1	1021.0	1020.8	1020.6	1020.4	1020.2	1020.0	1019.9	1019.8	1019.6	1019.8
150°	1040.7	1040.5	1040.3	1040.1	1039.9	1039.8	1039.8	1039.8	1039.8	1039.8	1040.0
152.5°	1057.5	1057.6	1057.7	1057.8	1057.9	1057.8	1057.5	1057.2	1056.9	1056.6	1057.0
155°	1080.0	1080.6	1081.2	1081.7	1082.3	1082.2	1081.4	1080.6	1079.9	1079.1	1079.7
157.5°	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8	1099.5
160°	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4	1111.6
162.5°	1121.1	1122.5	1123.8	1125.1	1126.4	1126.4	1125.3	1124.1	1123.0	1121.8	1122.1
165°	1134.9	1136.7	1138.4	1140.1	1141.9	1142.0	1140.5	1138.9	1137.4	1135.8	1135.8
167.5°	1145.2	1147.2	1149.1	1151.1	1153.0	1153.1	1151.4	1149.7	1148.0	1146.2	1146.4
170°	1151.5	1153.4	1155.4	1157.3	1159.3	1159.4	1157.9	1156.3	1154.8	1153.2	1153.1
172.5°	1154.9	1157.1	1159.2	1161.2	1163.4	1163.6	1162.1	1160.5	1159.0	1157.4	1157.3
175°	1159.3	1161.7	1164.0	1166.3	1168.6	1169.0	1167.2	1165.4	1163.7	1162.0	1161.7
177.5°	1162.2	1164.0	1165.9	1167.7	1169.6	1169.9	1168.6	1167.4	1166.1	1164.9	1164.6
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1757.9	1750.2	1746.4	1737.6	1727.1	1721.6	1716.7	1709.5	1700.1	1690.2	1683.1
5°	1847.1	1830.7	1810.0	1785.3	1763.2	1742.0	1723.4	1704.9	1683.5	1661.6	1639.5
7.5°	1938.7	1906.3	1871.2	1830.7	1791.1	1755.3	1722.3	1690.7	1654.9	1622.9	1593.7
10°	2002.5	1958.5	1909.7	1858.1	1806.6	1761.9	1717.9	1678.0	1634.0	1594.8	1561.9
12.5°	2054.2	2002.5	1943.8	1879.6	1817.6	1763.5	1713.0	1661.0	1610.9	1568.5	1524.5
15°	2139.9	2069.2	1990.1	1913.1	1832.7	1759.1	1691.1	1630.6	1573.6	1513.7	1471.8
17.5°	2199.0	2115.0	2018.9	1926.3	1831.3	1744.6	1666.0	1594.1	1528.2	1467.1	1417.2
20°	2234.1	2141.3	2034.8	1929.6	1823.1	1730.3	1645.7	1566.0	1497.9	1431.9	1380.4
22.5°	2253.9	2151.2	2034.8	1924.7	1814.3	1713.7	1620.9	1537.9	1463.8	1397.8	1340.7
25°	2260.3	2150.3	2031.4	1904.9	1783.9	1677.3	1581.1	1491.0	1408.5	1342.6	1282.0
27.5°	2251.5	2121.9	2000.2	1870.4	1745.5	1633.2	1532.1	1437.5	1355.0	1284.1	1222.1
30°	2238.3	2099.4	1968.8	1834.1	1707.5	1599.7	1493.1	1402.4	1316.5	1242.9	1180.3
32.5°	2209.7	2071.9	1931.4	1793.4	1665.3	1554.0	1452.9	1361.7	1277.4	1202.2	1135.7
35°	2153.0	2013.4	1860.9	1719.2	1593.5	1478.0	1383.1	1295.1	1214.7	1134.3	1064.1
37.5°	2078.4	1935.8	1784.0	1628.9	1503.0	1394.0	1306.9	1224.3	1145.8	1072.4	994.7
40°	2008.0	1878.1	1721.3	1567.4	1438.1	1332.9	1252.5	1177.6	1098.5	1025.6	948.0
42.5°	1922.8	1812.1	1653.7	1499.2	1371.6	1270.2	1195.3	1122.1	1050.2	979.5	898.5
45°	1780.5	1696.6	1548.1	1399.6	1271.1	1170.7	1102.0	1037.3	974.0	906.7	830.4
47.5°	1617.4	1560.6	1432.4	1280.4	1161.5	1071.2	1004.8	951.9	898.5	831.1	764.1
50°	1504.1	1467.7	1343.9	1205.1	1091.7	1008.5	940.4	890.9	846.2	781.6	721.8
52.5°	1383.1	1363.7	1259.2	1126.4	1016.8	935.3	877.2	832.6	787.4	733.7	677.8
55°	1198.9	1209.2	1120.5	1005.7	902.6	833.9	780.9	743.8	705.3	660.0	616.6
57.5°	1010.6	1048.2	988.7	887.9	791.3	727.7	687.9	656.6	624.3	586.7	549.7
60°	897.8	929.4	895.7	807.0	722.5	663.4	626.3	602.2	569.9	535.5	507.3
62.5°	787.8	821.7	801.7	730.0	651.5	600.7	567.9	545.5	521.5	491.5	462.3
65°	649.6	671.6	662.0	612.5	556.8	513.5	483.3	466.7	444.8	422.8	396.7
67.5°	497.6	540.0	534.4	508.2	460.0	426.2	406.4	391.8	371.8	355.4	337.7
70°	409.1	448.2	447.5	426.2	400.1	368.4	354.7	342.3	324.4	308.7	294.2
72.5°	334.8	370.7	376.0	359.6	341.8	317.9	304.7	296.2	278.8	267.9	256.2
75°	234.5	260.5	267.4	267.4	259.2	246.8	235.1	229.6	217.2	207.6	200.7
77.5°	153.7	170.2	180.9	183.4	184.7	180.6	170.9	167.0	157.6	154.1	147.5
80°	108.6	119.6	132.0	136.1	139.6	138.2	134.1	131.3	122.3	118.9	116.1
82.5°	75.1	81.1	91.3	100.4	99.4	103.0	99.4	97.2	90.5	89.2	86.4
85°	39.2	39.9	41.2	47.4	50.9	52.3	53.0	51.6	49.5	49.5	44.7
87.5°	16.4	15.6	16.4	16.0	16.1	17.9	19.1	19.2	18.0	16.8	15.6
90°	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6	4.7	6.9	9.0
92.5°	15.4	13.9	12.3	11.5	11.4	11.2	11.1	11.0	11.1	11.2	11.4
95°	18.8	18.6	18.4	21.6	28.2	34.8	41.4	48.0	41.4	34.8	28.2
97.5°	66.3	87.9	109.6	118.3	114.3	110.1	106.0	101.9	106.0	110.1	114.3
100°	91.9	118.6	145.4	157.0	153.5	150.1	146.5	143.1	146.5	150.1	153.5
102.5°	191.9	195.4	198.9	199.3	196.8	194.2	191.7	189.2	191.7	194.2	196.8
105°	270.3	269.2	268.3	267.3	266.0	264.9	263.7	262.6	263.7	264.9	266.0
107.5°	336.7	335.4	334.1	333.1	332.5	331.9	331.4	330.8	331.4	331.9	332.5
110°	382.4	381.3	380.0	379.2	378.6	378.0	377.5	376.9	377.5	378.0	378.6



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	427.6	427.1	426.5	425.7	424.6	423.6	422.6	421.5	422.6	423.6	424.6
115°	492.4	492.6	492.8	492.6	492.0	491.5	490.9	490.3	490.9	491.5	492.0
117.5°	556.7	556.3	555.9	555.3	554.5	553.7	552.9	552.2	552.9	553.7	554.5
120°	597.1	597.3	597.4	597.2	596.4	595.6	594.9	594.1	594.9	595.6	596.4
122.5°	635.9	635.7	635.4	635.0	634.6	634.0	633.6	633.2	633.6	634.0	634.6
125°	691.6	692.1	692.4	692.2	691.5	690.7	689.9	689.1	689.9	690.7	691.5
127.5°	745.3	744.4	743.5	743.0	742.8	742.6	742.4	742.2	742.4	742.6	742.8
130°	778.7	778.2	777.6	777.1	777.0	776.8	776.6	776.4	776.6	776.8	777.0
132.5°	811.2	810.5	809.8	809.2	808.8	808.5	808.1	807.8	808.1	808.5	808.8
135°	856.0	855.2	854.5	854.1	854.3	854.5	854.7	854.9	854.7	854.5	854.3
137.5°	899.1	898.2	897.3	896.9	896.8	896.7	896.6	896.6	896.6	896.7	896.8
140°	926.5	926.2	925.7	925.4	925.0	924.6	924.2	923.9	924.2	924.6	925.0
142.5°	951.9	951.7	951.5	951.1	950.4	949.6	948.9	948.2	948.9	949.6	950.4
145°	988.3	988.3	988.3	988.1	987.5	986.9	986.4	985.8	986.4	986.9	987.5
147.5°	1020.0	1020.2	1020.4	1019.9	1018.8	1017.8	1016.7	1015.5	1016.7	1017.8	1018.8
150°	1040.3	1040.4	1040.6	1040.3	1039.6	1038.8	1038.0	1037.2	1038.0	1038.8	1039.6
152.5°	1057.3	1057.7	1058.0	1057.8	1057.2	1056.6	1056.0	1055.3	1056.0	1056.6	1057.2
155°	1080.3	1080.8	1081.4	1081.6	1081.4	1081.2	1081.1	1080.8	1081.1	1081.2	1081.4
157.5°	1100.1	1100.8	1101.5	1101.8	1101.9	1102.1	1102.2	1102.3	1102.2	1102.1	1101.9
160°	1111.7	1112.0	1112.2	1112.5	1113.1	1113.7	1114.3	1114.8	1114.3	1113.7	1113.1
162.5°	1122.2	1122.4	1122.6	1123.1	1123.8	1124.6	1125.3	1126.0	1125.3	1124.6	1123.8
165°	1135.8	1135.8	1135.8	1136.3	1137.2	1138.2	1139.2	1140.1	1139.2	1138.2	1137.2
167.5°	1146.5	1146.6	1146.8	1147.3	1148.3	1149.3	1150.3	1151.3	1150.3	1149.3	1148.3
170°	1152.9	1152.6	1152.4	1153.0	1154.1	1155.3	1156.4	1157.6	1156.4	1155.3	1154.1
172.5°	1157.0	1156.8	1156.7	1157.1	1158.3	1159.4	1160.6	1161.7	1160.6	1159.4	1158.3
175°	1161.6	1161.4	1161.2	1161.7	1162.9	1164.0	1165.2	1166.3	1165.2	1164.0	1162.9
177.5°	1164.3	1164.0	1163.7	1164.1	1165.2	1166.2	1167.3	1168.4	1167.3	1166.2	1165.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1675.4	1669.9	1662.8	1654.5	1644.6	1635.8	1631.9	1635.3	1636.9	1632.5	1631.9
5°	1624.4	1607.2	1593.5	1572.9	1556.3	1542.6	1533.0	1528.9	1530.3	1519.2	1516.5
7.5°	1567.1	1546.7	1524.1	1499.7	1476.9	1456.6	1446.0	1440.3	1428.7	1423.7	1415.3
10°	1530.3	1502.7	1480.7	1451.8	1425.7	1401.7	1390.0	1380.4	1368.6	1363.1	1351.5
12.5°	1492.3	1460.3	1436.1	1406.2	1379.5	1350.6	1339.4	1321.5	1303.2	1291.7	1276.7
15°	1438.8	1400.3	1370.7	1335.0	1303.4	1270.4	1240.8	1207.8	1195.4	1169.3	1154.2
17.5°	1376.2	1337.2	1300.6	1252.7	1203.9	1162.9	1131.4	1099.8	1080.8	1064.1	1056.4
20°	1335.0	1299.2	1248.4	1192.7	1138.4	1093.0	1067.6	1047.0	1026.3	1014.7	1006.4
22.5°	1296.0	1250.3	1191.2	1131.1	1076.8	1041.3	1019.8	998.6	981.8	970.7	959.7
25°	1230.5	1170.7	1108.1	1039.4	1002.3	971.4	948.0	930.7	920.5	906.0	900.5
27.5°	1163.3	1090.8	1021.8	975.6	936.9	908.6	888.3	875.4	862.3	853.1	845.9
30°	1111.6	1038.0	976.1	932.1	892.9	869.6	853.1	838.0	827.7	820.1	814.6
32.5°	1060.4	986.9	934.9	887.6	856.7	833.9	816.2	804.9	796.9	787.1	783.8
35°	986.4	921.2	875.8	833.2	801.5	780.9	767.2	755.5	748.6	745.9	743.8
37.5°	915.4	861.9	813.1	778.2	750.0	733.7	717.6	711.8	707.1	702.1	704.4
40°	870.3	820.1	776.8	739.7	717.0	699.1	689.5	682.6	678.5	678.5	678.5
42.5°	831.2	782.1	739.9	706.7	684.0	668.9	658.1	652.4	651.0	650.5	653.8
45°	770.6	725.2	682.6	655.1	635.8	620.8	614.6	609.8	609.8	612.5	613.2
47.5°	710.5	668.0	633.8	603.0	585.4	575.9	570.6	568.1	568.3	571.1	574.3
50°	673.6	631.7	598.1	570.6	554.1	545.1	540.3	539.0	540.3	540.3	545.1
52.5°	633.5	596.0	562.8	539.8	521.1	512.7	510.1	508.2	508.9	511.2	513.2
55°	574.7	541.0	509.4	487.4	473.6	468.1	461.9	462.6	461.2	462.6	462.6
57.5°	515.7	485.4	456.1	438.6	426.5	418.5	411.7	413.7	411.6	411.4	410.3
60°	477.8	444.8	421.4	405.6	391.8	385.0	378.8	380.1	378.1	376.7	373.9
62.5°	436.5	409.1	386.8	371.5	360.5	352.5	346.3	344.9	340.2	335.4	329.4
65°	376.7	354.0	334.1	319.7	309.4	303.2	298.3	294.2	283.9	272.9	267.4
67.5°	318.6	302.2	283.6	271.4	263.0	254.9	245.7	238.7	229.0	223.0	219.6
70°	281.1	265.4	249.5	237.8	228.9	221.4	211.0	206.2	199.3	196.6	193.2
72.5°	245.4	230.7	216.0	205.4	195.9	190.0	181.9	177.1	174.1	173.0	169.5
75°	191.1	179.4	168.4	158.8	151.3	147.1	143.7	140.3	138.9	132.7	129.2
77.5°	139.4	131.7	124.8	118.0	112.6	109.9	103.2	99.3	96.9	94.0	93.3
80°	108.6	103.1	96.3	92.1	84.6	81.8	79.0	78.4	77.7	77.0	76.3
82.5°	81.7	76.2	69.3	66.8	64.7	63.1	61.5	60.8	60.1	60.5	60.4
85°	41.2	38.5	38.5	37.8	37.1	36.4	35.7	35.7	35.0	35.7	35.0
87.5°	16.0	15.8	16.1	15.3	16.2	16.4	16.2	16.4	17.2	16.4	16.4
90°	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5	22.6	23.8	24.6
92.5°	11.5	12.3	13.9	15.4	17.0	18.5	19.6	20.8	22.0	23.2	23.8
95°	21.6	18.4	18.6	18.8	19.0	19.2	20.3	21.5	22.6	23.8	24.5
97.5°	118.3	109.6	87.9	66.3	44.7	23.0	23.2	23.2	23.4	23.5	23.7
100°	157.0	145.4	118.6	91.9	65.2	38.4	35.1	31.8	28.5	25.2	23.7
102.5°	199.3	198.9	195.4	191.9	188.4	184.9	149.4	113.8	78.3	42.7	25.0
105°	267.3	268.3	269.2	270.3	271.2	272.2	273.9	275.7	277.4	279.1	276.6
107.5°	333.1	334.1	335.4	336.7	338.0	339.3	340.2	341.0	341.9	342.8	343.5
110°	379.2	380.0	381.3	382.4	383.6	384.7	385.1	385.5	385.9	386.2	386.8



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	425.7	426.5	427.1	427.6	428.1	428.7	428.6	428.5	428.4	428.3	428.7
115°	492.6	492.8	492.6	492.4	492.2	492.0	492.4	492.8	493.2	493.5	493.8
117.5°	555.3	555.9	556.3	556.7	557.2	557.6	557.5	557.4	557.4	557.3	557.2
120°	597.2	597.4	597.3	597.1	596.8	596.7	597.1	597.4	597.9	598.2	598.2
122.5°	635.0	635.4	635.7	635.9	636.2	636.5	636.7	637.0	637.1	637.4	637.3
125°	692.2	692.4	692.1	691.6	691.3	690.9	691.5	692.1	692.7	693.2	693.6
127.5°	743.0	743.5	744.4	745.3	746.1	747.1	747.0	746.8	746.7	746.6	746.5
130°	777.1	777.6	778.2	778.7	779.3	779.9	780.1	780.2	780.5	780.7	780.8
132.5°	809.2	809.8	810.5	811.2	811.9	812.7	812.9	813.0	813.3	813.5	813.5
135°	854.1	854.5	855.2	856.0	856.8	857.6	857.9	858.3	858.7	859.1	859.5
137.5°	896.9	897.3	898.2	899.1	899.9	900.8	901.2	901.6	902.1	902.5	902.7
140°	925.4	925.7	926.2	926.5	927.0	927.3	927.9	928.5	929.0	929.6	930.1
142.5°	951.1	951.5	951.7	951.9	952.2	952.4	952.9	953.3	953.7	954.2	954.3
145°	988.1	988.3	988.3	988.3	988.3	988.3	988.6	988.8	988.9	989.1	989.5
147.5°	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8	1019.9	1020.0	1020.2	1020.4
150°	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8	1039.8	1039.8	1039.8	1039.9
152.5°	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9	1057.2	1057.5	1057.8	1057.9
155°	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9	1080.6	1081.4	1082.2	1082.3
157.5°	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9
160°	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0
162.5°	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0	1124.1	1125.3	1126.4	1126.4
165°	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4	1138.9	1140.5	1142.0	1141.9
167.5°	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0	1149.7	1151.4	1153.1	1153.0
170°	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8	1156.3	1157.9	1159.4	1159.3
172.5°	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0	1160.5	1162.1	1163.6	1163.4
175°	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7	1165.4	1167.2	1169.0	1168.6
177.5°	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1	1167.4	1168.6	1169.9	1169.6
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1628.7	1629.8	1625.9	1624.8	1625.9	1629.8	1628.7	1631.9	1632.5	1636.9	1635.3
5°	1511.0	1509.6	1506.1	1506.8	1506.1	1509.6	1511.0	1516.5	1519.2	1530.3	1528.9
7.5°	1410.3	1405.0	1406.4	1401.0	1406.4	1405.0	1410.3	1415.3	1423.7	1428.7	1440.3
10°	1348.8	1341.2	1335.0	1329.5	1335.0	1341.2	1348.8	1351.5	1363.1	1368.6	1380.4
12.5°	1264.6	1258.1	1249.7	1251.4	1249.7	1258.1	1264.6	1276.7	1291.7	1303.2	1321.5
15°	1145.2	1135.0	1118.4	1120.5	1118.4	1135.0	1145.2	1154.2	1169.3	1195.4	1207.8
17.5°	1044.2	1044.3	1036.8	1038.5	1036.8	1044.3	1044.2	1056.4	1064.1	1080.8	1099.8
20°	992.0	987.1	987.8	985.8	987.8	987.1	992.0	1006.4	1014.7	1026.3	1047.0
22.5°	955.6	949.8	944.9	940.6	944.9	949.8	955.6	959.7	970.7	981.8	998.6
25°	894.3	890.2	884.1	882.7	884.1	890.2	894.3	900.5	906.0	920.5	930.7
27.5°	840.4	839.6	837.2	834.0	837.2	839.6	840.4	845.9	853.1	862.3	875.4
30°	809.1	807.7	806.3	804.3	806.3	807.7	809.1	814.6	820.1	827.7	838.0
32.5°	781.1	780.2	778.9	779.0	778.9	780.2	781.1	783.8	787.1	796.9	804.9
35°	741.1	740.4	739.0	738.3	739.0	740.4	741.1	743.8	745.9	748.6	755.5
37.5°	703.7	705.4	704.6	704.5	704.6	705.4	703.7	704.4	702.1	707.1	711.8
40°	677.8	678.5	679.8	679.2	679.8	678.5	677.8	678.5	678.5	678.5	682.6
42.5°	656.3	656.5	658.4	656.1	658.4	656.5	656.3	653.8	650.5	651.0	652.4
45°	618.0	622.2	621.5	621.5	621.5	622.2	618.0	613.2	612.5	609.8	609.8
47.5°	576.1	579.6	580.6	580.5	580.6	579.6	576.1	574.3	571.1	568.3	568.1
50°	548.5	547.2	549.2	548.5	549.2	547.2	548.5	545.1	540.3	540.3	539.0
52.5°	515.1	515.3	515.1	514.4	515.1	515.3	515.1	513.2	511.2	508.9	508.2
55°	463.3	464.0	462.6	463.3	462.6	464.0	463.3	462.6	462.6	461.2	462.6
57.5°	407.3	403.9	405.3	403.6	405.3	403.9	407.3	410.3	411.4	411.6	413.7
60°	367.1	361.6	360.2	357.5	360.2	361.6	367.1	373.9	376.7	378.1	380.1
62.5°	322.0	318.1	313.5	315.6	313.5	318.1	322.0	329.4	335.4	340.2	344.9
65°	261.9	259.2	257.1	259.8	257.1	259.2	261.9	267.4	272.9	283.9	294.2
67.5°	216.8	215.3	215.3	214.0	215.3	215.3	216.8	219.6	223.0	229.0	238.7
70°	193.2	191.1	191.1	189.8	191.1	191.1	193.2	193.2	196.6	199.3	206.2
72.5°	168.9	166.9	167.5	166.6	167.5	166.9	168.9	169.5	173.0	174.1	177.1
75°	125.1	121.7	121.7	122.3	121.7	121.7	125.1	129.2	132.7	138.9	140.3
77.5°	93.3	92.6	93.6	92.4	93.6	92.6	93.3	93.3	94.0	96.9	99.3
80°	76.3	75.6	74.9	77.0	74.9	75.6	76.3	76.3	77.0	77.7	78.4
82.5°	59.2	59.2	59.0	61.6	59.0	59.2	59.2	60.4	60.5	60.1	60.8
85°	35.7	34.4	35.7	34.4	35.7	34.4	35.7	35.0	35.7	35.0	35.7
87.5°	17.7	17.2	16.7	17.3	16.7	17.2	17.7	16.4	16.4	17.2	16.4
90°	25.0	25.4	25.7	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5
92.5°	23.8	23.9	24.0	24.1	24.0	23.9	23.8	23.8	23.2	22.0	20.8
95°	24.7	24.9	25.1	25.3	25.1	24.9	24.7	24.5	23.8	22.6	21.5
97.5°	23.8	24.0	24.2	24.5	24.2	24.0	23.8	23.7	23.5	23.4	23.2
100°	23.8	24.0	24.2	24.5	24.2	24.0	23.8	23.7	25.2	28.5	31.8
102.5°	25.0	25.1	25.1	25.1	25.1	25.1	25.0	25.0	42.7	78.3	113.8
105°	269.6	262.6	255.6	248.7	255.6	262.6	269.6	276.6	279.1	277.4	275.7
107.5°	344.3	345.0	345.8	346.5	345.8	345.0	344.3	343.5	342.8	341.9	341.0
110°	387.4	387.9	388.5	389.1	388.5	387.9	387.4	386.8	386.2	385.9	385.5



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	429.5	430.2	430.9	431.6	430.9	430.2	429.5	428.7	428.3	428.4	428.5
115°	493.8	493.8	493.8	493.8	493.8	493.8	493.8	493.8	493.5	493.2	492.8
117.5°	557.2	557.1	557.0	556.9	557.0	557.1	557.2	557.2	557.3	557.4	557.4
120°	597.9	597.4	597.1	596.7	597.1	597.4	597.9	598.2	598.2	597.9	597.4
122.5°	637.0	636.5	636.2	635.8	636.2	636.5	637.0	637.3	637.4	637.1	637.0
125°	693.8	694.0	694.2	694.4	694.2	694.0	693.8	693.6	693.2	692.7	692.1
127.5°	746.3	746.1	746.0	745.9	746.0	746.1	746.3	746.5	746.6	746.7	746.8
130°	780.8	780.8	780.8	780.8	780.8	780.8	780.8	780.8	780.7	780.5	780.2
132.5°	813.3	813.1	813.0	812.9	813.0	813.1	813.3	813.5	813.5	813.3	813.0
135°	859.9	860.2	860.7	861.0	860.7	860.2	859.9	859.5	859.1	858.7	858.3
137.5°	902.5	902.4	902.3	902.2	902.3	902.4	902.5	902.7	902.5	902.1	901.6
140°	930.2	930.4	930.6	930.8	930.6	930.4	930.2	930.1	929.6	929.0	928.5
142.5°	954.4	954.4	954.5	954.5	954.5	954.4	954.4	954.3	954.2	953.7	953.3
145°	989.8	990.2	990.6	991.0	990.6	990.2	989.8	989.5	989.1	988.9	988.8
147.5°	1020.6	1020.8	1021.0	1021.1	1021.0	1020.8	1020.6	1020.4	1020.2	1020.0	1019.9
150°	1040.1	1040.3	1040.5	1040.7	1040.5	1040.3	1040.1	1039.9	1039.8	1039.8	1039.8
152.5°	1057.8	1057.7	1057.6	1057.5	1057.6	1057.7	1057.8	1057.9	1057.8	1057.5	1057.2
155°	1081.7	1081.2	1080.6	1080.0	1080.6	1081.2	1081.7	1082.3	1082.2	1081.4	1080.6
157.5°	1101.8	1100.8	1099.8	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8
160°	1114.8	1113.7	1112.5	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7
162.5°	1125.1	1123.8	1122.5	1121.1	1122.5	1123.8	1125.1	1126.4	1126.4	1125.3	1124.1
165°	1140.1	1138.4	1136.7	1134.9	1136.7	1138.4	1140.1	1141.9	1142.0	1140.5	1138.9
167.5°	1151.1	1149.1	1147.2	1145.2	1147.2	1149.1	1151.1	1153.0	1153.1	1151.4	1149.7
170°	1157.3	1155.4	1153.4	1151.5	1153.4	1155.4	1157.3	1159.3	1159.4	1157.9	1156.3
172.5°	1161.2	1159.2	1157.1	1154.9	1157.1	1159.2	1161.2	1163.4	1163.6	1162.1	1160.5
175°	1166.3	1164.0	1161.7	1159.3	1161.7	1164.0	1166.3	1168.6	1169.0	1167.2	1165.4
177.5°	1167.7	1165.9	1164.0	1162.2	1164.0	1165.9	1167.7	1169.6	1169.9	1168.6	1167.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1631.9	1635.8	1644.6	1654.5	1662.8	1669.9	1675.4	1683.1	1690.2	1700.1	1709.5
5°	1533.0	1542.6	1556.3	1572.9	1593.5	1607.2	1624.4	1639.5	1661.6	1683.5	1704.9
7.5°	1446.0	1456.6	1476.9	1499.7	1524.1	1546.7	1567.1	1593.7	1622.9	1654.9	1690.7
10°	1390.0	1401.7	1425.7	1451.8	1480.7	1502.7	1530.3	1561.9	1594.8	1634.0	1678.0
12.5°	1339.4	1350.6	1379.5	1406.2	1436.1	1460.3	1492.3	1524.5	1568.5	1610.9	1661.0
15°	1240.8	1270.4	1303.4	1335.0	1370.7	1400.3	1438.8	1471.8	1513.7	1573.6	1630.6
17.5°	1131.4	1162.9	1203.9	1252.7	1300.6	1337.2	1376.2	1417.2	1467.1	1528.2	1594.1
20°	1067.6	1093.0	1138.4	1192.7	1248.4	1299.2	1335.0	1380.4	1431.9	1497.9	1566.0
22.5°	1019.8	1041.3	1076.8	1131.1	1191.2	1250.3	1296.0	1340.7	1397.8	1463.8	1537.9
25°	948.0	971.4	1002.3	1039.4	1108.1	1170.7	1230.5	1282.0	1342.6	1408.5	1491.0
27.5°	888.3	908.6	936.9	975.6	1021.8	1090.8	1163.3	1222.1	1284.1	1355.0	1437.5
30°	853.1	869.6	892.9	932.1	976.1	1038.0	1111.6	1180.3	1242.9	1316.5	1402.4
32.5°	816.2	833.9	856.7	887.6	934.9	986.9	1060.4	1135.7	1202.2	1277.4	1361.7
35°	767.2	780.9	801.5	833.2	875.8	921.2	986.4	1064.1	1134.3	1214.7	1295.1
37.5°	717.6	733.7	750.0	778.2	813.1	861.9	915.4	994.7	1072.4	1145.8	1224.3
40°	689.5	699.1	717.0	739.7	776.8	820.1	870.3	948.0	1025.6	1098.5	1177.6
42.5°	658.1	668.9	684.0	706.7	739.9	782.1	831.2	898.5	979.5	1050.2	1122.1
45°	614.6	620.8	635.8	655.1	682.6	725.2	770.6	830.4	906.7	974.0	1037.3
47.5°	570.6	575.9	585.4	603.0	633.8	668.0	710.5	764.1	831.1	898.5	951.9
50°	540.3	545.1	554.1	570.6	598.1	631.7	673.6	721.8	781.6	846.2	890.9
52.5°	510.1	512.7	521.1	539.8	562.8	596.0	633.5	677.8	733.7	787.4	832.6
55°	461.9	468.1	473.6	487.4	509.4	541.0	574.7	616.6	660.0	705.3	743.8
57.5°	411.7	418.5	426.5	438.6	456.1	485.4	515.7	549.7	586.7	624.3	656.6
60°	378.8	385.0	391.8	405.6	421.4	444.8	477.8	507.3	535.5	569.9	602.2
62.5°	346.3	352.5	360.5	371.5	386.8	409.1	436.5	462.3	491.5	521.5	545.5
65°	298.3	303.2	309.4	319.7	334.1	354.0	376.7	396.7	422.8	444.8	466.7
67.5°	245.7	254.9	263.0	271.4	283.6	302.2	318.6	337.7	355.4	371.8	391.8
70°	211.0	221.4	228.9	237.8	249.5	265.4	281.1	294.2	308.7	324.4	342.3
72.5°	181.9	190.0	195.9	205.4	216.0	230.7	245.4	256.2	267.9	278.8	296.2
75°	143.7	147.1	151.3	158.8	168.4	179.4	191.1	200.7	207.6	217.2	229.6
77.5°	103.2	109.9	112.6	118.0	124.8	131.7	139.4	147.5	154.1	157.6	167.0
80°	79.0	81.8	84.6	92.1	96.3	103.1	108.6	116.1	118.9	122.3	131.3
82.5°	61.5	63.1	64.7	66.8	69.3	76.2	81.7	86.4	89.2	90.5	97.2
85°	35.7	36.4	37.1	37.8	38.5	38.5	41.2	44.7	49.5	49.5	51.6
87.5°	16.2	16.4	16.2	15.3	16.1	15.8	16.0	15.6	16.8	18.0	19.2
90°	20.3	19.2	17.7	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6
92.5°	19.6	18.5	17.0	15.4	13.9	12.3	11.5	11.4	11.2	11.1	11.0
95°	20.3	19.2	19.0	18.8	18.6	18.4	21.6	28.2	34.8	41.4	48.0
97.5°	23.2	23.0	44.7	66.3	87.9	109.6	118.3	114.3	110.1	106.0	101.9
100°	35.1	38.4	65.2	91.9	118.6	145.4	157.0	153.5	150.1	146.5	143.1
102.5°	149.4	184.9	188.4	191.9	195.4	198.9	199.3	196.8	194.2	191.7	189.2
105°	273.9	272.2	271.2	270.3	269.2	268.3	267.3	266.0	264.9	263.7	262.6
107.5°	340.2	339.3	338.0	336.7	335.4	334.1	333.1	332.5	331.9	331.4	330.8
110°	385.1	384.7	383.6	382.4	381.3	380.0	379.2	378.6	378.0	377.5	376.9



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	428.6	428.7	428.1	427.6	427.1	426.5	425.7	424.6	423.6	422.6	421.5
115°	492.4	492.0	492.2	492.4	492.6	492.8	492.6	492.0	491.5	490.9	490.3
117.5°	557.5	557.6	557.2	556.7	556.3	555.9	555.3	554.5	553.7	552.9	552.2
120°	597.1	596.7	596.8	597.1	597.3	597.4	597.2	596.4	595.6	594.9	594.1
122.5°	636.7	636.5	636.2	635.9	635.7	635.4	635.0	634.6	634.0	633.6	633.2
125°	691.5	690.9	691.3	691.6	692.1	692.4	692.2	691.5	690.7	689.9	689.1
127.5°	747.0	747.1	746.1	745.3	744.4	743.5	743.0	742.8	742.6	742.4	742.2
130°	780.1	779.9	779.3	778.7	778.2	777.6	777.1	777.0	776.8	776.6	776.4
132.5°	812.9	812.7	811.9	811.2	810.5	809.8	809.2	808.8	808.5	808.1	807.8
135°	857.9	857.6	856.8	856.0	855.2	854.5	854.1	854.3	854.5	854.7	854.9
137.5°	901.2	900.8	899.9	899.1	898.2	897.3	896.9	896.8	896.7	896.6	896.6
140°	927.9	927.3	927.0	926.5	926.2	925.7	925.4	925.0	924.6	924.2	923.9
142.5°	952.9	952.4	952.2	951.9	951.7	951.5	951.1	950.4	949.6	948.9	948.2
145°	988.6	988.3	988.3	988.3	988.3	988.3	988.1	987.5	986.9	986.4	985.8
147.5°	1019.8	1019.6	1019.8	1020.0	1020.2	1020.4	1019.9	1018.8	1017.8	1016.7	1015.5
150°	1039.8	1039.8	1040.0	1040.3	1040.4	1040.6	1040.3	1039.6	1038.8	1038.0	1037.2
152.5°	1056.9	1056.6	1057.0	1057.3	1057.7	1058.0	1057.8	1057.2	1056.6	1056.0	1055.3
155°	1079.9	1079.1	1079.7	1080.3	1080.8	1081.4	1081.6	1081.4	1081.2	1081.1	1080.8
157.5°	1099.8	1098.8	1099.5	1100.1	1100.8	1101.5	1101.8	1101.9	1102.1	1102.2	1102.3
160°	1112.5	1111.4	1111.6	1111.7	1112.0	1112.2	1112.5	1113.1	1113.7	1114.3	1114.8
162.5°	1123.0	1121.8	1122.1	1122.2	1122.4	1122.6	1123.1	1123.8	1124.6	1125.3	1126.0
165°	1137.4	1135.8	1135.8	1135.8	1135.8	1135.8	1136.3	1137.2	1138.2	1139.2	1140.1
167.5°	1148.0	1146.2	1146.4	1146.5	1146.6	1146.8	1147.3	1148.3	1149.3	1150.3	1151.3
170°	1154.8	1153.2	1153.1	1152.9	1152.6	1152.4	1153.0	1154.1	1155.3	1156.4	1157.6
172.5°	1159.0	1157.4	1157.3	1157.0	1156.8	1156.7	1157.1	1158.3	1159.4	1160.6	1161.7
175°	1163.7	1162.0	1161.7	1161.6	1161.4	1161.2	1161.7	1162.9	1164.0	1165.2	1166.3
177.5°	1166.1	1164.9	1164.6	1164.3	1164.0	1163.7	1164.1	1165.2	1166.2	1167.3	1168.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1716.7	1721.6	1727.1	1737.6	1746.4	1750.2	1757.9	1763.4	1761.8	1769.4	1782.6
5°	1723.4	1742.0	1763.2	1785.3	1810.0	1830.7	1847.1	1863.6	1876.7	1892.5	1915.9
7.5°	1722.3	1755.3	1791.1	1830.7	1871.2	1906.3	1938.7	1971.7	2001.0	2033.0	2074.9
10°	1717.9	1761.9	1806.6	1858.1	1909.7	1958.5	2002.5	2043.8	2082.9	2124.9	2177.8
12.5°	1713.0	1763.5	1817.6	1879.6	1943.8	2002.5	2054.2	2113.6	2162.7	2216.7	2277.9
15°	1691.1	1759.1	1832.7	1913.1	1990.1	2069.2	2139.9	2212.9	2280.9	2345.5	2422.5
17.5°	1666.0	1744.6	1831.3	1926.3	2018.9	2115.0	2199.0	2290.8	2360.3	2447.1	2518.6
20°	1645.7	1730.3	1823.1	1929.6	2034.8	2141.3	2234.1	2327.6	2406.0	2493.3	2584.0
22.5°	1620.9	1713.7	1814.3	1924.7	2034.8	2151.2	2253.9	2346.9	2443.9	2542.3	2635.8
25°	1581.1	1677.3	1783.9	1904.9	2031.4	2150.3	2260.3	2375.8	2480.3	2586.8	2670.6
27.5°	1532.1	1633.2	1745.5	1870.4	2000.2	2121.9	2251.5	2374.6	2479.7	2582.2	2655.4
30°	1493.1	1599.7	1707.5	1834.1	1968.8	2099.4	2238.3	2361.3	2472.0	2564.1	2605.4
32.5°	1452.9	1554.0	1665.3	1793.4	1931.4	2071.9	2209.7	2335.5	2437.9	2493.2	2494.2
35°	1383.1	1478.0	1593.5	1719.2	1860.9	2013.4	2153.0	2276.7	2339.3	2344.2	2276.7
37.5°	1306.9	1394.0	1503.0	1628.9	1784.0	1935.8	2078.4	2160.9	2181.8	2111.8	1987.2
40°	1252.5	1332.9	1438.1	1567.4	1721.3	1878.1	2008.0	2068.5	2046.5	1933.0	1794.2
42.5°	1195.3	1270.2	1371.6	1499.2	1653.7	1812.1	1922.8	1955.2	1896.9	1765.9	1603.4
45°	1102.0	1170.7	1271.1	1399.6	1548.1	1696.6	1780.5	1763.9	1667.0	1511.7	1329.5
47.5°	1004.8	1071.2	1161.5	1280.4	1432.4	1560.6	1617.4	1567.6	1429.7	1258.8	1110.6
50°	940.4	1008.5	1091.7	1205.1	1343.9	1467.7	1504.1	1428.5	1275.1	1110.9	974.7
52.5°	877.2	935.3	1016.8	1126.4	1259.2	1363.7	1383.1	1296.0	1137.7	990.4	869.7
55°	780.9	833.9	902.6	1005.7	1120.5	1209.2	1198.9	1086.8	943.1	817.3	722.5
57.5°	687.9	727.7	791.3	887.9	988.7	1048.2	1010.6	915.0	781.1	678.1	598.1
60°	626.3	663.4	722.5	807.0	895.7	929.4	897.8	794.0	688.1	593.9	526.6
62.5°	567.9	600.7	651.5	730.0	801.7	821.7	787.8	697.2	601.8	521.3	465.5
65°	483.3	513.5	556.8	612.5	662.0	671.6	649.6	556.8	484.7	417.2	378.8
67.5°	406.4	426.2	460.0	508.2	534.4	540.0	497.6	439.3	375.7	334.2	305.2
70°	354.7	368.4	400.1	426.2	447.5	448.2	409.1	362.3	313.5	279.8	258.5
72.5°	304.7	317.9	341.8	359.6	376.0	370.7	334.8	297.9	258.5	233.1	217.2
75°	235.1	246.8	259.2	267.4	267.4	260.5	234.5	206.9	184.3	169.1	164.3
77.5°	170.9	180.6	184.7	183.4	180.9	170.2	153.7	135.7	127.6	120.5	116.8
80°	134.1	138.2	139.6	136.1	132.0	119.6	108.6	101.1	93.5	90.7	89.4
82.5°	99.4	103.0	99.4	100.4	91.3	81.1	75.1	72.5	69.3	68.2	66.8
85°	53.0	52.3	50.9	47.4	41.2	39.9	39.2	38.5	37.1	37.8	36.4
87.5°	19.1	17.9	16.1	16.0	16.4	15.6	16.4	16.7	17.0	16.7	18.1
90°	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5
92.5°	11.1	11.2	11.4	11.5	12.3	13.9	15.4	17.0	18.5	19.6	20.8
95°	41.4	34.8	28.2	21.6	18.4	18.6	18.8	19.0	19.2	20.3	21.5
97.5°	106.0	110.1	114.3	118.3	109.6	87.9	66.3	44.7	23.0	23.2	23.2
100°	146.5	150.1	153.5	157.0	145.4	118.6	91.9	65.2	38.4	35.1	31.8
102.5°	191.7	194.2	196.8	199.3	198.9	195.4	191.9	188.4	184.9	149.4	113.8
105°	263.7	264.9	266.0	267.3	268.3	269.2	270.3	271.2	272.2	273.9	275.7
107.5°	331.4	331.9	332.5	333.1	334.1	335.4	336.7	338.0	339.3	340.2	341.0
110°	377.5	378.0	378.6	379.2	380.0	381.3	382.4	383.6	384.7	385.1	385.5



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	422.6	423.6	424.6	425.7	426.5	427.1	427.6	428.1	428.7	428.6	428.5
115°	490.9	491.5	492.0	492.6	492.8	492.6	492.4	492.2	492.0	492.4	492.8
117.5°	552.9	553.7	554.5	555.3	555.9	556.3	556.7	557.2	557.6	557.5	557.4
120°	594.9	595.6	596.4	597.2	597.4	597.3	597.1	596.8	596.7	597.1	597.4
122.5°	633.6	634.0	634.6	635.0	635.4	635.7	635.9	636.2	636.5	636.7	637.0
125°	689.9	690.7	691.5	692.2	692.4	692.1	691.6	691.3	690.9	691.5	692.1
127.5°	742.4	742.6	742.8	743.0	743.5	744.4	745.3	746.1	747.1	747.0	746.8
130°	776.6	776.8	777.0	777.1	777.6	778.2	778.7	779.3	779.9	780.1	780.2
132.5°	808.1	808.5	808.8	809.2	809.8	810.5	811.2	811.9	812.7	812.9	813.0
135°	854.7	854.5	854.3	854.1	854.5	855.2	856.0	856.8	857.6	857.9	858.3
137.5°	896.6	896.7	896.8	896.9	897.3	898.2	899.1	899.9	900.8	901.2	901.6
140°	924.2	924.6	925.0	925.4	925.7	926.2	926.5	927.0	927.3	927.9	928.5
142.5°	948.9	949.6	950.4	951.1	951.5	951.7	951.9	952.2	952.4	952.9	953.3
145°	986.4	986.9	987.5	988.1	988.3	988.3	988.3	988.3	988.3	988.6	988.8
147.5°	1016.7	1017.8	1018.8	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8	1019.9
150°	1038.0	1038.8	1039.6	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8	1039.8
152.5°	1056.0	1056.6	1057.2	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9	1057.2
155°	1081.1	1081.2	1081.4	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9	1080.6
157.5°	1102.2	1102.1	1101.9	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8	1100.8
160°	1114.3	1113.7	1113.1	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5	1113.7
162.5°	1125.3	1124.6	1123.8	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0	1124.1
165°	1139.2	1138.2	1137.2	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4	1138.9
167.5°	1150.3	1149.3	1148.3	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0	1149.7
170°	1156.4	1155.3	1154.1	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8	1156.3
172.5°	1160.6	1159.4	1158.3	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0	1160.5
175°	1165.2	1164.0	1162.9	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7	1165.4
177.5°	1167.3	1166.2	1165.2	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1	1167.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1789.8	1792.0	1793.6	1799.1	1799.7	1804.7	1799.7
5°	1937.9	1947.5	1962.6	1977.7	1979.1	1988.7	1971.5
7.5°	2103.9	2126.2	2140.1	2164.6	2174.2	2180.2	2170.3
10°	2218.4	2238.9	2275.4	2293.3	2311.2	2313.9	2305.7
12.5°	2328.9	2361.6	2390.3	2424.1	2423.4	2447.6	2438.7
15°	2476.1	2509.8	2549.7	2587.5	2601.3	2601.3	2612.3
17.5°	2581.2	2642.9	2684.2	2713.9	2746.2	2751.9	2748.1
20°	2652.1	2718.8	2762.8	2801.3	2823.3	2829.5	2829.5
22.5°	2704.9	2761.7	2804.6	2839.2	2857.4	2864.6	2862.5
25°	2741.5	2790.2	2816.4	2826.7	2831.5	2830.2	2817.1
27.5°	2691.4	2689.2	2672.7	2641.1	2617.4	2602.9	2586.4
30°	2595.7	2560.0	2518.8	2473.4	2414.9	2370.2	2356.5
32.5°	2453.3	2373.0	2303.2	2227.6	2164.7	2120.0	2101.4
35°	2177.8	2050.6	1946.8	1856.1	1790.1	1748.9	1735.1
37.5°	1850.8	1727.8	1599.2	1511.2	1456.6	1414.9	1399.3
40°	1643.0	1508.9	1396.9	1314.4	1258.0	1217.5	1216.8
42.5°	1453.2	1325.3	1219.8	1160.4	1099.6	1072.8	1072.6
45°	1189.9	1087.5	998.2	951.4	915.0	892.9	886.7
47.5°	985.2	900.5	841.0	803.7	774.0	760.0	751.0
50°	870.3	796.1	748.6	716.3	699.8	681.9	680.5
52.5°	774.6	714.6	677.7	651.4	630.5	619.7	620.1
55°	651.0	603.6	577.5	557.5	541.0	532.8	529.3
57.5°	548.5	512.8	493.9	475.5	468.6	462.1	460.3
60°	484.7	460.5	442.7	428.3	417.9	415.9	415.2
62.5°	431.9	406.7	394.3	383.1	375.7	372.5	371.2
65°	356.1	337.5	326.5	317.6	314.9	310.0	309.4
67.5°	287.1	276.0	268.6	262.4	258.7	258.5	258.5
70°	244.7	238.5	232.4	228.9	226.9	225.5	225.5
72.5°	208.4	203.9	198.8	197.0	196.6	195.2	194.7
75°	158.8	153.9	154.6	151.3	148.5	145.1	143.0
77.5°	112.6	109.2	108.5	108.1	105.7	105.3	106.4
80°	87.3	83.9	83.2	83.9	83.2	81.1	81.1
82.5°	66.4	63.5	62.9	62.4	61.7	62.4	61.3
85°	35.7	34.4	34.4	34.4	35.7	35.0	34.4
87.5°	17.2	16.9	17.6	17.1	17.2	16.7	17.3
90°	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	22.0	23.2	23.8	23.8	23.9	24.0	24.1
95°	22.6	23.8	24.5	24.7	24.9	25.1	25.3
97.5°	23.4	23.5	23.7	23.8	24.0	24.2	24.5
100°	28.5	25.2	23.7	23.8	24.0	24.2	24.5
102.5°	78.3	42.7	25.0	25.0	25.1	25.1	25.1
105°	277.4	279.1	276.6	269.6	262.6	255.6	248.7
107.5°	341.9	342.8	343.5	344.3	345.0	345.8	346.5
110°	385.9	386.2	386.8	387.4	387.9	388.5	389.1



TEST NUMBER: P333103-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	428.4	428.3	428.7	429.5	430.2	430.9	431.6
115°	493.2	493.5	493.8	493.8	493.8	493.8	493.8
117.5°	557.4	557.3	557.2	557.2	557.1	557.0	556.9
120°	597.9	598.2	598.2	597.9	597.4	597.1	596.7
122.5°	637.1	637.4	637.3	637.0	636.5	636.2	635.8
125°	692.7	693.2	693.6	693.8	694.0	694.2	694.4
127.5°	746.7	746.6	746.5	746.3	746.1	746.0	745.9
130°	780.5	780.7	780.8	780.8	780.8	780.8	780.8
132.5°	813.3	813.5	813.5	813.3	813.1	813.0	812.9
135°	858.7	859.1	859.5	859.9	860.2	860.7	861.0
137.5°	902.1	902.5	902.7	902.5	902.4	902.3	902.2
140°	929.0	929.6	930.1	930.2	930.4	930.6	930.8
142.5°	953.7	954.2	954.3	954.4	954.4	954.5	954.5
145°	988.9	989.1	989.5	989.8	990.2	990.6	991.0
147.5°	1020.0	1020.2	1020.4	1020.6	1020.8	1021.0	1021.1
150°	1039.8	1039.8	1039.9	1040.1	1040.3	1040.5	1040.7
152.5°	1057.5	1057.8	1057.9	1057.8	1057.7	1057.6	1057.5
155°	1081.4	1082.2	1082.3	1081.7	1081.2	1080.6	1080.0
157.5°	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8
160°	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4
162.5°	1125.3	1126.4	1126.4	1125.1	1123.8	1122.5	1121.1
165°	1140.5	1142.0	1141.9	1140.1	1138.4	1136.7	1134.9
167.5°	1151.4	1153.1	1153.0	1151.1	1149.1	1147.2	1145.2
170°	1157.9	1159.4	1159.3	1157.3	1155.4	1153.4	1151.5
172.5°	1162.1	1163.6	1163.4	1161.2	1159.2	1157.1	1154.9
175°	1167.2	1169.0	1168.6	1166.3	1164.0	1161.7	1159.3
177.5°	1168.6	1169.9	1169.6	1167.7	1165.9	1164.0	1162.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3

(END OF REPORT)