

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333105-935

Luminaire Tested: **S124RDIW-S1195D1050U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333105-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1050U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7759.7 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333105-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333105-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14495	14495	14495
5°	14528	14350	14439
10°	14437	14178	14178
15°	14271	13881	13778
20°	14044	13489	13241
25°	13752	13030	12699
30°	13470	12547	12021
35°	13157	12046	11340
40°	12779	11475	10606
45°	12432	10909	9857
50°	12036	10257	9065
55°	11610	9578	8204
60°	11144	8835	7325
65°	10714	7904	6460
70°	10093	6878	5486
75°	9304	5705	4460
80°	8117	4347	4091
85°	6873	3946	3696



TEST NUMBER: P333105-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.7	2.2
10°-20°	470.4	6.1
20°-30°	679.2	8.8
30°-40°	769.9	9.9
40°-50°	743.4	9.6
50°-60°	618.2	8.0
60°-70°	426.9	5.5
70°-80°	216.4	2.8
80°-90°	58.9	0.8
90°-100°	39.9	0.5
100°-110°	254.3	3.3
110°-120°	486.6	6.3
120°-130°	617.7	8.0
130°-140°	660.8	8.5
140°-150°	618.0	8.0
150°-160°	498.3	6.4
160°-170°	321.4	4.1
170°-180°	110.8	1.4
0°-30°	1318.2	17.0
0°-40°	2088.1	26.9
0°-60°	3449.7	44.5
0°-90°	4151.9	53.5
90°-120°	780.8	10.1
90°-150°	2677.3	34.5
90°-180°	3608.0	46.5
0°-180°	7759.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1796	1796	1796	1796	1796	
5°	1793	1787	1771	1784	1782	170
15°	1708	1694	1661	1658	1648	481
25°	1544	1517	1463	1440	1426	711
35°	1335	1290	1222	1177	1151	834
45°	1089	1036	956	890	863	839
55°	825	768	680	612	583	738
65°	561	500	414	357	338	554
75°	298	247	183	152	143	315
85°	74	48	43	40	40	84
90°	3	12	19	24	26	6
95°	48	20	19	24	25	62
105°	263	268	272	278	249	275
115°	490	493	492	494	494	482
125°	689	692	691	693	694	615
135°	855	854	858	859	861	658
145°	986	988	988	989	991	616
155°	1081	1082	1079	1082	1080	498
165°	1140	1136	1136	1142	1135	322
175°	1166	1161	1162	1169	1159	111
180°	1166	1166	1166	1166	1166	



TEST NUMBER: P333105-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1799.9	1799.0	1798.0	1797.0	1796.0	1794.2	1791.6	1788.8	1786.1	1783.5	1786.1
5°	1792.8	1791.6	1790.4	1789.2	1788.0	1785.5	1781.8	1778.1	1774.5	1770.8	1773.8
7.5°	1776.6	1775.3	1774.0	1772.7	1771.4	1768.4	1763.7	1758.9	1754.1	1749.4	1751.4
10°	1761.2	1759.6	1758.2	1756.6	1755.1	1751.5	1746.1	1740.6	1735.1	1729.6	1730.8
12.5°	1741.4	1739.7	1737.8	1736.0	1734.3	1730.2	1723.7	1717.3	1710.7	1704.3	1705.0
15°	1707.5	1704.8	1702.1	1699.4	1696.6	1691.3	1683.8	1676.1	1668.4	1660.8	1660.2
17.5°	1666.6	1662.6	1658.6	1654.7	1650.7	1644.2	1635.0	1625.8	1616.6	1607.5	1605.8
20°	1634.7	1630.7	1626.8	1622.8	1618.9	1611.6	1601.3	1590.9	1580.5	1570.1	1567.6
22.5°	1599.5	1595.1	1590.6	1586.1	1581.7	1573.9	1562.7	1551.6	1540.5	1529.4	1525.7
25°	1543.9	1538.4	1532.9	1527.5	1522.0	1512.9	1500.5	1487.9	1475.4	1462.8	1457.7
27.5°	1485.7	1478.8	1471.9	1465.0	1458.0	1447.9	1434.5	1421.2	1407.7	1394.4	1387.9
30°	1445.0	1437.4	1429.7	1422.0	1414.5	1403.4	1389.1	1374.7	1360.4	1346.0	1338.3
32.5°	1402.1	1393.4	1384.8	1376.2	1367.6	1355.9	1341.0	1326.2	1311.3	1296.5	1287.6
35°	1335.0	1325.2	1315.4	1305.6	1295.9	1283.3	1268.1	1252.8	1237.5	1222.3	1211.9
37.5°	1263.3	1253.1	1243.0	1233.0	1222.9	1209.4	1192.5	1175.5	1158.6	1141.7	1130.1
40°	1212.6	1202.6	1192.5	1182.4	1172.3	1158.6	1141.2	1123.7	1106.3	1088.9	1076.1
42.5°	1164.2	1153.7	1143.1	1132.5	1122.0	1107.6	1089.4	1071.3	1053.2	1035.0	1021.9
45°	1088.9	1077.5	1066.3	1055.0	1043.7	1028.8	1010.6	992.2	973.9	955.5	940.6
47.5°	1011.1	999.4	987.7	976.0	964.4	949.0	930.0	910.9	891.8	872.8	857.2
50°	958.3	946.3	934.4	922.6	910.6	894.8	875.3	855.7	836.2	816.7	801.4
52.5°	904.4	892.7	881.1	869.4	857.7	841.8	821.8	801.8	781.7	761.6	746.1
55°	824.9	812.7	800.5	788.2	776.0	760.0	740.1	720.3	700.4	680.5	664.7
57.5°	746.2	733.6	720.8	708.2	695.4	679.3	659.8	640.2	620.6	601.1	585.0
60°	690.2	678.0	665.7	653.5	641.3	625.4	605.9	586.3	566.7	547.2	531.3
62.5°	639.6	626.9	614.2	601.5	588.8	572.4	552.3	532.3	512.2	492.2	477.5
65°	560.9	547.8	534.7	521.5	508.4	492.1	472.5	453.0	433.4	413.8	400.7
67.5°	479.2	466.7	454.1	441.5	429.0	413.5	395.4	377.3	359.1	341.0	329.7
70°	427.6	414.7	401.9	389.1	376.3	361.1	343.7	326.3	308.9	291.4	281.4
72.5°	372.6	361.0	349.4	337.8	326.1	312.1	295.7	279.2	262.8	246.3	237.7
75°	298.3	287.1	275.7	264.4	253.1	240.3	225.9	211.5	197.3	182.9	175.8
77.5°	223.0	213.4	203.8	194.2	184.6	174.0	162.4	150.8	139.2	127.6	123.5
80°	174.6	165.7	156.9	148.0	139.1	130.2	121.0	111.8	102.6	93.5	92.6
82.5°	132.9	124.7	116.6	108.4	100.3	93.6	88.3	83.1	77.8	72.6	71.9
85°	74.2	68.1	62.0	55.9	49.8	46.3	45.4	44.4	43.6	42.6	42.0
87.5°	25.8	24.3	22.7	21.3	19.7	18.9	19.0	19.1	19.2	19.2	19.2
90°	2.6	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3
92.5°	11.0	11.1	11.2	11.4	11.5	12.3	13.9	15.4	17.0	18.5	19.6
95°	48.0	41.4	34.8	28.2	21.6	18.4	18.6	18.8	19.0	19.2	20.3
97.5°	101.9	106.0	110.1	114.3	118.3	109.6	87.9	66.3	44.7	23.0	23.2
100°	143.1	146.5	150.1	153.5	157.0	145.4	118.6	91.9	65.2	38.4	35.1
102.5°	189.2	191.7	194.2	196.8	199.3	198.9	195.4	191.9	188.4	184.9	149.4
105°	262.6	263.7	264.9	266.0	267.3	268.3	269.2	270.3	271.2	272.2	273.9
107.5°	330.8	331.4	331.9	332.5	333.1	334.1	335.4	336.7	338.0	339.3	340.2
110°	376.9	377.5	378.0	378.6	379.2	380.0	381.3	382.4	383.6	384.7	385.1



TEST NUMBER: P333105-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.5	422.6	423.6	424.6	425.7	426.5	427.1	427.6	428.1	428.7	428.6
115°	490.3	490.9	491.5	492.0	492.6	492.8	492.6	492.4	492.2	492.0	492.4
117.5°	552.2	552.9	553.7	554.5	555.3	555.9	556.3	556.7	557.2	557.6	557.5
120°	594.1	594.9	595.6	596.4	597.2	597.4	597.3	597.1	596.8	596.7	597.1
122.5°	633.2	633.6	634.0	634.6	635.0	635.4	635.7	635.9	636.2	636.5	636.7
125°	689.1	689.9	690.7	691.5	692.2	692.4	692.1	691.6	691.3	690.9	691.5
127.5°	742.2	742.4	742.6	742.8	743.0	743.5	744.4	745.3	746.1	747.1	747.0
130°	776.4	776.6	776.8	777.0	777.1	777.6	778.2	778.7	779.3	779.9	780.1
132.5°	807.8	808.1	808.5	808.8	809.2	809.8	810.5	811.2	811.9	812.7	812.9
135°	854.9	854.7	854.5	854.3	854.1	854.5	855.2	856.0	856.8	857.6	857.9
137.5°	896.6	896.6	896.7	896.8	896.9	897.3	898.2	899.1	899.9	900.8	901.2
140°	923.9	924.2	924.6	925.0	925.4	925.7	926.2	926.5	927.0	927.3	927.9
142.5°	948.2	948.9	949.6	950.4	951.1	951.5	951.7	951.9	952.2	952.4	952.9
145°	985.8	986.4	986.9	987.5	988.1	988.3	988.3	988.3	988.3	988.3	988.6
147.5°	1015.5	1016.7	1017.8	1018.8	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8
150°	1037.2	1038.0	1038.8	1039.6	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8
152.5°	1055.3	1056.0	1056.6	1057.2	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9
155°	1080.8	1081.1	1081.2	1081.4	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9
157.5°	1102.3	1102.2	1102.1	1101.9	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8
160°	1114.8	1114.3	1113.7	1113.1	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5
162.5°	1126.0	1125.3	1124.6	1123.8	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0
165°	1140.1	1139.2	1138.2	1137.2	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4
167.5°	1151.3	1150.3	1149.3	1148.3	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0
170°	1157.6	1156.4	1155.3	1154.1	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8
172.5°	1161.7	1160.6	1159.4	1158.3	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0
175°	1166.3	1165.2	1164.0	1162.9	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7
177.5°	1168.4	1167.3	1166.2	1165.2	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333105-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1788.8	1791.6	1794.2	1795.4	1795.2	1794.9	1794.7	1794.5
5°	1776.9	1779.9	1783.0	1784.3	1783.6	1783.0	1782.4	1781.8
7.5°	1753.3	1755.2	1757.2	1757.6	1756.7	1755.8	1754.7	1753.8
10°	1732.0	1733.2	1734.5	1734.5	1733.2	1732.0	1730.8	1729.6
12.5°	1705.7	1706.5	1707.2	1706.7	1705.0	1703.3	1701.6	1699.9
15°	1659.6	1659.0	1658.4	1657.0	1654.8	1652.7	1650.6	1648.5
17.5°	1604.0	1602.3	1600.6	1598.2	1594.9	1591.6	1588.5	1585.2
20°	1565.2	1562.7	1560.3	1557.1	1553.2	1549.2	1545.2	1541.2
22.5°	1522.1	1518.4	1514.8	1511.3	1508.0	1504.8	1501.6	1498.3
25°	1452.4	1447.3	1442.1	1438.0	1434.9	1431.8	1428.7	1425.7
27.5°	1381.6	1375.1	1368.7	1363.3	1358.9	1354.5	1350.1	1345.7
30°	1330.7	1323.1	1315.4	1309.2	1304.2	1299.4	1294.5	1289.6
32.5°	1278.8	1269.9	1261.0	1254.3	1249.7	1245.0	1240.4	1235.7
35°	1201.4	1191.1	1180.7	1172.8	1167.3	1161.7	1156.2	1150.7
37.5°	1118.4	1106.8	1095.3	1086.7	1081.2	1075.6	1070.2	1064.7
40°	1063.2	1050.4	1037.6	1028.4	1022.9	1017.4	1011.9	1006.4
42.5°	1008.8	995.7	982.7	973.3	967.5	961.8	956.1	950.3
45°	925.6	910.6	895.6	885.4	879.9	874.4	868.9	863.4
47.5°	841.7	826.2	810.7	799.9	793.8	787.8	781.7	775.7
50°	786.1	770.9	755.5	745.0	739.3	733.4	727.6	721.8
52.5°	730.6	715.1	699.6	688.8	682.8	676.7	670.6	664.6
55°	648.8	632.9	617.0	606.1	600.4	594.5	588.8	582.9
57.5°	568.9	552.7	536.6	526.3	521.9	517.5	513.1	508.7
60°	515.4	499.6	483.6	473.3	468.4	463.5	458.6	453.7
62.5°	462.9	448.2	433.5	424.2	420.3	416.5	412.5	408.6
65°	387.5	374.4	361.3	352.8	349.2	345.5	341.9	338.2
67.5°	318.4	307.0	295.8	288.1	284.0	280.0	276.0	271.9
70°	271.3	261.2	251.2	244.6	241.5	238.5	235.4	232.4
72.5°	229.1	220.5	211.9	206.2	203.4	200.6	197.8	194.9
75°	168.8	161.8	154.7	150.3	148.5	146.6	144.8	143.0
77.5°	119.4	115.3	111.2	108.9	108.3	107.8	107.3	106.7
80°	91.7	90.7	89.8	89.2	88.9	88.6	88.3	88.0
82.5°	71.3	70.6	69.9	69.4	69.1	68.8	68.5	68.2
85°	41.4	40.8	40.2	39.9	39.9	39.9	39.9	39.9
87.5°	19.2	19.2	19.2	19.4	19.6	20.0	20.3	20.7
90°	21.5	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	20.8	22.0	23.2	23.8	23.8	23.9	24.0	24.1
95°	21.5	22.6	23.8	24.5	24.7	24.9	25.1	25.3
97.5°	23.2	23.4	23.5	23.7	23.8	24.0	24.2	24.5
100°	31.8	28.5	25.2	23.7	23.8	24.0	24.2	24.5
102.5°	113.8	78.3	42.7	25.0	25.0	25.1	25.1	25.1
105°	275.7	277.4	279.1	276.6	269.6	262.6	255.6	248.7
107.5°	341.0	341.9	342.8	343.5	344.3	345.0	345.8	346.5
110°	385.5	385.9	386.2	386.8	387.4	387.9	388.5	389.1





TEST NUMBER: P333105-935

CATALOG NUMBER: S124RDIW-S1195D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.5	428.4	428.3	428.7	429.5	430.2	430.9	431.6
115°	492.8	493.2	493.5	493.8	493.8	493.8	493.8	493.8
117.5°	557.4	557.4	557.3	557.2	557.2	557.1	557.0	556.9
120°	597.4	597.9	598.2	598.2	597.9	597.4	597.1	596.7
122.5°	637.0	637.1	637.4	637.3	637.0	636.5	636.2	635.8
125°	692.1	692.7	693.2	693.6	693.8	694.0	694.2	694.4
127.5°	746.8	746.7	746.6	746.5	746.3	746.1	746.0	745.9
130°	780.2	780.5	780.7	780.8	780.8	780.8	780.8	780.8
132.5°	813.0	813.3	813.5	813.5	813.3	813.1	813.0	812.9
135°	858.3	858.7	859.1	859.5	859.9	860.2	860.7	861.0
137.5°	901.6	902.1	902.5	902.7	902.5	902.4	902.3	902.2
140°	928.5	929.0	929.6	930.1	930.2	930.4	930.6	930.8
142.5°	953.3	953.7	954.2	954.3	954.4	954.4	954.5	954.5
145°	988.8	988.9	989.1	989.5	989.8	990.2	990.6	991.0
147.5°	1019.9	1020.0	1020.2	1020.4	1020.6	1020.8	1021.0	1021.1
150°	1039.8	1039.8	1039.8	1039.9	1040.1	1040.3	1040.5	1040.7
152.5°	1057.2	1057.5	1057.8	1057.9	1057.8	1057.7	1057.6	1057.5
155°	1080.6	1081.4	1082.2	1082.3	1081.7	1081.2	1080.6	1080.0
157.5°	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8
160°	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4
162.5°	1124.1	1125.3	1126.4	1126.4	1125.1	1123.8	1122.5	1121.1
165°	1138.9	1140.5	1142.0	1141.9	1140.1	1138.4	1136.7	1134.9
167.5°	1149.7	1151.4	1153.1	1153.0	1151.1	1149.1	1147.2	1145.2
170°	1156.3	1157.9	1159.4	1159.3	1157.3	1155.4	1153.4	1151.5
172.5°	1160.5	1162.1	1163.6	1163.4	1161.2	1159.2	1157.1	1154.9
175°	1165.4	1167.2	1169.0	1168.6	1166.3	1164.0	1161.7	1159.3
177.5°	1167.4	1168.6	1169.9	1169.6	1167.7	1165.9	1164.0	1162.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3

(END OF REPORT)