

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333034-830

Luminaire Tested: **S124RDIW-S350D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333034-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6450.0 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333034-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333034-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P333034-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	0.8
10°-20°	152.6	2.4
20°-30°	220.4	3.4
30°-40°	249.8	3.9
40°-50°	241.2	3.7
50°-60°	200.6	3.1
60°-70°	138.5	2.1
70°-80°	70.2	1.1
80°-90°	23.5	0.4
90°-100°	121.2	1.9
100°-110°	359.1	5.6
110°-120°	609.4	9.4
120°-130°	803.6	12.5
130°-140°	902.4	14.0
140°-150°	886.8	13.7
150°-160°	745.9	11.6
160°-170°	496.2	7.7
170°-180°	173.8	2.7
0°-30°	427.8	6.6
0°-40°	677.6	10.5
0°-60°	1119.4	17.4
0°-90°	1351.7	21.0
90°-120°	1089.7	16.9
90°-150°	3682.5	57.1
90°-180°	5098.0	79.0
0°-180°	6450.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	4	20	31	40	43	7
95°	85	98	108	112	112	95
105°	331	333	338	342	347	351
115°	620	619	617	615	614	611
125°	902	902	901	898	895	804
135°	1164	1172	1172	1170	1165	900
145°	1414	1420	1421	1420	1416	885
155°	1620	1620	1619	1624	1619	745
165°	1764	1760	1757	1764	1759	497
175°	1835	1828	1826	1835	1826	174
180°	1838	1838	1838	1838	1838	



TEST NUMBER: P333034-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	9.0	9.1	9.1	9.2	9.3	9.5	10.0	10.4	10.8	11.2	11.6
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	30.4	34.4	38.4	42.3	46.4	49.2	51.0	52.8	54.5	56.3	57.4
95°	85.3	88.1	91.0	93.8	96.6	99.2	101.4	103.6	105.8	108.0	109.0
97.5°	148.9	151.2	153.4	155.8	158.1	160.5	163.1	165.6	168.2	170.8	171.9
100°	199.0	200.2	201.5	202.7	204.1	206.0	209.0	211.8	214.6	217.4	218.1
102.5°	251.3	251.8	252.3	252.8	253.3	254.9	257.4	260.0	262.6	265.2	266.1
105°	331.1	331.5	331.8	332.1	332.4	333.2	334.4	335.7	337.0	338.3	339.2
107.5°	415.0	415.4	415.8	416.1	416.5	416.8	417.0	417.2	417.4	417.5	418.4
110°	471.8	472.5	473.1	473.7	474.4	474.6	474.2	473.9	473.5	473.3	472.6



TEST NUMBER: P333034-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.9	531.1	531.2	531.3	531.5	531.2	530.7	530.1	529.5	529.0	528.9
115°	619.6	619.6	619.6	619.6	619.6	619.3	618.7	618.0	617.5	616.8	616.5
117.5°	703.2	703.4	703.7	704.0	704.3	704.2	703.7	703.2	702.8	702.4	701.3
120°	758.9	760.2	761.5	762.7	763.9	764.1	763.2	762.2	761.3	760.3	758.7
122.5°	816.9	817.4	817.9	818.4	818.9	819.0	818.5	818.0	817.7	817.2	816.1
125°	902.5	902.5	902.5	902.5	902.5	902.3	902.0	901.6	901.4	901.1	900.4
127.5°	980.1	981.0	981.9	982.9	983.8	984.1	983.5	983.1	982.6	982.0	981.4
130°	1034.6	1035.6	1036.5	1037.5	1038.4	1038.9	1038.9	1038.9	1038.9	1038.9	1038.3
132.5°	1090.3	1091.1	1091.7	1092.4	1093.2	1093.3	1093.1	1092.9	1092.6	1092.3	1091.7
135°	1163.9	1165.8	1167.7	1169.7	1171.6	1172.5	1172.5	1172.5	1172.5	1172.5	1171.9
137.5°	1244.2	1245.0	1245.9	1246.8	1247.6	1248.4	1248.9	1249.3	1249.9	1250.4	1249.5
140°	1297.6	1298.2	1298.8	1299.5	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0
142.5°	1346.4	1347.1	1347.7	1348.3	1349.0	1349.2	1348.9	1348.7	1348.4	1348.1	1348.1
145°	1414.1	1415.3	1416.6	1417.9	1419.2	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9
147.5°	1481.2	1482.7	1484.2	1485.7	1487.2	1487.9	1487.6	1487.3	1487.1	1486.9	1486.6
150°	1522.1	1523.3	1524.7	1525.9	1527.2	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8
152.5°	1560.8	1561.5	1562.3	1563.0	1563.8	1564.3	1564.5	1564.8	1565.1	1565.3	1566.0
155°	1620.1	1620.1	1620.1	1620.1	1620.1	1620.0	1619.7	1619.4	1619.1	1618.7	1620.0
157.5°	1670.2	1669.6	1669.1	1668.5	1667.9	1667.6	1667.5	1667.5	1667.5	1667.4	1668.3
160°	1699.8	1699.4	1699.1	1698.8	1698.5	1698.2	1697.9	1697.5	1697.2	1697.0	1697.9
162.5°	1727.0	1726.3	1725.4	1724.6	1723.7	1723.2	1722.9	1722.6	1722.2	1721.9	1723.6
165°	1763.7	1762.7	1761.8	1760.9	1759.9	1759.2	1758.5	1757.8	1757.3	1756.6	1758.5
167.5°	1791.9	1790.5	1789.2	1787.9	1786.6	1785.9	1786.0	1786.0	1786.1	1786.2	1788.1
170°	1807.8	1806.2	1804.6	1803.0	1801.5	1800.8	1801.1	1801.5	1801.8	1802.0	1803.9
172.5°	1819.1	1817.8	1816.5	1815.1	1813.8	1813.2	1813.3	1813.4	1813.4	1813.5	1815.6
175°	1834.8	1833.2	1831.6	1830.0	1828.4	1827.5	1827.2	1826.8	1826.6	1826.3	1828.4
177.5°	1839.8	1838.6	1837.4	1836.1	1834.8	1834.2	1834.2	1834.2	1834.2	1834.2	1836.0
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333034-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	11.9	12.2	12.4	12.7	12.9	13.1	13.3	13.5
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	58.5	59.7	60.8	61.5	61.9	62.3	62.7	63.1
95°	109.9	110.8	111.8	112.3	112.3	112.3	112.3	112.3
97.5°	173.1	174.3	175.4	176.0	176.0	176.0	176.0	176.0
100°	218.7	219.3	220.0	220.3	220.3	220.3	220.3	220.3
102.5°	266.9	267.9	268.7	269.3	269.6	269.8	270.0	270.3
105°	340.2	341.1	342.0	343.0	343.9	344.9	345.8	346.8
107.5°	419.3	420.2	421.1	421.5	421.4	421.4	421.3	421.2
110°	472.0	471.4	470.7	470.9	471.8	472.8	473.7	474.7



TEST NUMBER: P333034-830

CATALOG NUMBER: S124RDIW-S350D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	528.7	528.6	528.5	528.5	528.7	528.9	529.0	529.2
115°	616.1	615.9	615.6	615.2	614.9	614.6	614.3	614.0
117.5°	700.2	699.2	698.0	697.2	696.5	696.0	695.3	694.7
120°	757.1	755.6	754.0	753.6	754.2	754.8	755.4	756.1
122.5°	815.0	814.0	812.9	811.8	810.7	809.5	808.4	807.3
125°	899.8	899.2	898.5	897.9	897.2	896.6	896.0	895.3
127.5°	980.8	980.1	979.5	978.9	978.5	978.0	977.4	976.9
130°	1037.6	1037.0	1036.3	1035.4	1034.2	1032.9	1031.6	1030.4
132.5°	1091.1	1090.4	1089.8	1089.2	1088.7	1088.3	1087.7	1087.2
135°	1171.2	1170.6	1170.0	1169.1	1168.2	1167.2	1166.3	1165.4
137.5°	1248.8	1247.9	1247.1	1246.8	1247.0	1247.2	1247.4	1247.5
140°	1299.8	1299.5	1299.1	1298.8	1298.5	1298.2	1297.9	1297.6
142.5°	1348.0	1347.9	1347.9	1347.8	1347.7	1347.7	1347.6	1347.6
145°	1420.6	1420.2	1419.9	1419.3	1418.3	1417.4	1416.5	1415.5
147.5°	1486.4	1486.1	1485.8	1485.5	1485.3	1485.0	1484.6	1484.3
150°	1527.8	1527.8	1527.8	1527.7	1527.3	1527.0	1526.7	1526.4
152.5°	1566.8	1567.5	1568.3	1568.3	1567.4	1566.7	1565.8	1565.0
155°	1621.3	1622.5	1623.8	1623.8	1622.5	1621.3	1620.0	1618.7
157.5°	1669.2	1670.2	1671.1	1671.0	1670.0	1669.0	1667.8	1666.8
160°	1698.8	1699.8	1700.7	1700.3	1698.8	1697.2	1695.6	1694.0
162.5°	1725.3	1727.0	1728.7	1728.8	1727.2	1725.7	1724.1	1722.5
165°	1760.4	1762.3	1764.2	1764.5	1763.2	1762.0	1760.7	1759.4
167.5°	1790.0	1791.9	1793.8	1793.8	1791.8	1789.8	1787.8	1785.8
170°	1805.9	1807.8	1809.7	1809.5	1807.3	1805.1	1802.9	1800.6
172.5°	1817.8	1819.9	1822.0	1822.0	1819.8	1817.6	1815.3	1813.2
175°	1830.7	1832.9	1835.1	1835.1	1832.9	1830.7	1828.4	1826.3
177.5°	1837.8	1839.5	1841.3	1841.2	1839.1	1837.1	1835.1	1833.1
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6

(END OF REPORT)