

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333109-935

Luminaire Tested: **S124RDIW-S1195D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333109-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1340U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8771.5 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333109-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333109-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	75	70	66	63	60	56	53	50	48	42	41	39	34
3	81	72	65	59	74	67	60	55	56	52	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	38	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14495	14495	14495
5°	14528	14350	14439
10°	14437	14178	14178
15°	14271	13881	13778
20°	14044	13489	13241
25°	13752	13030	12699
30°	13470	12547	12021
35°	13157	12046	11340
40°	12779	11475	10606
45°	12432	10909	9857
50°	12036	10257	9065
55°	11610	9578	8204
60°	11144	8835	7325
65°	10714	7904	6460
70°	10093	6878	5486
75°	9304	5705	4460
80°	8117	4347	4091
85°	6873	3946	3696



TEST NUMBER: P333109-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.7	1.9
10°-20°	470.4	5.4
20°-30°	679.2	7.7
30°-40°	769.9	8.8
40°-50°	743.4	8.5
50°-60°	618.2	7.0
60°-70°	426.9	4.9
70°-80°	216.4	2.5
80°-90°	59.8	0.7
90°-100°	51.1	0.6
100°-110°	325.6	3.7
110°-120°	622.9	7.1
120°-130°	790.7	9.0
130°-140°	846.0	9.6
140°-150°	791.1	9.0
150°-160°	638.0	7.3
160°-170°	411.5	4.7
170°-180°	141.8	1.6
0°-30°	1318.2	15.0
0°-40°	2088.1	23.8
0°-60°	3449.7	39.3
0°-90°	4152.8	47.3
90°-120°	999.5	11.4
90°-150°	3427.4	39.1
90°-180°	4619.0	52.7
0°-180°	8771.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1796	1796	1796	1796	1796	
5°	1793	1787	1771	1784	1782	170
15°	1708	1694	1661	1658	1648	481
25°	1544	1517	1463	1440	1426	711
35°	1335	1290	1222	1177	1151	834
45°	1089	1036	956	890	863	839
55°	825	768	680	612	583	738
65°	561	500	414	357	338	554
75°	298	247	183	152	143	315
85°	74	48	43	40	40	84
90°	3	15	24	31	34	6
95°	61	26	24	31	32	79
105°	336	343	348	356	318	352
115°	628	631	630	632	632	617
125°	882	886	884	888	889	787
135°	1094	1094	1098	1100	1102	843
145°	1262	1265	1265	1266	1269	788
155°	1384	1385	1382	1385	1383	638
165°	1460	1454	1454	1462	1453	412
175°	1493	1487	1488	1496	1484	142
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333109-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1799.9	1799.0	1798.0	1797.0	1796.0	1794.2	1791.6	1788.8	1786.1	1783.5	1786.1
5°	1792.8	1791.6	1790.4	1789.2	1788.0	1785.5	1781.8	1778.1	1774.5	1770.8	1773.8
7.5°	1776.6	1775.3	1774.0	1772.7	1771.4	1768.4	1763.7	1758.9	1754.1	1749.4	1751.4
10°	1761.2	1759.6	1758.2	1756.6	1755.1	1751.5	1746.1	1740.6	1735.1	1729.6	1730.8
12.5°	1741.4	1739.7	1737.8	1736.0	1734.3	1730.2	1723.7	1717.3	1710.7	1704.3	1705.0
15°	1707.5	1704.8	1702.1	1699.4	1696.6	1691.3	1683.8	1676.1	1668.4	1660.8	1660.2
17.5°	1666.6	1662.6	1658.6	1654.7	1650.7	1644.2	1635.0	1625.8	1616.6	1607.5	1605.8
20°	1634.7	1630.7	1626.8	1622.8	1618.9	1611.6	1601.3	1590.9	1580.5	1570.1	1567.6
22.5°	1599.5	1595.1	1590.6	1586.1	1581.7	1573.9	1562.7	1551.6	1540.5	1529.4	1525.7
25°	1543.9	1538.4	1532.9	1527.5	1522.0	1512.9	1500.5	1487.9	1475.4	1462.8	1457.7
27.5°	1485.7	1478.8	1471.9	1465.0	1458.0	1447.9	1434.5	1421.2	1407.7	1394.4	1387.9
30°	1445.0	1437.4	1429.7	1422.0	1414.5	1403.4	1389.1	1374.7	1360.4	1346.0	1338.3
32.5°	1402.1	1393.4	1384.8	1376.2	1367.6	1355.9	1341.0	1326.2	1311.3	1296.5	1287.6
35°	1335.0	1325.2	1315.4	1305.6	1295.9	1283.3	1268.1	1252.8	1237.5	1222.3	1211.9
37.5°	1263.3	1253.1	1243.0	1233.0	1222.9	1209.4	1192.5	1175.5	1158.6	1141.7	1130.1
40°	1212.6	1202.6	1192.5	1182.4	1172.3	1158.6	1141.2	1123.7	1106.3	1088.9	1076.1
42.5°	1164.2	1153.7	1143.1	1132.5	1122.0	1107.6	1089.4	1071.3	1053.2	1035.0	1021.9
45°	1088.9	1077.5	1066.3	1055.0	1043.7	1028.8	1010.6	992.2	973.9	955.5	940.6
47.5°	1011.1	999.4	987.7	976.0	964.4	949.0	930.0	910.9	891.8	872.8	857.2
50°	958.3	946.3	934.4	922.6	910.6	894.8	875.3	855.7	836.2	816.7	801.4
52.5°	904.4	892.7	881.1	869.4	857.7	841.8	821.8	801.8	781.7	761.6	746.1
55°	824.9	812.7	800.5	788.2	776.0	760.0	740.1	720.3	700.4	680.5	664.7
57.5°	746.2	733.6	720.8	708.2	695.4	679.3	659.8	640.2	620.6	601.1	585.0
60°	690.2	678.0	665.7	653.5	641.3	625.4	605.9	586.3	566.7	547.2	531.3
62.5°	639.6	626.9	614.2	601.5	588.8	572.4	552.3	532.3	512.2	492.2	477.5
65°	560.9	547.8	534.7	521.5	508.4	492.1	472.5	453.0	433.4	413.8	400.7
67.5°	479.2	466.7	454.1	441.5	429.0	413.5	395.4	377.3	359.1	341.0	329.7
70°	427.6	414.7	401.9	389.1	376.3	361.1	343.7	326.3	308.9	291.4	281.4
72.5°	372.6	361.0	349.4	337.8	326.1	312.1	295.7	279.2	262.8	246.3	237.7
75°	298.3	287.1	275.7	264.4	253.1	240.3	225.9	211.5	197.3	182.9	175.8
77.5°	223.0	213.4	203.8	194.2	184.6	174.0	162.4	150.8	139.2	127.6	123.5
80°	174.6	165.7	156.9	148.0	139.1	130.2	121.0	111.8	102.6	93.5	92.6
82.5°	132.9	124.7	116.6	108.4	100.3	93.6	88.3	83.1	77.8	72.6	71.9
85°	74.2	68.1	62.0	55.9	49.8	46.3	45.4	44.4	43.6	42.6	42.0
87.5°	26.0	24.5	23.2	21.7	20.3	19.7	19.9	20.0	20.1	20.3	20.4
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	14.0	14.2	14.4	14.6	14.6	15.8	17.7	19.7	21.7	23.7	25.1
95°	61.4	53.0	44.5	36.1	27.6	23.6	23.8	24.1	24.3	24.5	26.1
97.5°	130.4	135.7	140.9	146.2	151.4	140.3	112.5	84.9	57.2	29.4	29.6
100°	183.1	187.6	192.1	196.6	201.0	186.1	151.9	117.6	83.3	49.2	44.9
102.5°	242.1	245.4	248.7	251.9	255.2	254.6	250.1	245.7	241.3	236.8	191.2
105°	336.1	337.6	339.1	340.6	342.1	343.5	344.7	345.9	347.2	348.4	350.7
107.5°	423.4	424.2	425.0	425.7	426.5	427.7	429.4	431.0	432.7	434.5	435.5
110°	482.4	483.2	484.0	484.7	485.4	486.6	488.0	489.5	491.0	492.5	493.0



TEST NUMBER: P333109-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.6	541.0	542.3	543.6	545.0	546.0	546.7	547.4	548.1	548.8	548.7
115°	627.6	628.4	629.1	629.8	630.6	630.9	630.6	630.3	630.1	629.8	630.3
117.5°	706.9	707.9	708.9	709.9	710.8	711.6	712.2	712.7	713.3	713.9	713.8
120°	760.5	761.5	762.5	763.5	764.5	764.8	764.7	764.4	764.1	763.9	764.4
122.5°	810.5	811.1	811.8	812.4	813.0	813.4	813.7	814.1	814.4	814.8	815.1
125°	882.3	883.2	884.2	885.2	886.2	886.5	886.0	885.5	884.9	884.5	885.2
127.5°	950.1	950.4	950.6	950.9	951.1	951.8	953.0	954.1	955.3	956.4	956.2
130°	993.9	994.2	994.5	994.6	994.9	995.4	996.2	996.9	997.6	998.4	998.7
132.5°	1034.1	1034.6	1035.0	1035.4	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6
135°	1094.4	1094.2	1093.9	1093.7	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3
137.5°	1147.8	1147.9	1148.0	1148.1	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7
140°	1182.7	1183.2	1183.6	1184.1	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8
142.5°	1213.9	1214.8	1215.7	1216.6	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9
145°	1262.0	1262.7	1263.4	1264.2	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6
147.5°	1300.1	1301.5	1303.0	1304.3	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4
150°	1327.8	1328.9	1329.8	1330.8	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2
152.5°	1351.1	1351.9	1352.6	1353.4	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1
155°	1383.7	1383.9	1384.1	1384.4	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4
157.5°	1411.2	1411.0	1410.8	1410.7	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0
160°	1427.2	1426.5	1425.7	1425.0	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3
162.5°	1441.5	1440.5	1439.7	1438.7	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6
165°	1459.7	1458.4	1457.2	1455.9	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0
167.5°	1473.9	1472.7	1471.4	1470.1	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6
170°	1482.0	1480.5	1478.9	1477.5	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3
172.5°	1487.3	1485.8	1484.4	1482.8	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7
175°	1493.1	1491.6	1490.1	1488.7	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8
177.5°	1495.8	1494.4	1493.0	1491.6	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333109-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5	1795.5
2.5°	1788.8	1791.6	1794.2	1795.4	1795.2	1794.9	1794.7	1794.5
5°	1776.9	1779.9	1783.0	1784.3	1783.6	1783.0	1782.4	1781.8
7.5°	1753.3	1755.2	1757.2	1757.6	1756.7	1755.8	1754.7	1753.8
10°	1732.0	1733.2	1734.5	1734.5	1733.2	1732.0	1730.8	1729.6
12.5°	1705.7	1706.5	1707.2	1706.7	1705.0	1703.3	1701.6	1699.9
15°	1659.6	1659.0	1658.4	1657.0	1654.8	1652.7	1650.6	1648.5
17.5°	1604.0	1602.3	1600.6	1598.2	1594.9	1591.6	1588.5	1585.2
20°	1565.2	1562.7	1560.3	1557.1	1553.2	1549.2	1545.2	1541.2
22.5°	1522.1	1518.4	1514.8	1511.3	1508.0	1504.8	1501.6	1498.3
25°	1452.4	1447.3	1442.1	1438.0	1434.9	1431.8	1428.7	1425.7
27.5°	1381.6	1375.1	1368.7	1363.3	1358.9	1354.5	1350.1	1345.7
30°	1330.7	1323.1	1315.4	1309.2	1304.2	1299.4	1294.5	1289.6
32.5°	1278.8	1269.9	1261.0	1254.3	1249.7	1245.0	1240.4	1235.7
35°	1201.4	1191.1	1180.7	1172.8	1167.3	1161.7	1156.2	1150.7
37.5°	1118.4	1106.8	1095.3	1086.7	1081.2	1075.6	1070.2	1064.7
40°	1063.2	1050.4	1037.6	1028.4	1022.9	1017.4	1011.9	1006.4
42.5°	1008.8	995.7	982.7	973.3	967.5	961.8	956.1	950.3
45°	925.6	910.6	895.6	885.4	879.9	874.4	868.9	863.4
47.5°	841.7	826.2	810.7	799.9	793.8	787.8	781.7	775.7
50°	786.1	770.9	755.5	745.0	739.3	733.4	727.6	721.8
52.5°	730.6	715.1	699.6	688.8	682.8	676.7	670.6	664.6
55°	648.8	632.9	617.0	606.1	600.4	594.5	588.8	582.9
57.5°	568.9	552.7	536.6	526.3	521.9	517.5	513.1	508.7
60°	515.4	499.6	483.6	473.3	468.4	463.5	458.6	453.7
62.5°	462.9	448.2	433.5	424.2	420.3	416.5	412.5	408.6
65°	387.5	374.4	361.3	352.8	349.2	345.5	341.9	338.2
67.5°	318.4	307.0	295.8	288.1	284.0	280.0	276.0	271.9
70°	271.3	261.2	251.2	244.6	241.5	238.5	235.4	232.4
72.5°	229.1	220.5	211.9	206.2	203.4	200.6	197.8	194.9
75°	168.8	161.8	154.7	150.3	148.5	146.6	144.8	143.0
77.5°	119.4	115.3	111.2	108.9	108.3	107.8	107.3	106.7
80°	91.7	90.7	89.8	89.2	88.9	88.6	88.3	88.0
82.5°	71.3	70.6	69.9	69.4	69.1	68.8	68.5	68.2
85°	41.4	40.8	40.2	39.9	39.9	39.9	39.9	39.9
87.5°	20.4	20.5	20.5	20.8	21.1	21.4	21.8	22.1
90°	27.6	29.0	30.6	31.5	32.0	32.5	33.0	33.5
92.5°	26.7	28.2	29.6	30.4	30.6	30.7	30.7	30.8
95°	27.6	29.0	30.6	31.4	31.6	31.9	32.1	32.4
97.5°	29.8	30.0	30.0	30.3	30.6	30.7	31.0	31.3
100°	40.7	36.5	32.3	30.3	30.6	30.7	31.0	31.3
102.5°	145.8	100.2	54.7	31.9	32.0	32.0	32.1	32.2
105°	352.9	355.2	357.4	354.0	345.1	336.1	327.2	318.3
107.5°	436.6	437.7	438.8	439.8	440.7	441.7	442.6	443.6
110°	493.5	494.0	494.5	495.1	495.8	496.6	497.3	498.1



TEST NUMBER: P333109-935

CATALOG NUMBER: S124RDIW-S1195D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	548.5	548.5	548.4	548.8	549.7	550.7	551.6	552.6
115°	630.9	631.4	631.8	632.1	632.1	632.1	632.1	632.1
117.5°	713.6	713.5	713.4	713.3	713.3	713.2	713.1	712.9
120°	764.8	765.3	765.9	765.9	765.3	764.8	764.4	763.9
122.5°	815.4	815.7	816.0	815.9	815.4	814.9	814.4	813.9
125°	886.0	886.7	887.4	887.9	888.2	888.5	888.7	889.0
127.5°	956.1	956.0	955.8	955.6	955.5	955.2	955.0	954.8
130°	998.8	999.1	999.4	999.5	999.5	999.5	999.5	999.5
132.5°	1040.9	1041.1	1041.4	1041.4	1041.2	1041.0	1040.8	1040.6
135°	1098.8	1099.2	1099.8	1100.3	1100.8	1101.2	1101.7	1102.3
137.5°	1154.3	1154.8	1155.4	1155.5	1155.4	1155.3	1155.1	1154.9
140°	1188.6	1189.4	1190.1	1190.6	1190.8	1191.1	1191.4	1191.6
142.5°	1220.4	1220.9	1221.5	1221.8	1221.8	1221.8	1221.9	1221.9
145°	1265.8	1266.0	1266.3	1266.7	1267.1	1267.7	1268.2	1268.7
147.5°	1305.7	1305.9	1306.1	1306.3	1306.6	1306.8	1307.0	1307.3
150°	1331.2	1331.2	1331.2	1331.3	1331.5	1331.8	1332.1	1332.3
152.5°	1353.4	1353.8	1354.2	1354.4	1354.2	1354.0	1353.9	1353.8
155°	1383.5	1384.4	1385.4	1385.5	1384.8	1384.1	1383.3	1382.6
157.5°	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7
160°	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8
162.5°	1439.2	1440.6	1442.1	1442.0	1440.4	1438.6	1436.9	1435.3
165°	1458.0	1460.0	1462.0	1461.8	1459.7	1457.4	1455.2	1452.9
167.5°	1471.8	1473.9	1476.2	1476.0	1473.5	1471.0	1468.6	1466.1
170°	1480.3	1482.3	1484.3	1484.0	1481.6	1479.1	1476.6	1474.1
172.5°	1485.7	1487.7	1489.7	1489.4	1486.6	1483.9	1481.3	1478.6
175°	1492.0	1494.3	1496.5	1496.1	1493.1	1490.1	1487.1	1484.2
177.5°	1494.5	1496.1	1497.7	1497.3	1494.9	1492.5	1490.1	1487.7
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1

(END OF REPORT)