

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333017-830

Luminaire Tested: **S124RDIW-S350D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333017-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D470U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3114.5 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333017-830

CATALOG NUMBER: S124RDIW-S350D470U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333017-830

CATALOG NUMBER: S124RDIW-S350D470U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P333017-830

CATALOG NUMBER: S124RDIW-S350D470U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	1.8
10°-20°	152.6	4.9
20°-30°	220.4	7.1
30°-40°	249.8	8.0
40°-50°	241.2	7.7
50°-60°	200.6	6.4
60°-70°	138.5	4.4
70°-80°	70.2	2.3
80°-90°	19.7	0.6
90°-100°	19.5	0.6
100°-110°	124.6	4.0
110°-120°	238.3	7.7
120°-130°	302.4	9.7
130°-140°	323.6	10.4
140°-150°	302.6	9.7
150°-160°	244.0	7.8
160°-170°	157.4	5.1
170°-180°	54.2	1.7
0°-30°	427.8	13.7
0°-40°	677.6	21.8
0°-60°	1119.4	35.9
0°-90°	1347.8	43.3
90°-120°	382.4	12.3
90°-150°	1311.0	42.1
90°-180°	1767.0	56.7
0°-180°	3114.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	1	6	9	12	13	2
95°	24	10	9	12	12	30
105°	129	131	133	136	122	135
115°	240	241	241	242	242	236
125°	337	339	338	340	340	301
135°	419	418	420	421	422	322
145°	483	484	484	484	485	301
155°	529	530	528	530	529	244
165°	558	556	556	559	556	158
175°	571	569	569	572	568	54
180°	571	571	571	571	571	



TEST NUMBER: P333017-830

CATALOG NUMBER: S124RDIW-S350D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.5	8.0	7.6	7.2	6.8	6.6	6.7	6.7	6.8	6.9	6.9
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	5.4	5.5	5.5	5.6	5.7	6.0	6.8	7.5	8.3	9.0	9.6
95°	23.5	20.3	17.1	13.9	10.6	9.0	9.1	9.2	9.3	9.4	10.0
97.5°	49.9	51.9	53.9	55.9	58.0	53.6	43.1	32.4	21.9	11.3	11.3
100°	70.0	71.7	73.5	75.2	76.9	71.2	58.1	45.0	31.9	18.8	17.2
102.5°	92.7	93.9	95.1	96.3	97.6	97.4	95.7	94.0	92.3	90.6	73.1
105°	128.6	129.1	129.7	130.3	130.8	131.4	131.9	132.3	132.8	133.3	134.1
107.5°	162.0	162.3	162.6	162.9	163.2	163.6	164.2	164.9	165.5	166.2	166.5
110°	184.5	184.8	185.1	185.4	185.7	186.1	186.6	187.3	187.8	188.4	188.6



TEST NUMBER: P333017-830

CATALOG NUMBER: S124RDIW-S350D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	206.4	206.9	207.5	207.9	208.5	208.9	209.2	209.3	209.6	209.9	209.9
115°	240.1	240.3	240.6	240.9	241.2	241.3	241.2	241.1	241.0	240.9	241.1
117.5°	270.4	270.8	271.2	271.5	271.9	272.2	272.4	272.6	272.9	273.1	273.0
120°	290.9	291.2	291.6	292.0	292.4	292.6	292.5	292.4	292.3	292.2	292.4
122.5°	310.0	310.3	310.5	310.8	310.9	311.1	311.2	311.4	311.5	311.7	311.8
125°	337.4	337.8	338.2	338.6	338.9	339.0	338.8	338.7	338.5	338.3	338.6
127.5°	363.4	363.5	363.6	363.7	363.8	364.1	364.5	365.0	365.4	365.8	365.8
130°	380.1	380.2	380.4	380.5	380.6	380.8	381.1	381.4	381.6	381.9	382.0
132.5°	395.6	395.7	395.9	396.1	396.2	396.5	396.9	397.2	397.6	397.9	398.0
135°	418.6	418.5	418.4	418.3	418.2	418.4	418.8	419.1	419.5	419.9	420.1
137.5°	439.0	439.0	439.1	439.1	439.2	439.4	439.8	440.3	440.6	441.1	441.3
140°	452.3	452.5	452.7	452.9	453.1	453.3	453.5	453.7	453.9	454.1	454.4
142.5°	464.3	464.7	465.1	465.3	465.7	465.9	466.0	466.2	466.3	466.4	466.6
145°	482.7	483.0	483.2	483.5	483.8	484.0	484.0	484.0	484.0	484.0	484.1
147.5°	497.3	497.9	498.3	498.9	499.5	499.6	499.5	499.5	499.4	499.3	499.4
150°	507.9	508.3	508.7	509.1	509.4	509.5	509.4	509.3	509.3	509.2	509.2
152.5°	516.8	517.1	517.4	517.6	518.0	518.0	517.9	517.7	517.6	517.4	517.6
155°	529.2	529.3	529.4	529.5	529.6	529.5	529.2	529.0	528.7	528.4	528.8
157.5°	539.8	539.7	539.6	539.6	539.5	539.3	539.0	538.7	538.4	538.1	538.6
160°	545.9	545.6	545.4	545.1	544.8	544.6	544.5	544.4	544.3	544.2	544.8
162.5°	551.4	551.0	550.6	550.3	550.0	549.7	549.6	549.5	549.4	549.3	549.9
165°	558.3	557.8	557.3	556.9	556.4	556.2	556.2	556.2	556.2	556.2	556.9
167.5°	563.7	563.3	562.8	562.3	561.8	561.5	561.5	561.4	561.4	561.3	562.1
170°	566.8	566.3	565.7	565.1	564.6	564.3	564.4	564.5	564.6	564.7	565.4
172.5°	568.9	568.4	567.8	567.2	566.7	566.4	566.5	566.6	566.7	566.8	567.5
175°	571.1	570.5	570.0	569.4	568.8	568.6	568.7	568.8	568.9	569.0	569.9
177.5°	572.1	571.7	571.1	570.5	570.0	569.9	570.0	570.1	570.2	570.4	571.0
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333017-830

CATALOG NUMBER: S124RDIW-S350D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	7.0	7.0	7.0	7.1	7.2	7.4	7.4	7.5
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	10.2	10.7	11.3	11.6	11.7	11.7	11.8	11.8
95°	10.6	11.1	11.7	12.0	12.1	12.2	12.3	12.3
97.5°	11.4	11.4	11.5	11.6	11.7	11.8	11.9	12.0
100°	15.6	13.9	12.3	11.6	11.7	11.8	11.9	12.0
102.5°	55.7	38.4	20.9	12.3	12.3	12.3	12.3	12.3
105°	135.0	135.8	136.7	135.4	132.0	128.6	125.2	121.8
107.5°	167.0	167.4	167.9	168.2	168.6	168.9	169.3	169.7
110°	188.8	189.0	189.2	189.4	189.6	189.9	190.2	190.5



TEST NUMBER: P333017-830

CATALOG NUMBER: S124RDIW-S350D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	209.8	209.8	209.7	209.9	210.3	210.7	211.0	211.3
115°	241.3	241.5	241.7	241.8	241.8	241.8	241.8	241.8
117.5°	273.0	273.0	272.9	272.9	272.8	272.8	272.8	272.7
120°	292.6	292.8	292.9	292.9	292.8	292.6	292.4	292.2
122.5°	311.9	312.0	312.1	312.1	311.9	311.7	311.5	311.3
125°	338.8	339.1	339.4	339.6	339.7	339.8	339.9	340.0
127.5°	365.7	365.6	365.6	365.5	365.4	365.3	365.3	365.2
130°	382.1	382.2	382.3	382.3	382.3	382.3	382.3	382.3
132.5°	398.1	398.2	398.3	398.3	398.2	398.2	398.1	398.0
135°	420.3	420.5	420.7	420.8	421.0	421.2	421.4	421.6
137.5°	441.5	441.7	442.0	442.0	442.0	441.9	441.9	441.8
140°	454.7	455.0	455.2	455.4	455.5	455.6	455.7	455.8
142.5°	466.7	467.0	467.2	467.3	467.3	467.4	467.4	467.4
145°	484.2	484.3	484.4	484.5	484.7	484.8	485.0	485.2
147.5°	499.5	499.5	499.5	499.6	499.7	499.8	499.9	500.0
150°	509.2	509.2	509.2	509.3	509.3	509.4	509.5	509.6
152.5°	517.6	517.8	518.0	518.0	518.0	517.9	517.8	517.8
155°	529.1	529.5	529.9	530.0	529.7	529.4	529.1	528.9
157.5°	539.0	539.5	540.0	540.0	539.5	539.0	538.6	538.1
160°	545.4	545.9	546.5	546.5	545.9	545.4	544.8	544.2
162.5°	550.4	551.0	551.6	551.6	550.9	550.3	549.6	549.0
165°	557.7	558.5	559.2	559.1	558.3	557.4	556.6	555.7
167.5°	563.0	563.8	564.7	564.6	563.6	562.7	561.8	560.8
170°	566.2	566.9	567.8	567.7	566.7	565.7	564.8	563.8
172.5°	568.3	569.0	569.8	569.7	568.6	567.6	566.6	565.5
175°	570.7	571.6	572.4	572.2	571.1	570.0	568.8	567.7
177.5°	571.7	572.2	572.9	572.7	571.8	570.9	570.0	569.1
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1

(END OF REPORT)