

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333019-830

Luminaire Tested: **S124RDIW-S350D770U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333019-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D770U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4295.7 lumens
Efficiency: N/A
Efficacy: 141.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33																												
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	34	28																												
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29	24																												
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21																												
4	72	62	54	48	65	56	49	45	45	40	37	35	32	29	26	24	22	18																												
5	66	55	47	42	59	50	43	38	40	36	32	31	28	25	23	21	19	16																												
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14																												
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	19	17	15	12																												
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11																												
9	48	37	29	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10																												
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	15	13	11	9																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4469	4469	4469	4469
5°	5185	4483	3963	4483
10°	6133	4464	3536	4464
15°	7084	4422	3039	4422
20°	7887	4365	2748	4365
25°	8143	4309	2551	4309
30°	7128	4242	2433	4242
35°	5549	4142	2361	4142
40°	4161	4027	2323	4027
45°	3286	3843	2302	3843
50°	2773	3631	2236	3631
55°	2417	3398	2115	3398
60°	2175	3155	1873	3155
65°	1918	2894	1612	2894
70°	1725	2622	1452	2622
75°	1447	2324	1238	2324
80°	1223	1980	1162	1980
85°	1028	1556	1028	1556



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	1.2
10°-20°	161.8	3.8
20°-30°	253.1	5.9
30°-40°	281.4	6.5
40°-50°	249.6	5.8
50°-60°	194.5	4.5
60°-70°	127.4	3.0
70°-80°	62.6	1.5
80°-90°	18.2	0.4
90°-100°	32.0	0.7
100°-110°	204.0	4.7
110°-120°	390.2	9.1
120°-130°	495.4	11.5
130°-140°	530.0	12.3
140°-150°	495.6	11.5
150°-160°	399.7	9.3
160°-170°	257.8	6.0
170°-180°	88.8	2.1
0°-30°	468.6	10.9
0°-40°	749.9	17.5
0°-60°	1194.1	27.8
0°-90°	1402.2	32.6
90°-120°	626.2	14.6
90°-150°	2147.2	50.0
90°-180°	2894.0	67.4
0°-180°	4295.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	554	554	554	554	554	
5°	640	553	489	553	640	65
15°	848	529	364	529	848	241
25°	914	484	286	484	914	406
35°	563	420	240	420	563	353
45°	288	337	202	337	288	228
55°	172	241	150	241	172	156
65°	100	152	84	152	100	101
75°	46	74	40	74	46	51
85°	11	17	11	17	11	13
90°	21	2	21	2	21	10
95°	20	38	20	38	20	16
105°	199	211	199	211	199	174
115°	396	393	396	393	396	392
125°	557	553	557	553	557	496
135°	690	686	690	686	690	532
145°	795	791	795	791	795	497
155°	866	867	866	867	866	399
165°	910	914	910	914	910	257
175°	930	935	930	935	930	89
180°	935	935	935	935	935	



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	584.0	585.6	584.0	583.8	582.0	581.5	580.8	578.4	574.2	571.7	572.2
5°	639.8	645.4	642.2	641.8	636.9	632.0	628.9	621.7	614.1	609.0	604.7
7.5°	704.3	707.5	705.5	702.4	694.5	689.9	682.7	673.4	659.7	649.3	639.8
10°	748.2	750.8	750.0	744.1	738.4	726.5	719.8	706.7	689.5	675.9	663.2
12.5°	791.4	794.2	786.4	786.6	775.6	766.3	755.7	739.1	719.3	701.8	685.9
15°	847.6	844.0	844.0	839.6	827.4	814.5	803.5	786.1	761.1	740.2	718.0
17.5°	891.7	893.0	891.2	880.6	871.0	857.6	837.5	817.3	794.1	765.9	743.4
20°	918.1	918.1	916.2	909.0	896.5	882.2	860.6	838.5	809.1	780.7	755.4
22.5°	928.9	929.5	927.2	921.3	910.1	896.2	877.7	855.3	824.9	793.1	761.6
25°	914.2	918.4	918.8	917.3	913.9	905.4	889.6	866.7	839.4	804.8	770.9
27.5°	839.2	844.6	849.3	857.1	867.3	872.6	873.4	861.7	837.9	804.6	770.5
30°	764.7	769.1	783.6	802.6	817.3	830.7	842.4	845.5	832.1	802.2	766.3
32.5°	681.8	688.0	702.5	722.8	747.3	770.1	796.1	809.4	809.0	791.1	757.9
35°	563.0	567.5	580.9	602.3	631.7	665.4	706.7	738.8	760.6	759.1	738.8
37.5°	454.1	459.1	472.6	490.4	519.0	560.6	600.6	644.9	685.2	707.9	701.2
40°	394.8	395.0	408.2	426.5	453.3	489.7	533.1	582.2	627.3	664.1	671.2
42.5°	348.1	348.1	356.8	376.5	395.8	430.0	471.6	520.3	573.1	615.6	634.4
45°	287.8	289.7	296.9	308.7	323.9	352.9	386.2	431.4	490.5	540.9	572.4
47.5°	243.6	246.7	251.2	260.8	272.9	292.2	319.7	360.4	408.5	463.9	508.7
50°	220.8	221.3	227.1	232.4	242.9	258.4	282.4	316.3	360.5	413.8	463.5
52.5°	201.2	201.1	204.6	211.4	219.9	231.9	251.4	282.2	321.4	369.2	420.6
55°	171.7	172.9	175.6	180.9	187.4	195.9	211.2	234.4	265.2	306.0	352.7
57.5°	149.4	150.0	152.0	154.3	160.2	166.5	178.0	194.1	220.0	253.4	296.9
60°	134.7	135.0	135.6	138.9	143.6	149.5	157.3	170.9	192.7	223.3	257.7
62.5°	120.5	120.8	121.9	124.3	128.0	132.0	140.2	151.1	169.2	195.3	226.2
65°	100.4	100.6	102.2	103.0	105.9	109.5	115.6	122.9	135.4	157.3	180.7
67.5°	83.9	83.9	84.0	85.2	87.2	89.5	93.1	99.1	108.5	121.9	142.5
70°	73.1	73.1	73.6	74.3	75.4	77.4	79.5	83.9	90.8	101.7	117.5
72.5°	63.2	63.3	63.8	63.9	64.5	66.2	67.7	70.5	75.6	83.9	96.7
75°	46.4	47.0	48.2	49.1	50.2	50.0	51.6	53.3	54.9	59.8	67.1
77.5°	34.5	34.2	34.3	35.1	35.2	35.4	36.6	37.9	39.1	41.4	44.0
80°	26.3	26.3	27.0	27.2	27.0	27.2	28.4	29.0	29.4	30.3	32.8
82.5°	19.9	20.3	20.1	20.3	20.4	20.6	21.6	21.7	22.1	22.5	23.5
85°	11.1	11.4	11.6	11.1	11.1	11.1	11.6	11.8	12.3	12.1	12.5
87.5°	8.1	7.9	8.0	7.9	8.0	7.7	7.7	7.9	7.4	7.4	7.1
90°	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2	16.3	15.4	14.1
92.5°	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7	15.7	14.8	13.6
95°	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2	16.3	15.4	15.3
97.5°	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6	18.5	35.8
100°	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5	28.2	30.8	52.2
102.5°	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3	119.8	148.4	151.1
105°	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1	219.7	218.3	217.5
107.5°	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5	272.9	272.1	271.1
110°	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2	308.9	308.5	307.6



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7	343.7	343.8	343.4
115°	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2	394.9	394.5	394.7
117.5°	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0	447.1	447.2	446.9
120°	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5	478.7
122.5°	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9	510.7	510.5	510.2
125°	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1	554.6	554.1	554.4
127.5°	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0	599.1	599.2	598.4
130°	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8	625.7	625.5	625.0
132.5°	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1	652.0	651.8	651.2
135°	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3	688.1	687.8	687.1
137.5°	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1	722.7	722.5	721.8
140°	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6	744.1	743.8	743.4
142.5°	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6	764.2	763.8	763.6
145°	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0	792.9	792.7	792.7
147.5°	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9	817.8	817.7	817.8
150°	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0	834.0	834.0	834.2
152.5°	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9	847.6	847.4	847.7
155°	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7	866.1	865.4	865.9
157.5°	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3	881.7
160°	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4	891.5
162.5°	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6	900.7	899.8	899.8
165°	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4	912.2	911.0	911.0
167.5°	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1	920.7	919.4	919.5
170°	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4	926.1	924.9	924.7
172.5°	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8	929.5	928.3	928.1
175°	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7	933.3	931.9	931.8
177.5°	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3	935.3	934.2	934.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	570.4	568.0	566.7	563.8	560.4	558.6	557.0	554.7	551.7	548.5	546.2
5°	599.4	594.0	587.3	579.3	572.2	565.2	559.2	553.2	546.3	539.1	532.1
7.5°	629.1	618.6	607.2	594.0	581.3	569.6	558.8	548.7	537.1	526.6	517.2
10°	649.8	635.6	619.7	602.9	586.3	571.7	557.4	544.5	530.3	517.6	506.8
12.5°	666.6	649.8	630.7	609.9	589.7	572.2	555.8	538.9	522.7	509.0	494.6
15°	694.4	671.5	645.8	620.8	594.7	570.8	548.7	529.1	510.6	491.2	477.6
17.5°	713.6	686.3	655.1	625.1	594.3	566.1	540.6	517.3	495.9	476.1	459.9
20°	725.0	694.8	660.3	626.1	591.5	561.5	534.0	508.1	486.1	464.7	447.9
22.5°	731.4	698.0	660.3	624.5	588.7	556.1	526.0	499.1	475.0	453.6	435.1
25°	733.5	697.8	659.2	618.1	578.9	544.3	513.0	483.8	457.0	435.6	416.0
27.5°	730.6	688.5	649.0	606.9	566.4	530.0	497.2	466.5	439.7	416.7	396.5
30°	726.3	681.3	638.9	595.1	554.1	519.1	484.5	455.1	427.2	403.3	383.0
32.5°	717.0	672.3	626.7	581.9	540.4	504.3	471.5	441.9	414.5	390.1	368.5
35°	698.6	653.4	603.9	557.9	517.1	479.6	448.8	420.3	394.2	368.1	345.3
37.5°	674.4	628.2	578.9	528.6	487.7	452.3	424.1	397.3	371.8	348.0	322.8
40°	651.6	609.4	558.6	508.6	466.7	432.5	406.4	382.1	356.5	332.8	307.6
42.5°	624.0	588.1	536.6	486.4	445.1	412.2	387.9	364.1	340.7	317.8	291.5
45°	577.8	550.5	502.4	454.2	412.5	379.8	357.6	336.6	316.1	294.3	269.5
47.5°	524.8	506.4	464.9	415.5	376.9	347.6	326.0	308.9	291.5	269.7	248.0
50°	488.0	476.3	436.1	391.1	354.2	327.3	305.2	289.1	274.6	253.6	234.2
52.5°	448.8	442.5	408.6	365.5	330.0	303.5	284.6	270.2	255.5	238.1	220.0
55°	389.0	392.4	363.6	326.3	292.8	270.6	253.4	241.4	228.8	214.1	200.1
57.5°	327.9	340.2	320.8	288.1	256.7	236.1	223.2	213.1	202.6	190.4	178.3
60°	291.3	301.6	290.7	261.8	234.4	215.3	203.2	195.4	184.9	173.8	164.7
62.5°	255.6	266.6	260.1	236.9	211.4	194.9	184.3	177.0	169.2	159.5	150.0
65°	210.8	217.9	214.8	198.8	180.7	166.6	156.8	151.5	144.3	137.2	128.8
67.5°	161.5	175.2	173.4	164.9	149.3	138.3	131.9	127.1	120.6	115.4	109.6
70°	132.7	145.4	145.2	138.3	129.8	119.6	115.1	111.1	105.3	100.2	95.5
72.5°	108.7	120.3	122.1	116.7	110.9	103.1	98.9	96.1	90.5	87.0	83.1
75°	76.1	84.5	86.8	86.8	84.1	80.1	76.3	74.5	70.5	67.4	65.1
77.5°	49.9	55.2	58.7	59.5	59.9	58.5	55.4	54.2	51.1	50.0	47.9
80°	35.3	38.8	42.8	44.2	45.2	44.9	43.5	42.6	39.7	38.5	37.7
82.5°	24.3	26.3	29.6	32.6	32.2	33.5	32.2	31.6	29.3	28.9	28.1
85°	12.7	12.9	13.4	15.4	16.5	17.0	17.2	16.8	16.0	16.0	14.5
87.5°	6.9	6.4	6.5	6.2	6.1	6.5	6.7	6.5	6.3	6.1	5.9
90°	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1	3.8	5.6	7.3
92.5°	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9	9.0	9.0	9.0
95°	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5	33.2	27.9	22.6
97.5°	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7	85.0	88.3	91.6
100°	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7	117.5	120.4	123.1
102.5°	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7	153.7	155.8	157.9
105°	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6	211.5	212.4	213.4
107.5°	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3	265.8	266.3	266.7
110°	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3	302.7	303.2	303.7



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1	338.9	339.8	340.5
115°	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2	393.7	394.2	394.5
117.5°	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9	443.5	444.1	444.7
120°	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5	477.1	477.7	478.3
122.5°	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8	508.1	508.5	508.9
125°	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7	553.4	553.9	554.6
127.5°	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2	595.4	595.6	595.7
130°	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6	622.8	623.0	623.1
132.5°	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9	648.2	648.5	648.7
135°	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6	685.5	685.3	685.1
137.5°	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1	719.2	719.3	719.3
140°	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9	741.2	741.5	741.9
142.5°	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5	761.1	761.7	762.1
145°	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6	791.1	791.5	792.0
147.5°	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5	815.4	816.2	817.1
150°	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9	832.5	833.1	833.8
152.5°	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4	846.9	847.4	847.9
155°	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9	867.0	867.1	867.3
157.5°	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1	884.0	883.9	883.8
160°	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1	893.6	893.2	892.8
162.5°	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1	902.5	901.9	901.4
165°	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5	913.6	912.9	912.1
167.5°	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4	922.6	921.8	921.0
170°	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4	927.5	926.5	925.6
172.5°	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8	930.9	929.9	929.0
175°	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4	934.4	933.6	932.6
177.5°	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1	936.2	935.4	934.4
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	543.7	541.9	539.6	536.9	533.7	530.8	529.5	530.7	531.2	529.7	529.5
5°	527.1	521.5	517.1	510.4	505.0	500.6	497.5	496.1	496.5	492.9	492.1
7.5°	508.5	501.9	494.6	486.6	479.3	472.7	469.3	467.4	463.5	461.9	459.2
10°	496.5	487.7	480.5	471.1	462.6	454.9	451.0	447.9	444.1	442.3	438.6
12.5°	484.3	473.9	466.0	456.3	447.6	438.3	434.6	428.9	422.9	419.1	414.2
15°	466.8	454.4	444.8	433.2	422.9	412.3	402.7	391.9	388.0	379.5	374.6
17.5°	446.6	433.9	422.1	406.5	390.7	377.3	367.1	356.8	350.7	345.3	342.8
20°	433.2	421.6	405.1	387.0	369.4	354.7	346.4	339.7	333.0	329.2	326.6
22.5°	420.6	405.7	386.5	367.0	349.4	337.9	330.9	324.0	318.6	315.0	311.4
25°	399.3	379.8	359.6	337.2	325.3	315.2	307.6	302.0	298.7	294.0	292.2
27.5°	377.5	353.9	331.6	316.6	304.1	294.8	288.2	284.1	279.8	276.8	274.5
30°	360.7	336.9	316.8	302.5	289.7	282.2	276.8	271.9	268.5	266.1	264.4
32.5°	344.1	320.3	303.4	288.0	278.0	270.6	264.9	261.2	258.5	255.4	254.3
35°	320.1	298.9	284.2	270.3	260.1	253.4	248.9	245.2	242.9	242.0	241.4
37.5°	297.0	279.7	263.8	252.5	243.4	238.1	232.8	230.9	229.4	227.8	228.6
40°	282.4	266.1	252.0	240.1	232.6	226.9	223.8	221.5	220.2	220.2	220.2
42.5°	269.8	253.8	240.1	229.3	222.0	217.1	213.6	211.7	211.2	211.0	212.2
45°	250.1	235.4	221.5	212.5	206.3	201.4	199.4	197.8	197.8	198.8	199.0
47.5°	230.5	216.8	205.7	195.7	189.9	186.9	185.1	184.4	184.5	185.3	186.3
50°	218.6	205.0	194.1	185.1	179.8	176.9	175.3	174.8	175.3	175.3	176.9
52.5°	205.6	193.4	182.7	175.1	169.1	166.4	165.5	164.9	165.1	165.9	166.5
55°	186.5	175.6	165.3	158.2	153.7	151.9	149.9	150.1	149.7	150.1	150.1
57.5°	167.3	157.5	148.0	142.3	138.4	135.8	133.7	134.2	133.6	133.5	133.1
60°	155.0	144.3	136.8	131.6	127.1	124.9	122.9	123.4	122.7	122.2	121.3
62.5°	141.7	132.7	125.5	120.6	117.0	114.4	112.4	112.0	110.4	108.9	106.9
65°	122.2	114.9	108.4	103.8	100.4	98.4	96.8	95.5	92.1	88.6	86.8
67.5°	103.4	98.0	92.0	88.0	85.3	82.8	79.7	77.5	74.4	72.4	71.3
70°	91.2	86.1	81.0	77.2	74.3	71.8	68.5	66.9	64.7	63.8	62.7
72.5°	79.6	74.8	70.1	66.6	63.6	61.6	59.0	57.5	56.5	56.1	55.0
75°	62.0	58.2	54.7	51.6	49.1	47.7	46.7	45.5	45.1	43.1	41.9
77.5°	45.2	42.7	40.5	38.3	36.6	35.6	33.5	32.2	31.5	30.5	30.3
80°	35.3	33.5	31.2	29.9	27.4	26.6	25.6	25.4	25.2	25.0	24.8
82.5°	26.5	24.7	22.5	21.7	21.0	20.5	20.0	19.7	19.5	19.6	19.6
85°	13.4	12.5	12.5	12.3	12.1	11.8	11.6	11.6	11.4	11.6	11.4
87.5°	6.2	6.4	6.6	6.5	7.0	7.2	7.2	7.4	7.7	7.5	7.7
90°	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2	18.2	19.1	19.7
92.5°	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7	17.6	18.6	19.0
95°	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2	18.2	19.1	19.7
97.5°	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7	18.8	18.9	18.9
100°	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5	22.8	20.2	18.9
102.5°	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3	62.8	34.3	20.0
105°	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1	222.4	223.9	221.8
107.5°	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5	274.2	274.9	275.5
110°	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2	309.4	309.8	310.2



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7	343.7	343.6	343.8
115°	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2	395.5	395.9	396.0
117.5°	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0	447.0	447.0	446.9
120°	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2	479.5	479.8	479.8
122.5°	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9	511.0	511.2	511.1
125°	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1	555.5	556.0	556.3
127.5°	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0	598.9	598.8	598.7
130°	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8	625.9	626.1	626.1
132.5°	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1	652.2	652.4	652.4
135°	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3	688.7	689.0	689.3
137.5°	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1	723.5	723.8	724.0
140°	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6	745.1	745.6	745.9
142.5°	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6	764.9	765.3	765.4
145°	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0	793.1	793.3	793.5
147.5°	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9	818.1	818.2	818.4
150°	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0	834.0	834.0	834.1
152.5°	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9	848.1	848.4	848.5
155°	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7	867.3	867.9	868.0
157.5°	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9	883.7	884.5	884.5
160°	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2	894.1	895.0	895.0
162.5°	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6	902.5	903.4	903.4
165°	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4	914.6	915.9	915.9
167.5°	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1	923.4	924.8	924.7
170°	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4	928.7	929.9	929.7
172.5°	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8	932.0	933.2	933.0
175°	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7	936.1	937.5	937.3
177.5°	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3	937.3	938.3	938.0
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	528.5	528.9	527.6	527.3	527.6	528.9	528.5	529.5	529.7	531.2	530.7
5°	490.3	489.8	488.7	489.0	488.7	489.8	490.3	492.1	492.9	496.5	496.1
7.5°	457.6	455.9	456.4	454.6	456.4	455.9	457.6	459.2	461.9	463.5	467.4
10°	437.6	435.2	433.2	431.4	433.2	435.2	437.6	438.6	442.3	444.1	447.9
12.5°	410.4	408.2	405.6	406.0	405.6	408.2	410.4	414.2	419.1	422.9	428.9
15°	371.6	368.3	363.0	363.6	363.0	368.3	371.6	374.6	379.5	388.0	391.9
17.5°	338.8	338.8	336.4	337.1	336.4	338.8	338.8	342.8	345.3	350.7	356.8
20°	321.9	320.4	320.6	319.9	320.6	320.4	321.9	326.6	329.2	333.0	339.7
22.5°	310.1	308.2	306.6	305.3	306.6	308.2	310.1	311.4	315.0	318.6	324.0
25°	290.2	288.9	286.9	286.4	286.9	288.9	290.2	292.2	294.0	298.7	302.0
27.5°	272.7	272.5	271.6	270.6	271.6	272.5	272.7	274.5	276.8	279.8	284.1
30°	262.6	262.1	261.6	261.0	261.6	262.1	262.6	264.4	266.1	268.5	271.9
32.5°	253.4	253.2	252.7	252.8	252.7	253.2	253.4	254.3	255.4	258.5	261.2
35°	240.4	240.3	239.8	239.6	239.8	240.3	240.4	241.4	242.0	242.9	245.2
37.5°	228.4	228.9	228.7	228.6	228.7	228.9	228.4	228.6	227.8	229.4	230.9
40°	220.0	220.2	220.6	220.4	220.6	220.2	220.0	220.2	220.2	220.2	221.5
42.5°	213.0	213.0	213.7	212.9	213.7	213.0	213.0	212.2	211.0	211.2	211.7
45°	200.6	201.9	201.6	201.6	201.6	201.9	200.6	199.0	198.8	197.8	197.8
47.5°	186.9	188.1	188.4	188.3	188.4	188.1	186.9	186.3	185.3	184.5	184.4
50°	178.0	177.6	178.2	178.0	178.2	177.6	178.0	176.9	175.3	175.3	174.8
52.5°	167.1	167.2	167.2	166.9	167.2	167.2	167.1	166.5	165.9	165.1	164.9
55°	150.3	150.6	150.1	150.3	150.1	150.6	150.3	150.1	150.1	149.7	150.1
57.5°	132.1	131.1	131.5	131.0	131.5	131.1	132.1	133.1	133.5	133.6	134.2
60°	119.1	117.3	116.9	116.0	116.9	117.3	119.1	121.3	122.2	122.7	123.4
62.5°	104.5	103.2	101.7	102.5	101.7	103.2	104.5	106.9	108.9	110.4	112.0
65°	85.0	84.1	83.4	84.4	83.4	84.1	85.0	86.8	88.6	92.1	95.5
67.5°	70.3	69.8	69.8	69.5	69.8	69.8	70.3	71.3	72.4	74.4	77.5
70°	62.7	62.0	62.0	61.5	62.0	62.0	62.7	62.7	63.8	64.7	66.9
72.5°	54.9	54.2	54.4	54.1	54.4	54.2	54.9	55.0	56.1	56.5	57.5
75°	40.6	39.5	39.5	39.7	39.5	39.5	40.6	41.9	43.1	45.1	45.5
77.5°	30.3	30.1	30.3	30.0	30.3	30.1	30.3	30.3	30.5	31.5	32.2
80°	24.8	24.5	24.3	25.0	24.3	24.5	24.8	24.8	25.0	25.2	25.4
82.5°	19.2	19.2	19.1	20.0	19.1	19.2	19.2	19.6	19.6	19.5	19.7
85°	11.6	11.1	11.6	11.1	11.6	11.1	11.6	11.4	11.6	11.4	11.6
87.5°	8.1	8.0	7.9	8.1	7.9	8.0	8.1	7.7	7.5	7.7	7.4
90°	20.1	20.4	20.6	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2
92.5°	19.1	19.2	19.2	19.3	19.2	19.2	19.1	19.0	18.6	17.6	16.7
95°	19.8	20.0	20.2	20.3	20.2	20.0	19.8	19.7	19.1	18.2	17.2
97.5°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	18.9	18.8	18.7
100°	19.1	19.3	19.4	19.6	19.4	19.3	19.1	18.9	20.2	22.8	25.5
102.5°	20.1	20.1	20.1	20.2	20.1	20.1	20.1	20.0	34.3	62.8	91.3
105°	216.2	210.6	205.0	199.4	205.0	210.6	216.2	221.8	223.9	222.4	221.1
107.5°	276.2	276.7	277.3	277.9	277.3	276.7	276.2	275.5	274.9	274.2	273.5
110°	310.7	311.1	311.6	312.1	311.6	311.1	310.7	310.2	309.8	309.4	309.2



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	344.4	345.0	345.6	346.2	345.6	345.0	344.4	343.8	343.6	343.7	343.7
115°	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0	395.9	395.5	395.2
117.5°	446.9	446.8	446.7	446.7	446.7	446.8	446.9	446.9	447.0	447.0	447.0
120°	479.5	479.2	478.9	478.5	478.9	479.2	479.5	479.8	479.8	479.5	479.2
122.5°	510.9	510.5	510.2	509.9	510.2	510.5	510.9	511.1	511.2	511.0	510.9
125°	556.5	556.6	556.8	556.9	556.8	556.6	556.5	556.3	556.0	555.5	555.1
127.5°	598.6	598.4	598.3	598.2	598.3	598.4	598.6	598.7	598.8	598.9	599.0
130°	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	626.1	625.9	625.8
132.5°	652.3	652.1	652.1	652.0	652.1	652.1	652.3	652.4	652.4	652.2	652.1
135°	689.6	689.9	690.2	690.5	690.2	689.9	689.6	689.3	689.0	688.7	688.3
137.5°	723.9	723.8	723.7	723.6	723.7	723.8	723.9	724.0	723.8	723.5	723.1
140°	746.0	746.2	746.4	746.5	746.4	746.2	746.0	745.9	745.6	745.1	744.6
142.5°	765.4	765.4	765.5	765.5	765.5	765.4	765.4	765.4	765.3	764.9	764.6
145°	793.8	794.2	794.5	794.8	794.5	794.2	793.8	793.5	793.3	793.1	793.0
147.5°	818.5	818.7	818.9	819.0	818.9	818.7	818.5	818.4	818.2	818.1	817.9
150°	834.2	834.3	834.5	834.6	834.5	834.3	834.2	834.1	834.0	834.0	834.0
152.5°	848.4	848.3	848.2	848.1	848.2	848.3	848.4	848.5	848.4	848.1	847.9
155°	867.5	867.0	866.6	866.2	866.6	867.0	867.5	868.0	867.9	867.3	866.7
157.5°	883.7	882.9	882.0	881.3	882.0	882.9	883.7	884.5	884.5	883.7	882.9
160°	894.1	893.2	892.3	891.4	892.3	893.2	894.1	895.0	895.0	894.1	893.2
162.5°	902.4	901.3	900.2	899.2	900.2	901.3	902.4	903.4	903.4	902.5	901.6
165°	914.5	913.0	911.6	910.2	911.6	913.0	914.5	915.9	915.9	914.6	913.4
167.5°	923.1	921.6	920.0	918.5	920.0	921.6	923.1	924.7	924.8	923.4	922.1
170°	928.2	926.6	925.1	923.5	925.1	926.6	928.2	929.7	929.9	928.7	927.4
172.5°	931.3	929.7	928.0	926.3	928.0	929.7	931.3	933.0	933.2	932.0	930.8
175°	935.4	933.6	931.7	929.8	931.7	933.6	935.4	937.3	937.5	936.1	934.7
177.5°	936.5	935.0	933.6	932.1	933.6	935.0	936.5	938.0	938.3	937.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	529.5	530.8	533.7	536.9	539.6	541.9	543.7	546.2	548.5	551.7	554.7
5°	497.5	500.6	505.0	510.4	517.1	521.5	527.1	532.1	539.1	546.3	553.2
7.5°	469.3	472.7	479.3	486.6	494.6	501.9	508.5	517.2	526.6	537.1	548.7
10°	451.0	454.9	462.6	471.1	480.5	487.7	496.5	506.8	517.6	530.3	544.5
12.5°	434.6	438.3	447.6	456.3	466.0	473.9	484.3	494.6	509.0	522.7	538.9
15°	402.7	412.3	422.9	433.2	444.8	454.4	466.8	477.6	491.2	510.6	529.1
17.5°	367.1	377.3	390.7	406.5	422.1	433.9	446.6	459.9	476.1	495.9	517.3
20°	346.4	354.7	369.4	387.0	405.1	421.6	433.2	447.9	464.7	486.1	508.1
22.5°	330.9	337.9	349.4	367.0	386.5	405.7	420.6	435.1	453.6	475.0	499.1
25°	307.6	315.2	325.3	337.2	359.6	379.8	399.3	416.0	435.6	457.0	483.8
27.5°	288.2	294.8	304.1	316.6	331.6	353.9	377.5	396.5	416.7	439.7	466.5
30°	276.8	282.2	289.7	302.5	316.8	336.9	360.7	383.0	403.3	427.2	455.1
32.5°	264.9	270.6	278.0	288.0	303.4	320.3	344.1	368.5	390.1	414.5	441.9
35°	248.9	253.4	260.1	270.3	284.2	298.9	320.1	345.3	368.1	394.2	420.3
37.5°	232.8	238.1	243.4	252.5	263.8	279.7	297.0	322.8	348.0	371.8	397.3
40°	223.8	226.9	232.6	240.1	252.0	266.1	282.4	307.6	332.8	356.5	382.1
42.5°	213.6	217.1	222.0	229.3	240.1	253.8	269.8	291.5	317.8	340.7	364.1
45°	199.4	201.4	206.3	212.5	221.5	235.4	250.1	269.5	294.3	316.1	336.6
47.5°	185.1	186.9	189.9	195.7	205.7	216.8	230.5	248.0	269.7	291.5	308.9
50°	175.3	176.9	179.8	185.1	194.1	205.0	218.6	234.2	253.6	274.6	289.1
52.5°	165.5	166.4	169.1	175.1	182.7	193.4	205.6	220.0	238.1	255.5	270.2
55°	149.9	151.9	153.7	158.2	165.3	175.6	186.5	200.1	214.1	228.8	241.4
57.5°	133.7	135.8	138.4	142.3	148.0	157.5	167.3	178.3	190.4	202.6	213.1
60°	122.9	124.9	127.1	131.6	136.8	144.3	155.0	164.7	173.8	184.9	195.4
62.5°	112.4	114.4	117.0	120.6	125.5	132.7	141.7	150.0	159.5	169.2	177.0
65°	96.8	98.4	100.4	103.8	108.4	114.9	122.2	128.8	137.2	144.3	151.5
67.5°	79.7	82.8	85.3	88.0	92.0	98.0	103.4	109.6	115.4	120.6	127.1
70°	68.5	71.8	74.3	77.2	81.0	86.1	91.2	95.5	100.2	105.3	111.1
72.5°	59.0	61.6	63.6	66.6	70.1	74.8	79.6	83.1	87.0	90.5	96.1
75°	46.7	47.7	49.1	51.6	54.7	58.2	62.0	65.1	67.4	70.5	74.5
77.5°	33.5	35.6	36.6	38.3	40.5	42.7	45.2	47.9	50.0	51.1	54.2
80°	25.6	26.6	27.4	29.9	31.2	33.5	35.3	37.7	38.5	39.7	42.6
82.5°	20.0	20.5	21.0	21.7	22.5	24.7	26.5	28.1	28.9	29.3	31.6
85°	11.6	11.8	12.1	12.3	12.5	12.5	13.4	14.5	16.0	16.0	16.8
87.5°	7.2	7.2	7.0	6.5	6.6	6.4	6.2	5.9	6.1	6.3	6.5
90°	16.3	15.4	14.1	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1
92.5°	15.7	14.8	13.6	12.3	11.1	9.9	9.1	9.0	9.0	9.0	8.9
95°	16.3	15.4	15.3	15.1	14.9	14.8	17.3	22.6	27.9	33.2	38.5
97.5°	18.6	18.5	35.8	53.2	70.5	87.8	94.9	91.6	88.3	85.0	81.7
100°	28.2	30.8	52.2	73.7	95.2	116.6	125.9	123.1	120.4	117.5	114.7
102.5°	119.8	148.4	151.1	153.9	156.7	159.5	159.9	157.9	155.8	153.7	151.7
105°	219.7	218.3	217.5	216.7	215.9	215.2	214.3	213.4	212.4	211.5	210.6
107.5°	272.9	272.1	271.1	270.0	269.0	268.0	267.2	266.7	266.3	265.8	265.3
110°	308.9	308.5	307.6	306.7	305.8	304.8	304.1	303.7	303.2	302.7	302.3



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	343.7	343.8	343.4	342.9	342.5	342.0	341.4	340.5	339.8	338.9	338.1
115°	394.9	394.5	394.7	394.9	395.0	395.2	395.0	394.5	394.2	393.7	393.2
117.5°	447.1	447.2	446.9	446.5	446.2	445.8	445.4	444.7	444.1	443.5	442.9
120°	478.9	478.5	478.7	478.9	479.0	479.2	478.9	478.3	477.7	477.1	476.5
122.5°	510.7	510.5	510.2	510.0	509.8	509.5	509.3	508.9	508.5	508.1	507.8
125°	554.6	554.1	554.4	554.8	555.1	555.3	555.2	554.6	553.9	553.4	552.7
127.5°	599.1	599.2	598.4	597.8	597.0	596.3	595.9	595.7	595.6	595.4	595.2
130°	625.7	625.5	625.0	624.5	624.1	623.6	623.3	623.1	623.0	622.8	622.6
132.5°	652.0	651.8	651.2	650.6	650.0	649.4	648.9	648.7	648.5	648.2	647.9
135°	688.1	687.8	687.1	686.5	685.9	685.2	685.0	685.1	685.3	685.5	685.6
137.5°	722.7	722.5	721.8	721.0	720.4	719.7	719.3	719.3	719.3	719.2	719.1
140°	744.1	743.8	743.4	743.1	742.8	742.4	742.2	741.9	741.5	741.2	740.9
142.5°	764.2	763.8	763.6	763.5	763.3	763.1	762.7	762.1	761.7	761.1	760.5
145°	792.9	792.7	792.7	792.7	792.7	792.7	792.5	792.0	791.5	791.1	790.6
147.5°	817.8	817.7	817.8	818.0	818.2	818.3	818.0	817.1	816.2	815.4	814.5
150°	834.0	834.0	834.2	834.2	834.4	834.6	834.3	833.8	833.1	832.5	831.9
152.5°	847.6	847.4	847.7	848.0	848.2	848.5	848.4	847.9	847.4	846.9	846.4
155°	866.1	865.4	865.9	866.4	866.9	867.3	867.5	867.3	867.1	867.0	866.9
157.5°	882.0	881.3	881.7	882.3	882.9	883.4	883.7	883.8	883.9	884.0	884.1
160°	892.3	891.4	891.5	891.6	891.8	891.9	892.3	892.8	893.2	893.6	894.1
162.5°	900.7	899.8	899.8	900.0	900.2	900.3	900.7	901.4	901.9	902.5	903.1
165°	912.2	911.0	911.0	911.0	911.0	911.0	911.3	912.1	912.9	913.6	914.5
167.5°	920.7	919.4	919.5	919.5	919.6	919.7	920.1	921.0	921.8	922.6	923.4
170°	926.1	924.9	924.7	924.6	924.4	924.3	924.7	925.6	926.5	927.5	928.4
172.5°	929.5	928.3	928.1	927.9	927.8	927.7	928.0	929.0	929.9	930.9	931.8
175°	933.3	931.9	931.8	931.6	931.4	931.3	931.7	932.6	933.6	934.4	935.4
177.5°	935.3	934.2	934.1	933.8	933.6	933.3	933.6	934.4	935.4	936.2	937.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	557.0	558.6	560.4	563.8	566.7	568.0	570.4	572.2	571.7	574.2	578.4
5°	559.2	565.2	572.2	579.3	587.3	594.0	599.4	604.7	609.0	614.1	621.7
7.5°	558.8	569.6	581.3	594.0	607.2	618.6	629.1	639.8	649.3	659.7	673.4
10°	557.4	571.7	586.3	602.9	619.7	635.6	649.8	663.2	675.9	689.5	706.7
12.5°	555.8	572.2	589.7	609.9	630.7	649.8	666.6	685.9	701.8	719.3	739.1
15°	548.7	570.8	594.7	620.8	645.8	671.5	694.4	718.0	740.2	761.1	786.1
17.5°	540.6	566.1	594.3	625.1	655.1	686.3	713.6	743.4	765.9	794.1	817.3
20°	534.0	561.5	591.5	626.1	660.3	694.8	725.0	755.4	780.7	809.1	838.5
22.5°	526.0	556.1	588.7	624.5	660.3	698.0	731.4	761.6	793.1	824.9	855.3
25°	513.0	544.3	578.9	618.1	659.2	697.8	733.5	770.9	804.8	839.4	866.7
27.5°	497.2	530.0	566.4	606.9	649.0	688.5	730.6	770.5	804.6	837.9	861.7
30°	484.5	519.1	554.1	595.1	638.9	681.3	726.3	766.3	802.2	832.1	845.5
32.5°	471.5	504.3	540.4	581.9	626.7	672.3	717.0	757.9	791.1	809.0	809.4
35°	448.8	479.6	517.1	557.9	603.9	653.4	698.6	738.8	759.1	760.6	738.8
37.5°	424.1	452.3	487.7	528.6	578.9	628.2	674.4	701.2	707.9	685.2	644.9
40°	406.4	432.5	466.7	508.6	558.6	609.4	651.6	671.2	664.1	627.3	582.2
42.5°	387.9	412.2	445.1	486.4	536.6	588.1	624.0	634.4	615.6	573.1	520.3
45°	357.6	379.8	412.5	454.2	502.4	550.5	577.8	572.4	540.9	490.5	431.4
47.5°	326.0	347.6	376.9	415.5	464.9	506.4	524.8	508.7	463.9	408.5	360.4
50°	305.2	327.3	354.2	391.1	436.1	476.3	488.0	463.5	413.8	360.5	316.3
52.5°	284.6	303.5	330.0	365.5	408.6	442.5	448.8	420.6	369.2	321.4	282.2
55°	253.4	270.6	292.8	326.3	363.6	392.4	389.0	352.7	306.0	265.2	234.4
57.5°	223.2	236.1	256.7	288.1	320.8	340.2	327.9	296.9	253.4	220.0	194.1
60°	203.2	215.3	234.4	261.8	290.7	301.6	291.3	257.7	223.3	192.7	170.9
62.5°	184.3	194.9	211.4	236.9	260.1	266.6	255.6	226.2	195.3	169.2	151.1
65°	156.8	166.6	180.7	198.8	214.8	217.9	210.8	180.7	157.3	135.4	122.9
67.5°	131.9	138.3	149.3	164.9	173.4	175.2	161.5	142.5	121.9	108.5	99.1
70°	115.1	119.6	129.8	138.3	145.2	145.4	132.7	117.5	101.7	90.8	83.9
72.5°	98.9	103.1	110.9	116.7	122.1	120.3	108.7	96.7	83.9	75.6	70.5
75°	76.3	80.1	84.1	86.8	86.8	84.5	76.1	67.1	59.8	54.9	53.3
77.5°	55.4	58.5	59.9	59.5	58.7	55.2	49.9	44.0	41.4	39.1	37.9
80°	43.5	44.9	45.2	44.2	42.8	38.8	35.3	32.8	30.3	29.4	29.0
82.5°	32.2	33.5	32.2	32.6	29.6	26.3	24.3	23.5	22.5	22.1	21.7
85°	17.2	17.0	16.5	15.4	13.4	12.9	12.7	12.5	12.1	12.3	11.8
87.5°	6.7	6.5	6.1	6.2	6.5	6.4	6.9	7.1	7.4	7.4	7.9
90°	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2
92.5°	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7	16.7
95°	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3	17.2
97.5°	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6	18.7
100°	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2	25.5
102.5°	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8	91.3
105°	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7	221.1
107.5°	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9	273.5
110°	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9	309.2



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7	343.7
115°	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9	395.2
117.5°	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1	447.0
120°	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9	479.2
122.5°	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7	510.9
125°	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6	555.1
127.5°	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1	599.0
130°	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7	625.8
132.5°	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0	652.1
135°	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1	688.3
137.5°	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7	723.1
140°	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1	744.6
142.5°	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2	764.6
145°	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9	793.0
147.5°	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8	817.9
150°	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0	834.0
152.5°	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6	847.9
155°	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1	866.7
157.5°	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0	882.9
160°	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3	893.2
162.5°	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7	901.6
165°	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2	913.4
167.5°	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7	922.1
170°	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1	927.4
172.5°	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5	930.8
175°	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3	934.7
177.5°	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3	936.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	580.8	581.5	582.0	583.8	584.0	585.6	584.0
5°	628.9	632.0	636.9	641.8	642.2	645.4	639.8
7.5°	682.7	689.9	694.5	702.4	705.5	707.5	704.3
10°	719.8	726.5	738.4	744.1	750.0	750.8	748.2
12.5°	755.7	766.3	775.6	786.6	786.4	794.2	791.4
15°	803.5	814.5	827.4	839.6	844.0	844.0	847.6
17.5°	837.5	857.6	871.0	880.6	891.2	893.0	891.7
20°	860.6	882.2	896.5	909.0	916.2	918.1	918.1
22.5°	877.7	896.2	910.1	921.3	927.2	929.5	928.9
25°	889.6	905.4	913.9	917.3	918.8	918.4	914.2
27.5°	873.4	872.6	867.3	857.1	849.3	844.6	839.2
30°	842.4	830.7	817.3	802.6	783.6	769.1	764.7
32.5°	796.1	770.1	747.3	722.8	702.5	688.0	681.8
35°	706.7	665.4	631.7	602.3	580.9	567.5	563.0
37.5°	600.6	560.6	519.0	490.4	472.6	459.1	454.1
40°	533.1	489.7	453.3	426.5	408.2	395.0	394.8
42.5°	471.6	430.0	395.8	376.5	356.8	348.1	348.1
45°	386.2	352.9	323.9	308.7	296.9	289.7	287.8
47.5°	319.7	292.2	272.9	260.8	251.2	246.7	243.6
50°	282.4	258.4	242.9	232.4	227.1	221.3	220.8
52.5°	251.4	231.9	219.9	211.4	204.6	201.1	201.2
55°	211.2	195.9	187.4	180.9	175.6	172.9	171.7
57.5°	178.0	166.5	160.2	154.3	152.0	150.0	149.4
60°	157.3	149.5	143.6	138.9	135.6	135.0	134.7
62.5°	140.2	132.0	128.0	124.3	121.9	120.8	120.5
65°	115.6	109.5	105.9	103.0	102.2	100.6	100.4
67.5°	93.1	89.5	87.2	85.2	84.0	83.9	83.9
70°	79.5	77.4	75.4	74.3	73.6	73.1	73.1
72.5°	67.7	66.2	64.5	63.9	63.8	63.3	63.2
75°	51.6	50.0	50.2	49.1	48.2	47.0	46.4
77.5°	36.6	35.4	35.2	35.1	34.3	34.2	34.5
80°	28.4	27.2	27.0	27.2	27.0	26.3	26.3
82.5°	21.6	20.6	20.4	20.3	20.1	20.3	19.9
85°	11.6	11.1	11.1	11.1	11.6	11.4	11.1
87.5°	7.7	7.7	8.0	7.9	8.0	7.9	8.1
90°	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.4	309.8	310.2	310.7	311.1	311.6	312.1



TEST NUMBER: P333019-830

CATALOG NUMBER: S124RDIW-S350D770U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)