

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333023-935

Luminaire Tested: **S124RDIW-S350D1050U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333023-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1050U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4889.6 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26																												
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	31	30	29	23																												
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25	19																												
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17																												
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14																												
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13																												
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11																												
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10																												
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	12	9																												
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8																												
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	9	7																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.0
10°-20°	147.8	3.0
20°-30°	231.2	4.7
30°-40°	257.0	5.3
40°-50°	228.0	4.7
50°-60°	177.7	3.6
60°-70°	116.3	2.4
70°-80°	57.2	1.2
80°-90°	17.5	0.4
90°-100°	39.9	0.8
100°-110°	254.3	5.2
110°-120°	486.6	10.0
120°-130°	617.7	12.6
130°-140°	660.8	13.5
140°-150°	618.0	12.6
150°-160°	498.3	10.2
160°-170°	321.4	6.6
170°-180°	110.8	2.3
0°-30°	428.0	8.8
0°-40°	685.0	14.0
0°-60°	1090.8	22.3
0°-90°	1281.8	26.2
90°-120°	780.8	16.0
90°-150°	2677.3	54.8
90°-180°	3608.0	73.8
0°-180°	4889.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	26	3	26	3	26	12
95°	25	48	25	48	25	20
105°	249	263	249	263	249	217
115°	494	490	494	490	494	489
125°	694	689	694	689	694	618
135°	861	855	861	855	861	663
145°	991	986	991	986	991	619
155°	1080	1081	1080	1081	1080	498
165°	1135	1140	1135	1140	1135	321
175°	1159	1166	1159	1166	1159	110
180°	1166	1166	1166	1166	1166	



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	8.8	8.6	8.7	8.6	8.7	8.4	8.3	8.4	7.8	7.7	7.4
90°	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5	20.3	19.2	17.7
92.5°	24.1	24.0	23.9	23.8	23.8	23.2	22.0	20.8	19.6	18.5	17.0
95°	25.3	25.1	24.9	24.7	24.5	23.8	22.6	21.5	20.3	19.2	19.0
97.5°	24.5	24.2	24.0	23.8	23.7	23.5	23.4	23.2	23.2	23.0	44.7
100°	24.5	24.2	24.0	23.8	23.7	25.2	28.5	31.8	35.1	38.4	65.2
102.5°	25.1	25.1	25.1	25.0	25.0	42.7	78.3	113.8	149.4	184.9	188.4
105°	248.7	255.6	262.6	269.6	276.6	279.1	277.4	275.7	273.9	272.2	271.2
107.5°	346.5	345.8	345.0	344.3	343.5	342.8	341.9	341.0	340.2	339.3	338.0
110°	389.1	388.5	387.9	387.4	386.8	386.2	385.9	385.5	385.1	384.7	383.6



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	431.6	430.9	430.2	429.5	428.7	428.3	428.4	428.5	428.6	428.7	428.1
115°	493.8	493.8	493.8	493.8	493.8	493.5	493.2	492.8	492.4	492.0	492.2
117.5°	556.9	557.0	557.1	557.2	557.2	557.3	557.4	557.4	557.5	557.6	557.2
120°	596.7	597.1	597.4	597.9	598.2	598.2	597.9	597.4	597.1	596.7	596.8
122.5°	635.8	636.2	636.5	637.0	637.3	637.4	637.1	637.0	636.7	636.5	636.2
125°	694.4	694.2	694.0	693.8	693.6	693.2	692.7	692.1	691.5	690.9	691.3
127.5°	745.9	746.0	746.1	746.3	746.5	746.6	746.7	746.8	747.0	747.1	746.1
130°	780.8	780.8	780.8	780.8	780.8	780.7	780.5	780.2	780.1	779.9	779.3
132.5°	812.9	813.0	813.1	813.3	813.5	813.5	813.3	813.0	812.9	812.7	811.9
135°	861.0	860.7	860.2	859.9	859.5	859.1	858.7	858.3	857.9	857.6	856.8
137.5°	902.2	902.3	902.4	902.5	902.7	902.5	902.1	901.6	901.2	900.8	899.9
140°	930.8	930.6	930.4	930.2	930.1	929.6	929.0	928.5	927.9	927.3	927.0
142.5°	954.5	954.5	954.4	954.4	954.3	954.2	953.7	953.3	952.9	952.4	952.2
145°	991.0	990.6	990.2	989.8	989.5	989.1	988.9	988.8	988.6	988.3	988.3
147.5°	1021.1	1021.0	1020.8	1020.6	1020.4	1020.2	1020.0	1019.9	1019.8	1019.6	1019.8
150°	1040.7	1040.5	1040.3	1040.1	1039.9	1039.8	1039.8	1039.8	1039.8	1039.8	1040.0
152.5°	1057.5	1057.6	1057.7	1057.8	1057.9	1057.8	1057.5	1057.2	1056.9	1056.6	1057.0
155°	1080.0	1080.6	1081.2	1081.7	1082.3	1082.2	1081.4	1080.6	1079.9	1079.1	1079.7
157.5°	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8	1099.5
160°	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4	1111.6
162.5°	1121.1	1122.5	1123.8	1125.1	1126.4	1126.4	1125.3	1124.1	1123.0	1121.8	1122.1
165°	1134.9	1136.7	1138.4	1140.1	1141.9	1142.0	1140.5	1138.9	1137.4	1135.8	1135.8
167.5°	1145.2	1147.2	1149.1	1151.1	1153.0	1153.1	1151.4	1149.7	1148.0	1146.2	1146.4
170°	1151.5	1153.4	1155.4	1157.3	1159.3	1159.4	1157.9	1156.3	1154.8	1153.2	1153.1
172.5°	1154.9	1157.1	1159.2	1161.2	1163.4	1163.6	1162.1	1160.5	1159.0	1157.4	1157.3
175°	1159.3	1161.7	1164.0	1166.3	1168.6	1169.0	1167.2	1165.4	1163.7	1162.0	1161.7
177.5°	1162.2	1164.0	1165.9	1167.7	1169.6	1169.9	1168.6	1167.4	1166.1	1164.9	1164.6
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	7.1	6.6	6.7	6.3	6.0	6.3	6.4	6.0	6.0	5.9	5.9
90°	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6	4.7	6.9	9.0
92.5°	15.4	13.9	12.3	11.5	11.4	11.2	11.1	11.0	11.1	11.2	11.4
95°	18.8	18.6	18.4	21.6	28.2	34.8	41.4	48.0	41.4	34.8	28.2
97.5°	66.3	87.9	109.6	118.3	114.3	110.1	106.0	101.9	106.0	110.1	114.3
100°	91.9	118.6	145.4	157.0	153.5	150.1	146.5	143.1	146.5	150.1	153.5
102.5°	191.9	195.4	198.9	199.3	196.8	194.2	191.7	189.2	191.7	194.2	196.8
105°	270.3	269.2	268.3	267.3	266.0	264.9	263.7	262.6	263.7	264.9	266.0
107.5°	336.7	335.4	334.1	333.1	332.5	331.9	331.4	330.8	331.4	331.9	332.5
110°	382.4	381.3	380.0	379.2	378.6	378.0	377.5	376.9	377.5	378.0	378.6



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	427.6	427.1	426.5	425.7	424.6	423.6	422.6	421.5	422.6	423.6	424.6
115°	492.4	492.6	492.8	492.6	492.0	491.5	490.9	490.3	490.9	491.5	492.0
117.5°	556.7	556.3	555.9	555.3	554.5	553.7	552.9	552.2	552.9	553.7	554.5
120°	597.1	597.3	597.4	597.2	596.4	595.6	594.9	594.1	594.9	595.6	596.4
122.5°	635.9	635.7	635.4	635.0	634.6	634.0	633.6	633.2	633.6	634.0	634.6
125°	691.6	692.1	692.4	692.2	691.5	690.7	689.9	689.1	689.9	690.7	691.5
127.5°	745.3	744.4	743.5	743.0	742.8	742.6	742.4	742.2	742.4	742.6	742.8
130°	778.7	778.2	777.6	777.1	777.0	776.8	776.6	776.4	776.6	776.8	777.0
132.5°	811.2	810.5	809.8	809.2	808.8	808.5	808.1	807.8	808.1	808.5	808.8
135°	856.0	855.2	854.5	854.1	854.3	854.5	854.7	854.9	854.7	854.5	854.3
137.5°	899.1	898.2	897.3	896.9	896.8	896.7	896.6	896.6	896.6	896.7	896.8
140°	926.5	926.2	925.7	925.4	925.0	924.6	924.2	923.9	924.2	924.6	925.0
142.5°	951.9	951.7	951.5	951.1	950.4	949.6	948.9	948.2	948.9	949.6	950.4
145°	988.3	988.3	988.3	988.1	987.5	986.9	986.4	985.8	986.4	986.9	987.5
147.5°	1020.0	1020.2	1020.4	1019.9	1018.8	1017.8	1016.7	1015.5	1016.7	1017.8	1018.8
150°	1040.3	1040.4	1040.6	1040.3	1039.6	1038.8	1038.0	1037.2	1038.0	1038.8	1039.6
152.5°	1057.3	1057.7	1058.0	1057.8	1057.2	1056.6	1056.0	1055.3	1056.0	1056.6	1057.2
155°	1080.3	1080.8	1081.4	1081.6	1081.4	1081.2	1081.1	1080.8	1081.1	1081.2	1081.4
157.5°	1100.1	1100.8	1101.5	1101.8	1101.9	1102.1	1102.2	1102.3	1102.2	1102.1	1101.9
160°	1111.7	1112.0	1112.2	1112.5	1113.1	1113.7	1114.3	1114.8	1114.3	1113.7	1113.1
162.5°	1122.2	1122.4	1122.6	1123.1	1123.8	1124.6	1125.3	1126.0	1125.3	1124.6	1123.8
165°	1135.8	1135.8	1135.8	1136.3	1137.2	1138.2	1139.2	1140.1	1139.2	1138.2	1137.2
167.5°	1146.5	1146.6	1146.8	1147.3	1148.3	1149.3	1150.3	1151.3	1150.3	1149.3	1148.3
170°	1152.9	1152.6	1152.4	1153.0	1154.1	1155.3	1156.4	1157.6	1156.4	1155.3	1154.1
172.5°	1157.0	1156.8	1156.7	1157.1	1158.3	1159.4	1160.6	1161.7	1160.6	1159.4	1158.3
175°	1161.6	1161.4	1161.2	1161.7	1162.9	1164.0	1165.2	1166.3	1165.2	1164.0	1162.9
177.5°	1164.3	1164.0	1163.7	1164.1	1165.2	1166.2	1167.3	1168.4	1167.3	1166.2	1165.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	6.3	6.5	6.8	6.8	7.3	7.6	7.7	7.9	8.3	8.2	8.4
90°	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5	22.6	23.8	24.6
92.5°	11.5	12.3	13.9	15.4	17.0	18.5	19.6	20.8	22.0	23.2	23.8
95°	21.6	18.4	18.6	18.8	19.0	19.2	20.3	21.5	22.6	23.8	24.5
97.5°	118.3	109.6	87.9	66.3	44.7	23.0	23.2	23.2	23.4	23.5	23.7
100°	157.0	145.4	118.6	91.9	65.2	38.4	35.1	31.8	28.5	25.2	23.7
102.5°	199.3	198.9	195.4	191.9	188.4	184.9	149.4	113.8	78.3	42.7	25.0
105°	267.3	268.3	269.2	270.3	271.2	272.2	273.9	275.7	277.4	279.1	276.6
107.5°	333.1	334.1	335.4	336.7	338.0	339.3	340.2	341.0	341.9	342.8	343.5
110°	379.2	380.0	381.3	382.4	383.6	384.7	385.1	385.5	385.9	386.2	386.8



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	425.7	426.5	427.1	427.6	428.1	428.7	428.6	428.5	428.4	428.3	428.7
115°	492.6	492.8	492.6	492.4	492.2	492.0	492.4	492.8	493.2	493.5	493.8
117.5°	555.3	555.9	556.3	556.7	557.2	557.6	557.5	557.4	557.4	557.3	557.2
120°	597.2	597.4	597.3	597.1	596.8	596.7	597.1	597.4	597.9	598.2	598.2
122.5°	635.0	635.4	635.7	635.9	636.2	636.5	636.7	637.0	637.1	637.4	637.3
125°	692.2	692.4	692.1	691.6	691.3	690.9	691.5	692.1	692.7	693.2	693.6
127.5°	743.0	743.5	744.4	745.3	746.1	747.1	747.0	746.8	746.7	746.6	746.5
130°	777.1	777.6	778.2	778.7	779.3	779.9	780.1	780.2	780.5	780.7	780.8
132.5°	809.2	809.8	810.5	811.2	811.9	812.7	812.9	813.0	813.3	813.5	813.5
135°	854.1	854.5	855.2	856.0	856.8	857.6	857.9	858.3	858.7	859.1	859.5
137.5°	896.9	897.3	898.2	899.1	899.9	900.8	901.2	901.6	902.1	902.5	902.7
140°	925.4	925.7	926.2	926.5	927.0	927.3	927.9	928.5	929.0	929.6	930.1
142.5°	951.1	951.5	951.7	951.9	952.2	952.4	952.9	953.3	953.7	954.2	954.3
145°	988.1	988.3	988.3	988.3	988.3	988.3	988.6	988.8	988.9	989.1	989.5
147.5°	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8	1019.9	1020.0	1020.2	1020.4
150°	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8	1039.8	1039.8	1039.8	1039.9
152.5°	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9	1057.2	1057.5	1057.8	1057.9
155°	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9	1080.6	1081.4	1082.2	1082.3
157.5°	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9
160°	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0
162.5°	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0	1124.1	1125.3	1126.4	1126.4
165°	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4	1138.9	1140.5	1142.0	1141.9
167.5°	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0	1149.7	1151.4	1153.1	1153.0
170°	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8	1156.3	1157.9	1159.4	1159.3
172.5°	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0	1160.5	1162.1	1163.6	1163.4
175°	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7	1165.4	1167.2	1169.0	1168.6
177.5°	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1	1167.4	1168.6	1169.9	1169.6
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	8.8	8.7	8.6	8.8	8.6	8.7	8.8	8.4	8.2	8.3	7.9
90°	25.0	25.4	25.7	26.2	25.7	25.4	25.0	24.6	23.8	22.6	21.5
92.5°	23.8	23.9	24.0	24.1	24.0	23.9	23.8	23.8	23.2	22.0	20.8
95°	24.7	24.9	25.1	25.3	25.1	24.9	24.7	24.5	23.8	22.6	21.5
97.5°	23.8	24.0	24.2	24.5	24.2	24.0	23.8	23.7	23.5	23.4	23.2
100°	23.8	24.0	24.2	24.5	24.2	24.0	23.8	23.7	25.2	28.5	31.8
102.5°	25.0	25.1	25.1	25.1	25.1	25.1	25.0	25.0	42.7	78.3	113.8
105°	269.6	262.6	255.6	248.7	255.6	262.6	269.6	276.6	279.1	277.4	275.7
107.5°	344.3	345.0	345.8	346.5	345.8	345.0	344.3	343.5	342.8	341.9	341.0
110°	387.4	387.9	388.5	389.1	388.5	387.9	387.4	386.8	386.2	385.9	385.5



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	429.5	430.2	430.9	431.6	430.9	430.2	429.5	428.7	428.3	428.4	428.5
115°	493.8	493.8	493.8	493.8	493.8	493.8	493.8	493.8	493.5	493.2	492.8
117.5°	557.2	557.1	557.0	556.9	557.0	557.1	557.2	557.2	557.3	557.4	557.4
120°	597.9	597.4	597.1	596.7	597.1	597.4	597.9	598.2	598.2	597.9	597.4
122.5°	637.0	636.5	636.2	635.8	636.2	636.5	637.0	637.3	637.4	637.1	637.0
125°	693.8	694.0	694.2	694.4	694.2	694.0	693.8	693.6	693.2	692.7	692.1
127.5°	746.3	746.1	746.0	745.9	746.0	746.1	746.3	746.5	746.6	746.7	746.8
130°	780.8	780.8	780.8	780.8	780.8	780.8	780.8	780.8	780.7	780.5	780.2
132.5°	813.3	813.1	813.0	812.9	813.0	813.1	813.3	813.5	813.5	813.3	813.0
135°	859.9	860.2	860.7	861.0	860.7	860.2	859.9	859.5	859.1	858.7	858.3
137.5°	902.5	902.4	902.3	902.2	902.3	902.4	902.5	902.7	902.5	902.1	901.6
140°	930.2	930.4	930.6	930.8	930.6	930.4	930.2	930.1	929.6	929.0	928.5
142.5°	954.4	954.4	954.5	954.5	954.5	954.4	954.4	954.3	954.2	953.7	953.3
145°	989.8	990.2	990.6	991.0	990.6	990.2	989.8	989.5	989.1	988.9	988.8
147.5°	1020.6	1020.8	1021.0	1021.1	1021.0	1020.8	1020.6	1020.4	1020.2	1020.0	1019.9
150°	1040.1	1040.3	1040.5	1040.7	1040.5	1040.3	1040.1	1039.9	1039.8	1039.8	1039.8
152.5°	1057.8	1057.7	1057.6	1057.5	1057.6	1057.7	1057.8	1057.9	1057.8	1057.5	1057.2
155°	1081.7	1081.2	1080.6	1080.0	1080.6	1081.2	1081.7	1082.3	1082.2	1081.4	1080.6
157.5°	1101.8	1100.8	1099.8	1098.8	1099.8	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8
160°	1114.8	1113.7	1112.5	1111.4	1112.5	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7
162.5°	1125.1	1123.8	1122.5	1121.1	1122.5	1123.8	1125.1	1126.4	1126.4	1125.3	1124.1
165°	1140.1	1138.4	1136.7	1134.9	1136.7	1138.4	1140.1	1141.9	1142.0	1140.5	1138.9
167.5°	1151.1	1149.1	1147.2	1145.2	1147.2	1149.1	1151.1	1153.0	1153.1	1151.4	1149.7
170°	1157.3	1155.4	1153.4	1151.5	1153.4	1155.4	1157.3	1159.3	1159.4	1157.9	1156.3
172.5°	1161.2	1159.2	1157.1	1154.9	1157.1	1159.2	1161.2	1163.4	1163.6	1162.1	1160.5
175°	1166.3	1164.0	1161.7	1159.3	1161.7	1164.0	1166.3	1168.6	1169.0	1167.2	1165.4
177.5°	1167.7	1165.9	1164.0	1162.2	1164.0	1165.9	1167.7	1169.6	1169.9	1168.6	1167.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	7.7	7.6	7.3	6.8	6.8	6.5	6.3	5.9	5.9	6.0	6.0
90°	20.3	19.2	17.7	16.1	14.6	13.0	11.1	9.0	6.9	4.7	2.6
92.5°	19.6	18.5	17.0	15.4	13.9	12.3	11.5	11.4	11.2	11.1	11.0
95°	20.3	19.2	19.0	18.8	18.6	18.4	21.6	28.2	34.8	41.4	48.0
97.5°	23.2	23.0	44.7	66.3	87.9	109.6	118.3	114.3	110.1	106.0	101.9
100°	35.1	38.4	65.2	91.9	118.6	145.4	157.0	153.5	150.1	146.5	143.1
102.5°	149.4	184.9	188.4	191.9	195.4	198.9	199.3	196.8	194.2	191.7	189.2
105°	273.9	272.2	271.2	270.3	269.2	268.3	267.3	266.0	264.9	263.7	262.6
107.5°	340.2	339.3	338.0	336.7	335.4	334.1	333.1	332.5	331.9	331.4	330.8
110°	385.1	384.7	383.6	382.4	381.3	380.0	379.2	378.6	378.0	377.5	376.9



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	428.6	428.7	428.1	427.6	427.1	426.5	425.7	424.6	423.6	422.6	421.5
115°	492.4	492.0	492.2	492.4	492.6	492.8	492.6	492.0	491.5	490.9	490.3
117.5°	557.5	557.6	557.2	556.7	556.3	555.9	555.3	554.5	553.7	552.9	552.2
120°	597.1	596.7	596.8	597.1	597.3	597.4	597.2	596.4	595.6	594.9	594.1
122.5°	636.7	636.5	636.2	635.9	635.7	635.4	635.0	634.6	634.0	633.6	633.2
125°	691.5	690.9	691.3	691.6	692.1	692.4	692.2	691.5	690.7	689.9	689.1
127.5°	747.0	747.1	746.1	745.3	744.4	743.5	743.0	742.8	742.6	742.4	742.2
130°	780.1	779.9	779.3	778.7	778.2	777.6	777.1	777.0	776.8	776.6	776.4
132.5°	812.9	812.7	811.9	811.2	810.5	809.8	809.2	808.8	808.5	808.1	807.8
135°	857.9	857.6	856.8	856.0	855.2	854.5	854.1	854.3	854.5	854.7	854.9
137.5°	901.2	900.8	899.9	899.1	898.2	897.3	896.9	896.8	896.7	896.6	896.6
140°	927.9	927.3	927.0	926.5	926.2	925.7	925.4	925.0	924.6	924.2	923.9
142.5°	952.9	952.4	952.2	951.9	951.7	951.5	951.1	950.4	949.6	948.9	948.2
145°	988.6	988.3	988.3	988.3	988.3	988.3	988.1	987.5	986.9	986.4	985.8
147.5°	1019.8	1019.6	1019.8	1020.0	1020.2	1020.4	1019.9	1018.8	1017.8	1016.7	1015.5
150°	1039.8	1039.8	1040.0	1040.3	1040.4	1040.6	1040.3	1039.6	1038.8	1038.0	1037.2
152.5°	1056.9	1056.6	1057.0	1057.3	1057.7	1058.0	1057.8	1057.2	1056.6	1056.0	1055.3
155°	1079.9	1079.1	1079.7	1080.3	1080.8	1081.4	1081.6	1081.4	1081.2	1081.1	1080.8
157.5°	1099.8	1098.8	1099.5	1100.1	1100.8	1101.5	1101.8	1101.9	1102.1	1102.2	1102.3
160°	1112.5	1111.4	1111.6	1111.7	1112.0	1112.2	1112.5	1113.1	1113.7	1114.3	1114.8
162.5°	1123.0	1121.8	1122.1	1122.2	1122.4	1122.6	1123.1	1123.8	1124.6	1125.3	1126.0
165°	1137.4	1135.8	1135.8	1135.8	1135.8	1135.8	1136.3	1137.2	1138.2	1139.2	1140.1
167.5°	1148.0	1146.2	1146.4	1146.5	1146.6	1146.8	1147.3	1148.3	1149.3	1150.3	1151.3
170°	1154.8	1153.2	1153.1	1152.9	1152.6	1152.4	1153.0	1154.1	1155.3	1156.4	1157.6
172.5°	1159.0	1157.4	1157.3	1157.0	1156.8	1156.7	1157.1	1158.3	1159.4	1160.6	1161.7
175°	1163.7	1162.0	1161.7	1161.6	1161.4	1161.2	1161.7	1162.9	1164.0	1165.2	1166.3
177.5°	1166.1	1164.9	1164.6	1164.3	1164.0	1163.7	1164.1	1165.2	1166.2	1167.3	1168.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	6.4	6.3	6.0	6.3	6.7	6.6	7.1	7.4	7.7	7.8	8.4
90°	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3	21.5
92.5°	11.1	11.2	11.4	11.5	12.3	13.9	15.4	17.0	18.5	19.6	20.8
95°	41.4	34.8	28.2	21.6	18.4	18.6	18.8	19.0	19.2	20.3	21.5
97.5°	106.0	110.1	114.3	118.3	109.6	87.9	66.3	44.7	23.0	23.2	23.2
100°	146.5	150.1	153.5	157.0	145.4	118.6	91.9	65.2	38.4	35.1	31.8
102.5°	191.7	194.2	196.8	199.3	198.9	195.4	191.9	188.4	184.9	149.4	113.8
105°	263.7	264.9	266.0	267.3	268.3	269.2	270.3	271.2	272.2	273.9	275.7
107.5°	331.4	331.9	332.5	333.1	334.1	335.4	336.7	338.0	339.3	340.2	341.0
110°	377.5	378.0	378.6	379.2	380.0	381.3	382.4	383.6	384.7	385.1	385.5



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	422.6	423.6	424.6	425.7	426.5	427.1	427.6	428.1	428.7	428.6	428.5
115°	490.9	491.5	492.0	492.6	492.8	492.6	492.4	492.2	492.0	492.4	492.8
117.5°	552.9	553.7	554.5	555.3	555.9	556.3	556.7	557.2	557.6	557.5	557.4
120°	594.9	595.6	596.4	597.2	597.4	597.3	597.1	596.8	596.7	597.1	597.4
122.5°	633.6	634.0	634.6	635.0	635.4	635.7	635.9	636.2	636.5	636.7	637.0
125°	689.9	690.7	691.5	692.2	692.4	692.1	691.6	691.3	690.9	691.5	692.1
127.5°	742.4	742.6	742.8	743.0	743.5	744.4	745.3	746.1	747.1	747.0	746.8
130°	776.6	776.8	777.0	777.1	777.6	778.2	778.7	779.3	779.9	780.1	780.2
132.5°	808.1	808.5	808.8	809.2	809.8	810.5	811.2	811.9	812.7	812.9	813.0
135°	854.7	854.5	854.3	854.1	854.5	855.2	856.0	856.8	857.6	857.9	858.3
137.5°	896.6	896.7	896.8	896.9	897.3	898.2	899.1	899.9	900.8	901.2	901.6
140°	924.2	924.6	925.0	925.4	925.7	926.2	926.5	927.0	927.3	927.9	928.5
142.5°	948.9	949.6	950.4	951.1	951.5	951.7	951.9	952.2	952.4	952.9	953.3
145°	986.4	986.9	987.5	988.1	988.3	988.3	988.3	988.3	988.3	988.6	988.8
147.5°	1016.7	1017.8	1018.8	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8	1019.9
150°	1038.0	1038.8	1039.6	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8	1039.8
152.5°	1056.0	1056.6	1057.2	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9	1057.2
155°	1081.1	1081.2	1081.4	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9	1080.6
157.5°	1102.2	1102.1	1101.9	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8	1100.8
160°	1114.3	1113.7	1113.1	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5	1113.7
162.5°	1125.3	1124.6	1123.8	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0	1124.1
165°	1139.2	1138.2	1137.2	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4	1138.9
167.5°	1150.3	1149.3	1148.3	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0	1149.7
170°	1156.4	1155.3	1154.1	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8	1156.3
172.5°	1160.6	1159.4	1158.3	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0	1160.5
175°	1165.2	1164.0	1162.9	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7	1165.4
177.5°	1167.3	1166.2	1165.2	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1	1167.4
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	8.3	8.4	8.7	8.6	8.7	8.6	8.8
90°	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	22.0	23.2	23.8	23.8	23.9	24.0	24.1
95°	22.6	23.8	24.5	24.7	24.9	25.1	25.3
97.5°	23.4	23.5	23.7	23.8	24.0	24.2	24.5
100°	28.5	25.2	23.7	23.8	24.0	24.2	24.5
102.5°	78.3	42.7	25.0	25.0	25.1	25.1	25.1
105°	277.4	279.1	276.6	269.6	262.6	255.6	248.7
107.5°	341.9	342.8	343.5	344.3	345.0	345.8	346.5
110°	385.9	386.2	386.8	387.4	387.9	388.5	389.1



TEST NUMBER: P333023-935

CATALOG NUMBER: S124RDIW-S350D1050U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	428.4	428.3	428.7	429.5	430.2	430.9	431.6
115°	493.2	493.5	493.8	493.8	493.8	493.8	493.8
117.5°	557.4	557.3	557.2	557.2	557.1	557.0	556.9
120°	597.9	598.2	598.2	597.9	597.4	597.1	596.7
122.5°	637.1	637.4	637.3	637.0	636.5	636.2	635.8
125°	692.7	693.2	693.6	693.8	694.0	694.2	694.4
127.5°	746.7	746.6	746.5	746.3	746.1	746.0	745.9
130°	780.5	780.7	780.8	780.8	780.8	780.8	780.8
132.5°	813.3	813.5	813.5	813.3	813.1	813.0	812.9
135°	858.7	859.1	859.5	859.9	860.2	860.7	861.0
137.5°	902.1	902.5	902.7	902.5	902.4	902.3	902.2
140°	929.0	929.6	930.1	930.2	930.4	930.6	930.8
142.5°	953.7	954.2	954.3	954.4	954.4	954.5	954.5
145°	988.9	989.1	989.5	989.8	990.2	990.6	991.0
147.5°	1020.0	1020.2	1020.4	1020.6	1020.8	1021.0	1021.1
150°	1039.8	1039.8	1039.9	1040.1	1040.3	1040.5	1040.7
152.5°	1057.5	1057.8	1057.9	1057.8	1057.7	1057.6	1057.5
155°	1081.4	1082.2	1082.3	1081.7	1081.2	1080.6	1080.0
157.5°	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8
160°	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4
162.5°	1125.3	1126.4	1126.4	1125.1	1123.8	1122.5	1121.1
165°	1140.5	1142.0	1141.9	1140.1	1138.4	1136.7	1134.9
167.5°	1151.4	1153.1	1153.0	1151.1	1149.1	1147.2	1145.2
170°	1157.9	1159.4	1159.3	1157.3	1155.4	1153.4	1151.5
172.5°	1162.1	1163.6	1163.4	1161.2	1159.2	1157.1	1154.9
175°	1167.2	1169.0	1168.6	1166.3	1164.0	1161.7	1159.3
177.5°	1168.6	1169.9	1169.6	1167.7	1165.9	1164.0	1162.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3

(END OF REPORT)