

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333045-830

Luminaire Tested: **S124RDIW-S575D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333045-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1050U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6166.3 lumens
Efficiency: N/A
Efficacy: 136.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333045-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333045-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P333045-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.5
10°-20°	250.9	4.1
20°-30°	362.3	5.9
30°-40°	410.7	6.7
40°-50°	396.6	6.4
50°-60°	329.8	5.3
60°-70°	227.7	3.7
70°-80°	115.4	1.9
80°-90°	33.3	0.5
90°-100°	43.7	0.7
100°-110°	278.4	4.5
110°-120°	532.6	8.6
120°-130°	676.2	11.0
130°-140°	723.4	11.7
140°-150°	676.5	11.0
150°-160°	545.5	8.8
160°-170°	351.9	5.7
170°-180°	121.3	2.0
0°-30°	703.2	11.4
0°-40°	1113.9	18.1
0°-60°	1840.3	29.8
0°-90°	2216.8	36.0
90°-120°	854.7	13.9
90°-150°	2930.8	47.5
90°-180°	3949.0	64.0
0°-180°	6166.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	3	13	21	27	29	4
95°	52	22	21	26	28	68
105°	288	293	298	304	272	301
115°	537	539	539	540	540	528
125°	754	758	756	759	760	673
135°	936	935	939	941	942	721
145°	1079	1082	1082	1083	1085	674
155°	1183	1184	1181	1185	1182	545
165°	1248	1244	1243	1250	1242	353
175°	1277	1271	1272	1280	1269	122
180°	1277	1277	1277	1277	1277	



TEST NUMBER: P333045-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	14.0	13.5	12.9	12.3	11.8	11.6	11.8	12.0	12.3	12.4	12.5
90°	2.8	5.2	7.5	9.9	12.2	14.2	15.9	17.6	19.3	21.0	22.2
92.5°	12.1	12.2	12.3	12.4	12.5	13.5	15.2	16.9	18.6	20.3	21.5
95°	52.5	45.3	38.1	30.9	23.7	20.2	20.4	20.5	20.8	21.0	22.2
97.5°	111.5	116.0	120.6	125.1	129.5	120.0	96.2	72.6	48.9	25.2	25.4
100°	156.7	160.4	164.3	168.1	171.9	159.2	129.9	100.6	71.4	42.0	38.5
102.5°	207.1	209.8	212.6	215.5	218.2	217.7	214.0	210.1	206.2	202.5	163.5
105°	287.5	288.7	290.0	291.2	292.6	293.7	294.7	295.9	296.9	297.9	299.8
107.5°	362.1	362.8	363.4	364.0	364.7	365.7	367.1	368.6	370.0	371.5	372.4
110°	412.6	413.2	413.8	414.4	415.1	416.0	417.4	418.6	419.9	421.1	421.6



TEST NUMBER: P333045-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.5	462.6	463.7	464.9	466.0	466.9	467.5	468.1	468.6	469.3	469.2
115°	536.7	537.3	538.0	538.6	539.2	539.4	539.2	539.0	538.9	538.6	539.0
117.5°	604.5	605.3	606.1	607.0	607.8	608.5	609.0	609.4	609.9	610.4	610.3
120°	650.4	651.2	652.1	652.9	653.7	654.0	653.8	653.7	653.4	653.2	653.7
122.5°	693.1	693.6	694.1	694.7	695.1	695.6	695.9	696.2	696.4	696.7	697.0
125°	754.4	755.3	756.1	757.0	757.8	758.0	757.6	757.1	756.8	756.3	757.0
127.5°	812.5	812.7	812.9	813.1	813.3	813.9	814.9	815.9	816.8	817.8	817.7
130°	849.9	850.2	850.4	850.6	850.7	851.2	851.9	852.4	853.1	853.8	853.9
132.5°	884.3	884.7	885.0	885.4	885.8	886.5	887.2	888.1	888.8	889.7	889.9
135°	935.9	935.7	935.5	935.2	935.0	935.4	936.2	937.1	937.9	938.8	939.1
137.5°	981.5	981.6	981.7	981.8	981.8	982.3	983.3	984.2	985.1	986.1	986.6
140°	1011.3	1011.7	1012.2	1012.6	1013.0	1013.4	1013.9	1014.3	1014.7	1015.1	1015.8
142.5°	1038.0	1038.8	1039.5	1040.4	1041.1	1041.6	1041.9	1042.1	1042.4	1042.6	1043.1
145°	1079.1	1079.8	1080.3	1081.0	1081.7	1081.9	1081.9	1081.9	1081.9	1081.9	1082.2
147.5°	1111.7	1113.0	1114.2	1115.3	1116.5	1117.0	1116.8	1116.6	1116.3	1116.2	1116.3
150°	1135.5	1136.3	1137.2	1138.0	1138.9	1139.2	1139.0	1138.8	1138.5	1138.3	1138.3
152.5°	1155.3	1156.0	1156.7	1157.3	1158.0	1158.2	1157.8	1157.4	1157.1	1156.7	1157.0
155°	1183.2	1183.5	1183.6	1183.8	1184.0	1183.8	1183.2	1182.6	1181.9	1181.3	1182.1
157.5°	1206.7	1206.5	1206.5	1206.3	1206.2	1205.8	1205.0	1204.3	1203.6	1202.9	1204.0
160°	1220.4	1219.8	1219.2	1218.5	1217.9	1217.5	1217.3	1217.0	1216.8	1216.6	1217.9
162.5°	1232.7	1231.9	1231.1	1230.2	1229.5	1228.9	1228.7	1228.5	1228.3	1228.0	1229.4
165°	1248.1	1247.1	1246.0	1244.9	1243.9	1243.4	1243.4	1243.4	1243.4	1243.4	1245.1
167.5°	1260.4	1259.2	1258.2	1257.1	1255.9	1255.4	1255.2	1255.1	1255.0	1254.8	1256.7
170°	1267.2	1265.9	1264.7	1263.4	1262.2	1261.6	1261.8	1262.1	1262.3	1262.4	1264.1
172.5°	1271.8	1270.5	1269.2	1268.0	1266.7	1266.2	1266.4	1266.6	1266.9	1267.1	1268.8
175°	1276.8	1275.5	1274.2	1273.0	1271.7	1271.2	1271.4	1271.6	1271.8	1272.1	1273.9
177.5°	1279.0	1277.9	1276.7	1275.5	1274.3	1273.9	1274.2	1274.6	1274.9	1275.3	1276.6
180°	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8



TEST NUMBER: P333045-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	12.6	12.8	12.9	13.1	13.3	13.5	13.8	13.9
90°	23.6	24.8	26.1	27.0	27.3	27.8	28.2	28.7
92.5°	22.8	24.0	25.4	26.0	26.1	26.2	26.3	26.4
95°	23.6	24.8	26.1	26.9	27.1	27.2	27.5	27.7
97.5°	25.4	25.6	25.7	25.9	26.1	26.3	26.5	26.8
100°	34.8	31.2	27.6	25.9	26.1	26.3	26.5	26.8
102.5°	124.6	85.7	46.8	27.3	27.3	27.4	27.4	27.5
105°	301.8	303.7	305.6	302.7	295.1	287.5	279.8	272.2
107.5°	373.3	374.3	375.2	376.1	376.9	377.7	378.5	379.3
110°	422.0	422.4	422.8	423.4	424.0	424.6	425.3	425.9



TEST NUMBER: P333045-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	469.1	469.0	468.9	469.3	470.1	470.9	471.7	472.5
115°	539.4	539.9	540.3	540.5	540.5	540.5	540.5	540.5
117.5°	610.2	610.2	610.1	610.0	609.9	609.8	609.7	609.6
120°	654.0	654.5	654.9	654.9	654.5	654.0	653.7	653.2
122.5°	697.3	697.5	697.8	697.7	697.3	696.8	696.4	696.0
125°	757.6	758.3	758.8	759.3	759.5	759.7	760.0	760.2
127.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.6	816.5
130°	854.1	854.4	854.6	854.7	854.7	854.7	854.7	854.7
132.5°	890.0	890.3	890.5	890.5	890.3	890.1	890.0	889.9
135°	939.6	940.0	940.5	940.8	941.3	941.7	942.2	942.5
137.5°	987.0	987.5	988.0	988.2	988.0	987.9	987.8	987.6
140°	1016.4	1017.0	1017.7	1018.1	1018.3	1018.5	1018.7	1019.0
142.5°	1043.6	1044.1	1044.5	1044.7	1044.8	1044.8	1044.9	1044.9
145°	1082.4	1082.6	1082.8	1083.2	1083.5	1084.0	1084.4	1084.9
147.5°	1116.5	1116.6	1116.8	1117.0	1117.3	1117.5	1117.7	1117.9
150°	1138.3	1138.3	1138.3	1138.4	1138.6	1138.9	1139.1	1139.3
152.5°	1157.3	1157.6	1158.0	1158.1	1158.0	1157.8	1157.7	1157.6
155°	1183.0	1183.8	1184.7	1184.8	1184.1	1183.6	1182.9	1182.2
157.5°	1205.0	1206.2	1207.3	1207.3	1206.2	1205.0	1204.0	1202.9
160°	1219.2	1220.4	1221.7	1221.7	1220.4	1219.2	1217.9	1216.6
162.5°	1230.6	1231.9	1233.1	1233.1	1231.6	1230.2	1228.8	1227.3
165°	1246.8	1248.5	1250.2	1250.0	1248.1	1246.2	1244.3	1242.4
167.5°	1258.6	1260.5	1262.3	1262.2	1260.1	1257.9	1255.8	1253.7
170°	1265.8	1267.5	1269.2	1269.0	1266.9	1264.8	1262.6	1260.6
172.5°	1270.5	1272.1	1273.8	1273.6	1271.2	1268.9	1266.7	1264.3
175°	1275.8	1277.7	1279.7	1279.3	1276.8	1274.2	1271.7	1269.1
177.5°	1278.0	1279.3	1280.7	1280.3	1278.3	1276.3	1274.2	1272.2
180°	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8

(END OF REPORT)