

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333038-830

Luminaire Tested: **S124RDIW-S575D470U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333038-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D470U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3746.9 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333038-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333038-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P333038-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.0	2.4
10°-20°	250.9	6.7
20°-30°	362.3	9.7
30°-40°	410.7	11.0
40°-50°	396.6	10.6
50°-60°	329.8	8.8
60°-70°	227.7	6.1
70°-80°	115.4	3.1
80°-90°	31.3	0.8
90°-100°	36.4	1.0
100°-110°	107.9	2.9
110°-120°	183.1	4.9
120°-130°	241.5	6.4
130°-140°	271.2	7.2
140°-150°	266.5	7.1
150°-160°	224.1	6.0
160°-170°	149.1	4.0
170°-180°	52.2	1.4
0°-30°	703.2	18.8
0°-40°	1113.9	29.7
0°-60°	1840.3	49.1
0°-90°	2214.8	59.1
90°-120°	327.5	8.7
90°-150°	1106.7	29.5
90°-180°	1532.0	40.9
0°-180°	3746.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	1	6	9	12	13	3
95°	26	29	32	34	34	29
105°	100	100	102	103	104	106
115°	186	186	185	185	184	184
125°	271	271	271	270	269	242
135°	350	352	352	352	350	270
145°	425	427	427	427	425	266
155°	487	487	486	488	486	224
165°	530	529	528	530	529	149
175°	551	549	549	552	549	52
180°	552	552	552	552	552	



TEST NUMBER: P333038-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	13.8	12.9	12.1	11.2	10.4	10.0	10.0	10.1	10.1	10.1	10.1
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	9.1	10.4	11.5	12.7	13.9	14.8	15.4	15.8	16.4	16.9	17.2
95°	25.6	26.5	27.3	28.2	29.0	29.8	30.4	31.1	31.8	32.4	32.7
97.5°	44.8	45.4	46.1	46.8	47.5	48.3	49.0	49.8	50.5	51.4	51.7
100°	59.8	60.1	60.5	60.9	61.4	61.9	62.8	63.6	64.5	65.3	65.5
102.5°	75.5	75.7	75.8	76.0	76.2	76.6	77.4	78.1	78.9	79.7	79.9
105°	99.5	99.6	99.7	99.8	99.9	100.1	100.5	100.9	101.2	101.6	101.9
107.5°	124.7	124.8	125.0	125.1	125.2	125.3	125.4	125.4	125.5	125.5	125.7
110°	141.8	141.9	142.1	142.3	142.5	142.6	142.5	142.4	142.3	142.2	142.0



TEST NUMBER: P333038-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.6	159.6	159.7	159.7	159.8	159.7	159.5	159.3	159.1	159.0	158.9
115°	186.2	186.2	186.2	186.2	186.2	186.2	186.0	185.8	185.6	185.4	185.3
117.5°	211.3	211.4	211.5	211.6	211.6	211.6	211.5	211.3	211.2	211.0	210.8
120°	228.1	228.5	228.8	229.2	229.6	229.6	229.3	229.0	228.8	228.5	228.0
122.5°	245.5	245.6	245.8	245.9	246.1	246.1	246.0	245.8	245.7	245.6	245.2
125°	271.2	271.2	271.2	271.2	271.2	271.2	271.1	271.0	270.9	270.8	270.6
127.5°	294.5	294.8	295.1	295.4	295.7	295.8	295.6	295.4	295.3	295.1	294.9
130°	310.9	311.2	311.5	311.8	312.1	312.2	312.2	312.2	312.2	312.2	312.0
132.5°	327.6	327.9	328.1	328.3	328.5	328.6	328.5	328.4	328.4	328.3	328.1
135°	349.8	350.3	350.9	351.5	352.0	352.3	352.3	352.3	352.3	352.3	352.1
137.5°	373.9	374.2	374.4	374.7	374.9	375.1	375.3	375.5	375.6	375.8	375.5
140°	389.9	390.1	390.3	390.5	390.7	390.8	390.8	390.8	390.8	390.8	390.7
142.5°	404.6	404.8	405.0	405.2	405.4	405.5	405.4	405.3	405.2	405.1	405.1
145°	425.0	425.4	425.7	426.1	426.5	426.7	426.8	426.9	427.0	427.1	427.0
147.5°	445.2	445.5	446.0	446.5	447.0	447.1	447.0	447.0	447.0	446.9	446.8
150°	457.4	457.8	458.2	458.5	458.9	459.1	459.1	459.1	459.1	459.1	459.1
152.5°	469.0	469.3	469.5	469.8	470.0	470.1	470.1	470.2	470.3	470.4	470.6
155°	486.9	486.9	486.9	486.9	486.9	486.8	486.7	486.6	486.5	486.4	486.8
157.5°	501.9	501.7	501.6	501.4	501.2	501.1	501.1	501.1	501.1	501.1	501.3
160°	510.9	510.8	510.7	510.6	510.5	510.4	510.3	510.2	510.1	510.0	510.3
162.5°	519.1	518.8	518.5	518.3	518.0	517.8	517.7	517.6	517.6	517.5	518.0
165°	530.0	529.7	529.4	529.1	528.9	528.7	528.5	528.3	528.1	527.9	528.5
167.5°	538.5	538.1	537.7	537.3	536.9	536.7	536.7	536.8	536.8	536.8	537.3
170°	543.3	542.8	542.3	541.9	541.4	541.2	541.3	541.4	541.5	541.6	542.2
172.5°	546.7	546.3	545.9	545.5	545.1	544.9	544.9	545.0	545.0	545.0	545.6
175°	551.4	550.9	550.4	550.0	549.5	549.2	549.1	549.0	548.9	548.8	549.5
177.5°	552.9	552.5	552.1	551.8	551.4	551.2	551.2	551.2	551.2	551.2	551.8
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2



TEST NUMBER: P333038-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	10.1	10.1	10.0	10.1	10.3	10.5	10.7	10.7
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	17.6	17.9	18.3	18.5	18.7	18.8	18.9	18.9
95°	33.0	33.3	33.6	33.7	33.7	33.7	33.7	33.7
97.5°	52.0	52.4	52.7	52.9	52.9	52.9	52.9	52.9
100°	65.7	65.9	66.1	66.2	66.2	66.2	66.2	66.2
102.5°	80.2	80.5	80.8	81.0	81.0	81.1	81.2	81.2
105°	102.3	102.5	102.8	103.1	103.4	103.7	104.0	104.2
107.5°	126.0	126.3	126.6	126.7	126.7	126.7	126.6	126.6
110°	141.9	141.7	141.5	141.5	141.8	142.0	142.3	142.6





TEST NUMBER: P333038-830

CATALOG NUMBER: S124RDIW-S575D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.9	158.8	158.8	158.8	158.9	158.9	159.0	159.0
115°	185.2	185.1	185.0	184.9	184.8	184.7	184.6	184.5
117.5°	210.5	210.1	209.8	209.5	209.3	209.2	209.0	208.8
120°	227.5	227.1	226.6	226.5	226.7	226.9	227.1	227.2
122.5°	245.0	244.6	244.3	243.9	243.6	243.3	242.9	242.6
125°	270.4	270.2	270.0	269.8	269.7	269.5	269.3	269.1
127.5°	294.7	294.5	294.4	294.2	294.1	293.9	293.8	293.6
130°	311.8	311.6	311.4	311.1	310.8	310.4	310.0	309.6
132.5°	327.9	327.7	327.5	327.3	327.2	327.1	326.9	326.8
135°	351.9	351.8	351.6	351.4	351.1	350.8	350.5	350.2
137.5°	375.2	375.0	374.8	374.7	374.8	374.8	374.8	374.9
140°	390.6	390.5	390.4	390.3	390.2	390.1	390.0	389.9
142.5°	405.1	405.1	405.1	405.0	405.0	405.0	405.0	405.0
145°	426.9	426.8	426.7	426.5	426.2	425.9	425.7	425.4
147.5°	446.7	446.6	446.6	446.5	446.4	446.3	446.2	446.1
150°	459.1	459.1	459.1	459.1	459.0	458.9	458.8	458.7
152.5°	470.9	471.1	471.4	471.3	471.1	470.8	470.6	470.3
155°	487.2	487.6	488.0	488.0	487.6	487.2	486.8	486.4
157.5°	501.6	501.9	502.2	502.2	501.9	501.5	501.2	500.9
160°	510.6	510.9	511.1	511.0	510.6	510.1	509.5	509.1
162.5°	518.5	519.1	519.5	519.5	519.1	518.6	518.1	517.6
165°	529.0	529.6	530.2	530.3	529.9	529.5	529.1	528.8
167.5°	537.9	538.5	539.0	539.0	538.5	537.9	537.2	536.7
170°	542.7	543.3	543.8	543.8	543.1	542.4	541.8	541.1
172.5°	546.3	547.0	547.5	547.5	546.9	546.2	545.5	544.9
175°	550.2	550.8	551.5	551.5	550.8	550.2	549.5	548.8
177.5°	552.3	552.8	553.4	553.3	552.7	552.1	551.5	550.9
180°	552.2	552.2	552.2	552.2	552.2	552.2	552.2	552.2

(END OF REPORT)