

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333041-830

Luminaire Tested: **S124RDIW-S575D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333041-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D770U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5109.3 lumens  
Efficiency: N/A  
Efficacy: 135.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333041-830

CATALOG NUMBER: S124RDIW-S575D770U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333041-830

CATALOG NUMBER: S124RDIW-S575D770U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P333041-830

CATALOG NUMBER: S124RDIW-S575D770U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.0	1.8
10°-20°	250.9	4.9
20°-30°	362.3	7.1
30°-40°	410.7	8.0
40°-50°	396.6	7.8
50°-60°	329.8	6.5
60°-70°	227.7	4.5
70°-80°	115.4	2.3
80°-90°	32.3	0.6
90°-100°	32.0	0.6
100°-110°	204.0	4.0
110°-120°	390.2	7.6
120°-130°	495.4	9.7
130°-140°	530.0	10.4
140°-150°	495.6	9.7
150°-160°	399.7	7.8
160°-170°	257.8	5.0
170°-180°	88.8	1.7
0°-30°	703.2	13.8
0°-40°	1113.9	21.8
0°-60°	1840.3	36.0
0°-90°	2215.8	43.4
90°-120°	626.2	12.3
90°-150°	2147.2	42.0
90°-180°	2894.0	56.6
0°-180°	5109.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	2	10	15	19	21	4
95°	38	16	15	19	20	49
105°	211	215	218	223	199	220
115°	393	395	394	396	396	387
125°	553	555	554	556	557	493
135°	686	685	688	689	690	528
145°	791	793	793	793	795	494
155°	867	867	865	868	866	400
165°	914	911	911	916	910	258
175°	935	932	932	937	930	89
180°	935	935	935	935	935	



TEST NUMBER: P333041-830

CATALOG NUMBER: S124RDIW-S575D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	13.9	13.2	12.5	11.8	11.1	10.8	10.9	11.0	11.2	11.3	11.3
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	8.9	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7
95°	38.5	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3
97.5°	81.7	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6
100°	114.7	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2
102.5°	151.7	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8
105°	210.6	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7
107.5°	265.3	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9
110°	302.3	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9



TEST NUMBER: P333041-830

CATALOG NUMBER: S124RDIW-S575D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	338.1	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7
115°	393.2	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9
117.5°	442.9	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1
120°	476.5	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9
122.5°	507.8	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7
125°	552.7	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6
127.5°	595.2	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1
130°	622.6	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7
132.5°	647.9	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0
135°	685.6	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1
137.5°	719.1	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7
140°	740.9	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1
142.5°	760.5	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2
145°	790.6	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9
147.5°	814.5	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8
150°	831.9	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0
152.5°	846.4	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6
155°	866.9	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1
157.5°	884.1	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0
160°	894.1	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3
162.5°	903.1	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7
165°	914.5	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2
167.5°	923.4	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7
170°	928.4	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1
172.5°	931.8	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5
175°	935.4	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3
177.5°	937.1	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P333041-830

CATALOG NUMBER: S124RDIW-S575D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	11.4	11.5	11.5	11.7	11.9	12.1	12.3	12.4
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	16.7	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	17.2	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.7	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	25.5	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	91.3	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	221.1	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	273.5	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.2	309.4	309.8	310.2	310.7	311.1	311.6	312.1





TEST NUMBER: P333041-830

CATALOG NUMBER: S124RDIW-S575D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	343.7	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.2	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	510.9	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.1	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	599.0	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.8	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.1	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.3	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.1	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	744.6	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.6	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.0	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	817.9	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	847.9	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	866.7	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	901.6	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	913.4	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	922.1	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	927.4	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	930.8	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	934.7	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	936.3	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)