

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333027-935

Luminaire Tested: **S124RDIW-S350D1340U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333027-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1340U935-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5901.4 lumens  
Efficiency: N/A  
Efficacy: 126.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	88	84	81	81	78	75	72	59	57	56	42	41	40	27	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	37	36	34	24	23	22	16
3	76	67	61	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.0	0.8
10°-20°	147.8	2.5
20°-30°	231.2	3.9
30°-40°	257.0	4.4
40°-50°	228.0	3.9
50°-60°	177.7	3.0
60°-70°	116.3	2.0
70°-80°	57.2	1.0
80°-90°	18.4	0.3
90°-100°	51.1	0.9
100°-110°	325.6	5.5
110°-120°	622.9	10.6
120°-130°	790.7	13.4
130°-140°	846.0	14.3
140°-150°	791.1	13.4
150°-160°	638.0	10.8
160°-170°	411.5	7.0
170°-180°	141.8	2.4
0°-30°	428.0	7.3
0°-40°	685.0	11.6
0°-60°	1090.8	18.5
0°-90°	1282.7	21.7
90°-120°	999.5	16.9
90°-150°	3427.4	58.1
90°-180°	4619.0	78.3
0°-180°	5901.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	34	3	34	3	34	15
95°	32	61	32	61	32	26
105°	318	336	318	336	318	278
115°	632	628	632	628	632	626
125°	889	882	889	882	889	792
135°	1102	1094	1102	1094	1102	848
145°	1269	1262	1269	1262	1269	793
155°	1383	1384	1383	1384	1383	638
165°	1453	1460	1453	1460	1453	410
175°	1484	1493	1484	1493	1484	141
180°	1493	1493	1493	1493	1493	



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	10.2	10.0	10.1	10.0	10.1	9.7	9.6	9.6	9.0	8.9	8.4
90°	33.5	33.0	32.5	32.0	31.5	30.6	29.0	27.6	26.1	24.5	22.6
92.5°	30.8	30.7	30.7	30.6	30.4	29.6	28.2	26.7	25.1	23.7	21.7
95°	32.4	32.1	31.9	31.6	31.4	30.6	29.0	27.6	26.1	24.5	24.3
97.5°	31.3	31.0	30.7	30.6	30.3	30.0	30.0	29.8	29.6	29.4	27.2
100°	31.3	31.0	30.7	30.6	30.3	32.3	36.5	40.7	44.9	49.2	83.3
102.5°	32.2	32.1	32.0	32.0	31.9	54.7	100.2	145.8	191.2	236.8	241.3
105°	318.3	327.2	336.1	345.1	354.0	357.4	355.2	352.9	350.7	348.4	347.2
107.5°	443.6	442.6	441.7	440.7	439.8	438.8	437.7	436.6	435.5	434.5	432.7
110°	498.1	497.3	496.6	495.8	495.1	494.5	494.0	493.5	493.0	492.5	491.0



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	552.6	551.6	550.7	549.7	548.8	548.4	548.5	548.5	548.7	548.8	548.1
115°	632.1	632.1	632.1	632.1	632.1	631.8	631.4	630.9	630.3	629.8	630.1
117.5°	712.9	713.1	713.2	713.3	713.3	713.4	713.5	713.6	713.8	713.9	713.3
120°	763.9	764.4	764.8	765.3	765.9	765.9	765.3	764.8	764.4	763.9	764.1
122.5°	813.9	814.4	814.9	815.4	815.9	816.0	815.7	815.4	815.1	814.8	814.4
125°	889.0	888.7	888.5	888.2	887.9	887.4	886.7	886.0	885.2	884.5	884.9
127.5°	954.8	955.0	955.2	955.5	955.6	955.8	956.0	956.1	956.2	956.4	955.3
130°	999.5	999.5	999.5	999.5	999.5	999.4	999.1	998.8	998.7	998.4	997.6
132.5°	1040.6	1040.8	1041.0	1041.2	1041.4	1041.4	1041.1	1040.9	1040.6	1040.3	1039.4
135°	1102.3	1101.7	1101.2	1100.8	1100.3	1099.8	1099.2	1098.8	1098.3	1097.8	1096.8
137.5°	1154.9	1155.1	1155.3	1155.4	1155.5	1155.4	1154.8	1154.3	1153.7	1153.1	1152.1
140°	1191.6	1191.4	1191.1	1190.8	1190.6	1190.1	1189.4	1188.6	1187.8	1187.1	1186.6
142.5°	1221.9	1221.9	1221.8	1221.8	1221.8	1221.5	1220.9	1220.4	1219.9	1219.3	1219.0
145°	1268.7	1268.2	1267.7	1267.1	1266.7	1266.3	1266.0	1265.8	1265.6	1265.3	1265.3
147.5°	1307.3	1307.0	1306.8	1306.6	1306.3	1306.1	1305.9	1305.7	1305.4	1305.3	1305.5
150°	1332.3	1332.1	1331.8	1331.5	1331.3	1331.2	1331.2	1331.2	1331.2	1331.2	1331.5
152.5°	1353.8	1353.9	1354.0	1354.2	1354.4	1354.2	1353.8	1353.4	1353.1	1352.6	1353.1
155°	1382.6	1383.3	1384.1	1384.8	1385.5	1385.4	1384.4	1383.5	1382.4	1381.5	1382.2
157.5°	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7	1407.6
160°	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8	1423.0
162.5°	1435.3	1436.9	1438.6	1440.4	1442.0	1442.1	1440.6	1439.2	1437.6	1436.1	1436.4
165°	1452.9	1455.2	1457.4	1459.7	1461.8	1462.0	1460.0	1458.0	1456.0	1454.1	1454.1
167.5°	1466.1	1468.6	1471.0	1473.5	1476.0	1476.2	1473.9	1471.8	1469.6	1467.4	1467.6
170°	1474.1	1476.6	1479.1	1481.6	1484.0	1484.3	1482.3	1480.3	1478.3	1476.4	1476.1
172.5°	1478.6	1481.3	1483.9	1486.6	1489.4	1489.7	1487.7	1485.7	1483.7	1481.7	1481.4
175°	1484.2	1487.1	1490.1	1493.1	1496.1	1496.5	1494.3	1492.0	1489.8	1487.5	1487.3
177.5°	1487.7	1490.1	1492.5	1494.9	1497.3	1497.7	1496.1	1494.5	1492.9	1491.3	1490.9
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	8.0	7.5	7.4	6.9	6.5	6.6	6.6	6.2	6.3	6.3	6.4
90°	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4	6.1	8.8	11.5
92.5°	19.7	17.7	15.8	14.6	14.6	14.4	14.2	14.0	14.2	14.4	14.6
95°	24.1	23.8	23.6	27.6	36.1	44.5	53.0	61.4	53.0	44.5	36.1
97.5°	84.9	112.5	140.3	151.4	146.2	140.9	135.7	130.4	135.7	140.9	146.2
100°	117.6	151.9	186.1	201.0	196.6	192.1	187.6	183.1	187.6	192.1	196.6
102.5°	245.7	250.1	254.6	255.2	251.9	248.7	245.4	242.1	245.4	248.7	251.9
105°	345.9	344.7	343.5	342.1	340.6	339.1	337.6	336.1	337.6	339.1	340.6
107.5°	431.0	429.4	427.7	426.5	425.7	425.0	424.2	423.4	424.2	425.0	425.7
110°	489.5	488.0	486.6	485.4	484.7	484.0	483.2	482.4	483.2	484.0	484.7





TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	547.4	546.7	546.0	545.0	543.6	542.3	541.0	539.6	541.0	542.3	543.6
115°	630.3	630.6	630.9	630.6	629.8	629.1	628.4	627.6	628.4	629.1	629.8
117.5°	712.7	712.2	711.6	710.8	709.9	708.9	707.9	706.9	707.9	708.9	709.9
120°	764.4	764.7	764.8	764.5	763.5	762.5	761.5	760.5	761.5	762.5	763.5
122.5°	814.1	813.7	813.4	813.0	812.4	811.8	811.1	810.5	811.1	811.8	812.4
125°	885.5	886.0	886.5	886.2	885.2	884.2	883.2	882.3	883.2	884.2	885.2
127.5°	954.1	953.0	951.8	951.1	950.9	950.6	950.4	950.1	950.4	950.6	950.9
130°	996.9	996.2	995.4	994.9	994.6	994.5	994.2	993.9	994.2	994.5	994.6
132.5°	1038.5	1037.6	1036.6	1035.9	1035.4	1035.0	1034.6	1034.1	1034.6	1035.0	1035.4
135°	1095.8	1094.8	1093.8	1093.5	1093.7	1093.9	1094.2	1094.4	1094.2	1093.9	1093.7
137.5°	1151.0	1149.9	1148.8	1148.2	1148.1	1148.0	1147.9	1147.8	1147.9	1148.0	1148.1
140°	1186.1	1185.6	1185.2	1184.6	1184.1	1183.6	1183.2	1182.7	1183.2	1183.6	1184.1
142.5°	1218.7	1218.4	1218.1	1217.5	1216.6	1215.7	1214.8	1213.9	1214.8	1215.7	1216.6
145°	1265.3	1265.3	1265.3	1264.9	1264.2	1263.4	1262.7	1262.0	1262.7	1263.4	1264.2
147.5°	1305.8	1306.1	1306.3	1305.7	1304.3	1303.0	1301.5	1300.1	1301.5	1303.0	1304.3
150°	1331.7	1332.0	1332.1	1331.8	1330.8	1329.8	1328.9	1327.8	1328.9	1329.8	1330.8
152.5°	1353.5	1354.0	1354.4	1354.3	1353.4	1352.6	1351.9	1351.1	1351.9	1352.6	1353.4
155°	1382.9	1383.7	1384.4	1384.7	1384.4	1384.1	1383.9	1383.7	1383.9	1384.1	1384.4
157.5°	1408.3	1409.2	1410.1	1410.6	1410.7	1410.8	1411.0	1411.2	1411.0	1410.8	1410.7
160°	1423.2	1423.5	1423.7	1424.3	1425.0	1425.7	1426.5	1427.2	1426.5	1425.7	1425.0
162.5°	1436.7	1436.9	1437.2	1437.8	1438.7	1439.7	1440.5	1441.5	1440.5	1439.7	1438.7
165°	1454.1	1454.1	1454.1	1454.7	1455.9	1457.2	1458.4	1459.7	1458.4	1457.2	1455.9
167.5°	1467.7	1467.9	1468.0	1468.8	1470.1	1471.4	1472.7	1473.9	1472.7	1471.4	1470.1
170°	1475.8	1475.6	1475.4	1476.0	1477.5	1478.9	1480.5	1482.0	1480.5	1478.9	1477.5
172.5°	1481.3	1481.0	1480.7	1481.4	1482.8	1484.4	1485.8	1487.3	1485.8	1484.4	1482.8
175°	1487.0	1486.8	1486.5	1487.1	1488.7	1490.1	1491.6	1493.1	1491.6	1490.1	1488.7
177.5°	1490.6	1490.1	1489.7	1490.2	1491.6	1493.0	1494.4	1495.8	1494.4	1493.0	1491.6
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	6.9	7.2	7.7	7.7	8.3	8.7	8.8	9.1	9.6	9.6	9.7
90°	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6	29.0	30.6	31.5
92.5°	14.6	15.8	17.7	19.7	21.7	23.7	25.1	26.7	28.2	29.6	30.4
95°	27.6	23.6	23.8	24.1	24.3	24.5	26.1	27.6	29.0	30.6	31.4
97.5°	151.4	140.3	112.5	84.9	57.2	29.4	29.6	29.8	30.0	30.0	30.3
100°	201.0	186.1	151.9	117.6	83.3	49.2	44.9	40.7	36.5	32.3	30.3
102.5°	255.2	254.6	250.1	245.7	241.3	236.8	191.2	145.8	100.2	54.7	31.9
105°	342.1	343.5	344.7	345.9	347.2	348.4	350.7	352.9	355.2	357.4	354.0
107.5°	426.5	427.7	429.4	431.0	432.7	434.5	435.5	436.6	437.7	438.8	439.8
110°	485.4	486.6	488.0	489.5	491.0	492.5	493.0	493.5	494.0	494.5	495.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	545.0	546.0	546.7	547.4	548.1	548.8	548.7	548.5	548.5	548.4	548.8
115°	630.6	630.9	630.6	630.3	630.1	629.8	630.3	630.9	631.4	631.8	632.1
117.5°	710.8	711.6	712.2	712.7	713.3	713.9	713.8	713.6	713.5	713.4	713.3
120°	764.5	764.8	764.7	764.4	764.1	763.9	764.4	764.8	765.3	765.9	765.9
122.5°	813.0	813.4	813.7	814.1	814.4	814.8	815.1	815.4	815.7	816.0	815.9
125°	886.2	886.5	886.0	885.5	884.9	884.5	885.2	886.0	886.7	887.4	887.9
127.5°	951.1	951.8	953.0	954.1	955.3	956.4	956.2	956.1	956.0	955.8	955.6
130°	994.9	995.4	996.2	996.9	997.6	998.4	998.7	998.8	999.1	999.4	999.5
132.5°	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6	1040.9	1041.1	1041.4	1041.4
135°	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3	1098.8	1099.2	1099.8	1100.3
137.5°	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7	1154.3	1154.8	1155.4	1155.5
140°	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8	1188.6	1189.4	1190.1	1190.6
142.5°	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9	1220.4	1220.9	1221.5	1221.8
145°	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6	1265.8	1266.0	1266.3	1266.7
147.5°	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4	1305.7	1305.9	1306.1	1306.3
150°	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2	1331.2	1331.2	1331.2	1331.3
152.5°	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1	1353.4	1353.8	1354.2	1354.4
155°	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4	1383.5	1384.4	1385.4	1385.5
157.5°	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9
160°	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7
162.5°	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6	1439.2	1440.6	1442.1	1442.0
165°	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0	1458.0	1460.0	1462.0	1461.8
167.5°	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6	1471.8	1473.9	1476.2	1476.0
170°	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3	1480.3	1482.3	1484.3	1484.0
172.5°	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7	1485.7	1487.7	1489.7	1489.4
175°	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8	1492.0	1494.3	1496.5	1496.1
177.5°	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9	1494.5	1496.1	1497.7	1497.3
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	10.2	10.1	10.0	10.2	10.0	10.1	10.2	9.7	9.6	9.6	9.1
90°	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	30.6	29.0	27.6
92.5°	30.6	30.7	30.7	30.8	30.7	30.7	30.6	30.4	29.6	28.2	26.7
95°	31.6	31.9	32.1	32.4	32.1	31.9	31.6	31.4	30.6	29.0	27.6
97.5°	30.6	30.7	31.0	31.3	31.0	30.7	30.6	30.3	30.0	30.0	29.8
100°	30.6	30.7	31.0	31.3	31.0	30.7	30.6	30.3	32.3	36.5	40.7
102.5°	32.0	32.0	32.1	32.2	32.1	32.0	32.0	31.9	54.7	100.2	145.8
105°	345.1	336.1	327.2	318.3	327.2	336.1	345.1	354.0	357.4	355.2	352.9
107.5°	440.7	441.7	442.6	443.6	442.6	441.7	440.7	439.8	438.8	437.7	436.6
110°	495.8	496.6	497.3	498.1	497.3	496.6	495.8	495.1	494.5	494.0	493.5



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	549.7	550.7	551.6	552.6	551.6	550.7	549.7	548.8	548.4	548.5	548.5
115°	632.1	632.1	632.1	632.1	632.1	632.1	632.1	632.1	631.8	631.4	630.9
117.5°	713.3	713.2	713.1	712.9	713.1	713.2	713.3	713.3	713.4	713.5	713.6
120°	765.3	764.8	764.4	763.9	764.4	764.8	765.3	765.9	765.9	765.3	764.8
122.5°	815.4	814.9	814.4	813.9	814.4	814.9	815.4	815.9	816.0	815.7	815.4
125°	888.2	888.5	888.7	889.0	888.7	888.5	888.2	887.9	887.4	886.7	886.0
127.5°	955.5	955.2	955.0	954.8	955.0	955.2	955.5	955.6	955.8	956.0	956.1
130°	999.5	999.5	999.5	999.5	999.5	999.5	999.5	999.5	999.4	999.1	998.8
132.5°	1041.2	1041.0	1040.8	1040.6	1040.8	1041.0	1041.2	1041.4	1041.4	1041.1	1040.9
135°	1100.8	1101.2	1101.7	1102.3	1101.7	1101.2	1100.8	1100.3	1099.8	1099.2	1098.8
137.5°	1155.4	1155.3	1155.1	1154.9	1155.1	1155.3	1155.4	1155.5	1155.4	1154.8	1154.3
140°	1190.8	1191.1	1191.4	1191.6	1191.4	1191.1	1190.8	1190.6	1190.1	1189.4	1188.6
142.5°	1221.8	1221.8	1221.9	1221.9	1221.9	1221.8	1221.8	1221.8	1221.5	1220.9	1220.4
145°	1267.1	1267.7	1268.2	1268.7	1268.2	1267.7	1267.1	1266.7	1266.3	1266.0	1265.8
147.5°	1306.6	1306.8	1307.0	1307.3	1307.0	1306.8	1306.6	1306.3	1306.1	1305.9	1305.7
150°	1331.5	1331.8	1332.1	1332.3	1332.1	1331.8	1331.5	1331.3	1331.2	1331.2	1331.2
152.5°	1354.2	1354.0	1353.9	1353.8	1353.9	1354.0	1354.2	1354.4	1354.2	1353.8	1353.4
155°	1384.8	1384.1	1383.3	1382.6	1383.3	1384.1	1384.8	1385.5	1385.4	1384.4	1383.5
157.5°	1410.6	1409.3	1408.0	1406.7	1408.0	1409.3	1410.6	1411.9	1411.9	1410.6	1409.3
160°	1427.2	1425.7	1424.3	1422.8	1424.3	1425.7	1427.2	1428.7	1428.7	1427.2	1425.7
162.5°	1440.4	1438.6	1436.9	1435.3	1436.9	1438.6	1440.4	1442.0	1442.1	1440.6	1439.2
165°	1459.7	1457.4	1455.2	1452.9	1455.2	1457.4	1459.7	1461.8	1462.0	1460.0	1458.0
167.5°	1473.5	1471.0	1468.6	1466.1	1468.6	1471.0	1473.5	1476.0	1476.2	1473.9	1471.8
170°	1481.6	1479.1	1476.6	1474.1	1476.6	1479.1	1481.6	1484.0	1484.3	1482.3	1480.3
172.5°	1486.6	1483.9	1481.3	1478.6	1481.3	1483.9	1486.6	1489.4	1489.7	1487.7	1485.7
175°	1493.1	1490.1	1487.1	1484.2	1487.1	1490.1	1493.1	1496.1	1496.5	1494.3	1492.0
177.5°	1494.9	1492.5	1490.1	1487.7	1490.1	1492.5	1494.9	1497.3	1497.7	1496.1	1494.5
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	8.8	8.7	8.3	7.7	7.7	7.2	6.9	6.4	6.3	6.3	6.2
90°	26.1	24.5	22.6	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4
92.5°	25.1	23.7	21.7	19.7	17.7	15.8	14.6	14.6	14.4	14.2	14.0
95°	26.1	24.5	24.3	24.1	23.8	23.6	27.6	36.1	44.5	53.0	61.4
97.5°	29.6	29.4	57.2	84.9	112.5	140.3	151.4	146.2	140.9	135.7	130.4
100°	44.9	49.2	83.3	117.6	151.9	186.1	201.0	196.6	192.1	187.6	183.1
102.5°	191.2	236.8	241.3	245.7	250.1	254.6	255.2	251.9	248.7	245.4	242.1
105°	350.7	348.4	347.2	345.9	344.7	343.5	342.1	340.6	339.1	337.6	336.1
107.5°	435.5	434.5	432.7	431.0	429.4	427.7	426.5	425.7	425.0	424.2	423.4
110°	493.0	492.5	491.0	489.5	488.0	486.6	485.4	484.7	484.0	483.2	482.4



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	548.7	548.8	548.1	547.4	546.7	546.0	545.0	543.6	542.3	541.0	539.6
115°	630.3	629.8	630.1	630.3	630.6	630.9	630.6	629.8	629.1	628.4	627.6
117.5°	713.8	713.9	713.3	712.7	712.2	711.6	710.8	709.9	708.9	707.9	706.9
120°	764.4	763.9	764.1	764.4	764.7	764.8	764.5	763.5	762.5	761.5	760.5
122.5°	815.1	814.8	814.4	814.1	813.7	813.4	813.0	812.4	811.8	811.1	810.5
125°	885.2	884.5	884.9	885.5	886.0	886.5	886.2	885.2	884.2	883.2	882.3
127.5°	956.2	956.4	955.3	954.1	953.0	951.8	951.1	950.9	950.6	950.4	950.1
130°	998.7	998.4	997.6	996.9	996.2	995.4	994.9	994.6	994.5	994.2	993.9
132.5°	1040.6	1040.3	1039.4	1038.5	1037.6	1036.6	1035.9	1035.4	1035.0	1034.6	1034.1
135°	1098.3	1097.8	1096.8	1095.8	1094.8	1093.8	1093.5	1093.7	1093.9	1094.2	1094.4
137.5°	1153.7	1153.1	1152.1	1151.0	1149.9	1148.8	1148.2	1148.1	1148.0	1147.9	1147.8
140°	1187.8	1187.1	1186.6	1186.1	1185.6	1185.2	1184.6	1184.1	1183.6	1183.2	1182.7
142.5°	1219.9	1219.3	1219.0	1218.7	1218.4	1218.1	1217.5	1216.6	1215.7	1214.8	1213.9
145°	1265.6	1265.3	1265.3	1265.3	1265.3	1265.3	1264.9	1264.2	1263.4	1262.7	1262.0
147.5°	1305.4	1305.3	1305.5	1305.8	1306.1	1306.3	1305.7	1304.3	1303.0	1301.5	1300.1
150°	1331.2	1331.2	1331.5	1331.7	1332.0	1332.1	1331.8	1330.8	1329.8	1328.9	1327.8
152.5°	1353.1	1352.6	1353.1	1353.5	1354.0	1354.4	1354.3	1353.4	1352.6	1351.9	1351.1
155°	1382.4	1381.5	1382.2	1382.9	1383.7	1384.4	1384.7	1384.4	1384.1	1383.9	1383.7
157.5°	1408.0	1406.7	1407.6	1408.3	1409.2	1410.1	1410.6	1410.7	1410.8	1411.0	1411.2
160°	1424.3	1422.8	1423.0	1423.2	1423.5	1423.7	1424.3	1425.0	1425.7	1426.5	1427.2
162.5°	1437.6	1436.1	1436.4	1436.7	1436.9	1437.2	1437.8	1438.7	1439.7	1440.5	1441.5
165°	1456.0	1454.1	1454.1	1454.1	1454.1	1454.1	1454.7	1455.9	1457.2	1458.4	1459.7
167.5°	1469.6	1467.4	1467.6	1467.7	1467.9	1468.0	1468.8	1470.1	1471.4	1472.7	1473.9
170°	1478.3	1476.4	1476.1	1475.8	1475.6	1475.4	1476.0	1477.5	1478.9	1480.5	1482.0
172.5°	1483.7	1481.7	1481.4	1481.3	1481.0	1480.7	1481.4	1482.8	1484.4	1485.8	1487.3
175°	1489.8	1487.5	1487.3	1487.0	1486.8	1486.5	1487.1	1488.7	1490.1	1491.6	1493.1
177.5°	1492.9	1491.3	1490.9	1490.6	1490.1	1489.7	1490.2	1491.6	1493.0	1494.4	1495.8
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	6.6	6.6	6.5	6.9	7.4	7.5	8.0	8.4	8.9	9.0	9.6
90°	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6
92.5°	14.2	14.4	14.6	14.6	15.8	17.7	19.7	21.7	23.7	25.1	26.7
95°	53.0	44.5	36.1	27.6	23.6	23.8	24.1	24.3	24.5	26.1	27.6
97.5°	135.7	140.9	146.2	151.4	140.3	112.5	84.9	57.2	29.4	29.6	29.8
100°	187.6	192.1	196.6	201.0	186.1	151.9	117.6	83.3	49.2	44.9	40.7
102.5°	245.4	248.7	251.9	255.2	254.6	250.1	245.7	241.3	236.8	191.2	145.8
105°	337.6	339.1	340.6	342.1	343.5	344.7	345.9	347.2	348.4	350.7	352.9
107.5°	424.2	425.0	425.7	426.5	427.7	429.4	431.0	432.7	434.5	435.5	436.6
110°	483.2	484.0	484.7	485.4	486.6	488.0	489.5	491.0	492.5	493.0	493.5





TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	541.0	542.3	543.6	545.0	546.0	546.7	547.4	548.1	548.8	548.7	548.5
115°	628.4	629.1	629.8	630.6	630.9	630.6	630.3	630.1	629.8	630.3	630.9
117.5°	707.9	708.9	709.9	710.8	711.6	712.2	712.7	713.3	713.9	713.8	713.6
120°	761.5	762.5	763.5	764.5	764.8	764.7	764.4	764.1	763.9	764.4	764.8
122.5°	811.1	811.8	812.4	813.0	813.4	813.7	814.1	814.4	814.8	815.1	815.4
125°	883.2	884.2	885.2	886.2	886.5	886.0	885.5	884.9	884.5	885.2	886.0
127.5°	950.4	950.6	950.9	951.1	951.8	953.0	954.1	955.3	956.4	956.2	956.1
130°	994.2	994.5	994.6	994.9	995.4	996.2	996.9	997.6	998.4	998.7	998.8
132.5°	1034.6	1035.0	1035.4	1035.9	1036.6	1037.6	1038.5	1039.4	1040.3	1040.6	1040.9
135°	1094.2	1093.9	1093.7	1093.5	1093.8	1094.8	1095.8	1096.8	1097.8	1098.3	1098.8
137.5°	1147.9	1148.0	1148.1	1148.2	1148.8	1149.9	1151.0	1152.1	1153.1	1153.7	1154.3
140°	1183.2	1183.6	1184.1	1184.6	1185.2	1185.6	1186.1	1186.6	1187.1	1187.8	1188.6
142.5°	1214.8	1215.7	1216.6	1217.5	1218.1	1218.4	1218.7	1219.0	1219.3	1219.9	1220.4
145°	1262.7	1263.4	1264.2	1264.9	1265.3	1265.3	1265.3	1265.3	1265.3	1265.6	1265.8
147.5°	1301.5	1303.0	1304.3	1305.7	1306.3	1306.1	1305.8	1305.5	1305.3	1305.4	1305.7
150°	1328.9	1329.8	1330.8	1331.8	1332.1	1332.0	1331.7	1331.5	1331.2	1331.2	1331.2
152.5°	1351.9	1352.6	1353.4	1354.3	1354.4	1354.0	1353.5	1353.1	1352.6	1353.1	1353.4
155°	1383.9	1384.1	1384.4	1384.7	1384.4	1383.7	1382.9	1382.2	1381.5	1382.4	1383.5
157.5°	1411.0	1410.8	1410.7	1410.6	1410.1	1409.2	1408.3	1407.6	1406.7	1408.0	1409.3
160°	1426.5	1425.7	1425.0	1424.3	1423.7	1423.5	1423.2	1423.0	1422.8	1424.3	1425.7
162.5°	1440.5	1439.7	1438.7	1437.8	1437.2	1436.9	1436.7	1436.4	1436.1	1437.6	1439.2
165°	1458.4	1457.2	1455.9	1454.7	1454.1	1454.1	1454.1	1454.1	1454.1	1456.0	1458.0
167.5°	1472.7	1471.4	1470.1	1468.8	1468.0	1467.9	1467.7	1467.6	1467.4	1469.6	1471.8
170°	1480.5	1478.9	1477.5	1476.0	1475.4	1475.6	1475.8	1476.1	1476.4	1478.3	1480.3
172.5°	1485.8	1484.4	1482.8	1481.4	1480.7	1481.0	1481.3	1481.4	1481.7	1483.7	1485.7
175°	1491.6	1490.1	1488.7	1487.1	1486.5	1486.8	1487.0	1487.3	1487.5	1489.8	1492.0
177.5°	1494.4	1493.0	1491.6	1490.2	1489.7	1490.1	1490.6	1490.9	1491.3	1492.9	1494.5
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	9.6	9.7	10.1	10.0	10.1	10.0	10.2
90°	29.0	30.6	31.5	32.0	32.5	33.0	33.5
92.5°	28.2	29.6	30.4	30.6	30.7	30.7	30.8
95°	29.0	30.6	31.4	31.6	31.9	32.1	32.4
97.5°	30.0	30.0	30.3	30.6	30.7	31.0	31.3
100°	36.5	32.3	30.3	30.6	30.7	31.0	31.3
102.5°	100.2	54.7	31.9	32.0	32.0	32.1	32.2
105°	355.2	357.4	354.0	345.1	336.1	327.2	318.3
107.5°	437.7	438.8	439.8	440.7	441.7	442.6	443.6
110°	494.0	494.5	495.1	495.8	496.6	497.3	498.1



TEST NUMBER: P333027-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	548.5	548.4	548.8	549.7	550.7	551.6	552.6
115°	631.4	631.8	632.1	632.1	632.1	632.1	632.1
117.5°	713.5	713.4	713.3	713.3	713.2	713.1	712.9
120°	765.3	765.9	765.9	765.3	764.8	764.4	763.9
122.5°	815.7	816.0	815.9	815.4	814.9	814.4	813.9
125°	886.7	887.4	887.9	888.2	888.5	888.7	889.0
127.5°	956.0	955.8	955.6	955.5	955.2	955.0	954.8
130°	999.1	999.4	999.5	999.5	999.5	999.5	999.5
132.5°	1041.1	1041.4	1041.4	1041.2	1041.0	1040.8	1040.6
135°	1099.2	1099.8	1100.3	1100.8	1101.2	1101.7	1102.3
137.5°	1154.8	1155.4	1155.5	1155.4	1155.3	1155.1	1154.9
140°	1189.4	1190.1	1190.6	1190.8	1191.1	1191.4	1191.6
142.5°	1220.9	1221.5	1221.8	1221.8	1221.8	1221.9	1221.9
145°	1266.0	1266.3	1266.7	1267.1	1267.7	1268.2	1268.7
147.5°	1305.9	1306.1	1306.3	1306.6	1306.8	1307.0	1307.3
150°	1331.2	1331.2	1331.3	1331.5	1331.8	1332.1	1332.3
152.5°	1353.8	1354.2	1354.4	1354.2	1354.0	1353.9	1353.8
155°	1384.4	1385.4	1385.5	1384.8	1384.1	1383.3	1382.6
157.5°	1410.6	1411.9	1411.9	1410.6	1409.3	1408.0	1406.7
160°	1427.2	1428.7	1428.7	1427.2	1425.7	1424.3	1422.8
162.5°	1440.6	1442.1	1442.0	1440.4	1438.6	1436.9	1435.3
165°	1460.0	1462.0	1461.8	1459.7	1457.4	1455.2	1452.9
167.5°	1473.9	1476.2	1476.0	1473.5	1471.0	1468.6	1466.1
170°	1482.3	1484.3	1484.0	1481.6	1479.1	1476.6	1474.1
172.5°	1487.7	1489.7	1489.4	1486.6	1483.9	1481.3	1478.6
175°	1494.3	1496.5	1496.1	1493.1	1490.1	1487.1	1484.2
177.5°	1496.1	1497.7	1497.3	1494.9	1492.5	1490.1	1487.7
180°	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1

(END OF REPORT)