

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333069-830

Luminaire Tested: **S124RDIW-S795D1340U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333069-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1340U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8085.9 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333069-830

CATALOG NUMBER: S124RDIW-S795D1340U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333069-830

CATALOG NUMBER: S124RDIW-S795D1340U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	79	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	54	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	21	19	15
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	18	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10571	10571	10571
5°	10594	10464	10529
10°	10528	10339	10339
15°	10407	10122	10046
20°	10241	9836	9655
25°	10029	9502	9260
30°	9822	9149	8766
35°	9594	8784	8270
40°	9319	8368	7734
45°	9065	7955	7188
50°	8776	7479	6610
55°	8466	6984	5983
60°	8126	6442	5341
65°	7815	5765	4713
70°	7360	5016	4001
75°	6784	4161	3250
80°	5918	3166	2985
85°	5011	2881	2686



TEST NUMBER: P333069-830

CATALOG NUMBER: S124RDIW-S795D1340U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	1.5
10°-20°	343.0	4.2
20°-30°	495.3	6.1
30°-40°	561.4	6.9
40°-50°	542.1	6.7
50°-60°	450.8	5.6
60°-70°	311.3	3.8
70°-80°	157.8	2.0
80°-90°	45.2	0.6
90°-100°	55.9	0.7
100°-110°	356.4	4.4
110°-120°	681.9	8.4
120°-130°	865.6	10.7
130°-140°	926.1	11.5
140°-150°	866.0	10.7
150°-160°	698.4	8.6
160°-170°	450.5	5.6
170°-180°	155.3	1.9
0°-30°	961.2	11.9
0°-40°	1522.6	18.8
0°-60°	2515.6	31.1
0°-90°	3029.8	37.5
90°-120°	1094.2	13.5
90°-150°	3752.0	46.4
90°-180°	5056.0	62.5
0°-180°	8085.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1307	1303	1291	1301	1299	124
15°	1245	1235	1211	1209	1202	351
25°	1126	1106	1067	1050	1040	519
35°	974	940	891	858	839	608
45°	794	756	697	649	630	612
55°	602	560	496	446	425	538
65°	409	365	302	260	247	404
75°	218	180	133	111	104	230
85°	54	35	31	29	29	61
90°	4	17	27	34	37	6
95°	67	28	27	34	35	86
105°	368	375	381	389	348	385
115°	687	690	690	692	692	676
125°	966	970	968	972	973	862
135°	1198	1197	1202	1204	1207	923
145°	1382	1385	1385	1386	1389	863
155°	1515	1516	1512	1517	1514	698
165°	1598	1592	1592	1600	1590	451
175°	1635	1628	1628	1638	1625	156
180°	1635	1635	1635	1635	1635	



TEST NUMBER: P333069-830

CATALOG NUMBER: S124RDIW-S795D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1312.6	1311.8	1311.1	1310.4	1309.7	1308.3	1306.4	1304.5	1302.5	1300.5	1302.5
5°	1307.3	1306.5	1305.5	1304.7	1303.7	1302.0	1299.3	1296.7	1293.9	1291.3	1293.5
7.5°	1295.5	1294.6	1293.6	1292.7	1291.8	1289.6	1286.1	1282.6	1279.1	1275.6	1277.1
10°	1284.3	1283.2	1282.0	1280.9	1279.8	1277.2	1273.3	1269.2	1265.3	1261.2	1262.1
12.5°	1269.8	1268.6	1267.2	1265.9	1264.7	1261.7	1257.0	1252.2	1247.5	1242.7	1243.3
15°	1245.2	1243.2	1241.1	1239.2	1237.2	1233.4	1227.8	1222.2	1216.6	1211.1	1210.6
17.5°	1215.3	1212.4	1209.5	1206.6	1203.7	1198.9	1192.2	1185.5	1178.8	1172.1	1170.9
20°	1192.0	1189.1	1186.3	1183.4	1180.4	1175.3	1167.6	1160.1	1152.4	1144.9	1143.1
22.5°	1166.4	1163.1	1159.9	1156.6	1153.4	1147.6	1139.5	1131.4	1123.3	1115.2	1112.6
25°	1125.9	1121.8	1117.9	1113.8	1109.8	1103.2	1094.1	1085.0	1075.8	1066.7	1062.9
27.5°	1083.4	1078.4	1073.3	1068.3	1063.2	1055.8	1046.0	1036.3	1026.5	1016.8	1012.1
30°	1053.7	1048.1	1042.5	1037.0	1031.4	1023.4	1013.0	1002.5	991.9	981.5	975.9
32.5°	1022.4	1016.2	1009.8	1003.5	997.3	988.7	977.9	967.0	956.2	945.4	939.0
35°	973.5	966.4	959.2	952.1	945.0	935.9	924.7	913.5	902.4	891.3	883.7
37.5°	921.1	913.8	906.4	899.1	891.7	881.9	869.6	857.2	844.9	832.5	824.1
40°	884.3	876.9	869.6	862.2	854.9	844.8	832.1	819.4	806.7	794.0	784.7
42.5°	848.9	841.2	833.6	825.9	818.1	807.7	794.5	781.2	768.0	754.7	745.2
45°	794.0	785.8	777.5	769.3	761.0	750.3	736.9	723.5	710.1	696.8	685.9
47.5°	737.3	728.8	720.3	711.7	703.2	692.0	678.2	664.2	650.4	636.4	625.1
50°	698.8	690.1	681.4	672.7	664.0	652.5	638.3	624.1	609.7	595.5	584.4
52.5°	659.5	651.0	642.4	634.0	625.5	613.9	599.3	584.7	570.0	555.4	544.1
55°	601.5	592.6	583.7	574.8	565.9	554.2	539.7	525.2	510.8	496.2	484.7
57.5°	544.2	534.9	525.7	516.4	507.1	495.3	481.1	466.8	452.6	438.3	426.6
60°	503.3	494.4	485.5	476.5	467.6	456.1	441.8	427.5	413.3	399.0	387.4
62.5°	466.4	457.1	447.9	438.6	429.3	417.4	402.7	388.1	373.5	358.9	348.2
65°	409.1	399.4	389.8	380.3	370.7	358.8	344.5	330.3	316.0	301.8	292.2
67.5°	349.5	340.4	331.1	322.0	312.7	301.6	288.3	275.1	261.8	248.6	240.3
70°	311.8	302.5	293.0	283.7	274.4	263.3	250.6	237.9	225.3	212.5	205.2
72.5°	271.7	263.3	254.8	246.3	237.8	227.6	215.7	203.6	191.6	179.6	173.3
75°	217.5	209.3	201.0	192.8	184.5	175.2	164.8	154.3	143.8	133.4	128.2
77.5°	162.6	155.6	148.6	141.7	134.6	126.9	118.5	110.0	101.5	93.0	90.0
80°	127.3	120.8	114.4	107.9	101.5	94.9	88.2	81.5	74.8	68.1	67.5
82.5°	96.9	91.0	85.0	79.1	73.1	68.2	64.5	60.6	56.7	53.0	52.4
85°	54.1	49.7	45.2	40.8	36.3	33.7	33.1	32.4	31.8	31.1	30.6
87.5°	19.1	18.4	17.5	16.7	15.8	15.6	15.8	16.1	16.3	16.6	16.8
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	15.4	15.6	15.7	15.9	16.0	17.2	19.4	21.6	23.8	25.9	27.5
95°	67.2	58.0	48.7	39.5	30.3	25.8	26.1	26.4	26.6	26.9	28.6
97.5°	142.8	148.5	154.3	160.0	165.8	153.5	123.2	92.9	62.6	32.2	32.4
100°	200.5	205.4	210.3	215.2	220.1	203.8	166.3	128.8	91.2	53.8	49.2
102.5°	265.0	268.6	272.2	275.8	279.4	278.7	273.8	269.0	264.1	259.2	209.3
105°	368.0	369.6	371.3	372.9	374.5	376.0	377.4	378.7	380.0	381.4	383.9
107.5°	463.5	464.4	465.2	466.0	466.8	468.2	470.0	471.8	473.7	475.6	476.7
110°	528.1	529.0	529.8	530.6	531.4	532.6	534.2	535.8	537.5	539.1	539.7



TEST NUMBER: P333069-830

CATALOG NUMBER: S124RDIW-S795D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	590.7	592.2	593.7	595.1	596.6	597.7	598.5	599.3	600.0	600.8	600.7
115°	687.0	687.9	688.7	689.5	690.3	690.6	690.3	690.0	689.8	689.5	690.0
117.5°	773.8	775.0	776.0	777.1	778.2	779.0	779.7	780.2	780.8	781.5	781.4
120°	832.5	833.6	834.7	835.8	836.9	837.3	837.1	836.8	836.5	836.2	836.8
122.5°	887.3	888.0	888.6	889.3	889.9	890.4	890.8	891.2	891.6	891.9	892.3
125°	965.8	966.9	968.0	969.0	970.2	970.4	969.9	969.3	968.7	968.3	969.0
127.5°	1040.1	1040.4	1040.7	1040.9	1041.2	1042.0	1043.2	1044.4	1045.8	1047.0	1046.8
130°	1088.1	1088.4	1088.6	1088.8	1089.1	1089.7	1090.5	1091.3	1092.1	1093.0	1093.3
132.5°	1132.1	1132.6	1133.0	1133.5	1134.0	1134.8	1135.9	1136.8	1137.8	1138.9	1139.2
135°	1198.1	1197.8	1197.5	1197.3	1197.0	1197.4	1198.4	1199.6	1200.7	1201.7	1202.3
137.5°	1256.5	1256.6	1256.7	1256.9	1257.0	1257.6	1258.8	1260.0	1261.2	1262.3	1263.0
140°	1294.7	1295.2	1295.7	1296.3	1296.8	1297.4	1297.9	1298.4	1299.0	1299.6	1300.3
142.5°	1328.9	1329.8	1330.9	1331.8	1332.8	1333.4	1333.8	1334.1	1334.5	1334.7	1335.4
145°	1381.5	1382.2	1383.1	1383.9	1384.7	1385.2	1385.2	1385.2	1385.2	1385.2	1385.4
147.5°	1423.2	1424.7	1426.3	1427.9	1429.4	1430.0	1429.7	1429.5	1429.2	1428.9	1429.1
150°	1453.6	1454.7	1455.8	1456.9	1457.9	1458.3	1458.1	1457.8	1457.5	1457.3	1457.3
152.5°	1479.0	1479.9	1480.7	1481.6	1482.5	1482.7	1482.2	1481.7	1481.2	1480.7	1481.2
155°	1514.8	1514.9	1515.2	1515.5	1515.8	1515.5	1514.8	1513.9	1513.1	1512.3	1513.3
157.5°	1544.8	1544.6	1544.5	1544.3	1544.2	1543.6	1542.7	1541.7	1540.9	1539.9	1541.3
160°	1562.4	1561.6	1560.8	1559.9	1559.2	1558.6	1558.3	1558.0	1557.7	1557.6	1559.2
162.5°	1578.0	1577.0	1576.0	1575.0	1574.0	1573.3	1573.0	1572.7	1572.4	1572.2	1573.8
165°	1597.9	1596.5	1595.2	1593.7	1592.4	1591.8	1591.8	1591.8	1591.8	1591.8	1593.9
167.5°	1613.5	1612.1	1610.7	1609.3	1607.9	1607.0	1606.9	1606.8	1606.6	1606.4	1608.8
170°	1622.3	1620.7	1619.0	1617.4	1615.8	1615.1	1615.3	1615.6	1615.9	1616.2	1618.3
172.5°	1628.1	1626.5	1624.9	1623.2	1621.6	1621.0	1621.3	1621.6	1621.7	1622.0	1624.2
175°	1634.6	1632.9	1631.3	1629.7	1628.0	1627.3	1627.6	1627.9	1628.1	1628.4	1630.9
177.5°	1637.5	1636.0	1634.4	1632.9	1631.4	1630.8	1631.3	1631.7	1632.1	1632.6	1634.3
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333069-830

CATALOG NUMBER: S124RDIW-S795D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1304.5	1306.4	1308.3	1309.3	1309.1	1308.9	1308.7	1308.5
5°	1295.7	1298.0	1300.2	1301.1	1300.6	1300.2	1299.8	1299.3
7.5°	1278.5	1280.0	1281.4	1281.7	1281.0	1280.3	1279.6	1278.8
10°	1263.0	1263.9	1264.8	1264.8	1263.9	1263.0	1262.1	1261.2
12.5°	1243.9	1244.3	1244.9	1244.5	1243.3	1242.1	1240.8	1239.5
15°	1210.2	1209.8	1209.3	1208.3	1206.7	1205.1	1203.6	1202.0
17.5°	1169.7	1168.5	1167.2	1165.4	1163.0	1160.6	1158.3	1155.9
20°	1141.3	1139.5	1137.7	1135.5	1132.6	1129.6	1126.7	1123.9
22.5°	1109.9	1107.2	1104.6	1102.0	1099.7	1097.3	1095.0	1092.6
25°	1059.1	1055.4	1051.6	1048.6	1046.3	1044.1	1041.9	1039.6
27.5°	1007.4	1002.8	998.1	994.1	990.9	987.7	984.5	981.3
30°	970.3	964.8	959.2	954.6	951.1	947.5	944.0	940.4
32.5°	932.5	926.0	919.5	914.6	911.3	907.9	904.5	901.1
35°	876.1	868.6	861.0	855.2	851.2	847.2	843.1	839.1
37.5°	815.6	807.1	798.6	792.4	788.4	784.4	780.4	776.4
40°	775.3	765.9	756.6	749.9	745.9	741.9	737.9	733.9
42.5°	735.7	726.1	716.6	709.7	705.5	701.3	697.2	693.0
45°	675.0	664.0	653.1	645.6	641.6	637.6	633.6	629.6
47.5°	613.8	602.5	591.2	583.2	578.9	574.5	570.0	565.6
50°	573.3	562.1	550.9	543.3	539.0	534.8	530.6	526.3
52.5°	532.8	521.5	510.1	502.3	497.9	493.4	489.1	484.7
55°	473.1	461.5	450.0	442.1	437.8	433.6	429.3	425.1
57.5°	414.8	403.0	391.2	383.8	380.6	377.4	374.2	371.0
60°	375.9	364.3	352.7	345.1	341.6	338.0	334.4	330.8
62.5°	337.5	326.9	316.1	309.3	306.5	303.7	300.8	297.9
65°	282.6	273.1	263.4	257.3	254.7	251.9	249.3	246.7
67.5°	232.1	223.9	215.7	210.1	207.2	204.2	201.2	198.3
70°	197.8	190.5	183.1	178.3	176.2	173.9	171.6	169.5
72.5°	167.1	160.8	154.5	150.3	148.4	146.3	144.2	142.1
75°	123.1	118.0	112.8	109.6	108.3	107.0	105.6	104.2
77.5°	87.1	84.1	81.1	79.4	79.0	78.6	78.2	77.8
80°	66.8	66.2	65.5	65.0	64.8	64.6	64.4	64.2
82.5°	51.9	51.5	51.0	50.6	50.4	50.1	50.0	49.8
85°	30.2	29.8	29.3	29.0	29.0	29.0	29.0	29.0
87.5°	16.9	17.1	17.2	17.4	17.7	18.0	18.3	18.6
90°	30.2	31.8	33.5	34.5	35.1	35.6	36.1	36.7
92.5°	29.2	30.8	32.4	33.3	33.5	33.6	33.6	33.7
95°	30.2	31.8	33.5	34.4	34.6	34.9	35.2	35.4
97.5°	32.6	32.8	32.9	33.2	33.5	33.6	33.9	34.2
100°	44.6	40.0	35.3	33.2	33.5	33.6	33.9	34.2
102.5°	159.6	109.7	59.9	35.0	35.1	35.1	35.2	35.3
105°	386.3	388.8	391.2	387.6	377.8	368.0	358.2	348.5
107.5°	478.0	479.2	480.3	481.5	482.5	483.5	484.6	485.6
110°	540.3	540.7	541.3	542.0	542.8	543.7	544.4	545.3



TEST NUMBER: P333069-830

CATALOG NUMBER: S124RDIW-S795D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	600.5	600.4	600.3	600.8	601.8	602.9	603.9	604.9
115°	690.6	691.2	691.6	691.9	691.9	691.9	691.9	691.9
117.5°	781.2	781.1	781.0	780.9	780.8	780.7	780.6	780.4
120°	837.3	837.8	838.4	838.4	837.8	837.3	836.8	836.2
122.5°	892.6	893.0	893.2	893.2	892.6	892.0	891.6	891.0
125°	969.9	970.7	971.5	972.0	972.3	972.6	972.9	973.2
127.5°	1046.7	1046.5	1046.3	1046.1	1045.9	1045.7	1045.5	1045.3
130°	1093.4	1093.7	1094.0	1094.2	1094.2	1094.2	1094.2	1094.2
132.5°	1139.4	1139.7	1140.0	1140.0	1139.8	1139.6	1139.3	1139.2
135°	1202.9	1203.3	1203.9	1204.5	1205.0	1205.5	1206.1	1206.6
137.5°	1263.6	1264.1	1264.8	1265.0	1264.8	1264.7	1264.5	1264.3
140°	1301.2	1302.0	1302.8	1303.3	1303.6	1303.9	1304.2	1304.5
142.5°	1336.0	1336.5	1337.2	1337.5	1337.6	1337.6	1337.7	1337.7
145°	1385.6	1385.9	1386.2	1386.7	1387.1	1387.7	1388.3	1388.8
147.5°	1429.4	1429.6	1429.7	1430.0	1430.3	1430.6	1430.8	1431.1
150°	1457.3	1457.3	1457.3	1457.4	1457.6	1457.9	1458.2	1458.5
152.5°	1481.6	1482.1	1482.4	1482.6	1482.4	1482.2	1482.1	1482.0
155°	1514.5	1515.5	1516.6	1516.7	1516.0	1515.1	1514.3	1513.5
157.5°	1542.8	1544.2	1545.6	1545.6	1544.2	1542.8	1541.3	1539.9
160°	1560.8	1562.4	1564.1	1564.1	1562.4	1560.8	1559.2	1557.6
162.5°	1575.5	1577.1	1578.7	1578.6	1576.8	1574.9	1573.0	1571.2
165°	1596.1	1598.3	1600.4	1600.2	1597.9	1595.4	1593.0	1590.5
167.5°	1611.2	1613.5	1616.0	1615.8	1613.1	1610.3	1607.7	1605.0
170°	1620.5	1622.7	1624.8	1624.6	1621.9	1619.2	1616.5	1613.7
172.5°	1626.4	1628.6	1630.8	1630.4	1627.4	1624.5	1621.6	1618.6
175°	1633.3	1635.8	1638.2	1637.8	1634.6	1631.3	1628.0	1624.8
177.5°	1636.1	1637.8	1639.6	1639.1	1636.4	1633.9	1631.3	1628.6
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6

(END OF REPORT)