

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333030-935

Luminaire Tested: **S124RDIW-S350D1340U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333030-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5239.7 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333030-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333030-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	15
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P333030-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.0
10°-20°	139.4	2.7
20°-30°	201.3	3.8
30°-40°	228.2	4.4
40°-50°	220.4	4.2
50°-60°	183.2	3.5
60°-70°	126.5	2.4
70°-80°	64.1	1.2
80°-90°	20.8	0.4
90°-100°	95.2	1.8
100°-110°	282.1	5.4
110°-120°	478.8	9.1
120°-130°	631.3	12.0
130°-140°	709.0	13.5
140°-150°	696.7	13.3
150°-160°	586.0	11.2
160°-170°	389.9	7.4
170°-180°	136.5	2.6
0°-30°	390.7	7.5
0°-40°	619.0	11.8
0°-60°	1022.6	19.5
0°-90°	1234.0	23.6
90°-120°	856.1	16.3
90°-150°	2893.2	55.2
90°-180°	4006.0	76.5
0°-180°	5239.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	3	15	24	31	34	5
95°	67	77	85	88	88	75
105°	260	261	266	269	272	276
115°	487	487	485	484	482	480
125°	709	709	708	706	703	632
135°	914	921	921	919	916	707
145°	1111	1115	1117	1115	1112	695
155°	1273	1273	1272	1276	1272	585
165°	1386	1382	1380	1386	1382	390
175°	1442	1436	1435	1442	1435	137
180°	1444	1444	1444	1444	1444	



TEST NUMBER: P333030-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	8.2	8.1	8.1	8.1	8.0	8.2	8.5	8.9	9.1	9.5	9.7
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	23.9	27.0	30.1	33.2	36.4	38.7	40.0	41.4	42.8	44.3	45.1
95°	67.0	69.2	71.5	73.7	75.9	77.9	79.6	81.4	83.1	84.9	85.6
97.5°	117.0	118.8	120.6	122.3	124.2	126.1	128.1	130.2	132.2	134.2	135.1
100°	156.4	157.3	158.3	159.3	160.3	161.9	164.1	166.3	168.6	170.8	171.3
102.5°	197.4	197.9	198.2	198.6	199.0	200.2	202.2	204.3	206.3	208.4	209.1
105°	260.2	260.5	260.7	260.9	261.1	261.7	262.8	263.8	264.8	265.8	266.5
107.5°	326.1	326.3	326.7	326.9	327.3	327.4	327.6	327.8	328.0	328.0	328.7
110°	370.7	371.2	371.7	372.2	372.7	372.8	372.6	372.3	372.1	371.9	371.3



TEST NUMBER: P333030-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	417.2	417.2	417.3	417.5	417.6	417.4	417.0	416.5	416.0	415.6	415.5
115°	486.8	486.8	486.8	486.8	486.8	486.6	486.1	485.6	485.1	484.6	484.4
117.5°	552.5	552.7	552.9	553.1	553.3	553.2	552.8	552.5	552.2	551.8	551.0
120°	596.2	597.3	598.2	599.3	600.2	600.4	599.6	598.9	598.1	597.4	596.2
122.5°	641.8	642.2	642.7	643.0	643.4	643.4	643.1	642.7	642.4	642.0	641.2
125°	709.0	709.0	709.0	709.0	709.0	708.9	708.7	708.4	708.2	707.9	707.4
127.5°	770.0	770.8	771.5	772.2	773.0	773.2	772.7	772.4	772.0	771.5	771.1
130°	812.9	813.6	814.4	815.1	815.9	816.2	816.2	816.2	816.2	816.2	815.7
132.5°	856.7	857.2	857.7	858.3	858.8	859.0	858.8	858.6	858.4	858.2	857.7
135°	914.5	916.0	917.5	918.9	920.5	921.2	921.2	921.2	921.2	921.2	920.8
137.5°	977.5	978.2	978.9	979.6	980.2	980.9	981.2	981.6	982.0	982.4	981.7
140°	1019.5	1019.9	1020.5	1021.0	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5
142.5°	1057.9	1058.3	1058.9	1059.4	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2
145°	1111.0	1112.1	1113.0	1114.0	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4
147.5°	1163.7	1164.9	1166.1	1167.3	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0
150°	1195.9	1196.9	1197.9	1198.9	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1226.2	1226.8	1227.4	1228.0	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5
155°	1272.9	1272.9	1272.9	1272.9	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8
157.5°	1312.3	1311.8	1311.4	1310.9	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8
160°	1335.5	1335.2	1335.0	1334.7	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9
162.5°	1356.9	1356.2	1355.6	1355.0	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3
165°	1385.7	1385.0	1384.2	1383.5	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6
167.5°	1407.8	1406.8	1405.8	1404.7	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9
170°	1420.3	1419.1	1417.9	1416.6	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4
172.5°	1429.3	1428.2	1427.2	1426.2	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5
175°	1441.6	1440.3	1439.1	1437.9	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6
177.5°	1445.5	1444.6	1443.6	1442.6	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333030-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	9.9	10.2	10.4	10.6	10.8	10.9	11.1	11.3
90°	27.6	29.0	30.5	31.5	32.0	32.5	33.0	33.5
92.5°	46.0	46.9	47.8	48.4	48.6	49.0	49.2	49.6
95°	86.4	87.1	87.8	88.3	88.3	88.3	88.3	88.3
97.5°	136.0	136.9	137.8	138.3	138.3	138.3	138.3	138.3
100°	171.9	172.4	172.8	173.1	173.1	173.1	173.1	173.1
102.5°	209.7	210.4	211.1	211.5	211.8	212.0	212.2	212.4
105°	267.3	268.0	268.7	269.5	270.2	271.0	271.7	272.4
107.5°	329.4	330.1	330.9	331.1	331.1	331.1	331.1	331.0
110°	370.8	370.3	369.9	370.0	370.7	371.4	372.2	373.0



TEST NUMBER: P333030-935

CATALOG NUMBER: S124RDIW-S350D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	415.4	415.3	415.2	415.3	415.3	415.5	415.7	415.9
115°	484.1	483.9	483.6	483.4	483.1	482.8	482.6	482.4
117.5°	550.2	549.3	548.5	547.8	547.3	546.8	546.3	545.8
120°	595.0	593.7	592.5	592.0	592.5	593.1	593.6	594.0
122.5°	640.3	639.6	638.7	637.8	636.9	636.0	635.2	634.2
125°	707.0	706.5	705.9	705.4	705.0	704.5	704.0	703.4
127.5°	770.6	770.1	769.6	769.1	768.8	768.4	767.9	767.6
130°	815.3	814.8	814.2	813.6	812.5	811.5	810.5	809.5
132.5°	857.2	856.8	856.3	855.8	855.4	855.0	854.6	854.2
135°	920.2	919.7	919.2	918.6	917.8	917.1	916.4	915.6
137.5°	981.1	980.5	979.8	979.6	979.7	979.9	980.0	980.2
140°	1021.2	1021.0	1020.7	1020.5	1020.2	1019.9	1019.7	1019.5
142.5°	1059.1	1059.1	1059.0	1058.9	1058.9	1058.9	1058.9	1058.8
145°	1116.1	1115.9	1115.6	1115.2	1114.4	1113.6	1112.9	1112.2
147.5°	1167.8	1167.6	1167.4	1167.2	1166.9	1166.7	1166.5	1166.2
150°	1200.3	1200.3	1200.3	1200.2	1200.0	1199.7	1199.5	1199.3
152.5°	1231.1	1231.7	1232.3	1232.2	1231.6	1230.9	1230.3	1229.6
155°	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9
157.5°	1311.5	1312.3	1313.0	1312.9	1312.1	1311.2	1310.4	1309.6
160°	1334.7	1335.5	1336.2	1335.9	1334.7	1333.5	1332.2	1331.0
162.5°	1355.6	1356.9	1358.2	1358.3	1357.0	1355.8	1354.6	1353.3
165°	1383.1	1384.6	1386.1	1386.4	1385.3	1384.3	1383.4	1382.3
167.5°	1406.4	1407.8	1409.3	1409.3	1407.7	1406.2	1404.7	1403.2
170°	1418.8	1420.3	1421.9	1421.7	1420.0	1418.2	1416.5	1414.8
172.5°	1428.1	1429.9	1431.6	1431.5	1429.8	1428.1	1426.3	1424.6
175°	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9
177.5°	1443.9	1445.3	1446.7	1446.6	1445.0	1443.4	1441.8	1440.2
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8

(END OF REPORT)