

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333074-830

Luminaire Tested: **S124RDIW-S795D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333074-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1560U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8128.9 lumens  
Efficiency: N/A  
Efficacy: 119.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333074-830

CATALOG NUMBER: S124RDIW-S795D1560U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333074-830

CATALOG NUMBER: S124RDIW-S795D1560U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	84	86	83	79	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	54	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	55	47	42	60	51	44	39	42	36	33	33	29	27	25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10571	10571	10571
5°	10594	10464	10529
10°	10528	10339	10339
15°	10407	10122	10046
20°	10241	9836	9655
25°	10029	9502	9260
30°	9822	9149	8766
35°	9594	8784	8270
40°	9319	8368	7734
45°	9065	7955	7188
50°	8776	7479	6610
55°	8466	6984	5983
60°	8126	6442	5341
65°	7815	5765	4713
70°	7360	5016	4001
75°	6784	4161	3250
80°	5918	3166	2985
85°	5011	2881	2686



TEST NUMBER: P333074-830

CATALOG NUMBER: S124RDIW-S795D1560U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.0	1.5
10°-20°	343.0	4.2
20°-30°	495.3	6.1
30°-40°	561.4	6.9
40°-50°	542.1	6.7
50°-60°	450.8	5.5
60°-70°	311.3	3.8
70°-80°	157.8	1.9
80°-90°	46.0	0.6
90°-100°	121.2	1.5
100°-110°	359.1	4.4
110°-120°	609.4	7.5
120°-130°	803.6	9.9
130°-140°	902.4	11.1
140°-150°	886.8	10.9
150°-160°	745.9	9.2
160°-170°	496.2	6.1
170°-180°	173.8	2.1
0°-30°	961.2	11.8
0°-40°	1522.6	18.7
0°-60°	2515.6	30.9
0°-90°	3030.6	37.3
90°-120°	1089.7	13.4
90°-150°	3682.5	45.3
90°-180°	5098.0	62.7
0°-180°	8128.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1307	1303	1291	1301	1299	124
15°	1245	1235	1211	1209	1202	351
25°	1126	1106	1067	1050	1040	519
35°	974	940	891	858	839	608
45°	794	756	697	649	630	612
55°	602	560	496	446	425	538
65°	409	365	302	260	247	404
75°	218	180	133	111	104	230
85°	54	35	31	29	29	61
90°	4	20	31	40	43	8
95°	85	98	108	112	112	95
105°	331	333	338	342	347	351
115°	620	619	617	615	614	611
125°	902	902	901	898	895	804
135°	1164	1172	1172	1170	1165	900
145°	1414	1420	1421	1420	1416	885
155°	1620	1620	1619	1624	1619	745
165°	1764	1760	1757	1764	1759	497
175°	1835	1828	1826	1835	1826	174
180°	1838	1838	1838	1838	1838	



TEST NUMBER: P333074-830

CATALOG NUMBER: S124RDIW-S795D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1312.6	1311.8	1311.1	1310.4	1309.7	1308.3	1306.4	1304.5	1302.5	1300.5	1302.5
5°	1307.3	1306.5	1305.5	1304.7	1303.7	1302.0	1299.3	1296.7	1293.9	1291.3	1293.5
7.5°	1295.5	1294.6	1293.6	1292.7	1291.8	1289.6	1286.1	1282.6	1279.1	1275.6	1277.1
10°	1284.3	1283.2	1282.0	1280.9	1279.8	1277.2	1273.3	1269.2	1265.3	1261.2	1262.1
12.5°	1269.8	1268.6	1267.2	1265.9	1264.7	1261.7	1257.0	1252.2	1247.5	1242.7	1243.3
15°	1245.2	1243.2	1241.1	1239.2	1237.2	1233.4	1227.8	1222.2	1216.6	1211.1	1210.6
17.5°	1215.3	1212.4	1209.5	1206.6	1203.7	1198.9	1192.2	1185.5	1178.8	1172.1	1170.9
20°	1192.0	1189.1	1186.3	1183.4	1180.4	1175.3	1167.6	1160.1	1152.4	1144.9	1143.1
22.5°	1166.4	1163.1	1159.9	1156.6	1153.4	1147.6	1139.5	1131.4	1123.3	1115.2	1112.6
25°	1125.9	1121.8	1117.9	1113.8	1109.8	1103.2	1094.1	1085.0	1075.8	1066.7	1062.9
27.5°	1083.4	1078.4	1073.3	1068.3	1063.2	1055.8	1046.0	1036.3	1026.5	1016.8	1012.1
30°	1053.7	1048.1	1042.5	1037.0	1031.4	1023.4	1013.0	1002.5	991.9	981.5	975.9
32.5°	1022.4	1016.2	1009.8	1003.5	997.3	988.7	977.9	967.0	956.2	945.4	939.0
35°	973.5	966.4	959.2	952.1	945.0	935.9	924.7	913.5	902.4	891.3	883.7
37.5°	921.1	913.8	906.4	899.1	891.7	881.9	869.6	857.2	844.9	832.5	824.1
40°	884.3	876.9	869.6	862.2	854.9	844.8	832.1	819.4	806.7	794.0	784.7
42.5°	848.9	841.2	833.6	825.9	818.1	807.7	794.5	781.2	768.0	754.7	745.2
45°	794.0	785.8	777.5	769.3	761.0	750.3	736.9	723.5	710.1	696.8	685.9
47.5°	737.3	728.8	720.3	711.7	703.2	692.0	678.2	664.2	650.4	636.4	625.1
50°	698.8	690.1	681.4	672.7	664.0	652.5	638.3	624.1	609.7	595.5	584.4
52.5°	659.5	651.0	642.4	634.0	625.5	613.9	599.3	584.7	570.0	555.4	544.1
55°	601.5	592.6	583.7	574.8	565.9	554.2	539.7	525.2	510.8	496.2	484.7
57.5°	544.2	534.9	525.7	516.4	507.1	495.3	481.1	466.8	452.6	438.3	426.6
60°	503.3	494.4	485.5	476.5	467.6	456.1	441.8	427.5	413.3	399.0	387.4
62.5°	466.4	457.1	447.9	438.6	429.3	417.4	402.7	388.1	373.5	358.9	348.2
65°	409.1	399.4	389.8	380.3	370.7	358.8	344.5	330.3	316.0	301.8	292.2
67.5°	349.5	340.4	331.1	322.0	312.7	301.6	288.3	275.1	261.8	248.6	240.3
70°	311.8	302.5	293.0	283.7	274.4	263.3	250.6	237.9	225.3	212.5	205.2
72.5°	271.7	263.3	254.8	246.3	237.8	227.6	215.7	203.6	191.6	179.6	173.3
75°	217.5	209.3	201.0	192.8	184.5	175.2	164.8	154.3	143.8	133.4	128.2
77.5°	162.6	155.6	148.6	141.7	134.6	126.9	118.5	110.0	101.5	93.0	90.0
80°	127.3	120.8	114.4	107.9	101.5	94.9	88.2	81.5	74.8	68.1	67.5
82.5°	96.9	91.0	85.0	79.1	73.1	68.2	64.5	60.6	56.7	53.0	52.4
85°	54.1	49.7	45.2	40.8	36.3	33.7	33.1	32.4	31.8	31.1	30.6
87.5°	19.3	18.6	17.8	17.1	16.4	16.2	16.5	16.9	17.2	17.4	17.7
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	30.4	34.4	38.4	42.3	46.4	49.2	51.0	52.8	54.5	56.3	57.4
95°	85.3	88.1	91.0	93.8	96.6	99.2	101.4	103.6	105.8	108.0	109.0
97.5°	148.9	151.2	153.4	155.8	158.1	160.5	163.1	165.6	168.2	170.8	171.9
100°	199.0	200.2	201.5	202.7	204.1	206.0	209.0	211.8	214.6	217.4	218.1
102.5°	251.3	251.8	252.3	252.8	253.3	254.9	257.4	260.0	262.6	265.2	266.1
105°	331.1	331.5	331.8	332.1	332.4	333.2	334.4	335.7	337.0	338.3	339.2
107.5°	415.0	415.4	415.8	416.1	416.5	416.8	417.0	417.2	417.4	417.5	418.4
110°	471.8	472.5	473.1	473.7	474.4	474.6	474.2	473.9	473.5	473.3	472.6



TEST NUMBER: P333074-830

CATALOG NUMBER: S124RDIW-S795D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.9	531.1	531.2	531.3	531.5	531.2	530.7	530.1	529.5	529.0	528.9
115°	619.6	619.6	619.6	619.6	619.6	619.3	618.7	618.0	617.5	616.8	616.5
117.5°	703.2	703.4	703.7	704.0	704.3	704.2	703.7	703.2	702.8	702.4	701.3
120°	758.9	760.2	761.5	762.7	763.9	764.1	763.2	762.2	761.3	760.3	758.7
122.5°	816.9	817.4	817.9	818.4	818.9	819.0	818.5	818.0	817.7	817.2	816.1
125°	902.5	902.5	902.5	902.5	902.5	902.3	902.0	901.6	901.4	901.1	900.4
127.5°	980.1	981.0	981.9	982.9	983.8	984.1	983.5	983.1	982.6	982.0	981.4
130°	1034.6	1035.6	1036.5	1037.5	1038.4	1038.9	1038.9	1038.9	1038.9	1038.9	1038.3
132.5°	1090.3	1091.1	1091.7	1092.4	1093.2	1093.3	1093.1	1092.9	1092.6	1092.3	1091.7
135°	1163.9	1165.8	1167.7	1169.7	1171.6	1172.5	1172.5	1172.5	1172.5	1172.5	1171.9
137.5°	1244.2	1245.0	1245.9	1246.8	1247.6	1248.4	1248.9	1249.3	1249.9	1250.4	1249.5
140°	1297.6	1298.2	1298.8	1299.5	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0
142.5°	1346.4	1347.1	1347.7	1348.3	1349.0	1349.2	1348.9	1348.7	1348.4	1348.1	1348.1
145°	1414.1	1415.3	1416.6	1417.9	1419.2	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9
147.5°	1481.2	1482.7	1484.2	1485.7	1487.2	1487.9	1487.6	1487.3	1487.1	1486.9	1486.6
150°	1522.1	1523.3	1524.7	1525.9	1527.2	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8
152.5°	1560.8	1561.5	1562.3	1563.0	1563.8	1564.3	1564.5	1564.8	1565.1	1565.3	1566.0
155°	1620.1	1620.1	1620.1	1620.1	1620.1	1620.0	1619.7	1619.4	1619.1	1618.7	1620.0
157.5°	1670.2	1669.6	1669.1	1668.5	1667.9	1667.6	1667.5	1667.5	1667.5	1667.4	1668.3
160°	1699.8	1699.4	1699.1	1698.8	1698.5	1698.2	1697.9	1697.5	1697.2	1697.0	1697.9
162.5°	1727.0	1726.3	1725.4	1724.6	1723.7	1723.2	1722.9	1722.6	1722.2	1721.9	1723.6
165°	1763.7	1762.7	1761.8	1760.9	1759.9	1759.2	1758.5	1757.8	1757.3	1756.6	1758.5
167.5°	1791.9	1790.5	1789.2	1787.9	1786.6	1785.9	1786.0	1786.0	1786.1	1786.2	1788.1
170°	1807.8	1806.2	1804.6	1803.0	1801.5	1800.8	1801.1	1801.5	1801.8	1802.0	1803.9
172.5°	1819.1	1817.8	1816.5	1815.1	1813.8	1813.2	1813.3	1813.4	1813.4	1813.5	1815.6
175°	1834.8	1833.2	1831.6	1830.0	1828.4	1827.5	1827.2	1826.8	1826.6	1826.3	1828.4
177.5°	1839.8	1838.6	1837.4	1836.1	1834.8	1834.2	1834.2	1834.2	1834.2	1834.2	1836.0
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P333074-830

CATALOG NUMBER: S124RDIW-S795D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1304.5	1306.4	1308.3	1309.3	1309.1	1308.9	1308.7	1308.5
5°	1295.7	1298.0	1300.2	1301.1	1300.6	1300.2	1299.8	1299.3
7.5°	1278.5	1280.0	1281.4	1281.7	1281.0	1280.3	1279.6	1278.8
10°	1263.0	1263.9	1264.8	1264.8	1263.9	1263.0	1262.1	1261.2
12.5°	1243.9	1244.3	1244.9	1244.5	1243.3	1242.1	1240.8	1239.5
15°	1210.2	1209.8	1209.3	1208.3	1206.7	1205.1	1203.6	1202.0
17.5°	1169.7	1168.5	1167.2	1165.4	1163.0	1160.6	1158.3	1155.9
20°	1141.3	1139.5	1137.7	1135.5	1132.6	1129.6	1126.7	1123.9
22.5°	1109.9	1107.2	1104.6	1102.0	1099.7	1097.3	1095.0	1092.6
25°	1059.1	1055.4	1051.6	1048.6	1046.3	1044.1	1041.9	1039.6
27.5°	1007.4	1002.8	998.1	994.1	990.9	987.7	984.5	981.3
30°	970.3	964.8	959.2	954.6	951.1	947.5	944.0	940.4
32.5°	932.5	926.0	919.5	914.6	911.3	907.9	904.5	901.1
35°	876.1	868.6	861.0	855.2	851.2	847.2	843.1	839.1
37.5°	815.6	807.1	798.6	792.4	788.4	784.4	780.4	776.4
40°	775.3	765.9	756.6	749.9	745.9	741.9	737.9	733.9
42.5°	735.7	726.1	716.6	709.7	705.5	701.3	697.2	693.0
45°	675.0	664.0	653.1	645.6	641.6	637.6	633.6	629.6
47.5°	613.8	602.5	591.2	583.2	578.9	574.5	570.0	565.6
50°	573.3	562.1	550.9	543.3	539.0	534.8	530.6	526.3
52.5°	532.8	521.5	510.1	502.3	497.9	493.4	489.1	484.7
55°	473.1	461.5	450.0	442.1	437.8	433.6	429.3	425.1
57.5°	414.8	403.0	391.2	383.8	380.6	377.4	374.2	371.0
60°	375.9	364.3	352.7	345.1	341.6	338.0	334.4	330.8
62.5°	337.5	326.9	316.1	309.3	306.5	303.7	300.8	297.9
65°	282.6	273.1	263.4	257.3	254.7	251.9	249.3	246.7
67.5°	232.1	223.9	215.7	210.1	207.2	204.2	201.2	198.3
70°	197.8	190.5	183.1	178.3	176.2	173.9	171.6	169.5
72.5°	167.1	160.8	154.5	150.3	148.4	146.3	144.2	142.1
75°	123.1	118.0	112.8	109.6	108.3	107.0	105.6	104.2
77.5°	87.1	84.1	81.1	79.4	79.0	78.6	78.2	77.8
80°	66.8	66.2	65.5	65.0	64.8	64.6	64.4	64.2
82.5°	51.9	51.5	51.0	50.6	50.4	50.1	50.0	49.8
85°	30.2	29.8	29.3	29.0	29.0	29.0	29.0	29.0
87.5°	17.9	18.1	18.3	18.6	18.9	19.1	19.4	19.8
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	58.5	59.7	60.8	61.5	61.9	62.3	62.7	63.1
95°	109.9	110.8	111.8	112.3	112.3	112.3	112.3	112.3
97.5°	173.1	174.3	175.4	176.0	176.0	176.0	176.0	176.0
100°	218.7	219.3	220.0	220.3	220.3	220.3	220.3	220.3
102.5°	266.9	267.9	268.7	269.3	269.6	269.8	270.0	270.3
105°	340.2	341.1	342.0	343.0	343.9	344.9	345.8	346.8
107.5°	419.3	420.2	421.1	421.5	421.4	421.4	421.3	421.2
110°	472.0	471.4	470.7	470.9	471.8	472.8	473.7	474.7





TEST NUMBER: P333074-830

CATALOG NUMBER: S124RDIW-S795D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	528.7	528.6	528.5	528.5	528.7	528.9	529.0	529.2
115°	616.1	615.9	615.6	615.2	614.9	614.6	614.3	614.0
117.5°	700.2	699.2	698.0	697.2	696.5	696.0	695.3	694.7
120°	757.1	755.6	754.0	753.6	754.2	754.8	755.4	756.1
122.5°	815.0	814.0	812.9	811.8	810.7	809.5	808.4	807.3
125°	899.8	899.2	898.5	897.9	897.2	896.6	896.0	895.3
127.5°	980.8	980.1	979.5	978.9	978.5	978.0	977.4	976.9
130°	1037.6	1037.0	1036.3	1035.4	1034.2	1032.9	1031.6	1030.4
132.5°	1091.1	1090.4	1089.8	1089.2	1088.7	1088.3	1087.7	1087.2
135°	1171.2	1170.6	1170.0	1169.1	1168.2	1167.2	1166.3	1165.4
137.5°	1248.8	1247.9	1247.1	1246.8	1247.0	1247.2	1247.4	1247.5
140°	1299.8	1299.5	1299.1	1298.8	1298.5	1298.2	1297.9	1297.6
142.5°	1348.0	1347.9	1347.9	1347.8	1347.7	1347.7	1347.6	1347.6
145°	1420.6	1420.2	1419.9	1419.3	1418.3	1417.4	1416.5	1415.5
147.5°	1486.4	1486.1	1485.8	1485.5	1485.3	1485.0	1484.6	1484.3
150°	1527.8	1527.8	1527.8	1527.7	1527.3	1527.0	1526.7	1526.4
152.5°	1566.8	1567.5	1568.3	1568.3	1567.4	1566.7	1565.8	1565.0
155°	1621.3	1622.5	1623.8	1623.8	1622.5	1621.3	1620.0	1618.7
157.5°	1669.2	1670.2	1671.1	1671.0	1670.0	1669.0	1667.8	1666.8
160°	1698.8	1699.8	1700.7	1700.3	1698.8	1697.2	1695.6	1694.0
162.5°	1725.3	1727.0	1728.7	1728.8	1727.2	1725.7	1724.1	1722.5
165°	1760.4	1762.3	1764.2	1764.5	1763.2	1762.0	1760.7	1759.4
167.5°	1790.0	1791.9	1793.8	1793.8	1791.8	1789.8	1787.8	1785.8
170°	1805.9	1807.8	1809.7	1809.5	1807.3	1805.1	1802.9	1800.6
172.5°	1817.8	1819.9	1822.0	1822.0	1819.8	1817.6	1815.3	1813.2
175°	1830.7	1832.9	1835.1	1835.1	1832.9	1830.7	1828.4	1826.3
177.5°	1837.8	1839.5	1841.3	1841.2	1839.1	1837.1	1835.1	1833.1
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6

(END OF REPORT)