

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333017-935

Luminaire Tested: **S124RDIW-S350D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333017-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D470U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2845.0 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333017-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333017-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P333017-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.8
10°-20°	139.4	4.9
20°-30°	201.3	7.1
30°-40°	228.2	8.0
40°-50°	220.4	7.7
50°-60°	183.2	6.4
60°-70°	126.5	4.4
70°-80°	64.1	2.3
80°-90°	18.0	0.6
90°-100°	17.8	0.6
100°-110°	113.8	4.0
110°-120°	217.6	7.6
120°-130°	276.3	9.7
130°-140°	295.6	10.4
140°-150°	276.4	9.7
150°-160°	222.9	7.8
160°-170°	143.8	5.1
170°-180°	49.6	1.7
0°-30°	390.7	13.7
0°-40°	619.0	21.8
0°-60°	1022.6	35.9
0°-90°	1231.2	43.3
90°-120°	349.2	12.3
90°-150°	1197.5	42.1
90°-180°	1614.0	56.7
0°-180°	2845.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	1	5	9	11	12	2
95°	21	9	9	11	11	28
105°	117	120	122	124	111	123
115°	219	220	220	221	221	216
125°	308	310	309	310	311	275
135°	382	382	384	384	385	295
145°	441	442	442	443	443	275
155°	484	484	483	484	483	223
165°	510	508	508	511	508	144
175°	522	520	520	523	519	50
180°	522	522	522	522	522	



TEST NUMBER: P333017-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	7.7	7.3	7.0	6.5	6.2	6.0	6.1	6.1	6.2	6.3	6.3
90°	1.2	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1
92.5°	4.9	5.0	5.0	5.1	5.2	5.5	6.2	6.9	7.6	8.3	8.8
95°	21.4	18.5	15.6	12.7	9.6	8.3	8.4	8.4	8.5	8.6	9.1
97.5°	45.5	47.4	49.2	51.1	53.0	49.0	39.3	29.6	20.0	10.3	10.3
100°	64.0	65.5	67.2	68.7	70.3	65.0	53.0	41.1	29.1	17.1	15.7
102.5°	84.6	85.8	86.9	88.0	89.2	88.9	87.4	85.8	84.3	82.7	66.8
105°	117.4	118.0	118.5	119.0	119.5	120.0	120.5	120.9	121.3	121.7	122.5
107.5°	148.0	148.3	148.5	148.8	149.0	149.5	150.0	150.6	151.2	151.8	152.1
110°	168.6	168.8	169.1	169.4	169.6	170.0	170.5	171.1	171.6	172.1	172.3



TEST NUMBER: P333017-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.6	189.0	189.5	189.9	190.5	190.8	191.1	191.2	191.5	191.7	191.7
115°	219.3	219.6	219.8	220.1	220.3	220.4	220.3	220.2	220.2	220.1	220.2
117.5°	247.0	247.4	247.7	248.1	248.4	248.7	248.8	249.0	249.3	249.4	249.3
120°	265.7	266.0	266.4	266.7	267.1	267.3	267.2	267.1	267.0	266.9	267.1
122.5°	283.2	283.4	283.6	283.9	284.0	284.2	284.3	284.5	284.6	284.7	284.8
125°	308.2	308.6	308.9	309.3	309.6	309.7	309.5	309.4	309.2	309.0	309.3
127.5°	332.0	332.1	332.2	332.3	332.3	332.6	332.9	333.4	333.8	334.2	334.2
130°	347.2	347.3	347.5	347.6	347.7	347.8	348.1	348.4	348.6	348.9	349.0
132.5°	361.4	361.4	361.6	361.8	362.0	362.2	362.6	362.8	363.2	363.5	363.6
135°	382.4	382.3	382.2	382.1	382.0	382.2	382.5	382.9	383.2	383.6	383.7
137.5°	401.1	401.1	401.1	401.1	401.2	401.4	401.7	402.2	402.5	402.9	403.1
140°	413.2	413.4	413.5	413.7	413.9	414.1	414.2	414.5	414.7	414.8	415.1
142.5°	424.1	424.5	424.8	425.1	425.4	425.6	425.7	425.9	425.9	426.0	426.2
145°	440.9	441.2	441.4	441.7	442.0	442.1	442.1	442.1	442.1	442.1	442.2
147.5°	454.3	454.8	455.2	455.7	456.2	456.4	456.3	456.2	456.2	456.1	456.2
150°	464.0	464.3	464.7	465.0	465.4	465.5	465.4	465.3	465.2	465.1	465.1
152.5°	472.1	472.3	472.6	472.9	473.2	473.2	473.1	472.9	472.8	472.6	472.8
155°	483.5	483.5	483.6	483.7	483.8	483.7	483.5	483.2	482.9	482.7	483.0
157.5°	493.1	493.0	492.9	492.9	492.8	492.7	492.4	492.1	491.8	491.5	492.0
160°	498.7	498.4	498.2	497.9	497.7	497.5	497.4	497.3	497.2	497.1	497.7
162.5°	503.7	503.3	503.0	502.7	502.4	502.1	502.0	502.0	501.9	501.8	502.3
165°	510.0	509.5	509.1	508.7	508.2	508.1	508.1	508.1	508.1	508.1	508.8
167.5°	515.0	514.5	514.1	513.7	513.2	512.9	512.9	512.8	512.8	512.7	513.5
170°	517.8	517.3	516.8	516.3	515.7	515.5	515.6	515.7	515.7	515.8	516.5
172.5°	519.7	519.2	518.7	518.1	517.6	517.4	517.5	517.5	517.6	517.7	518.4
175°	521.7	521.2	520.6	520.1	519.6	519.4	519.5	519.6	519.7	519.8	520.6
177.5°	522.6	522.2	521.7	521.2	520.7	520.6	520.6	520.8	520.9	521.1	521.6
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7



TEST NUMBER: P333017-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	6.4	6.4	6.4	6.5	6.5	6.7	6.8	6.9
90°	9.6	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	9.3	9.8	10.3	10.6	10.7	10.7	10.8	10.8
95°	9.6	10.2	10.7	10.9	11.0	11.1	11.2	11.3
97.5°	10.4	10.4	10.5	10.6	10.7	10.8	10.8	10.9
100°	14.2	12.7	11.3	10.6	10.7	10.8	10.8	10.9
102.5°	50.9	35.0	19.1	11.2	11.2	11.2	11.2	11.3
105°	123.3	124.1	124.8	123.7	120.5	117.4	114.3	111.2
107.5°	152.6	152.9	153.3	153.7	154.0	154.3	154.6	155.0
110°	172.5	172.6	172.8	173.0	173.2	173.5	173.7	174.0



TEST NUMBER: P333017-935

CATALOG NUMBER: S124RDIW-S350D470U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.7	191.7	191.6	191.7	192.1	192.4	192.8	193.0
115°	220.4	220.6	220.8	220.8	220.8	220.8	220.8	220.8
117.5°	249.3	249.3	249.3	249.3	249.2	249.2	249.2	249.1
120°	267.3	267.4	267.6	267.6	267.4	267.3	267.1	266.9
122.5°	284.9	285.0	285.1	285.1	284.9	284.7	284.6	284.4
125°	309.5	309.8	310.0	310.2	310.3	310.4	310.5	310.6
127.5°	334.1	334.0	334.0	333.9	333.8	333.7	333.7	333.6
130°	349.0	349.1	349.2	349.2	349.2	349.2	349.2	349.2
132.5°	363.7	363.8	363.9	363.9	363.8	363.8	363.7	363.6
135°	383.9	384.1	384.3	384.4	384.6	384.8	385.0	385.1
137.5°	403.3	403.5	403.7	403.7	403.7	403.6	403.6	403.6
140°	415.3	415.6	415.9	416.0	416.1	416.2	416.3	416.4
142.5°	426.4	426.6	426.8	426.9	426.9	427.0	427.0	427.0
145°	442.3	442.4	442.5	442.6	442.7	442.9	443.1	443.2
147.5°	456.2	456.2	456.3	456.4	456.5	456.6	456.7	456.8
150°	465.1	465.1	465.1	465.2	465.3	465.4	465.5	465.5
152.5°	472.9	473.0	473.2	473.2	473.2	473.1	473.0	473.0
155°	483.4	483.7	484.1	484.1	483.9	483.6	483.4	483.1
157.5°	492.4	492.8	493.3	493.3	492.8	492.4	492.0	491.5
160°	498.2	498.7	499.2	499.2	498.7	498.2	497.7	497.1
162.5°	502.8	503.3	503.9	503.9	503.3	502.7	502.0	501.5
165°	509.5	510.1	510.8	510.7	510.0	509.2	508.4	507.6
167.5°	514.3	515.1	515.8	515.7	514.9	514.0	513.2	512.3
170°	517.2	517.9	518.7	518.6	517.6	516.8	515.9	515.1
172.5°	519.1	519.8	520.5	520.4	519.4	518.5	517.5	516.6
175°	521.3	522.1	522.9	522.7	521.7	520.6	519.6	518.6
177.5°	522.2	522.7	523.3	523.1	522.4	521.5	520.6	519.9
180°	521.7	521.7	521.7	521.7	521.7	521.7	521.7	521.7

(END OF REPORT)