

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333021-935

Luminaire Tested: **S124RDIW-S350D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333021-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D770U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3875.4 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333021-935

CATALOG NUMBER: S124RDIW-S350D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333021-935

CATALOG NUMBER: S124RDIW-S350D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	34	27
2	86	78	73	68	77	71	66	62	56	53	50	43	41	39	31	30	28	23
3	78	69	62	57	70	62	56	52	50	46	42	38	36	33	28	26	24	20
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	66	54	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	19	16	15	12
8	52	40	32	27	46	36	30	25	29	25	21	23	20	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P333021-935

CATALOG NUMBER: S124RDIW-S350D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.3
10°-20°	139.4	3.6
20°-30°	201.3	5.2
30°-40°	228.2	5.9
40°-50°	220.4	5.7
50°-60°	183.2	4.7
60°-70°	126.5	3.3
70°-80°	64.1	1.7
80°-90°	18.9	0.5
90°-100°	29.2	0.8
100°-110°	186.3	4.8
110°-120°	356.5	9.2
120°-130°	452.5	11.7
130°-140°	484.2	12.5
140°-150°	452.7	11.7
150°-160°	365.1	9.4
160°-170°	235.5	6.1
170°-180°	81.2	2.1
0°-30°	390.7	10.1
0°-40°	619.0	16.0
0°-60°	1022.6	26.4
0°-90°	1232.2	31.8
90°-120°	572.0	14.8
90°-150°	1961.4	50.6
90°-180°	2643.0	68.2
0°-180°	3875.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	2	9	14	18	19	3
95°	35	15	14	18	18	45
105°	192	196	199	204	182	201
115°	359	361	360	362	362	353
125°	505	507	506	508	509	451
135°	626	626	628	630	631	482
145°	722	724	724	725	726	451
155°	792	792	791	793	791	365
165°	835	832	832	837	832	236
175°	854	851	851	856	849	81
180°	854	854	854	854	854	



TEST NUMBER: P333021-935

CATALOG NUMBER: S124RDIW-S350D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	7.9	7.6	7.3	7.1	6.8	6.7	6.9	7.1	7.2	7.4	7.5
90°	1.9	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9
92.5°	8.1	8.2	8.3	8.3	8.4	9.0	10.2	11.3	12.4	13.5	14.4
95°	35.1	30.3	25.5	20.7	15.8	13.5	13.6	13.8	13.9	14.0	14.9
97.5°	74.6	77.7	80.7	83.7	86.7	80.2	64.4	48.6	32.7	16.9	17.0
100°	104.8	107.4	109.9	112.4	115.0	106.5	87.0	67.3	47.7	28.2	25.7
102.5°	138.5	140.4	142.3	144.2	146.0	145.7	143.2	140.6	138.0	135.5	109.4
105°	192.3	193.2	194.1	194.9	195.8	196.6	197.3	197.9	198.7	199.4	200.7
107.5°	242.4	242.8	243.2	243.7	244.1	244.8	245.7	246.7	247.6	248.6	249.3
110°	276.1	276.6	277.0	277.4	277.8	278.4	279.3	280.2	281.0	281.8	282.1



TEST NUMBER: P333021-935

CATALOG NUMBER: S124RDIW-S350D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.8	309.6	310.4	311.1	311.9	312.5	312.9	313.2	313.7	314.1	314.0
115°	359.2	359.6	360.1	360.4	360.8	361.0	360.8	360.8	360.6	360.4	360.8
117.5°	404.6	405.1	405.7	406.2	406.8	407.3	407.6	407.9	408.2	408.5	408.5
120°	435.2	435.8	436.4	437.0	437.5	437.7	437.6	437.5	437.3	437.1	437.5
122.5°	463.9	464.2	464.5	464.9	465.2	465.5	465.7	465.9	466.1	466.3	466.5
125°	504.9	505.5	506.0	506.6	507.1	507.3	507.0	506.8	506.4	506.2	506.6
127.5°	543.7	543.9	544.1	544.2	544.3	544.8	545.4	546.0	546.6	547.3	547.3
130°	568.8	568.9	569.1	569.2	569.4	569.6	570.1	570.5	570.9	571.4	571.5
132.5°	591.9	592.1	592.4	592.5	592.8	593.2	593.7	594.3	594.9	595.4	595.6
135°	626.3	626.2	626.0	625.9	625.8	625.9	626.5	627.1	627.7	628.3	628.5
137.5°	656.9	656.9	657.0	657.0	657.1	657.5	658.1	658.7	659.4	660.0	660.2
140°	676.8	677.1	677.3	677.7	678.0	678.2	678.6	678.8	679.1	679.4	679.8
142.5°	694.7	695.3	695.8	696.2	696.7	697.1	697.2	697.4	697.6	697.8	698.1
145°	722.2	722.6	723.1	723.5	723.9	724.1	724.1	724.1	724.1	724.1	724.3
147.5°	744.1	744.9	745.6	746.4	747.3	747.5	747.4	747.3	747.1	747.0	747.1
150°	759.9	760.4	761.0	761.6	762.2	762.4	762.2	762.1	762.0	761.8	761.8
152.5°	773.2	773.6	774.1	774.6	775.0	775.1	774.8	774.6	774.4	774.1	774.3
155°	791.9	792.0	792.1	792.3	792.5	792.3	791.9	791.4	791.0	790.6	791.2
157.5°	807.6	807.5	807.4	807.4	807.3	806.9	806.5	806.0	805.5	805.0	805.7
160°	816.7	816.3	816.0	815.5	815.1	814.8	814.7	814.5	814.3	814.2	815.1
162.5°	824.9	824.4	823.9	823.4	822.8	822.4	822.3	822.2	822.0	821.9	822.8
165°	835.3	834.6	833.9	833.2	832.5	832.2	832.2	832.2	832.2	832.2	833.3
167.5°	843.5	842.7	842.1	841.3	840.5	840.2	840.1	840.0	839.9	839.8	841.0
170°	848.1	847.2	846.4	845.5	844.7	844.3	844.5	844.6	844.7	844.9	846.0
172.5°	851.2	850.3	849.5	848.6	847.7	847.4	847.6	847.7	847.8	848.0	849.1
175°	854.5	853.6	852.8	852.0	851.1	850.8	850.8	851.0	851.2	851.3	852.6
177.5°	856.0	855.2	854.5	853.6	852.8	852.6	852.8	853.0	853.3	853.4	854.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5



TEST NUMBER: P333021-935

CATALOG NUMBER: S124RDIW-S350D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	7.6	7.7	7.7	7.9	8.0	8.2	8.3	8.4
90°	15.8	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	15.2	16.1	17.0	17.4	17.5	17.6	17.6	17.7
95°	15.8	16.6	17.5	18.0	18.1	18.3	18.4	18.5
97.5°	17.0	17.1	17.2	17.3	17.5	17.7	17.7	17.9
100°	23.3	20.8	18.4	17.3	17.5	17.7	17.7	17.9
102.5°	83.4	57.3	31.3	18.3	18.3	18.3	18.3	18.4
105°	202.0	203.2	204.5	202.6	197.5	192.3	187.3	182.2
107.5°	249.9	250.5	251.2	251.7	252.3	252.8	253.3	253.8
110°	282.4	282.7	283.0	283.4	283.8	284.2	284.6	285.1



TEST NUMBER: P333021-935

CATALOG NUMBER: S124RDIW-S350D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.9	313.9	313.8	314.1	314.6	315.1	315.7	316.2
115°	361.0	361.3	361.6	361.7	361.7	361.7	361.7	361.7
117.5°	408.4	408.4	408.3	408.2	408.2	408.1	408.0	408.0
120°	437.7	438.0	438.2	438.2	438.0	437.7	437.5	437.1
122.5°	466.7	466.8	467.0	466.9	466.7	466.3	466.1	465.8
125°	507.0	507.5	507.9	508.2	508.3	508.4	508.6	508.8
127.5°	547.2	547.1	547.0	546.9	546.8	546.6	546.6	546.5
130°	571.6	571.8	572.0	572.0	572.0	572.0	572.0	572.0
132.5°	595.6	595.8	596.0	596.0	595.9	595.7	595.6	595.6
135°	628.8	629.1	629.4	629.6	629.9	630.3	630.5	630.8
137.5°	660.6	660.9	661.2	661.3	661.2	661.2	661.1	661.0
140°	680.2	680.6	681.1	681.4	681.5	681.7	681.8	681.9
142.5°	698.4	698.7	699.0	699.2	699.2	699.2	699.3	699.3
145°	724.4	724.5	724.7	724.9	725.1	725.5	725.7	726.0
147.5°	747.2	747.3	747.4	747.6	747.7	747.9	748.0	748.1
150°	761.8	761.8	761.8	761.9	762.1	762.2	762.3	762.4
152.5°	774.6	774.7	775.0	775.1	775.0	774.9	774.8	774.7
155°	791.7	792.3	792.8	792.9	792.5	792.0	791.6	791.3
157.5°	806.5	807.3	808.0	808.0	807.3	806.5	805.7	805.0
160°	816.0	816.7	817.6	817.6	816.7	816.0	815.1	814.2
162.5°	823.6	824.4	825.3	825.3	824.3	823.3	822.3	821.4
165°	834.4	835.5	836.6	836.6	835.3	834.1	832.8	831.5
167.5°	842.3	843.5	844.8	844.7	843.3	841.9	840.4	839.0
170°	847.1	848.3	849.5	849.3	847.9	846.4	845.1	843.6
172.5°	850.2	851.4	852.5	852.3	850.8	849.3	847.7	846.2
175°	853.9	855.1	856.4	856.2	854.5	852.8	851.1	849.4
177.5°	855.3	856.2	857.1	856.9	855.5	854.1	852.8	851.4
180°	854.5	854.5	854.5	854.5	854.5	854.5	854.5	854.5

(END OF REPORT)