

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333062-830

Luminaire Tested: **S124RDIW-S795D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333062-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D770U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5537.3 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333062-830

CATALOG NUMBER: S124RDIW-S795D770U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333062-830

CATALOG NUMBER: S124RDIW-S795D770U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86		73	73	73		60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71		64	63	61		54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59		57	54	51		48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50		51	47	44		43	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43		45	41	38		38	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37		41	36	33		35	31	29	26
6	64	52	44	38	60	49	42	37	43	37	33		37	32	29		31	28	25	23
7	60	47	39	34	55	44	37	32	39	33	29		34	29	26		29	25	23	20
8	55	43	35	30	51	40	33	29	35	30	26		31	26	23		26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23		28	24	21		24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21		26	22	19		23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10571	10571	10571
5°	10594	10464	10529
10°	10528	10339	10339
15°	10407	10122	10046
20°	10241	9836	9655
25°	10029	9502	9260
30°	9822	9149	8766
35°	9594	8784	8270
40°	9319	8368	7734
45°	9065	7955	7188
50°	8776	7479	6610
55°	8466	6984	5983
60°	8126	6442	5341
65°	7815	5765	4713
70°	7360	5016	4001
75°	6784	4161	3250
80°	5918	3166	2985
85°	5011	2881	2686



TEST NUMBER: P333062-830

CATALOG NUMBER: S124RDIW-S795D770U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	2.2
10°-20°	343.0	6.2
20°-30°	495.3	8.9
30°-40°	561.4	10.1
40°-50°	542.1	9.8
50°-60°	450.8	8.1
60°-70°	311.3	5.6
70°-80°	157.8	2.8
80°-90°	43.2	0.8
90°-100°	59.7	1.1
100°-110°	176.7	3.2
110°-120°	300.0	5.4
120°-130°	395.5	7.1
130°-140°	444.2	8.0
140°-150°	436.5	7.9
150°-160°	367.1	6.6
160°-170°	244.3	4.4
170°-180°	85.5	1.5
0°-30°	961.2	17.4
0°-40°	1522.6	27.5
0°-60°	2515.6	45.4
0°-90°	3027.8	54.7
90°-120°	536.4	9.7
90°-150°	1812.6	32.7
90°-180°	2510.0	45.3
0°-180°	5537.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1307	1303	1291	1301	1299	124
15°	1245	1235	1211	1209	1202	351
25°	1126	1106	1067	1050	1040	519
35°	974	940	891	858	839	608
45°	794	756	697	649	630	612
55°	602	560	496	446	425	538
65°	409	365	302	260	247	404
75°	218	180	133	111	104	230
85°	54	35	31	29	29	61
90°	2	10	15	19	21	5
95°	42	48	53	55	55	47
105°	163	164	166	169	171	173
115°	305	305	304	303	302	301
125°	444	444	444	442	441	396
135°	573	577	577	576	574	443
145°	696	699	700	699	697	435
155°	798	797	797	799	797	367
165°	868	866	865	868	866	245
175°	903	900	899	903	899	86
180°	904	904	904	904	904	



TEST NUMBER: P333062-830

CATALOG NUMBER: S124RDIW-S795D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1312.6	1311.8	1311.1	1310.4	1309.7	1308.3	1306.4	1304.5	1302.5	1300.5	1302.5
5°	1307.3	1306.5	1305.5	1304.7	1303.7	1302.0	1299.3	1296.7	1293.9	1291.3	1293.5
7.5°	1295.5	1294.6	1293.6	1292.7	1291.8	1289.6	1286.1	1282.6	1279.1	1275.6	1277.1
10°	1284.3	1283.2	1282.0	1280.9	1279.8	1277.2	1273.3	1269.2	1265.3	1261.2	1262.1
12.5°	1269.8	1268.6	1267.2	1265.9	1264.7	1261.7	1257.0	1252.2	1247.5	1242.7	1243.3
15°	1245.2	1243.2	1241.1	1239.2	1237.2	1233.4	1227.8	1222.2	1216.6	1211.1	1210.6
17.5°	1215.3	1212.4	1209.5	1206.6	1203.7	1198.9	1192.2	1185.5	1178.8	1172.1	1170.9
20°	1192.0	1189.1	1186.3	1183.4	1180.4	1175.3	1167.6	1160.1	1152.4	1144.9	1143.1
22.5°	1166.4	1163.1	1159.9	1156.6	1153.4	1147.6	1139.5	1131.4	1123.3	1115.2	1112.6
25°	1125.9	1121.8	1117.9	1113.8	1109.8	1103.2	1094.1	1085.0	1075.8	1066.7	1062.9
27.5°	1083.4	1078.4	1073.3	1068.3	1063.2	1055.8	1046.0	1036.3	1026.5	1016.8	1012.1
30°	1053.7	1048.1	1042.5	1037.0	1031.4	1023.4	1013.0	1002.5	991.9	981.5	975.9
32.5°	1022.4	1016.2	1009.8	1003.5	997.3	988.7	977.9	967.0	956.2	945.4	939.0
35°	973.5	966.4	959.2	952.1	945.0	935.9	924.7	913.5	902.4	891.3	883.7
37.5°	921.1	913.8	906.4	899.1	891.7	881.9	869.6	857.2	844.9	832.5	824.1
40°	884.3	876.9	869.6	862.2	854.9	844.8	832.1	819.4	806.7	794.0	784.7
42.5°	848.9	841.2	833.6	825.9	818.1	807.7	794.5	781.2	768.0	754.7	745.2
45°	794.0	785.8	777.5	769.3	761.0	750.3	736.9	723.5	710.1	696.8	685.9
47.5°	737.3	728.8	720.3	711.7	703.2	692.0	678.2	664.2	650.4	636.4	625.1
50°	698.8	690.1	681.4	672.7	664.0	652.5	638.3	624.1	609.7	595.5	584.4
52.5°	659.5	651.0	642.4	634.0	625.5	613.9	599.3	584.7	570.0	555.4	544.1
55°	601.5	592.6	583.7	574.8	565.9	554.2	539.7	525.2	510.8	496.2	484.7
57.5°	544.2	534.9	525.7	516.4	507.1	495.3	481.1	466.8	452.6	438.3	426.6
60°	503.3	494.4	485.5	476.5	467.6	456.1	441.8	427.5	413.3	399.0	387.4
62.5°	466.4	457.1	447.9	438.6	429.3	417.4	402.7	388.1	373.5	358.9	348.2
65°	409.1	399.4	389.8	380.3	370.7	358.8	344.5	330.3	316.0	301.8	292.2
67.5°	349.5	340.4	331.1	322.0	312.7	301.6	288.3	275.1	261.8	248.6	240.3
70°	311.8	302.5	293.0	283.7	274.4	263.3	250.6	237.9	225.3	212.5	205.2
72.5°	271.7	263.3	254.8	246.3	237.8	227.6	215.7	203.6	191.6	179.6	173.3
75°	217.5	209.3	201.0	192.8	184.5	175.2	164.8	154.3	143.8	133.4	128.2
77.5°	162.6	155.6	148.6	141.7	134.6	126.9	118.5	110.0	101.5	93.0	90.0
80°	127.3	120.8	114.4	107.9	101.5	94.9	88.2	81.5	74.8	68.1	67.5
82.5°	96.9	91.0	85.0	79.1	73.1	68.2	64.5	60.6	56.7	53.0	52.4
85°	54.1	49.7	45.2	40.8	36.3	33.7	33.1	32.4	31.8	31.1	30.6
87.5°	18.9	17.8	16.7	15.6	14.5	14.0	14.1	14.1	14.2	14.3	14.3
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	15.0	17.0	18.9	20.8	22.8	24.2	25.1	25.9	26.9	27.7	28.3
95°	41.9	43.4	44.8	46.2	47.6	48.8	49.9	51.0	52.1	53.2	53.6
97.5°	73.3	74.5	75.6	76.6	77.8	79.0	80.3	81.5	82.8	84.1	84.6
100°	97.9	98.6	99.2	99.8	100.4	101.4	102.8	104.2	105.7	107.1	107.4
102.5°	123.7	123.9	124.1	124.4	124.7	125.5	126.7	128.0	129.2	130.5	131.0
105°	163.0	163.2	163.3	163.4	163.6	164.0	164.7	165.2	165.9	166.5	166.9
107.5°	204.2	204.4	204.6	204.8	205.0	205.2	205.3	205.4	205.5	205.6	205.9
110°	232.2	232.5	232.9	233.2	233.5	233.6	233.4	233.3	233.1	232.9	232.6



TEST NUMBER: P333062-830

CATALOG NUMBER: S124RDIW-S795D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	261.4	261.4	261.5	261.6	261.6	261.5	261.2	260.9	260.6	260.3	260.3
115°	305.0	305.0	305.0	305.0	305.0	304.8	304.5	304.3	303.9	303.6	303.4
117.5°	346.1	346.3	346.4	346.5	346.7	346.6	346.4	346.2	345.9	345.7	345.2
120°	373.5	374.2	374.8	375.4	376.1	376.1	375.7	375.2	374.8	374.3	373.4
122.5°	402.1	402.4	402.6	402.8	403.1	403.1	402.9	402.7	402.5	402.3	401.7
125°	444.2	444.2	444.2	444.2	444.2	444.1	443.9	443.8	443.7	443.5	443.2
127.5°	482.4	482.9	483.3	483.8	484.3	484.4	484.1	483.9	483.6	483.4	483.1
130°	509.3	509.7	510.2	510.7	511.1	511.3	511.3	511.3	511.3	511.3	511.0
132.5°	536.7	537.1	537.3	537.7	538.1	538.2	538.0	537.9	537.8	537.6	537.3
135°	573.0	573.8	574.8	575.7	576.6	577.1	577.1	577.1	577.1	577.1	576.8
137.5°	612.4	612.8	613.2	613.7	614.2	614.4	614.7	614.9	615.2	615.5	615.0
140°	638.7	638.9	639.3	639.6	639.9	640.1	640.1	640.1	640.1	640.1	639.9
142.5°	662.7	663.1	663.4	663.6	664.0	664.1	663.9	663.8	663.7	663.5	663.5
145°	696.1	696.6	697.3	698.0	698.5	698.9	699.1	699.3	699.4	699.6	699.4
147.5°	729.1	729.8	730.6	731.3	732.1	732.4	732.3	732.1	732.0	731.9	731.7
150°	749.2	749.8	750.5	751.1	751.7	752.1	752.1	752.1	752.1	752.1	752.1
152.5°	768.3	768.6	769.0	769.4	769.8	770.0	770.1	770.2	770.3	770.4	770.8
155°	797.5	797.5	797.5	797.5	797.5	797.4	797.2	797.1	796.9	796.8	797.4
157.5°	822.1	821.8	821.5	821.2	821.0	820.9	820.8	820.8	820.8	820.7	821.1
160°	836.7	836.5	836.3	836.2	836.0	835.8	835.8	835.6	835.4	835.3	835.8
162.5°	850.1	849.7	849.2	848.9	848.5	848.2	848.0	847.9	847.7	847.5	848.4
165°	868.2	867.7	867.2	866.8	866.3	865.9	865.5	865.3	865.0	864.6	865.5
167.5°	881.9	881.4	880.7	880.1	879.4	879.0	879.1	879.1	879.1	879.2	880.1
170°	889.9	889.0	888.3	887.5	886.7	886.4	886.6	886.7	886.8	887.0	888.0
172.5°	895.4	894.8	894.1	893.4	892.8	892.5	892.5	892.6	892.6	892.6	893.7
175°	903.1	902.3	901.5	900.8	900.0	899.6	899.4	899.2	899.1	898.9	900.0
177.5°	905.6	905.0	904.4	903.8	903.1	902.9	902.9	902.9	902.9	902.9	903.7
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P333062-830

CATALOG NUMBER: S124RDIW-S795D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4	1309.4
2.5°	1304.5	1306.4	1308.3	1309.3	1309.1	1308.9	1308.7	1308.5
5°	1295.7	1298.0	1300.2	1301.1	1300.6	1300.2	1299.8	1299.3
7.5°	1278.5	1280.0	1281.4	1281.7	1281.0	1280.3	1279.6	1278.8
10°	1263.0	1263.9	1264.8	1264.8	1263.9	1263.0	1262.1	1261.2
12.5°	1243.9	1244.3	1244.9	1244.5	1243.3	1242.1	1240.8	1239.5
15°	1210.2	1209.8	1209.3	1208.3	1206.7	1205.1	1203.6	1202.0
17.5°	1169.7	1168.5	1167.2	1165.4	1163.0	1160.6	1158.3	1155.9
20°	1141.3	1139.5	1137.7	1135.5	1132.6	1129.6	1126.7	1123.9
22.5°	1109.9	1107.2	1104.6	1102.0	1099.7	1097.3	1095.0	1092.6
25°	1059.1	1055.4	1051.6	1048.6	1046.3	1044.1	1041.9	1039.6
27.5°	1007.4	1002.8	998.1	994.1	990.9	987.7	984.5	981.3
30°	970.3	964.8	959.2	954.6	951.1	947.5	944.0	940.4
32.5°	932.5	926.0	919.5	914.6	911.3	907.9	904.5	901.1
35°	876.1	868.6	861.0	855.2	851.2	847.2	843.1	839.1
37.5°	815.6	807.1	798.6	792.4	788.4	784.4	780.4	776.4
40°	775.3	765.9	756.6	749.9	745.9	741.9	737.9	733.9
42.5°	735.7	726.1	716.6	709.7	705.5	701.3	697.2	693.0
45°	675.0	664.0	653.1	645.6	641.6	637.6	633.6	629.6
47.5°	613.8	602.5	591.2	583.2	578.9	574.5	570.0	565.6
50°	573.3	562.1	550.9	543.3	539.0	534.8	530.6	526.3
52.5°	532.8	521.5	510.1	502.3	497.9	493.4	489.1	484.7
55°	473.1	461.5	450.0	442.1	437.8	433.6	429.3	425.1
57.5°	414.8	403.0	391.2	383.8	380.6	377.4	374.2	371.0
60°	375.9	364.3	352.7	345.1	341.6	338.0	334.4	330.8
62.5°	337.5	326.9	316.1	309.3	306.5	303.7	300.8	297.9
65°	282.6	273.1	263.4	257.3	254.7	251.9	249.3	246.7
67.5°	232.1	223.9	215.7	210.1	207.2	204.2	201.2	198.3
70°	197.8	190.5	183.1	178.3	176.2	173.9	171.6	169.5
72.5°	167.1	160.8	154.5	150.3	148.4	146.3	144.2	142.1
75°	123.1	118.0	112.8	109.6	108.3	107.0	105.6	104.2
77.5°	87.1	84.1	81.1	79.4	79.0	78.6	78.2	77.8
80°	66.8	66.2	65.5	65.0	64.8	64.6	64.4	64.2
82.5°	51.9	51.5	51.0	50.6	50.4	50.1	50.0	49.8
85°	30.2	29.8	29.3	29.0	29.0	29.0	29.0	29.0
87.5°	14.3	14.3	14.3	14.4	14.7	15.0	15.2	15.5
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	28.8	29.4	30.0	30.3	30.5	30.7	30.9	31.1
95°	54.1	54.6	55.0	55.2	55.2	55.2	55.2	55.2
97.5°	85.2	85.8	86.3	86.6	86.6	86.6	86.6	86.6
100°	107.6	107.9	108.3	108.4	108.4	108.4	108.4	108.4
102.5°	131.4	131.9	132.2	132.5	132.7	132.8	132.9	133.1
105°	167.4	167.9	168.3	168.8	169.3	169.8	170.2	170.7
107.5°	206.4	206.8	207.3	207.5	207.5	207.5	207.4	207.4
110°	232.3	232.1	231.7	231.8	232.2	232.7	233.2	233.7



TEST NUMBER: P333062-830

CATALOG NUMBER: S124RDIW-S795D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	260.2	260.1	260.1	260.1	260.2	260.3	260.4	260.5
115°	303.3	303.1	302.9	302.8	302.7	302.6	302.4	302.2
117.5°	344.7	344.1	343.6	343.2	342.9	342.5	342.2	342.0
120°	372.7	371.9	371.2	370.9	371.3	371.6	371.8	372.1
122.5°	401.1	400.7	400.1	399.5	399.0	398.4	397.9	397.4
125°	442.9	442.6	442.2	442.0	441.7	441.3	441.0	440.7
127.5°	482.8	482.5	482.1	481.8	481.6	481.4	481.1	480.9
130°	510.8	510.4	510.1	509.6	509.1	508.4	507.7	507.2
132.5°	537.1	536.8	536.4	536.1	535.9	535.6	535.4	535.2
135°	576.5	576.2	575.9	575.5	575.0	574.6	574.1	573.6
137.5°	614.6	614.3	613.9	613.7	613.8	613.9	614.0	614.1
140°	639.8	639.6	639.4	639.3	639.1	638.9	638.9	638.7
142.5°	663.5	663.5	663.5	663.5	663.4	663.4	663.4	663.3
145°	699.3	699.1	698.9	698.6	698.1	697.7	697.2	696.7
147.5°	731.6	731.5	731.3	731.2	731.0	730.9	730.8	730.6
150°	752.1	752.1	752.1	752.0	751.8	751.6	751.5	751.3
152.5°	771.2	771.6	771.9	771.9	771.6	771.2	770.7	770.3
155°	798.1	798.6	799.3	799.3	798.6	798.1	797.4	796.8
157.5°	821.6	822.1	822.6	822.6	822.0	821.5	821.0	820.4
160°	836.2	836.7	837.2	837.0	836.2	835.4	834.6	833.9
162.5°	849.2	850.1	850.9	850.9	850.2	849.4	848.7	847.8
165°	866.5	867.4	868.4	868.6	867.9	867.2	866.7	866.0
167.5°	881.1	881.9	882.9	882.9	881.9	881.0	880.1	879.0
170°	888.9	889.9	890.8	890.7	889.6	888.5	887.4	886.4
172.5°	894.8	895.8	896.8	896.8	895.7	894.7	893.5	892.5
175°	901.1	902.2	903.2	903.2	902.2	901.1	900.0	898.9
177.5°	904.6	905.4	906.3	906.3	905.2	904.3	903.2	902.3
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5

(END OF REPORT)