

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333045-935

Luminaire Tested: **S124RDIW-S575D1050U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333045-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1050U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5632.8 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333045-935

CATALOG NUMBER: S124RDIW-S575D1050U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333045-935

CATALOG NUMBER: S124RDIW-S575D1050U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7064	7064	7064
5°	7080	6994	7037
10°	7035	6909	6909
15°	6955	6764	6714
20°	6844	6574	6453
25°	6702	6350	6188
30°	6564	6114	5858
35°	6412	5870	5527
40°	6227	5592	5168
45°	6058	5316	4804
50°	5865	4999	4417
55°	5658	4669	3997
60°	5430	4306	3570
65°	5223	3851	3148
70°	4919	3354	2672
75°	4535	2779	2174
80°	3956	2115	1994
85°	3353	1927	1806



TEST NUMBER: P333045-935

CATALOG NUMBER: S124RDIW-S575D1050U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.2	1.5
10°-20°	229.2	4.1
20°-30°	331.0	5.9
30°-40°	375.2	6.7
40°-50°	362.3	6.4
50°-60°	301.3	5.3
60°-70°	208.0	3.7
70°-80°	105.4	1.9
80°-90°	30.4	0.5
90°-100°	39.9	0.7
100°-110°	254.3	4.5
110°-120°	486.6	8.6
120°-130°	617.7	11.0
130°-140°	660.8	11.7
140°-150°	618.0	11.0
150°-160°	498.3	8.8
160°-170°	321.4	5.7
170°-180°	110.8	2.0
0°-30°	642.4	11.4
0°-40°	1017.6	18.1
0°-60°	1681.1	29.8
0°-90°	2025.0	36.0
90°-120°	780.8	13.9
90°-150°	2677.3	47.5
90°-180°	3608.0	64.1
0°-180°	5632.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	874	871	863	869	868	83
15°	832	825	809	808	803	234
25°	752	740	713	702	695	347
35°	651	628	596	573	561	406
45°	531	505	466	434	421	409
55°	402	374	332	298	284	359
65°	273	244	202	174	165	270
75°	145	120	89	74	70	154
85°	36	23	21	20	20	41
90°	3	12	19	24	26	4
95°	48	20	19	24	25	62
105°	263	268	272	278	249	275
115°	490	493	492	494	494	482
125°	689	692	691	693	694	615
135°	855	854	858	859	861	658
145°	986	988	988	989	991	616
155°	1081	1082	1079	1082	1080	498
165°	1140	1136	1136	1142	1135	322
175°	1166	1161	1162	1169	1159	111
180°	1166	1166	1166	1166	1166	



TEST NUMBER: P333045-935

CATALOG NUMBER: S124RDIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	877.2	876.7	876.2	875.7	875.3	874.3	873.1	871.8	870.4	869.1	870.4
5°	873.7	873.1	872.5	871.8	871.3	870.1	868.3	866.5	864.7	863.0	864.4
7.5°	865.7	865.1	864.5	863.9	863.2	861.8	859.5	857.1	854.8	852.5	853.4
10°	858.2	857.6	856.8	856.0	855.3	853.6	850.9	848.2	845.5	842.8	843.4
12.5°	848.6	847.7	846.9	846.0	845.2	843.2	840.0	836.8	833.7	830.5	830.9
15°	832.2	830.8	829.5	828.1	826.7	824.2	820.5	816.8	813.0	809.3	809.1
17.5°	812.2	810.2	808.3	806.3	804.4	801.2	796.8	792.3	787.8	783.3	782.6
20°	796.6	794.7	792.7	790.8	788.8	785.4	780.3	775.2	770.2	765.2	764.0
22.5°	779.5	777.3	775.2	772.9	770.8	767.0	761.6	756.1	750.7	745.3	743.5
25°	752.4	749.8	747.0	744.3	741.7	737.3	731.2	725.0	718.9	712.9	710.3
27.5°	724.0	720.7	717.3	713.9	710.5	705.6	699.0	692.6	686.0	679.5	676.4
30°	704.1	700.4	696.7	693.0	689.3	683.9	676.9	669.9	662.9	655.9	652.2
32.5°	683.3	679.1	674.9	670.6	666.5	660.7	653.5	646.3	639.0	631.8	627.5
35°	650.6	645.8	641.0	636.3	631.5	625.4	617.9	610.5	603.0	595.6	590.6
37.5°	615.6	610.7	605.8	600.9	595.9	589.4	581.1	572.8	564.6	556.4	550.7
40°	590.9	586.0	581.1	576.2	571.3	564.6	556.1	547.6	539.2	530.6	524.3
42.5°	567.3	562.2	557.1	551.9	546.7	539.8	530.9	522.0	513.2	504.4	498.0
45°	530.6	525.1	519.6	514.1	508.6	501.4	492.4	483.5	474.6	465.6	458.3
47.5°	492.8	487.1	481.3	475.6	469.9	462.4	453.1	443.9	434.6	425.3	417.8
50°	467.0	461.2	455.4	449.5	443.8	436.1	426.5	417.1	407.5	398.0	390.5
52.5°	440.7	435.1	429.4	423.7	417.9	410.3	400.5	390.7	380.9	371.2	363.6
55°	402.0	396.1	390.1	384.1	378.2	370.3	360.7	351.0	341.3	331.7	323.9
57.5°	363.7	357.5	351.3	345.1	338.9	331.1	321.5	311.9	302.5	292.9	285.1
60°	336.3	330.4	324.4	318.5	312.5	304.8	295.2	285.7	276.2	266.7	258.9
62.5°	311.7	305.5	299.3	293.1	286.9	279.0	269.1	259.4	249.6	239.9	232.7
65°	273.4	267.0	260.5	254.2	247.7	239.8	230.2	220.8	211.2	201.6	195.3
67.5°	233.6	227.4	221.3	215.2	209.1	201.6	192.7	183.8	175.0	166.2	160.7
70°	208.4	202.1	195.9	189.6	183.4	176.0	167.5	159.0	150.5	142.1	137.2
72.5°	181.6	175.9	170.2	164.6	158.9	152.1	144.1	136.1	128.0	120.0	115.9
75°	145.4	139.9	134.4	128.9	123.4	117.1	110.1	103.1	96.1	89.1	85.7
77.5°	108.7	104.0	99.4	94.6	90.0	84.8	79.1	73.5	67.8	62.2	60.2
80°	85.1	80.8	76.5	72.2	67.8	63.5	59.0	54.5	50.0	45.5	45.1
82.5°	64.7	60.8	56.8	52.9	48.9	45.6	43.0	40.5	38.0	35.4	35.0
85°	36.2	33.2	30.2	27.2	24.3	22.6	22.1	21.7	21.2	20.8	20.5
87.5°	12.8	12.3	11.8	11.3	10.8	10.6	10.8	10.9	11.2	11.4	11.5
90°	2.6	4.7	6.9	9.0	11.1	13.0	14.6	16.1	17.7	19.2	20.3
92.5°	11.0	11.1	11.2	11.4	11.5	12.3	13.9	15.4	17.0	18.5	19.6
95°	48.0	41.4	34.8	28.2	21.6	18.4	18.6	18.8	19.0	19.2	20.3
97.5°	101.9	106.0	110.1	114.3	118.3	109.6	87.9	66.3	44.7	23.0	23.2
100°	143.1	146.5	150.1	153.5	157.0	145.4	118.6	91.9	65.2	38.4	35.1
102.5°	189.2	191.7	194.2	196.8	199.3	198.9	195.4	191.9	188.4	184.9	149.4
105°	262.6	263.7	264.9	266.0	267.3	268.3	269.2	270.3	271.2	272.2	273.9
107.5°	330.8	331.4	331.9	332.5	333.1	334.1	335.4	336.7	338.0	339.3	340.2
110°	376.9	377.5	378.0	378.6	379.2	380.0	381.3	382.4	383.6	384.7	385.1



TEST NUMBER: P333045-935

CATALOG NUMBER: S124RDIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.5	422.6	423.6	424.6	425.7	426.5	427.1	427.6	428.1	428.7	428.6
115°	490.3	490.9	491.5	492.0	492.6	492.8	492.6	492.4	492.2	492.0	492.4
117.5°	552.2	552.9	553.7	554.5	555.3	555.9	556.3	556.7	557.2	557.6	557.5
120°	594.1	594.9	595.6	596.4	597.2	597.4	597.3	597.1	596.8	596.7	597.1
122.5°	633.2	633.6	634.0	634.6	635.0	635.4	635.7	635.9	636.2	636.5	636.7
125°	689.1	689.9	690.7	691.5	692.2	692.4	692.1	691.6	691.3	690.9	691.5
127.5°	742.2	742.4	742.6	742.8	743.0	743.5	744.4	745.3	746.1	747.1	747.0
130°	776.4	776.6	776.8	777.0	777.1	777.6	778.2	778.7	779.3	779.9	780.1
132.5°	807.8	808.1	808.5	808.8	809.2	809.8	810.5	811.2	811.9	812.7	812.9
135°	854.9	854.7	854.5	854.3	854.1	854.5	855.2	856.0	856.8	857.6	857.9
137.5°	896.6	896.6	896.7	896.8	896.9	897.3	898.2	899.1	899.9	900.8	901.2
140°	923.9	924.2	924.6	925.0	925.4	925.7	926.2	926.5	927.0	927.3	927.9
142.5°	948.2	948.9	949.6	950.4	951.1	951.5	951.7	951.9	952.2	952.4	952.9
145°	985.8	986.4	986.9	987.5	988.1	988.3	988.3	988.3	988.3	988.3	988.6
147.5°	1015.5	1016.7	1017.8	1018.8	1019.9	1020.4	1020.2	1020.0	1019.8	1019.6	1019.8
150°	1037.2	1038.0	1038.8	1039.6	1040.3	1040.6	1040.4	1040.3	1040.0	1039.8	1039.8
152.5°	1055.3	1056.0	1056.6	1057.2	1057.8	1058.0	1057.7	1057.3	1057.0	1056.6	1056.9
155°	1080.8	1081.1	1081.2	1081.4	1081.6	1081.4	1080.8	1080.3	1079.7	1079.1	1079.9
157.5°	1102.3	1102.2	1102.1	1101.9	1101.8	1101.5	1100.8	1100.1	1099.5	1098.8	1099.8
160°	1114.8	1114.3	1113.7	1113.1	1112.5	1112.2	1112.0	1111.7	1111.6	1111.4	1112.5
162.5°	1126.0	1125.3	1124.6	1123.8	1123.1	1122.6	1122.4	1122.2	1122.1	1121.8	1123.0
165°	1140.1	1139.2	1138.2	1137.2	1136.3	1135.8	1135.8	1135.8	1135.8	1135.8	1137.4
167.5°	1151.3	1150.3	1149.3	1148.3	1147.3	1146.8	1146.6	1146.5	1146.4	1146.2	1148.0
170°	1157.6	1156.4	1155.3	1154.1	1153.0	1152.4	1152.6	1152.9	1153.1	1153.2	1154.8
172.5°	1161.7	1160.6	1159.4	1158.3	1157.1	1156.7	1156.8	1157.0	1157.3	1157.4	1159.0
175°	1166.3	1165.2	1164.0	1162.9	1161.7	1161.2	1161.4	1161.6	1161.7	1162.0	1163.7
177.5°	1168.4	1167.3	1166.2	1165.2	1164.1	1163.7	1164.0	1164.3	1164.6	1164.9	1166.1
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3



TEST NUMBER: P333045-935

CATALOG NUMBER: S124RDIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	871.8	873.1	874.3	874.9	874.9	874.7	874.6	874.5
5°	865.9	867.5	868.9	869.5	869.2	868.9	868.6	868.3
7.5°	854.4	855.3	856.4	856.5	856.1	855.6	855.1	854.6
10°	844.0	844.6	845.2	845.2	844.6	844.0	843.4	842.8
12.5°	831.2	831.6	832.0	831.7	830.9	830.1	829.2	828.4
15°	808.7	808.5	808.1	807.5	806.4	805.4	804.3	803.3
17.5°	781.7	780.8	780.0	778.8	777.2	775.7	774.0	772.5
20°	762.8	761.6	760.3	758.8	756.9	754.9	753.0	751.1
22.5°	741.8	739.9	738.1	736.5	734.9	733.3	731.8	730.1
25°	707.8	705.2	702.7	700.8	699.2	697.8	696.3	694.7
27.5°	673.2	670.1	667.0	664.3	662.2	660.0	658.0	655.8
30°	648.5	644.7	641.0	638.0	635.6	633.2	630.9	628.4
32.5°	623.2	618.9	614.5	611.2	609.0	606.7	604.4	602.2
35°	585.5	580.4	575.4	571.5	568.9	566.1	563.4	560.8
37.5°	545.0	539.4	533.7	529.6	526.8	524.2	521.5	518.8
40°	518.1	511.9	505.6	501.2	498.4	495.8	493.1	490.4
42.5°	491.6	485.3	478.9	474.3	471.5	468.7	465.9	463.1
45°	451.1	443.8	436.4	431.4	428.8	426.1	423.4	420.8
47.5°	410.2	402.6	395.0	389.8	386.8	383.9	381.0	378.0
50°	383.1	375.7	368.2	363.1	360.2	357.4	354.6	351.7
52.5°	356.0	348.4	341.0	335.7	332.7	329.8	326.8	323.9
55°	316.2	308.4	300.7	295.4	292.6	289.7	286.9	284.0
57.5°	277.2	269.3	261.5	256.5	254.3	252.2	250.0	247.9
60°	251.2	243.4	235.7	230.7	228.3	225.8	223.5	221.1
62.5°	225.6	218.4	211.3	206.7	204.8	202.9	201.0	199.1
65°	188.9	182.4	176.1	171.9	170.2	168.4	166.6	164.8
67.5°	155.2	149.6	144.1	140.4	138.4	136.5	134.5	132.5
70°	132.2	127.3	122.3	119.2	117.7	116.2	114.7	113.2
72.5°	111.7	107.5	103.2	100.5	99.1	97.7	96.3	95.0
75°	82.2	78.9	75.4	73.3	72.3	71.5	70.6	69.7
77.5°	58.2	56.2	54.2	53.0	52.8	52.5	52.3	52.0
80°	44.7	44.3	43.7	43.5	43.3	43.1	43.0	42.9
82.5°	34.7	34.4	34.1	33.8	33.7	33.5	33.4	33.2
85°	20.1	19.9	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	11.5	11.7	11.8	12.0	12.1	12.3	12.6	12.7
90°	21.5	22.6	23.8	24.6	25.0	25.4	25.7	26.2
92.5°	20.8	22.0	23.2	23.8	23.8	23.9	24.0	24.1
95°	21.5	22.6	23.8	24.5	24.7	24.9	25.1	25.3
97.5°	23.2	23.4	23.5	23.7	23.8	24.0	24.2	24.5
100°	31.8	28.5	25.2	23.7	23.8	24.0	24.2	24.5
102.5°	113.8	78.3	42.7	25.0	25.0	25.1	25.1	25.1
105°	275.7	277.4	279.1	276.6	269.6	262.6	255.6	248.7
107.5°	341.0	341.9	342.8	343.5	344.3	345.0	345.8	346.5
110°	385.5	385.9	386.2	386.8	387.4	387.9	388.5	389.1



TEST NUMBER: P333045-935

CATALOG NUMBER: S124RDIW-S575D1050U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.5	428.4	428.3	428.7	429.5	430.2	430.9	431.6
115°	492.8	493.2	493.5	493.8	493.8	493.8	493.8	493.8
117.5°	557.4	557.4	557.3	557.2	557.2	557.1	557.0	556.9
120°	597.4	597.9	598.2	598.2	597.9	597.4	597.1	596.7
122.5°	637.0	637.1	637.4	637.3	637.0	636.5	636.2	635.8
125°	692.1	692.7	693.2	693.6	693.8	694.0	694.2	694.4
127.5°	746.8	746.7	746.6	746.5	746.3	746.1	746.0	745.9
130°	780.2	780.5	780.7	780.8	780.8	780.8	780.8	780.8
132.5°	813.0	813.3	813.5	813.5	813.3	813.1	813.0	812.9
135°	858.3	858.7	859.1	859.5	859.9	860.2	860.7	861.0
137.5°	901.6	902.1	902.5	902.7	902.5	902.4	902.3	902.2
140°	928.5	929.0	929.6	930.1	930.2	930.4	930.6	930.8
142.5°	953.3	953.7	954.2	954.3	954.4	954.4	954.5	954.5
145°	988.8	988.9	989.1	989.5	989.8	990.2	990.6	991.0
147.5°	1019.9	1020.0	1020.2	1020.4	1020.6	1020.8	1021.0	1021.1
150°	1039.8	1039.8	1039.8	1039.9	1040.1	1040.3	1040.5	1040.7
152.5°	1057.2	1057.5	1057.8	1057.9	1057.8	1057.7	1057.6	1057.5
155°	1080.6	1081.4	1082.2	1082.3	1081.7	1081.2	1080.6	1080.0
157.5°	1100.8	1101.8	1102.9	1102.9	1101.8	1100.8	1099.8	1098.8
160°	1113.7	1114.8	1116.0	1116.0	1114.8	1113.7	1112.5	1111.4
162.5°	1124.1	1125.3	1126.4	1126.4	1125.1	1123.8	1122.5	1121.1
165°	1138.9	1140.5	1142.0	1141.9	1140.1	1138.4	1136.7	1134.9
167.5°	1149.7	1151.4	1153.1	1153.0	1151.1	1149.1	1147.2	1145.2
170°	1156.3	1157.9	1159.4	1159.3	1157.3	1155.4	1153.4	1151.5
172.5°	1160.5	1162.1	1163.6	1163.4	1161.2	1159.2	1157.1	1154.9
175°	1165.4	1167.2	1169.0	1168.6	1166.3	1164.0	1161.7	1159.3
177.5°	1167.4	1168.6	1169.9	1169.6	1167.7	1165.9	1164.0	1162.2
180°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3

(END OF REPORT)