

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332821-930

Luminaire Tested: **S124DIW-S1020D1050U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332821-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1020D1050U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7029.6 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332821-930

CATALOG NUMBER: S124DIW-S1020D1050U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332821-930

CATALOG NUMBER: S124DIW-S1020D1050U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	16	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11357	11357	11357
5°	11391	11255	11336
10°	11320	11163	11218
15°	11183	11004	11032
20°	11001	10808	10817
25°	10794	10583	10553
30°	10540	10318	10224
35°	10276	10042	9909
40°	10003	9729	9551
45°	9717	9421	9240
50°	9401	9146	8862
55°	9060	8790	8504
60°	8719	8391	8136
65°	8334	8010	7687
70°	7903	7504	7211
75°	7243	6890	6716
80°	6448	6183	6025
85°	5641	5428	5326



TEST NUMBER: P332821-930

CATALOG NUMBER: S124DIW-S1020D1050U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.5	1.9
10°-20°	373.3	5.3
20°-30°	549.4	7.8
30°-40°	638.7	9.1
40°-50°	638.7	9.1
50°-60°	558.7	7.9
60°-70°	414.9	5.9
70°-80°	235.7	3.4
80°-90°	71.2	1.0
90°-100°	37.8	0.5
100°-110°	240.8	3.4
110°-120°	460.7	6.6
120°-130°	584.9	8.3
130°-140°	625.8	8.9
140°-150°	585.2	8.3
150°-160°	471.9	6.7
160°-170°	304.4	4.3
170°-180°	104.9	1.5
0°-30°	1055.2	15.0
0°-40°	1693.9	24.1
0°-60°	2891.3	41.1
0°-90°	3613.2	51.4
90°-120°	739.3	10.5
90°-150°	2535.2	36.1
90°-180°	3416.0	48.6
0°-180°	7029.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1406	1401	1389	1400	1399	133
15°	1338	1333	1317	1323	1320	377
25°	1212	1204	1188	1189	1185	557
35°	1043	1034	1019	1011	1006	652
45°	851	843	825	813	809	656
55°	644	640	624	611	604	576
65°	436	430	419	408	402	432
75°	232	227	221	217	215	247
85°	61	61	59	59	58	67
90°	2	11	18	23	25	5
95°	45	19	18	23	24	58
105°	249	254	258	263	236	260
115°	464	466	466	467	468	457
125°	653	656	654	657	658	582
135°	810	809	812	814	815	623
145°	933	936	936	937	938	583
155°	1023	1024	1022	1025	1023	472
165°	1080	1076	1076	1081	1075	305
175°	1104	1100	1100	1107	1098	105
180°	1104	1104	1104	1104	1104	



TEST NUMBER: P332821-930

CATALOG NUMBER: S124DIW-S1020D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1410.4	1409.8	1409.2	1408.6	1408.0	1406.6	1404.4	1402.2	1400.0	1397.7	1399.8
5°	1405.7	1404.7	1403.7	1402.6	1401.7	1399.8	1397.0	1394.2	1391.6	1388.8	1391.6
7.5°	1392.6	1391.6	1390.6	1389.6	1388.6	1386.6	1383.5	1380.5	1377.4	1374.4	1376.6
10°	1380.9	1379.9	1378.8	1377.9	1376.9	1374.8	1371.5	1368.2	1365.0	1361.7	1363.7
12.5°	1365.5	1364.6	1363.5	1362.5	1361.5	1359.3	1355.8	1352.4	1348.9	1345.5	1347.7
15°	1338.1	1337.0	1336.0	1335.1	1334.0	1331.6	1327.9	1324.1	1320.4	1316.6	1318.1
17.5°	1304.9	1303.7	1302.4	1301.1	1299.9	1297.5	1293.9	1290.4	1286.8	1283.3	1284.2
20°	1280.5	1279.3	1278.1	1276.8	1275.5	1273.0	1269.3	1265.5	1261.8	1258.0	1258.7
22.5°	1254.4	1252.7	1251.1	1249.4	1247.8	1245.0	1241.3	1237.5	1233.8	1230.0	1231.4
25°	1211.8	1210.1	1208.3	1206.5	1204.8	1202.2	1198.7	1195.1	1191.6	1188.1	1188.4
27.5°	1163.1	1161.3	1159.4	1157.6	1155.8	1153.3	1150.1	1146.8	1143.5	1140.3	1139.7
30°	1130.7	1128.6	1126.6	1124.6	1122.6	1120.0	1116.7	1113.5	1110.2	1106.9	1106.0
32.5°	1096.3	1094.5	1092.7	1091.0	1089.2	1086.5	1083.0	1079.6	1076.1	1072.7	1071.5
35°	1042.7	1041.0	1039.2	1037.5	1035.7	1033.1	1029.6	1026.1	1022.5	1019.0	1017.2
37.5°	986.1	984.5	982.9	981.3	979.7	977.1	973.2	969.5	965.7	962.0	960.1
40°	949.2	947.1	945.1	943.1	941.1	938.2	934.5	930.7	927.0	923.2	920.7
42.5°	909.5	908.2	907.0	905.9	904.7	902.0	897.8	893.6	889.5	885.3	882.4
45°	851.1	849.3	847.6	845.8	844.1	841.1	837.1	833.2	829.2	825.2	822.4
47.5°	789.9	788.8	787.6	786.4	785.1	782.7	779.0	775.3	771.6	767.8	764.8
50°	748.5	747.5	746.5	745.5	744.4	742.2	738.7	735.2	731.7	728.2	724.7
52.5°	707.9	706.7	705.5	704.3	703.1	700.7	696.9	693.2	689.5	685.8	682.7
55°	643.7	642.9	642.1	641.4	640.7	638.5	635.0	631.5	628.0	624.5	621.5
57.5°	582.4	581.5	580.7	579.8	578.9	576.7	573.3	569.9	566.4	563.0	560.1
60°	540.0	538.7	537.4	536.2	534.9	532.7	529.5	526.2	522.9	519.7	517.4
62.5°	498.5	497.4	496.4	495.3	494.2	492.0	488.5	485.1	481.6	478.2	476.1
65°	436.3	435.0	433.7	432.5	431.2	429.3	426.8	424.4	421.8	419.3	416.9
67.5°	373.6	372.4	371.3	370.1	368.9	367.2	364.8	362.4	360.0	357.6	355.1
70°	334.8	333.0	331.3	329.5	327.8	325.9	323.9	321.9	319.9	317.9	315.8
72.5°	293.3	291.6	289.8	288.0	286.3	284.6	283.0	281.4	279.8	278.2	276.6
75°	232.2	231.0	229.7	228.4	227.2	225.9	224.7	223.5	222.2	220.9	220.0
77.5°	173.8	173.3	172.7	172.2	171.6	170.8	169.7	168.6	167.5	166.4	166.1
80°	138.7	137.9	137.1	136.4	135.7	135.0	134.5	134.0	133.5	133.0	132.5
82.5°	104.4	104.0	103.7	103.3	103.0	102.7	102.6	102.6	102.5	102.3	102.1
85°	60.9	60.9	60.9	60.9	60.9	60.7	60.1	59.6	59.1	58.6	58.6
87.5°	24.0	24.1	24.4	24.5	24.8	24.9	25.0	25.1	25.2	25.3	25.5
90°	2.4	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2
92.5°	10.4	10.5	10.6	10.8	10.8	11.7	13.1	14.6	16.1	17.5	18.6
95°	45.4	39.2	32.9	26.7	20.5	17.4	17.6	17.8	18.0	18.2	19.2
97.5°	96.4	100.4	104.3	108.2	112.0	103.8	83.2	62.8	42.3	21.8	21.9
100°	135.5	138.8	142.1	145.4	148.7	137.7	112.3	87.0	61.7	36.4	33.3
102.5°	179.1	181.5	183.9	186.4	188.7	188.3	185.1	181.7	178.4	175.1	141.5
105°	248.7	249.7	250.9	251.9	253.1	254.0	254.9	255.9	256.8	257.7	259.3
107.5°	313.2	313.8	314.3	314.9	315.4	316.3	317.6	318.9	320.1	321.3	322.1
110°	356.9	357.4	357.9	358.5	359.1	359.9	361.0	362.1	363.2	364.3	364.7



TEST NUMBER: P332821-930

CATALOG NUMBER: S124DIW-S1020D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	399.2	400.1	401.1	402.1	403.1	403.9	404.4	404.9	405.4	405.9	405.9
115°	464.2	464.8	465.4	465.9	466.4	466.6	466.4	466.3	466.1	465.9	466.3
117.5°	522.9	523.6	524.3	525.1	525.8	526.4	526.8	527.2	527.6	528.0	527.9
120°	562.6	563.3	564.0	564.8	565.5	565.7	565.6	565.4	565.2	565.0	565.4
122.5°	599.6	600.0	600.4	600.9	601.3	601.7	601.9	602.2	602.4	602.7	602.9
125°	652.6	653.3	654.0	654.8	655.5	655.7	655.3	654.9	654.6	654.2	654.8
127.5°	702.8	703.0	703.2	703.4	703.5	704.0	704.9	705.7	706.5	707.4	707.4
130°	735.2	735.4	735.6	735.7	735.9	736.3	736.9	737.4	737.9	738.5	738.7
132.5°	764.9	765.2	765.6	765.9	766.2	766.8	767.4	768.2	768.8	769.6	769.7
135°	809.5	809.3	809.2	808.9	808.8	809.1	809.8	810.6	811.3	812.0	812.4
137.5°	849.0	849.1	849.1	849.2	849.3	849.7	850.5	851.3	852.2	853.0	853.4
140°	874.8	875.1	875.5	875.9	876.3	876.6	877.0	877.3	877.8	878.1	878.6
142.5°	897.9	898.5	899.2	899.9	900.6	901.0	901.2	901.4	901.6	901.9	902.3
145°	933.4	934.0	934.5	935.1	935.6	935.9	935.9	935.9	935.9	935.9	936.1
147.5°	961.6	962.7	963.8	964.7	965.8	966.2	966.0	965.9	965.6	965.5	965.6
150°	982.2	982.9	983.7	984.4	985.1	985.4	985.2	985.0	984.8	984.6	984.6
152.5°	999.3	1000.0	1000.5	1001.1	1001.7	1001.8	1001.5	1001.2	1000.9	1000.5	1000.8
155°	1023.4	1023.7	1023.9	1024.0	1024.2	1024.0	1023.4	1023.0	1022.4	1021.8	1022.5
157.5°	1043.8	1043.7	1043.6	1043.4	1043.3	1043.0	1042.4	1041.7	1041.1	1040.5	1041.5
160°	1055.6	1055.2	1054.6	1054.0	1053.4	1053.1	1053.0	1052.7	1052.6	1052.4	1053.4
162.5°	1066.2	1065.6	1064.9	1064.1	1063.5	1063.0	1062.8	1062.7	1062.5	1062.3	1063.4
165°	1079.6	1078.7	1077.8	1076.8	1076.0	1075.5	1075.5	1075.5	1075.5	1075.5	1077.0
167.5°	1090.2	1089.2	1088.3	1087.4	1086.4	1085.9	1085.7	1085.7	1085.6	1085.4	1087.0
170°	1096.2	1095.0	1094.0	1092.8	1091.8	1091.3	1091.4	1091.7	1091.8	1092.0	1093.5
172.5°	1100.1	1099.0	1097.9	1096.8	1095.7	1095.3	1095.4	1095.6	1095.8	1096.0	1097.5
175°	1104.4	1103.3	1102.2	1101.1	1100.0	1099.6	1099.8	1099.9	1100.1	1100.3	1102.0
177.5°	1106.4	1105.4	1104.3	1103.3	1102.3	1102.0	1102.2	1102.5	1102.8	1103.1	1104.2
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P332821-930

CATALOG NUMBER: S124DIW-S1020D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1401.7	1403.8	1405.8	1406.7	1406.5	1406.3	1406.1	1405.9
5°	1394.2	1397.0	1399.8	1400.9	1400.4	1399.9	1399.4	1398.9
7.5°	1378.8	1381.0	1383.2	1384.1	1383.8	1383.5	1383.2	1382.9
10°	1365.7	1367.7	1369.7	1370.4	1369.9	1369.5	1369.0	1368.5
12.5°	1349.9	1352.1	1354.3	1355.0	1354.4	1353.6	1352.9	1352.3
15°	1319.6	1321.1	1322.7	1323.0	1322.3	1321.5	1320.8	1320.0
17.5°	1285.2	1286.1	1287.0	1287.3	1286.8	1286.3	1285.8	1285.2
20°	1259.5	1260.3	1261.0	1261.1	1260.6	1260.1	1259.6	1259.1
22.5°	1232.7	1234.1	1235.4	1235.7	1234.8	1233.9	1233.0	1232.1
25°	1188.6	1188.9	1189.1	1188.7	1187.7	1186.7	1185.7	1184.7
27.5°	1139.1	1138.5	1137.9	1137.0	1135.7	1134.5	1133.2	1132.0
30°	1105.0	1103.9	1102.9	1101.8	1100.6	1099.3	1098.0	1096.8
32.5°	1070.2	1069.1	1067.9	1066.7	1065.4	1064.1	1062.9	1061.6
35°	1015.5	1013.7	1012.0	1010.5	1009.3	1008.0	1006.7	1005.5
37.5°	958.1	956.3	954.4	952.6	951.0	949.3	947.6	946.0
40°	918.2	915.7	913.2	911.3	910.0	908.8	907.6	906.3
42.5°	879.5	876.6	873.7	871.8	871.0	870.1	869.3	868.5
45°	819.6	816.8	814.1	812.4	811.6	810.9	810.1	809.3
47.5°	761.7	758.6	755.5	752.9	751.1	749.1	747.2	745.3
50°	721.2	717.7	714.2	711.7	710.1	708.7	707.2	705.6
52.5°	679.6	676.5	673.4	670.9	669.0	667.1	665.2	663.2
55°	618.5	615.5	612.5	610.3	608.7	607.2	605.7	604.2
57.5°	557.3	554.4	551.5	549.3	547.9	546.5	545.0	543.6
60°	515.2	512.9	510.6	508.9	507.6	506.4	505.2	503.9
62.5°	474.1	472.0	469.9	468.3	467.1	465.8	464.6	463.3
65°	414.3	411.8	409.3	407.4	406.2	405.0	403.7	402.4
67.5°	352.8	350.3	348.0	346.6	346.2	345.8	345.5	345.2
70°	313.9	311.9	309.9	308.5	307.8	307.0	306.2	305.5
72.5°	275.0	273.4	271.8	270.6	269.9	269.1	268.4	267.6
75°	218.9	217.9	217.0	216.3	216.1	215.8	215.6	215.3
77.5°	165.8	165.5	165.2	164.7	164.0	163.4	162.7	162.1
80°	132.0	131.5	131.0	130.6	130.4	130.1	129.9	129.6
82.5°	101.7	101.4	101.2	100.9	100.6	100.4	100.1	99.9
85°	58.6	58.6	58.6	58.5	58.2	58.0	57.7	57.5
87.5°	25.7	25.9	26.2	26.3	26.4	26.4	26.5	26.6
90°	20.4	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	19.7	20.8	21.9	22.5	22.6	22.7	22.7	22.8
95°	20.4	21.4	22.6	23.2	23.4	23.6	23.8	24.0
97.5°	22.0	22.2	22.3	22.4	22.6	22.7	22.9	23.2
100°	30.1	27.0	23.9	22.4	22.6	22.7	22.9	23.2
102.5°	107.8	74.1	40.4	23.6	23.6	23.7	23.7	23.8
105°	261.1	262.7	264.3	261.9	255.3	248.7	242.1	235.5
107.5°	322.9	323.8	324.6	325.3	326.0	326.7	327.4	328.1
110°	365.0	365.4	365.7	366.2	366.8	367.3	367.9	368.4





TEST NUMBER: P332821-930

CATALOG NUMBER: S124DIW-S1020D1050U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	405.8	405.7	405.6	405.9	406.7	407.3	408.1	408.7
115°	466.6	467.0	467.3	467.6	467.6	467.6	467.6	467.6
117.5°	527.8	527.8	527.7	527.7	527.6	527.5	527.4	527.3
120°	565.7	566.1	566.5	566.5	566.1	565.7	565.4	565.0
122.5°	603.2	603.3	603.6	603.5	603.2	602.8	602.4	602.0
125°	655.3	655.9	656.4	656.8	657.0	657.1	657.4	657.5
127.5°	707.2	707.1	706.9	706.9	706.7	706.5	706.4	706.3
130°	738.8	739.1	739.2	739.3	739.3	739.3	739.3	739.3
132.5°	769.9	770.1	770.3	770.3	770.1	770.0	769.9	769.7
135°	812.8	813.1	813.5	813.8	814.2	814.6	815.0	815.3
137.5°	853.8	854.2	854.6	854.8	854.6	854.5	854.4	854.3
140°	879.2	879.7	880.3	880.7	880.8	881.0	881.2	881.4
142.5°	902.7	903.1	903.5	903.7	903.8	903.8	903.8	903.8
145°	936.3	936.5	936.6	936.9	937.3	937.7	938.0	938.4
147.5°	965.8	965.9	966.0	966.2	966.5	966.6	966.8	966.9
150°	984.6	984.6	984.6	984.7	984.9	985.1	985.3	985.5
152.5°	1001.1	1001.4	1001.7	1001.8	1001.7	1001.5	1001.4	1001.4
155°	1023.3	1024.0	1024.7	1024.8	1024.3	1023.8	1023.2	1022.6
157.5°	1042.4	1043.3	1044.3	1044.3	1043.3	1042.4	1041.5	1040.5
160°	1054.6	1055.6	1056.8	1056.8	1055.6	1054.6	1053.4	1052.4
162.5°	1064.5	1065.6	1066.7	1066.7	1065.4	1064.1	1062.9	1061.6
165°	1078.5	1079.9	1081.4	1081.2	1079.6	1078.0	1076.4	1074.6
167.5°	1088.7	1090.3	1091.8	1091.8	1090.0	1088.1	1086.3	1084.4
170°	1094.9	1096.4	1097.9	1097.7	1095.8	1094.1	1092.2	1090.4
172.5°	1098.9	1100.4	1101.9	1101.6	1099.6	1097.6	1095.7	1093.6
175°	1103.6	1105.2	1106.9	1106.6	1104.4	1102.2	1100.0	1097.8
177.5°	1105.5	1106.6	1107.8	1107.5	1105.7	1104.0	1102.2	1100.5
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4

(END OF REPORT)