

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333042-935

Luminaire Tested: **S124RDIW-S575D770U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333042-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D770U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4316.5 lumens  
Efficiency: N/A  
Efficacy: 114.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333042-935

CATALOG NUMBER: S124RDIW-S575D770U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333042-935

CATALOG NUMBER: S124RDIW-S575D770U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82		67	67	67		53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	67		59	58	56		47	46	45	40
2	89	82	76	71	81	75	70	66	63	60	56		52	50	47		42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48		46	43	40		37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41		41	38	35		34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35		37	33	30		30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31		34	30	26		28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27		31	27	23		25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24		28	24	21		23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22		26	22	19		21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20		24	20	17		20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7064	7064	7064
5°	7080	6994	7037
10°	7035	6909	6909
15°	6955	6764	6714
20°	6844	6574	6453
25°	6702	6350	6188
30°	6564	6114	5858
35°	6412	5870	5527
40°	6227	5592	5168
45°	6058	5316	4804
50°	5865	4999	4417
55°	5658	4669	3997
60°	5430	4306	3570
65°	5223	3851	3148
70°	4919	3354	2672
75°	4535	2779	2174
80°	3956	2115	1994
85°	3353	1927	1806



TEST NUMBER: P333042-935

CATALOG NUMBER: S124RDIW-S575D770U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.2	1.9
10°-20°	229.2	5.3
20°-30°	331.0	7.7
30°-40°	375.2	8.7
40°-50°	362.3	8.4
50°-60°	301.3	7.0
60°-70°	208.0	4.8
70°-80°	105.4	2.4
80°-90°	29.5	0.7
90°-100°	54.5	1.3
100°-110°	161.4	3.7
110°-120°	274.0	6.3
120°-130°	361.3	8.4
130°-140°	405.8	9.4
140°-150°	398.7	9.2
150°-160°	335.4	7.8
160°-170°	223.1	5.2
170°-180°	78.1	1.8
0°-30°	642.4	14.9
0°-40°	1017.6	23.6
0°-60°	1681.1	38.9
0°-90°	2024.1	46.9
90°-120°	489.9	11.4
90°-150°	1655.8	38.4
90°-180°	2292.0	53.1
0°-180°	4316.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	874	871	863	869	868	83
15°	832	825	809	808	803	234
25°	752	740	713	702	695	347
35°	651	628	596	573	561	406
45°	531	505	466	434	421	409
55°	402	374	332	298	284	359
65°	273	244	202	174	165	270
75°	145	120	89	74	70	154
85°	36	23	21	20	20	41
90°	2	9	14	18	19	4
95°	38	44	49	50	50	43
105°	149	150	152	154	156	158
115°	279	278	277	277	276	275
125°	406	406	405	404	403	362
135°	523	527	527	526	524	405
145°	636	638	639	638	636	398
155°	728	728	728	730	728	335
165°	793	791	790	793	791	223
175°	825	822	821	825	821	78
180°	826	826	826	826	826	



TEST NUMBER: P333042-935

CATALOG NUMBER: S124RDIW-S575D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	877.2	876.7	876.2	875.7	875.3	874.3	873.1	871.8	870.4	869.1	870.4
5°	873.7	873.1	872.5	871.8	871.3	870.1	868.3	866.5	864.7	863.0	864.4
7.5°	865.7	865.1	864.5	863.9	863.2	861.8	859.5	857.1	854.8	852.5	853.4
10°	858.2	857.6	856.8	856.0	855.3	853.6	850.9	848.2	845.5	842.8	843.4
12.5°	848.6	847.7	846.9	846.0	845.2	843.2	840.0	836.8	833.7	830.5	830.9
15°	832.2	830.8	829.5	828.1	826.7	824.2	820.5	816.8	813.0	809.3	809.1
17.5°	812.2	810.2	808.3	806.3	804.4	801.2	796.8	792.3	787.8	783.3	782.6
20°	796.6	794.7	792.7	790.8	788.8	785.4	780.3	775.2	770.2	765.2	764.0
22.5°	779.5	777.3	775.2	772.9	770.8	767.0	761.6	756.1	750.7	745.3	743.5
25°	752.4	749.8	747.0	744.3	741.7	737.3	731.2	725.0	718.9	712.9	710.3
27.5°	724.0	720.7	717.3	713.9	710.5	705.6	699.0	692.6	686.0	679.5	676.4
30°	704.1	700.4	696.7	693.0	689.3	683.9	676.9	669.9	662.9	655.9	652.2
32.5°	683.3	679.1	674.9	670.6	666.5	660.7	653.5	646.3	639.0	631.8	627.5
35°	650.6	645.8	641.0	636.3	631.5	625.4	617.9	610.5	603.0	595.6	590.6
37.5°	615.6	610.7	605.8	600.9	595.9	589.4	581.1	572.8	564.6	556.4	550.7
40°	590.9	586.0	581.1	576.2	571.3	564.6	556.1	547.6	539.2	530.6	524.3
42.5°	567.3	562.2	557.1	551.9	546.7	539.8	530.9	522.0	513.2	504.4	498.0
45°	530.6	525.1	519.6	514.1	508.6	501.4	492.4	483.5	474.6	465.6	458.3
47.5°	492.8	487.1	481.3	475.6	469.9	462.4	453.1	443.9	434.6	425.3	417.8
50°	467.0	461.2	455.4	449.5	443.8	436.1	426.5	417.1	407.5	398.0	390.5
52.5°	440.7	435.1	429.4	423.7	417.9	410.3	400.5	390.7	380.9	371.2	363.6
55°	402.0	396.1	390.1	384.1	378.2	370.3	360.7	351.0	341.3	331.7	323.9
57.5°	363.7	357.5	351.3	345.1	338.9	331.1	321.5	311.9	302.5	292.9	285.1
60°	336.3	330.4	324.4	318.5	312.5	304.8	295.2	285.7	276.2	266.7	258.9
62.5°	311.7	305.5	299.3	293.1	286.9	279.0	269.1	259.4	249.6	239.9	232.7
65°	273.4	267.0	260.5	254.2	247.7	239.8	230.2	220.8	211.2	201.6	195.3
67.5°	233.6	227.4	221.3	215.2	209.1	201.6	192.7	183.8	175.0	166.2	160.7
70°	208.4	202.1	195.9	189.6	183.4	176.0	167.5	159.0	150.5	142.1	137.2
72.5°	181.6	175.9	170.2	164.6	158.9	152.1	144.1	136.1	128.0	120.0	115.9
75°	145.4	139.9	134.4	128.9	123.4	117.1	110.1	103.1	96.1	89.1	85.7
77.5°	108.7	104.0	99.4	94.6	90.0	84.8	79.1	73.5	67.8	62.2	60.2
80°	85.1	80.8	76.5	72.2	67.8	63.5	59.0	54.5	50.0	45.5	45.1
82.5°	64.7	60.8	56.8	52.9	48.9	45.6	43.0	40.5	38.0	35.4	35.0
85°	36.2	33.2	30.2	27.2	24.3	22.6	22.1	21.7	21.2	20.8	20.5
87.5°	12.7	12.1	11.5	10.8	10.2	9.9	10.0	10.1	10.2	10.3	10.3
90°	1.9	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9
92.5°	13.7	15.5	17.2	19.0	20.8	22.1	22.9	23.7	24.5	25.3	25.8
95°	38.3	39.6	40.9	42.2	43.5	44.6	45.5	46.6	47.6	48.6	49.0
97.5°	67.0	68.0	69.1	70.0	71.0	72.2	73.4	74.5	75.7	76.8	77.3
100°	89.5	90.1	90.6	91.2	91.7	92.6	93.9	95.2	96.5	97.8	98.1
102.5°	113.0	113.2	113.4	113.7	113.9	114.6	115.7	116.9	118.0	119.2	119.7
105°	148.9	149.0	149.2	149.3	149.5	149.8	150.4	150.9	151.5	152.1	152.5
107.5°	186.6	186.8	186.9	187.1	187.3	187.4	187.5	187.6	187.7	187.8	188.1
110°	212.2	212.4	212.8	213.0	213.3	213.4	213.2	213.1	212.9	212.8	212.5



TEST NUMBER: P333042-935

CATALOG NUMBER: S124RDIW-S575D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	238.8	238.8	238.8	238.9	238.9	238.8	238.6	238.3	238.1	237.8	237.8
115°	278.6	278.6	278.6	278.6	278.6	278.4	278.2	277.9	277.6	277.3	277.2
117.5°	316.2	316.3	316.4	316.5	316.7	316.6	316.4	316.2	316.0	315.8	315.3
120°	341.2	341.8	342.3	342.9	343.5	343.5	343.2	342.8	342.3	341.9	341.1
122.5°	367.3	367.6	367.7	368.0	368.2	368.2	368.1	367.8	367.6	367.5	367.0
125°	405.8	405.8	405.8	405.8	405.8	405.7	405.5	405.4	405.3	405.1	404.8
127.5°	440.7	441.1	441.5	442.0	442.4	442.5	442.2	442.0	441.8	441.6	441.3
130°	465.2	465.6	466.1	466.5	466.9	467.1	467.1	467.1	467.1	467.1	466.8
132.5°	490.3	490.6	490.9	491.2	491.5	491.6	491.5	491.4	491.3	491.1	490.9
135°	523.4	524.2	525.0	525.9	526.8	527.2	527.2	527.2	527.2	527.2	526.9
137.5°	559.4	559.8	560.2	560.6	561.0	561.3	561.5	561.7	562.0	562.2	561.8
140°	583.4	583.7	584.0	584.3	584.5	584.7	584.7	584.7	584.7	584.7	584.5
142.5°	605.4	605.7	606.0	606.2	606.6	606.7	606.5	606.4	606.3	606.1	606.1
145°	635.8	636.4	637.0	637.6	638.1	638.4	638.6	638.8	638.9	639.0	638.9
147.5°	666.0	666.7	667.4	668.0	668.7	669.0	668.9	668.7	668.7	668.6	668.4
150°	684.4	684.9	685.5	686.1	686.6	687.0	687.0	687.0	687.0	687.0	687.0
152.5°	701.8	702.1	702.5	702.8	703.2	703.4	703.4	703.6	703.7	703.8	704.1
155°	728.5	728.5	728.5	728.5	728.5	728.4	728.2	728.1	728.0	727.9	728.4
157.5°	751.0	750.7	750.4	750.2	749.9	749.8	749.8	749.8	749.8	749.7	750.1
160°	764.3	764.1	764.0	763.9	763.7	763.5	763.4	763.3	763.1	763.0	763.4
162.5°	776.5	776.2	775.8	775.4	775.1	774.8	774.6	774.6	774.4	774.2	775.0
165°	793.1	792.6	792.2	791.8	791.3	791.0	790.7	790.4	790.1	789.8	790.7
167.5°	805.6	805.1	804.5	803.9	803.3	803.0	803.1	803.1	803.1	803.1	804.0
170°	812.9	812.1	811.4	810.7	810.0	809.7	809.9	810.0	810.1	810.3	811.1
172.5°	817.9	817.3	816.7	816.1	815.5	815.3	815.3	815.4	815.4	815.4	816.4
175°	825.0	824.2	823.5	822.9	822.2	821.7	821.6	821.4	821.3	821.1	822.2
177.5°	827.2	826.7	826.1	825.6	825.0	824.8	824.8	824.8	824.8	824.8	825.5
180°	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2



TEST NUMBER: P333042-935

CATALOG NUMBER: S124RDIW-S575D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	871.8	873.1	874.3	874.9	874.9	874.7	874.6	874.5
5°	865.9	867.5	868.9	869.5	869.2	868.9	868.6	868.3
7.5°	854.4	855.3	856.4	856.5	856.1	855.6	855.1	854.6
10°	844.0	844.6	845.2	845.2	844.6	844.0	843.4	842.8
12.5°	831.2	831.6	832.0	831.7	830.9	830.1	829.2	828.4
15°	808.7	808.5	808.1	807.5	806.4	805.4	804.3	803.3
17.5°	781.7	780.8	780.0	778.8	777.2	775.7	774.0	772.5
20°	762.8	761.6	760.3	758.8	756.9	754.9	753.0	751.1
22.5°	741.8	739.9	738.1	736.5	734.9	733.3	731.8	730.1
25°	707.8	705.2	702.7	700.8	699.2	697.8	696.3	694.7
27.5°	673.2	670.1	667.0	664.3	662.2	660.0	658.0	655.8
30°	648.5	644.7	641.0	638.0	635.6	633.2	630.9	628.4
32.5°	623.2	618.9	614.5	611.2	609.0	606.7	604.4	602.2
35°	585.5	580.4	575.4	571.5	568.9	566.1	563.4	560.8
37.5°	545.0	539.4	533.7	529.6	526.8	524.2	521.5	518.8
40°	518.1	511.9	505.6	501.2	498.4	495.8	493.1	490.4
42.5°	491.6	485.3	478.9	474.3	471.5	468.7	465.9	463.1
45°	451.1	443.8	436.4	431.4	428.8	426.1	423.4	420.8
47.5°	410.2	402.6	395.0	389.8	386.8	383.9	381.0	378.0
50°	383.1	375.7	368.2	363.1	360.2	357.4	354.6	351.7
52.5°	356.0	348.4	341.0	335.7	332.7	329.8	326.8	323.9
55°	316.2	308.4	300.7	295.4	292.6	289.7	286.9	284.0
57.5°	277.2	269.3	261.5	256.5	254.3	252.2	250.0	247.9
60°	251.2	243.4	235.7	230.7	228.3	225.8	223.5	221.1
62.5°	225.6	218.4	211.3	206.7	204.8	202.9	201.0	199.1
65°	188.9	182.4	176.1	171.9	170.2	168.4	166.6	164.8
67.5°	155.2	149.6	144.1	140.4	138.4	136.5	134.5	132.5
70°	132.2	127.3	122.3	119.2	117.7	116.2	114.7	113.2
72.5°	111.7	107.5	103.2	100.5	99.1	97.7	96.3	95.0
75°	82.2	78.9	75.4	73.3	72.3	71.5	70.6	69.7
77.5°	58.2	56.2	54.2	53.0	52.8	52.5	52.3	52.0
80°	44.7	44.3	43.7	43.5	43.3	43.1	43.0	42.9
82.5°	34.7	34.4	34.1	33.8	33.7	33.5	33.4	33.2
85°	20.1	19.9	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	10.4	10.5	10.5	10.7	10.8	11.0	11.2	11.4
90°	15.8	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	26.3	26.9	27.4	27.7	27.9	28.1	28.2	28.4
95°	49.4	49.9	50.3	50.5	50.5	50.5	50.5	50.5
97.5°	77.8	78.4	78.9	79.1	79.1	79.1	79.1	79.1
100°	98.3	98.6	98.9	99.0	99.0	99.0	99.0	99.0
102.5°	120.0	120.5	120.8	121.1	121.2	121.3	121.4	121.6
105°	152.9	153.3	153.8	154.2	154.6	155.1	155.5	155.9
107.5°	188.6	188.9	189.3	189.5	189.5	189.5	189.4	189.4
110°	212.2	212.0	211.6	211.7	212.2	212.6	213.0	213.4





TEST NUMBER: P333042-935

CATALOG NUMBER: S124RDIW-S575D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	237.7	237.6	237.6	237.6	237.7	237.8	237.9	238.0
115°	277.1	276.9	276.7	276.6	276.5	276.4	276.2	276.0
117.5°	314.9	314.4	313.8	313.5	313.2	312.9	312.6	312.4
120°	340.4	339.8	339.1	338.8	339.1	339.4	339.7	339.9
122.5°	366.4	366.0	365.5	365.0	364.5	363.9	363.5	363.0
125°	404.6	404.3	404.0	403.7	403.5	403.1	402.9	402.6
127.5°	441.0	440.7	440.4	440.1	440.0	439.7	439.5	439.3
130°	466.6	466.2	466.0	465.5	465.0	464.4	463.8	463.3
132.5°	490.6	490.3	490.0	489.7	489.6	489.3	489.0	488.9
135°	526.6	526.3	526.1	525.7	525.3	524.9	524.4	524.0
137.5°	561.5	561.1	560.8	560.6	560.7	560.8	560.9	560.9
140°	584.4	584.3	584.1	584.0	583.8	583.7	583.6	583.4
142.5°	606.1	606.1	606.1	606.1	606.0	606.0	606.0	605.9
145°	638.8	638.6	638.4	638.2	637.7	637.3	636.9	636.5
147.5°	668.3	668.2	668.0	668.0	667.8	667.7	667.5	667.4
150°	687.0	687.0	687.0	686.9	686.7	686.6	686.5	686.3
152.5°	704.5	704.8	705.2	705.2	704.8	704.5	704.0	703.7
155°	729.0	729.5	730.1	730.1	729.5	729.0	728.4	727.9
157.5°	750.5	751.0	751.4	751.4	750.9	750.4	749.9	749.4
160°	763.9	764.3	764.7	764.6	763.9	763.1	762.4	761.7
162.5°	775.8	776.5	777.3	777.3	776.6	775.9	775.2	774.5
165°	791.5	792.4	793.2	793.4	792.8	792.2	791.7	791.1
167.5°	804.9	805.6	806.5	806.5	805.6	804.8	803.9	803.0
170°	812.0	812.9	813.7	813.6	812.6	811.7	810.6	809.7
172.5°	817.3	818.3	819.2	819.2	818.2	817.3	816.2	815.3
175°	823.1	824.1	825.1	825.1	824.1	823.1	822.2	821.1
177.5°	826.3	827.1	827.9	827.9	826.9	826.0	825.1	824.2
180°	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2

(END OF REPORT)