

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332833-930

Luminaire Tested: **S124DIW-S1020D1560U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332833-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1560U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8699.7 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332833-930

CATALOG NUMBER: S124DIW-S1020D1560U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332833-930

CATALOG NUMBER: S124DIW-S1020D1560U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11357	11357	11357
5°	11391	11255	11336
10°	11320	11163	11218
15°	11183	11004	11032
20°	11001	10808	10817
25°	10794	10583	10553
30°	10540	10318	10224
35°	10276	10042	9909
40°	10003	9729	9551
45°	9717	9421	9240
50°	9401	9146	8862
55°	9060	8790	8504
60°	8719	8391	8136
65°	8334	8010	7687
70°	7903	7504	7211
75°	7243	6890	6716
80°	6448	6183	6025
85°	5641	5428	5326



TEST NUMBER: P332833-930

CATALOG NUMBER: S124DIW-S1020D1560U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	1.5
10°-20°	373.3	4.3
20°-30°	549.4	6.3
30°-40°	638.7	7.3
40°-50°	638.7	7.3
50°-60°	558.7	6.4
60°-70°	414.9	4.8
70°-80°	235.7	2.7
80°-90°	72.8	0.8
90°-100°	56.2	0.6
100°-110°	358.5	4.1
110°-120°	685.8	7.9
120°-130°	870.5	10.0
130°-140°	931.4	10.7
140°-150°	871.0	10.0
150°-160°	702.4	8.1
160°-170°	453.0	5.2
170°-180°	156.1	1.8
0°-30°	1055.2	12.1
0°-40°	1693.9	19.5
0°-60°	2891.3	33.2
0°-90°	3614.8	41.6
90°-120°	1100.5	12.6
90°-150°	3773.4	43.4
90°-180°	5085.0	58.5
0°-180°	8699.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1406	1401	1389	1400	1399	133
15°	1338	1333	1317	1323	1320	377
25°	1212	1204	1188	1189	1185	557
35°	1043	1034	1019	1011	1006	652
45°	851	843	825	813	809	656
55°	644	640	624	611	604	576
65°	436	430	419	408	402	432
75°	232	227	221	217	215	247
85°	61	61	59	59	58	67
90°	4	17	27	34	37	6
95°	68	28	27	34	36	87
105°	370	377	384	392	350	387
115°	691	694	693	696	696	680
125°	971	976	974	977	979	867
135°	1205	1204	1209	1211	1214	928
145°	1389	1393	1393	1394	1397	868
155°	1523	1524	1521	1525	1522	702
165°	1607	1601	1601	1610	1600	454
175°	1644	1637	1638	1647	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P332833-930

CATALOG NUMBER: S124DIW-S1020D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1410.4	1409.8	1409.2	1408.6	1408.0	1406.6	1404.4	1402.2	1400.0	1397.7	1399.8
5°	1405.7	1404.7	1403.7	1402.6	1401.7	1399.8	1397.0	1394.2	1391.6	1388.8	1391.6
7.5°	1392.6	1391.6	1390.6	1389.6	1388.6	1386.6	1383.5	1380.5	1377.4	1374.4	1376.6
10°	1380.9	1379.9	1378.8	1377.9	1376.9	1374.8	1371.5	1368.2	1365.0	1361.7	1363.7
12.5°	1365.5	1364.6	1363.5	1362.5	1361.5	1359.3	1355.8	1352.4	1348.9	1345.5	1347.7
15°	1338.1	1337.0	1336.0	1335.1	1334.0	1331.6	1327.9	1324.1	1320.4	1316.6	1318.1
17.5°	1304.9	1303.7	1302.4	1301.1	1299.9	1297.5	1293.9	1290.4	1286.8	1283.3	1284.2
20°	1280.5	1279.3	1278.1	1276.8	1275.5	1273.0	1269.3	1265.5	1261.8	1258.0	1258.7
22.5°	1254.4	1252.7	1251.1	1249.4	1247.8	1245.0	1241.3	1237.5	1233.8	1230.0	1231.4
25°	1211.8	1210.1	1208.3	1206.5	1204.8	1202.2	1198.7	1195.1	1191.6	1188.1	1188.4
27.5°	1163.1	1161.3	1159.4	1157.6	1155.8	1153.3	1150.1	1146.8	1143.5	1140.3	1139.7
30°	1130.7	1128.6	1126.6	1124.6	1122.6	1120.0	1116.7	1113.5	1110.2	1106.9	1106.0
32.5°	1096.3	1094.5	1092.7	1091.0	1089.2	1086.5	1083.0	1079.6	1076.1	1072.7	1071.5
35°	1042.7	1041.0	1039.2	1037.5	1035.7	1033.1	1029.6	1026.1	1022.5	1019.0	1017.2
37.5°	986.1	984.5	982.9	981.3	979.7	977.1	973.2	969.5	965.7	962.0	960.1
40°	949.2	947.1	945.1	943.1	941.1	938.2	934.5	930.7	927.0	923.2	920.7
42.5°	909.5	908.2	907.0	905.9	904.7	902.0	897.8	893.6	889.5	885.3	882.4
45°	851.1	849.3	847.6	845.8	844.1	841.1	837.1	833.2	829.2	825.2	822.4
47.5°	789.9	788.8	787.6	786.4	785.1	782.7	779.0	775.3	771.6	767.8	764.8
50°	748.5	747.5	746.5	745.5	744.4	742.2	738.7	735.2	731.7	728.2	724.7
52.5°	707.9	706.7	705.5	704.3	703.1	700.7	696.9	693.2	689.5	685.8	682.7
55°	643.7	642.9	642.1	641.4	640.7	638.5	635.0	631.5	628.0	624.5	621.5
57.5°	582.4	581.5	580.7	579.8	578.9	576.7	573.3	569.9	566.4	563.0	560.1
60°	540.0	538.7	537.4	536.2	534.9	532.7	529.5	526.2	522.9	519.7	517.4
62.5°	498.5	497.4	496.4	495.3	494.2	492.0	488.5	485.1	481.6	478.2	476.1
65°	436.3	435.0	433.7	432.5	431.2	429.3	426.8	424.4	421.8	419.3	416.9
67.5°	373.6	372.4	371.3	370.1	368.9	367.2	364.8	362.4	360.0	357.6	355.1
70°	334.8	333.0	331.3	329.5	327.8	325.9	323.9	321.9	319.9	317.9	315.8
72.5°	293.3	291.6	289.8	288.0	286.3	284.6	283.0	281.4	279.8	278.2	276.6
75°	232.2	231.0	229.7	228.4	227.2	225.9	224.7	223.5	222.2	220.9	220.0
77.5°	173.8	173.3	172.7	172.2	171.6	170.8	169.7	168.6	167.5	166.4	166.1
80°	138.7	137.9	137.1	136.4	135.7	135.0	134.5	134.0	133.5	133.0	132.5
82.5°	104.4	104.0	103.7	103.3	103.0	102.7	102.6	102.6	102.5	102.3	102.1
85°	60.9	60.9	60.9	60.9	60.9	60.7	60.1	59.6	59.1	58.6	58.6
87.5°	24.2	24.6	24.9	25.4	25.8	26.1	26.3	26.6	26.8	27.1	27.4
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	15.5	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7
95°	67.6	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7
97.5°	143.6	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6
100°	201.6	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5
102.5°	266.5	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5
105°	370.1	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0
107.5°	466.2	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5
110°	531.2	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7



TEST NUMBER: P332833-930

CATALOG NUMBER: S124DIW-S1020D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	594.1	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1
115°	691.0	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0
117.5°	778.3	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8
120°	837.3	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6
122.5°	892.3	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4
125°	971.3	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6
127.5°	1046.0	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8
130°	1094.3	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4
132.5°	1138.5	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7
135°	1204.9	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2
137.5°	1263.7	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2
140°	1302.0	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8
142.5°	1336.4	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0
145°	1389.4	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3
147.5°	1431.4	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3
150°	1461.9	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6
152.5°	1487.4	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6
155°	1523.4	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0
157.5°	1553.6	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1
160°	1571.3	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1
162.5°	1587.1	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7
165°	1607.0	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0
167.5°	1622.7	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0
170°	1631.6	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6
172.5°	1637.4	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5
175°	1643.8	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1
177.5°	1646.8	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332833-930

CATALOG NUMBER: S124DIW-S1020D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1401.7	1403.8	1405.8	1406.7	1406.5	1406.3	1406.1	1405.9
5°	1394.2	1397.0	1399.8	1400.9	1400.4	1399.9	1399.4	1398.9
7.5°	1378.8	1381.0	1383.2	1384.1	1383.8	1383.5	1383.2	1382.9
10°	1365.7	1367.7	1369.7	1370.4	1369.9	1369.5	1369.0	1368.5
12.5°	1349.9	1352.1	1354.3	1355.0	1354.4	1353.6	1352.9	1352.3
15°	1319.6	1321.1	1322.7	1323.0	1322.3	1321.5	1320.8	1320.0
17.5°	1285.2	1286.1	1287.0	1287.3	1286.8	1286.3	1285.8	1285.2
20°	1259.5	1260.3	1261.0	1261.1	1260.6	1260.1	1259.6	1259.1
22.5°	1232.7	1234.1	1235.4	1235.7	1234.8	1233.9	1233.0	1232.1
25°	1188.6	1188.9	1189.1	1188.7	1187.7	1186.7	1185.7	1184.7
27.5°	1139.1	1138.5	1137.9	1137.0	1135.7	1134.5	1133.2	1132.0
30°	1105.0	1103.9	1102.9	1101.8	1100.6	1099.3	1098.0	1096.8
32.5°	1070.2	1069.1	1067.9	1066.7	1065.4	1064.1	1062.9	1061.6
35°	1015.5	1013.7	1012.0	1010.5	1009.3	1008.0	1006.7	1005.5
37.5°	958.1	956.3	954.4	952.6	951.0	949.3	947.6	946.0
40°	918.2	915.7	913.2	911.3	910.0	908.8	907.6	906.3
42.5°	879.5	876.6	873.7	871.8	871.0	870.1	869.3	868.5
45°	819.6	816.8	814.1	812.4	811.6	810.9	810.1	809.3
47.5°	761.7	758.6	755.5	752.9	751.1	749.1	747.2	745.3
50°	721.2	717.7	714.2	711.7	710.1	708.7	707.2	705.6
52.5°	679.6	676.5	673.4	670.9	669.0	667.1	665.2	663.2
55°	618.5	615.5	612.5	610.3	608.7	607.2	605.7	604.2
57.5°	557.3	554.4	551.5	549.3	547.9	546.5	545.0	543.6
60°	515.2	512.9	510.6	508.9	507.6	506.4	505.2	503.9
62.5°	474.1	472.0	469.9	468.3	467.1	465.8	464.6	463.3
65°	414.3	411.8	409.3	407.4	406.2	405.0	403.7	402.4
67.5°	352.8	350.3	348.0	346.6	346.2	345.8	345.5	345.2
70°	313.9	311.9	309.9	308.5	307.8	307.0	306.2	305.5
72.5°	275.0	273.4	271.8	270.6	269.9	269.1	268.4	267.6
75°	218.9	217.9	217.0	216.3	216.1	215.8	215.6	215.3
77.5°	165.8	165.5	165.2	164.7	164.0	163.4	162.7	162.1
80°	132.0	131.5	131.0	130.6	130.4	130.1	129.9	129.6
82.5°	101.7	101.4	101.2	100.9	100.6	100.4	100.1	99.9
85°	58.6	58.6	58.6	58.5	58.2	58.0	57.7	57.5
87.5°	27.7	28.0	28.4	28.6	28.7	28.8	28.9	29.0
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	29.4	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	30.3	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.8	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	44.8	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	160.5	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	388.5	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	480.7	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.3	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P332833-930

CATALOG NUMBER: S124DIW-S1020D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	604.0	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	694.6	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.7	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	897.7	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	975.4	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.6	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1099.8	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.0	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1209.7	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1270.8	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1308.6	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1343.6	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.6	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.5	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.0	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1523.1	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1584.5	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1605.2	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1620.4	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1629.8	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1635.7	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1642.6	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1645.4	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)