

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333068-935

Luminaire Tested: **S124RDIW-S795D1340U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333068-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1340U935-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6882.9 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180° — 45°-225° - - 90°-270° - · - 135°-315°



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																												
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36																												
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31																												
3	80	71	64	59	73	66	59	55	54	50	46	44	41	38	35	33	31	26																												
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	23																												
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20																												
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18																												
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	24	21	19	16																												
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14																												
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13																												
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	19	16	14	12																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9175	9175	9175	9175
5°	10643	9203	8135	9203
10°	12591	9163	7260	9163
15°	14543	9078	6238	9078
20°	16192	8961	5642	8961
25°	16715	8847	5238	8847
30°	14632	8708	4994	8708
35°	11391	8502	4847	8502
40°	8541	8266	4769	8266
45°	6744	7889	4727	7889
50°	5693	7454	4589	7454
55°	4963	6973	4345	6973
60°	4466	6476	3846	6476
65°	3935	5939	3307	5939
70°	3545	5384	2984	5384
75°	2969	4769	2542	4769
80°	2515	4068	2385	4068
85°	2121	3186	2121	3186



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	1.6
10°-20°	332.2	4.8
20°-30°	519.5	7.5
30°-40°	577.6	8.4
40°-50°	512.4	7.4
50°-60°	399.3	5.8
60°-70°	261.4	3.8
70°-80°	128.6	1.9
80°-90°	36.0	0.5
90°-100°	95.2	1.4
100°-110°	282.1	4.1
110°-120°	478.8	7.0
120°-130°	631.3	9.2
130°-140°	709.0	10.3
140°-150°	696.7	10.1
150°-160°	586.0	8.5
160°-170°	389.9	5.7
170°-180°	136.5	2.0
0°-30°	961.8	14.0
0°-40°	1539.4	22.4
0°-60°	2451.2	35.6
0°-90°	2877.2	41.8
90°-120°	856.1	12.4
90°-150°	2893.2	42.0
90°-180°	4006.0	58.2
0°-180°	6882.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1136	1136	1136	1136	1136	
5°	1313	1136	1004	1136	1313	133
15°	1740	1086	746	1086	1740	495
25°	1876	993	588	993	1876	832
35°	1156	863	492	863	1156	724
45°	591	691	414	691	591	468
55°	353	495	309	495	353	321
65°	206	311	173	311	206	207
75°	95	153	82	153	95	105
85°	23	34	23	34	23	27
90°	34	3	34	3	34	18
95°	88	67	88	67	88	92
105°	272	260	272	260	272	287
115°	482	487	482	487	482	477
125°	703	709	703	709	703	628
135°	916	914	916	914	916	707
145°	1112	1111	1112	1111	1112	696
155°	1272	1273	1272	1273	1272	585
165°	1382	1386	1382	1386	1382	389
175°	1435	1442	1435	1442	1435	136
180°	1444	1444	1444	1444	1444	



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1198.8	1202.1	1198.8	1198.4	1194.8	1193.7	1192.2	1187.5	1178.6	1173.5	1174.7
5°	1313.3	1324.7	1318.4	1317.4	1307.3	1297.3	1290.8	1276.2	1260.6	1250.1	1241.4
7.5°	1445.7	1452.3	1448.3	1441.8	1425.6	1416.3	1401.4	1382.2	1354.3	1332.9	1313.4
10°	1535.9	1541.4	1539.5	1527.6	1515.7	1491.4	1477.6	1450.7	1415.4	1387.5	1361.4
12.5°	1624.4	1630.4	1614.2	1614.8	1592.2	1573.1	1551.3	1517.3	1476.6	1440.6	1407.9
15°	1740.1	1732.8	1732.8	1723.5	1698.4	1671.8	1649.4	1613.7	1562.4	1519.3	1474.0
17.5°	1830.6	1833.1	1829.4	1807.8	1788.0	1760.5	1719.3	1677.7	1630.0	1572.3	1526.0
20°	1884.7	1884.7	1880.7	1866.0	1840.4	1811.0	1766.6	1721.3	1660.9	1602.7	1550.5
22.5°	1906.8	1908.2	1903.3	1891.3	1868.2	1839.6	1801.8	1755.8	1693.4	1628.0	1563.3
25°	1876.5	1885.2	1886.1	1882.9	1876.0	1858.6	1826.2	1779.0	1723.1	1652.2	1582.5
27.5°	1722.9	1733.8	1743.4	1759.3	1780.4	1791.3	1792.8	1768.8	1720.1	1651.7	1581.7
30°	1569.7	1578.9	1608.6	1647.5	1677.8	1705.3	1729.1	1735.5	1708.1	1646.7	1573.0
32.5°	1399.7	1412.2	1442.0	1483.8	1534.2	1580.7	1634.2	1661.5	1660.8	1623.9	1555.7
35°	1155.8	1164.9	1192.4	1236.4	1296.8	1366.0	1450.7	1516.6	1561.5	1558.2	1516.6
37.5°	932.1	942.5	970.3	1006.7	1065.3	1150.9	1232.9	1323.7	1406.7	1453.3	1439.4
40°	810.5	811.0	838.0	875.6	930.5	1005.1	1094.4	1195.2	1287.6	1363.2	1377.9
42.5°	714.5	714.6	732.5	772.9	812.5	882.8	968.0	1068.1	1176.3	1263.6	1302.4
45°	590.7	594.9	609.5	633.8	664.9	724.4	792.6	885.6	1006.9	1110.4	1175.0
47.5°	500.2	506.3	515.6	535.4	560.2	599.9	656.3	739.8	838.5	952.4	1044.2
50°	453.3	454.3	466.1	477.2	498.7	530.3	579.7	649.3	739.9	849.5	951.6
52.5°	413.0	412.8	420.0	433.9	451.4	476.0	516.0	579.4	659.8	757.9	863.2
55°	352.6	354.9	360.4	371.3	384.6	402.1	433.6	481.3	544.5	628.3	723.9
57.5°	306.6	307.8	312.1	316.8	329.0	341.6	365.3	398.4	451.7	520.3	609.5
60°	276.6	277.1	278.4	285.2	294.9	306.8	322.8	350.8	395.6	458.4	528.9
62.5°	247.3	248.1	250.2	255.2	262.7	270.9	287.7	310.1	347.2	400.9	464.4
65°	206.0	206.6	209.7	211.5	217.5	224.8	237.2	252.3	277.9	322.8	370.9
67.5°	172.2	172.2	172.4	174.9	178.9	183.8	191.2	203.3	222.7	250.2	292.6
70°	150.2	150.2	151.1	152.5	154.8	158.9	163.0	172.2	186.4	208.8	241.3
72.5°	129.7	130.0	131.0	131.2	132.4	135.8	138.9	144.7	155.2	172.2	198.5
75°	95.2	96.6	98.9	100.7	103.1	102.5	105.8	109.4	112.6	122.7	137.8
77.5°	70.9	70.2	70.4	72.0	72.2	72.8	75.0	77.8	80.2	85.0	90.4
80°	54.1	54.1	55.4	55.9	55.4	55.9	58.1	59.5	60.4	62.3	67.3
82.5°	40.8	41.6	41.2	41.6	41.8	42.3	44.3	44.5	45.5	46.1	48.3
85°	22.9	23.3	23.8	22.9	22.9	22.9	23.8	24.3	25.2	24.7	25.7
87.5°	14.7	14.3	14.6	14.5	14.7	14.1	14.2	14.6	13.6	13.7	13.3
90°	33.5	33.0	32.5	32.0	31.5	30.5	29.0	27.6	26.1	24.5	22.6
92.5°	49.6	49.2	49.0	48.6	48.4	47.8	46.9	46.0	45.1	44.3	42.8
95°	88.3	88.3	88.3	88.3	88.3	87.8	87.1	86.4	85.6	84.9	83.1
97.5°	138.3	138.3	138.3	138.3	138.3	137.8	136.9	136.0	135.1	134.2	132.2
100°	173.1	173.1	173.1	173.1	173.1	172.8	172.4	171.9	171.3	170.8	168.6
102.5°	212.4	212.2	212.0	211.8	211.5	211.1	210.4	209.7	209.1	208.4	206.3
105°	272.4	271.7	271.0	270.2	269.5	268.7	268.0	267.3	266.5	265.8	264.8
107.5°	331.0	331.1	331.1	331.1	331.1	330.9	330.1	329.4	328.7	328.0	328.0
110°	373.0	372.2	371.4	370.7	370.0	369.9	370.3	370.8	371.3	371.9	372.1



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.9	415.7	415.5	415.3	415.3	415.2	415.3	415.4	415.5	415.6	416.0
115°	482.4	482.6	482.8	483.1	483.4	483.6	483.9	484.1	484.4	484.6	485.1
117.5°	545.8	546.3	546.8	547.3	547.8	548.5	549.3	550.2	551.0	551.8	552.2
120°	594.0	593.6	593.1	592.5	592.0	592.5	593.7	595.0	596.2	597.4	598.1
122.5°	634.2	635.2	636.0	636.9	637.8	638.7	639.6	640.3	641.2	642.0	642.4
125°	703.4	704.0	704.5	705.0	705.4	705.9	706.5	707.0	707.4	707.9	708.2
127.5°	767.6	767.9	768.4	768.8	769.1	769.6	770.1	770.6	771.1	771.5	772.0
130°	809.5	810.5	811.5	812.5	813.6	814.2	814.8	815.3	815.7	816.2	816.2
132.5°	854.2	854.6	855.0	855.4	855.8	856.3	856.8	857.2	857.7	858.2	858.4
135°	915.6	916.4	917.1	917.8	918.6	919.2	919.7	920.2	920.8	921.2	921.2
137.5°	980.2	980.0	979.9	979.7	979.6	979.8	980.5	981.1	981.7	982.4	982.0
140°	1019.5	1019.7	1019.9	1020.2	1020.5	1020.7	1021.0	1021.2	1021.5	1021.7	1021.7
142.5°	1058.8	1058.9	1058.9	1058.9	1058.9	1059.0	1059.1	1059.1	1059.2	1059.2	1059.5
145°	1112.2	1112.9	1113.6	1114.4	1115.2	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4
147.5°	1166.2	1166.5	1166.7	1166.9	1167.2	1167.4	1167.6	1167.8	1168.0	1168.2	1168.4
150°	1199.3	1199.5	1199.7	1200.0	1200.2	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1229.6	1230.3	1230.9	1231.6	1232.2	1232.3	1231.7	1231.1	1230.5	1229.9	1229.7
155°	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9	1272.0
157.5°	1309.6	1310.4	1311.2	1312.1	1312.9	1313.0	1312.3	1311.5	1310.8	1310.0	1310.1
160°	1331.0	1332.2	1333.5	1334.7	1335.9	1336.2	1335.5	1334.7	1333.9	1333.3	1333.5
162.5°	1353.3	1354.6	1355.8	1357.0	1358.3	1358.2	1356.9	1355.6	1354.3	1352.9	1353.1
165°	1382.3	1383.4	1384.3	1385.3	1386.4	1386.1	1384.6	1383.1	1381.6	1380.1	1380.6
167.5°	1403.2	1404.7	1406.2	1407.7	1409.3	1409.3	1407.8	1406.4	1404.9	1403.3	1403.3
170°	1414.8	1416.5	1418.2	1420.0	1421.7	1421.9	1420.3	1418.8	1417.4	1415.8	1415.7
172.5°	1424.6	1426.3	1428.1	1429.8	1431.5	1431.6	1429.9	1428.1	1426.5	1424.8	1424.8
175°	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9	1435.1
177.5°	1440.2	1441.8	1443.4	1445.0	1446.6	1446.7	1445.3	1443.9	1442.5	1441.1	1441.1
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1171.0	1165.9	1163.3	1157.4	1150.5	1146.8	1143.5	1138.8	1132.5	1125.9	1121.1
5°	1230.4	1219.4	1205.7	1189.2	1174.6	1160.4	1148.0	1135.7	1121.5	1106.7	1092.1
7.5°	1291.4	1269.8	1246.5	1219.4	1193.2	1169.2	1147.3	1126.2	1102.3	1081.1	1061.6
10°	1333.9	1304.6	1272.0	1237.8	1203.4	1173.6	1144.4	1117.8	1088.5	1062.4	1040.3
12.5°	1368.3	1333.9	1294.8	1252.0	1210.7	1174.7	1141.0	1106.4	1073.1	1044.7	1015.5
15°	1425.5	1378.3	1325.7	1274.4	1220.8	1171.8	1126.4	1086.2	1048.2	1008.3	980.4
17.5°	1464.7	1408.8	1344.8	1283.1	1219.9	1162.1	1109.8	1061.8	1018.0	977.2	944.0
20°	1488.2	1426.4	1355.4	1285.4	1214.4	1152.5	1096.2	1043.1	997.8	953.8	919.5
22.5°	1501.4	1433.0	1355.4	1282.0	1208.5	1141.6	1079.8	1024.4	975.1	931.1	893.1
25°	1505.6	1432.4	1353.1	1268.9	1188.3	1117.3	1053.2	993.2	938.2	894.3	854.0
27.5°	1499.8	1413.5	1332.3	1245.9	1162.7	1087.9	1020.6	957.6	902.6	855.4	814.1
30°	1491.0	1398.4	1311.5	1221.7	1137.5	1065.6	994.5	934.1	876.9	827.9	786.3
32.5°	1471.9	1380.2	1286.5	1194.6	1109.2	1035.2	967.9	907.1	850.9	800.8	756.6
35°	1434.2	1341.3	1239.6	1145.2	1061.4	984.5	921.4	862.7	809.2	755.5	708.9
37.5°	1384.5	1289.5	1188.4	1085.0	1001.2	928.6	870.6	815.5	763.3	714.4	662.6
40°	1337.6	1251.0	1146.6	1044.0	957.9	887.9	834.3	784.4	731.8	683.2	631.5
42.5°	1280.7	1207.0	1101.6	998.6	913.6	846.1	796.3	747.4	699.5	652.5	598.5
45°	1186.0	1130.1	1031.2	932.3	846.7	779.8	734.0	691.0	648.8	604.0	553.2
47.5°	1077.4	1039.6	954.2	852.9	773.7	713.5	669.3	634.1	598.5	553.6	509.0
50°	1001.9	977.7	895.2	802.7	727.2	671.8	626.5	593.5	563.7	520.6	480.8
52.5°	921.4	908.4	838.8	750.4	677.3	623.0	584.3	554.7	524.5	488.8	451.5
55°	798.6	805.5	746.4	669.9	601.2	555.4	520.2	495.4	469.8	439.6	410.8
57.5°	673.1	698.2	658.6	591.4	527.0	484.7	458.2	437.4	415.9	390.8	366.2
60°	598.1	619.1	596.7	537.6	481.3	441.9	417.2	401.1	379.6	356.7	337.9
62.5°	524.8	547.3	534.0	486.3	434.0	400.1	378.3	363.4	347.4	327.4	307.9
65°	432.7	447.4	441.0	408.0	370.9	342.1	321.9	310.9	296.3	281.6	264.2
67.5°	331.4	359.7	356.0	338.5	306.4	283.9	270.7	261.0	247.6	236.8	224.9
70°	272.4	298.6	298.1	283.9	266.5	245.5	236.3	228.1	216.1	205.6	196.0
72.5°	223.0	246.9	250.5	239.6	227.6	211.7	202.9	197.3	185.7	178.5	170.7
75°	156.2	173.6	178.1	178.1	172.6	164.4	156.6	152.9	144.7	138.3	133.7
77.5°	102.4	113.4	120.5	122.2	123.0	120.3	113.8	111.2	105.0	102.6	98.2
80°	72.3	79.6	87.9	90.7	93.0	92.0	89.3	87.5	81.5	79.2	77.4
82.5°	50.0	54.1	60.8	66.8	66.2	68.6	66.2	64.7	60.3	59.4	57.6
85°	26.1	26.5	27.5	31.6	33.9	34.8	35.3	34.4	33.0	33.0	29.8
87.5°	12.9	12.1	12.5	12.1	11.8	12.7	13.3	13.1	12.6	12.1	11.5
90°	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4	6.1	8.8	11.5
92.5°	41.4	40.0	38.7	36.4	33.2	30.1	27.0	23.9	27.0	30.1	33.2
95°	81.4	79.6	77.9	75.9	73.7	71.5	69.2	67.0	69.2	71.5	73.7
97.5°	130.2	128.1	126.1	124.2	122.3	120.6	118.8	117.0	118.8	120.6	122.3
100°	166.3	164.1	161.9	160.3	159.3	158.3	157.3	156.4	157.3	158.3	159.3
102.5°	204.3	202.2	200.2	199.0	198.6	198.2	197.9	197.4	197.9	198.2	198.6
105°	263.8	262.8	261.7	261.1	260.9	260.7	260.5	260.2	260.5	260.7	260.9
107.5°	327.8	327.6	327.4	327.3	326.9	326.7	326.3	326.1	326.3	326.7	326.9
110°	372.3	372.6	372.8	372.7	372.2	371.7	371.2	370.7	371.2	371.7	372.2





TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.5	417.0	417.4	417.6	417.5	417.3	417.2	417.2	417.2	417.3	417.5
115°	485.6	486.1	486.6	486.8	486.8	486.8	486.8	486.8	486.8	486.8	486.8
117.5°	552.5	552.8	553.2	553.3	553.1	552.9	552.7	552.5	552.7	552.9	553.1
120°	598.9	599.6	600.4	600.2	599.3	598.2	597.3	596.2	597.3	598.2	599.3
122.5°	642.7	643.1	643.4	643.4	643.0	642.7	642.2	641.8	642.2	642.7	643.0
125°	708.4	708.7	708.9	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
127.5°	772.4	772.7	773.2	773.0	772.2	771.5	770.8	770.0	770.8	771.5	772.2
130°	816.2	816.2	816.2	815.9	815.1	814.4	813.6	812.9	813.6	814.4	815.1
132.5°	858.6	858.8	859.0	858.8	858.3	857.7	857.2	856.7	857.2	857.7	858.3
135°	921.2	921.2	921.2	920.5	918.9	917.5	916.0	914.5	916.0	917.5	918.9
137.5°	981.6	981.2	980.9	980.2	979.6	978.9	978.2	977.5	978.2	978.9	979.6
140°	1021.7	1021.7	1021.7	1021.5	1021.0	1020.5	1019.9	1019.5	1019.9	1020.5	1021.0
142.5°	1059.6	1059.8	1060.0	1059.9	1059.4	1058.9	1058.3	1057.9	1058.3	1058.9	1059.4
145°	1116.1	1115.9	1115.6	1115.0	1114.0	1113.0	1112.1	1111.0	1112.1	1113.0	1114.0
147.5°	1168.6	1168.8	1169.0	1168.5	1167.3	1166.1	1164.9	1163.7	1164.9	1166.1	1167.3
150°	1200.3	1200.3	1200.3	1199.9	1198.9	1197.9	1196.9	1195.9	1196.9	1197.9	1198.9
152.5°	1229.4	1229.2	1229.1	1228.6	1228.0	1227.4	1226.8	1226.2	1226.8	1227.4	1228.0
155°	1272.3	1272.6	1272.8	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9	1272.9
157.5°	1310.1	1310.2	1310.2	1310.4	1310.9	1311.4	1311.8	1312.3	1311.8	1311.4	1310.9
160°	1333.8	1333.9	1334.2	1334.5	1334.7	1335.0	1335.2	1335.5	1335.2	1335.0	1334.7
162.5°	1353.4	1353.7	1353.9	1354.4	1355.0	1355.6	1356.2	1356.9	1356.2	1355.6	1355.0
165°	1381.1	1381.6	1382.2	1382.8	1383.5	1384.2	1385.0	1385.7	1385.0	1384.2	1383.5
167.5°	1403.3	1403.3	1403.2	1403.7	1404.7	1405.8	1406.8	1407.8	1406.8	1405.8	1404.7
170°	1415.4	1415.1	1414.9	1415.4	1416.6	1417.9	1419.1	1420.3	1419.1	1417.9	1416.6
172.5°	1424.7	1424.7	1424.6	1425.1	1426.2	1427.2	1428.2	1429.3	1428.2	1427.2	1426.2
175°	1435.4	1435.6	1435.8	1436.6	1437.9	1439.1	1440.3	1441.6	1440.3	1439.1	1437.9
177.5°	1441.1	1441.1	1441.1	1441.6	1442.6	1443.6	1444.6	1445.5	1444.6	1443.6	1442.6
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1116.0	1112.3	1107.6	1102.1	1095.5	1089.7	1087.1	1089.3	1090.4	1087.4	1087.1
5°	1082.0	1070.6	1061.4	1047.7	1036.7	1027.5	1021.1	1018.4	1019.3	1012.0	1010.1
7.5°	1043.9	1030.3	1015.3	999.0	983.8	970.3	963.3	959.4	951.7	948.3	942.7
10°	1019.3	1001.0	986.4	967.1	949.7	933.7	925.9	919.5	911.7	908.0	900.3
12.5°	994.0	972.8	956.7	936.7	918.9	899.6	892.2	880.3	868.1	860.4	850.4
15°	958.4	932.8	913.1	889.2	868.2	846.2	826.6	804.5	796.3	778.9	768.9
17.5°	916.7	890.7	866.3	834.4	801.9	774.6	753.6	732.5	720.0	708.9	703.7
20°	889.2	865.5	831.6	794.4	758.3	728.1	711.1	697.4	683.6	675.9	670.4
22.5°	863.2	832.8	793.5	753.5	717.3	693.6	679.2	665.1	654.0	646.6	639.2
25°	819.7	779.8	738.1	692.3	667.6	647.0	631.5	620.0	613.1	603.6	599.9
27.5°	774.9	726.6	680.6	649.9	624.1	605.3	591.7	583.1	574.4	568.3	563.5
30°	740.5	691.5	650.2	621.0	594.9	579.3	568.3	558.2	551.3	546.3	542.6
32.5°	706.4	657.4	622.8	591.2	570.7	555.4	543.7	536.2	530.8	524.3	522.1
35°	657.1	613.6	583.4	555.0	533.9	520.2	511.0	503.3	498.7	496.8	495.4
37.5°	609.8	574.1	541.7	518.3	499.6	488.8	477.9	474.2	471.0	467.7	469.2
40°	579.7	546.3	517.5	492.8	477.6	465.7	459.3	454.7	451.9	451.9	451.9
42.5°	553.7	521.0	492.9	470.7	455.6	445.6	438.4	434.5	433.6	433.3	435.5
45°	513.3	483.1	454.7	436.4	423.5	413.5	409.4	406.1	406.1	408.0	408.5
47.5°	473.3	445.0	422.2	401.7	389.9	383.7	380.0	378.4	378.6	380.5	382.5
50°	448.8	420.9	398.4	380.0	369.1	363.1	359.9	359.0	359.9	359.9	363.1
52.5°	422.0	397.0	375.0	359.6	347.1	341.5	339.8	338.5	339.1	340.5	341.9
55°	382.8	360.4	339.3	324.7	315.5	311.9	307.7	308.2	307.3	308.2	308.2
57.5°	343.5	323.4	303.8	292.1	284.1	278.8	274.3	275.6	274.2	274.1	273.3
60°	318.2	296.3	280.7	270.2	261.0	256.4	252.3	253.2	251.8	250.9	249.1
62.5°	290.8	272.4	257.6	247.5	240.1	234.8	230.7	229.8	226.6	223.4	219.5
65°	250.9	235.8	222.6	212.9	206.0	201.9	198.7	196.0	189.1	181.8	178.1
67.5°	212.2	201.3	188.9	180.8	175.2	169.8	163.7	159.0	152.6	148.5	146.3
70°	187.3	176.8	166.3	158.4	152.5	147.5	140.6	137.4	132.8	131.0	128.6
72.5°	163.5	153.7	143.9	136.8	130.5	126.6	121.1	118.0	116.0	115.2	113.0
75°	127.3	119.5	112.2	105.8	100.7	98.0	95.7	93.4	92.5	88.3	86.1
77.5°	92.9	87.7	83.2	78.6	75.0	73.2	68.8	66.1	64.6	62.7	62.2
80°	72.3	68.7	64.1	61.4	56.3	54.5	52.7	52.2	51.7	51.3	50.8
82.5°	54.4	50.7	46.1	44.5	43.1	42.0	40.9	40.5	40.0	40.3	40.2
85°	27.5	25.7	25.7	25.2	24.7	24.3	23.8	23.8	23.3	23.8	23.3
87.5°	12.1	12.1	12.5	12.1	12.9	13.3	13.3	13.6	14.2	13.8	14.0
90°	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6	29.0	30.5	31.5
92.5°	36.4	38.7	40.0	41.4	42.8	44.3	45.1	46.0	46.9	47.8	48.4
95°	75.9	77.9	79.6	81.4	83.1	84.9	85.6	86.4	87.1	87.8	88.3
97.5°	124.2	126.1	128.1	130.2	132.2	134.2	135.1	136.0	136.9	137.8	138.3
100°	160.3	161.9	164.1	166.3	168.6	170.8	171.3	171.9	172.4	172.8	173.1
102.5°	199.0	200.2	202.2	204.3	206.3	208.4	209.1	209.7	210.4	211.1	211.5
105°	261.1	261.7	262.8	263.8	264.8	265.8	266.5	267.3	268.0	268.7	269.5
107.5°	327.3	327.4	327.6	327.8	328.0	328.0	328.7	329.4	330.1	330.9	331.1
110°	372.7	372.8	372.6	372.3	372.1	371.9	371.3	370.8	370.3	369.9	370.0



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	417.6	417.4	417.0	416.5	416.0	415.6	415.5	415.4	415.3	415.2	415.3
115°	486.8	486.6	486.1	485.6	485.1	484.6	484.4	484.1	483.9	483.6	483.4
117.5°	553.3	553.2	552.8	552.5	552.2	551.8	551.0	550.2	549.3	548.5	547.8
120°	600.2	600.4	599.6	598.9	598.1	597.4	596.2	595.0	593.7	592.5	592.0
122.5°	643.4	643.4	643.1	642.7	642.4	642.0	641.2	640.3	639.6	638.7	637.8
125°	709.0	708.9	708.7	708.4	708.2	707.9	707.4	707.0	706.5	705.9	705.4
127.5°	773.0	773.2	772.7	772.4	772.0	771.5	771.1	770.6	770.1	769.6	769.1
130°	815.9	816.2	816.2	816.2	816.2	816.2	815.7	815.3	814.8	814.2	813.6
132.5°	858.8	859.0	858.8	858.6	858.4	858.2	857.7	857.2	856.8	856.3	855.8
135°	920.5	921.2	921.2	921.2	921.2	921.2	920.8	920.2	919.7	919.2	918.6
137.5°	980.2	980.9	981.2	981.6	982.0	982.4	981.7	981.1	980.5	979.8	979.6
140°	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.2	1021.0	1020.7	1020.5
142.5°	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2	1059.1	1059.1	1059.0	1058.9
145°	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4	1116.1	1115.9	1115.6	1115.2
147.5°	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0	1167.8	1167.6	1167.4	1167.2
150°	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.2
152.5°	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5	1231.1	1231.7	1232.3	1232.2
155°	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8
157.5°	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8	1311.5	1312.3	1313.0	1312.9
160°	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9	1334.7	1335.5	1336.2	1335.9
162.5°	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3	1355.6	1356.9	1358.2	1358.3
165°	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6	1383.1	1384.6	1386.1	1386.4
167.5°	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9	1406.4	1407.8	1409.3	1409.3
170°	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4	1418.8	1420.3	1421.9	1421.7
172.5°	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5	1428.1	1429.9	1431.6	1431.5
175°	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8
177.5°	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5	1443.9	1445.3	1446.7	1446.6
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1084.9	1085.6	1083.1	1082.3	1083.1	1085.6	1084.9	1087.1	1087.4	1090.4	1089.3
5°	1006.5	1005.6	1003.3	1003.8	1003.3	1005.6	1006.5	1010.1	1012.0	1019.3	1018.4
7.5°	939.4	935.9	936.9	933.2	936.9	935.9	939.4	942.7	948.3	951.7	959.4
10°	898.5	893.4	889.2	885.6	889.2	893.4	898.5	900.3	908.0	911.7	919.5
12.5°	842.4	838.1	832.5	833.6	832.5	838.1	842.4	850.4	860.4	868.1	880.3
15°	762.8	756.0	745.0	746.4	745.0	756.0	762.8	768.9	778.9	796.3	804.5
17.5°	695.6	695.7	690.6	691.8	690.6	695.7	695.6	703.7	708.9	720.0	732.5
20°	660.7	657.5	658.0	656.7	658.0	657.5	660.7	670.4	675.9	683.6	697.4
22.5°	636.6	632.7	629.5	626.6	629.5	632.7	636.6	639.2	646.6	654.0	665.1
25°	595.7	593.0	588.8	588.0	588.8	593.0	595.7	599.9	603.6	613.1	620.0
27.5°	559.8	559.3	557.7	555.5	557.7	559.3	559.8	563.5	568.3	574.4	583.1
30°	539.0	538.0	537.1	535.7	537.1	538.0	539.0	542.6	546.3	551.3	558.2
32.5°	520.3	519.7	518.8	518.9	518.8	519.7	520.3	522.1	524.3	530.8	536.2
35°	493.6	493.2	492.2	491.8	492.2	493.2	493.6	495.4	496.8	498.7	503.3
37.5°	468.7	469.9	469.3	469.2	469.3	469.9	468.7	469.2	467.7	471.0	474.2
40°	451.5	451.9	452.9	452.5	452.9	451.9	451.5	451.9	451.9	451.9	454.7
42.5°	437.2	437.3	438.6	437.0	438.6	437.3	437.2	435.5	433.3	433.6	434.5
45°	411.6	414.4	414.0	414.0	414.0	414.4	411.6	408.5	408.0	406.1	406.1
47.5°	383.7	386.1	386.8	386.7	386.8	386.1	383.7	382.5	380.5	378.6	378.4
50°	365.4	364.5	365.8	365.4	365.8	364.5	365.4	363.1	359.9	359.9	359.0
52.5°	343.1	343.3	343.2	342.7	343.2	343.3	343.1	341.9	340.5	339.1	338.5
55°	308.7	309.1	308.2	308.7	308.2	309.1	308.7	308.2	308.2	307.3	308.2
57.5°	271.3	269.1	270.0	268.9	270.0	269.1	271.3	273.3	274.1	274.2	275.6
60°	244.5	240.8	240.0	238.2	240.0	240.8	244.5	249.1	250.9	251.8	253.2
62.5°	214.5	211.9	208.8	210.3	208.8	211.9	214.5	219.5	223.4	226.6	229.8
65°	174.4	172.6	171.3	173.1	171.3	172.6	174.4	178.1	181.8	189.1	196.0
67.5°	144.4	143.4	143.4	142.5	143.4	143.4	144.4	146.3	148.5	152.6	159.0
70°	128.6	127.3	127.3	126.4	127.3	127.3	128.6	128.6	131.0	132.8	137.4
72.5°	112.5	111.2	111.6	111.0	111.6	111.2	112.5	113.0	115.2	116.0	118.0
75°	83.3	81.0	81.0	81.5	81.0	81.0	83.3	86.1	88.3	92.5	93.4
77.5°	62.2	61.7	62.3	61.6	62.3	61.7	62.2	62.2	62.7	64.6	66.1
80°	50.8	50.4	49.9	51.3	49.9	50.4	50.8	50.8	51.3	51.7	52.2
82.5°	39.4	39.3	39.3	41.1	39.3	39.3	39.4	40.2	40.3	40.0	40.5
85°	23.8	22.9	23.8	22.9	23.8	22.9	23.8	23.3	23.8	23.3	23.8
87.5°	14.8	14.6	14.3	14.7	14.3	14.6	14.8	14.0	13.8	14.2	13.6
90°	32.0	32.5	33.0	33.5	33.0	32.5	32.0	31.5	30.5	29.0	27.6
92.5°	48.6	49.0	49.2	49.6	49.2	49.0	48.6	48.4	47.8	46.9	46.0
95°	88.3	88.3	88.3	88.3	88.3	88.3	88.3	88.3	87.8	87.1	86.4
97.5°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	137.8	136.9	136.0
100°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	172.8	172.4	171.9
102.5°	211.8	212.0	212.2	212.4	212.2	212.0	211.8	211.5	211.1	210.4	209.7
105°	270.2	271.0	271.7	272.4	271.7	271.0	270.2	269.5	268.7	268.0	267.3
107.5°	331.1	331.1	331.1	331.0	331.1	331.1	331.1	331.1	330.9	330.1	329.4
110°	370.7	371.4	372.2	373.0	372.2	371.4	370.7	370.0	369.9	370.3	370.8



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	415.3	415.5	415.7	415.9	415.7	415.5	415.3	415.3	415.2	415.3	415.4
115°	483.1	482.8	482.6	482.4	482.6	482.8	483.1	483.4	483.6	483.9	484.1
117.5°	547.3	546.8	546.3	545.8	546.3	546.8	547.3	547.8	548.5	549.3	550.2
120°	592.5	593.1	593.6	594.0	593.6	593.1	592.5	592.0	592.5	593.7	595.0
122.5°	636.9	636.0	635.2	634.2	635.2	636.0	636.9	637.8	638.7	639.6	640.3
125°	705.0	704.5	704.0	703.4	704.0	704.5	705.0	705.4	705.9	706.5	707.0
127.5°	768.8	768.4	767.9	767.6	767.9	768.4	768.8	769.1	769.6	770.1	770.6
130°	812.5	811.5	810.5	809.5	810.5	811.5	812.5	813.6	814.2	814.8	815.3
132.5°	855.4	855.0	854.6	854.2	854.6	855.0	855.4	855.8	856.3	856.8	857.2
135°	917.8	917.1	916.4	915.6	916.4	917.1	917.8	918.6	919.2	919.7	920.2
137.5°	979.7	979.9	980.0	980.2	980.0	979.9	979.7	979.6	979.8	980.5	981.1
140°	1020.2	1019.9	1019.7	1019.5	1019.7	1019.9	1020.2	1020.5	1020.7	1021.0	1021.2
142.5°	1058.9	1058.9	1058.9	1058.8	1058.9	1058.9	1058.9	1058.9	1059.0	1059.1	1059.1
145°	1114.4	1113.6	1112.9	1112.2	1112.9	1113.6	1114.4	1115.2	1115.6	1115.9	1116.1
147.5°	1166.9	1166.7	1166.5	1166.2	1166.5	1166.7	1166.9	1167.2	1167.4	1167.6	1167.8
150°	1200.0	1199.7	1199.5	1199.3	1199.5	1199.7	1200.0	1200.2	1200.3	1200.3	1200.3
152.5°	1231.6	1230.9	1230.3	1229.6	1230.3	1230.9	1231.6	1232.2	1232.3	1231.7	1231.1
155°	1274.8	1273.8	1272.8	1271.9	1272.8	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8
157.5°	1312.1	1311.2	1310.4	1309.6	1310.4	1311.2	1312.1	1312.9	1313.0	1312.3	1311.5
160°	1334.7	1333.5	1332.2	1331.0	1332.2	1333.5	1334.7	1335.9	1336.2	1335.5	1334.7
162.5°	1357.0	1355.8	1354.6	1353.3	1354.6	1355.8	1357.0	1358.3	1358.2	1356.9	1355.6
165°	1385.3	1384.3	1383.4	1382.3	1383.4	1384.3	1385.3	1386.4	1386.1	1384.6	1383.1
167.5°	1407.7	1406.2	1404.7	1403.2	1404.7	1406.2	1407.7	1409.3	1409.3	1407.8	1406.4
170°	1420.0	1418.2	1416.5	1414.8	1416.5	1418.2	1420.0	1421.7	1421.9	1420.3	1418.8
172.5°	1429.8	1428.1	1426.3	1424.6	1426.3	1428.1	1429.8	1431.5	1431.6	1429.9	1428.1
175°	1440.0	1438.3	1436.6	1434.9	1436.6	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3
177.5°	1445.0	1443.4	1441.8	1440.2	1441.8	1443.4	1445.0	1446.6	1446.7	1445.3	1443.9
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1087.1	1089.7	1095.5	1102.1	1107.6	1112.3	1116.0	1121.1	1125.9	1132.5	1138.8
5°	1021.1	1027.5	1036.7	1047.7	1061.4	1070.6	1082.0	1092.1	1106.7	1121.5	1135.7
7.5°	963.3	970.3	983.8	999.0	1015.3	1030.3	1043.9	1061.6	1081.1	1102.3	1126.2
10°	925.9	933.7	949.7	967.1	986.4	1001.0	1019.3	1040.3	1062.4	1088.5	1117.8
12.5°	892.2	899.6	918.9	936.7	956.7	972.8	994.0	1015.5	1044.7	1073.1	1106.4
15°	826.6	846.2	868.2	889.2	913.1	932.8	958.4	980.4	1008.3	1048.2	1086.2
17.5°	753.6	774.6	801.9	834.4	866.3	890.7	916.7	944.0	977.2	1018.0	1061.8
20°	711.1	728.1	758.3	794.4	831.6	865.5	889.2	919.5	953.8	997.8	1043.1
22.5°	679.2	693.6	717.3	753.5	793.5	832.8	863.2	893.1	931.1	975.1	1024.4
25°	631.5	647.0	667.6	692.3	738.1	779.8	819.7	854.0	894.3	938.2	993.2
27.5°	591.7	605.3	624.1	649.9	680.6	726.6	774.9	814.1	855.4	902.6	957.6
30°	568.3	579.3	594.9	621.0	650.2	691.5	740.5	786.3	827.9	876.9	934.1
32.5°	543.7	555.4	570.7	591.2	622.8	657.4	706.4	756.6	800.8	850.9	907.1
35°	511.0	520.2	533.9	555.0	583.4	613.6	657.1	708.9	755.5	809.2	862.7
37.5°	477.9	488.8	499.6	518.3	541.7	574.1	609.8	662.6	714.4	763.3	815.5
40°	459.3	465.7	477.6	492.8	517.5	546.3	579.7	631.5	683.2	731.8	784.4
42.5°	438.4	445.6	455.6	470.7	492.9	521.0	553.7	598.5	652.5	699.5	747.4
45°	409.4	413.5	423.5	436.4	454.7	483.1	513.3	553.2	604.0	648.8	691.0
47.5°	380.0	383.7	389.9	401.7	422.2	445.0	473.3	509.0	553.6	598.5	634.1
50°	359.9	363.1	369.1	380.0	398.4	420.9	448.8	480.8	520.6	563.7	593.5
52.5°	339.8	341.5	347.1	359.6	375.0	397.0	422.0	451.5	488.8	524.5	554.7
55°	307.7	311.9	315.5	324.7	339.3	360.4	382.8	410.8	439.6	469.8	495.4
57.5°	274.3	278.8	284.1	292.1	303.8	323.4	343.5	366.2	390.8	415.9	437.4
60°	252.3	256.4	261.0	270.2	280.7	296.3	318.2	337.9	356.7	379.6	401.1
62.5°	230.7	234.8	240.1	247.5	257.6	272.4	290.8	307.9	327.4	347.4	363.4
65°	198.7	201.9	206.0	212.9	222.6	235.8	250.9	264.2	281.6	296.3	310.9
67.5°	163.7	169.8	175.2	180.8	188.9	201.3	212.2	224.9	236.8	247.6	261.0
70°	140.6	147.5	152.5	158.4	166.3	176.8	187.3	196.0	205.6	216.1	228.1
72.5°	121.1	126.6	130.5	136.8	143.9	153.7	163.5	170.7	178.5	185.7	197.3
75°	95.7	98.0	100.7	105.8	112.2	119.5	127.3	133.7	138.3	144.7	152.9
77.5°	68.8	73.2	75.0	78.6	83.2	87.7	92.9	98.2	102.6	105.0	111.2
80°	52.7	54.5	56.3	61.4	64.1	68.7	72.3	77.4	79.2	81.5	87.5
82.5°	40.9	42.0	43.1	44.5	46.1	50.7	54.4	57.6	59.4	60.3	64.7
85°	23.8	24.3	24.7	25.2	25.7	25.7	27.5	29.8	33.0	33.0	34.4
87.5°	13.3	13.3	12.9	12.1	12.5	12.1	12.1	11.5	12.1	12.6	13.1
90°	26.1	24.5	22.6	20.6	18.6	16.6	14.3	11.5	8.8	6.1	3.4
92.5°	45.1	44.3	42.8	41.4	40.0	38.7	36.4	33.2	30.1	27.0	23.9
95°	85.6	84.9	83.1	81.4	79.6	77.9	75.9	73.7	71.5	69.2	67.0
97.5°	135.1	134.2	132.2	130.2	128.1	126.1	124.2	122.3	120.6	118.8	117.0
100°	171.3	170.8	168.6	166.3	164.1	161.9	160.3	159.3	158.3	157.3	156.4
102.5°	209.1	208.4	206.3	204.3	202.2	200.2	199.0	198.6	198.2	197.9	197.4
105°	266.5	265.8	264.8	263.8	262.8	261.7	261.1	260.9	260.7	260.5	260.2
107.5°	328.7	328.0	328.0	327.8	327.6	327.4	327.3	326.9	326.7	326.3	326.1
110°	371.3	371.9	372.1	372.3	372.6	372.8	372.7	372.2	371.7	371.2	370.7



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.5	415.6	416.0	416.5	417.0	417.4	417.6	417.5	417.3	417.2	417.2
115°	484.4	484.6	485.1	485.6	486.1	486.6	486.8	486.8	486.8	486.8	486.8
117.5°	551.0	551.8	552.2	552.5	552.8	553.2	553.3	553.1	552.9	552.7	552.5
120°	596.2	597.4	598.1	598.9	599.6	600.4	600.2	599.3	598.2	597.3	596.2
122.5°	641.2	642.0	642.4	642.7	643.1	643.4	643.4	643.0	642.7	642.2	641.8
125°	707.4	707.9	708.2	708.4	708.7	708.9	709.0	709.0	709.0	709.0	709.0
127.5°	771.1	771.5	772.0	772.4	772.7	773.2	773.0	772.2	771.5	770.8	770.0
130°	815.7	816.2	816.2	816.2	816.2	816.2	815.9	815.1	814.4	813.6	812.9
132.5°	857.7	858.2	858.4	858.6	858.8	859.0	858.8	858.3	857.7	857.2	856.7
135°	920.8	921.2	921.2	921.2	921.2	921.2	920.5	918.9	917.5	916.0	914.5
137.5°	981.7	982.4	982.0	981.6	981.2	980.9	980.2	979.6	978.9	978.2	977.5
140°	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.0	1020.5	1019.9	1019.5
142.5°	1059.2	1059.2	1059.5	1059.6	1059.8	1060.0	1059.9	1059.4	1058.9	1058.3	1057.9
145°	1116.4	1116.6	1116.4	1116.1	1115.9	1115.6	1115.0	1114.0	1113.0	1112.1	1111.0
147.5°	1168.0	1168.2	1168.4	1168.6	1168.8	1169.0	1168.5	1167.3	1166.1	1164.9	1163.7
150°	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1199.9	1198.9	1197.9	1196.9	1195.9
152.5°	1230.5	1229.9	1229.7	1229.4	1229.2	1229.1	1228.6	1228.0	1227.4	1226.8	1226.2
155°	1272.8	1271.9	1272.0	1272.3	1272.6	1272.8	1272.9	1272.9	1272.9	1272.9	1272.9
157.5°	1310.8	1310.0	1310.1	1310.1	1310.2	1310.2	1310.4	1310.9	1311.4	1311.8	1312.3
160°	1333.9	1333.3	1333.5	1333.8	1333.9	1334.2	1334.5	1334.7	1335.0	1335.2	1335.5
162.5°	1354.3	1352.9	1353.1	1353.4	1353.7	1353.9	1354.4	1355.0	1355.6	1356.2	1356.9
165°	1381.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.8	1383.5	1384.2	1385.0	1385.7
167.5°	1404.9	1403.3	1403.3	1403.3	1403.3	1403.2	1403.7	1404.7	1405.8	1406.8	1407.8
170°	1417.4	1415.8	1415.7	1415.4	1415.1	1414.9	1415.4	1416.6	1417.9	1419.1	1420.3
172.5°	1426.5	1424.8	1424.8	1424.7	1424.7	1424.6	1425.1	1426.2	1427.2	1428.2	1429.3
175°	1436.6	1434.9	1435.1	1435.4	1435.6	1435.8	1436.6	1437.9	1439.1	1440.3	1441.6
177.5°	1442.5	1441.1	1441.1	1441.1	1441.1	1441.1	1441.6	1442.6	1443.6	1444.6	1445.5
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1143.5	1146.8	1150.5	1157.4	1163.3	1165.9	1171.0	1174.7	1173.5	1178.6	1187.5
5°	1148.0	1160.4	1174.6	1189.2	1205.7	1219.4	1230.4	1241.4	1250.1	1260.6	1276.2
7.5°	1147.3	1169.2	1193.2	1219.4	1246.5	1269.8	1291.4	1313.4	1332.9	1354.3	1382.2
10°	1144.4	1173.6	1203.4	1237.8	1272.0	1304.6	1333.9	1361.4	1387.5	1415.4	1450.7
12.5°	1141.0	1174.7	1210.7	1252.0	1294.8	1333.9	1368.3	1407.9	1440.6	1476.6	1517.3
15°	1126.4	1171.8	1220.8	1274.4	1325.7	1378.3	1425.5	1474.0	1519.3	1562.4	1613.7
17.5°	1109.8	1162.1	1219.9	1283.1	1344.8	1408.8	1464.7	1526.0	1572.3	1630.0	1677.7
20°	1096.2	1152.5	1214.4	1285.4	1355.4	1426.4	1488.2	1550.5	1602.7	1660.9	1721.3
22.5°	1079.8	1141.6	1208.5	1282.0	1355.4	1433.0	1501.4	1563.3	1628.0	1693.4	1755.8
25°	1053.2	1117.3	1188.3	1268.9	1353.1	1432.4	1505.6	1582.5	1652.2	1723.1	1779.0
27.5°	1020.6	1087.9	1162.7	1245.9	1332.3	1413.5	1499.8	1581.7	1651.7	1720.1	1768.8
30°	994.5	1065.6	1137.5	1221.7	1311.5	1398.4	1491.0	1573.0	1646.7	1708.1	1735.5
32.5°	967.9	1035.2	1109.2	1194.6	1286.5	1380.2	1471.9	1555.7	1623.9	1660.8	1661.5
35°	921.4	984.5	1061.4	1145.2	1239.6	1341.3	1434.2	1516.6	1558.2	1561.5	1516.6
37.5°	870.6	928.6	1001.2	1085.0	1188.4	1289.5	1384.5	1439.4	1453.3	1406.7	1323.7
40°	834.3	887.9	957.9	1044.0	1146.6	1251.0	1337.6	1377.9	1363.2	1287.6	1195.2
42.5°	796.3	846.1	913.6	998.6	1101.6	1207.0	1280.7	1302.4	1263.6	1176.3	1068.1
45°	734.0	779.8	846.7	932.3	1031.2	1130.1	1186.0	1175.0	1110.4	1006.9	885.6
47.5°	669.3	713.5	773.7	852.9	954.2	1039.6	1077.4	1044.2	952.4	838.5	739.8
50°	626.5	671.8	727.2	802.7	895.2	977.7	1001.9	951.6	849.5	739.9	649.3
52.5°	584.3	623.0	677.3	750.4	838.8	908.4	921.4	863.2	757.9	659.8	579.4
55°	520.2	555.4	601.2	669.9	746.4	805.5	798.6	723.9	628.3	544.5	481.3
57.5°	458.2	484.7	527.0	591.4	658.6	698.2	673.1	609.5	520.3	451.7	398.4
60°	417.2	441.9	481.3	537.6	596.7	619.1	598.1	528.9	458.4	395.6	350.8
62.5°	378.3	400.1	434.0	486.3	534.0	547.3	524.8	464.4	400.9	347.2	310.1
65°	321.9	342.1	370.9	408.0	441.0	447.4	432.7	370.9	322.8	277.9	252.3
67.5°	270.7	283.9	306.4	338.5	356.0	359.7	331.4	292.6	250.2	222.7	203.3
70°	236.3	245.5	266.5	283.9	298.1	298.6	272.4	241.3	208.8	186.4	172.2
72.5°	202.9	211.7	227.6	239.6	250.5	246.9	223.0	198.5	172.2	155.2	144.7
75°	156.6	164.4	172.6	178.1	178.1	173.6	156.2	137.8	122.7	112.6	109.4
77.5°	113.8	120.3	123.0	122.2	120.5	113.4	102.4	90.4	85.0	80.2	77.8
80°	89.3	92.0	93.0	90.7	87.9	79.6	72.3	67.3	62.3	60.4	59.5
82.5°	66.2	68.6	66.2	66.8	60.8	54.1	50.0	48.3	46.1	45.5	44.5
85°	35.3	34.8	33.9	31.6	27.5	26.5	26.1	25.7	24.7	25.2	24.3
87.5°	13.3	12.7	11.8	12.1	12.5	12.1	12.9	13.3	13.7	13.6	14.6
90°	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1	27.6
92.5°	27.0	30.1	33.2	36.4	38.7	40.0	41.4	42.8	44.3	45.1	46.0
95°	69.2	71.5	73.7	75.9	77.9	79.6	81.4	83.1	84.9	85.6	86.4
97.5°	118.8	120.6	122.3	124.2	126.1	128.1	130.2	132.2	134.2	135.1	136.0
100°	157.3	158.3	159.3	160.3	161.9	164.1	166.3	168.6	170.8	171.3	171.9
102.5°	197.9	198.2	198.6	199.0	200.2	202.2	204.3	206.3	208.4	209.1	209.7
105°	260.5	260.7	260.9	261.1	261.7	262.8	263.8	264.8	265.8	266.5	267.3
107.5°	326.3	326.7	326.9	327.3	327.4	327.6	327.8	328.0	328.0	328.7	329.4
110°	371.2	371.7	372.2	372.7	372.8	372.6	372.3	372.1	371.9	371.3	370.8





TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	417.2	417.3	417.5	417.6	417.4	417.0	416.5	416.0	415.6	415.5	415.4
115°	486.8	486.8	486.8	486.8	486.6	486.1	485.6	485.1	484.6	484.4	484.1
117.5°	552.7	552.9	553.1	553.3	553.2	552.8	552.5	552.2	551.8	551.0	550.2
120°	597.3	598.2	599.3	600.2	600.4	599.6	598.9	598.1	597.4	596.2	595.0
122.5°	642.2	642.7	643.0	643.4	643.4	643.1	642.7	642.4	642.0	641.2	640.3
125°	709.0	709.0	709.0	709.0	708.9	708.7	708.4	708.2	707.9	707.4	707.0
127.5°	770.8	771.5	772.2	773.0	773.2	772.7	772.4	772.0	771.5	771.1	770.6
130°	813.6	814.4	815.1	815.9	816.2	816.2	816.2	816.2	816.2	815.7	815.3
132.5°	857.2	857.7	858.3	858.8	859.0	858.8	858.6	858.4	858.2	857.7	857.2
135°	916.0	917.5	918.9	920.5	921.2	921.2	921.2	921.2	921.2	920.8	920.2
137.5°	978.2	978.9	979.6	980.2	980.9	981.2	981.6	982.0	982.4	981.7	981.1
140°	1019.9	1020.5	1021.0	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5	1021.2
142.5°	1058.3	1058.9	1059.4	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2	1059.1
145°	1112.1	1113.0	1114.0	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4	1116.1
147.5°	1164.9	1166.1	1167.3	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0	1167.8
150°	1196.9	1197.9	1198.9	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1226.8	1227.4	1228.0	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5	1231.1
155°	1272.9	1272.9	1272.9	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8	1273.8
157.5°	1311.8	1311.4	1310.9	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8	1311.5
160°	1335.2	1335.0	1334.7	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9	1334.7
162.5°	1356.2	1355.6	1355.0	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3	1355.6
165°	1385.0	1384.2	1383.5	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6	1383.1
167.5°	1406.8	1405.8	1404.7	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9	1406.4
170°	1419.1	1417.9	1416.6	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4	1418.8
172.5°	1428.2	1427.2	1426.2	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5	1428.1
175°	1440.3	1439.1	1437.9	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6	1438.3
177.5°	1444.6	1443.6	1442.6	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5	1443.9
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1192.2	1193.7	1194.8	1198.4	1198.8	1202.1	1198.8
5°	1290.8	1297.3	1307.3	1317.4	1318.4	1324.7	1313.3
7.5°	1401.4	1416.3	1425.6	1441.8	1448.3	1452.3	1445.7
10°	1477.6	1491.4	1515.7	1527.6	1539.5	1541.4	1535.9
12.5°	1551.3	1573.1	1592.2	1614.8	1614.2	1630.4	1624.4
15°	1649.4	1671.8	1698.4	1723.5	1732.8	1732.8	1740.1
17.5°	1719.3	1760.5	1788.0	1807.8	1829.4	1833.1	1830.6
20°	1766.6	1811.0	1840.4	1866.0	1880.7	1884.7	1884.7
22.5°	1801.8	1839.6	1868.2	1891.3	1903.3	1908.2	1906.8
25°	1826.2	1858.6	1876.0	1882.9	1886.1	1885.2	1876.5
27.5°	1792.8	1791.3	1780.4	1759.3	1743.4	1733.8	1722.9
30°	1729.1	1705.3	1677.8	1647.5	1608.6	1578.9	1569.7
32.5°	1634.2	1580.7	1534.2	1483.8	1442.0	1412.2	1399.7
35°	1450.7	1366.0	1296.8	1236.4	1192.4	1164.9	1155.8
37.5°	1232.9	1150.9	1065.3	1006.7	970.3	942.5	932.1
40°	1094.4	1005.1	930.5	875.6	838.0	811.0	810.5
42.5°	968.0	882.8	812.5	772.9	732.5	714.6	714.5
45°	792.6	724.4	664.9	633.8	609.5	594.9	590.7
47.5°	656.3	599.9	560.2	535.4	515.6	506.3	500.2
50°	579.7	530.3	498.7	477.2	466.1	454.3	453.3
52.5°	516.0	476.0	451.4	433.9	420.0	412.8	413.0
55°	433.6	402.1	384.6	371.3	360.4	354.9	352.6
57.5°	365.3	341.6	329.0	316.8	312.1	307.8	306.6
60°	322.8	306.8	294.9	285.2	278.4	277.1	276.6
62.5°	287.7	270.9	262.7	255.2	250.2	248.1	247.3
65°	237.2	224.8	217.5	211.5	209.7	206.6	206.0
67.5°	191.2	183.8	178.9	174.9	172.4	172.2	172.2
70°	163.0	158.9	154.8	152.5	151.1	150.2	150.2
72.5°	138.9	135.8	132.4	131.2	131.0	130.0	129.7
75°	105.8	102.5	103.1	100.7	98.9	96.6	95.2
77.5°	75.0	72.8	72.2	72.0	70.4	70.2	70.9
80°	58.1	55.9	55.4	55.9	55.4	54.1	54.1
82.5°	44.3	42.3	41.8	41.6	41.2	41.6	40.8
85°	23.8	22.9	22.9	22.9	23.8	23.3	22.9
87.5°	14.2	14.1	14.7	14.5	14.6	14.3	14.7
90°	29.0	30.5	31.5	32.0	32.5	33.0	33.5
92.5°	46.9	47.8	48.4	48.6	49.0	49.2	49.6
95°	87.1	87.8	88.3	88.3	88.3	88.3	88.3
97.5°	136.9	137.8	138.3	138.3	138.3	138.3	138.3
100°	172.4	172.8	173.1	173.1	173.1	173.1	173.1
102.5°	210.4	211.1	211.5	211.8	212.0	212.2	212.4
105°	268.0	268.7	269.5	270.2	271.0	271.7	272.4
107.5°	330.1	330.9	331.1	331.1	331.1	331.1	331.0
110°	370.3	369.9	370.0	370.7	371.4	372.2	373.0



TEST NUMBER: P333068-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	415.3	415.2	415.3	415.3	415.5	415.7	415.9
115°	483.9	483.6	483.4	483.1	482.8	482.6	482.4
117.5°	549.3	548.5	547.8	547.3	546.8	546.3	545.8
120°	593.7	592.5	592.0	592.5	593.1	593.6	594.0
122.5°	639.6	638.7	637.8	636.9	636.0	635.2	634.2
125°	706.5	705.9	705.4	705.0	704.5	704.0	703.4
127.5°	770.1	769.6	769.1	768.8	768.4	767.9	767.6
130°	814.8	814.2	813.6	812.5	811.5	810.5	809.5
132.5°	856.8	856.3	855.8	855.4	855.0	854.6	854.2
135°	919.7	919.2	918.6	917.8	917.1	916.4	915.6
137.5°	980.5	979.8	979.6	979.7	979.9	980.0	980.2
140°	1021.0	1020.7	1020.5	1020.2	1019.9	1019.7	1019.5
142.5°	1059.1	1059.0	1058.9	1058.9	1058.9	1058.9	1058.8
145°	1115.9	1115.6	1115.2	1114.4	1113.6	1112.9	1112.2
147.5°	1167.6	1167.4	1167.2	1166.9	1166.7	1166.5	1166.2
150°	1200.3	1200.3	1200.2	1200.0	1199.7	1199.5	1199.3
152.5°	1231.7	1232.3	1232.2	1231.6	1230.9	1230.3	1229.6
155°	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9
157.5°	1312.3	1313.0	1312.9	1312.1	1311.2	1310.4	1309.6
160°	1335.5	1336.2	1335.9	1334.7	1333.5	1332.2	1331.0
162.5°	1356.9	1358.2	1358.3	1357.0	1355.8	1354.6	1353.3
165°	1384.6	1386.1	1386.4	1385.3	1384.3	1383.4	1382.3
167.5°	1407.8	1409.3	1409.3	1407.7	1406.2	1404.7	1403.2
170°	1420.3	1421.9	1421.7	1420.0	1418.2	1416.5	1414.8
172.5°	1429.9	1431.6	1431.5	1429.8	1428.1	1426.3	1424.6
175°	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9
177.5°	1445.3	1446.7	1446.6	1445.0	1443.4	1441.8	1440.2
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8

(END OF REPORT)