

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332857-930

Luminaire Tested: **S124DIW-S1195D1340U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332857-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1340U930-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8547.0 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332857-930

CATALOG NUMBER: S124DIW-S1195D1340U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332857-930

CATALOG NUMBER: S124DIW-S1195D1340U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13116	13116	13116
5°	13156	12998	13092
10°	13073	12892	12956
15°	12915	12709	12741
20°	12706	12482	12493
25°	12466	12222	12188
30°	12172	11918	11808
35°	11869	11599	11445
40°	11552	11236	11031
45°	11222	10880	10671
50°	10857	10562	10236
55°	10463	10151	9821
60°	10069	9689	9397
65°	9626	9251	8879
70°	9128	8665	8327
75°	8366	7960	7757
80°	7443	7141	6960
85°	6512	6271	6150



TEST NUMBER: P332857-930

CATALOG NUMBER: S124DIW-S1195D1340U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.0	1.8
10°-20°	431.1	5.0
20°-30°	634.5	7.4
30°-40°	737.7	8.6
40°-50°	737.7	8.6
50°-60°	645.3	7.5
60°-70°	479.2	5.6
70°-80°	272.3	3.2
80°-90°	82.7	1.0
90°-100°	48.4	0.6
100°-110°	308.3	3.6
110°-120°	589.8	6.9
120°-130°	748.7	8.8
130°-140°	801.1	9.4
140°-150°	749.1	8.8
150°-160°	604.1	7.1
160°-170°	389.6	4.6
170°-180°	134.3	1.6
0°-30°	1218.6	14.3
0°-40°	1956.3	22.9
0°-60°	3339.3	39.1
0°-90°	4173.4	48.8
90°-120°	946.5	11.1
90°-150°	3245.5	38.0
90°-180°	4374.0	51.2
0°-180°	8547.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1625	1625	1625	1625	1625	
5°	1623	1618	1604	1617	1616	154
15°	1545	1539	1521	1528	1524	435
25°	1400	1390	1372	1373	1368	644
35°	1204	1195	1177	1168	1161	753
45°	983	973	953	939	935	757
55°	743	739	721	706	698	666
65°	504	497	484	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	3	15	23	29	32	6
95°	58	24	23	29	31	75
105°	318	325	330	337	301	333
115°	594	597	596	598	598	585
125°	835	839	838	841	842	746
135°	1036	1036	1040	1042	1044	798
145°	1195	1198	1198	1199	1201	746
155°	1310	1311	1308	1312	1309	604
165°	1382	1377	1377	1384	1376	390
175°	1414	1408	1409	1417	1405	135
180°	1414	1414	1414	1414	1414	



TEST NUMBER: P332857-930

CATALOG NUMBER: S124DIW-S1195D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1628.9	1628.2	1627.5	1626.8	1626.1	1624.5	1622.0	1619.4	1616.9	1614.4	1616.7
5°	1623.4	1622.3	1621.1	1620.0	1618.9	1616.7	1613.5	1610.3	1607.1	1603.9	1607.1
7.5°	1608.3	1607.2	1606.1	1604.8	1603.7	1601.4	1597.8	1594.3	1590.8	1587.2	1589.8
10°	1594.8	1593.7	1592.5	1591.3	1590.2	1587.7	1584.0	1580.2	1576.5	1572.7	1575.0
12.5°	1577.1	1576.0	1574.8	1573.6	1572.5	1569.9	1565.9	1562.0	1558.0	1554.0	1556.5
15°	1545.3	1544.2	1543.0	1541.9	1540.7	1538.0	1533.6	1529.3	1524.9	1520.6	1522.3
17.5°	1507.1	1505.6	1504.1	1502.8	1501.3	1498.5	1494.4	1490.3	1486.2	1482.1	1483.2
20°	1479.0	1477.5	1476.0	1474.6	1473.2	1470.2	1465.9	1461.6	1457.3	1452.9	1453.8
22.5°	1448.7	1446.8	1445.0	1443.0	1441.1	1437.9	1433.6	1429.3	1425.0	1420.6	1422.2
25°	1399.5	1397.5	1395.5	1393.4	1391.4	1388.4	1384.3	1380.3	1376.2	1372.1	1372.5
27.5°	1343.3	1341.2	1339.1	1337.0	1335.0	1332.0	1328.3	1324.5	1320.8	1317.0	1316.3
30°	1305.8	1303.5	1301.1	1298.9	1296.6	1293.5	1289.7	1286.0	1282.2	1278.5	1277.3
32.5°	1266.2	1264.1	1262.1	1260.0	1257.8	1254.8	1250.8	1246.8	1242.8	1238.8	1237.5
35°	1204.3	1202.2	1200.2	1198.2	1196.1	1193.1	1189.0	1185.0	1181.0	1176.9	1174.8
37.5°	1138.9	1137.0	1135.2	1133.3	1131.5	1128.4	1124.1	1119.7	1115.3	1111.0	1108.8
40°	1096.2	1093.9	1091.5	1089.2	1087.0	1083.6	1079.3	1074.9	1070.6	1066.2	1063.3
42.5°	1050.4	1049.0	1047.6	1046.2	1044.8	1041.7	1036.9	1032.1	1027.3	1022.5	1019.1
45°	982.9	980.9	978.8	976.8	974.9	971.5	966.9	962.2	957.6	953.0	949.8
47.5°	912.3	910.9	909.5	908.2	906.8	904.0	899.7	895.4	891.1	886.9	883.3
50°	864.5	863.3	862.1	861.0	859.8	857.2	853.1	849.1	845.1	841.0	837.0
52.5°	817.6	816.2	814.8	813.4	812.0	809.2	804.9	800.6	796.4	792.1	788.5
55°	743.4	742.5	741.7	740.8	739.9	737.4	733.4	729.4	725.3	721.2	717.8
57.5°	672.5	671.6	670.6	669.6	668.6	666.1	662.1	658.1	654.1	650.1	646.9
60°	623.6	622.2	620.7	619.3	617.8	615.2	611.5	607.7	603.9	600.1	597.5
62.5°	575.7	574.5	573.2	572.0	570.9	568.3	564.3	560.3	556.3	552.3	549.9
65°	503.9	502.4	500.9	499.5	498.1	495.9	493.0	490.1	487.2	484.3	481.4
67.5°	431.5	430.2	428.8	427.5	426.2	424.0	421.3	418.5	415.7	412.9	410.2
70°	386.7	384.7	382.6	380.6	378.5	376.4	374.1	371.8	369.4	367.1	364.8
72.5°	338.8	336.7	334.7	332.6	330.7	328.7	326.9	325.0	323.2	321.3	319.4
75°	268.2	266.8	265.3	263.8	262.4	261.0	259.5	258.0	256.7	255.2	254.0
77.5°	200.7	200.1	199.5	198.9	198.2	197.2	196.0	194.7	193.5	192.2	191.8
80°	160.1	159.2	158.4	157.5	156.7	156.0	155.4	154.7	154.2	153.6	153.0
82.5°	120.6	120.2	119.8	119.4	119.0	118.7	118.5	118.5	118.3	118.2	117.9
85°	70.3	70.3	70.3	70.3	70.3	70.0	69.5	68.9	68.2	67.7	67.7
87.5°	27.7	28.0	28.3	28.5	28.9	29.1	29.2	29.4	29.5	29.7	29.9
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	13.3	13.5	13.6	13.8	13.9	14.9	16.8	18.7	20.5	22.4	23.8
95°	58.1	50.1	42.2	34.2	26.2	22.3	22.6	22.8	23.0	23.2	24.7
97.5°	123.5	128.5	133.5	138.4	143.4	132.8	106.6	80.4	54.1	27.9	28.0
100°	173.4	177.7	181.9	186.1	190.4	176.3	143.8	111.4	78.9	46.6	42.6
102.5°	229.3	232.4	235.5	238.6	241.7	241.1	236.8	232.7	228.4	224.2	181.1
105°	318.3	319.7	321.1	322.5	323.9	325.2	326.4	327.6	328.7	330.0	332.1
107.5°	401.0	401.7	402.4	403.1	403.8	405.0	406.6	408.1	409.8	411.4	412.4
110°	456.8	457.5	458.3	458.9	459.7	460.7	462.1	463.5	465.0	466.4	466.8



TEST NUMBER: P332857-930

CATALOG NUMBER: S124DIW-S1195D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	510.9	512.3	513.6	514.8	516.1	517.0	517.7	518.4	519.0	519.7	519.6
115°	594.3	595.0	595.7	596.4	597.1	597.4	597.1	596.9	596.6	596.4	596.9
117.5°	669.4	670.3	671.2	672.2	673.1	673.8	674.4	674.9	675.4	676.0	675.9
120°	720.2	721.1	722.0	723.0	723.9	724.2	724.1	723.8	723.6	723.3	723.8
122.5°	767.5	768.1	768.7	769.2	769.8	770.2	770.5	770.9	771.2	771.5	771.8
125°	835.4	836.3	837.3	838.2	839.2	839.4	838.9	838.5	838.0	837.6	838.2
127.5°	899.7	899.9	900.2	900.4	900.7	901.3	902.4	903.4	904.6	905.6	905.5
130°	941.2	941.4	941.7	941.8	942.1	942.6	943.3	944.0	944.7	945.4	945.7
132.5°	979.3	979.7	980.1	980.5	980.9	981.6	982.5	983.3	984.2	985.1	985.4
135°	1036.3	1036.1	1035.8	1035.7	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0
137.5°	1086.9	1087.0	1087.0	1087.2	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5
140°	1119.9	1120.4	1120.8	1121.3	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8
142.5°	1149.5	1150.3	1151.2	1152.0	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1
145°	1195.0	1195.6	1196.4	1197.1	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4
147.5°	1231.1	1232.4	1233.8	1235.1	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2
150°	1257.4	1258.3	1259.2	1260.2	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5
152.5°	1279.4	1280.1	1280.8	1281.6	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2
155°	1310.3	1310.4	1310.7	1310.9	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0
157.5°	1336.3	1336.1	1335.9	1335.8	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3
160°	1351.4	1350.8	1350.1	1349.3	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7
162.5°	1365.0	1364.1	1363.3	1362.4	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3
165°	1382.2	1381.0	1379.8	1378.6	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8
167.5°	1395.7	1394.5	1393.3	1392.0	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6
170°	1403.3	1401.9	1400.4	1399.1	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9
172.5°	1408.3	1407.0	1405.6	1404.1	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9
175°	1413.9	1412.4	1411.0	1409.7	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7
177.5°	1416.4	1415.1	1413.7	1412.4	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P332857-930

CATALOG NUMBER: S124DIW-S1195D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1618.9	1621.3	1623.6	1624.6	1624.4	1624.2	1623.9	1623.7
5°	1610.3	1613.5	1616.7	1618.0	1617.4	1616.8	1616.2	1615.6
7.5°	1592.4	1594.9	1597.4	1598.6	1598.2	1597.8	1597.5	1597.2
10°	1577.3	1579.6	1581.9	1582.8	1582.3	1581.7	1581.0	1580.5
12.5°	1559.0	1561.5	1564.2	1565.0	1564.2	1563.3	1562.5	1561.7
15°	1524.0	1525.8	1527.5	1528.0	1527.1	1526.2	1525.3	1524.5
17.5°	1484.3	1485.4	1486.5	1486.7	1486.1	1485.6	1485.0	1484.4
20°	1454.7	1455.5	1456.4	1456.5	1456.0	1455.4	1454.8	1454.2
22.5°	1423.8	1425.3	1426.9	1427.1	1426.1	1425.1	1424.0	1422.9
25°	1372.8	1373.0	1373.4	1372.9	1371.7	1370.6	1369.5	1368.3
27.5°	1315.6	1314.9	1314.2	1313.1	1311.7	1310.3	1308.8	1307.3
30°	1276.1	1275.0	1273.8	1272.5	1271.1	1269.7	1268.2	1266.7
32.5°	1236.1	1234.7	1233.3	1231.9	1230.4	1229.0	1227.6	1226.1
35°	1172.9	1170.9	1168.8	1167.1	1165.6	1164.2	1162.7	1161.3
37.5°	1106.6	1104.4	1102.2	1100.2	1098.3	1096.3	1094.5	1092.5
40°	1060.5	1057.5	1054.7	1052.5	1051.1	1049.6	1048.1	1046.7
42.5°	1015.8	1012.4	1009.1	1006.9	1005.9	1004.9	1004.0	1003.0
45°	946.6	943.5	940.3	938.2	937.3	936.5	935.6	934.7
47.5°	879.7	876.1	872.5	869.6	867.4	865.2	863.0	860.8
50°	832.9	828.8	824.8	821.9	820.2	818.5	816.7	815.0
52.5°	784.9	781.3	777.7	774.9	772.7	770.5	768.3	766.1
55°	714.3	710.9	707.4	704.7	703.0	701.3	699.5	697.8
57.5°	643.6	640.3	637.0	634.5	632.8	631.1	629.4	627.8
60°	594.9	592.4	589.8	587.7	586.3	584.8	583.4	582.0
62.5°	547.5	545.1	542.7	540.9	539.4	537.9	536.5	535.1
65°	478.5	475.6	472.7	470.6	469.1	467.7	466.2	464.8
67.5°	407.4	404.6	401.9	400.2	399.8	399.4	399.0	398.6
70°	362.5	360.2	357.8	356.3	355.4	354.6	353.7	352.8
72.5°	317.6	315.8	313.9	312.5	311.7	310.8	309.9	309.1
75°	252.8	251.7	250.5	249.8	249.6	249.2	248.9	248.7
77.5°	191.4	191.1	190.8	190.2	189.5	188.7	187.9	187.2
80°	152.5	151.9	151.3	150.9	150.6	150.3	150.0	149.7
82.5°	117.5	117.2	116.8	116.5	116.2	115.9	115.6	115.4
85°	67.7	67.7	67.7	67.6	67.3	66.9	66.7	66.4
87.5°	30.2	30.5	30.7	31.0	31.1	31.1	31.2	31.3
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	25.3	26.7	28.0	28.8	28.9	29.0	29.1	29.2
95°	26.1	27.5	28.9	29.8	29.9	30.2	30.4	30.7
97.5°	28.2	28.4	28.5	28.7	28.9	29.1	29.4	29.6
100°	38.6	34.6	30.6	28.7	28.9	29.1	29.4	29.6
102.5°	138.0	94.9	51.8	30.2	30.3	30.3	30.4	30.5
105°	334.2	336.3	338.4	335.3	326.8	318.3	309.8	301.4
107.5°	413.4	414.5	415.5	416.5	417.4	418.2	419.1	420.0
110°	467.3	467.7	468.2	468.8	469.5	470.3	470.9	471.7





TEST NUMBER: P332857-930

CATALOG NUMBER: S124DIW-S1195D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	519.4	519.3	519.3	519.7	520.6	521.5	522.4	523.3
115°	597.4	597.9	598.3	598.5	598.5	598.5	598.5	598.5
117.5°	675.7	675.6	675.6	675.5	675.4	675.3	675.2	675.1
120°	724.2	724.7	725.2	725.2	724.7	724.2	723.8	723.3
122.5°	772.1	772.4	772.7	772.6	772.1	771.6	771.2	770.7
125°	838.9	839.7	840.3	840.8	841.1	841.3	841.6	841.8
127.5°	905.4	905.2	905.1	904.9	904.7	904.5	904.3	904.2
130°	945.8	946.1	946.3	946.5	946.5	946.5	946.5	946.5
132.5°	985.6	985.9	986.1	986.1	985.9	985.8	985.5	985.4
135°	1040.5	1040.9	1041.4	1041.9	1042.4	1042.8	1043.3	1043.7
137.5°	1093.0	1093.5	1094.1	1094.2	1094.1	1094.0	1093.8	1093.6
140°	1125.5	1126.3	1126.9	1127.4	1127.6	1127.9	1128.1	1128.4
142.5°	1155.6	1156.1	1156.7	1156.9	1157.0	1157.0	1157.1	1157.1
145°	1198.6	1198.8	1199.1	1199.5	1199.9	1200.4	1200.9	1201.3
147.5°	1236.4	1236.6	1236.7	1237.0	1237.2	1237.5	1237.6	1237.9
150°	1260.5	1260.5	1260.5	1260.6	1260.9	1261.1	1261.3	1261.6
152.5°	1281.6	1282.0	1282.3	1282.5	1282.3	1282.1	1282.1	1281.9
155°	1310.0	1310.9	1311.9	1312.0	1311.3	1310.6	1309.9	1309.2
157.5°	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0
160°	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3
162.5°	1362.8	1364.2	1365.5	1365.5	1363.9	1362.3	1360.7	1359.1
165°	1380.6	1382.5	1384.4	1384.2	1382.2	1380.1	1377.9	1375.8
167.5°	1393.7	1395.7	1397.8	1397.7	1395.3	1392.9	1390.7	1388.3
170°	1401.7	1403.6	1405.5	1405.2	1403.0	1400.6	1398.2	1395.9
172.5°	1406.8	1408.8	1410.6	1410.3	1407.7	1405.2	1402.6	1400.1
175°	1412.8	1415.0	1417.1	1416.7	1413.9	1411.0	1408.2	1405.4
177.5°	1415.2	1416.7	1418.2	1417.8	1415.5	1413.3	1411.0	1408.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9

(END OF REPORT)