

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333070-935

Luminaire Tested: **S124RDIW-S795D1340U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333070-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1340U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6773.4 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333070-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333070-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35
2	88	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	31	30	25
4	73	63	55	49	66	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13
9	49	37	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P333070-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	1.7
10°-20°	313.3	4.6
20°-30°	452.4	6.7
30°-40°	512.8	7.6
40°-50°	495.2	7.3
50°-60°	411.8	6.1
60°-70°	284.4	4.2
70°-80°	144.1	2.1
80°-90°	41.3	0.6
90°-100°	95.2	1.4
100°-110°	282.1	4.2
110°-120°	478.8	7.1
120°-130°	631.3	9.3
130°-140°	709.0	10.5
140°-150°	696.7	10.3
150°-160°	586.0	8.7
160°-170°	389.9	5.8
170°-180°	136.5	2.0
0°-30°	878.1	13.0
0°-40°	1390.9	20.5
0°-60°	2297.9	33.9
0°-90°	2767.7	40.9
90°-120°	856.1	12.6
90°-150°	2893.2	42.7
90°-180°	4006.0	59.1
0°-180°	6773.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	3	15	24	31	34	7
95°	67	77	85	88	88	75
105°	260	261	266	269	272	276
115°	487	487	485	484	482	480
125°	709	709	708	706	703	632
135°	914	921	921	919	916	707
145°	1111	1115	1117	1115	1112	695
155°	1273	1273	1272	1276	1272	585
165°	1386	1382	1380	1386	1382	390
175°	1442	1436	1435	1442	1435	137
180°	1444	1444	1444	1444	1444	



TEST NUMBER: P333070-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.5	16.8	16.0	15.2	14.5	14.2	14.5	14.7	14.9	15.2	15.3
90°	3.4	6.1	8.8	11.5	14.3	16.6	18.6	20.6	22.6	24.5	26.1
92.5°	23.9	27.0	30.1	33.2	36.4	38.7	40.0	41.4	42.8	44.3	45.1
95°	67.0	69.2	71.5	73.7	75.9	77.9	79.6	81.4	83.1	84.9	85.6
97.5°	117.0	118.8	120.6	122.3	124.2	126.1	128.1	130.2	132.2	134.2	135.1
100°	156.4	157.3	158.3	159.3	160.3	161.9	164.1	166.3	168.6	170.8	171.3
102.5°	197.4	197.9	198.2	198.6	199.0	200.2	202.2	204.3	206.3	208.4	209.1
105°	260.2	260.5	260.7	260.9	261.1	261.7	262.8	263.8	264.8	265.8	266.5
107.5°	326.1	326.3	326.7	326.9	327.3	327.4	327.6	327.8	328.0	328.0	328.7
110°	370.7	371.2	371.7	372.2	372.7	372.8	372.6	372.3	372.1	371.9	371.3



TEST NUMBER: P333070-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	417.2	417.2	417.3	417.5	417.6	417.4	417.0	416.5	416.0	415.6	415.5
115°	486.8	486.8	486.8	486.8	486.8	486.6	486.1	485.6	485.1	484.6	484.4
117.5°	552.5	552.7	552.9	553.1	553.3	553.2	552.8	552.5	552.2	551.8	551.0
120°	596.2	597.3	598.2	599.3	600.2	600.4	599.6	598.9	598.1	597.4	596.2
122.5°	641.8	642.2	642.7	643.0	643.4	643.4	643.1	642.7	642.4	642.0	641.2
125°	709.0	709.0	709.0	709.0	709.0	708.9	708.7	708.4	708.2	707.9	707.4
127.5°	770.0	770.8	771.5	772.2	773.0	773.2	772.7	772.4	772.0	771.5	771.1
130°	812.9	813.6	814.4	815.1	815.9	816.2	816.2	816.2	816.2	816.2	815.7
132.5°	856.7	857.2	857.7	858.3	858.8	859.0	858.8	858.6	858.4	858.2	857.7
135°	914.5	916.0	917.5	918.9	920.5	921.2	921.2	921.2	921.2	921.2	920.8
137.5°	977.5	978.2	978.9	979.6	980.2	980.9	981.2	981.6	982.0	982.4	981.7
140°	1019.5	1019.9	1020.5	1021.0	1021.5	1021.7	1021.7	1021.7	1021.7	1021.7	1021.5
142.5°	1057.9	1058.3	1058.9	1059.4	1059.9	1060.0	1059.8	1059.6	1059.5	1059.2	1059.2
145°	1111.0	1112.1	1113.0	1114.0	1115.0	1115.6	1115.9	1116.1	1116.4	1116.6	1116.4
147.5°	1163.7	1164.9	1166.1	1167.3	1168.5	1169.0	1168.8	1168.6	1168.4	1168.2	1168.0
150°	1195.9	1196.9	1197.9	1198.9	1199.9	1200.3	1200.3	1200.3	1200.3	1200.3	1200.3
152.5°	1226.2	1226.8	1227.4	1228.0	1228.6	1229.1	1229.2	1229.4	1229.7	1229.9	1230.5
155°	1272.9	1272.9	1272.9	1272.9	1272.9	1272.8	1272.6	1272.3	1272.0	1271.9	1272.8
157.5°	1312.3	1311.8	1311.4	1310.9	1310.4	1310.2	1310.2	1310.1	1310.1	1310.0	1310.8
160°	1335.5	1335.2	1335.0	1334.7	1334.5	1334.2	1333.9	1333.8	1333.5	1333.3	1333.9
162.5°	1356.9	1356.2	1355.6	1355.0	1354.4	1353.9	1353.7	1353.4	1353.1	1352.9	1354.3
165°	1385.7	1385.0	1384.2	1383.5	1382.8	1382.2	1381.6	1381.1	1380.6	1380.1	1381.6
167.5°	1407.8	1406.8	1405.8	1404.7	1403.7	1403.2	1403.3	1403.3	1403.3	1403.3	1404.9
170°	1420.3	1419.1	1417.9	1416.6	1415.4	1414.9	1415.1	1415.4	1415.7	1415.8	1417.4
172.5°	1429.3	1428.2	1427.2	1426.2	1425.1	1424.6	1424.7	1424.7	1424.8	1424.8	1426.5
175°	1441.6	1440.3	1439.1	1437.9	1436.6	1435.8	1435.6	1435.4	1435.1	1434.9	1436.6
177.5°	1445.5	1444.6	1443.6	1442.6	1441.6	1441.1	1441.1	1441.1	1441.1	1441.1	1442.5
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8



TEST NUMBER: P333070-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	15.4	15.6	15.7	15.9	16.2	16.4	16.7	17.0
90°	27.6	29.0	30.5	31.5	32.0	32.5	33.0	33.5
92.5°	46.0	46.9	47.8	48.4	48.6	49.0	49.2	49.6
95°	86.4	87.1	87.8	88.3	88.3	88.3	88.3	88.3
97.5°	136.0	136.9	137.8	138.3	138.3	138.3	138.3	138.3
100°	171.9	172.4	172.8	173.1	173.1	173.1	173.1	173.1
102.5°	209.7	210.4	211.1	211.5	211.8	212.0	212.2	212.4
105°	267.3	268.0	268.7	269.5	270.2	271.0	271.7	272.4
107.5°	329.4	330.1	330.9	331.1	331.1	331.1	331.1	331.0
110°	370.8	370.3	369.9	370.0	370.7	371.4	372.2	373.0



TEST NUMBER: P333070-935

CATALOG NUMBER: S124RDIW-S795D1340U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	415.4	415.3	415.2	415.3	415.3	415.5	415.7	415.9
115°	484.1	483.9	483.6	483.4	483.1	482.8	482.6	482.4
117.5°	550.2	549.3	548.5	547.8	547.3	546.8	546.3	545.8
120°	595.0	593.7	592.5	592.0	592.5	593.1	593.6	594.0
122.5°	640.3	639.6	638.7	637.8	636.9	636.0	635.2	634.2
125°	707.0	706.5	705.9	705.4	705.0	704.5	704.0	703.4
127.5°	770.6	770.1	769.6	769.1	768.8	768.4	767.9	767.6
130°	815.3	814.8	814.2	813.6	812.5	811.5	810.5	809.5
132.5°	857.2	856.8	856.3	855.8	855.4	855.0	854.6	854.2
135°	920.2	919.7	919.2	918.6	917.8	917.1	916.4	915.6
137.5°	981.1	980.5	979.8	979.6	979.7	979.9	980.0	980.2
140°	1021.2	1021.0	1020.7	1020.5	1020.2	1019.9	1019.7	1019.5
142.5°	1059.1	1059.1	1059.0	1058.9	1058.9	1058.9	1058.9	1058.8
145°	1116.1	1115.9	1115.6	1115.2	1114.4	1113.6	1112.9	1112.2
147.5°	1167.8	1167.6	1167.4	1167.2	1166.9	1166.7	1166.5	1166.2
150°	1200.3	1200.3	1200.3	1200.2	1200.0	1199.7	1199.5	1199.3
152.5°	1231.1	1231.7	1232.3	1232.2	1231.6	1230.9	1230.3	1229.6
155°	1273.8	1274.8	1275.8	1275.8	1274.8	1273.8	1272.8	1271.9
157.5°	1311.5	1312.3	1313.0	1312.9	1312.1	1311.2	1310.4	1309.6
160°	1334.7	1335.5	1336.2	1335.9	1334.7	1333.5	1332.2	1331.0
162.5°	1355.6	1356.9	1358.2	1358.3	1357.0	1355.8	1354.6	1353.3
165°	1383.1	1384.6	1386.1	1386.4	1385.3	1384.3	1383.4	1382.3
167.5°	1406.4	1407.8	1409.3	1409.3	1407.7	1406.2	1404.7	1403.2
170°	1418.8	1420.3	1421.9	1421.7	1420.0	1418.2	1416.5	1414.8
172.5°	1428.1	1429.9	1431.6	1431.5	1429.8	1428.1	1426.3	1424.6
175°	1438.3	1440.0	1441.8	1441.8	1440.0	1438.3	1436.6	1434.9
177.5°	1443.9	1445.3	1446.7	1446.6	1445.0	1443.4	1441.8	1440.2
180°	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8	1443.8

(END OF REPORT)