

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332859-930

Luminaire Tested: **S124DIW-S1195D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332859-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U930-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9425.2 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	97	93	89	86	89	85	82	79	71	69	67	59	57	55	47	46	45	39				
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	40	38	33				
3	81	72	64	59	74	66	60	55	56	51	47	46	42	40	37	35	33	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12686	12686	12686	12686
5°	14939	12719	11225	12719
10°	17887	12663	10107	12663
15°	21163	12534	9281	12534
20°	23566	12404	8546	12404
25°	23947	12211	8036	12211
30°	20377	12027	7876	12027
35°	15666	11727	7877	11727
40°	12211	11374	8026	11374
45°	10182	10843	8161	10843
50°	8961	10194	8437	10194
55°	8210	9419	8777	9419
60°	7694	8724	9185	8724
65°	7163	7947	9524	7947
70°	6545	7176	9741	7176
75°	5845	6313	9623	6313
80°	4900	5174	9321	5174
85°	3622	3742	8929	3742



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.1	1.6
10°-20°	471.9	5.0
20°-30°	748.2	7.9
30°-40°	832.7	8.8
40°-50°	758.0	8.0
50°-60°	619.4	6.6
60°-70°	442.2	4.7
70°-80°	243.5	2.6
80°-90°	71.2	0.8
90°-100°	56.2	0.6
100°-110°	358.5	3.8
110°-120°	685.8	7.3
120°-130°	870.5	9.2
130°-140°	931.4	9.9
140°-150°	871.0	9.2
150°-160°	702.4	7.5
160°-170°	453.0	4.8
170°-180°	156.1	1.7
0°-30°	1373.2	14.6
0°-40°	2205.9	23.4
0°-60°	3583.3	38.0
0°-90°	4340.2	46.0
90°-120°	1100.5	11.7
90°-150°	3773.4	40.0
90°-180°	5085.0	54.0
0°-180°	9425.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1571	1571	1571	1571	1571	
5°	1844	1570	1385	1570	1844	187
15°	2532	1500	1110	1500	2532	715
25°	2688	1371	902	1371	2688	1185
35°	1590	1190	799	1190	1590	1009
45°	892	950	715	950	892	703
55°	583	669	624	669	583	527
65°	375	416	499	416	375	371
75°	187	202	308	202	187	199
85°	39	40	96	40	39	49
90°	37	4	37	4	37	17
95°	36	68	36	68	36	28
105°	350	370	350	370	350	306
115°	696	691	696	691	696	689
125°	979	971	979	971	979	872
135°	1214	1205	1214	1205	1214	934
145°	1397	1389	1397	1389	1397	873
155°	1522	1523	1522	1523	1522	702
165°	1600	1607	1600	1607	1600	452
175°	1634	1644	1634	1644	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4
2.5°	1672.4	1671.9	1666.7	1665.7	1662.0	1657.3	1656.3	1648.0	1631.3	1623.4	1621.4
5°	1843.5	1856.5	1839.6	1836.3	1834.3	1812.9	1801.8	1788.8	1758.8	1741.3	1727.6
7.5°	2047.6	2049.2	2041.8	2035.8	2019.3	2000.5	1972.4	1942.5	1906.7	1869.6	1841.7
10°	2182.0	2187.2	2178.7	2177.4	2144.2	2123.4	2081.7	2046.6	2006.2	1961.3	1920.3
12.5°	2323.6	2316.3	2312.0	2284.1	2278.0	2240.0	2191.6	2155.4	2093.2	2041.5	1987.0
15°	2532.2	2517.9	2508.8	2470.4	2451.4	2398.7	2347.3	2307.6	2226.3	2148.8	2090.2
17.5°	2654.5	2668.9	2647.8	2632.0	2583.2	2546.3	2493.7	2410.4	2346.7	2250.5	2176.5
20°	2743.1	2744.4	2732.6	2716.4	2678.0	2631.1	2573.8	2482.7	2406.5	2310.9	2209.3
22.5°	2767.0	2767.3	2762.3	2747.2	2718.0	2680.1	2622.2	2546.3	2454.0	2349.9	2248.4
25°	2688.4	2685.8	2691.6	2708.6	2697.5	2685.8	2652.6	2596.0	2510.1	2400.0	2290.7
27.5°	2396.2	2414.2	2447.3	2488.9	2529.1	2559.6	2568.3	2556.6	2503.4	2413.0	2298.3
30°	2185.9	2208.0	2232.8	2274.4	2355.2	2401.3	2452.1	2490.5	2469.1	2396.8	2290.0
32.5°	1954.7	1960.1	1996.8	2044.2	2118.1	2207.1	2287.6	2365.5	2391.4	2353.5	2264.5
35°	1589.6	1598.7	1638.4	1685.3	1775.8	1884.5	2005.6	2113.6	2202.8	2238.6	2193.0
37.5°	1297.2	1323.4	1351.4	1401.7	1481.4	1579.3	1705.1	1844.9	1977.8	2066.9	2081.9
40°	1158.7	1174.9	1195.1	1233.5	1301.2	1397.6	1505.6	1665.7	1807.0	1934.6	1976.3
42.5°	1049.3	1058.8	1071.2	1106.0	1157.5	1253.4	1352.0	1492.9	1634.7	1787.2	1857.0
45°	891.8	901.6	922.3	942.6	981.6	1048.0	1139.8	1255.6	1398.2	1545.3	1674.2
47.5°	778.0	784.2	796.6	818.2	851.4	895.2	969.9	1066.7	1198.8	1341.6	1479.0
50°	713.5	718.6	728.4	748.0	773.3	812.4	873.6	964.0	1067.6	1211.4	1346.1
52.5°	662.4	664.5	671.6	684.9	705.1	737.9	788.1	863.0	959.2	1087.4	1221.7
55°	583.3	585.9	592.4	602.1	619.7	640.5	678.9	734.9	818.9	930.2	1046.7
57.5°	518.1	520.0	525.5	529.2	543.6	560.6	590.1	630.1	693.7	788.1	892.2
60°	476.5	475.2	481.7	484.9	494.7	509.1	531.8	570.2	625.6	701.7	797.4
62.5°	435.9	434.1	439.5	443.8	449.4	461.6	480.3	510.4	555.2	624.1	706.8
65°	375.0	372.3	375.6	380.8	386.0	392.5	406.2	432.8	468.7	518.1	581.3
67.5°	313.7	316.5	317.0	319.6	322.6	331.5	340.8	359.7	385.0	424.5	478.1
70°	277.3	277.9	280.5	280.5	282.5	290.3	298.2	309.2	333.9	370.4	414.0
72.5°	240.8	243.6	242.6	244.6	246.1	251.3	257.0	267.5	288.6	315.7	352.5
75°	187.4	189.4	189.4	190.0	192.0	194.0	198.5	206.4	221.4	241.5	266.8
77.5°	136.7	137.0	137.9	140.2	140.2	143.3	146.8	153.0	160.4	174.2	189.7
80°	105.4	106.7	106.1	107.4	107.4	110.0	111.3	119.1	122.4	131.5	143.8
82.5°	77.4	78.6	78.5	80.3	81.4	81.9	83.7	86.8	90.1	98.2	103.2
85°	39.1	40.4	39.1	40.4	42.3	43.0	44.9	45.6	48.2	50.1	54.7
87.5°	18.8	20.3	20.1	20.6	21.5	21.9	22.0	21.2	22.9	23.2	24.8
90°	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3	28.7	27.1	24.9
92.5°	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4	27.7	26.1	23.9
95°	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3	28.7	27.1	26.7
97.5°	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8	32.6	32.4	62.9
100°	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8	49.5	54.1	91.8
102.5°	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5	210.5	260.7	265.5
105°	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5	386.0	383.6	382.2
107.5°	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7	479.5	478.3	476.4
110°	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3	542.7	542.2	540.5



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0	604.1	604.2	603.4
115°	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6	694.0	693.4	693.7
117.5°	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7	785.8	785.9	785.3
120°	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0	841.2
122.5°	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7	897.4	897.1	896.7
125°	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4	974.6	973.8	974.3
127.5°	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6	1052.8	1053.0	1051.7
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8	1099.4	1099.2	1098.4
132.5°	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0	1145.7	1145.4	1144.4
135°	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7	1209.2	1208.6	1207.5
137.5°	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8	1270.2	1269.6	1268.4
140°	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6	1307.8	1306.9	1306.4
142.5°	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6	1343.0	1342.4	1342.1
145°	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6	1393.3	1393.0	1393.0
147.5°	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5	1437.3	1437.0	1437.3
150°	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6	1465.6	1465.6	1465.8
152.5°	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0	1489.6	1489.1	1489.6
155°	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1	1522.0	1520.9	1521.8
157.5°	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7	1549.6
160°	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4	1566.7
162.5°	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5	1582.7	1581.1	1581.4
165°	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2	1603.0	1600.8	1600.8
167.5°	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4	1618.0	1615.6	1615.8
170°	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8	1627.6	1625.4	1625.1
172.5°	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7	1633.5	1631.3	1631.0
175°	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6	1640.1	1637.7	1637.4
177.5°	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4	1643.6	1641.8	1641.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4
2.5°	1621.9	1614.6	1609.4	1605.2	1593.7	1587.0	1581.8	1574.5	1566.2	1557.3	1546.4
5°	1713.9	1691.8	1675.5	1650.8	1627.3	1607.9	1587.6	1569.5	1547.3	1523.2	1505.6
7.5°	1810.7	1777.8	1735.5	1699.0	1657.8	1622.0	1590.0	1557.2	1523.1	1490.0	1459.7
10°	1872.1	1829.8	1782.9	1727.6	1675.5	1629.3	1586.3	1544.7	1504.3	1464.0	1429.5
12.5°	1938.3	1885.5	1816.2	1751.6	1693.2	1631.4	1579.6	1528.5	1479.8	1437.5	1397.2
15°	2027.1	1950.8	1870.8	1784.2	1707.4	1635.2	1564.2	1499.7	1445.1	1389.1	1350.1
17.5°	2081.6	1987.4	1895.8	1805.3	1712.4	1621.2	1544.7	1470.4	1401.9	1346.3	1297.1
20°	2117.5	2023.8	1909.8	1819.4	1708.7	1615.0	1526.5	1443.8	1372.2	1313.0	1262.2
22.5°	2148.8	2040.4	1926.6	1807.4	1697.3	1597.8	1501.0	1417.7	1344.6	1282.2	1233.5
25°	2165.7	2041.3	1917.7	1799.2	1674.2	1556.4	1468.5	1370.9	1292.7	1227.0	1174.9
27.5°	2167.6	2034.6	1894.7	1763.0	1634.0	1524.3	1413.3	1326.1	1245.0	1175.5	1125.5
30°	2161.8	2023.2	1872.7	1730.2	1600.7	1481.6	1385.2	1290.2	1207.5	1138.5	1086.4
32.5°	2143.6	1999.2	1844.6	1693.8	1559.5	1443.0	1343.5	1253.2	1172.6	1104.6	1049.9
35°	2090.8	1948.2	1783.5	1626.7	1489.4	1371.6	1281.7	1189.9	1109.2	1044.8	992.1
37.5°	2008.4	1879.5	1712.1	1549.8	1414.9	1296.6	1207.5	1124.5	1051.8	986.3	932.3
40°	1936.6	1823.3	1655.4	1497.1	1351.4	1238.8	1155.4	1079.3	1007.0	945.2	893.7
42.5°	1853.7	1755.1	1600.2	1432.6	1292.0	1178.8	1097.6	1029.2	961.2	904.0	852.6
45°	1706.1	1641.0	1495.3	1340.3	1193.8	1087.0	1009.6	949.7	892.4	836.5	793.5
47.5°	1536.4	1504.1	1381.3	1234.2	1095.1	989.9	922.8	867.5	817.2	769.8	731.9
50°	1422.3	1406.7	1300.6	1158.7	1025.9	926.9	859.2	811.7	768.7	727.1	691.3
52.5°	1309.9	1309.3	1213.7	1083.7	960.8	865.5	798.3	753.9	716.7	682.8	650.7
55°	1137.8	1156.1	1081.2	965.3	855.3	769.4	708.9	669.2	643.1	615.1	591.1
57.5°	979.9	1010.2	948.4	846.4	754.6	675.4	622.7	592.9	565.2	548.2	530.7
60°	876.9	905.5	857.3	771.4	684.8	617.1	567.0	540.3	516.2	504.5	492.1
62.5°	785.1	810.7	775.0	695.4	620.2	555.1	512.8	487.1	470.9	458.1	450.0
65°	654.2	675.7	645.1	587.2	522.7	470.7	436.1	416.0	400.3	395.1	386.0
67.5°	528.8	548.4	531.8	482.6	430.9	391.5	364.5	345.1	335.9	331.3	324.8
70°	454.4	473.9	456.3	413.4	373.7	340.5	315.0	304.0	294.2	292.3	283.2
72.5°	391.3	404.6	387.0	353.4	319.5	291.5	271.8	260.2	255.2	251.7	246.7
75°	293.6	305.3	293.6	267.5	243.4	224.0	207.0	202.4	196.6	194.6	191.4
77.5°	207.8	217.9	209.0	192.7	174.7	159.6	150.5	144.6	143.3	140.0	141.5
80°	158.8	165.3	156.9	145.8	131.5	121.1	114.5	111.3	107.4	106.1	108.7
82.5°	114.1	116.9	112.6	105.2	94.5	87.7	83.3	79.6	78.8	79.0	79.0
85°	59.3	58.6	58.0	51.4	48.2	43.6	41.0	40.4	39.7	41.0	42.3
87.5°	24.3	24.4	23.5	20.9	18.7	16.6	15.4	14.3	15.4	16.6	17.6
90°	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7	6.7	9.7	12.7
92.5°	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5	15.7	15.8	16.0
95°	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6	58.3	49.1	39.8
97.5°	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6	149.4	155.2	161.0
100°	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6	206.6	211.5	216.4
102.5°	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5	270.2	273.8	277.4
105°	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1	371.7	373.3	375.0
107.5°	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2	467.1	467.9	468.7
110°	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2	532.0	532.8	533.6



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1	595.6	597.0	598.5
115°	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0	691.8	692.6	693.4
117.5°	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3	779.3	780.5	781.5
120°	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3	838.4	839.5	840.6
122.5°	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3	893.0	893.6	894.3
125°	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3	972.4	973.5	974.6
127.5°	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0	1046.4	1046.6	1046.8
130°	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3	1094.5	1094.8	1095.1
132.5°	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5	1139.0	1139.5	1140.0
135°	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9	1204.6	1204.4	1204.1
137.5°	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7	1263.8	1263.9	1264.0
140°	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0	1302.6	1303.2	1303.7
142.5°	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4	1337.4	1338.5	1339.5
145°	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4	1390.2	1391.0	1391.8
147.5°	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4	1432.9	1434.4	1436.0
150°	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9	1463.0	1464.0	1465.2
152.5°	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4	1488.3	1489.2	1490.0
155°	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4	1523.6	1523.9	1524.2
157.5°	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6	1553.5	1553.3	1553.1
160°	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3	1570.5	1569.7	1568.9
162.5°	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1	1586.0	1584.9	1584.0
165°	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0	1605.6	1604.3	1602.9
167.5°	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7	1621.3	1619.8	1618.5
170°	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6	1629.9	1628.2	1626.6
172.5°	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4	1635.8	1634.2	1632.6
175°	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8	1642.2	1640.5	1638.9
177.5°	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8	1645.3	1643.7	1642.2
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4
2.5°	1541.2	1536.5	1529.7	1520.4	1512.5	1504.2	1502.1	1499.0	1505.2	1500.1	1498.4
5°	1490.7	1477.0	1459.4	1439.2	1427.5	1410.6	1407.4	1400.8	1394.3	1393.7	1387.2
7.5°	1437.1	1417.1	1394.1	1373.5	1354.5	1336.0	1323.9	1321.3	1311.7	1306.0	1299.5
10°	1402.8	1378.0	1351.4	1331.9	1309.7	1290.2	1276.5	1268.7	1262.2	1255.0	1248.5
12.5°	1362.2	1335.9	1313.9	1292.7	1266.5	1251.6	1229.1	1215.6	1214.3	1214.4	1197.5
15°	1314.9	1288.9	1255.0	1225.1	1210.7	1182.1	1169.7	1154.1	1144.4	1134.6	1126.8
17.5°	1260.9	1228.5	1202.0	1167.7	1140.4	1117.5	1101.3	1091.9	1077.2	1063.4	1053.4
20°	1227.0	1192.5	1164.6	1128.0	1098.1	1070.2	1056.5	1043.5	1032.4	1020.7	1009.6
22.5°	1192.6	1156.6	1122.3	1087.0	1059.1	1029.6	1016.4	998.7	988.1	981.6	970.5
25°	1138.5	1099.4	1060.4	1026.5	997.9	971.8	954.3	940.6	928.9	923.7	916.6
27.5°	1079.6	1040.9	1003.1	964.7	932.1	913.3	899.2	888.9	882.2	875.2	872.0
30°	1042.2	1001.8	961.5	925.6	895.7	876.9	863.8	856.6	851.4	848.2	844.9
32.5°	1004.1	964.3	921.9	889.2	862.3	845.5	835.7	828.5	825.9	824.8	823.6
35°	943.2	902.9	863.8	834.5	809.1	802.6	794.2	790.3	789.0	793.5	795.5
37.5°	884.3	846.8	810.8	782.4	765.8	756.3	753.4	753.5	758.2	762.2	767.0
40°	846.2	809.8	775.9	751.2	735.6	729.7	728.4	731.6	736.9	741.4	746.7
42.5°	809.3	773.3	742.6	719.4	708.5	703.1	703.9	707.2	714.4	720.1	727.9
45°	751.9	721.9	691.9	673.1	664.0	665.3	665.3	671.2	678.2	686.7	695.2
47.5°	697.8	667.6	643.0	627.1	622.4	621.3	624.9	632.6	642.9	653.3	665.1
50°	661.4	632.8	611.2	596.9	591.7	593.7	598.8	606.0	618.4	631.4	643.8
52.5°	624.4	598.3	578.5	565.2	561.5	565.0	570.2	581.6	592.4	606.4	621.4
55°	567.0	544.9	529.2	519.4	518.1	520.1	525.9	538.3	553.9	571.5	585.9
57.5°	509.8	491.3	477.0	470.3	470.9	472.7	482.3	497.1	513.7	532.5	551.0
60°	471.2	454.4	442.6	437.4	438.1	442.0	453.7	467.4	488.2	506.5	525.9
62.5°	434.8	420.0	408.8	404.1	403.2	411.8	423.0	437.2	458.0	478.3	499.4
65°	376.3	364.5	355.4	352.8	354.7	361.3	375.6	394.4	412.1	433.5	455.7
67.5°	318.9	309.3	303.0	304.3	306.6	316.3	328.2	344.5	364.4	386.7	408.5
70°	282.5	273.4	268.2	268.8	272.7	284.5	294.9	311.1	332.6	355.4	373.7
72.5°	245.0	239.0	234.3	237.1	241.0	249.1	262.0	278.3	297.3	318.5	337.7
75°	188.1	188.1	185.5	187.4	193.3	201.1	210.9	227.8	246.7	263.7	279.2
77.5°	139.6	138.1	139.8	142.2	145.5	154.8	166.0	178.1	192.3	209.2	222.1
80°	106.7	107.4	110.6	114.5	115.9	123.0	134.8	145.8	156.9	171.2	183.6
82.5°	80.2	80.9	82.5	87.5	88.8	96.4	104.0	115.1	125.1	134.8	145.0
85°	43.6	43.6	46.9	48.8	52.1	57.3	61.8	68.3	77.5	84.0	93.8
87.5°	19.8	20.3	22.8	24.3	26.3	29.4	30.7	36.8	39.2	42.2	47.0
90°	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3	32.0	33.6	34.7
92.5°	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4	31.0	32.6	33.5
95°	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3	32.0	33.6	34.6
97.5°	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8	32.9	33.1	33.3
100°	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8	40.2	35.5	33.3
102.5°	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5	110.3	60.3	35.2
105°	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5	391.0	393.5	389.7
107.5°	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7	481.9	483.1	484.2
110°	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3	543.9	544.4	545.1



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0	603.8	603.7	604.2
115°	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6	695.0	695.6	695.9
117.5°	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7	785.5	785.5	785.4
120°	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0	842.6	843.2	843.2
122.5°	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7	898.1	898.4	898.2
125°	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4	976.2	977.1	977.6
127.5°	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6	1052.5	1052.3	1052.1
130°	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8	1100.0	1100.2	1100.4
132.5°	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0	1146.2	1146.5	1146.6
135°	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7	1210.2	1210.8	1211.4
137.5°	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8	1271.4	1272.0	1272.2
140°	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6	1309.5	1310.3	1310.8
142.5°	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6	1344.2	1344.8	1345.1
145°	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6	1393.8	1394.1	1394.6
147.5°	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5	1437.7	1437.9	1438.2
150°	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6	1465.6	1465.6	1465.7
152.5°	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0	1490.4	1490.9	1491.0
155°	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1	1524.2	1525.3	1525.4
157.5°	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4
160°	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0
162.5°	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5	1586.1	1587.7	1587.6
165°	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2	1607.4	1609.6	1609.4
167.5°	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4	1622.8	1625.2	1625.1
170°	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8	1632.0	1634.2	1633.9
172.5°	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7	1637.9	1640.1	1639.6
175°	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6	1645.1	1647.6	1647.1
177.5°	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4	1647.1	1648.9	1648.5
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4
2.5°	1497.5	1496.4	1492.7	1492.2	1492.7	1496.4	1497.5	1498.4	1500.1	1505.2	1499.0
5°	1383.2	1380.0	1378.0	1385.2	1378.0	1380.0	1383.2	1387.2	1393.7	1394.3	1400.8
7.5°	1297.2	1294.6	1288.9	1287.0	1288.9	1294.6	1297.2	1299.5	1306.0	1311.7	1321.3
10°	1242.0	1239.4	1234.2	1232.9	1234.2	1239.4	1242.0	1248.5	1255.0	1262.2	1268.7
12.5°	1188.9	1183.7	1182.7	1184.0	1182.7	1183.7	1188.9	1197.5	1214.4	1214.3	1215.6
15°	1118.3	1115.7	1108.6	1110.5	1108.6	1115.7	1118.3	1126.8	1134.6	1144.4	1154.1
17.5°	1048.8	1045.7	1037.0	1044.6	1037.0	1045.7	1048.8	1053.4	1063.4	1077.2	1091.9
20°	1005.0	999.9	995.3	994.7	995.3	999.9	1005.0	1009.6	1020.7	1032.4	1043.5
22.5°	963.4	958.7	958.3	954.1	958.3	958.7	963.4	970.5	981.6	988.1	998.7
25°	911.3	906.8	905.5	902.2	905.5	906.8	911.3	916.6	923.7	928.9	940.6
27.5°	871.4	869.1	866.8	867.8	866.8	869.1	871.4	872.0	875.2	882.2	888.9
30°	846.9	846.2	844.9	844.9	844.9	846.2	846.9	844.9	848.2	851.4	856.6
32.5°	826.6	826.5	827.2	827.2	827.2	826.5	826.6	823.6	824.8	825.9	828.5
35°	798.1	800.0	801.3	799.3	801.3	800.0	798.1	795.5	793.5	789.0	790.3
37.5°	772.3	774.2	776.1	778.3	776.1	774.2	772.3	767.0	762.2	758.2	753.5
40°	752.5	757.1	758.3	761.6	758.3	757.1	752.5	746.7	741.4	736.9	731.6
42.5°	733.8	738.8	742.2	742.8	742.2	738.8	733.8	727.9	720.1	714.4	707.2
45°	705.0	710.2	714.8	714.8	714.8	710.2	705.0	695.2	686.7	678.2	671.2
47.5°	675.1	682.7	687.3	688.4	687.3	682.7	675.1	665.1	653.3	642.9	632.6
50°	654.8	664.0	668.5	671.8	668.5	664.0	654.8	643.8	631.4	618.4	606.0
52.5°	635.0	644.2	650.3	652.0	650.3	644.2	635.0	621.4	606.4	592.4	581.6
55°	600.8	613.8	621.0	623.6	621.0	613.8	600.8	585.9	571.5	553.9	538.3
57.5°	568.5	580.5	588.8	590.8	588.8	580.5	568.5	551.0	532.5	513.7	497.1
60°	543.6	556.5	567.0	568.9	567.0	556.5	543.6	525.9	506.5	488.2	467.4
62.5°	518.0	531.6	541.0	546.0	541.0	531.6	518.0	499.4	478.3	458.0	437.2
65°	473.9	487.5	496.7	498.6	496.7	487.5	473.9	455.7	433.5	412.1	394.4
67.5°	425.7	439.4	445.4	449.1	445.4	439.4	425.7	408.5	386.7	364.4	344.5
70°	391.8	402.9	409.4	412.7	409.4	402.9	391.8	373.7	355.4	332.6	311.1
72.5°	353.4	364.9	372.5	373.1	372.5	364.9	353.4	337.7	318.5	297.3	278.3
75°	294.2	304.7	308.5	308.5	308.5	304.7	294.2	279.2	263.7	246.7	227.8
77.5°	232.9	238.2	243.2	244.3	243.2	238.2	232.9	222.1	209.2	192.3	178.1
80°	193.3	196.6	200.5	200.5	200.5	196.6	193.3	183.6	171.2	156.9	145.8
82.5°	152.7	155.5	159.4	158.8	159.4	155.5	152.7	145.0	134.8	125.1	115.1
85°	92.5	98.3	97.7	96.4	97.7	98.3	92.5	93.8	84.0	77.5	68.3
87.5°	48.7	49.3	51.0	52.2	51.0	49.3	48.7	47.0	42.2	39.2	36.8
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.6	32.0	30.3
92.5°	33.6	33.8	33.8	33.9	33.8	33.8	33.6	33.5	32.6	31.0	29.4
95°	34.8	35.1	35.4	35.6	35.4	35.1	34.8	34.6	33.6	32.0	30.3
97.5°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	33.1	32.9	32.8
100°	33.6	33.9	34.2	34.4	34.2	33.9	33.6	33.3	35.5	40.2	44.8
102.5°	35.2	35.3	35.4	35.4	35.4	35.3	35.2	35.2	60.3	110.3	160.5
105°	379.9	370.1	360.3	350.4	360.3	370.1	379.9	389.7	393.5	391.0	388.5
107.5°	485.3	486.2	487.3	488.4	487.3	486.2	485.3	484.2	483.1	481.9	480.7
110°	545.9	546.7	547.6	548.4	547.6	546.7	545.9	545.1	544.4	543.9	543.3



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	605.3	606.3	607.3	608.4	607.3	606.3	605.3	604.2	603.7	603.8	604.0
115°	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.9	695.6	695.0	694.6
117.5°	785.2	785.1	785.1	784.9	785.1	785.1	785.2	785.4	785.5	785.5	785.7
120°	842.6	842.0	841.6	841.0	841.6	842.0	842.6	843.2	843.2	842.6	842.0
122.5°	897.7	897.2	896.6	896.1	896.6	897.2	897.7	898.2	898.4	898.1	897.7
125°	977.9	978.1	978.4	978.7	978.4	978.1	977.9	977.6	977.1	976.2	975.4
127.5°	1051.9	1051.7	1051.4	1051.2	1051.4	1051.7	1051.9	1052.1	1052.3	1052.5	1052.6
130°	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.4	1100.2	1100.0	1099.8
132.5°	1146.3	1146.1	1145.9	1145.7	1145.9	1146.1	1146.3	1146.6	1146.5	1146.2	1146.0
135°	1211.9	1212.4	1213.0	1213.5	1213.0	1212.4	1211.9	1211.4	1210.8	1210.2	1209.7
137.5°	1272.0	1271.9	1271.7	1271.5	1271.7	1271.9	1272.0	1272.2	1272.0	1271.4	1270.8
140°	1311.1	1311.3	1311.6	1311.9	1311.6	1311.3	1311.1	1310.8	1310.3	1309.5	1308.6
142.5°	1345.2	1345.2	1345.2	1345.3	1345.2	1345.2	1345.2	1345.1	1344.8	1344.2	1343.6
145°	1395.1	1395.6	1396.2	1396.7	1396.2	1395.6	1395.1	1394.6	1394.1	1393.8	1393.6
147.5°	1438.4	1438.7	1439.0	1439.2	1439.0	1438.7	1438.4	1438.2	1437.9	1437.7	1437.5
150°	1466.0	1466.2	1466.6	1466.8	1466.6	1466.2	1466.0	1465.7	1465.6	1465.6	1465.6
152.5°	1490.9	1490.7	1490.5	1490.4	1490.5	1490.7	1490.9	1491.0	1490.9	1490.4	1490.0
155°	1524.6	1523.8	1523.0	1522.2	1523.0	1523.8	1524.6	1525.4	1525.3	1524.2	1523.1
157.5°	1553.0	1551.5	1550.1	1548.7	1550.1	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5
160°	1571.3	1569.7	1568.1	1566.4	1568.1	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7
162.5°	1585.8	1583.9	1582.0	1580.1	1582.0	1583.9	1585.8	1587.6	1587.7	1586.1	1584.5
165°	1607.0	1604.5	1602.1	1599.6	1602.1	1604.5	1607.0	1609.4	1609.6	1607.4	1605.2
167.5°	1622.3	1619.6	1616.8	1614.1	1616.8	1619.6	1622.3	1625.1	1625.2	1622.8	1620.4
170°	1631.2	1628.4	1625.7	1622.9	1625.7	1628.4	1631.2	1633.9	1634.2	1632.0	1629.8
172.5°	1636.7	1633.8	1630.8	1627.8	1630.8	1633.8	1636.7	1639.6	1640.1	1637.9	1635.7
175°	1643.8	1640.5	1637.3	1634.0	1637.3	1640.5	1643.8	1647.1	1647.6	1645.1	1642.6
177.5°	1645.8	1643.2	1640.5	1637.9	1640.5	1643.2	1645.8	1648.5	1648.9	1647.1	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4
2.5°	1502.1	1504.2	1512.5	1520.4	1529.7	1536.5	1541.2	1546.4	1557.3	1566.2	1574.5
5°	1407.4	1410.6	1427.5	1439.2	1459.4	1477.0	1490.7	1505.6	1523.2	1547.3	1569.5
7.5°	1323.9	1336.0	1354.5	1373.5	1394.1	1417.1	1437.1	1459.7	1490.0	1523.1	1557.2
10°	1276.5	1290.2	1309.7	1331.9	1351.4	1378.0	1402.8	1429.5	1464.0	1504.3	1544.7
12.5°	1229.1	1251.6	1266.5	1292.7	1313.9	1335.9	1362.2	1397.2	1437.5	1479.8	1528.5
15°	1169.7	1182.1	1210.7	1225.1	1255.0	1288.9	1314.9	1350.1	1389.1	1445.1	1499.7
17.5°	1101.3	1117.5	1140.4	1167.7	1202.0	1228.5	1260.9	1297.1	1346.3	1401.9	1470.4
20°	1056.5	1070.2	1098.1	1128.0	1164.6	1192.5	1227.0	1262.2	1313.0	1372.2	1443.8
22.5°	1016.4	1029.6	1059.1	1087.0	1122.3	1156.6	1192.6	1233.5	1282.2	1344.6	1417.7
25°	954.3	971.8	997.9	1026.5	1060.4	1099.4	1138.5	1174.9	1227.0	1292.7	1370.9
27.5°	899.2	913.3	932.1	964.7	1003.1	1040.9	1079.6	1125.5	1175.5	1245.0	1326.1
30°	863.8	876.9	895.7	925.6	961.5	1001.8	1042.2	1086.4	1138.5	1207.5	1290.2
32.5°	835.7	845.5	862.3	889.2	921.9	964.3	1004.1	1049.9	1104.6	1172.6	1253.2
35°	794.2	802.6	809.1	834.5	863.8	902.9	943.2	992.1	1044.8	1109.2	1189.9
37.5°	753.4	756.3	765.8	782.4	810.8	846.8	884.3	932.3	986.3	1051.8	1124.5
40°	728.4	729.7	735.6	751.2	775.9	809.8	846.2	893.7	945.2	1007.0	1079.3
42.5°	703.9	703.1	708.5	719.4	742.6	773.3	809.3	852.6	904.0	961.2	1029.2
45°	665.3	665.3	664.0	673.1	691.9	721.9	751.9	793.5	836.5	892.4	949.7
47.5°	624.9	621.3	622.4	627.1	643.0	667.6	697.8	731.9	769.8	817.2	867.5
50°	598.8	593.7	591.7	596.9	611.2	632.8	661.4	691.3	727.1	768.7	811.7
52.5°	570.2	565.0	561.5	565.2	578.5	598.3	624.4	650.7	682.8	716.7	753.9
55°	525.9	520.1	518.1	519.4	529.2	544.9	567.0	591.1	615.1	643.1	669.2
57.5°	482.3	472.7	470.9	470.3	477.0	491.3	509.8	530.7	548.2	565.2	592.9
60°	453.7	442.0	438.1	437.4	442.6	454.4	471.2	492.1	504.5	516.2	540.3
62.5°	423.0	411.8	403.2	404.1	408.8	420.0	434.8	450.0	458.1	470.9	487.1
65°	375.6	361.3	354.7	352.8	355.4	364.5	376.3	386.0	395.1	400.3	416.0
67.5°	328.2	316.3	306.6	304.3	303.0	309.3	318.9	324.8	331.3	335.9	345.1
70°	294.9	284.5	272.7	268.8	268.2	273.4	282.5	283.2	292.3	294.2	304.0
72.5°	262.0	249.1	241.0	237.1	234.3	239.0	245.0	246.7	251.7	255.2	260.2
75°	210.9	201.1	193.3	187.4	185.5	188.1	188.1	191.4	194.6	196.6	202.4
77.5°	166.0	154.8	145.5	142.2	139.8	138.1	139.6	141.5	140.0	143.3	144.6
80°	134.8	123.0	115.9	114.5	110.6	107.4	106.7	108.7	106.1	107.4	111.3
82.5°	104.0	96.4	88.8	87.5	82.5	80.9	80.2	79.0	79.0	78.8	79.6
85°	61.8	57.3	52.1	48.8	46.9	43.6	43.6	42.3	41.0	39.7	40.4
87.5°	30.7	29.4	26.3	24.3	22.8	20.3	19.8	17.6	16.6	15.4	14.3
90°	28.7	27.1	24.9	22.7	20.5	18.3	15.7	12.7	9.7	6.7	3.7
92.5°	27.7	26.1	23.9	21.7	19.5	17.3	16.1	16.0	15.8	15.7	15.5
95°	28.7	27.1	26.7	26.5	26.3	25.9	30.5	39.8	49.1	58.3	67.6
97.5°	32.6	32.4	62.9	93.4	123.9	154.4	166.8	161.0	155.2	149.4	143.6
100°	49.5	54.1	91.8	129.5	167.2	204.9	221.3	216.4	211.5	206.6	201.6
102.5°	210.5	260.7	265.5	270.5	275.4	280.3	281.0	277.4	273.8	270.2	266.5
105°	386.0	383.6	382.2	380.9	379.5	378.1	376.7	375.0	373.3	371.7	370.1
107.5°	479.5	478.3	476.4	474.6	472.7	470.8	469.5	468.7	467.9	467.1	466.2
110°	542.7	542.2	540.5	538.9	537.3	535.7	534.4	533.6	532.8	532.0	531.2



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	604.1	604.2	603.4	602.7	601.9	601.1	600.0	598.5	597.0	595.6	594.1
115°	694.0	693.4	693.7	694.0	694.2	694.6	694.2	693.4	692.6	691.8	691.0
117.5°	785.8	785.9	785.3	784.7	784.1	783.5	782.7	781.5	780.5	779.3	778.3
120°	841.6	841.0	841.2	841.6	841.8	842.0	841.6	840.6	839.5	838.4	837.3
122.5°	897.4	897.1	896.7	896.3	895.9	895.5	895.0	894.3	893.6	893.0	892.3
125°	974.6	973.8	974.3	974.9	975.4	975.9	975.7	974.6	973.5	972.4	971.3
127.5°	1052.8	1053.0	1051.7	1050.4	1049.2	1047.9	1047.2	1046.8	1046.6	1046.4	1046.0
130°	1099.4	1099.2	1098.4	1097.6	1096.7	1095.9	1095.4	1095.1	1094.8	1094.5	1094.3
132.5°	1145.7	1145.4	1144.4	1143.3	1142.3	1141.3	1140.5	1140.0	1139.5	1139.0	1138.5
135°	1209.2	1208.6	1207.5	1206.4	1205.3	1204.2	1203.8	1204.1	1204.4	1204.6	1204.9
137.5°	1270.2	1269.6	1268.4	1267.2	1266.0	1264.8	1264.1	1264.0	1263.9	1263.8	1263.7
140°	1307.8	1306.9	1306.4	1305.9	1305.3	1304.8	1304.2	1303.7	1303.2	1302.6	1302.0
142.5°	1343.0	1342.4	1342.1	1341.7	1341.4	1341.1	1340.4	1339.5	1338.5	1337.4	1336.4
145°	1393.3	1393.0	1393.0	1393.0	1393.0	1393.0	1392.6	1391.8	1391.0	1390.2	1389.4
147.5°	1437.3	1437.0	1437.3	1437.6	1437.9	1438.1	1437.5	1436.0	1434.4	1432.9	1431.4
150°	1465.6	1465.6	1465.8	1466.2	1466.4	1466.6	1466.2	1465.2	1464.0	1463.0	1461.9
152.5°	1489.6	1489.1	1489.6	1490.1	1490.6	1491.2	1490.9	1490.0	1489.2	1488.3	1487.4
155°	1522.0	1520.9	1521.8	1522.6	1523.4	1524.2	1524.4	1524.2	1523.9	1523.6	1523.4
157.5°	1550.1	1548.7	1549.6	1550.5	1551.4	1552.4	1553.0	1553.1	1553.3	1553.5	1553.6
160°	1568.1	1566.4	1566.7	1566.9	1567.2	1567.5	1568.1	1568.9	1569.7	1570.5	1571.3
162.5°	1582.7	1581.1	1581.4	1581.7	1581.9	1582.3	1582.9	1584.0	1584.9	1586.0	1587.1
165°	1603.0	1600.8	1600.8	1600.8	1600.8	1600.8	1601.5	1602.9	1604.3	1605.6	1607.0
167.5°	1618.0	1615.6	1615.8	1615.9	1616.1	1616.2	1617.0	1618.5	1619.8	1621.3	1622.7
170°	1627.6	1625.4	1625.1	1624.9	1624.6	1624.3	1625.0	1626.6	1628.2	1629.9	1631.6
172.5°	1633.5	1631.3	1631.0	1630.8	1630.5	1630.2	1630.9	1632.6	1634.2	1635.8	1637.4
175°	1640.1	1637.7	1637.4	1637.1	1636.9	1636.6	1637.3	1638.9	1640.5	1642.2	1643.8
177.5°	1643.6	1641.8	1641.4	1641.0	1640.5	1640.1	1640.7	1642.2	1643.7	1645.3	1646.8
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4
2.5°	1581.8	1587.0	1593.7	1605.2	1609.4	1614.6	1621.9	1621.4	1623.4	1631.3	1648.0
5°	1587.6	1607.9	1627.3	1650.8	1675.5	1691.8	1713.9	1727.6	1741.3	1758.8	1788.8
7.5°	1590.0	1622.0	1657.8	1699.0	1735.5	1777.8	1810.7	1841.7	1869.6	1906.7	1942.5
10°	1586.3	1629.3	1675.5	1727.6	1782.9	1829.8	1872.1	1920.3	1961.3	2006.2	2046.6
12.5°	1579.6	1631.4	1693.2	1751.6	1816.2	1885.5	1938.3	1987.0	2041.5	2093.2	2155.4
15°	1564.2	1635.2	1707.4	1784.2	1870.8	1950.8	2027.1	2090.2	2148.8	2226.3	2307.6
17.5°	1544.7	1621.2	1712.4	1805.3	1895.8	1987.4	2081.6	2176.5	2250.5	2346.7	2410.4
20°	1526.5	1615.0	1708.7	1819.4	1909.8	2023.8	2117.5	2209.3	2310.9	2406.5	2482.7
22.5°	1501.0	1597.8	1697.3	1807.4	1926.6	2040.4	2148.8	2248.4	2349.9	2454.0	2546.3
25°	1468.5	1556.4	1674.2	1799.2	1917.7	2041.3	2165.7	2290.7	2400.0	2510.1	2596.0
27.5°	1413.3	1524.3	1634.0	1763.0	1894.7	2034.6	2167.6	2298.3	2413.0	2503.4	2556.6
30°	1385.2	1481.6	1600.7	1730.2	1872.7	2023.2	2161.8	2290.0	2396.8	2469.1	2490.5
32.5°	1343.5	1443.0	1559.5	1693.8	1844.6	1999.2	2143.6	2264.5	2353.5	2391.4	2365.5
35°	1281.7	1371.6	1489.4	1626.7	1783.5	1948.2	2090.8	2193.0	2238.6	2202.8	2113.6
37.5°	1207.5	1296.6	1414.9	1549.8	1712.1	1879.5	2008.4	2081.9	2066.9	1977.8	1844.9
40°	1155.4	1238.8	1351.4	1497.1	1655.4	1823.3	1936.6	1976.3	1934.6	1807.0	1665.7
42.5°	1097.6	1178.8	1292.0	1432.6	1600.2	1755.1	1853.7	1857.0	1787.2	1634.7	1492.9
45°	1009.6	1087.0	1193.8	1340.3	1495.3	1641.0	1706.1	1674.2	1545.3	1398.2	1255.6
47.5°	922.8	989.9	1095.1	1234.2	1381.3	1504.1	1536.4	1479.0	1341.6	1198.8	1066.7
50°	859.2	926.9	1025.9	1158.7	1300.6	1406.7	1422.3	1346.1	1211.4	1067.6	964.0
52.5°	798.3	865.5	960.8	1083.7	1213.7	1309.3	1309.9	1221.7	1087.4	959.2	863.0
55°	708.9	769.4	855.3	965.3	1081.2	1156.1	1137.8	1046.7	930.2	818.9	734.9
57.5°	622.7	675.4	754.6	846.4	948.4	1010.2	979.9	892.2	788.1	693.7	630.1
60°	567.0	617.1	684.8	771.4	857.3	905.5	876.9	797.4	701.7	625.6	570.2
62.5°	512.8	555.1	620.2	695.4	775.0	810.7	785.1	706.8	624.1	555.2	510.4
65°	436.1	470.7	522.7	587.2	645.1	675.7	654.2	581.3	518.1	468.7	432.8
67.5°	364.5	391.5	430.9	482.6	531.8	548.4	528.8	478.1	424.5	385.0	359.7
70°	315.0	340.5	373.7	413.4	456.3	473.9	454.4	414.0	370.4	333.9	309.2
72.5°	271.8	291.5	319.5	353.4	387.0	404.6	391.3	352.5	315.7	288.6	267.5
75°	207.0	224.0	243.4	267.5	293.6	305.3	293.6	266.8	241.5	221.4	206.4
77.5°	150.5	159.6	174.7	192.7	209.0	217.9	207.8	189.7	174.2	160.4	153.0
80°	114.5	121.1	131.5	145.8	156.9	165.3	158.8	143.8	131.5	122.4	119.1
82.5°	83.3	87.7	94.5	105.2	112.6	116.9	114.1	103.2	98.2	90.1	86.8
85°	41.0	43.6	48.2	51.4	58.0	58.6	59.3	54.7	50.1	48.2	45.6
87.5°	15.4	16.6	18.7	20.9	23.5	24.4	24.3	24.8	23.2	22.9	21.2
90°	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7	30.3
92.5°	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7	29.4
95°	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7	30.3
97.5°	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6	32.8
100°	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5	44.8
102.5°	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5	160.5
105°	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0	388.5
107.5°	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5	480.7
110°	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7	543.3



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1	604.0
115°	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0	694.6
117.5°	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8	785.7
120°	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6	842.0
122.5°	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4	897.7
125°	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6	975.4
127.5°	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8	1052.6
130°	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4	1099.8
132.5°	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7	1146.0
135°	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2	1209.7
137.5°	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2	1270.8
140°	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8	1308.6
142.5°	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0	1343.6
145°	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3	1393.6
147.5°	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3	1437.5
150°	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6	1465.6
152.5°	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6	1490.0
155°	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0	1523.1
157.5°	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1	1551.5
160°	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1	1569.7
162.5°	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7	1584.5
165°	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0	1605.2
167.5°	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0	1620.4
170°	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6	1629.8
172.5°	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5	1635.7
175°	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1	1642.6
177.5°	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6	1645.4
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4	1571.4
2.5°	1656.3	1657.3	1662.0	1665.7	1666.7	1671.9	1672.4
5°	1801.8	1812.9	1834.3	1836.3	1839.6	1856.5	1843.5
7.5°	1972.4	2000.5	2019.3	2035.8	2041.8	2049.2	2047.6
10°	2081.7	2123.4	2144.2	2177.4	2178.7	2187.2	2182.0
12.5°	2191.6	2240.0	2278.0	2284.1	2312.0	2316.3	2323.6
15°	2347.3	2398.7	2451.4	2470.4	2508.8	2517.9	2532.2
17.5°	2493.7	2546.3	2583.2	2632.0	2647.8	2668.9	2654.5
20°	2573.8	2631.1	2678.0	2716.4	2732.6	2744.4	2743.1
22.5°	2622.2	2680.1	2718.0	2747.2	2762.3	2767.3	2767.0
25°	2652.6	2685.8	2697.5	2708.6	2691.6	2685.8	2688.4
27.5°	2568.3	2559.6	2529.1	2488.9	2447.3	2414.2	2396.2
30°	2452.1	2401.3	2355.2	2274.4	2232.8	2208.0	2185.9
32.5°	2287.6	2207.1	2118.1	2044.2	1996.8	1960.1	1954.7
35°	2005.6	1884.5	1775.8	1685.3	1638.4	1598.7	1589.6
37.5°	1705.1	1579.3	1481.4	1401.7	1351.4	1323.4	1297.2
40°	1505.6	1397.6	1301.2	1233.5	1195.1	1174.9	1158.7
42.5°	1352.0	1253.4	1157.5	1106.0	1071.2	1058.8	1049.3
45°	1139.8	1048.0	981.6	942.6	922.3	901.6	891.8
47.5°	969.9	895.2	851.4	818.2	796.6	784.2	778.0
50°	873.6	812.4	773.3	748.0	728.4	718.6	713.5
52.5°	788.1	737.9	705.1	684.9	671.6	664.5	662.4
55°	678.9	640.5	619.7	602.1	592.4	585.9	583.3
57.5°	590.1	560.6	543.6	529.2	525.5	520.0	518.1
60°	531.8	509.1	494.7	484.9	481.7	475.2	476.5
62.5°	480.3	461.6	449.4	443.8	439.5	434.1	435.9
65°	406.2	392.5	386.0	380.8	375.6	372.3	375.0
67.5°	340.8	331.5	322.6	319.6	317.0	316.5	313.7
70°	298.2	290.3	282.5	280.5	280.5	277.9	277.3
72.5°	257.0	251.3	246.1	244.6	242.6	243.6	240.8
75°	198.5	194.0	192.0	190.0	189.4	189.4	187.4
77.5°	146.8	143.3	140.2	140.2	137.9	137.0	136.7
80°	111.3	110.0	107.4	107.4	106.1	106.7	105.4
82.5°	83.7	81.9	81.4	80.3	78.5	78.6	77.4
85°	44.9	43.0	42.3	40.4	39.1	40.4	39.1
87.5°	22.0	21.9	21.5	20.6	20.1	20.3	18.8
90°	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P332859-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)