

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333072-935

Luminaire Tested: **S124RDIW-S795D1560U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333072-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1560U935-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7535.2 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	15				
8	53	41	34	28	48	38	31	27	32	26	23	26	22	19	20	17	16	13				
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9175	9175	9175	9175
5°	10643	9203	8135	9203
10°	12591	9163	7260	9163
15°	14543	9078	6238	9078
20°	16192	8961	5642	8961
25°	16715	8847	5238	8847
30°	14632	8708	4994	8708
35°	11391	8502	4847	8502
40°	8541	8266	4769	8266
45°	6744	7889	4727	7889
50°	5693	7454	4589	7454
55°	4963	6973	4345	6973
60°	4466	6476	3846	6476
65°	3935	5939	3307	5939
70°	3545	5384	2984	5384
75°	2969	4769	2542	4769
80°	2515	4068	2385	4068
85°	2121	3186	2121	3186



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	1.5
10°-20°	332.2	4.4
20°-30°	519.5	6.9
30°-40°	577.6	7.7
40°-50°	512.4	6.8
50°-60°	399.3	5.3
60°-70°	261.4	3.5
70°-80°	128.6	1.7
80°-90°	36.7	0.5
90°-100°	110.7	1.5
100°-110°	328.0	4.4
110°-120°	556.7	7.4
120°-130°	734.0	9.7
130°-140°	824.4	10.9
140°-150°	810.1	10.8
150°-160°	681.3	9.0
160°-170°	453.3	6.0
170°-180°	158.7	2.1
0°-30°	961.8	12.8
0°-40°	1539.4	20.4
0°-60°	2451.2	32.5
0°-90°	2877.9	38.2
90°-120°	995.4	13.2
90°-150°	3363.9	44.6
90°-180°	4657.0	61.8
0°-180°	7535.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1136	1136	1136	1136	1136	
5°	1313	1136	1004	1136	1313	133
15°	1740	1086	746	1086	1740	495
25°	1876	993	588	993	1876	832
35°	1156	863	492	863	1156	724
45°	591	691	414	691	591	468
55°	353	495	309	495	353	321
65°	206	311	173	311	206	207
75°	95	153	82	153	95	105
85°	23	34	23	34	23	27
90°	39	4	39	4	39	21
95°	102	78	102	78	102	107
105°	317	302	317	302	317	334
115°	561	566	561	566	561	554
125°	818	824	818	824	818	730
135°	1064	1063	1064	1063	1064	822
145°	1293	1292	1293	1292	1293	809
155°	1479	1480	1479	1480	1479	681
165°	1607	1611	1607	1611	1607	453
175°	1668	1676	1668	1676	1668	158
180°	1679	1679	1679	1679	1679	



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1198.8	1202.1	1198.8	1198.4	1194.8	1193.7	1192.2	1187.5	1178.6	1173.5	1174.7
5°	1313.3	1324.7	1318.4	1317.4	1307.3	1297.3	1290.8	1276.2	1260.6	1250.1	1241.4
7.5°	1445.7	1452.3	1448.3	1441.8	1425.6	1416.3	1401.4	1382.2	1354.3	1332.9	1313.4
10°	1535.9	1541.4	1539.5	1527.6	1515.7	1491.4	1477.6	1450.7	1415.4	1387.5	1361.4
12.5°	1624.4	1630.4	1614.2	1614.8	1592.2	1573.1	1551.3	1517.3	1476.6	1440.6	1407.9
15°	1740.1	1732.8	1732.8	1723.5	1698.4	1671.8	1649.4	1613.7	1562.4	1519.3	1474.0
17.5°	1830.6	1833.1	1829.4	1807.8	1788.0	1760.5	1719.3	1677.7	1630.0	1572.3	1526.0
20°	1884.7	1884.7	1880.7	1866.0	1840.4	1811.0	1766.6	1721.3	1660.9	1602.7	1550.5
22.5°	1906.8	1908.2	1903.3	1891.3	1868.2	1839.6	1801.8	1755.8	1693.4	1628.0	1563.3
25°	1876.5	1885.2	1886.1	1882.9	1876.0	1858.6	1826.2	1779.0	1723.1	1652.2	1582.5
27.5°	1722.9	1733.8	1743.4	1759.3	1780.4	1791.3	1792.8	1768.8	1720.1	1651.7	1581.7
30°	1569.7	1578.9	1608.6	1647.5	1677.8	1705.3	1729.1	1735.5	1708.1	1646.7	1573.0
32.5°	1399.7	1412.2	1442.0	1483.8	1534.2	1580.7	1634.2	1661.5	1660.8	1623.9	1555.7
35°	1155.8	1164.9	1192.4	1236.4	1296.8	1366.0	1450.7	1516.6	1561.5	1558.2	1516.6
37.5°	932.1	942.5	970.3	1006.7	1065.3	1150.9	1232.9	1323.7	1406.7	1453.3	1439.4
40°	810.5	811.0	838.0	875.6	930.5	1005.1	1094.4	1195.2	1287.6	1363.2	1377.9
42.5°	714.5	714.6	732.5	772.9	812.5	882.8	968.0	1068.1	1176.3	1263.6	1302.4
45°	590.7	594.9	609.5	633.8	664.9	724.4	792.6	885.6	1006.9	1110.4	1175.0
47.5°	500.2	506.3	515.6	535.4	560.2	599.9	656.3	739.8	838.5	952.4	1044.2
50°	453.3	454.3	466.1	477.2	498.7	530.3	579.7	649.3	739.9	849.5	951.6
52.5°	413.0	412.8	420.0	433.9	451.4	476.0	516.0	579.4	659.8	757.9	863.2
55°	352.6	354.9	360.4	371.3	384.6	402.1	433.6	481.3	544.5	628.3	723.9
57.5°	306.6	307.8	312.1	316.8	329.0	341.6	365.3	398.4	451.7	520.3	609.5
60°	276.6	277.1	278.4	285.2	294.9	306.8	322.8	350.8	395.6	458.4	528.9
62.5°	247.3	248.1	250.2	255.2	262.7	270.9	287.7	310.1	347.2	400.9	464.4
65°	206.0	206.6	209.7	211.5	217.5	224.8	237.2	252.3	277.9	322.8	370.9
67.5°	172.2	172.2	172.4	174.9	178.9	183.8	191.2	203.3	222.7	250.2	292.6
70°	150.2	150.2	151.1	152.5	154.8	158.9	163.0	172.2	186.4	208.8	241.3
72.5°	129.7	130.0	131.0	131.2	132.4	135.8	138.9	144.7	155.2	172.2	198.5
75°	95.2	96.6	98.9	100.7	103.1	102.5	105.8	109.4	112.6	122.7	137.8
77.5°	70.9	70.2	70.4	72.0	72.2	72.8	75.0	77.8	80.2	85.0	90.4
80°	54.1	54.1	55.4	55.9	55.4	55.9	58.1	59.5	60.4	62.3	67.3
82.5°	40.8	41.6	41.2	41.6	41.8	42.3	44.3	44.5	45.5	46.1	48.3
85°	22.9	23.3	23.8	22.9	22.9	22.9	23.8	24.3	25.2	24.7	25.7
87.5°	15.8	15.3	15.6	15.5	15.8	15.2	15.2	15.6	14.5	14.5	14.0
90°	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0	30.3	28.6	26.3
92.5°	57.6	57.3	56.9	56.6	56.2	55.5	54.5	53.5	52.4	51.4	49.8
95°	102.5	102.5	102.5	102.5	102.5	102.1	101.3	100.4	99.5	98.7	96.7
97.5°	160.7	160.7	160.7	160.7	160.7	160.2	159.2	158.2	157.0	156.0	153.7
100°	201.2	201.2	201.2	201.2	201.2	201.0	200.4	199.8	199.2	198.6	196.0
102.5°	246.9	246.7	246.5	246.2	246.0	245.5	244.7	243.8	243.1	242.3	239.9
105°	316.8	315.9	315.0	314.2	313.3	312.5	311.6	310.7	309.9	309.0	307.8
107.5°	384.8	384.9	385.0	385.0	385.0	384.7	383.8	383.1	382.2	381.4	381.3
110°	433.6	432.7	431.9	431.0	430.2	430.0	430.6	431.2	431.7	432.3	432.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.5	483.3	483.1	482.9	482.8	482.8	482.8	482.9	483.1	483.2	483.7
115°	560.9	561.1	561.5	561.7	562.0	562.3	562.6	562.8	563.2	563.4	564.0
117.5°	634.6	635.2	635.8	636.3	636.9	637.7	638.7	639.6	640.6	641.6	642.0
120°	690.7	690.1	689.5	689.0	688.4	688.8	690.3	691.6	693.1	694.6	695.4
122.5°	737.4	738.5	739.5	740.5	741.6	742.6	743.6	744.5	745.5	746.5	746.9
125°	817.9	818.5	819.1	819.6	820.2	820.8	821.4	821.9	822.5	823.1	823.4
127.5°	892.4	892.9	893.4	893.8	894.2	894.8	895.4	896.0	896.5	897.1	897.6
130°	941.2	942.4	943.6	944.7	945.8	946.7	947.3	947.9	948.5	949.0	949.0
132.5°	993.2	993.6	994.1	994.5	995.0	995.5	996.1	996.7	997.3	997.8	998.1
135°	1064.5	1065.4	1066.3	1067.1	1068.0	1068.8	1069.4	1069.9	1070.5	1071.1	1071.1
137.5°	1139.6	1139.4	1139.3	1139.1	1138.9	1139.2	1140.0	1140.7	1141.4	1142.2	1141.8
140°	1185.3	1185.6	1185.9	1186.2	1186.5	1186.7	1187.1	1187.3	1187.6	1187.9	1187.9
142.5°	1231.0	1231.1	1231.1	1231.1	1231.2	1231.3	1231.3	1231.4	1231.5	1231.5	1231.7
145°	1293.0	1293.9	1294.8	1295.6	1296.5	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0
147.5°	1355.9	1356.2	1356.5	1356.8	1357.0	1357.3	1357.5	1357.8	1358.0	1358.2	1358.5
150°	1394.3	1394.6	1394.9	1395.2	1395.5	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1429.6	1430.4	1431.2	1431.8	1432.6	1432.6	1431.9	1431.2	1430.6	1429.9	1429.7
155°	1478.7	1479.9	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7	1479.0
157.5°	1522.6	1523.5	1524.6	1525.5	1526.5	1526.6	1525.7	1524.8	1524.0	1523.1	1523.2
160°	1547.5	1548.9	1550.4	1551.9	1553.2	1553.6	1552.7	1551.9	1551.0	1550.1	1550.4
162.5°	1573.5	1574.9	1576.4	1577.8	1579.2	1579.2	1577.6	1576.1	1574.5	1573.0	1573.2
165°	1607.2	1608.3	1609.6	1610.7	1611.9	1611.5	1609.8	1608.1	1606.4	1604.6	1605.2
167.5°	1631.3	1633.1	1635.0	1636.8	1638.6	1638.6	1636.8	1635.1	1633.4	1631.7	1631.6
170°	1644.9	1646.9	1648.9	1651.0	1652.9	1653.1	1651.4	1649.7	1647.9	1646.1	1645.9
172.5°	1656.3	1658.3	1660.4	1662.3	1664.4	1664.4	1662.4	1660.5	1658.5	1656.6	1656.5
175°	1668.3	1670.3	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3	1668.5
177.5°	1674.5	1676.4	1678.2	1680.0	1681.9	1682.0	1680.3	1678.8	1677.1	1675.5	1675.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1171.0	1165.9	1163.3	1157.4	1150.5	1146.8	1143.5	1138.8	1132.5	1125.9	1121.1
5°	1230.4	1219.4	1205.7	1189.2	1174.6	1160.4	1148.0	1135.7	1121.5	1106.7	1092.1
7.5°	1291.4	1269.8	1246.5	1219.4	1193.2	1169.2	1147.3	1126.2	1102.3	1081.1	1061.6
10°	1333.9	1304.6	1272.0	1237.8	1203.4	1173.6	1144.4	1117.8	1088.5	1062.4	1040.3
12.5°	1368.3	1333.9	1294.8	1252.0	1210.7	1174.7	1141.0	1106.4	1073.1	1044.7	1015.5
15°	1425.5	1378.3	1325.7	1274.4	1220.8	1171.8	1126.4	1086.2	1048.2	1008.3	980.4
17.5°	1464.7	1408.8	1344.8	1283.1	1219.9	1162.1	1109.8	1061.8	1018.0	977.2	944.0
20°	1488.2	1426.4	1355.4	1285.4	1214.4	1152.5	1096.2	1043.1	997.8	953.8	919.5
22.5°	1501.4	1433.0	1355.4	1282.0	1208.5	1141.6	1079.8	1024.4	975.1	931.1	893.1
25°	1505.6	1432.4	1353.1	1268.9	1188.3	1117.3	1053.2	993.2	938.2	894.3	854.0
27.5°	1499.8	1413.5	1332.3	1245.9	1162.7	1087.9	1020.6	957.6	902.6	855.4	814.1
30°	1491.0	1398.4	1311.5	1221.7	1137.5	1065.6	994.5	934.1	876.9	827.9	786.3
32.5°	1471.9	1380.2	1286.5	1194.6	1109.2	1035.2	967.9	907.1	850.9	800.8	756.6
35°	1434.2	1341.3	1239.6	1145.2	1061.4	984.5	921.4	862.7	809.2	755.5	708.9
37.5°	1384.5	1289.5	1188.4	1085.0	1001.2	928.6	870.6	815.5	763.3	714.4	662.6
40°	1337.6	1251.0	1146.6	1044.0	957.9	887.9	834.3	784.4	731.8	683.2	631.5
42.5°	1280.7	1207.0	1101.6	998.6	913.6	846.1	796.3	747.4	699.5	652.5	598.5
45°	1186.0	1130.1	1031.2	932.3	846.7	779.8	734.0	691.0	648.8	604.0	553.2
47.5°	1077.4	1039.6	954.2	852.9	773.7	713.5	669.3	634.1	598.5	553.6	509.0
50°	1001.9	977.7	895.2	802.7	727.2	671.8	626.5	593.5	563.7	520.6	480.8
52.5°	921.4	908.4	838.8	750.4	677.3	623.0	584.3	554.7	524.5	488.8	451.5
55°	798.6	805.5	746.4	669.9	601.2	555.4	520.2	495.4	469.8	439.6	410.8
57.5°	673.1	698.2	658.6	591.4	527.0	484.7	458.2	437.4	415.9	390.8	366.2
60°	598.1	619.1	596.7	537.6	481.3	441.9	417.2	401.1	379.6	356.7	337.9
62.5°	524.8	547.3	534.0	486.3	434.0	400.1	378.3	363.4	347.4	327.4	307.9
65°	432.7	447.4	441.0	408.0	370.9	342.1	321.9	310.9	296.3	281.6	264.2
67.5°	331.4	359.7	356.0	338.5	306.4	283.9	270.7	261.0	247.6	236.8	224.9
70°	272.4	298.6	298.1	283.9	266.5	245.5	236.3	228.1	216.1	205.6	196.0
72.5°	223.0	246.9	250.5	239.6	227.6	211.7	202.9	197.3	185.7	178.5	170.7
75°	156.2	173.6	178.1	178.1	172.6	164.4	156.6	152.9	144.7	138.3	133.7
77.5°	102.4	113.4	120.5	122.2	123.0	120.3	113.8	111.2	105.0	102.6	98.2
80°	72.3	79.6	87.9	90.7	93.0	92.0	89.3	87.5	81.5	79.2	77.4
82.5°	50.0	54.1	60.8	66.8	66.2	68.6	66.2	64.7	60.3	59.4	57.6
85°	26.1	26.5	27.5	31.6	33.9	34.8	35.3	34.4	33.0	33.0	29.8
87.5°	13.6	12.7	13.0	12.5	12.2	13.0	13.5	13.3	12.7	12.3	11.9
90°	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9	7.1	10.2	13.4
92.5°	48.2	46.6	44.9	42.4	38.7	35.0	31.4	27.8	31.4	35.0	38.7
95°	94.6	92.6	90.6	88.3	85.7	83.1	80.5	77.9	80.5	83.1	85.7
97.5°	151.3	149.0	146.6	144.4	142.3	140.2	138.1	136.0	138.1	140.2	142.3
100°	193.5	190.9	188.2	186.4	185.2	184.1	182.9	181.8	182.9	184.1	185.2
102.5°	237.5	235.1	232.8	231.4	230.9	230.5	230.0	229.5	230.0	230.5	230.9
105°	306.7	305.5	304.4	303.7	303.3	303.1	302.8	302.5	302.8	303.1	303.3
107.5°	381.1	380.9	380.7	380.5	380.1	379.8	379.4	379.1	379.4	379.8	380.1
110°	432.9	433.2	433.5	433.3	432.7	432.1	431.6	431.0	431.6	432.1	432.7





TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	484.2	484.7	485.3	485.5	485.3	485.3	485.2	485.0	485.2	485.3	485.3
115°	564.6	565.2	565.8	566.0	566.0	566.0	566.0	566.0	566.0	566.0	566.0
117.5°	642.4	642.8	643.3	643.3	643.1	642.8	642.6	642.4	642.6	642.8	643.1
120°	696.3	697.2	698.0	697.8	696.7	695.6	694.4	693.3	694.4	695.6	696.7
122.5°	747.3	747.7	748.1	748.0	747.6	747.2	746.7	746.2	746.7	747.2	747.6
125°	823.6	824.0	824.2	824.4	824.4	824.4	824.4	824.4	824.4	824.4	824.4
127.5°	898.0	898.5	899.0	898.7	897.9	897.0	896.1	895.3	896.1	897.0	897.9
130°	949.0	949.0	949.0	948.6	947.7	946.8	946.0	945.1	946.0	946.8	947.7
132.5°	998.3	998.5	998.8	998.6	997.9	997.3	996.7	996.0	996.7	997.3	997.9
135°	1071.1	1071.1	1071.1	1070.2	1068.5	1066.7	1065.0	1063.2	1065.0	1066.7	1068.5
137.5°	1141.3	1140.8	1140.4	1139.7	1138.9	1138.1	1137.3	1136.5	1137.3	1138.1	1138.9
140°	1187.9	1187.9	1187.9	1187.6	1187.1	1186.5	1185.9	1185.3	1185.9	1186.5	1187.1
142.5°	1232.0	1232.2	1232.4	1232.3	1231.7	1231.1	1230.5	1229.9	1230.5	1231.1	1231.7
145°	1297.7	1297.4	1297.1	1296.4	1295.2	1294.1	1292.9	1291.8	1292.9	1294.1	1295.2
147.5°	1358.7	1358.9	1359.2	1358.6	1357.2	1355.8	1354.4	1353.1	1354.4	1355.8	1357.2
150°	1395.6	1395.6	1395.6	1395.1	1393.9	1392.8	1391.5	1390.4	1391.5	1392.8	1393.9
152.5°	1429.4	1429.2	1429.0	1428.5	1427.8	1427.1	1426.4	1425.7	1426.4	1427.1	1427.8
155°	1479.3	1479.5	1479.9	1480.0	1480.0	1480.0	1480.0	1480.0	1480.0	1480.0	1480.0
157.5°	1523.2	1523.3	1523.4	1523.6	1524.1	1524.7	1525.2	1525.7	1525.2	1524.7	1524.1
160°	1550.7	1551.0	1551.3	1551.5	1551.9	1552.1	1552.4	1552.7	1552.4	1552.1	1551.9
162.5°	1573.6	1573.8	1574.1	1574.6	1575.4	1576.1	1576.9	1577.6	1576.9	1576.1	1575.4
165°	1605.8	1606.4	1607.0	1607.7	1608.5	1609.4	1610.2	1611.1	1610.2	1609.4	1608.5
167.5°	1631.5	1631.5	1631.4	1632.0	1633.2	1634.4	1635.6	1636.8	1635.6	1634.4	1633.2
170°	1645.6	1645.3	1645.0	1645.6	1647.0	1648.5	1649.9	1651.4	1649.9	1648.5	1647.0
172.5°	1656.5	1656.4	1656.3	1656.9	1658.1	1659.3	1660.5	1661.7	1660.5	1659.3	1658.1
175°	1668.8	1669.1	1669.4	1670.3	1671.7	1673.2	1674.6	1676.0	1674.6	1673.2	1671.7
177.5°	1675.5	1675.5	1675.5	1676.1	1677.2	1678.4	1679.6	1680.7	1679.6	1678.4	1677.2
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1116.0	1112.3	1107.6	1102.1	1095.5	1089.7	1087.1	1089.3	1090.4	1087.4	1087.1
5°	1082.0	1070.6	1061.4	1047.7	1036.7	1027.5	1021.1	1018.4	1019.3	1012.0	1010.1
7.5°	1043.9	1030.3	1015.3	999.0	983.8	970.3	963.3	959.4	951.7	948.3	942.7
10°	1019.3	1001.0	986.4	967.1	949.7	933.7	925.9	919.5	911.7	908.0	900.3
12.5°	994.0	972.8	956.7	936.7	918.9	899.6	892.2	880.3	868.1	860.4	850.4
15°	958.4	932.8	913.1	889.2	868.2	846.2	826.6	804.5	796.3	778.9	768.9
17.5°	916.7	890.7	866.3	834.4	801.9	774.6	753.6	732.5	720.0	708.9	703.7
20°	889.2	865.5	831.6	794.4	758.3	728.1	711.1	697.4	683.6	675.9	670.4
22.5°	863.2	832.8	793.5	753.5	717.3	693.6	679.2	665.1	654.0	646.6	639.2
25°	819.7	779.8	738.1	692.3	667.6	647.0	631.5	620.0	613.1	603.6	599.9
27.5°	774.9	726.6	680.6	649.9	624.1	605.3	591.7	583.1	574.4	568.3	563.5
30°	740.5	691.5	650.2	621.0	594.9	579.3	568.3	558.2	551.3	546.3	542.6
32.5°	706.4	657.4	622.8	591.2	570.7	555.4	543.7	536.2	530.8	524.3	522.1
35°	657.1	613.6	583.4	555.0	533.9	520.2	511.0	503.3	498.7	496.8	495.4
37.5°	609.8	574.1	541.7	518.3	499.6	488.8	477.9	474.2	471.0	467.7	469.2
40°	579.7	546.3	517.5	492.8	477.6	465.7	459.3	454.7	451.9	451.9	451.9
42.5°	553.7	521.0	492.9	470.7	455.6	445.6	438.4	434.5	433.6	433.3	435.5
45°	513.3	483.1	454.7	436.4	423.5	413.5	409.4	406.1	406.1	408.0	408.5
47.5°	473.3	445.0	422.2	401.7	389.9	383.7	380.0	378.4	378.6	380.5	382.5
50°	448.8	420.9	398.4	380.0	369.1	363.1	359.9	359.0	359.9	359.9	363.1
52.5°	422.0	397.0	375.0	359.6	347.1	341.5	339.8	338.5	339.1	340.5	341.9
55°	382.8	360.4	339.3	324.7	315.5	311.9	307.7	308.2	307.3	308.2	308.2
57.5°	343.5	323.4	303.8	292.1	284.1	278.8	274.3	275.6	274.2	274.1	273.3
60°	318.2	296.3	280.7	270.2	261.0	256.4	252.3	253.2	251.8	250.9	249.1
62.5°	290.8	272.4	257.6	247.5	240.1	234.8	230.7	229.8	226.6	223.4	219.5
65°	250.9	235.8	222.6	212.9	206.0	201.9	198.7	196.0	189.1	181.8	178.1
67.5°	212.2	201.3	188.9	180.8	175.2	169.8	163.7	159.0	152.6	148.5	146.3
70°	187.3	176.8	166.3	158.4	152.5	147.5	140.6	137.4	132.8	131.0	128.6
72.5°	163.5	153.7	143.9	136.8	130.5	126.6	121.1	118.0	116.0	115.2	113.0
75°	127.3	119.5	112.2	105.8	100.7	98.0	95.7	93.4	92.5	88.3	86.1
77.5°	92.9	87.7	83.2	78.6	75.0	73.2	68.8	66.1	64.6	62.7	62.2
80°	72.3	68.7	64.1	61.4	56.3	54.5	52.7	52.2	51.7	51.3	50.8
82.5°	54.4	50.7	46.1	44.5	43.1	42.0	40.9	40.5	40.0	40.3	40.2
85°	27.5	25.7	25.7	25.2	24.7	24.3	23.8	23.8	23.3	23.8	23.3
87.5°	12.5	12.7	13.1	12.8	13.7	14.1	14.1	14.5	15.2	14.8	15.0
90°	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0	33.8	35.5	36.7
92.5°	42.4	44.9	46.6	48.2	49.8	51.4	52.4	53.5	54.5	55.5	56.2
95°	88.3	90.6	92.6	94.6	96.7	98.7	99.5	100.4	101.3	102.1	102.5
97.5°	144.4	146.6	149.0	151.3	153.7	156.0	157.0	158.2	159.2	160.2	160.7
100°	186.4	188.2	190.9	193.5	196.0	198.6	199.2	199.8	200.4	201.0	201.2
102.5°	231.4	232.8	235.1	237.5	239.9	242.3	243.1	243.8	244.7	245.5	246.0
105°	303.7	304.4	305.5	306.7	307.8	309.0	309.9	310.7	311.6	312.5	313.3
107.5°	380.5	380.7	380.9	381.1	381.3	381.4	382.2	383.1	383.8	384.7	385.0
110°	433.3	433.5	433.2	432.9	432.6	432.3	431.7	431.2	430.6	430.0	430.2



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	485.5	485.3	484.7	484.2	483.7	483.2	483.1	482.9	482.8	482.8	482.8
115°	566.0	565.8	565.2	564.6	564.0	563.4	563.2	562.8	562.6	562.3	562.0
117.5°	643.3	643.3	642.8	642.4	642.0	641.6	640.6	639.6	638.7	637.7	636.9
120°	697.8	698.0	697.2	696.3	695.4	694.6	693.1	691.6	690.3	688.8	688.4
122.5°	748.0	748.1	747.7	747.3	746.9	746.5	745.5	744.5	743.6	742.6	741.6
125°	824.4	824.2	824.0	823.6	823.4	823.1	822.5	821.9	821.4	820.8	820.2
127.5°	898.7	899.0	898.5	898.0	897.6	897.1	896.5	896.0	895.4	894.8	894.2
130°	948.6	949.0	949.0	949.0	949.0	949.0	948.5	947.9	947.3	946.7	945.8
132.5°	998.6	998.8	998.5	998.3	998.1	997.8	997.3	996.7	996.1	995.5	995.0
135°	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5	1069.9	1069.4	1068.8	1068.0
137.5°	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4	1140.7	1140.0	1139.2	1138.9
140°	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6	1187.3	1187.1	1186.7	1186.5
142.5°	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5	1231.4	1231.3	1231.3	1231.2
145°	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0	1297.7	1297.4	1297.1	1296.5
147.5°	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0	1357.8	1357.5	1357.3	1357.0
150°	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.5
152.5°	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6	1431.2	1431.9	1432.6	1432.6
155°	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9	1481.0	1482.1	1483.3	1483.3
157.5°	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0	1524.8	1525.7	1526.6	1526.5
160°	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0	1551.9	1552.7	1553.6	1553.2
162.5°	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5	1576.1	1577.6	1579.2	1579.2
165°	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4	1608.1	1609.8	1611.5	1611.9
167.5°	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4	1635.1	1636.8	1638.6	1638.6
170°	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9	1649.7	1651.4	1653.1	1652.9
172.5°	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5	1660.5	1662.4	1664.4	1664.4
175°	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3	1672.3	1674.3	1676.4	1676.4
177.5°	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1	1678.8	1680.3	1682.0	1681.9
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1084.9	1085.6	1083.1	1082.3	1083.1	1085.6	1084.9	1087.1	1087.4	1090.4	1089.3
5°	1006.5	1005.6	1003.3	1003.8	1003.3	1005.6	1006.5	1010.1	1012.0	1019.3	1018.4
7.5°	939.4	935.9	936.9	933.2	936.9	935.9	939.4	942.7	948.3	951.7	959.4
10°	898.5	893.4	889.2	885.6	889.2	893.4	898.5	900.3	908.0	911.7	919.5
12.5°	842.4	838.1	832.5	833.6	832.5	838.1	842.4	850.4	860.4	868.1	880.3
15°	762.8	756.0	745.0	746.4	745.0	756.0	762.8	768.9	778.9	796.3	804.5
17.5°	695.6	695.7	690.6	691.8	690.6	695.7	695.6	703.7	708.9	720.0	732.5
20°	660.7	657.5	658.0	656.7	658.0	657.5	660.7	670.4	675.9	683.6	697.4
22.5°	636.6	632.7	629.5	626.6	629.5	632.7	636.6	639.2	646.6	654.0	665.1
25°	595.7	593.0	588.8	588.0	588.8	593.0	595.7	599.9	603.6	613.1	620.0
27.5°	559.8	559.3	557.7	555.5	557.7	559.3	559.8	563.5	568.3	574.4	583.1
30°	539.0	538.0	537.1	535.7	537.1	538.0	539.0	542.6	546.3	551.3	558.2
32.5°	520.3	519.7	518.8	518.9	518.8	519.7	520.3	522.1	524.3	530.8	536.2
35°	493.6	493.2	492.2	491.8	492.2	493.2	493.6	495.4	496.8	498.7	503.3
37.5°	468.7	469.9	469.3	469.2	469.3	469.9	468.7	469.2	467.7	471.0	474.2
40°	451.5	451.9	452.9	452.5	452.9	451.9	451.5	451.9	451.9	451.9	454.7
42.5°	437.2	437.3	438.6	437.0	438.6	437.3	437.2	435.5	433.3	433.6	434.5
45°	411.6	414.4	414.0	414.0	414.0	414.4	411.6	408.5	408.0	406.1	406.1
47.5°	383.7	386.1	386.8	386.7	386.8	386.1	383.7	382.5	380.5	378.6	378.4
50°	365.4	364.5	365.8	365.4	365.8	364.5	365.4	363.1	359.9	359.9	359.0
52.5°	343.1	343.3	343.2	342.7	343.2	343.3	343.1	341.9	340.5	339.1	338.5
55°	308.7	309.1	308.2	308.7	308.2	309.1	308.7	308.2	308.2	307.3	308.2
57.5°	271.3	269.1	270.0	268.9	270.0	269.1	271.3	273.3	274.1	274.2	275.6
60°	244.5	240.8	240.0	238.2	240.0	240.8	244.5	249.1	250.9	251.8	253.2
62.5°	214.5	211.9	208.8	210.3	208.8	211.9	214.5	219.5	223.4	226.6	229.8
65°	174.4	172.6	171.3	173.1	171.3	172.6	174.4	178.1	181.8	189.1	196.0
67.5°	144.4	143.4	143.4	142.5	143.4	143.4	144.4	146.3	148.5	152.6	159.0
70°	128.6	127.3	127.3	126.4	127.3	127.3	128.6	128.6	131.0	132.8	137.4
72.5°	112.5	111.2	111.6	111.0	111.6	111.2	112.5	113.0	115.2	116.0	118.0
75°	83.3	81.0	81.0	81.5	81.0	81.0	83.3	86.1	88.3	92.5	93.4
77.5°	62.2	61.7	62.3	61.6	62.3	61.7	62.2	62.2	62.7	64.6	66.1
80°	50.8	50.4	49.9	51.3	49.9	50.4	50.8	50.8	51.3	51.7	52.2
82.5°	39.4	39.3	39.3	41.1	39.3	39.3	39.4	40.2	40.3	40.0	40.5
85°	23.8	22.9	23.8	22.9	23.8	22.9	23.8	23.3	23.8	23.3	23.8
87.5°	15.8	15.6	15.3	15.8	15.3	15.6	15.8	15.0	14.8	15.2	14.5
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.5	33.8	32.0
92.5°	56.6	56.9	57.3	57.6	57.3	56.9	56.6	56.2	55.5	54.5	53.5
95°	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.5	102.1	101.3	100.4
97.5°	160.7	160.7	160.7	160.7	160.7	160.7	160.7	160.7	160.2	159.2	158.2
100°	201.2	201.2	201.2	201.2	201.2	201.2	201.2	201.2	201.0	200.4	199.8
102.5°	246.2	246.5	246.7	246.9	246.7	246.5	246.2	246.0	245.5	244.7	243.8
105°	314.2	315.0	315.9	316.8	315.9	315.0	314.2	313.3	312.5	311.6	310.7
107.5°	385.0	385.0	384.9	384.8	384.9	385.0	385.0	385.0	384.7	383.8	383.1
110°	431.0	431.9	432.7	433.6	432.7	431.9	431.0	430.2	430.0	430.6	431.2



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.9	483.1	483.3	483.5	483.3	483.1	482.9	482.8	482.8	482.8	482.9
115°	561.7	561.5	561.1	560.9	561.1	561.5	561.7	562.0	562.3	562.6	562.8
117.5°	636.3	635.8	635.2	634.6	635.2	635.8	636.3	636.9	637.7	638.7	639.6
120°	689.0	689.5	690.1	690.7	690.1	689.5	689.0	688.4	688.8	690.3	691.6
122.5°	740.5	739.5	738.5	737.4	738.5	739.5	740.5	741.6	742.6	743.6	744.5
125°	819.6	819.1	818.5	817.9	818.5	819.1	819.6	820.2	820.8	821.4	821.9
127.5°	893.8	893.4	892.9	892.4	892.9	893.4	893.8	894.2	894.8	895.4	896.0
130°	944.7	943.6	942.4	941.2	942.4	943.6	944.7	945.8	946.7	947.3	947.9
132.5°	994.5	994.1	993.6	993.2	993.6	994.1	994.5	995.0	995.5	996.1	996.7
135°	1067.1	1066.3	1065.4	1064.5	1065.4	1066.3	1067.1	1068.0	1068.8	1069.4	1069.9
137.5°	1139.1	1139.3	1139.4	1139.6	1139.4	1139.3	1139.1	1138.9	1139.2	1140.0	1140.7
140°	1186.2	1185.9	1185.6	1185.3	1185.6	1185.9	1186.2	1186.5	1186.7	1187.1	1187.3
142.5°	1231.1	1231.1	1231.1	1231.0	1231.1	1231.1	1231.1	1231.2	1231.3	1231.3	1231.4
145°	1295.6	1294.8	1293.9	1293.0	1293.9	1294.8	1295.6	1296.5	1297.1	1297.4	1297.7
147.5°	1356.8	1356.5	1356.2	1355.9	1356.2	1356.5	1356.8	1357.0	1357.3	1357.5	1357.8
150°	1395.2	1394.9	1394.6	1394.3	1394.6	1394.9	1395.2	1395.5	1395.6	1395.6	1395.6
152.5°	1431.8	1431.2	1430.4	1429.6	1430.4	1431.2	1431.8	1432.6	1432.6	1431.9	1431.2
155°	1482.1	1481.0	1479.9	1478.7	1479.9	1481.0	1482.1	1483.3	1483.3	1482.1	1481.0
157.5°	1525.5	1524.6	1523.5	1522.6	1523.5	1524.6	1525.5	1526.5	1526.6	1525.7	1524.8
160°	1551.9	1550.4	1548.9	1547.5	1548.9	1550.4	1551.9	1553.2	1553.6	1552.7	1551.9
162.5°	1577.8	1576.4	1574.9	1573.5	1574.9	1576.4	1577.8	1579.2	1579.2	1577.6	1576.1
165°	1610.7	1609.6	1608.3	1607.2	1608.3	1609.6	1610.7	1611.9	1611.5	1609.8	1608.1
167.5°	1636.8	1635.0	1633.1	1631.3	1633.1	1635.0	1636.8	1638.6	1638.6	1636.8	1635.1
170°	1651.0	1648.9	1646.9	1644.9	1646.9	1648.9	1651.0	1652.9	1653.1	1651.4	1649.7
172.5°	1662.3	1660.4	1658.3	1656.3	1658.3	1660.4	1662.3	1664.4	1664.4	1662.4	1660.5
175°	1674.3	1672.3	1670.3	1668.3	1670.3	1672.3	1674.3	1676.4	1676.4	1674.3	1672.3
177.5°	1680.0	1678.2	1676.4	1674.5	1676.4	1678.2	1680.0	1681.9	1682.0	1680.3	1678.8
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1087.1	1089.7	1095.5	1102.1	1107.6	1112.3	1116.0	1121.1	1125.9	1132.5	1138.8
5°	1021.1	1027.5	1036.7	1047.7	1061.4	1070.6	1082.0	1092.1	1106.7	1121.5	1135.7
7.5°	963.3	970.3	983.8	999.0	1015.3	1030.3	1043.9	1061.6	1081.1	1102.3	1126.2
10°	925.9	933.7	949.7	967.1	986.4	1001.0	1019.3	1040.3	1062.4	1088.5	1117.8
12.5°	892.2	899.6	918.9	936.7	956.7	972.8	994.0	1015.5	1044.7	1073.1	1106.4
15°	826.6	846.2	868.2	889.2	913.1	932.8	958.4	980.4	1008.3	1048.2	1086.2
17.5°	753.6	774.6	801.9	834.4	866.3	890.7	916.7	944.0	977.2	1018.0	1061.8
20°	711.1	728.1	758.3	794.4	831.6	865.5	889.2	919.5	953.8	997.8	1043.1
22.5°	679.2	693.6	717.3	753.5	793.5	832.8	863.2	893.1	931.1	975.1	1024.4
25°	631.5	647.0	667.6	692.3	738.1	779.8	819.7	854.0	894.3	938.2	993.2
27.5°	591.7	605.3	624.1	649.9	680.6	726.6	774.9	814.1	855.4	902.6	957.6
30°	568.3	579.3	594.9	621.0	650.2	691.5	740.5	786.3	827.9	876.9	934.1
32.5°	543.7	555.4	570.7	591.2	622.8	657.4	706.4	756.6	800.8	850.9	907.1
35°	511.0	520.2	533.9	555.0	583.4	613.6	657.1	708.9	755.5	809.2	862.7
37.5°	477.9	488.8	499.6	518.3	541.7	574.1	609.8	662.6	714.4	763.3	815.5
40°	459.3	465.7	477.6	492.8	517.5	546.3	579.7	631.5	683.2	731.8	784.4
42.5°	438.4	445.6	455.6	470.7	492.9	521.0	553.7	598.5	652.5	699.5	747.4
45°	409.4	413.5	423.5	436.4	454.7	483.1	513.3	553.2	604.0	648.8	691.0
47.5°	380.0	383.7	389.9	401.7	422.2	445.0	473.3	509.0	553.6	598.5	634.1
50°	359.9	363.1	369.1	380.0	398.4	420.9	448.8	480.8	520.6	563.7	593.5
52.5°	339.8	341.5	347.1	359.6	375.0	397.0	422.0	451.5	488.8	524.5	554.7
55°	307.7	311.9	315.5	324.7	339.3	360.4	382.8	410.8	439.6	469.8	495.4
57.5°	274.3	278.8	284.1	292.1	303.8	323.4	343.5	366.2	390.8	415.9	437.4
60°	252.3	256.4	261.0	270.2	280.7	296.3	318.2	337.9	356.7	379.6	401.1
62.5°	230.7	234.8	240.1	247.5	257.6	272.4	290.8	307.9	327.4	347.4	363.4
65°	198.7	201.9	206.0	212.9	222.6	235.8	250.9	264.2	281.6	296.3	310.9
67.5°	163.7	169.8	175.2	180.8	188.9	201.3	212.2	224.9	236.8	247.6	261.0
70°	140.6	147.5	152.5	158.4	166.3	176.8	187.3	196.0	205.6	216.1	228.1
72.5°	121.1	126.6	130.5	136.8	143.9	153.7	163.5	170.7	178.5	185.7	197.3
75°	95.7	98.0	100.7	105.8	112.2	119.5	127.3	133.7	138.3	144.7	152.9
77.5°	68.8	73.2	75.0	78.6	83.2	87.7	92.9	98.2	102.6	105.0	111.2
80°	52.7	54.5	56.3	61.4	64.1	68.7	72.3	77.4	79.2	81.5	87.5
82.5°	40.9	42.0	43.1	44.5	46.1	50.7	54.4	57.6	59.4	60.3	64.7
85°	23.8	24.3	24.7	25.2	25.7	25.7	27.5	29.8	33.0	33.0	34.4
87.5°	14.1	14.1	13.7	12.8	13.1	12.7	12.5	11.9	12.3	12.7	13.3
90°	30.3	28.6	26.3	23.9	21.6	19.4	16.6	13.4	10.2	7.1	3.9
92.5°	52.4	51.4	49.8	48.2	46.6	44.9	42.4	38.7	35.0	31.4	27.8
95°	99.5	98.7	96.7	94.6	92.6	90.6	88.3	85.7	83.1	80.5	77.9
97.5°	157.0	156.0	153.7	151.3	149.0	146.6	144.4	142.3	140.2	138.1	136.0
100°	199.2	198.6	196.0	193.5	190.9	188.2	186.4	185.2	184.1	182.9	181.8
102.5°	243.1	242.3	239.9	237.5	235.1	232.8	231.4	230.9	230.5	230.0	229.5
105°	309.9	309.0	307.8	306.7	305.5	304.4	303.7	303.3	303.1	302.8	302.5
107.5°	382.2	381.4	381.3	381.1	380.9	380.7	380.5	380.1	379.8	379.4	379.1
110°	431.7	432.3	432.6	432.9	433.2	433.5	433.3	432.7	432.1	431.6	431.0



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	483.1	483.2	483.7	484.2	484.7	485.3	485.5	485.3	485.3	485.2	485.0
115°	563.2	563.4	564.0	564.6	565.2	565.8	566.0	566.0	566.0	566.0	566.0
117.5°	640.6	641.6	642.0	642.4	642.8	643.3	643.3	643.1	642.8	642.6	642.4
120°	693.1	694.6	695.4	696.3	697.2	698.0	697.8	696.7	695.6	694.4	693.3
122.5°	745.5	746.5	746.9	747.3	747.7	748.1	748.0	747.6	747.2	746.7	746.2
125°	822.5	823.1	823.4	823.6	824.0	824.2	824.4	824.4	824.4	824.4	824.4
127.5°	896.5	897.1	897.6	898.0	898.5	899.0	898.7	897.9	897.0	896.1	895.3
130°	948.5	949.0	949.0	949.0	949.0	949.0	948.6	947.7	946.8	946.0	945.1
132.5°	997.3	997.8	998.1	998.3	998.5	998.8	998.6	997.9	997.3	996.7	996.0
135°	1070.5	1071.1	1071.1	1071.1	1071.1	1071.1	1070.2	1068.5	1066.7	1065.0	1063.2
137.5°	1141.4	1142.2	1141.8	1141.3	1140.8	1140.4	1139.7	1138.9	1138.1	1137.3	1136.5
140°	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6	1187.1	1186.5	1185.9	1185.3
142.5°	1231.5	1231.5	1231.7	1232.0	1232.2	1232.4	1232.3	1231.7	1231.1	1230.5	1229.9
145°	1298.0	1298.2	1298.0	1297.7	1297.4	1297.1	1296.4	1295.2	1294.1	1292.9	1291.8
147.5°	1358.0	1358.2	1358.5	1358.7	1358.9	1359.2	1358.6	1357.2	1355.8	1354.4	1353.1
150°	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.1	1393.9	1392.8	1391.5	1390.4
152.5°	1430.6	1429.9	1429.7	1429.4	1429.2	1429.0	1428.5	1427.8	1427.1	1426.4	1425.7
155°	1479.9	1478.7	1479.0	1479.3	1479.5	1479.9	1480.0	1480.0	1480.0	1480.0	1480.0
157.5°	1524.0	1523.1	1523.2	1523.2	1523.3	1523.4	1523.6	1524.1	1524.7	1525.2	1525.7
160°	1551.0	1550.1	1550.4	1550.7	1551.0	1551.3	1551.5	1551.9	1552.1	1552.4	1552.7
162.5°	1574.5	1573.0	1573.2	1573.6	1573.8	1574.1	1574.6	1575.4	1576.1	1576.9	1577.6
165°	1606.4	1604.6	1605.2	1605.8	1606.4	1607.0	1607.7	1608.5	1609.4	1610.2	1611.1
167.5°	1633.4	1631.7	1631.6	1631.5	1631.5	1631.4	1632.0	1633.2	1634.4	1635.6	1636.8
170°	1647.9	1646.1	1645.9	1645.6	1645.3	1645.0	1645.6	1647.0	1648.5	1649.9	1651.4
172.5°	1658.5	1656.6	1656.5	1656.5	1656.4	1656.3	1656.9	1658.1	1659.3	1660.5	1661.7
175°	1670.3	1668.3	1668.5	1668.8	1669.1	1669.4	1670.3	1671.7	1673.2	1674.6	1676.0
177.5°	1677.1	1675.5	1675.5	1675.5	1675.5	1675.5	1676.1	1677.2	1678.4	1679.6	1680.7
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1143.5	1146.8	1150.5	1157.4	1163.3	1165.9	1171.0	1174.7	1173.5	1178.6	1187.5
5°	1148.0	1160.4	1174.6	1189.2	1205.7	1219.4	1230.4	1241.4	1250.1	1260.6	1276.2
7.5°	1147.3	1169.2	1193.2	1219.4	1246.5	1269.8	1291.4	1313.4	1332.9	1354.3	1382.2
10°	1144.4	1173.6	1203.4	1237.8	1272.0	1304.6	1333.9	1361.4	1387.5	1415.4	1450.7
12.5°	1141.0	1174.7	1210.7	1252.0	1294.8	1333.9	1368.3	1407.9	1440.6	1476.6	1517.3
15°	1126.4	1171.8	1220.8	1274.4	1325.7	1378.3	1425.5	1474.0	1519.3	1562.4	1613.7
17.5°	1109.8	1162.1	1219.9	1283.1	1344.8	1408.8	1464.7	1526.0	1572.3	1630.0	1677.7
20°	1096.2	1152.5	1214.4	1285.4	1355.4	1426.4	1488.2	1550.5	1602.7	1660.9	1721.3
22.5°	1079.8	1141.6	1208.5	1282.0	1355.4	1433.0	1501.4	1563.3	1628.0	1693.4	1755.8
25°	1053.2	1117.3	1188.3	1268.9	1353.1	1432.4	1505.6	1582.5	1652.2	1723.1	1779.0
27.5°	1020.6	1087.9	1162.7	1245.9	1332.3	1413.5	1499.8	1581.7	1651.7	1720.1	1768.8
30°	994.5	1065.6	1137.5	1221.7	1311.5	1398.4	1491.0	1573.0	1646.7	1708.1	1735.5
32.5°	967.9	1035.2	1109.2	1194.6	1286.5	1380.2	1471.9	1555.7	1623.9	1660.8	1661.5
35°	921.4	984.5	1061.4	1145.2	1239.6	1341.3	1434.2	1516.6	1558.2	1561.5	1516.6
37.5°	870.6	928.6	1001.2	1085.0	1188.4	1289.5	1384.5	1439.4	1453.3	1406.7	1323.7
40°	834.3	887.9	957.9	1044.0	1146.6	1251.0	1337.6	1377.9	1363.2	1287.6	1195.2
42.5°	796.3	846.1	913.6	998.6	1101.6	1207.0	1280.7	1302.4	1263.6	1176.3	1068.1
45°	734.0	779.8	846.7	932.3	1031.2	1130.1	1186.0	1175.0	1110.4	1006.9	885.6
47.5°	669.3	713.5	773.7	852.9	954.2	1039.6	1077.4	1044.2	952.4	838.5	739.8
50°	626.5	671.8	727.2	802.7	895.2	977.7	1001.9	951.6	849.5	739.9	649.3
52.5°	584.3	623.0	677.3	750.4	838.8	908.4	921.4	863.2	757.9	659.8	579.4
55°	520.2	555.4	601.2	669.9	746.4	805.5	798.6	723.9	628.3	544.5	481.3
57.5°	458.2	484.7	527.0	591.4	658.6	698.2	673.1	609.5	520.3	451.7	398.4
60°	417.2	441.9	481.3	537.6	596.7	619.1	598.1	528.9	458.4	395.6	350.8
62.5°	378.3	400.1	434.0	486.3	534.0	547.3	524.8	464.4	400.9	347.2	310.1
65°	321.9	342.1	370.9	408.0	441.0	447.4	432.7	370.9	322.8	277.9	252.3
67.5°	270.7	283.9	306.4	338.5	356.0	359.7	331.4	292.6	250.2	222.7	203.3
70°	236.3	245.5	266.5	283.9	298.1	298.6	272.4	241.3	208.8	186.4	172.2
72.5°	202.9	211.7	227.6	239.6	250.5	246.9	223.0	198.5	172.2	155.2	144.7
75°	156.6	164.4	172.6	178.1	178.1	173.6	156.2	137.8	122.7	112.6	109.4
77.5°	113.8	120.3	123.0	122.2	120.5	113.4	102.4	90.4	85.0	80.2	77.8
80°	89.3	92.0	93.0	90.7	87.9	79.6	72.3	67.3	62.3	60.4	59.5
82.5°	66.2	68.6	66.2	66.8	60.8	54.1	50.0	48.3	46.1	45.5	44.5
85°	35.3	34.8	33.9	31.6	27.5	26.5	26.1	25.7	24.7	25.2	24.3
87.5°	13.5	13.0	12.2	12.5	13.0	12.7	13.6	14.0	14.5	14.5	15.6
90°	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3	32.0
92.5°	31.4	35.0	38.7	42.4	44.9	46.6	48.2	49.8	51.4	52.4	53.5
95°	80.5	83.1	85.7	88.3	90.6	92.6	94.6	96.7	98.7	99.5	100.4
97.5°	138.1	140.2	142.3	144.4	146.6	149.0	151.3	153.7	156.0	157.0	158.2
100°	182.9	184.1	185.2	186.4	188.2	190.9	193.5	196.0	198.6	199.2	199.8
102.5°	230.0	230.5	230.9	231.4	232.8	235.1	237.5	239.9	242.3	243.1	243.8
105°	302.8	303.1	303.3	303.7	304.4	305.5	306.7	307.8	309.0	309.9	310.7
107.5°	379.4	379.8	380.1	380.5	380.7	380.9	381.1	381.3	381.4	382.2	383.1
110°	431.6	432.1	432.7	433.3	433.5	433.2	432.9	432.6	432.3	431.7	431.2





TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	485.2	485.3	485.3	485.5	485.3	484.7	484.2	483.7	483.2	483.1	482.9
115°	566.0	566.0	566.0	566.0	565.8	565.2	564.6	564.0	563.4	563.2	562.8
117.5°	642.6	642.8	643.1	643.3	643.3	642.8	642.4	642.0	641.6	640.6	639.6
120°	694.4	695.6	696.7	697.8	698.0	697.2	696.3	695.4	694.6	693.1	691.6
122.5°	746.7	747.2	747.6	748.0	748.1	747.7	747.3	746.9	746.5	745.5	744.5
125°	824.4	824.4	824.4	824.4	824.2	824.0	823.6	823.4	823.1	822.5	821.9
127.5°	896.1	897.0	897.9	898.7	899.0	898.5	898.0	897.6	897.1	896.5	896.0
130°	946.0	946.8	947.7	948.6	949.0	949.0	949.0	949.0	949.0	948.5	947.9
132.5°	996.7	997.3	997.9	998.6	998.8	998.5	998.3	998.1	997.8	997.3	996.7
135°	1065.0	1066.7	1068.5	1070.2	1071.1	1071.1	1071.1	1071.1	1071.1	1070.5	1069.9
137.5°	1137.3	1138.1	1138.9	1139.7	1140.4	1140.8	1141.3	1141.8	1142.2	1141.4	1140.7
140°	1185.9	1186.5	1187.1	1187.6	1187.9	1187.9	1187.9	1187.9	1187.9	1187.6	1187.3
142.5°	1230.5	1231.1	1231.7	1232.3	1232.4	1232.2	1232.0	1231.7	1231.5	1231.5	1231.4
145°	1292.9	1294.1	1295.2	1296.4	1297.1	1297.4	1297.7	1298.0	1298.2	1298.0	1297.7
147.5°	1354.4	1355.8	1357.2	1358.6	1359.2	1358.9	1358.7	1358.5	1358.2	1358.0	1357.8
150°	1391.5	1392.8	1393.9	1395.1	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6	1395.6
152.5°	1426.4	1427.1	1427.8	1428.5	1429.0	1429.2	1429.4	1429.7	1429.9	1430.6	1431.2
155°	1480.0	1480.0	1480.0	1480.0	1479.9	1479.5	1479.3	1479.0	1478.7	1479.9	1481.0
157.5°	1525.2	1524.7	1524.1	1523.6	1523.4	1523.3	1523.2	1523.2	1523.1	1524.0	1524.8
160°	1552.4	1552.1	1551.9	1551.5	1551.3	1551.0	1550.7	1550.4	1550.1	1551.0	1551.9
162.5°	1576.9	1576.1	1575.4	1574.6	1574.1	1573.8	1573.6	1573.2	1573.0	1574.5	1576.1
165°	1610.2	1609.4	1608.5	1607.7	1607.0	1606.4	1605.8	1605.2	1604.6	1606.4	1608.1
167.5°	1635.6	1634.4	1633.2	1632.0	1631.4	1631.5	1631.5	1631.6	1631.7	1633.4	1635.1
170°	1649.9	1648.5	1647.0	1645.6	1645.0	1645.3	1645.6	1645.9	1646.1	1647.9	1649.7
172.5°	1660.5	1659.3	1658.1	1656.9	1656.3	1656.4	1656.5	1656.5	1656.6	1658.5	1660.5
175°	1674.6	1673.2	1671.7	1670.3	1669.4	1669.1	1668.8	1668.5	1668.3	1670.3	1672.3
177.5°	1679.6	1678.4	1677.2	1676.1	1675.5	1675.5	1675.5	1675.5	1675.5	1677.1	1678.8
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1192.2	1193.7	1194.8	1198.4	1198.8	1202.1	1198.8
5°	1290.8	1297.3	1307.3	1317.4	1318.4	1324.7	1313.3
7.5°	1401.4	1416.3	1425.6	1441.8	1448.3	1452.3	1445.7
10°	1477.6	1491.4	1515.7	1527.6	1539.5	1541.4	1535.9
12.5°	1551.3	1573.1	1592.2	1614.8	1614.2	1630.4	1624.4
15°	1649.4	1671.8	1698.4	1723.5	1732.8	1732.8	1740.1
17.5°	1719.3	1760.5	1788.0	1807.8	1829.4	1833.1	1830.6
20°	1766.6	1811.0	1840.4	1866.0	1880.7	1884.7	1884.7
22.5°	1801.8	1839.6	1868.2	1891.3	1903.3	1908.2	1906.8
25°	1826.2	1858.6	1876.0	1882.9	1886.1	1885.2	1876.5
27.5°	1792.8	1791.3	1780.4	1759.3	1743.4	1733.8	1722.9
30°	1729.1	1705.3	1677.8	1647.5	1608.6	1578.9	1569.7
32.5°	1634.2	1580.7	1534.2	1483.8	1442.0	1412.2	1399.7
35°	1450.7	1366.0	1296.8	1236.4	1192.4	1164.9	1155.8
37.5°	1232.9	1150.9	1065.3	1006.7	970.3	942.5	932.1
40°	1094.4	1005.1	930.5	875.6	838.0	811.0	810.5
42.5°	968.0	882.8	812.5	772.9	732.5	714.6	714.5
45°	792.6	724.4	664.9	633.8	609.5	594.9	590.7
47.5°	656.3	599.9	560.2	535.4	515.6	506.3	500.2
50°	579.7	530.3	498.7	477.2	466.1	454.3	453.3
52.5°	516.0	476.0	451.4	433.9	420.0	412.8	413.0
55°	433.6	402.1	384.6	371.3	360.4	354.9	352.6
57.5°	365.3	341.6	329.0	316.8	312.1	307.8	306.6
60°	322.8	306.8	294.9	285.2	278.4	277.1	276.6
62.5°	287.7	270.9	262.7	255.2	250.2	248.1	247.3
65°	237.2	224.8	217.5	211.5	209.7	206.6	206.0
67.5°	191.2	183.8	178.9	174.9	172.4	172.2	172.2
70°	163.0	158.9	154.8	152.5	151.1	150.2	150.2
72.5°	138.9	135.8	132.4	131.2	131.0	130.0	129.7
75°	105.8	102.5	103.1	100.7	98.9	96.6	95.2
77.5°	75.0	72.8	72.2	72.0	70.4	70.2	70.9
80°	58.1	55.9	55.4	55.9	55.4	54.1	54.1
82.5°	44.3	42.3	41.8	41.6	41.2	41.6	40.8
85°	23.8	22.9	22.9	22.9	23.8	23.3	22.9
87.5°	15.2	15.2	15.8	15.5	15.6	15.3	15.8
90°	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	54.5	55.5	56.2	56.6	56.9	57.3	57.6
95°	101.3	102.1	102.5	102.5	102.5	102.5	102.5
97.5°	159.2	160.2	160.7	160.7	160.7	160.7	160.7
100°	200.4	201.0	201.2	201.2	201.2	201.2	201.2
102.5°	244.7	245.5	246.0	246.2	246.5	246.7	246.9
105°	311.6	312.5	313.3	314.2	315.0	315.9	316.8
107.5°	383.8	384.7	385.0	385.0	385.0	384.9	384.8
110°	430.6	430.0	430.2	431.0	431.9	432.7	433.6



TEST NUMBER: P333072-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	482.8	482.8	482.8	482.9	483.1	483.3	483.5
115°	562.6	562.3	562.0	561.7	561.5	561.1	560.9
117.5°	638.7	637.7	636.9	636.3	635.8	635.2	634.6
120°	690.3	688.8	688.4	689.0	689.5	690.1	690.7
122.5°	743.6	742.6	741.6	740.5	739.5	738.5	737.4
125°	821.4	820.8	820.2	819.6	819.1	818.5	817.9
127.5°	895.4	894.8	894.2	893.8	893.4	892.9	892.4
130°	947.3	946.7	945.8	944.7	943.6	942.4	941.2
132.5°	996.1	995.5	995.0	994.5	994.1	993.6	993.2
135°	1069.4	1068.8	1068.0	1067.1	1066.3	1065.4	1064.5
137.5°	1140.0	1139.2	1138.9	1139.1	1139.3	1139.4	1139.6
140°	1187.1	1186.7	1186.5	1186.2	1185.9	1185.6	1185.3
142.5°	1231.3	1231.3	1231.2	1231.1	1231.1	1231.1	1231.0
145°	1297.4	1297.1	1296.5	1295.6	1294.8	1293.9	1293.0
147.5°	1357.5	1357.3	1357.0	1356.8	1356.5	1356.2	1355.9
150°	1395.6	1395.6	1395.5	1395.2	1394.9	1394.6	1394.3
152.5°	1431.9	1432.6	1432.6	1431.8	1431.2	1430.4	1429.6
155°	1482.1	1483.3	1483.3	1482.1	1481.0	1479.9	1478.7
157.5°	1525.7	1526.6	1526.5	1525.5	1524.6	1523.5	1522.6
160°	1552.7	1553.6	1553.2	1551.9	1550.4	1548.9	1547.5
162.5°	1577.6	1579.2	1579.2	1577.8	1576.4	1574.9	1573.5
165°	1609.8	1611.5	1611.9	1610.7	1609.6	1608.3	1607.2
167.5°	1636.8	1638.6	1638.6	1636.8	1635.0	1633.1	1631.3
170°	1651.4	1653.1	1652.9	1651.0	1648.9	1646.9	1644.9
172.5°	1662.4	1664.4	1664.4	1662.3	1660.4	1658.3	1656.3
175°	1674.3	1676.4	1676.4	1674.3	1672.3	1670.3	1668.3
177.5°	1680.3	1682.0	1681.9	1680.0	1678.2	1676.4	1674.5
180°	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6	1678.6

(END OF REPORT)