

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333073-935

Luminaire Tested: **S124RDIW-S795D1560U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333073-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1560U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8138.3 lumens  
Efficiency: N/A  
Efficacy: 119.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333073-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333073-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	78	76	65	63	61	51	49	48	37	36	35	29
2	86	79	73	68	77	71	67	62	57	54	51	45	42	40	33	31	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	62	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P333073-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.4	1.4
10°-20°	313.3	3.8
20°-30°	452.4	5.6
30°-40°	512.8	6.3
40°-50°	495.2	6.1
50°-60°	411.8	5.1
60°-70°	284.4	3.5
70°-80°	144.1	1.8
80°-90°	42.0	0.5
90°-100°	59.4	0.7
100°-110°	378.6	4.7
110°-120°	724.2	8.9
120°-130°	919.3	11.3
130°-140°	983.6	12.1
140°-150°	919.8	11.3
150°-160°	741.8	9.1
160°-170°	478.4	5.9
170°-180°	164.9	2.0
0°-30°	878.1	10.8
0°-40°	1390.9	17.1
0°-60°	2297.9	28.2
0°-90°	2768.4	34.0
90°-120°	1162.1	14.3
90°-150°	3984.9	49.0
90°-180°	5370.0	66.0
0°-180°	8138.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	4	18	29	36	39	6
95°	71	30	29	36	38	92
105°	391	399	405	414	370	409
115°	730	733	732	735	735	718
125°	1026	1030	1028	1032	1034	915
135°	1272	1272	1276	1279	1282	980
145°	1467	1471	1471	1472	1475	916
155°	1609	1610	1606	1611	1608	741
165°	1697	1691	1691	1700	1689	479
175°	1736	1729	1730	1740	1726	165
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P333073-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.7	17.0	16.3	15.6	15.0	14.8	15.1	15.4	15.7	15.9	16.2
90°	3.9	7.1	10.2	13.4	16.6	19.4	21.6	23.9	26.3	28.6	30.3
92.5°	16.4	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.6	29.3
95°	71.4	61.6	51.8	42.0	32.2	27.4	27.7	28.0	28.2	28.6	30.3
97.5°	151.6	157.7	163.8	170.0	176.2	163.1	130.9	98.7	66.5	34.3	34.4
100°	212.9	218.2	223.3	228.5	233.7	216.4	176.6	136.7	96.9	57.2	52.3
102.5°	281.5	285.3	289.1	292.9	296.7	296.0	290.8	285.7	280.4	275.3	222.3
105°	390.8	392.5	394.3	396.1	397.8	399.3	400.8	402.3	403.6	405.1	407.7
107.5°	492.3	493.3	494.1	495.0	495.8	497.2	499.2	501.2	503.1	505.1	506.4
110°	560.9	561.8	562.7	563.5	564.4	565.7	567.4	569.1	570.8	572.6	573.2



TEST NUMBER: P333073-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	627.4	629.0	630.5	632.1	633.6	634.8	635.6	636.5	637.2	638.1	637.9
115°	729.7	730.6	731.4	732.3	733.1	733.5	733.1	732.9	732.6	732.3	732.9
117.5°	821.9	823.0	824.2	825.4	826.6	827.4	828.0	828.7	829.3	829.9	829.8
120°	884.2	885.4	886.6	887.7	888.8	889.2	889.0	888.7	888.4	888.1	888.7
122.5°	942.4	943.1	943.7	944.4	945.2	945.7	946.2	946.5	946.9	947.4	947.7
125°	1025.8	1026.9	1028.0	1029.2	1030.4	1030.6	1030.1	1029.5	1028.9	1028.4	1029.2
127.5°	1104.7	1105.0	1105.3	1105.5	1105.9	1106.6	1108.0	1109.3	1110.6	1112.0	1111.8
130°	1155.6	1155.9	1156.2	1156.5	1156.8	1157.4	1158.2	1159.1	1159.9	1160.8	1161.1
132.5°	1202.3	1202.8	1203.4	1203.9	1204.5	1205.2	1206.3	1207.4	1208.5	1209.6	1209.9
135°	1272.5	1272.1	1271.9	1271.6	1271.3	1271.7	1272.9	1274.0	1275.2	1276.3	1276.9
137.5°	1334.6	1334.6	1334.7	1334.9	1335.0	1335.7	1337.0	1338.3	1339.5	1340.7	1341.4
140°	1375.0	1375.6	1376.2	1376.7	1377.3	1377.9	1378.5	1379.1	1379.7	1380.2	1381.1
142.5°	1411.4	1412.4	1413.5	1414.5	1415.6	1416.3	1416.6	1416.9	1417.3	1417.6	1418.2
145°	1467.2	1468.1	1469.0	1469.8	1470.7	1471.1	1471.1	1471.1	1471.1	1471.1	1471.4
147.5°	1511.7	1513.2	1514.8	1516.5	1518.1	1518.7	1518.5	1518.2	1517.9	1517.6	1517.9
150°	1543.9	1545.0	1546.1	1547.3	1548.4	1548.9	1548.6	1548.3	1548.0	1547.7	1547.7
152.5°	1570.8	1571.8	1572.7	1573.6	1574.5	1574.8	1574.2	1573.6	1573.1	1572.6	1573.1
155°	1608.8	1609.0	1609.3	1609.6	1609.9	1609.6	1608.8	1607.9	1607.1	1606.1	1607.3
157.5°	1640.7	1640.5	1640.4	1640.2	1640.0	1639.4	1638.4	1637.4	1636.5	1635.5	1637.0
160°	1659.4	1658.5	1657.7	1656.8	1656.0	1655.4	1655.0	1654.8	1654.5	1654.2	1656.0
162.5°	1676.0	1674.9	1673.8	1672.8	1671.6	1670.9	1670.6	1670.3	1670.1	1669.7	1671.5
165°	1697.0	1695.6	1694.2	1692.7	1691.3	1690.6	1690.6	1690.6	1690.6	1690.6	1692.8
167.5°	1713.6	1712.2	1710.6	1709.2	1707.6	1706.8	1706.7	1706.5	1706.3	1706.2	1708.7
170°	1723.0	1721.3	1719.5	1717.8	1716.1	1715.4	1715.6	1716.0	1716.2	1716.5	1718.8
172.5°	1729.2	1727.5	1725.8	1724.1	1722.3	1721.6	1721.9	1722.2	1722.4	1722.8	1725.0
175°	1735.9	1734.2	1732.5	1730.8	1729.1	1728.4	1728.6	1728.9	1729.2	1729.5	1732.1
177.5°	1739.1	1737.5	1735.9	1734.2	1732.7	1732.1	1732.5	1733.0	1733.5	1733.9	1735.8
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P333073-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	16.4	16.5	16.7	17.0	17.2	17.5	17.7	18.1
90°	32.0	33.8	35.5	36.7	37.2	37.8	38.4	38.9
92.5°	31.0	32.7	34.4	35.4	35.5	35.6	35.7	35.8
95°	32.0	33.8	35.5	36.5	36.8	37.1	37.4	37.6
97.5°	34.6	34.8	35.0	35.2	35.5	35.8	36.1	36.3
100°	47.4	42.4	37.5	35.2	35.5	35.8	36.1	36.3
102.5°	169.4	116.5	63.6	37.2	37.2	37.3	37.4	37.4
105°	410.3	412.9	415.5	411.6	401.2	390.8	380.5	370.1
107.5°	507.6	508.9	510.1	511.3	512.5	513.5	514.6	515.7
110°	573.8	574.4	574.9	575.7	576.5	577.4	578.2	579.1





TEST NUMBER: P333073-935

CATALOG NUMBER: S124RDIW-S795D1560U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.8	637.7	637.6	638.1	639.2	640.2	641.4	642.5
115°	733.5	734.0	734.6	734.9	734.9	734.9	734.9	734.9
117.5°	829.7	829.6	829.5	829.4	829.2	829.1	829.1	828.9
120°	889.2	889.8	890.4	890.4	889.8	889.2	888.7	888.1
122.5°	948.0	948.4	948.7	948.6	948.0	947.4	946.8	946.3
125°	1030.1	1031.0	1031.8	1032.4	1032.7	1032.9	1033.3	1033.5
127.5°	1111.6	1111.5	1111.3	1111.0	1110.9	1110.6	1110.3	1110.2
130°	1161.4	1161.7	1161.9	1162.1	1162.1	1162.1	1162.1	1162.1
132.5°	1210.2	1210.5	1210.7	1210.8	1210.6	1210.3	1210.1	1209.9
135°	1277.5	1278.1	1278.7	1279.3	1279.8	1280.4	1281.0	1281.5
137.5°	1342.0	1342.6	1343.3	1343.5	1343.3	1343.2	1343.0	1342.8
140°	1382.0	1382.9	1383.7	1384.2	1384.6	1384.8	1385.1	1385.4
142.5°	1418.9	1419.5	1420.1	1420.5	1420.6	1420.6	1420.6	1420.7
145°	1471.7	1472.0	1472.2	1472.7	1473.3	1473.9	1474.5	1475.0
147.5°	1518.0	1518.3	1518.5	1518.8	1519.1	1519.3	1519.7	1519.9
150°	1547.7	1547.7	1547.7	1547.9	1548.2	1548.4	1548.8	1549.0
152.5°	1573.6	1574.0	1574.5	1574.6	1574.4	1574.3	1574.1	1573.9
155°	1608.4	1609.6	1610.8	1610.9	1610.1	1609.2	1608.3	1607.5
157.5°	1638.5	1640.0	1641.5	1641.5	1640.0	1638.5	1637.0	1635.5
160°	1657.7	1659.4	1661.1	1661.1	1659.4	1657.7	1656.0	1654.2
162.5°	1673.3	1675.0	1676.7	1676.5	1674.6	1672.7	1670.7	1668.7
165°	1695.1	1697.5	1699.8	1699.6	1697.0	1694.4	1691.9	1689.3
167.5°	1711.2	1713.7	1716.3	1716.1	1713.2	1710.4	1707.4	1704.6
170°	1721.1	1723.5	1725.8	1725.4	1722.6	1719.7	1716.8	1713.9
172.5°	1727.3	1729.7	1732.0	1731.6	1728.5	1725.4	1722.3	1719.1
175°	1734.7	1737.3	1739.9	1739.5	1735.9	1732.5	1729.1	1725.6
177.5°	1737.6	1739.5	1741.3	1740.9	1738.1	1735.3	1732.5	1729.7
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9

(END OF REPORT)