

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332864-930

Luminaire Tested: **S124DIW-S1195D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332864-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1560U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8584.2 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332864-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332864-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	79	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13116	13116	13116
5°	13156	12998	13092
10°	13073	12892	12956
15°	12915	12709	12741
20°	12706	12482	12493
25°	12466	12222	12188
30°	12172	11918	11808
35°	11869	11599	11445
40°	11552	11236	11031
45°	11222	10880	10671
50°	10857	10562	10236
55°	10463	10151	9821
60°	10069	9689	9397
65°	9626	9251	8879
70°	9128	8665	8327
75°	8366	7960	7757
80°	7443	7141	6960
85°	6512	6271	6150



TEST NUMBER: P332864-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.0	1.8
10°-20°	431.1	5.0
20°-30°	634.5	7.4
30°-40°	737.7	8.6
40°-50°	737.7	8.6
50°-60°	645.3	7.5
60°-70°	479.2	5.6
70°-80°	272.3	3.2
80°-90°	83.3	1.0
90°-100°	104.8	1.2
100°-110°	310.6	3.6
110°-120°	527.1	6.1
120°-130°	695.1	8.1
130°-140°	780.6	9.1
140°-150°	767.1	8.9
150°-160°	645.2	7.5
160°-170°	429.2	5.0
170°-180°	150.3	1.8
0°-30°	1218.6	14.2
0°-40°	1956.3	22.8
0°-60°	3339.3	38.9
0°-90°	4174.1	48.6
90°-120°	942.5	11.0
90°-150°	3185.3	37.1
90°-180°	4410.0	51.4
0°-180°	8584.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1625	1625	1625	1625	1625	
5°	1623	1618	1604	1617	1616	154
15°	1545	1539	1521	1528	1524	435
25°	1400	1390	1372	1373	1368	644
35°	1204	1195	1177	1168	1161	753
45°	983	973	953	939	935	757
55°	743	739	721	706	698	666
65°	504	497	484	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	4	17	27	34	37	8
95°	74	85	93	97	97	82
105°	286	288	293	296	300	304
115°	536	536	534	532	531	528
125°	781	781	779	777	774	695
135°	1007	1014	1014	1012	1008	779
145°	1223	1228	1229	1228	1224	765
155°	1401	1401	1400	1405	1400	645
165°	1526	1522	1520	1526	1522	430
175°	1587	1581	1580	1587	1580	151
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P332864-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1628.9	1628.2	1627.5	1626.8	1626.1	1624.5	1622.0	1619.4	1616.9	1614.4	1616.7
5°	1623.4	1622.3	1621.1	1620.0	1618.9	1616.7	1613.5	1610.3	1607.1	1603.9	1607.1
7.5°	1608.3	1607.2	1606.1	1604.8	1603.7	1601.4	1597.8	1594.3	1590.8	1587.2	1589.8
10°	1594.8	1593.7	1592.5	1591.3	1590.2	1587.7	1584.0	1580.2	1576.5	1572.7	1575.0
12.5°	1577.1	1576.0	1574.8	1573.6	1572.5	1569.9	1565.9	1562.0	1558.0	1554.0	1556.5
15°	1545.3	1544.2	1543.0	1541.9	1540.7	1538.0	1533.6	1529.3	1524.9	1520.6	1522.3
17.5°	1507.1	1505.6	1504.1	1502.8	1501.3	1498.5	1494.4	1490.3	1486.2	1482.1	1483.2
20°	1479.0	1477.5	1476.0	1474.6	1473.2	1470.2	1465.9	1461.6	1457.3	1452.9	1453.8
22.5°	1448.7	1446.8	1445.0	1443.0	1441.1	1437.9	1433.6	1429.3	1425.0	1420.6	1422.2
25°	1399.5	1397.5	1395.5	1393.4	1391.4	1388.4	1384.3	1380.3	1376.2	1372.1	1372.5
27.5°	1343.3	1341.2	1339.1	1337.0	1335.0	1332.0	1328.3	1324.5	1320.8	1317.0	1316.3
30°	1305.8	1303.5	1301.1	1298.9	1296.6	1293.5	1289.7	1286.0	1282.2	1278.5	1277.3
32.5°	1266.2	1264.1	1262.1	1260.0	1257.8	1254.8	1250.8	1246.8	1242.8	1238.8	1237.5
35°	1204.3	1202.2	1200.2	1198.2	1196.1	1193.1	1189.0	1185.0	1181.0	1176.9	1174.8
37.5°	1138.9	1137.0	1135.2	1133.3	1131.5	1128.4	1124.1	1119.7	1115.3	1111.0	1108.8
40°	1096.2	1093.9	1091.5	1089.2	1087.0	1083.6	1079.3	1074.9	1070.6	1066.2	1063.3
42.5°	1050.4	1049.0	1047.6	1046.2	1044.8	1041.7	1036.9	1032.1	1027.3	1022.5	1019.1
45°	982.9	980.9	978.8	976.8	974.9	971.5	966.9	962.2	957.6	953.0	949.8
47.5°	912.3	910.9	909.5	908.2	906.8	904.0	899.7	895.4	891.1	886.9	883.3
50°	864.5	863.3	862.1	861.0	859.8	857.2	853.1	849.1	845.1	841.0	837.0
52.5°	817.6	816.2	814.8	813.4	812.0	809.2	804.9	800.6	796.4	792.1	788.5
55°	743.4	742.5	741.7	740.8	739.9	737.4	733.4	729.4	725.3	721.2	717.8
57.5°	672.5	671.6	670.6	669.6	668.6	666.1	662.1	658.1	654.1	650.1	646.9
60°	623.6	622.2	620.7	619.3	617.8	615.2	611.5	607.7	603.9	600.1	597.5
62.5°	575.7	574.5	573.2	572.0	570.9	568.3	564.3	560.3	556.3	552.3	549.9
65°	503.9	502.4	500.9	499.5	498.1	495.9	493.0	490.1	487.2	484.3	481.4
67.5°	431.5	430.2	428.8	427.5	426.2	424.0	421.3	418.5	415.7	412.9	410.2
70°	386.7	384.7	382.6	380.6	378.5	376.4	374.1	371.8	369.4	367.1	364.8
72.5°	338.8	336.7	334.7	332.6	330.7	328.7	326.9	325.0	323.2	321.3	319.4
75°	268.2	266.8	265.3	263.8	262.4	261.0	259.5	258.0	256.7	255.2	254.0
77.5°	200.7	200.1	199.5	198.9	198.2	197.2	196.0	194.7	193.5	192.2	191.8
80°	160.1	159.2	158.4	157.5	156.7	156.0	155.4	154.7	154.2	153.6	153.0
82.5°	120.6	120.2	119.8	119.4	119.0	118.7	118.5	118.5	118.3	118.2	117.9
85°	70.3	70.3	70.3	70.3	70.3	70.0	69.5	68.9	68.2	67.7	67.7
87.5°	27.8	28.2	28.5	28.9	29.3	29.6	29.8	30.0	30.2	30.4	30.7
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	26.3	29.8	33.2	36.6	40.1	42.6	44.1	45.7	47.1	48.7	49.7
95°	73.8	76.2	78.7	81.1	83.6	85.8	87.7	89.6	91.6	93.4	94.2
97.5°	128.8	130.8	132.7	134.8	136.7	138.8	141.0	143.2	145.5	147.7	148.7
100°	172.1	173.2	174.3	175.4	176.5	178.2	180.8	183.2	185.6	188.1	188.7
102.5°	217.4	217.8	218.3	218.7	219.1	220.5	222.7	224.9	227.1	229.4	230.2
105°	286.4	286.7	287.0	287.2	287.6	288.2	289.3	290.4	291.5	292.6	293.4
107.5°	359.0	359.3	359.6	360.0	360.3	360.5	360.7	360.9	361.0	361.2	361.9
110°	408.1	408.7	409.2	409.8	410.3	410.5	410.2	409.9	409.6	409.4	408.8



TEST NUMBER: P332864-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.3	459.4	459.5	459.6	459.7	459.5	459.0	458.5	458.0	457.5	457.5
115°	536.0	536.0	536.0	536.0	536.0	535.7	535.2	534.6	534.1	533.5	533.3
117.5°	608.3	608.5	608.7	608.9	609.2	609.1	608.7	608.3	607.9	607.6	606.6
120°	656.5	657.5	658.7	659.7	660.8	661.0	660.1	659.3	658.5	657.7	656.3
122.5°	706.6	707.0	707.5	707.9	708.3	708.4	708.0	707.6	707.3	706.9	706.0
125°	780.6	780.6	780.6	780.6	780.6	780.5	780.2	779.9	779.7	779.4	778.9
127.5°	847.7	848.6	849.4	850.2	851.0	851.3	850.8	850.4	849.9	849.5	848.9
130°	895.0	895.8	896.6	897.4	898.2	898.6	898.6	898.6	898.6	898.6	898.1
132.5°	943.1	943.8	944.4	944.9	945.6	945.7	945.5	945.3	945.1	944.9	944.4
135°	1006.8	1008.4	1010.1	1011.8	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7
137.5°	1076.2	1076.9	1077.7	1078.5	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8
140°	1122.4	1122.9	1123.5	1124.1	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5
142.5°	1164.7	1165.2	1165.8	1166.3	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1
145°	1223.2	1224.3	1225.4	1226.5	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1
147.5°	1281.2	1282.5	1283.9	1285.2	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9
150°	1316.6	1317.7	1318.8	1319.9	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1350.1	1350.7	1351.4	1352.0	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6
155°	1401.4	1401.4	1401.4	1401.4	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3
157.5°	1444.7	1444.2	1443.7	1443.2	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1
160°	1470.3	1470.0	1469.7	1469.5	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7
162.5°	1493.9	1493.2	1492.5	1491.8	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9
165°	1525.6	1524.8	1524.0	1523.1	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1
167.5°	1550.0	1548.8	1547.7	1546.5	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7
170°	1563.7	1562.4	1561.0	1559.6	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4
172.5°	1573.5	1572.4	1571.2	1570.1	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5
175°	1587.1	1585.7	1584.4	1583.0	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6
177.5°	1591.5	1590.4	1589.3	1588.2	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P332864-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1618.9	1621.3	1623.6	1624.6	1624.4	1624.2	1623.9	1623.7
5°	1610.3	1613.5	1616.7	1618.0	1617.4	1616.8	1616.2	1615.6
7.5°	1592.4	1594.9	1597.4	1598.6	1598.2	1597.8	1597.5	1597.2
10°	1577.3	1579.6	1581.9	1582.8	1582.3	1581.7	1581.0	1580.5
12.5°	1559.0	1561.5	1564.2	1565.0	1564.2	1563.3	1562.5	1561.7
15°	1524.0	1525.8	1527.5	1528.0	1527.1	1526.2	1525.3	1524.5
17.5°	1484.3	1485.4	1486.5	1486.7	1486.1	1485.6	1485.0	1484.4
20°	1454.7	1455.5	1456.4	1456.5	1456.0	1455.4	1454.8	1454.2
22.5°	1423.8	1425.3	1426.9	1427.1	1426.1	1425.1	1424.0	1422.9
25°	1372.8	1373.0	1373.4	1372.9	1371.7	1370.6	1369.5	1368.3
27.5°	1315.6	1314.9	1314.2	1313.1	1311.7	1310.3	1308.8	1307.3
30°	1276.1	1275.0	1273.8	1272.5	1271.1	1269.7	1268.2	1266.7
32.5°	1236.1	1234.7	1233.3	1231.9	1230.4	1229.0	1227.6	1226.1
35°	1172.9	1170.9	1168.8	1167.1	1165.6	1164.2	1162.7	1161.3
37.5°	1106.6	1104.4	1102.2	1100.2	1098.3	1096.3	1094.5	1092.5
40°	1060.5	1057.5	1054.7	1052.5	1051.1	1049.6	1048.1	1046.7
42.5°	1015.8	1012.4	1009.1	1006.9	1005.9	1004.9	1004.0	1003.0
45°	946.6	943.5	940.3	938.2	937.3	936.5	935.6	934.7
47.5°	879.7	876.1	872.5	869.6	867.4	865.2	863.0	860.8
50°	832.9	828.8	824.8	821.9	820.2	818.5	816.7	815.0
52.5°	784.9	781.3	777.7	774.9	772.7	770.5	768.3	766.1
55°	714.3	710.9	707.4	704.7	703.0	701.3	699.5	697.8
57.5°	643.6	640.3	637.0	634.5	632.8	631.1	629.4	627.8
60°	594.9	592.4	589.8	587.7	586.3	584.8	583.4	582.0
62.5°	547.5	545.1	542.7	540.9	539.4	537.9	536.5	535.1
65°	478.5	475.6	472.7	470.6	469.1	467.7	466.2	464.8
67.5°	407.4	404.6	401.9	400.2	399.8	399.4	399.0	398.6
70°	362.5	360.2	357.8	356.3	355.4	354.6	353.7	352.8
72.5°	317.6	315.8	313.9	312.5	311.7	310.8	309.9	309.1
75°	252.8	251.7	250.5	249.8	249.6	249.2	248.9	248.7
77.5°	191.4	191.1	190.8	190.2	189.5	188.7	187.9	187.2
80°	152.5	151.9	151.3	150.9	150.6	150.3	150.0	149.7
82.5°	117.5	117.2	116.8	116.5	116.2	115.9	115.6	115.4
85°	67.7	67.7	67.7	67.6	67.3	66.9	66.7	66.4
87.5°	31.1	31.4	31.7	32.0	32.0	32.1	32.3	32.4
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	50.6	51.6	52.6	53.2	53.6	53.9	54.2	54.5
95°	95.1	95.9	96.7	97.1	97.1	97.1	97.1	97.1
97.5°	149.8	150.7	151.7	152.2	152.2	152.2	152.2	152.2
100°	189.1	189.7	190.3	190.5	190.5	190.5	190.5	190.5
102.5°	230.9	231.7	232.4	232.9	233.2	233.4	233.6	233.8
105°	294.2	295.1	295.9	296.7	297.5	298.3	299.1	299.9
107.5°	362.7	363.5	364.3	364.6	364.5	364.5	364.4	364.4
110°	408.3	407.7	407.2	407.3	408.1	409.0	409.8	410.6





TEST NUMBER: P332864-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.3	457.2	457.1	457.1	457.3	457.5	457.6	457.8
115°	533.0	532.7	532.5	532.1	531.9	531.7	531.3	531.1
117.5°	605.7	604.8	603.8	603.1	602.5	602.0	601.4	600.9
120°	654.9	653.6	652.2	651.8	652.4	652.9	653.5	654.0
122.5°	705.0	704.1	703.2	702.2	701.2	700.3	699.3	698.3
125°	778.3	777.8	777.2	776.7	776.1	775.6	775.0	774.5
127.5°	848.4	847.8	847.3	846.8	846.4	846.0	845.5	845.1
130°	897.6	897.0	896.4	895.6	894.5	893.5	892.3	891.3
132.5°	943.8	943.2	942.6	942.2	941.8	941.3	940.9	940.4
135°	1013.1	1012.6	1012.0	1011.3	1010.5	1009.7	1008.9	1008.0
137.5°	1080.2	1079.5	1078.7	1078.5	1078.6	1078.8	1079.0	1079.1
140°	1124.3	1124.1	1123.7	1123.5	1123.2	1122.9	1122.7	1122.4
142.5°	1166.0	1166.0	1166.0	1165.9	1165.8	1165.8	1165.7	1165.6
145°	1228.8	1228.5	1228.2	1227.7	1226.9	1226.0	1225.2	1224.4
147.5°	1285.7	1285.5	1285.2	1285.0	1284.7	1284.5	1284.2	1283.9
150°	1321.5	1321.5	1321.5	1321.4	1321.1	1320.9	1320.6	1320.3
152.5°	1355.3	1355.9	1356.6	1356.6	1355.8	1355.2	1354.5	1353.7
155°	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2
157.5°	1443.9	1444.7	1445.5	1445.4	1444.5	1443.7	1442.7	1441.8
160°	1469.5	1470.3	1471.1	1470.8	1469.5	1468.1	1466.7	1465.3
162.5°	1492.4	1493.9	1495.3	1495.4	1494.0	1492.7	1491.3	1490.0
165°	1522.7	1524.4	1526.0	1526.3	1525.2	1524.1	1523.0	1521.9
167.5°	1548.3	1550.0	1551.6	1551.6	1549.9	1548.2	1546.5	1544.7
170°	1562.1	1563.7	1565.4	1565.2	1563.3	1561.4	1559.5	1557.5
172.5°	1572.4	1574.2	1576.1	1576.1	1574.1	1572.2	1570.3	1568.4
175°	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7
177.5°	1589.7	1591.1	1592.7	1592.6	1590.8	1589.1	1587.4	1585.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5

(END OF REPORT)