

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332845-930

Luminaire Tested: **S124DIW-S1195D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332845-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D770U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6674.6 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332845-930

CATALOG NUMBER: S124DIW-S1195D770U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332845-930

CATALOG NUMBER: S124DIW-S1195D770U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90		78	78	78		68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74		69	67	65		60	58	57	53
2	92	84	78	72	86	79	73	69	69	65	61		61	57	55		53	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52		54	50	46		47	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44		48	43	40		42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38		43	38	34		38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33		39	34	30		34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29		35	30	27		31	27	24	22
8	56	43	35	30	52	41	34	29	36	30	26		32	27	24		29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24		30	25	22		26	22	20	17
10	49	36	29	24	46	34	28	23	31	25	21		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13116	13116	13116
5°	13156	12998	13092
10°	13073	12892	12956
15°	12915	12709	12741
20°	12706	12482	12493
25°	12466	12222	12188
30°	12172	11918	11808
35°	11869	11599	11445
40°	11552	11236	11031
45°	11222	10880	10671
50°	10857	10562	10236
55°	10463	10151	9821
60°	10069	9689	9397
65°	9626	9251	8879
70°	9128	8665	8327
75°	8366	7960	7757
80°	7443	7141	6960
85°	6512	6271	6150



TEST NUMBER: P332845-930

CATALOG NUMBER: S124DIW-S1195D770U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.0	2.3
10°-20°	431.1	6.5
20°-30°	634.5	9.5
30°-40°	737.7	11.1
40°-50°	737.7	11.1
50°-60°	645.3	9.7
60°-70°	479.2	7.2
70°-80°	272.3	4.1
80°-90°	80.9	1.2
90°-100°	27.7	0.4
100°-110°	176.5	2.6
110°-120°	337.5	5.1
120°-130°	428.5	6.4
130°-140°	458.5	6.9
140°-150°	428.7	6.4
150°-160°	345.7	5.2
160°-170°	223.0	3.3
170°-180°	76.9	1.2
0°-30°	1218.6	18.3
0°-40°	1956.3	29.3
0°-60°	3339.3	50.0
0°-90°	4171.7	62.5
90°-120°	541.7	8.1
90°-150°	1857.3	27.8
90°-180°	2503.0	37.5
0°-180°	6674.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1625	1625	1625	1625	1625	
5°	1623	1618	1604	1617	1616	154
15°	1545	1539	1521	1528	1524	435
25°	1400	1390	1372	1373	1368	644
35°	1204	1195	1177	1168	1161	753
45°	983	973	953	939	935	757
55°	743	739	721	706	698	666
65°	504	497	484	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	2	8	13	17	18	5
95°	33	14	13	17	18	43
105°	182	186	189	193	172	191
115°	340	342	341	342	342	335
125°	478	480	479	481	482	427
135°	593	593	595	596	597	457
145°	684	686	686	686	688	427
155°	750	750	749	751	749	346
165°	791	788	788	792	787	223
175°	809	806	806	811	804	77
180°	809	809	809	809	809	



TEST NUMBER: P332845-930

CATALOG NUMBER: S124DIW-S1195D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1628.9	1628.2	1627.5	1626.8	1626.1	1624.5	1622.0	1619.4	1616.9	1614.4	1616.7
5°	1623.4	1622.3	1621.1	1620.0	1618.9	1616.7	1613.5	1610.3	1607.1	1603.9	1607.1
7.5°	1608.3	1607.2	1606.1	1604.8	1603.7	1601.4	1597.8	1594.3	1590.8	1587.2	1589.8
10°	1594.8	1593.7	1592.5	1591.3	1590.2	1587.7	1584.0	1580.2	1576.5	1572.7	1575.0
12.5°	1577.1	1576.0	1574.8	1573.6	1572.5	1569.9	1565.9	1562.0	1558.0	1554.0	1556.5
15°	1545.3	1544.2	1543.0	1541.9	1540.7	1538.0	1533.6	1529.3	1524.9	1520.6	1522.3
17.5°	1507.1	1505.6	1504.1	1502.8	1501.3	1498.5	1494.4	1490.3	1486.2	1482.1	1483.2
20°	1479.0	1477.5	1476.0	1474.6	1473.2	1470.2	1465.9	1461.6	1457.3	1452.9	1453.8
22.5°	1448.7	1446.8	1445.0	1443.0	1441.1	1437.9	1433.6	1429.3	1425.0	1420.6	1422.2
25°	1399.5	1397.5	1395.5	1393.4	1391.4	1388.4	1384.3	1380.3	1376.2	1372.1	1372.5
27.5°	1343.3	1341.2	1339.1	1337.0	1335.0	1332.0	1328.3	1324.5	1320.8	1317.0	1316.3
30°	1305.8	1303.5	1301.1	1298.9	1296.6	1293.5	1289.7	1286.0	1282.2	1278.5	1277.3
32.5°	1266.2	1264.1	1262.1	1260.0	1257.8	1254.8	1250.8	1246.8	1242.8	1238.8	1237.5
35°	1204.3	1202.2	1200.2	1198.2	1196.1	1193.1	1189.0	1185.0	1181.0	1176.9	1174.8
37.5°	1138.9	1137.0	1135.2	1133.3	1131.5	1128.4	1124.1	1119.7	1115.3	1111.0	1108.8
40°	1096.2	1093.9	1091.5	1089.2	1087.0	1083.6	1079.3	1074.9	1070.6	1066.2	1063.3
42.5°	1050.4	1049.0	1047.6	1046.2	1044.8	1041.7	1036.9	1032.1	1027.3	1022.5	1019.1
45°	982.9	980.9	978.8	976.8	974.9	971.5	966.9	962.2	957.6	953.0	949.8
47.5°	912.3	910.9	909.5	908.2	906.8	904.0	899.7	895.4	891.1	886.9	883.3
50°	864.5	863.3	862.1	861.0	859.8	857.2	853.1	849.1	845.1	841.0	837.0
52.5°	817.6	816.2	814.8	813.4	812.0	809.2	804.9	800.6	796.4	792.1	788.5
55°	743.4	742.5	741.7	740.8	739.9	737.4	733.4	729.4	725.3	721.2	717.8
57.5°	672.5	671.6	670.6	669.6	668.6	666.1	662.1	658.1	654.1	650.1	646.9
60°	623.6	622.2	620.7	619.3	617.8	615.2	611.5	607.7	603.9	600.1	597.5
62.5°	575.7	574.5	573.2	572.0	570.9	568.3	564.3	560.3	556.3	552.3	549.9
65°	503.9	502.4	500.9	499.5	498.1	495.9	493.0	490.1	487.2	484.3	481.4
67.5°	431.5	430.2	428.8	427.5	426.2	424.0	421.3	418.5	415.7	412.9	410.2
70°	386.7	384.7	382.6	380.6	378.5	376.4	374.1	371.8	369.4	367.1	364.8
72.5°	338.8	336.7	334.7	332.6	330.7	328.7	326.9	325.0	323.2	321.3	319.4
75°	268.2	266.8	265.3	263.8	262.4	261.0	259.5	258.0	256.7	255.2	254.0
77.5°	200.7	200.1	199.5	198.9	198.2	197.2	196.0	194.7	193.5	192.2	191.8
80°	160.1	159.2	158.4	157.5	156.7	156.0	155.4	154.7	154.2	153.6	153.0
82.5°	120.6	120.2	119.8	119.4	119.0	118.7	118.5	118.5	118.3	118.2	117.9
85°	70.3	70.3	70.3	70.3	70.3	70.0	69.5	68.9	68.2	67.7	67.7
87.5°	27.5	27.5	27.6	27.6	27.7	27.7	27.7	27.7	27.6	27.6	27.8
90°	1.8	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1
92.5°	7.7	7.7	7.8	7.8	7.9	8.6	9.6	10.7	11.7	12.8	13.6
95°	33.3	28.7	24.1	19.6	15.0	12.8	12.9	13.0	13.2	13.3	14.1
97.5°	70.7	73.5	76.4	79.2	82.1	76.0	61.0	46.0	31.0	16.0	16.1
100°	99.2	101.7	104.1	106.5	108.9	100.9	82.3	63.8	45.2	26.7	24.4
102.5°	131.2	133.0	134.8	136.6	138.3	137.9	135.6	133.1	130.7	128.3	103.6
105°	182.1	183.0	183.8	184.6	185.4	186.1	186.8	187.4	188.2	188.8	190.0
107.5°	229.5	229.9	230.3	230.7	231.1	231.8	232.7	233.6	234.5	235.4	236.0
110°	261.5	261.9	262.3	262.7	263.0	263.7	264.5	265.3	266.1	266.8	267.2



TEST NUMBER: P332845-930

CATALOG NUMBER: S124DIW-S1195D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.4	293.2	293.9	294.6	295.3	295.9	296.3	296.6	297.0	297.4	297.3
115°	340.1	340.6	341.0	341.3	341.7	341.9	341.7	341.6	341.4	341.3	341.6
117.5°	383.1	383.6	384.2	384.7	385.2	385.6	386.0	386.2	386.5	386.9	386.8
120°	412.1	412.7	413.2	413.8	414.3	414.5	414.3	414.3	414.1	413.9	414.3
122.5°	439.3	439.5	439.9	440.2	440.5	440.8	441.0	441.2	441.3	441.6	441.7
125°	478.1	478.7	479.2	479.7	480.2	480.4	480.1	479.9	479.6	479.3	479.7
127.5°	514.9	515.0	515.2	515.3	515.4	515.8	516.4	517.1	517.6	518.3	518.2
130°	538.6	538.7	538.9	539.0	539.2	539.4	539.8	540.2	540.6	541.0	541.2
132.5°	560.4	560.7	560.9	561.1	561.3	561.7	562.2	562.8	563.3	563.8	563.9
135°	593.0	593.0	592.8	592.6	592.6	592.7	593.3	593.8	594.4	594.9	595.2
137.5°	622.0	622.1	622.2	622.2	622.2	622.6	623.1	623.7	624.4	624.9	625.2
140°	640.9	641.2	641.4	641.7	642.0	642.2	642.5	642.8	643.0	643.4	643.7
142.5°	657.9	658.4	658.8	659.3	659.7	660.1	660.2	660.4	660.6	660.7	661.0
145°	683.9	684.3	684.7	685.1	685.5	685.7	685.7	685.7	685.7	685.7	685.8
147.5°	704.6	705.3	706.0	706.8	707.6	707.8	707.8	707.6	707.4	707.4	707.4
150°	719.6	720.1	720.6	721.2	721.7	721.9	721.8	721.6	721.5	721.4	721.4
152.5°	732.1	732.5	733.0	733.4	733.9	733.9	733.7	733.5	733.3	733.0	733.2
155°	749.8	750.0	750.1	750.2	750.4	750.2	749.8	749.4	749.0	748.6	749.2
157.5°	764.8	764.7	764.6	764.5	764.4	764.1	763.7	763.2	762.7	762.3	763.0
160°	773.4	773.0	772.7	772.3	771.8	771.5	771.4	771.3	771.1	771.0	771.8
162.5°	781.1	780.6	780.2	779.7	779.1	778.8	778.7	778.5	778.4	778.3	779.1
165°	791.0	790.3	789.6	789.0	788.3	788.0	788.0	788.0	788.0	788.0	789.0
167.5°	798.7	798.0	797.4	796.6	795.9	795.6	795.5	795.4	795.3	795.2	796.4
170°	803.1	802.3	801.4	800.6	799.9	799.5	799.6	799.8	799.9	800.1	801.1
172.5°	806.0	805.2	804.4	803.6	802.7	802.4	802.6	802.7	802.8	803.0	804.0
175°	809.1	808.3	807.6	806.7	805.9	805.6	805.7	805.8	806.0	806.1	807.3
177.5°	810.6	809.8	809.1	808.3	807.6	807.3	807.6	807.7	808.0	808.1	809.0
180°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1



TEST NUMBER: P332845-930

CATALOG NUMBER: S124DIW-S1195D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1618.9	1621.3	1623.6	1624.6	1624.4	1624.2	1623.9	1623.7
5°	1610.3	1613.5	1616.7	1618.0	1617.4	1616.8	1616.2	1615.6
7.5°	1592.4	1594.9	1597.4	1598.6	1598.2	1597.8	1597.5	1597.2
10°	1577.3	1579.6	1581.9	1582.8	1582.3	1581.7	1581.0	1580.5
12.5°	1559.0	1561.5	1564.2	1565.0	1564.2	1563.3	1562.5	1561.7
15°	1524.0	1525.8	1527.5	1528.0	1527.1	1526.2	1525.3	1524.5
17.5°	1484.3	1485.4	1486.5	1486.7	1486.1	1485.6	1485.0	1484.4
20°	1454.7	1455.5	1456.4	1456.5	1456.0	1455.4	1454.8	1454.2
22.5°	1423.8	1425.3	1426.9	1427.1	1426.1	1425.1	1424.0	1422.9
25°	1372.8	1373.0	1373.4	1372.9	1371.7	1370.6	1369.5	1368.3
27.5°	1315.6	1314.9	1314.2	1313.1	1311.7	1310.3	1308.8	1307.3
30°	1276.1	1275.0	1273.8	1272.5	1271.1	1269.7	1268.2	1266.7
32.5°	1236.1	1234.7	1233.3	1231.9	1230.4	1229.0	1227.6	1226.1
35°	1172.9	1170.9	1168.8	1167.1	1165.6	1164.2	1162.7	1161.3
37.5°	1106.6	1104.4	1102.2	1100.2	1098.3	1096.3	1094.5	1092.5
40°	1060.5	1057.5	1054.7	1052.5	1051.1	1049.6	1048.1	1046.7
42.5°	1015.8	1012.4	1009.1	1006.9	1005.9	1004.9	1004.0	1003.0
45°	946.6	943.5	940.3	938.2	937.3	936.5	935.6	934.7
47.5°	879.7	876.1	872.5	869.6	867.4	865.2	863.0	860.8
50°	832.9	828.8	824.8	821.9	820.2	818.5	816.7	815.0
52.5°	784.9	781.3	777.7	774.9	772.7	770.5	768.3	766.1
55°	714.3	710.9	707.4	704.7	703.0	701.3	699.5	697.8
57.5°	643.6	640.3	637.0	634.5	632.8	631.1	629.4	627.8
60°	594.9	592.4	589.8	587.7	586.3	584.8	583.4	582.0
62.5°	547.5	545.1	542.7	540.9	539.4	537.9	536.5	535.1
65°	478.5	475.6	472.7	470.6	469.1	467.7	466.2	464.8
67.5°	407.4	404.6	401.9	400.2	399.8	399.4	399.0	398.6
70°	362.5	360.2	357.8	356.3	355.4	354.6	353.7	352.8
72.5°	317.6	315.8	313.9	312.5	311.7	310.8	309.9	309.1
75°	252.8	251.7	250.5	249.8	249.6	249.2	248.9	248.7
77.5°	191.4	191.1	190.8	190.2	189.5	188.7	187.9	187.2
80°	152.5	151.9	151.3	150.9	150.6	150.3	150.0	149.7
82.5°	117.5	117.2	116.8	116.5	116.2	115.9	115.6	115.4
85°	67.7	67.7	67.7	67.6	67.3	66.9	66.7	66.4
87.5°	28.0	28.1	28.3	28.4	28.5	28.5	28.5	28.6
90°	14.9	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	14.4	15.2	16.1	16.5	16.6	16.6	16.6	16.7
95°	14.9	15.7	16.6	17.0	17.1	17.3	17.4	17.5
97.5°	16.1	16.2	16.3	16.4	16.6	16.7	16.8	17.0
100°	22.1	19.7	17.4	16.4	16.6	16.7	16.8	17.0
102.5°	79.0	54.3	29.7	17.3	17.4	17.4	17.4	17.4
105°	191.3	192.4	193.6	191.8	187.0	182.1	177.3	172.5
107.5°	236.6	237.2	237.8	238.3	238.9	239.4	239.9	240.4
110°	267.4	267.7	268.0	268.3	268.7	269.1	269.5	269.9



TEST NUMBER: P332845-930

CATALOG NUMBER: S124DIW-S1195D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.3	297.3	297.2	297.4	297.9	298.4	299.0	299.5
115°	341.9	342.1	342.4	342.5	342.5	342.5	342.5	342.5
117.5°	386.7	386.7	386.6	386.5	386.5	386.5	386.4	386.4
120°	414.5	414.7	415.0	415.0	414.7	414.5	414.3	413.9
122.5°	441.9	442.1	442.2	442.1	441.9	441.6	441.3	441.1
125°	480.1	480.5	480.9	481.2	481.4	481.4	481.6	481.8
127.5°	518.1	518.0	518.0	517.9	517.8	517.6	517.6	517.5
130°	541.3	541.4	541.6	541.6	541.6	541.6	541.6	541.6
132.5°	564.0	564.2	564.4	564.4	564.3	564.1	564.0	563.9
135°	595.4	595.7	596.0	596.2	596.5	596.8	597.0	597.3
137.5°	625.5	625.8	626.1	626.2	626.1	626.1	626.0	625.9
140°	644.1	644.5	644.9	645.2	645.3	645.5	645.6	645.7
142.5°	661.4	661.6	661.9	662.1	662.1	662.1	662.2	662.2
145°	685.9	686.1	686.2	686.4	686.6	687.0	687.2	687.5
147.5°	707.5	707.7	707.8	707.9	708.0	708.2	708.3	708.4
150°	721.4	721.4	721.4	721.5	721.6	721.7	721.9	721.9
152.5°	733.4	733.6	733.9	733.9	733.9	733.8	733.7	733.6
155°	749.7	750.2	750.7	750.8	750.4	750.0	749.6	749.3
157.5°	763.7	764.4	765.1	765.1	764.4	763.7	763.0	762.3
160°	772.7	773.4	774.2	774.2	773.4	772.7	771.8	771.0
162.5°	779.9	780.6	781.5	781.5	780.6	779.6	778.7	777.8
165°	790.1	791.2	792.2	792.2	791.0	789.8	788.6	787.3
167.5°	797.6	798.7	800.0	799.9	798.5	797.2	795.8	794.5
170°	802.2	803.3	804.4	804.2	802.9	801.5	800.2	798.8
172.5°	805.1	806.2	807.2	807.1	805.6	804.2	802.7	801.3
175°	808.5	809.8	811.0	810.7	809.1	807.6	805.9	804.3
177.5°	809.9	810.7	811.6	811.4	810.1	808.8	807.6	806.2
180°	809.1	809.1	809.1	809.1	809.1	809.1	809.1	809.1

(END OF REPORT)