

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333058-935

Luminaire Tested: **S124RDIW-S795D470U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333058-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D470U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4164.5 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333058-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333058-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20						20							20
RC	80					70						30							10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50
RCR																			
0	111	111	111	111		105	105	105	105		92	92	92		81	81	81		71
1	102	98	94	90		96	92	89	86		82	79	77		72	70	69		64
2	93	86	79	74		87	81	75	71		72	68	64		64	61	58		56
3	85	76	68	62		80	72	65	60		64	59	54		57	53	49		50
4	78	67	59	53		73	64	56	51		57	51	47		51	46	43		45
5	72	60	52	46		67	57	50	44		51	45	41		46	41	37		41
6	66	54	46	40		62	51	44	39		46	40	36		42	37	33		37
7	61	49	41	35		58	47	39	34		42	36	32		38	33	29		34
8	57	45	37	31		54	43	35	30		39	33	28		35	30	26		31
9	53	41	33	28		50	39	32	27		36	30	25		32	27	24		29
10	50	38	30	26		47	36	29	25		33	27	23		30	25	22		27

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P333058-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.4	2.7
10°-20°	313.3	7.5
20°-30°	452.4	10.9
30°-40°	512.8	12.3
40°-50°	495.2	11.9
50°-60°	411.8	9.9
60°-70°	284.4	6.8
70°-80°	144.1	3.5
80°-90°	38.5	0.9
90°-100°	33.3	0.8
100°-110°	98.6	2.4
110°-120°	167.3	4.0
120°-130°	220.6	5.3
130°-140°	247.7	5.9
140°-150°	243.4	5.8
150°-160°	204.8	4.9
160°-170°	136.2	3.3
170°-180°	47.7	1.1
0°-30°	878.1	21.1
0°-40°	1390.9	33.4
0°-60°	2297.9	55.2
0°-90°	2764.9	66.4
90°-120°	299.1	7.2
90°-150°	1010.9	24.3
90°-180°	1400.0	33.6
0°-180°	4164.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	1	5	9	11	12	4
95°	23	27	30	31	31	26
105°	91	91	93	94	95	96
115°	170	170	169	169	169	168
125°	248	248	247	247	246	221
135°	320	322	322	321	320	247
145°	388	390	390	390	389	243
155°	445	445	444	446	444	205
165°	484	483	482	484	483	136
175°	504	502	501	504	501	48
180°	504	504	504	504	504	



TEST NUMBER: P333058-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.0	16.0	14.9	13.8	12.7	12.1	12.1	12.1	12.0	12.0	11.9
90°	1.2	2.2	3.1	4.0	5.0	5.8	6.5	7.2	7.9	8.6	9.1
92.5°	8.4	9.5	10.5	11.6	12.7	13.5	14.0	14.5	15.0	15.4	15.8
95°	23.4	24.2	25.0	25.7	26.5	27.2	27.8	28.4	29.0	29.6	29.9
97.5°	40.9	41.5	42.1	42.8	43.4	44.1	44.8	45.5	46.1	46.9	47.2
100°	54.6	54.9	55.3	55.6	56.1	56.6	57.3	58.1	58.9	59.7	59.8
102.5°	69.0	69.1	69.2	69.4	69.6	70.0	70.7	71.4	72.1	72.8	73.0
105°	90.9	91.0	91.1	91.2	91.3	91.4	91.8	92.1	92.5	92.8	93.1
107.5°	113.9	114.0	114.2	114.3	114.3	114.4	114.5	114.5	114.6	114.6	114.9
110°	129.5	129.7	129.8	130.0	130.2	130.3	130.2	130.1	130.0	129.9	129.8



TEST NUMBER: P333058-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	145.8	145.8	145.9	145.9	145.9	145.9	145.7	145.5	145.3	145.3	145.2
115°	170.1	170.1	170.1	170.1	170.1	170.0	169.9	169.7	169.5	169.4	169.3
117.5°	193.0	193.1	193.2	193.3	193.3	193.3	193.2	193.0	193.0	192.8	192.5
120°	208.4	208.7	209.1	209.4	209.7	209.7	209.5	209.2	209.0	208.7	208.3
122.5°	224.3	224.4	224.5	224.6	224.8	224.8	224.7	224.5	224.5	224.4	224.0
125°	247.7	247.7	247.7	247.7	247.7	247.7	247.6	247.5	247.5	247.4	247.2
127.5°	269.1	269.3	269.6	269.8	270.1	270.2	270.0	269.8	269.8	269.6	269.4
130°	284.0	284.3	284.6	284.8	285.1	285.2	285.2	285.2	285.2	285.2	285.0
132.5°	299.3	299.5	299.7	299.9	300.1	300.1	300.1	300.0	300.0	299.9	299.7
135°	319.5	320.0	320.6	321.1	321.6	321.8	321.8	321.8	321.8	321.8	321.7
137.5°	341.6	341.8	342.0	342.2	342.5	342.7	342.9	343.0	343.1	343.3	343.0
140°	356.2	356.4	356.5	356.7	356.9	357.0	357.0	357.0	357.0	357.0	356.9
142.5°	369.6	369.8	370.0	370.1	370.3	370.4	370.3	370.2	370.1	370.1	370.1
145°	388.2	388.6	388.9	389.3	389.6	389.8	389.9	389.9	390.0	390.1	390.0
147.5°	406.7	407.0	407.4	407.9	408.3	408.5	408.4	408.3	408.3	408.2	408.1
150°	417.8	418.2	418.5	418.9	419.2	419.4	419.4	419.4	419.4	419.4	419.4
152.5°	428.4	428.7	428.9	429.1	429.3	429.5	429.5	429.6	429.6	429.7	429.9
155°	444.8	444.8	444.8	444.8	444.8	444.7	444.6	444.5	444.4	444.4	444.7
157.5°	458.5	458.3	458.2	458.1	457.9	457.8	457.8	457.8	457.7	457.7	458.0
160°	466.7	466.6	466.5	466.4	466.3	466.2	466.1	466.1	466.0	465.9	466.1
162.5°	474.2	473.9	473.6	473.5	473.2	473.0	472.9	472.9	472.8	472.7	473.2
165°	484.1	483.9	483.6	483.4	483.1	482.9	482.8	482.6	482.4	482.2	482.8
167.5°	491.9	491.5	491.2	490.9	490.4	490.3	490.3	490.3	490.3	490.3	490.9
170°	496.3	495.8	495.4	495.0	494.6	494.4	494.5	494.6	494.6	494.7	495.2
172.5°	499.4	499.0	498.7	498.3	497.9	497.7	497.7	497.8	497.8	497.8	498.4
175°	503.7	503.3	502.8	502.4	502.0	501.7	501.6	501.5	501.4	501.4	502.0
177.5°	505.1	504.7	504.4	504.0	503.7	503.5	503.5	503.5	503.5	503.5	504.0
180°	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5



TEST NUMBER: P333058-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	11.9	11.8	11.7	11.8	12.0	12.2	12.4	12.6
90°	9.6	10.2	10.7	11.0	11.2	11.4	11.5	11.7
92.5°	16.1	16.4	16.7	16.9	17.0	17.1	17.2	17.3
95°	30.1	30.4	30.7	30.8	30.8	30.8	30.8	30.8
97.5°	47.5	47.9	48.1	48.3	48.3	48.3	48.3	48.3
100°	60.0	60.2	60.4	60.4	60.4	60.4	60.4	60.4
102.5°	73.3	73.5	73.8	74.0	74.0	74.0	74.1	74.2
105°	93.4	93.7	93.9	94.2	94.5	94.7	95.0	95.2
107.5°	115.1	115.4	115.6	115.7	115.7	115.7	115.6	115.6
110°	129.6	129.4	129.2	129.2	129.5	129.8	130.0	130.3





TEST NUMBER: P333058-935

CATALOG NUMBER: S124RDIW-S795D470U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	145.2	145.1	145.1	145.1	145.2	145.2	145.3	145.3
115°	169.2	169.1	169.0	168.9	168.8	168.8	168.7	168.6
117.5°	192.3	191.9	191.7	191.4	191.2	191.1	190.9	190.7
120°	207.8	207.4	207.0	206.9	207.1	207.2	207.4	207.6
122.5°	223.8	223.4	223.2	222.8	222.6	222.2	221.9	221.6
125°	247.0	246.8	246.7	246.5	246.3	246.2	246.0	245.8
127.5°	269.2	269.1	268.9	268.7	268.6	268.5	268.4	268.2
130°	284.8	284.6	284.5	284.2	283.9	283.5	283.2	282.8
132.5°	299.5	299.4	299.2	299.0	298.9	298.8	298.6	298.5
135°	321.5	321.3	321.2	321.0	320.7	320.5	320.2	319.9
137.5°	342.8	342.6	342.3	342.2	342.3	342.3	342.4	342.5
140°	356.8	356.7	356.6	356.5	356.5	356.4	356.3	356.2
142.5°	370.1	370.1	370.1	370.0	370.0	370.0	370.0	370.0
145°	389.9	389.9	389.8	389.6	389.3	389.1	388.8	388.6
147.5°	408.0	407.9	407.9	407.9	407.8	407.7	407.6	407.5
150°	419.4	419.4	419.4	419.4	419.3	419.2	419.1	419.0
152.5°	430.2	430.3	430.6	430.5	430.3	430.1	429.9	429.6
155°	445.1	445.4	445.7	445.7	445.4	445.1	444.7	444.4
157.5°	458.2	458.5	458.7	458.7	458.5	458.1	457.9	457.5
160°	466.4	466.7	466.9	466.8	466.4	466.0	465.5	465.0
162.5°	473.6	474.2	474.6	474.6	474.2	473.7	473.3	472.9
165°	483.3	483.8	484.3	484.4	484.1	483.7	483.4	483.0
167.5°	491.4	491.9	492.4	492.4	491.9	491.4	490.8	490.3
170°	495.8	496.3	496.8	496.7	496.1	495.5	494.9	494.3
172.5°	499.0	499.6	500.2	500.2	499.6	498.9	498.3	497.7
175°	502.6	503.2	503.8	503.8	503.2	502.6	502.0	501.4
177.5°	504.5	505.0	505.5	505.4	504.9	504.4	503.8	503.3
180°	504.5	504.5	504.5	504.5	504.5	504.5	504.5	504.5

(END OF REPORT)