

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332720-930

Luminaire Tested: **S124DIW-S350D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332720-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D470U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2562.6 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332720-930

CATALOG NUMBER: S124DIW-S350D470U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332720-930

CATALOG NUMBER: S124DIW-S350D470U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25	21
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332720-930

CATALOG NUMBER: S124DIW-S350D470U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.4	1.8
10°-20°	127.8	5.0
20°-30°	188.1	7.3
30°-40°	218.7	8.5
40°-50°	218.7	8.5
50°-60°	191.3	7.5
60°-70°	142.1	5.5
70°-80°	80.7	3.1
80°-90°	24.7	1.0
90°-100°	31.5	1.2
100°-110°	93.3	3.6
110°-120°	158.4	6.2
120°-130°	208.9	8.2
130°-140°	234.6	9.2
140°-150°	230.5	9.0
150°-160°	193.9	7.6
160°-170°	129.0	5.0
170°-180°	45.2	1.8
0°-30°	361.2	14.1
0°-40°	579.9	22.6
0°-60°	989.8	38.6
0°-90°	1237.3	48.3
90°-120°	283.3	11.1
90°-150°	957.2	37.4
90°-180°	1325.0	51.7
0°-180°	2562.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	1	5	8	10	11	3
95°	22	25	28	29	29	25
105°	86	86	88	89	90	91
115°	161	161	160	160	160	159
125°	235	235	234	234	233	209
135°	303	305	305	304	303	234
145°	368	369	369	369	368	230
155°	421	421	421	422	421	194
165°	458	457	457	459	457	129
175°	477	475	475	477	475	45
180°	478	478	478	478	478	



TEST NUMBER: P332720-930

CATALOG NUMBER: S124DIW-S350D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.2	8.4	8.5	8.6	8.7	8.8	8.9	8.9	9.0	9.0	9.1
90°	1.1	2.0	2.9	3.8	4.7	5.5	6.2	6.8	7.5	8.2	8.6
92.5°	7.9	9.0	9.9	11.0	12.1	12.8	13.3	13.7	14.2	14.6	14.9
95°	22.2	22.9	23.6	24.4	25.1	25.8	26.3	26.9	27.5	28.0	28.3
97.5°	38.7	39.3	39.9	40.5	41.1	41.7	42.4	43.0	43.7	44.4	44.7
100°	51.7	52.0	52.3	52.7	53.1	53.6	54.3	55.0	55.8	56.5	56.7
102.5°	65.3	65.5	65.6	65.7	65.9	66.3	66.9	67.6	68.2	69.0	69.1
105°	86.1	86.2	86.3	86.3	86.4	86.6	86.9	87.2	87.6	87.9	88.1
107.5°	107.9	107.9	108.1	108.2	108.3	108.4	108.4	108.4	108.5	108.5	108.8
110°	122.6	122.8	122.9	123.1	123.3	123.4	123.3	123.2	123.1	123.0	122.9



TEST NUMBER: P332720-930

CATALOG NUMBER: S124DIW-S350D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.0	138.0	138.1	138.1	138.2	138.1	137.9	137.8	137.6	137.5	137.5
115°	161.1	161.1	161.1	161.1	161.1	161.0	160.9	160.7	160.5	160.4	160.3
117.5°	182.8	182.9	183.0	183.0	183.0	183.0	183.0	182.8	182.7	182.5	182.3
120°	197.3	197.6	198.0	198.3	198.6	198.6	198.4	198.1	197.9	197.6	197.2
122.5°	212.4	212.5	212.6	212.7	212.9	212.9	212.8	212.6	212.5	212.5	212.1
125°	234.6	234.6	234.6	234.6	234.6	234.6	234.5	234.4	234.3	234.2	234.1
127.5°	254.8	255.0	255.3	255.5	255.8	255.8	255.7	255.5	255.4	255.3	255.1
130°	269.0	269.2	269.5	269.7	269.9	270.0	270.0	270.0	270.0	270.0	269.9
132.5°	283.4	283.6	283.8	284.0	284.1	284.2	284.1	284.1	284.1	284.0	283.8
135°	302.6	303.0	303.5	304.0	304.5	304.8	304.8	304.8	304.8	304.8	304.6
137.5°	323.4	323.7	323.8	324.1	324.3	324.5	324.7	324.8	324.9	325.1	324.8
140°	337.3	337.5	337.6	337.8	337.9	338.0	338.0	338.0	338.0	338.0	337.9
142.5°	350.0	350.2	350.3	350.5	350.7	350.7	350.7	350.6	350.5	350.4	350.4
145°	367.6	367.9	368.3	368.6	368.9	369.1	369.2	369.2	369.3	369.4	369.3
147.5°	385.1	385.4	385.8	386.2	386.6	386.8	386.7	386.6	386.6	386.5	386.5
150°	395.7	396.0	396.3	396.6	397.0	397.1	397.1	397.1	397.1	397.1	397.1
152.5°	405.7	405.9	406.1	406.3	406.5	406.7	406.7	406.8	406.8	406.9	407.1
155°	421.2	421.2	421.2	421.2	421.2	421.1	421.0	420.9	420.9	420.8	421.1
157.5°	434.1	434.0	433.9	433.7	433.6	433.5	433.5	433.5	433.4	433.4	433.7
160°	441.9	441.8	441.7	441.6	441.6	441.5	441.4	441.3	441.2	441.2	441.4
162.5°	449.0	448.7	448.5	448.3	448.1	447.9	447.8	447.8	447.7	447.6	448.1
165°	458.4	458.2	458.0	457.7	457.5	457.3	457.1	457.0	456.8	456.6	457.1
167.5°	465.8	465.5	465.1	464.8	464.4	464.2	464.2	464.3	464.3	464.3	464.8
170°	469.9	469.5	469.1	468.7	468.3	468.1	468.2	468.3	468.4	468.5	469.0
172.5°	472.9	472.5	472.2	471.9	471.5	471.3	471.3	471.4	471.4	471.4	472.0
175°	477.0	476.5	476.1	475.7	475.3	475.1	475.0	474.9	474.8	474.7	475.3
177.5°	478.3	477.9	477.6	477.3	477.0	476.8	476.8	476.8	476.8	476.8	477.3
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7



TEST NUMBER: P332720-930

CATALOG NUMBER: S124DIW-S350D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	9.2	9.3	9.5	9.5	9.5	9.5	9.6	9.6
90°	9.1	9.6	10.1	10.4	10.6	10.8	10.9	11.1
92.5°	15.2	15.5	15.8	16.0	16.1	16.2	16.3	16.4
95°	28.5	28.8	29.0	29.2	29.2	29.2	29.2	29.2
97.5°	45.0	45.3	45.6	45.7	45.7	45.7	45.7	45.7
100°	56.8	57.0	57.2	57.2	57.2	57.2	57.2	57.2
102.5°	69.4	69.6	69.9	70.0	70.0	70.1	70.2	70.3
105°	88.5	88.7	88.9	89.2	89.4	89.7	89.9	90.2
107.5°	109.0	109.3	109.5	109.6	109.6	109.6	109.5	109.5
110°	122.7	122.5	122.4	122.4	122.6	122.9	123.1	123.4





TEST NUMBER: P332720-930

CATALOG NUMBER: S124DIW-S350D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.5	137.4	137.4	137.4	137.5	137.5	137.5	137.5
115°	160.2	160.1	160.0	160.0	159.9	159.8	159.7	159.6
117.5°	182.1	181.7	181.5	181.2	181.1	180.9	180.8	180.6
120°	196.8	196.4	196.0	195.9	196.1	196.2	196.4	196.6
122.5°	211.9	211.6	211.3	211.0	210.8	210.4	210.1	209.9
125°	233.9	233.7	233.6	233.4	233.3	233.1	232.9	232.8
127.5°	254.9	254.8	254.6	254.5	254.4	254.2	254.1	254.0
130°	269.7	269.5	269.4	269.1	268.8	268.5	268.2	267.8
132.5°	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.7
135°	304.4	304.3	304.1	303.9	303.7	303.5	303.2	303.0
137.5°	324.6	324.4	324.2	324.1	324.2	324.2	324.2	324.3
140°	337.9	337.8	337.7	337.6	337.5	337.5	337.4	337.3
142.5°	350.4	350.4	350.4	350.3	350.3	350.3	350.3	350.3
145°	369.2	369.2	369.1	368.9	368.7	368.4	368.2	367.9
147.5°	386.4	386.3	386.3	386.2	386.1	386.0	386.0	385.9
150°	397.1	397.1	397.1	397.1	397.1	397.0	396.9	396.8
152.5°	407.3	407.5	407.7	407.6	407.5	407.2	407.1	406.8
155°	421.4	421.8	422.1	422.1	421.8	421.4	421.1	420.8
157.5°	433.9	434.1	434.4	434.4	434.1	433.8	433.6	433.3
160°	441.6	441.9	442.1	442.1	441.6	441.2	440.8	440.3
162.5°	448.5	449.0	449.4	449.4	449.0	448.6	448.2	447.8
165°	457.6	458.1	458.6	458.7	458.4	458.0	457.7	457.4
167.5°	465.3	465.8	466.3	466.3	465.8	465.3	464.7	464.2
170°	469.4	469.9	470.4	470.3	469.8	469.2	468.6	468.1
172.5°	472.5	473.1	473.6	473.6	473.0	472.5	471.9	471.3
175°	475.9	476.5	477.0	477.0	476.5	475.9	475.3	474.7
177.5°	477.8	478.2	478.7	478.6	478.1	477.6	477.0	476.5
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7

(END OF REPORT)