

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333062-935

Luminaire Tested: **S124RDIW-S795D770U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333062-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D770U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5058.2 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333062-935

CATALOG NUMBER: S124RDIW-S795D770U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333062-935

CATALOG NUMBER: S124RDIW-S795D770U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P333062-935

CATALOG NUMBER: S124RDIW-S795D770U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.4	2.2
10°-20°	313.3	6.2
20°-30°	452.4	8.9
30°-40°	512.8	10.1
40°-50°	495.2	9.8
50°-60°	411.8	8.1
60°-70°	284.4	5.6
70°-80°	144.1	2.8
80°-90°	39.4	0.8
90°-100°	54.5	1.1
100°-110°	161.4	3.2
110°-120°	274.0	5.4
120°-130°	361.3	7.1
130°-140°	405.8	8.0
140°-150°	398.7	7.9
150°-160°	335.4	6.6
160°-170°	223.1	4.4
170°-180°	78.1	1.5
0°-30°	878.1	17.4
0°-40°	1390.9	27.5
0°-60°	2297.9	45.4
0°-90°	2765.9	54.7
90°-120°	489.9	9.7
90°-150°	1655.8	32.7
90°-180°	2292.0	45.3
0°-180°	5058.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	2	9	14	18	19	5
95°	38	44	49	50	50	43
105°	149	150	152	154	156	158
115°	279	278	277	277	276	275
125°	406	406	405	404	403	362
135°	523	527	527	526	524	405
145°	636	638	639	638	636	398
155°	728	728	728	730	728	335
165°	793	791	790	793	791	223
175°	825	822	821	825	821	78
180°	826	826	826	826	826	



TEST NUMBER: P333062-935

CATALOG NUMBER: S124RDIW-S795D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.2	16.3	15.2	14.3	13.3	12.8	12.9	12.9	13.0	13.1	13.1
90°	1.9	3.4	5.1	6.6	8.2	9.6	10.7	11.8	12.9	14.0	14.9
92.5°	13.7	15.5	17.2	19.0	20.8	22.1	22.9	23.7	24.5	25.3	25.8
95°	38.3	39.6	40.9	42.2	43.5	44.6	45.5	46.6	47.6	48.6	49.0
97.5°	67.0	68.0	69.1	70.0	71.0	72.2	73.4	74.5	75.7	76.8	77.3
100°	89.5	90.1	90.6	91.2	91.7	92.6	93.9	95.2	96.5	97.8	98.1
102.5°	113.0	113.2	113.4	113.7	113.9	114.6	115.7	116.9	118.0	119.2	119.7
105°	148.9	149.0	149.2	149.3	149.5	149.8	150.4	150.9	151.5	152.1	152.5
107.5°	186.6	186.8	186.9	187.1	187.3	187.4	187.5	187.6	187.7	187.8	188.1
110°	212.2	212.4	212.8	213.0	213.3	213.4	213.2	213.1	212.9	212.8	212.5



TEST NUMBER: P333062-935

CATALOG NUMBER: S124RDIW-S795D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	238.8	238.8	238.8	238.9	238.9	238.8	238.6	238.3	238.1	237.8	237.8
115°	278.6	278.6	278.6	278.6	278.6	278.4	278.2	277.9	277.6	277.3	277.2
117.5°	316.2	316.3	316.4	316.5	316.7	316.6	316.4	316.2	316.0	315.8	315.3
120°	341.2	341.8	342.3	342.9	343.5	343.5	343.2	342.8	342.3	341.9	341.1
122.5°	367.3	367.6	367.7	368.0	368.2	368.2	368.1	367.8	367.6	367.5	367.0
125°	405.8	405.8	405.8	405.8	405.8	405.7	405.5	405.4	405.3	405.1	404.8
127.5°	440.7	441.1	441.5	442.0	442.4	442.5	442.2	442.0	441.8	441.6	441.3
130°	465.2	465.6	466.1	466.5	466.9	467.1	467.1	467.1	467.1	467.1	466.8
132.5°	490.3	490.6	490.9	491.2	491.5	491.6	491.5	491.4	491.3	491.1	490.9
135°	523.4	524.2	525.0	525.9	526.8	527.2	527.2	527.2	527.2	527.2	526.9
137.5°	559.4	559.8	560.2	560.6	561.0	561.3	561.5	561.7	562.0	562.2	561.8
140°	583.4	583.7	584.0	584.3	584.5	584.7	584.7	584.7	584.7	584.7	584.5
142.5°	605.4	605.7	606.0	606.2	606.6	606.7	606.5	606.4	606.3	606.1	606.1
145°	635.8	636.4	637.0	637.6	638.1	638.4	638.6	638.8	638.9	639.0	638.9
147.5°	666.0	666.7	667.4	668.0	668.7	669.0	668.9	668.7	668.7	668.6	668.4
150°	684.4	684.9	685.5	686.1	686.6	687.0	687.0	687.0	687.0	687.0	687.0
152.5°	701.8	702.1	702.5	702.8	703.2	703.4	703.4	703.6	703.7	703.8	704.1
155°	728.5	728.5	728.5	728.5	728.5	728.4	728.2	728.1	728.0	727.9	728.4
157.5°	751.0	750.7	750.4	750.2	749.9	749.8	749.8	749.8	749.8	749.7	750.1
160°	764.3	764.1	764.0	763.9	763.7	763.5	763.4	763.3	763.1	763.0	763.4
162.5°	776.5	776.2	775.8	775.4	775.1	774.8	774.6	774.6	774.4	774.2	775.0
165°	793.1	792.6	792.2	791.8	791.3	791.0	790.7	790.4	790.1	789.8	790.7
167.5°	805.6	805.1	804.5	803.9	803.3	803.0	803.1	803.1	803.1	803.1	804.0
170°	812.9	812.1	811.4	810.7	810.0	809.7	809.9	810.0	810.1	810.3	811.1
172.5°	817.9	817.3	816.7	816.1	815.5	815.3	815.3	815.4	815.4	815.4	816.4
175°	825.0	824.2	823.5	822.9	822.2	821.7	821.6	821.4	821.3	821.1	822.2
177.5°	827.2	826.7	826.1	825.6	825.0	824.8	824.8	824.8	824.8	824.8	825.5
180°	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2



TEST NUMBER: P333062-935

CATALOG NUMBER: S124RDIW-S795D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	13.1	13.1	13.1	13.2	13.4	13.7	13.9	14.1
90°	15.8	16.6	17.5	18.0	18.3	18.6	18.9	19.2
92.5°	26.3	26.9	27.4	27.7	27.9	28.1	28.2	28.4
95°	49.4	49.9	50.3	50.5	50.5	50.5	50.5	50.5
97.5°	77.8	78.4	78.9	79.1	79.1	79.1	79.1	79.1
100°	98.3	98.6	98.9	99.0	99.0	99.0	99.0	99.0
102.5°	120.0	120.5	120.8	121.1	121.2	121.3	121.4	121.6
105°	152.9	153.3	153.8	154.2	154.6	155.1	155.5	155.9
107.5°	188.6	188.9	189.3	189.5	189.5	189.5	189.4	189.4
110°	212.2	212.0	211.6	211.7	212.2	212.6	213.0	213.4





TEST NUMBER: P333062-935

CATALOG NUMBER: S124RDIW-S795D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	237.7	237.6	237.6	237.6	237.7	237.8	237.9	238.0
115°	277.1	276.9	276.7	276.6	276.5	276.4	276.2	276.0
117.5°	314.9	314.4	313.8	313.5	313.2	312.9	312.6	312.4
120°	340.4	339.8	339.1	338.8	339.1	339.4	339.7	339.9
122.5°	366.4	366.0	365.5	365.0	364.5	363.9	363.5	363.0
125°	404.6	404.3	404.0	403.7	403.5	403.1	402.9	402.6
127.5°	441.0	440.7	440.4	440.1	440.0	439.7	439.5	439.3
130°	466.6	466.2	466.0	465.5	465.0	464.4	463.8	463.3
132.5°	490.6	490.3	490.0	489.7	489.6	489.3	489.0	488.9
135°	526.6	526.3	526.1	525.7	525.3	524.9	524.4	524.0
137.5°	561.5	561.1	560.8	560.6	560.7	560.8	560.9	560.9
140°	584.4	584.3	584.1	584.0	583.8	583.7	583.6	583.4
142.5°	606.1	606.1	606.1	606.1	606.0	606.0	606.0	605.9
145°	638.8	638.6	638.4	638.2	637.7	637.3	636.9	636.5
147.5°	668.3	668.2	668.0	668.0	667.8	667.7	667.5	667.4
150°	687.0	687.0	687.0	686.9	686.7	686.6	686.5	686.3
152.5°	704.5	704.8	705.2	705.2	704.8	704.5	704.0	703.7
155°	729.0	729.5	730.1	730.1	729.5	729.0	728.4	727.9
157.5°	750.5	751.0	751.4	751.4	750.9	750.4	749.9	749.4
160°	763.9	764.3	764.7	764.6	763.9	763.1	762.4	761.7
162.5°	775.8	776.5	777.3	777.3	776.6	775.9	775.2	774.5
165°	791.5	792.4	793.2	793.4	792.8	792.2	791.7	791.1
167.5°	804.9	805.6	806.5	806.5	805.6	804.8	803.9	803.0
170°	812.0	812.9	813.7	813.6	812.6	811.7	810.6	809.7
172.5°	817.3	818.3	819.2	819.2	818.2	817.3	816.2	815.3
175°	823.1	824.1	825.1	825.1	824.1	823.1	822.2	821.1
177.5°	826.3	827.1	827.9	827.9	826.9	826.0	825.1	824.2
180°	826.2	826.2	826.2	826.2	826.2	826.2	826.2	826.2

(END OF REPORT)