

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332726-930

Luminaire Tested: **S124DIW-S350D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332726-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D770U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3408.9 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332726-930

CATALOG NUMBER: S124DIW-S350D770U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332726-930

CATALOG NUMBER: S124DIW-S350D770U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30				
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	26				
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	22				
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19				
5	66	54	47	41	59	50	43	38	41	35	31	32	28	25	24	22	20	16				
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14				
7	56	44	36	31	51	40	33	28	33	28	24	26	22	20	20	17	15	13				
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11				
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10				
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332726-930

CATALOG NUMBER: S124DIW-S350D770U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.4	1.3
10°-20°	127.8	3.7
20°-30°	188.1	5.5
30°-40°	218.7	6.4
40°-50°	218.7	6.4
50°-60°	191.3	5.6
60°-70°	142.1	4.2
70°-80°	80.7	2.4
80°-90°	25.6	0.8
90°-100°	51.6	1.5
100°-110°	152.9	4.5
110°-120°	259.5	7.6
120°-130°	342.1	10.0
130°-140°	384.2	11.3
140°-150°	377.6	11.1
150°-160°	317.6	9.3
160°-170°	211.3	6.2
170°-180°	74.0	2.2
0°-30°	361.2	10.6
0°-40°	579.9	17.0
0°-60°	989.8	29.0
0°-90°	1238.2	36.3
90°-120°	463.9	13.6
90°-150°	1567.9	46.0
90°-180°	2171.0	63.7
0°-180°	3408.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	2	8	13	17	18	3
95°	36	42	46	48	48	40
105°	141	142	144	146	148	150
115°	264	264	263	262	261	260
125°	384	384	384	382	381	342
135°	496	499	499	498	496	383
145°	602	604	605	604	603	377
155°	690	690	689	691	689	317
165°	751	749	748	751	749	212
175°	781	778	778	781	778	74
180°	782	782	782	782	782	



TEST NUMBER: P332726-930

CATALOG NUMBER: S124DIW-S350D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.4	8.6	8.8	9.0	9.3	9.5	9.6	9.8	9.9	10.1	10.3
90°	1.8	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1
92.5°	13.0	14.7	16.3	18.0	19.7	21.0	21.7	22.4	23.2	24.0	24.5
95°	36.3	37.5	38.7	39.9	41.2	42.2	43.1	44.1	45.1	46.0	46.4
97.5°	63.4	64.4	65.4	66.3	67.3	68.3	69.5	70.5	71.7	72.7	73.2
100°	84.7	85.3	85.8	86.3	86.8	87.7	88.9	90.2	91.4	92.6	92.9
102.5°	107.0	107.2	107.4	107.6	107.9	108.5	109.6	110.7	111.8	112.9	113.3
105°	141.0	141.1	141.3	141.4	141.5	141.9	142.4	142.9	143.5	144.0	144.4
107.5°	176.7	176.8	177.0	177.2	177.3	177.5	177.6	177.7	177.7	177.8	178.1
110°	200.9	201.1	201.5	201.7	201.9	202.0	201.9	201.8	201.6	201.5	201.2



TEST NUMBER: P332726-930

CATALOG NUMBER: S124DIW-S350D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.1	226.1	226.2	226.2	226.2	226.2	225.9	225.7	225.4	225.2	225.2
115°	263.8	263.8	263.8	263.8	263.8	263.7	263.4	263.2	262.9	262.6	262.4
117.5°	299.4	299.5	299.6	299.7	299.9	299.8	299.6	299.5	299.2	299.1	298.6
120°	323.1	323.7	324.2	324.7	325.3	325.3	325.0	324.6	324.2	323.8	323.0
122.5°	347.8	348.1	348.2	348.5	348.7	348.7	348.5	348.3	348.1	348.0	347.5
125°	384.3	384.3	384.3	384.3	384.3	384.2	384.0	383.9	383.8	383.6	383.4
127.5°	417.3	417.7	418.1	418.5	418.9	419.0	418.7	418.6	418.3	418.2	417.8
130°	440.5	440.9	441.3	441.7	442.1	442.3	442.3	442.3	442.3	442.3	442.1
132.5°	464.2	464.6	464.8	465.1	465.5	465.5	465.4	465.3	465.2	465.0	464.8
135°	495.6	496.4	497.2	498.0	498.8	499.2	499.2	499.2	499.2	499.2	499.0
137.5°	529.7	530.1	530.4	530.8	531.2	531.5	531.7	531.9	532.1	532.4	532.0
140°	552.4	552.7	553.0	553.3	553.5	553.7	553.7	553.7	553.7	553.7	553.5
142.5°	573.2	573.6	573.8	574.1	574.4	574.5	574.3	574.2	574.1	574.0	574.0
145°	602.1	602.6	603.2	603.7	604.2	604.5	604.7	604.9	605.0	605.1	605.0
147.5°	630.6	631.3	631.9	632.6	633.2	633.5	633.4	633.2	633.2	633.1	632.9
150°	648.1	648.6	649.1	649.7	650.2	650.5	650.5	650.5	650.5	650.5	650.5
152.5°	664.6	664.9	665.2	665.5	665.9	666.0	666.1	666.3	666.3	666.4	666.8
155°	689.8	689.8	689.8	689.8	689.8	689.7	689.6	689.5	689.3	689.3	689.7
157.5°	711.1	710.9	710.6	710.4	710.1	710.0	710.0	710.0	710.0	709.9	710.3
160°	723.7	723.6	723.4	723.3	723.2	723.0	722.9	722.8	722.6	722.5	722.9
162.5°	735.3	735.0	734.6	734.3	733.9	733.7	733.5	733.4	733.3	733.1	733.9
165°	751.0	750.6	750.2	749.7	749.3	749.0	748.7	748.4	748.2	747.9	748.7
167.5°	762.9	762.4	761.8	761.2	760.7	760.3	760.4	760.4	760.4	760.5	761.3
170°	769.7	769.0	768.3	767.7	767.0	766.7	766.9	767.0	767.1	767.3	768.1
172.5°	774.5	774.0	773.4	772.8	772.3	772.0	772.0	772.1	772.1	772.1	773.1
175°	781.2	780.5	779.8	779.2	778.5	778.1	778.0	777.8	777.7	777.6	778.5
177.5°	783.3	782.9	782.3	781.8	781.2	781.0	781.0	781.0	781.0	781.0	781.7
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332726-930

CATALOG NUMBER: S124DIW-S350D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	10.4	10.5	10.7	10.8	10.8	10.9	11.0	11.0
90°	14.9	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	24.9	25.4	25.9	26.3	26.4	26.6	26.7	26.9
95°	46.8	47.2	47.6	47.8	47.8	47.8	47.8	47.8
97.5°	73.7	74.2	74.7	74.9	74.9	74.9	74.9	74.9
100°	93.1	93.4	93.7	93.8	93.8	93.8	93.8	93.8
102.5°	113.7	114.1	114.4	114.6	114.8	114.9	115.0	115.1
105°	144.8	145.2	145.6	146.0	146.4	146.8	147.2	147.7
107.5°	178.6	178.9	179.3	179.4	179.4	179.4	179.4	179.4
110°	201.0	200.7	200.4	200.5	200.9	201.3	201.7	202.1





TEST NUMBER: P332726-930

CATALOG NUMBER: S124DIW-S350D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.1	225.0	225.0	225.0	225.1	225.2	225.3	225.3
115°	262.4	262.2	262.0	262.0	261.8	261.7	261.5	261.4
117.5°	298.2	297.7	297.2	296.9	296.6	296.3	296.0	295.8
120°	322.4	321.7	321.1	320.8	321.1	321.4	321.6	321.9
122.5°	347.0	346.6	346.1	345.6	345.1	344.6	344.2	343.7
125°	383.1	382.9	382.5	382.3	382.0	381.7	381.5	381.2
127.5°	417.6	417.4	417.0	416.8	416.6	416.4	416.1	416.0
130°	441.8	441.5	441.2	440.8	440.3	439.8	439.2	438.7
132.5°	464.6	464.3	464.0	463.7	463.6	463.3	463.1	462.9
135°	498.6	498.4	498.1	497.8	497.4	497.0	496.6	496.2
137.5°	531.7	531.3	531.0	530.8	530.9	531.0	531.1	531.2
140°	553.4	553.3	553.1	553.0	552.9	552.7	552.6	552.4
142.5°	574.0	573.9	573.9	573.9	573.8	573.8	573.8	573.7
145°	604.9	604.7	604.5	604.3	603.9	603.5	603.1	602.7
147.5°	632.8	632.8	632.6	632.5	632.3	632.3	632.1	631.9
150°	650.5	650.5	650.5	650.4	650.3	650.1	650.0	649.9
152.5°	667.1	667.4	667.7	667.7	667.4	667.1	666.7	666.3
155°	690.3	690.8	691.4	691.4	690.8	690.3	689.7	689.3
157.5°	710.7	711.1	711.5	711.5	711.0	710.6	710.1	709.6
160°	723.3	723.7	724.1	724.0	723.3	722.6	721.9	721.3
162.5°	734.6	735.3	736.1	736.1	735.4	734.7	734.1	733.4
165°	749.5	750.3	751.1	751.3	750.7	750.2	749.7	749.1
167.5°	762.1	762.9	763.7	763.7	762.9	762.1	761.2	760.3
170°	768.9	769.7	770.5	770.5	769.5	768.6	767.6	766.7
172.5°	774.0	774.9	775.8	775.8	774.8	773.9	772.9	772.0
175°	779.4	780.4	781.3	781.3	780.4	779.4	778.5	777.6
177.5°	782.4	783.2	784.0	783.9	783.0	782.2	781.3	780.5
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4

(END OF REPORT)